

Signaling Control	E1968A	E6701C	E6701D	E6701E/T	E6701F	E6701G	E6701H	E6701I	E6701J	E6701K
Dynamic/Fixed/Ext dynamic Allocation	Yes/No/No	Yes/Yes/No	Yes/Yes/Yes	Yes/Yes/Yes	Yes/Yes/Yes	Yes	Yes	Yes	Yes	Yes
EGPRS2A 16QAM/32QAM DL, 16QAM UL	Opt 104	No	No	No	No	No	Yes	Yes	Yes	Yes
E-EDGE FANR in Test Mode	Opt 104	No	No	No	No	No	Yes	Yes	Yes	Yes
E-EDGE Downlink Dual Carrier	Opt 104	No	No	No	No	Yes	Yes	Yes	Yes	Yes
E-EDGE Reduced TTI	Opt 104	No	No	No	No	Yes	Yes	Yes	Yes	Yes
E-EDGE SSN and Time-based Fast Ack/Nack Response (FANR)	Opt 104	No	No	No	No	Yes	Yes	Yes	Yes	Yes
(E)GPRS Asymmetrical SRB Loopback	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes
EGPRS Flexible Timeslots	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes
EGPRS One Phase Access	No	No	No	No	No	No	Yes	Yes	Yes	Yes
Enhanced GAN (E6708A)	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes
E-OTD	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Extended UL TBF, Delayed DL TBF, and TBF Re-establish	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Extended SMS User Settings	Opt 409	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Fading with Baseband Studio	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes
Fast Switch Lab Application Call/Session Continuity	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes
Final Block Polling	No	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes
Forced Uplink Retransmission	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Frequency Hopping	No	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
GPRS Packet Paging	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes
GSM Repeated Paging	No	No	No	No	No	No	No	No	No	Yes
GSM Extended Paging	No	No	No	No	No	No	No	No	No	Yes
GSM Coordinated Paging	No	No	No	No	No	No	No	No	No	Yes
GPRS Point-to-point SMS	Opt 409	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
GSM Bell broadcast (CB) SMS	Opt 409	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
GSM Enhanced Power Control (EPC)	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes
GSM Point-to-point SMS	Opt 409	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Incremental Redundancy	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Independent DL/UL GPRS Coding Schemes	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes

Signaling Control	E1968A	E6701C	E6701D	E6701E/T	E6701F	E6701G	E6701H	E6701I	E6701J	E6701K
Infrequent Network Events	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Inter-RAT 2-Box 2G	No	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes
DTM <-> 3G PSD + Voice HO										
2G to LTE FDD/TDD HO	No	No	No	No	No	No	No	Yes	Yes	Yes
CM Service Reject	No	No	No	No	No	No	No	No	Yes	Yes
2G SRVCC Voice Capability (8960 and PXT)	No	No	No	No	No	No	No	No	Yes	Yes
2G SMS Over SGs (8960 and PXT)	No	No	No	No	No	No	No	No	Yes	Yes
IPv6 Support	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes
Two DUT IPv4 P-CSCF Addresses in Protocol Configuration Option (PCO)	No	No	No	No	No	No	No	No	Yes	Yes
LAU/RAU Reject	No	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes
Option to Ignore UE Requests	No	No	No	No	No	No	No	Yes	Yes	Yes
Mobile-originated Call Control	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes
Multi-page Custom CB SMS	Opt 409	No	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Multiple PDP Contexts	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Network Initiated Time Zone (NITZ)	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes
Network PDP Context Sisable	No	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes
Packet Flow Context	No	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes
Power Reduction Mode	No	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes
PSI Scheduling	No	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes
Push-to-talk Over Cellular (PTT or PoC)	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Repeating SACCH and FACCH	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes
RLC/MAC Window Size	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Robust Header Compression (RoHC)	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes
RRLP RR Header	No	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes
Secondary PDP Contexts	No	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes
Service Interoperability	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Alpha/Gamma Aetting	No	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes
Settable BEP_Period2	No	No	No	No	No	Yes	Yes	Yes	Yes	Yes
Settable Network Mode of Operation (NMO)	No	No	No	No	Yes	Yes	Yes	Yes	Yes	Yes

