

Installation
Guide

Keysight
i1000D Series
In-Circuit Test
Systems
(U9401B/U9403A/U9405A)

Installing software
release v3.60pa
for Win7 32 bit

This document describes the steps to install the i1000 Software and the necessary hardware drivers onto the i1000 test system.

Supported Products

U9401B – i1000D Press Down ICT System

U9403A – Keysight Mini ICT System

U9405 – i1000D Small Foot Print ICT System
(Inline/Offline)

Installation Procedure

This full installation takes approximately 20mins to complete it.

The installer will automatically prompt to install the Medalist i1000 software and also the additional 3rd party software required.


Two installation files are provided with this release:

Installers	Description
i1000_v03.60pa_x32_installer.exe	32-bit installer that can be used on both Win7 32bit testhead and test development workstation.


Uninstall Cypress EZ-USB Driver (**U9405A i1000 SFP ONLY**)

For **U9405A i1000 SFP Win7 32bit controller**, please follow the steps below to remove the old “Cypress EZ-USB” driver before starting the i1000 v.3.60pa software installation.

1. Launch Windows “Device Manager”




2. Right-Click on “Cypress EZ-USB Sample Device”




and then select the “Uninstall”.


3. Select “Delete the driver software for this device”, then click the “OK” button.



4. Click “Action” – “Scan for hardware changes”




5. A Device named “EZ-USB FX2” will be under “Other devices”.



Install i1000 System Software


1. Execute the appropriate installer by double clicking on the file. Click “Yes” if the pop-up window shown as below:




The setup Installer for the software will be launched and the Welcome screen will be displayed as above. Click “Next >”.




2. Read the License Agreement. Select “I accept the agreement” option and click “Next >”.




3. The next screen shows a list of plug-in modules that will be installed or copied into the “C:\Agilent_i1000” folder after the installation completes and also other 3rd party software which is required for the i1000 software to function correctly. Click “Next >”.



4. Select option “Create a desktop icon”. Click “Next >”.




5. Click **“Install”**. Installer will commence the installation with the Medalist i1000 software.




NOTE:


Click “Install this driver software anyway” if you see the pop-up Security check window shown as below.




6. USB Host driver will be installed automatically. Click “Next >”.




7. Select "I accept the terms of the license agreement". Click "Next >".




8. Click "Install". This may take a few minutes.




9. Click **“Finish”** when the installation is completed.




10. The SCPI Host software will be installed automatically. Click “Next >” to continue the installation.




11. Select “Typical” and then Click “Next >”.



12. Click **“Install”**.




13. Click **“Finish”**.




14. The Installer will then proceed to install Microsoft®.NET 4.5.1 Framework.




15. Read the license terms. Select “I have read and accept the license terms” option and click “Install”. If there is already an existing copy of the software installed on the system, the installer will prompt to select “Repair” or “Remove” option. Select “Repair” to allow the installer to verify the files.




16. .NET installation will commence. This installation may take a few minutes.



17. Click “Finish” when installation is completed.




18. Click “Next >” to install IO Libraries.




19. Select “Agree” and then click “Next >”.




20. Select “Typical” and then click “Next >”




21. Click “Next >”.




22. Click “Install”.



23. Click “Finish” to end the installation. The computer will restart to complete the installation.



24. Click “Finish” to complete the Keysight IO library installation after system reboot.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at:
www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
(BP-09-23-14)

This information is subject to change without notice.
© Keysight Technologies, 2018
Published in Malaysia, 24th July 2018
www.keysight.com

© Keysight Technologies 2018
Edition 1, July 2018
Document number: U9401-96009



U9401-96009

