

DP5700 Series DC Power Supplies

Power without Compromise

The DP5700 Series DC power supplies are compact and secure, designed to maximize space efficiency in lab and production environments. The 1.5 kW models are half-rack width, while the 3.4 kW models are full-rack width, both only 1U high. A removable SD memory supports sensitive security applications, enabling safe movement of test equipment between confidential spaces. Flexible system scaling is possible by connecting up to four units in parallel to increase current or two in series to increase voltage. Validate complex power devices faster, in less space, with no compromise on performance.



Figure 1. Keysight DP5700 Series DC power supplies

Performance Specifications

Model	1.5 kW Models		3.4 kW Models	
	DP5721A – DP5726A	DP5728A – DP5736A	DP5741AS/L/H – DP5746AS/L/H	DP5748AS/L/H – DP5756AS/L/H
DC Power Ratings				
Voltage	0 – 60 V	0 – 600 V	0 – 60 V	0 – 600 V
Current	0 – 150 A	0 – 19 A	0 – 340 A	0 – 42 A
Power	1.5 kW – 1.52 kW	1.5 kW – 1.56 kW	3,360 W – 3,400 W	3,360 W – 3,450 W
Output Ripple and Noise ¹				
CV rms	6 mV – 7 mV	8 mV – 100 mV	8 mV – 15 mV	15 mV – 100 mV
CV peak-to-peak	50 mV – 60 mV	75 mV – 500 mV	75 mV – 80 mV	80mV– 480mV
Load Regulation				
Voltage	3 mV – 8 mV	10 mV – 62 mV	6 mV – 11 mV	13 mV – 65 mV
Current	10 mA – 35 mA	5.52 mA – 8.8 mA	44.8 mA – 272 mA	4.48 mA – 33.6 mA
Programming and Measurement Accuracy				
Voltage ²	≤ 5 mV – ≤ 30 mV	≤ 40 mV – ≤ 300 mV	5 mV – 30 mV	40 mV – 300 mV
Current ^{2, 3}	0.1% + 50mA – 0.1% + 300mA	0.1% + 5.2mA – 0.1% + 38mA	0.1% + 112mA – 0.1% + 680mA	0.1% + 11.2mA – 0.1% + 84mA
Transient Response				
Recovery time	≤ 1ms ⁴	≤ 1ms – ≤ 2ms ⁴	1ms ⁵	1ms – 2ms ⁵
Setting band	0.05 V – 0.3 V	0.4 V – 3 V	0.05 V – 0.3 V	0.4 V – 3 V
Programming Resolution				
Voltage	0.2 mV – 1.2 mV	1.6 mV – 12 mV	0.2 mV – 1.2 mV	1.6 mV – 12 mV
Current	0.625 mA – 3.75 mA	0.065 mA – 0.475 mA	1.12 mA – 6.8 mA	0.112 mA – 0.85 mA
Measurement Resolution				
Voltage	1.1 mV – 1.2 mV	1.6 mV – 12 mV	1.1 mV – 1.2 mV	1.6 mV – 12 mV
Current	1.14 mA – 15 mA	0.104 mA – 1.5 mA	1.12 mA – 1.7 mA	0.168 mA – 1.68 mA
Command Response Time				
Command response time	< 25 ms			

1. From 5 Hz to 1 MHz for rms noise; from 20 Hz to 20 MHz for peak-to-peak noise.

2. Accuracy specifications are warranted at 23° C ±5° C

3. Percent of programmed value + offset.

4. Time for output voltage to recover within 1% of its rated output for a load change from 10% to 90% and 90% to 10% of its rated output current

5. Time for output voltage to recover within 0.5% of its rated output for a load change from 10% to 90% and 90% to 10% of its rated output current

More Information: www.keysight.com/find/DP5700

Compact, Secure, High-Density Power

Intuitive user interface and connectivity options

- LED indicators
- Rotary knobs and buttons
- LAN (LXI), USB, and GPIB
- Easy-to-use Standard Commands for Programmable Instruments (SCPI) with IVI-COM drivers
- Analog programming and monitoring

Flexible configuration and system integration

- Front, side, and rear air vents
- Stackable without airflow obstruction
- Parallel connections
- Universal AC input
- Programmable internal resistance for source impedance simulation
- Built-in arbitrary generator for custom waveform creation
- Adjustable slew rate control for optimized voltage transitions

Protective features

- Lockable controls to prevent accidental parameter changes
- Overtemperature Protection (OTP)
- Overcurrent Protection (OCP)
- Overvoltage Protection (OVP)
- Undervoltage Protection (UVP)
- Protection window for sensitive load circuitry
- Removable SD card option

Accessories

Part Number	Size	Description
DP5701A	1U half rack	Rack-mount slide kit for 1.5 kW models
N5740A	1U full rack	Rack-mount slide kit for 3.4 kW models
DP5705A		Removable SD memory option

For More Information

For more information on the Keysight DP5700 Series DC power supplies, please visit

www.keysight.com/find/DP5700

To find a distributor near you, visit:

www.keysight.com/find/distributors

Keysight enables innovators to push the boundaries of engineering by quickly solving design, emulation, and test challenges to create the best product experiences. Start your innovation journey at www.keysight.com.

This information is subject to change without notice. © Keysight Technologies, 2025, Published in USA, October 28, 2025, 3125-1392.EN