

# N99xxA/B/C/D FieldFox Handheld Analyzer Quick Start Guide

Congratulations, with this instrument you will achieve fast, accurate results with confidence.

## CAUTION

### IMPORTANT!

FULLY charge the FieldFox battery before using the FieldFox for the first time (The battery will be fully charged in about 4 hours).

When setting FieldFox on a surface, it is recommended to operate it with the kickstand open. The cooling is less effective when FieldFox is placed lying down flat on the instrument's back.

- For questions and to learn more, download the N9927-90020 (A-Series), N9938-90006 (B-Series), N9915-90020 (C-Series), or N9918-90020 (D-Series) User's Guide at [www.keysight.com/find/fieldfox](http://www.keysight.com/find/fieldfox).

## Step 2

Insert the supplied AC/DC adapter (15 VDC) into the power connector and into an electrical outlet (AC/DC adapter is not shown).

- N9912A and N9923A models: The power connector is located on the RIGHT side, under the middle-hinged cover.
- All other models: The power connector is located on the LEFT side, under the bottom-hinged cover. Refer to the next page for details.

## Step 1

Install the battery pack into the FieldFox battery compartment. The battery door is located on the lower-right side of the FieldFox (Press and slide the door down to open). For more, see Step 3.



## Step 3

Extend the kickstand and press the power button.



A/B/C-Series Power Connector Location



D-Series Power Connector Location

