

Release Notes

Keysight Technologies

BenchVue Software

BV0001B Digital Multimeter Control App

2021.1 Version Information

Released Date:	August 20, 2021
Requirements categories	
PC operating system & hardware:	Windows 10: 64-bit (version 1809 or later)
	Processor: Intel Core i5 (or equivalent)
	RAM: 8 GB
	Storage Drive: 900MB free space
	Display resolution: 1920x1080 recommended
Current List of BenchVue Enabled Keysight Instruments:	www.keysight.com/find/benchvueinstruments
File Name:	PathWaveBenchVueDMM-2021-1-Setup.exe

Notable changes

- Implemented Digitizer functionality for instruments 34465A, 34470A, 34460A and 34461A.
- Supports histogram chart type for both data logger & digitizer functionalities.
- List of supported instrument models can be viewed under the “?” dropdown menu in application.
- Defects & Bug fixes.

NOTE: Mobile app and test flow features are not available in current version of standalone software.

2021 Version Information

Released Date:	March 15, 2021
Requirements categories	
PC operating system & hardware:	Windows 10: 64-bit (version 1809 or later)
	Processor: Intel Core i5 (or equivalent)
	RAM: 8 GB
	Storage Drive: 900MB free space
	Display resolution: 1920x1080 recommended
Current List of BenchVue Enabled Keysight Instruments:	www.keysight.com/find/benchvueinstruments
File Name:	PathWaveBenchVueDMM_2021_Setup.exe

Notable changes

- Standalone Pathwave Benchvue platform (Does not require installation of prerequisite software)
- New Graphical User Interface
- Added support for EDU34450A

NOTE: Mobile app and test flow features are not available in current version of standalone software.

2019 Update 1 Version Information

Released Date:	September 20, 2019
Requirements categories	
PC operating system & hardware:	<p>Windows 10: 32-bit and 64-bit (Professional, Enterprise, Education, Home versions)</p> <p>Windows 8, 8.1: 32-bit and 64-bit (Professional, Enterprise, Core)</p> <p>Processor: 1 GHz or faster (2 GHz or greater recommended)</p> <p>RAM: 1 GB (32-bit) or 2 GB (64-bit) (3 GB or greater recommended)</p> <p>Interfaces: USB, GPIB, LAN, RS-232</p> <p>Display resolution: 1280x1024 minimum recommended for single instrument view (higher resolution recommended for multiple instrument view)</p>
Mobile Devices: (for companion BenchVue Mobile app)	<p>Apple iPhone, iPad, iPod Touch all models; iOS 9.0 and later.</p> <p>Android phone and tablets; Android 4.0.3 and later.</p>
Current List of BenchVue Enabled Keysight Instruments:	www.keysight.com/find/benchvueinstruments
File Name:	BenchVueDMM_2019_Update1.0.exe

Notable changes

- Fixed a defect when digitizing for international date/time formats
- Fixed a laughing defect for certain instruments when Windows locale is set to France
- Datalog graphing defect addressed where certain intervals were not graphed correctly
- Test Flow defect fix to display NPLC/Apertures values correctly
- Defects fixed for stability and usability

2019 Version Information

Released Date:	September 19, 2019
Requirements categories	
PC operating system & hardware:	<p>Windows 10: 32-bit and 64-bit (Professional, Enterprise, Education, Home versions)</p> <p>Windows 8, 8.1: 32-bit and 64-bit (Professional, Enterprise, Core)</p> <p>Windows 7: SP1 and later 32-bit and 64-bit (Professional, Enterprise, Ultimate, Home Basic, Home Premium)</p> <p>Processor: 1 GHz or faster (2 GHz or greater recommended)</p> <p>RAM: 1 GB (32-bit) or 2 GB (64-bit) (3 GB or greater recommended)</p> <p>Interfaces: USB, GPIB, LAN, RS-232</p> <p>Display resolution: 1280x1024 minimum recommended for single instrument view (higher resolution recommended for multiple instrument view)</p>
Mobile Devices: (for companion BenchVue Mobile app)	<p>Apple iPhone, iPad, iPod Touch all models; iOS 9.0 and later.</p> <p>Android phone and tablets; Android 4.0.3 and later.</p>
Current List of BenchVue Enabled Keysight Instruments:	www.keysight.com/find/benchvueinstruments
File Name:	BenchVueDMM_2019.exe

Notable changes

- Fixed a defect where digitizing timing for <1 NPLC wasn't reported correctly
- Fixed digitizing for 34470A that now have digitizing as a standard option
- Defects fixed for stability and usability

2018 Version Information

Released Date:	August 2, 2018
Requirements categories	
PC operating system & hardware:	<p>Windows 10: 32-bit and 64-bit (Professional, Enterprise, Education, Home versions)</p> <p>Windows 8, 8.1: 32-bit and 64-bit (Professional, Enterprise, Core)</p> <p>Windows 7: SP1 and later 32-bit and 64-bit (Professional, Enterprise, Ultimate, Home Basic, Home Premium)</p> <p>Processor: 1 GHz or faster (2 GHz or greater recommended)</p> <p>RAM: 1 GB (32-bit) or 2 GB (64-bit) (3 GB or greater recommended)</p> <p>Interfaces: USB, GPIB, LAN, RS-232</p> <p>Display resolution: 1280x1024 minimum recommended for single instrument view (higher resolution recommended for multiple instrument view)</p>
Mobile Devices: (for companion BenchVue Mobile app)	<p>Apple iPhone, iPad, iPod Touch all models; iOS 7.0 and later.</p> <p>Android phone and tablets; Android 4.0.3 and later.</p>
Current List of BenchVue Enabled Keysight Instruments:	www.keysight.com/find/benchvueinstruments
File Name:	BenchVueDMMsetup_2018.exe

Notable changes

- Get screenshots for TrueVolt DMMs
- Faster instrument interaction for a more responsive interface
- Improved Graphing based on user feedback
- Fixed a defect where full speed digitizing wasn't supported correctly
- Defects fixed for stability and usability

2017 Version Information

Released Date:	March 29, 2017
Requirements categories	
PC operating system & hardware:	<p>Windows 10: 32-bit and 64-bit (Professional, Enterprise, Education, Home versions)</p> <p>Windows 8, 8.1: 32-bit and 64-bit (Professional, Enterprise, Core)</p> <p>Windows 7: SP1 and later 32-bit and 64-bit (Professional, Enterprise, Ultimate, Home Basic, Home Premium)</p> <p>Processor: 1 GHz or faster (2 GHz or greater recommended)</p> <p>RAM: 1 GB (32-bit) or 2 GB (64-bit) (3 GB or greater recommended)</p> <p>Interfaces: USB, GPIB, LAN, RS-232</p> <p>Display resolution: 1280x1024 minimum recommended for single instrument view (higher resolution recommended for multiple instrument view)</p>
Mobile Devices: (for companion BenchVue Mobile app)	<p>Apple iPhone, iPad, iPod Touch all models; iOS 7.0 and later.</p> <p>Android phone and tablets; Android 4.0.3 and later.</p>
Current List of BenchVue Enabled Keysight Instruments:	www.keysight.com/find/benchvueinstruments
File Name:	BenchVueDMMsetup_v2017.exe

Notable changes

- BenchVue DMM app now requires a license
- App includes Test Flow automation and Command Expert blocks
- Support for new license terms
- Defects fixed for stability and usability

NOTE: Previous versions of this app are not compatible with the BenchVue 2017 Platform software. For compatibility, use the older versions of the BenchVue Platform software (3.7 and earlier). Download and install the older version of this app from the Apps tab within your version of BenchVue.