

Keysight Technologies

BenchVue LCR Meter Control and Automation App

2019 Version Information

Released Date:	Feb 28, 2019
Requirements categories	
PC operating system and hardware:	<p>Windows 10: 32-bit and 64-bit (Professional, Enterprise, Education, Home versions)</p> <p>Windows 8, 8.1: 32-bit and 64-bit (Professional, Enterprise, Core)</p> <p>Windows 7: SP1 and later 32-bit and 64-bit (Professional, Enterprise, Ultimate, Home Basic, Home Premium)</p> <p>Processor: 1 GHz or faster (2 GHz or greater recommended)</p> <p>RAM: 1 GB (32-bit) or 2 GB (64-bit) (3 GB or greater recommended)</p> <p>Interfaces: USB, GPIB, LAN, RS-232</p> <p>Display resolution: 1280x1024 minimum recommended for single instrument view (higher resolution recommended for multiple instrument view)</p>
Current List of BenchVue Enabled Keysight Instruments:	www.keysight.com/find/benchvueinstruments
File Name:	BenchVueLCRSetup_2019.exe

Notable changes

- Initial release.
- Connect and control your LCR meters to quickly view measurements, configure sweeps, build automated tests, and log data for analysis.
- Test Flow enabled for easy automation of instrument setup, measurements, and data acquisition