

BV0014B BenchVue LCR Meter Control & Automation App

2023 Version Information

Release Date:	Apr 22, 2023
Operating System:	Microsoft Windows 10 (64-bit, version 1809 or later)
System Requirements:	Processor: Intel Core i5 (or equivalent) RAM: 8GB Storage Drive: 900MB free space Display Resolution: 1920x1080 recommended
Supported Instruments:	www.keysight.com/find/BenchVueInstruments
Release Type:	Major Update Release
File Name:	BenchVueLCR-2023-Setup.exe

New Features and Enhancements

- Defects fixed for stability, usability, and performance enhancements.

Previous Release Name

2019 Version Information

Released Date:	Feb 28, 2019
Requirements categories	
PC operating system & hardware:	<p>Windows 10: 32-bit and 64-bit (Professional, Enterprise, Education, Home versions)</p> <p>Windows 8, 8.1: 32-bit and 64-bit (Professional, Enterprise, Core)</p> <p>Windows 7: SP1 and later 32-bit and 64-bit (Professional, Enterprise, Ultimate, Home Basic, Home Premium)</p> <p>Processor: 1 GHz or faster (2 GHz or greater recommended)</p> <p>RAM: 1 GB (32-bit) or 2 GB (64-bit) (3 GB or greater recommended)</p> <p>Interfaces: USB, GPIB, LAN, RS-232</p> <p>Display resolution: 1280x1024 minimum recommended for single instrument view (higher resolution recommended for multiple instrument view)</p>
Mobile Devices: (for companion BenchVue Mobile app)	<p>Apple iPhone, iPad, iPod Touch all models; iOS 7.0 and later.</p> <p>Android phone and tablets; Android 4.0.3 and later.</p>
Current List of BenchVue Enabled Keysight Instruments:	www.keysight.com/find/benchvueinstruments
File Name:	BenchVueLCRsetup_2019.exe

Notable changes

- Initial release.
- Connect and control your LCR meters to quickly view measurements, configure sweeps, build automated tests, and log data for analysis.
- Test Flow enabled for easy automation of instrument setup, measurements, and data acquisition