
E5920B – Agilent .720m Rack Cabinet (14U)

Technical Data

Product Number
Agilent E5920B

Store your equipment efficiently and attractively

The E5920B is a .720m, quartz gray rack cabinet. The table height of this rack is an ideal solution for your desk side racking needs.

There is no rear or front door available for this rack.

Features

- Quartz gray color
- 14EIA units EIA vertical rack space
- Snap-on/off side panels
- 2 inch, heavy-duty casters
- Solid base
- Shipping cost included in price
- Racks come fully assembled and ready for equipment installation

Specifications

- **Material:** Cold-rolled steel
- **Weight:** 51 kg (113 lbs.)
- **Color:** Quartz gray
- **Depth:** 765 mm (30.1 in)
- **Height:** 720 mm (28.4 in)
- **Width:** 600 mm (23.6 in)
- **Internal height:** 622.3mm (24.5 in)
- **Internal width:** 450 mm (17.7 in)
- **Internal depth:** 710 mm (27.9 in)

- **Maximum load capacity:** 180 kg (400 lbs)

Installation

This rack is delivered pre-assembled with all standard features.

Tools required for setup:

- T25 torx screwdriver, for removal of stabilizing shipping panels and rear door L-shaped slam guard.
- Adjustable wrench or 9/16" crescent wrench, for removal of rack from the pallet.

Standards

Conforms to the Electronic Industries Association (EIA) standard 310-D. It is a type A cabinet with 14U of vertical mounting space. One 'U' is equal to 44.45 mm (1.75").

What changed

Replaces: E5920A

- Color changed from parchment white to quartz gray



Refer to the Enclosures website for additional product information:

<http://enclosures.agilent.com>

Warranty

Three year replacement