

N9910X FIELDFOX ACCESSORIES MATRIX

FIELDFOX ANALYZER ACCESSORIES

Level	Item	Description
1	N9910X-800	T-Calibration kit, 3-in-1, open, short, load, DC to 6 GHz, Type-N(m), 50 ohm
2	1250-3607	Termination Type-N male open-short-load 50-Ohm Tee DC to 6 GHz
1	N9910X-801	T-Calibration kit, 3-in-1, open, short, load, DC to 6 GHz, Type-N(f), 50 ohm
2	1250-3605	Termination Type-N female open-short-load 50 ohm Tee DC to 6 GHz
1	N9910X-802	T-Calibration kit, 3-in-1, open, short, load, DC to 6 GHz, 7/16 DIN(m)
2	1250-3606	Termination 7/16 male open-short-load 50 ohm Tee DC to 6 GHz
1	N9910X-803	T-Calibration kit, 3-in-1, open, short, load, DC to 6 GHz, 7/16 DIN(f)
2	1250-3608	Termination 7/16 female open-short-load 50 ohm Tee DC to 6 GHz
1	N9910X-810	Rugged phase-stable cable, Type-N (m) to Type-N (m), 5 ft or 1.5 m
2	N9912-60012	Rugged Phase stable Coaxial RF cable, 60 inches, 8 GHz, N(m) to N(m)
1	N9910X-811	Rugged phase-stable cable, Type-N (m) to Type-N (f), 5 ft or 1.5 m
2	N9912-60011	Rugged Phase stable Coaxial RF cable, 60 inches, 8 GHz, N(m) to N(f)
1	N9910X-812	Rugged phase-stable cable, Type-N (m) to Type-N (m), 12 ft or 3.6 m
2	N9912-60014	Rugged Phase stable Coaxial RF cable, 12 ft, 8 GHz, N(m) to N(m)
1	N9910X-813	Rugged phase-stable cable, Type-N (m) to Type-N (f), 12 ft or 3.6 m
2	N9912-60013	Rugged Phase stable Coaxial RF cable, 12 ft, 8 GHz, N(m) to N(f)
1	N9910X-820	Antenna, directional, multiband, 800-2500 MHz, 10 dBi
2	0960-2781	ANTENNA-DIRECTIONAL 800-2500MHZ 10dB MULTI-BAND
2	8120-8862	Cable Assembly - Coaxial Type-N
1	N9910X-821	Antenna, telescopic whip, 70 MHz - 1 GHz
2	1250-0780	Adapter-Coaxial straight Female-BNC Male-N
2	0960-2775	Antenna Telescopic 70-1000MHz 10W 50 Ohm
1	N9910X-843	Coaxial adapter, Type-N(m) to 7/16 DIN(f)
2	1250-3543	Adapter-Coaxial Straight Male-N-Type Female-Jack 50-Ohm 7.5GHz
1	N9910X-845	Adapter kit - Type-N(f) to 7/16(f),Type-N(f) to 7/16(m),Type-N(f) to Type-N(f)
2	1250-2908	Adapter-Coaxial straight Male-7/16 Female-Type N
2	1250-2810	Adapter-Coaxial straight Female-7/16 Female-N
2	1250-3422	Adapter-Coaxial STR N-FEM N-FEM
1	N9910X-860	Fixed attenuator, 40 dB, 100 W, DC-3 GHz, Type-N(m) to Type-N(f)
2	0955-1458	Attenuator, fixed, 40 db 100W N-type
1	N9910X-861	Fixed attenuator, 40 dB, 50 W, DC-8.5 GHz, Type-N(m) to Type-N(f)
2	0955-1979	U-WAVE ATTENUATOR 8.5GHz MAX 50.0WATT N
1	N9910X-870	Extra battery
2	- N9910-60001	Tested Li-Ion Battery
1	N9910X-872	External battery charger
2	0950-5719	Power Supply Battery charger 60W 2-Output 3A 6.89X4.89X2.30-in Black
1	N9910X-873	AC / DC adapter (except for US / Canada / Europe / China)
2	0950-5824	Power Supply External AC-DC Adapter Switching 90W 1-Output 15V 6A Level 6
1	N9910X-874	External bias-tee, 2.5 MHz to 6 GHz, 1 W, 0.5 A
2	8121-1310	Cable Assembly-Coaxial RG/58C 50-Ohm straight BNC-Male to straight BNC-Male 36-in-LG
2	1250-3197	Adapter-Coaxial straight Female-BNC MALE-Banana Male
2	8710-2586	BNC Female to Minigator Test Clip Brass Nickel Plated
2	0955-2077	Microwave Bias-Tee 6GHz MAX 1 Watt
1	N9910X-880	Extra soft carrying case with backpack and shoulder strap
2	N9910-80001	Softcase, with backpack and shoulder strap
1	N9910X-881	Hard transit case
2	N9910-80004	Hard Transit Case
1	N9910X-884	Extra FieldFox shoulder strap
2	N9910-80003	Shoulder strap, instrument
1	N9910X-890	Extra Printed Users Guide (N9912A)
2	N9912-90001	Users guide, printed
1	N9910X-891	Extra Printed reference guide (N9912A)
2	N9912-90002	Quick Reference Guide, printed

1	N9910X-814	Rugged phase-stable cable, Type-N (m) to 7/16 (m), 60 inch or 1.5 m
2	N9912-60024	Rugged phase stable coaxial RF cable, 60 inches, 6 GHz, N(M) to 7/16 (M)
1	N9910X-815	Rugged phase-stable cable, Type-N (m) to 7/16 (m), 12 ft or 3.6 m
2	N9912-60025	Rugged phase stable coaxial RF cable, 144 inches, 6GHz, N(M) to 7/16 (M)
1	N9910X-816	Rugged phase-stable cable, Type-N (m) to Type-N (f), 3.28 ft or 1 m
2	N9923-60005	Cable Assy, N(m) to N(f), 1 meter with enhanced strain relief
1	N9910X-817	Rugged phase-stable cable, Type-N (m) to Type-N (m), 3.28 ft or 1 m
2	N9923-60006	Cable Assy, N(m) to N(m), 1 meter with enhanced strain relief
1	N9923X-890	Extra printed users guide
2	N9923-90001	Users guide, printed
1	N9910X-875	DC charger and adapter
2	0950-5156	POWER-SUPPLY-AUTO Charger Continuous 60-WATT 1-Output
1	N9910X-846	Coaxial adapter, 50 ohm type-N(m) to 75 ohm type-N(f)
2	1250-0597	Adapter-Coaxial straight Male-N 50 Ohm Female-N 75 Ohm
1	N9910X-877	AC / DC adapter for US / Canada / Europe / China only
2	0950-5824	Power Supply External AC-DC Adapter Switching 90W 1-Output 15V 6A Level 6

FIELDFOX MISCELLANEOUS ACCESSORIES

Level	Item	Description
1	N9910X-712	Trigger/Reference-In Cable, SMA (m) to BNC (f), 1 m or 3.28 ft
2	8121-2052	Cable Assembly-Coaxial A03/A13 Female-BNC to Male-SMA 1000mm-LG
1	N9910X-713	Bias-tee power cable, SMB (f) to BNC (m), 1 m or 3.28 ft
2	8121-2118	Cable Assembly-Coaxial A01/A07 50-Ohm Straight BNC Male to SMB Female 1000mm-LG
1	N9910X-886	Torque wrench, 17 mm, 90 N-cm (8in-lb)
2	8710-2789	Tool-Torque Wrench 17mm-open end
1	N9910X-876	Battery-rechargeable Li-Ion 10.8V 6.8A-HR
2	1420-0930	Battery-rechargeable Li-Ion 10.8V 6.8A-HR

FIELDFOX CABLES

Level	Item	Description
1	N9910X-709	Rugged phase-stable cable, 3.5 mm(f) to 3.5 mm(f), 26.5 GHz, 3.28 ft or 1 m
2	N9927-60025	Rugged Phase stable Cable Assembly-Coaxial 50-ohm 3.5mm (F) to 3.5mm (F), 1 meter LG
1	N9910X-708	Rugged phase-stable cable, 3.5 mm(m) to 3.5 mm(f), 26.5 GHz, 3.28 ft or 1 m
2	N9927-60024	Rugged Phase stable Cable Assembly-Coaxial 50-ohm 3.5mm (M) to 3.5mm (F), 1 meter LG
1	N9910X-705	Rugged phase-stable cable, Type-N(m) to TNC(m), 13 GHz, 5 ft or 1.5 m
2	N9927-60021	Rugged Phase stable Cable Assembly-Coaxial 50-ohm N (M) to TNC (M), 1.5 meter LG
1	N9910X-704	Rugged phase-stable cable, Type-N(m) to TNC(f), 13 GHz, 5 ft or 1.5 m
2	N9927-60020	Rugged Phase stable Cable Assembly-Coaxial 50-ohm N (M) to TNC (F), 1.5 meter LG
1	N9910X-701	Rugged phase-stable cable, Type-N(m) to Type-N(m), 18 GHz, 3.28 ft or 1 m
2	N9927-60017	Rugged Phase stable Cable Assembly-Coaxial 50-ohm N (M) to N (M), 1 meter LG
1	N9910X-700	Rugged phase-stable cable, Type-N(m) to Type-N(f), 18 GHz, 3.28 ft or 1 m
2	N9927-60016	Rugged Phase stable Cable Assembly-Coaxial 50-ohm N (M) to N (F), 1 meter LG
1	N9910X-714	Rugged phase-stable cable, 2.4 mm (f) to 2.4 mm (m), 50 GHz, 3.28 ft or 1 m
2	8121-2808	Rugged Phase stable Cable Assembly-Coaxial 50-Ohm 2.4mm-Jack 2.4mm-Plug 1m-LG
1	N9910X-715	Rugged phase-stable cable, 2.4 mm (f) to 2.4 mm (f), 50 GHz, 3.28 ft or 1 m
2	8121-2807	Rugged Phase stable Cable Assembly-Coaxial 50-Ohm 2.4mm-Jack 2.4mm-Jack 1m-LG
1	N9910X-716	Rugged phase-stable cable, Type-N(m) to Type-N(m), 18 GHz, 2 ft or 0.61 m
2	N9927-60068	Rugged Phase stable Cable Assembly-Coaxial 50-ohm N (M) to N (M), 2 FT LG

FIELDFOX ANTENNAS

Level	Item	Description
1	N9910X-825	Antenna, GPS, active
2	0960-3016	GPS active Antenna 1578MHz-MAX 4dBic 50-Ohm SMA Connector
1	N9910X-824	Antenna, cellular narrowband, PCS 1850 to 1990 MHz
2	1535-5249	Yagi Antenna 50-Ohm 1990MHz-MAX 500W
1	N9910X-823	Antenna, cellular narrowband, 824 to 869 MHz
2	1535-5248	Antenna-Yagi 7-Elements 824-896MHz 50-Ohm 500W Type N-Connector
1	N9910X-822	Directional antenna, 600 MHz to 9 GHz
2	0960-3241	Antenna-Handheld Log Periodic 50-Ohm 600MHz-9GHz

FIELDFOX ADAPTERS

Level	Item	Description
1	N9910X-852	Coaxial adapter, Type-N (m) to Type-N (f), 18 GHz
2	1250-3879	Adapter-Coaxial straight APN N-Male APN N-Female 50Ohm 18GHz
1	N9910X-851	Coaxial adapter, Type-N (f) to Type-N (f), 18 GHz
2	1250-3881	Adapter-Coaxial Straight Female-N Female-N 50-Ohm 18GHz
1	N9910X-850	Coaxial adapter, Type-N (m) to Type-N (m), 18 GHz
2	1250-1475	Adapter-Coaxial straight Male-N Male-N 50 Ohm
1	N9910X-849	Coaxial adapter, Type-N (f) to 3.5 mm (m), 18 GHz
2	1250-1750	Adapter-Coaxial straight Female-APC-N Male-APC-3.5
1	N9910X-848	Coaxial adapter, Type-N (f) to 3.5 mm (f), 18 GHz
2	1250-1745	Coaxial Adapter-Type N (female) to 3.5 mm (female)
1	N9910X-847	Adapter kit, Type-N (f) to TNC (m) adapter, Type-N (f) to TNC (f) adapter, 11 GHz
2	1250-3890	Adapter-Coaxial Straight N-Female TNC-Female 50-Ohm 11GHz-MAX
2	1250-3889	Adapter-Coaxial straight Female-N to Male-TNC 50-Ohm 11GHz
1	11904D	2.4 mm female to 2.92 mm male adapter
2	- 11904D-FG	2.4 mm female to 2.92 mm male adapter
1	N9910X-856	Coaxial adapter 2.4 mm (f) to 2.4 mm (f), 50 GHz
2	1250-2188	Adapter-Coaxial straight Female-2.4 mm Female-2.4 mm
1	N9910X-857	Coaxial adapter 2.4 mm (f) to 2.92 mm/K (f), 40 GHz
2	1250-3782	Adapter-Coaxial Straight 2.92 mm Jack 2.40 mm Jack 50-Ohm 40GHz
1	N9910X-601	Coaxial adapter, 2.4 mm NMD (f) to Type-N (f), 18 GHz
2	1250-4246	Adapter-Coaxial Straight NMD Jack-2.4mm Jack-Type N 50-Ohm 18GHz-MAX
1	N9910X-602	Coaxial adapter, 2.4 mm NMD (f) to 2.92 mm (f), 40 GHz
2	1250-4248	Adapter-Coaxial Straight NMD Jack-2.4mm Jack-2.92mm 50-Ohm 40GHz-MAX
1	N9910X-603	Coaxial adapter, 2.4 mm NMD (f) to 3.5 mm (f), 26.5 GHz
2	1250-4247	Adapter-Coaxial Straight NMD Jack-2.4mm Jack-3.5mm 50-Ohm 26.5GHz-MAX