

1180CZ Testmobile Scope Cart



Add mobility to your instruments

The Keysight Technologies, Inc. 1180CZ testmobile scope cart provides convenient mobility of test equipment to make it readily available when needed and effectively extend the amount of lab bench space. Allows several operators to cost effectively share expensive equipment.

Features

- Ergonomic design, test equipment is operator-accessible whether seated or standing
- Heavy-duty casters make moving instruments easy
- Includes a steel buckle and nylon strap to secure instruments to the cart
- Attractive quartz gray color
- Tilt tray adjusts 30-plus degrees for viewing comfort

Specifications

- Material: Cold-rolled steel
- Weight: 25.9 kg (57 lbs)
- Color: Quartz gray
- Casters: 101 mm (4 in) diameter
- Tilt tray load capacity: 29.5 kg (65 lbs)
- Total load capacity: 59 kg (130 lbs)
- Tilt tray width: 457 mm (18 in)
- Tilt tray depth: 457 mm (18 in)

Installation

The 1180CZ is shipped virtually assembled except for its handle and casters. Place the handle in the rear top of the cart and secure with screws provided. Insert the casters in the corner holes on the underside of the cart. Attach the nylon strap on the slots of the instrument tray and thread through buckle.

Tools required for installation:



- Torx T25 screwdriver

What you get in the box

- Scope cart assembly with tray
- Torx T25 screwdriver
- Tubular handle
- Four casters
- All mounting hardware
- Nylon strap with steel buckle
- Installation instructions

What changed

- Color changed from parchment white to quartz gray



Related products

1181BZ Keysight testmobile System cart

Optional accessory

35183B Work surface

Replacement parts

1530-2054 Tie-down assembly strap
1492-0134 Caster, swivel with brake

Learn more at: www.keysight.com

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

