

Keysight Technologies

E4463B

Front Door, 2.0 m Plexiglas

Data Sheet

Attractively secure rackmounted equipment

An attractive, transparent, smoke-colored Plexiglas front door gives a consistent appearance to the rack and is lockable to control access to the instruments and peripherals mounted in the rack.

Features

- Can be installed to hinge on either the right or the left side for maximum flexibility
- Provides 64 mm (2.52 in) of space to accommodate instrument front panels
- Does not interfere with access to the optional master power switch
- Attractive quartz gray color
- All mounting hardware included

Specifications

- Material: Cold-rolled steel
- Weight: 10.8 kg (24 lbs)
- Color: Quartz gray
- Height: 1825 mm (71.9 in)
- Depth: 60 mm (2.4 in)
- Width: 513 mm (20.2 in)

Installation

Attach the hinges and the latch to the front door assembly. Remove the side panels from the rack, attach the hinge brackets, and attach the front door to the rack. Reinstall the side panels.

Tools required for installation:

- Torx T25 screwdriver
- Crescent wrench for M3 nut
- Crescent wrench for M5 or 10-32 x 0.5 in nut

What you get in the box

- Door assembly with Plexiglas window
- Mounting hardware
- Installation instructions

What changed


Replaces: E4462A

- Color changed from parchment white to quartz gray

Compatibility

The E4463B can be used with:

E3662B	Keysight 1.6 m rack
--------	---------------------



Related products


Other door sizes are available.

E4460B	Keysight 1.1 m front door
E4461B	Keysight 1.3 m front door
E4462B	Keysight 1.6 m front door

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries: www.keysight.com/find/contactus (BP-9-7-17)



www.keysight.com/go/quality
Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

http://www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/enclosures

