

Keysight Technologies

Big5 Bench *Plus* Promotion: Get A Complimentary IP67 Industrial Handheld DMM

Simply purchase any eligible Keysight Bench test instrument and claim the sturdy U1282A, designed to help you stay productive, efficient and safe while you focus on tasks at hand.

PROMOTION START DATE: October 1, 2017

END DATE: March 31, 2018

PROMOTION CODE: 6.023

Availability:

- Worldwide except China, Hong Kong and Taiwan.

Promotion conditions:

- Customers must purchase a new Keysight Bench product (listed in the table).
- Must be purchased from an authorized Keysight channel partner.
- Purchases of premium used equipment are not eligible.
- Complimentary U1282A handheld DMM comes with batteries and user guides in multiple languages.
- Options can be purchased separately with the qualifying bench purchase.
- Keysight Technologies reserves the right to modify or discontinue this offering during the promotional period.
- If qualifying equipment in the original order is returned for any reason, the complimentary U1282A handheld DMM must also be returned.

The complimentary **Keysight U1282A Industrial Handheld Digital Multimeter** is your sturdy companion for measurements on the go. The DMM is IP67 certified (water and dust resistant), withstands a 10-ft drop, and has a long battery life of up to 800 hours. For a limited time, you can now own the U1282A (worth USD \$500) at no cost when you purchase any Keysight Big5 Bench *Plus* test instrument.



Qualifying Keysight products include:

Big5 Bench <i>Plus</i> Product Families	Model and Description
Big5 Bench <i>Plus</i> 1: Low-Profile Modular Power System (MPS) & DC Power Analyzer	N6700B/C Low-Profile MPS Mainframe, 400 W
	N6701A/C Low-Profile MPS Mainframe, 600 W
	N6702A/C Low-Profile MPS Mainframe, 1200 W
	N6705B/C DC Power Analyzer, 600 W
Big5 Bench <i>Plus</i> 2: Programmable DC Power Supply	E36102/3/4/5/6A DC Power Supply, Single Output, 30 W - 40 W models
	E36311/2/3A DC Power Supply, Triple Output, 80 W - 160 W models
Big5 Bench <i>Plus</i> 3: DAQ/Data Logger Switch Unit	34970A Data Acquisition/Switch Unit with GPIB & RS232
	34972A LXI Data Acquisition Switch Unit with LAN & USB
Big5 Bench <i>Plus</i> 4: Trueform Waveform Generator	33611/2A Waveform Generator, 80 MHz, single & dual channel models
	33621/2A Waveform Generator, 120 MHz, single & dual channel models
Big5 Bench <i>Plus</i> 5: B2900 Precision SMU/ Low-Noise Power Source/ Picoammeter/Electrometer	B2901/2A Precision SMU, 100 fA, single & dual channel models
	B2911/2A Precision SMU, single & dual channel models
	B2961/2A Low-Noise Power Source, 10 fA/100 nV resolution, single & dual channel models
	B2981/3A Femto/Picoammeter, 0.01 fA (Battery option on B2983A)
	B2985/7A Electrometer/High Resistance Meter, 0.01 fA (Battery option on B2987A)



Keysight Assurance Plans
www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

This information is subject to change without notice.

© Keysight Technologies, 2017
Published in USA, October 17, 2017
5992-2571EN

www.keysight.com

Take advantage of this offer

- Contact your Keysight authorized partner for more information or to place an order:
www.keysight.com/find/distributor
- To claim your complimentary handheld DMM:
www.keysight.com/find/BIG5BenchPLUSClaim

