

Keysight Technologies

CX3300 Current Waveform Analyzer



Quick Operation Guide

How to simulate the 50 MHz or 100 MHz bandwidth option on the mainframe with the 200 MHz option.

The mainframe has three maximum bandwidth options, 50 MHz, 100 MHz and 200 MHz. In order to simulate the 50 MHz or 100 MHz option on the mainframe with the 200 MHz option, follow the procedure below.

1. Click on the "Setting" icon.
2. The "Setting" dialog box opens.
3. Click on "Setting>Channels>Channel 1" to open the channel 1 setup panel.
4. Set the Bandwidth Limit setting to "ON".
5. Set the "Bandwidth Limit" to 50 MHz for checking the performance of the 50 MHz option and to 100 MHz for checking the performance of the 100 MHz option.

