Keysight InfiniiVision 1200 X-Series and EDUX1052A/G Oscilloscopes

KEYSIGHT TECHNOLOGIES

Programmer's Guide

Notices

© Keysight Technologies, Inc. 2005-2021

No part of this manual may be reproduced in any form or by any means (including electronic storage and retrieval or translation into a foreign language) without prior agreement and written consent from Keysight Technologies, Inc. as governed by United States and international copyright laws.

Revision

Version 02.12.0000

Edition

September 2021

Available in electronic format only

Published by:
Keysight Technologies, Inc.
1900 Garden of the Gods Road
Colorado Springs, CO 80907 USA

Warranty

The material contained in this document is provided "as is," and is subject to being changed, without notice, in future editions. Further, to the maximum extent permitted by applicable law, Keysight disclaims all warranties, either express or implied, with regard to this manual and any information contained herein, including but not limited to the implied warranties of merchantability and fitness for a particular purpose. Keysight shall not be liable for errors or for incidental or consequential damages in connection with the furnishing, use, or performance of this document or of any information contained herein. Should Keysight and the user have a separate written agreement with warranty terms covering the material in this document that conflict with these terms, the warranty terms in the separate agreement shall control.

Technology License

The hardware and/or software described in this document are furnished under a license and may be used or copied only in accordance with the terms of such license.

U.S. Government Rights

The Software is "commercial computer software," as defined by Federal Acquisition Regulation ("FAR") 2.101. Pursuant to FAR 12.212 and 27.405-3 and Department of Defense FAR Supplement ("DFARS") 227.7202, the U.S. government acquires commercial computer software under the same terms by which the software is customarily provided to the public. Accordingly, Keysight provides the Software to U.S. government customers under its standard commercial license, which is embodied in its End User License Agreement (EULA), a copy of which can be found at www.keysight.com/find/sweula. The license set forth in the EULA represents the exclusive authority by which the U.S. government may use, modify, distribute, or disclose the Software. The EULA and the license set forth therein, does not require or permit, among other things, that Keysight: (1) Furnish technical information related to commercial computer software or commercial computer software documentation that is not customarily provided to the public; or (2) Relinquish to, or otherwise provide, the government rights in excess of these rights customarily provided to the public to use, modify, reproduce, release, perform, display, or disclose commercial computer software or commercial computer software documentation. No additional government requirements beyond those set forth in the EULA shall apply, except to the extent that those terms, rights, or licenses are explicitly required from all providers of commercial computer software pursuant to the FAR and the DFARS and are set forth specifically in writing elsewhere in the EULA. Keysight shall be under no obligation to update, revise or otherwise modify the Software. With respect to any technical data as defined by FAR 2.101, pursuant to FAR 12.211 and 27.404.2 and DFARS 227.7102, the U.S. government acquires no greater than Limited Rights as defined in FAR 27.401 or DFAR 227.7103-5 (c), as applicable in any technical data.

Safety Notices

CAUTION

A **CAUTION** notice denotes a hazard. It calls attention to an operating procedure, practice, or the like that, if not correctly performed or adhered to, could result in damage to the product or loss of important data. Do not proceed beyond a **CAUTION** notice until the indicated conditions are fully understood and met.

WARNING

A WARNING notice denotes a hazard. It calls attention to an operating procedure, practice, or the like that, if not correctly performed or adhered to, could result in personal injury or death. Do not proceed beyond a WARNING notice until the indicated conditions are fully understood and met.

In This Book

This book is your guide to programming the InfiniiVision 1200 X-Series and EDUX1052A/G oscilloscopes:

Table 1 InfiniiVision 1200 X-Series and EDUX1052A/G Oscilloscopes Model Numbers, Bandwidths

Model:	EDUX1052A	EDUX1052G	DSOX1202A	DSOX1202G	DSOX1204A	DSOX1204G
Channels:	2				4	
Bandwidth:	50 MHz		70 MHz			
Bandwidth upgrades:			70 MHz to 100 MHz with D1202BW1A upgrade		70 MHz to 100 MHz with D1200BW1A upgrade	
			70 MHz to 200 MHz with D1202BW2A upgrade		70 MHz to 200 MHz with D1200BW2A upgrade	
			100 MHz to 200 MHz with D1202BW3A upgrade		100 MHz to 200 MHz with D1200BW3A upgrade	
Sampling rate:	1 GSa/s		2 GSa/s (interleaved), 1 GSa/s (non-interleaved)			
Memory:	200 kpts		2 Mpts (1 Mpts when the External Trig channel is on)		2 Mpts (interleaved), 1 Mpts (non-interleaved)	
Segmented memory:	No		Yes			
Waveform generator:	No	Yes (20 MHz)	No	Yes (20 MHz)	No	Yes (20 MHz)
Mask/limit test:	No		Yes			

The first few chapters describe how to set up and get started:

- Chapter 1, “What's New,” starting on page 25, describes programming command changes in the latest version of oscilloscope software.
- Chapter 2, “Setting Up,” starting on page 35, describes the steps you must take before you can program the oscilloscope.
- Chapter 3, “Getting Started,” starting on page 41, gives a general overview of oscilloscope program structure and shows how to program the oscilloscope using a few simple examples.
- Chapter 4, “Commands Quick Reference,” starting on page 55, is a brief listing of the 1200 X-Series and EDUX1052A/G oscilloscope commands and syntax.

The next chapters provide reference information on common commands, root level commands, other subsystem commands, and error messages:

- Chapter 5, “Common (*) Commands,” starting on page 117, describes commands defined by the IEEE 488.2 standard that are common to all instruments.
- Chapter 6, “Root (:) Commands,” starting on page 143, describes commands that reside at the root level of the command tree and control many of the basic functions of the oscilloscope.

- Chapter 7, ":ABUS Commands," starting on page 177, describes commands that control all oscilloscope functions associated with the analog channels bus display.
- Chapter 8, ":ACQuire Commands," starting on page 187, describes commands for setting the parameters used when acquiring and storing data.
- Chapter 9, ":CALibrate Commands," starting on page 201, describes utility commands for determining the state of the calibration factor protection button.
- Chapter 10, ":CHANnel<n> Commands," starting on page 211, describes commands that control all oscilloscope functions associated with individual analog channels or groups of channels.
- Chapter 11, ":DEMO Commands," starting on page 233, describes commands that control the demonstration/training signals that can be output on the oscilloscope's Demo terminal.
- Chapter 12, ":DISPlay Commands," starting on page 237, describes commands that control how waveforms, graticule, and text are displayed and written on the screen.
- Chapter 13, ":DVM Commands," starting on page 253, describes commands that control the digital voltmeter analysis feature.
- Chapter 14, ":EXTernal Trigger Commands," starting on page 261, describes commands that control the input characteristics of the external trigger input.
- Chapter 15, ":FFT Commands," starting on page 271, describes commands that control the FFT (Fast Fourier Transform) function for displaying the frequence content of a waveform.
- Chapter 16, ":FRANalysis Commands," starting on page 285, describes commands that control oscilloscope functions associated with the Frequency Response Analysis (FRA) feature, which is available in G-suffix oscilloscope models (that have a built-in waveform generator).
- Chapter 17, ":FUNCtion Commands," starting on page 301, describes commands that control math waveforms.
- Chapter 18, ":HARDcopy Commands," starting on page 323, describes commands that set and query the selection of hardcopy device and formatting options.
- Chapter 19, ":LISTer Commands," starting on page 337, describes commands that turn on/off the Lister display for decoded serial data and get the Lister data.
- Chapter 20, ":MARKer Commands," starting on page 341, describes commands that set and query the settings of X-axis markers (X1 and X2 cursors) and the Y-axis markers (Y1 and Y2 cursors).
- Chapter 21, ":MEASure Commands," starting on page 357, describes commands that select automatic measurements (and control markers).
- Chapter 22, ":MTESt Commands," starting on page 423, describes commands that control the mask test features provided with Option LMT.

- Chapter 23, ":RECall Commands," starting on page 457, describes commands that recall previously saved oscilloscope setups, reference waveforms, or masks.
- Chapter 24, ":SAVE Commands," starting on page 465, describes commands that save oscilloscope setups, screen images, and data.
- Chapter 25, ":SBUS<n> Commands," starting on page 487, describes commands that control oscilloscope functions associated with the serial decode bus and serial triggering.
- Chapter 26, ":SYSTem Commands," starting on page 575, describes commands that control basic system functions of the oscilloscope.
- Chapter 27, ":TIMebase Commands," starting on page 603, describes commands that control all horizontal sweep functions.
- Chapter 28, ":TRIGger Commands," starting on page 615, describes commands that control the trigger modes and parameters for each trigger type.
- Chapter 29, ":WAVeform Commands," starting on page 663, describes commands that provide access to waveform data.
- Chapter 30, ":WGEN Commands," starting on page 699, describes commands that control waveform generator functions and parameters on G-suffix models.
- Chapter 31, ":WMEMory<r> Commands," starting on page 731, describes commands that control reference waveforms.
- Chapter 32, "Obsolete and Discontinued Commands," starting on page 741, describes obsolete commands which still work but have been replaced by newer commands and discontinued commands which are no longer supported.
- Chapter 33, "Error Messages," starting on page 787, lists the instrument error messages that can occur while programming the oscilloscope.

The command descriptions in this reference show upper and lowercase characters. For example, :AUToscale indicates that the entire command name is :AUTOSCALE. The short form, :AUT, is also accepted by the oscilloscope.

Then, there are chapters that describe programming topics and conceptual information in more detail:

- Chapter 34, "Status Reporting," starting on page 795, describes the oscilloscope's status registers and how to check the status of the instrument.
- Chapter 35, "Synchronizing Acquisitions," starting on page 817, describes how to wait for acquisitions to complete before querying measurement results or performing other operations with the captured data.
- Chapter 36, "More About Oscilloscope Commands," starting on page 827, contains additional information about oscilloscope programming commands.

Finally, there is a chapter that contains programming examples:

- Chapter 37, "Programming Examples," starting on page 837.

See Also

- For more information on using the SICL, VISA, and VISA COM libraries in general, see the documentation that comes with the Keysight IO Libraries Suite.
- For information on controller PC interface configuration, see the documentation for the interface card used (for example, the Keysight 82350A GPIB interface).
- For information on oscilloscope front-panel operation, see the *User's Guide*.
- For detailed connectivity information, refer to the *Keysight Technologies USB/LAN/GPIB Connectivity Guide*. For a printable electronic copy of the *Connectivity Guide*, direct your Web browser to www.keysight.com and search for "Connectivity Guide".
- For the latest versions of this and other manuals, see: http://www.keysight.com/find/1200X-Series-manual

Contents

In This Book / 3

1 What's New

What's New in Version 2.12 / 26

What's New in Version 2.10 / 27

What's New in Version 2.01 / 30

Version 2.00 at Introduction / 31

Command Differences From 1000 X-Series Oscilloscopes / 32

2 Setting Up

Step 1. Install Keysight IO Libraries Suite software / 36

Step 2. Connect and set up the oscilloscope / 37

Using the USB (Device) Interface / 37

Using the LAN Interface / 37

Step 3. Verify the oscilloscope connection / 39

3 Getting Started

Basic Oscilloscope Program Structure / 42

Initializing / 42

Capturing Data / 42

Analyzing Captured Data / 43

Programming the Oscilloscope / 44
Referencing the IO Library / 44
Opening the Oscilloscope Connection via the IO Library / 45
Initializing the Interface and the Oscilloscope / 45
Using :AUToscale to Automate Oscilloscope Setup / 46
Using Other Oscilloscope Setup Commands / 46
Capturing Data with the :DIGitize Command / 47
Reading Query Responses from the Oscilloscope / 49
Reading Query Results into String Variables / 50
Reading Query Results into Numeric Variables / 50
Reading Definite-Length Block Query Response Data / 50
Sending Multiple Queries and Reading Results / 51
Checking Instrument Status / 52
Other Ways of Sending Commands / 53
Telnet Sockets / 53
Sending SCPI Commands Using Browser Web Control / 53

4 Commands Quick Reference

Command Summary / 56
Syntax Elements / 113
Number Format / 113
<NL> (Line Terminator) / 113
[ ] (Optional Syntax Terms) / 113
{ } (Braces) / 113
::= (Defined As) / 113
< > (Angle Brackets) / 114
... (Ellipsis) / 114
n,..,p (Value Ranges) / 114
d (Digits) / 114
Quoted ASCII String / 114
Definite-Length Block Response Data / 114

5 Common (*) Commands

*CLS (Clear Status) / 121
*ESE (Standard Event Status Enable) / 122
*ESR (Standard Event Status Register) / 124
*IDN (Identification Number) / 126
*LRN (Learn Device Setup) / 127
*OPC (Operation Complete) / 128
*OPT (Option Identification) / 129

*RCL (Recall) / 130
*RST (Reset) / 131
*SAV (Save) / 134
*SRE (Service Request Enable) / 135
*STB (Read Status Byte) / 137
*TRG (Trigger) / 139
*TST (Self Test) / 140
*WAI (Wait To Continue) / 141

6 Root (:) Commands

:AER (Arm Event Register) / 146
:AUToscale / 147
:AUToscale:AMODE / 149
:AUToscale:CHANnels / 150
:AUToscale:FDEBug / 151
:BLANk / 152
:DIGitize / 153
:MTEenable (Mask Test Event Enable Register) / 155
:MTERegister[:EVENt] (Mask Test Event Event Register) / 157
:OPEE (Operation Status Enable Register) / 159
:OPERegister:CONDition (Operation Status Condition Register) / 161
:OPERegister[:EVENt] (Operation Status Event Register) / 163
:OVLenable (Overload Event Enable Register) / 165
:OVLRegister (Overload Event Register) / 167
:PRINt / 169
:RUN / 170
:SERial / 171
:SINGle / 172
:STATus / 173
:STOP / 174
:TER (Trigger Event Register) / 175
:VIEW / 176

7 :ABUS Commands

:ABUS:BIT<m> / 179
:ABUS:BITS / 180
:ABUS:CLEar / 182
:ABUS:DISPlay / 183
:ABUS:LABel / 184
:ABUS:MASK / 185

8 :ACQuire Commands

:ACQuire:COMPlete / 189
:ACQuire:COUNt / 190
:ACQuire:MODE / 191
:ACQuire:POINts / 192
:ACQuire:SEGMented:ANALyze / 193
:ACQuire:SEGMented:COUNt / 194
:ACQuire:SEGMented:INDex / 195
:ACQuire:SRATe / 198
:ACQuire:TYPE / 199

9 :CALibrate Commands

:CALibrate:DATE / 203
:CALibrate:LABel / 204
:CALibrate:OUTPut / 205
:CALibrate:PROTected / 206
:CALibrate:STARt / 207
:CALibrate:STATus / 208
:CALibrate:TEMPerature / 209
:CALibrate:TIME / 210

10 :CHANnel<n> Commands

:CHANnel<n>:BANDwidth / 214
:CHANnel<n>:BWLimit / 215
:CHANnel<n>:COUPling / 216
:CHANnel<n>:DISPlay / 217
:CHANnel<n>:IMPedance / 218
:CHANnel<n>:INVert / 219
:CHANnel<n>:LABel / 220
:CHANnel<n>:OFFSet / 221
:CHANnel<n>:PROBe / 222
:CHANnel<n>:PROBe:HEAD[:TYPE] / 223
:CHANnel<n>:PROBe:ID / 224
:CHANnel<n>:PROBe:SKEW / 225
:CHANnel<n>:PROBe:STYPe / 226
:CHANnel<n>:PROTection / 227
:CHANnel<n>:RANGe / 228
:CHANnel<n>:SCALe / 229
:CHANnel<n>:UNITs / 230
:CHANnel<n>:VERNier / 231

11 :DEMO Commands

:DEMO:FUNCtion / 234
:DEMO:OUTPut / 236

12 :DISPlay Commands

:DISPlay:ANNotation / 239
:DISPlay:ANNotation:BACKground / 240
:DISPlay:ANNotation:COLor / 241
:DISPlay:ANNotation:TEXT / 242
:DISPlay:CLEar / 243
:DISPlay:DATA / 244
:DISPlay:INTensity:WAVeform / 245
:DISPlay:LABel / 246
:DISPlay:LABList / 247
:DISPlay:MENU:TIMeout / 248
:DISPlay:PERSistence / 249
:DISPlay:TRANsparent / 250
:DISPlay:VECTors / 251

13 :DVM Commands

:DVM:ARANge / 254
:DVM:CURRent / 255
:DVM:ENABle / 256
:DVM:FREQuency / 257
:DVM:MODE / 258
:DVM:SOURce / 259

14 :EXTernal Trigger Commands

:EXTernal:BWLimit / 263
:EXTernal:DISPlay / 264
:EXTernal:LABel / 265
:EXTernal:LEVel / 266
:EXTernal:POSition / 267
:EXTernal:PROBe / 268
:EXTernal:RANGe / 269
:EXTernal:UNITs / 270

15 :FFT Commands

:FFT:CENTer / 273
:FFT:DISPlay / 274
:FFT:OFFSet / 275

:FFT:RANGe / 276
:FFT:REFerence / 277
:FFT:SCALe / 278
:FFT:SOURce1 / 279
:FFT:SPAN / 280
:FFT:VTYPe / 281
:FFT:WINDow / 282

16 :FRANalysis Commands

:FRANalysis:DATA / 287
:FRANalysis:ENABle / 288
:FRANalysis:FREQuency:MODE / 289
:FRANalysis:FREQuency:SINGle / 290
:FRANalysis:FREQuency:STARt / 291
:FRANalysis:FREQuency:STOP / 292
:FRANalysis:RUN / 293
:FRANalysis:SOURce:INPut / 294
:FRANalysis:SOURce:OUTPut / 295
:FRANalysis:SWEep:POINts / 296
:FRANalysis:TRACe / 297
:FRANalysis:WGEN:LOAD / 298
:FRANalysis:WGEN:VOLTage / 299

17 :FUNCtion Commands

:FUNCtion:DISPlay / 304
:FUNCtion[:FFT]:CENTer / 305
:FUNCtion[:FFT]:PHASe:REFerence / 306
:FUNCtion[:FFT]:SPAN / 307
:FUNCtion[:FFT]:VTYPe / 308
:FUNCtion[:FFT]:WINDow / 309
:FUNCtion:FREQuency:LOWPass / 310
:FUNCtion:GOFT:OPERation / 311
:FUNCtion:GOFT:SOURce1 / 312
:FUNCtion:GOFT:SOURce2 / 313
:FUNCtion:OFFSet / 314
:FUNCtion:OPERation / 315
:FUNCtion:RANGe / 317
:FUNCtion:REFerence / 318
:FUNCtion:SCALe / 319
:FUNCtion:SOURce1 / 320
:FUNCtion:SOURce2 / 321

18 :HARDcopy Commands

:HARDcopy:AREA / 325
:HARDcopy:APRinter / 326
:HARDcopy:FACTors / 327
:HARDcopy:FFEed / 328
:HARDcopy:INKSaver / 329
:HARDcopy:LAYout / 330
:HARDcopy:NETWork:ADDRess / 331
:HARDcopy:NETWork:APPLy / 332
:HARDcopy:NETWork:SLOT / 333
:HARDcopy:PALette / 334
:HARDcopy:PRINter:LIST / 335
:HARDcopy:STARt / 336

19 :LISTer Commands

:LISTer:DATA / 338
:LISTer:DISPlay / 339
:LISTer:REFerence / 340

20 :MARKer Commands

:MARKer:MODE / 344
:MARKer:X1Position / 345
:MARKer:X1Y1source / 346
:MARKer:X2Position / 347
:MARKer:X2Y2source / 348
:MARKer:XDELta / 349
:MARKer:XUNits / 350
:MARKer:XUNits:USE / 351
:MARKer:Y1Position / 352
:MARKer:Y2Position / 353
:MARKer:YDELta / 354
:MARKer:YUNits / 355
:MARKer:YUNits:USE / 356

21 :MEASure Commands

:MEASure:ALL / 369
:MEASure:BRATe / 370
:MEASure:CLEar / 371
:MEASure:COUNter / 372
:MEASure:DEFine / 373
:MEASure:DELay / 376

:MEASure:DUTYcycle / 378
:MEASure:FALLtime / 379
:MEASure:FREQuency / 380
:MEASure:NDUTy / 381
:MEASure:NEDGes / 382
:MEASure:NPULses / 383
:MEASure:NWIDth / 384
:MEASure:OVERshoot / 385
:MEASure:PEDGes / 387
:MEASure:PERiod / 388
:MEASure:PHASe / 389
:MEASure:PPULses / 390
:MEASure:PREShoot / 391
:MEASure:PWIDth / 392
:MEASure:RESults / 393
:MEASure:RISetime / 396
:MEASure:SDEViation / 397
:MEASure:SHOW / 398
:MEASure:SOURce / 399
:MEASure:STATistics / 401
:MEASure:STATistics:DISPlay / 402
:MEASure:STATistics:INCRement / 403
:MEASure:STATistics:MCOunt / 404
:MEASure:STATistics:RESet / 405
:MEASure:STATistics:RSDeviation / 406
:MEASure:TEDGe / 407
:MEASure:TVALue / 409
:MEASure:VAMPlitude / 411
:MEASure:VAVerage / 412
:MEASure:VBASe / 413
:MEASure:VMAX / 414
:MEASure:VMIN / 415
:MEASure:VPP / 416
:MEASure:VRMS / 417
:MEASure:VTIMe / 418
:MEASure:VTOP / 419
:MEASure:WINDow / 420
:MEASure:XMAX / 421
:MEASure:XMIN / 422

22 :MTESt Commands

:MTESt:ALL / 428
:MTESt:AMASk:CREate / 429
:MTESt:AMASk:SOURce / 430
:MTESt:AMASk:UNITs / 431
:MTESt:AMASk:XDELta / 432
:MTESt:AMASk:YDELta / 433
:MTESt:COUNt:FWAVeforms / 434
:MTESt:COUNt:RESet / 435
:MTESt:COUNt:TIME / 436
:MTESt:COUNt:WAVeforms / 437
:MTESt:DATA / 438
:MTESt:DELete / 439
:MTESt:ENABle / 440
:MTESt:LOCK / 441
:MTESt:RMODe / 442
:MTESt:RMODe:FACTion:MEASure / 443
:MTESt:RMODe:FACTion:PRINt / 444
:MTESt:RMODe:FACTion:SAVE / 445
:MTESt:RMODe:FACTion:STOP / 446
:MTESt:RMODe:SIGMa / 447
:MTESt:RMODe:TIME / 448
:MTESt:RMODe:WAVeforms / 449
:MTESt:SCALe:BIND / 450
:MTESt:SCALe:X1 / 451
:MTESt:SCALe:XDELta / 452
:MTESt:SCALe:Y1 / 453
:MTESt:SCALe:Y2 / 454
:MTESt:SOURce / 455
:MTESt:TITLe / 456

23 :RECall Commands

:RECall:FILename / 459
:RECall:MASK[:STARt] / 460
:RECall:PWD / 461
:RECall:SETup[:STARt] / 462
:RECall:WMEMory<r>[:STARt] / 463

24 :SAVE Commands

:SAVE:FILename / 468
:SAVE:IMAGe[:STARt] / 469

:SAVE:IMAGe:FACTors / 470
:SAVE:IMAGe:FORMat / 471
:SAVE:IMAGe:INKSaver / 472
:SAVE:IMAGe:PALette / 473
:SAVE:LISTer[:STARt] / 474
:SAVE:MASK[:STARt] / 475
:SAVE:MULTi[:STARt] / 476
:SAVE:PWD / 477
:SAVE:SETup[:STARt] / 478
:SAVE:WAVeform[:STARt] / 479
:SAVE:WAVeform:FORMat / 480
:SAVE:WAVeform:LENGth / 481
:SAVE:WAVeform:LENGth:MAX / 482
:SAVE:WAVeform:SEGMented / 483
:SAVE:WMEMory:SOURce / 484
:SAVE:WMEMory[:STARt] / 485

25 :SBUS<n> Commands

General :SBUS<n> Commands / 489
:SBUS<n>:DISPlay / 490
:SBUS<n>:MODE / 491

:SBUS<n>:CAN Commands / 492
:SBUS<n>:CAN:COUNt:ERRor / 494
:SBUS<n>:CAN:COUNt:OVERload / 495
:SBUS<n>:CAN:COUNt:RESet / 496
:SBUS<n>:CAN:COUNt:TOTal / 497
:SBUS<n>:CAN:COUNt:UTILization / 498
:SBUS<n>:CAN:SAMPlepoint / 499
:SBUS<n>:CAN:SIGNal:BAUDrate / 500
:SBUS<n>:CAN:SIGNal:DEFinition / 501
:SBUS<n>:CAN:SOURce / 502
:SBUS<n>:CAN:TRIGger / 503
:SBUS<n>:CAN:TRIGger:PATTern:DATA / 505
:SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth / 506
:SBUS<n>:CAN:TRIGger:PATTern:ID / 507
:SBUS<n>:CAN:TRIGger:PATTern:ID:MODE / 508

:SBUS<n>:IIC Commands / 509
:SBUS<n>:IIC:ASIZe / 510
:SBUS<n>:IIC[:SOURce]:CLOCk / 511
:SBUS<n>:IIC[:SOURce]:DATA / 512

:SBUS<n>:IIC:TRIGger:PATTern:ADDRess / 513
:SBUS<n>:IIC:TRIGger:PATTern:DATA / 514
:SBUS<n>:IIC:TRIGger:PATTern:DATa2 / 515
:SBUS<n>:IIC:TRIGger:QUALifier / 516
:SBUS<n>:IIC:TRIGger[:TYPE] / 517

:SBUS<n>:LIN Commands / 519
:SBUS<n>:LIN:PARity / 521
:SBUS<n>:LIN:SAMPlepoint / 522
:SBUS<n>:LIN:SIGNal:BAUDrate / 523
:SBUS<n>:LIN:SOURce / 524
:SBUS<n>:LIN:STANdard / 525
:SBUS<n>:LIN:SYNCbreak / 526
:SBUS<n>:LIN:TRIGger / 527
:SBUS<n>:LIN:TRIGger:ID / 528
:SBUS<n>:LIN:TRIGger:PATTern:DATA / 529
:SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth / 531
:SBUS<n>:LIN:TRIGger:PATTern:FORMat / 532

:SBUS<n>:SPI Commands / 533
:SBUS<n>:SPI:BITorder / 535
:SBUS<n>:SPI:CLOCk:SLOPe / 536
:SBUS<n>:SPI:CLOCk:TIMeout / 537
:SBUS<n>:SPI:FRAMing / 538
:SBUS<n>:SPI:SOURce:CLOCk / 539
:SBUS<n>:SPI:SOURce:DATA / 540
:SBUS<n>:SPI:SOURce:FRAMe / 541
:SBUS<n>:SPI:SOURce:MISO / 542
:SBUS<n>:SPI:SOURce:MOSI / 543
:SBUS<n>:SPI:TRIGger:PATTern:DATA / 544
:SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA / 545
:SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh / 546
:SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA / 547
:SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh / 548
:SBUS<n>:SPI:TRIGger:PATTern:WIDTh / 549
:SBUS<n>:SPI:TRIGger:TYPE / 550
:SBUS<n>:SPI:WIDTh / 551

:SBUS<n>:UART Commands / 552
:SBUS<n>:UART:BASE / 555
:SBUS<n>:UART:BAUDrate / 556
:SBUS<n>:UART:BITorder / 557
:SBUS<n>:UART:COUNt:ERRor / 558

:SBUS<n>:UART:COUNt:RESet / 559
:SBUS<n>:UART:COUNt:RXFRames / 560
:SBUS<n>:UART:COUNt:TXFRames / 561
:SBUS<n>:UART:FRAMing / 562
:SBUS<n>:UART:PARity / 563
:SBUS<n>:UART:POLarity / 564
:SBUS<n>:UART:SOURce:RX / 565
:SBUS<n>:UART:SOURce:TX / 566
:SBUS<n>:UART:TRIGger:BASE / 567
:SBUS<n>:UART:TRIGger:BURSt / 568
:SBUS<n>:UART:TRIGger:DATA / 569
:SBUS<n>:UART:TRIGger:IDLE / 570
:SBUS<n>:UART:TRIGger:QUALifier / 571
:SBUS<n>:UART:TRIGger:TYPE / 572
:SBUS<n>:UART:WIDTh / 573

26 :SYSTem Commands

:SYSTem:DATE / 578
:SYSTem:DIDentifier / 579
:SYSTem:DSP / 580
:SYSTem:ERRor / 581
:SYSTem:LOCK / 582
:SYSTem:MENU / 583
:SYSTem:PERSona[:MANufacturer] / 584
:SYSTem:PERSona[:MANufacturer]:DEFault / 585
:SYSTem:PRESet / 586
:SYSTem:PROTection:LOCK / 589
:SYSTem:RLOGger / 590
:SYSTem:RLOGger:DESTination / 591
:SYSTem:RLOGger:DISPlay / 592
:SYSTem:RLOGger:FNAMe / 593
:SYSTem:RLOGger:STATe / 594
:SYSTem:RLOGger:TRANsparent / 595
:SYSTem:RLOGger:WMODe / 596
:SYSTem:SETup / 597
:SYSTem:TIME / 599
:SYSTem:TZONe / 600
:SYSTem:USB:EJECt / 601
:SYSTem:USB:PLISt / 602

27 :TIMebase Commands

:TIMebase:MODE / 605
:TIMebase:POSition / 606
:TIMebase:RANGe / 607
:TIMebase:REFerence / 608
:TIMebase:SCALe / 609
:TIMebase:VERNier / 610
:TIMebase:WINDow:POSition / 611
:TIMebase:WINDow:RANGe / 612
:TIMebase:WINDow:SCALe / 613

28 :TRIGger Commands

General :TRIGger Commands / 617
:TRIGger:FORCe / 618
:TRIGger:HFReject / 619
:TRIGger:HOLDoff / 620
:TRIGger:LEVel:ASETup / 621
:TRIGger:LEVel:HIGH / 622
:TRIGger:LEVel:LOW / 623
:TRIGger:MODE / 624
:TRIGger:NREJect / 625
:TRIGger:SWEep / 626

:TRIGger[:EDGE] Commands / 627
:TRIGger[:EDGE]:COUPling / 628
:TRIGger[:EDGE]:LEVel / 629
:TRIGger[:EDGE]:REJect / 630
:TRIGger[:EDGE]:SLOPe / 631
:TRIGger[:EDGE]:SOURce / 632

:TRIGger:GLITch Commands / 633
:TRIGger:GLITch:GREaterthan / 634
:TRIGger:GLITch:LESSthan / 635
:TRIGger:GLITch:LEVel / 636
:TRIGger:GLITch:POLarity / 637
:TRIGger:GLITch:QUALifier / 638
:TRIGger:GLITch:RANGe / 639
:TRIGger:GLITch:SOURce / 640

:TRIGger:PATTern Commands / 641
:TRIGger:PATTern / 642
:TRIGger:PATTern:FORMat / 644
:TRIGger:PATTern:QUALifier / 645

:TRIGger:SHOLd Commands / 646
:TRIGger:SHOLd:SLOPe / 647
:TRIGger:SHOLd:SOURce:CLOCk / 648
:TRIGger:SHOLd:SOURce:DATA / 649
:TRIGger:SHOLd:TIME:HOLD / 650
:TRIGger:SHOLd:TIME:SETup / 651
:TRIGger:TRANsition Commands / 652
:TRIGger:TRANsition:QUALifier / 653
:TRIGger:TRANsition:SLOPe / 654
:TRIGger:TRANsition:SOURce / 655
:TRIGger:TRANsition:TIME / 656
:TRIGger:TV Commands / 657
:TRIGger:TV:LINE / 658
:TRIGger:TV:MODE / 659
:TRIGger:TV:POLarity / 660
:TRIGger:TV:SOURce / 661
:TRIGger:TV:STANdard / 662

29 :WAVeform Commands

:WAVeform:BYTeorder / 670
:WAVeform:COUNt / 671
:WAVeform:DATA / 672
:WAVeform:FORMat / 674
:WAVeform:POINts / 675
:WAVeform:POINts:MODE / 677
:WAVeform:PREamble / 679
:WAVeform:SEGMented:COUNt / 682
:WAVeform:SEGMented:TTAG / 683
:WAVeform:SOURce / 684
:WAVeform:SOURce:SUBSource / 688
:WAVeform:TYPE / 689
:WAVeform:UNSigned / 690
:WAVeform:VIEW / 691
:WAVeform:XINCrement / 692
:WAVeform:XORigin / 693
:WAVeform:XREFerence / 694
:WAVeform:YINCrement / 695
:WAVeform:YORigin / 696
:WAVeform:YREFerence / 697

30 :WGEN Commands

:WGEN:FREQuency / 702
:WGEN:FUNCtion / 703
:WGEN:FUNCtion:PULSe:WIDTh / 706
:WGEN:FUNCtion:RAMP:SYMMetry / 707
:WGEN:FUNCtion:SQUare:DCYCle / 708
:WGEN:MODulation:AM:DEPTh / 709
:WGEN:MODulation:AM:FREQuency / 710
:WGEN:MODulation:FM:DEViation / 711
:WGEN:MODulation:FM:FREQuency / 712
:WGEN:MODulation:FSKey:FREQuency / 713
:WGEN:MODulation:FSKey:RATE / 714
:WGEN:MODulation:FUNCtion / 715
:WGEN:MODulation:FUNCtion:RAMP:SYMMetry / 716
:WGEN:MODulation:NOISe / 717
:WGEN:MODulation:STATe / 718
:WGEN:MODulation:TYPE / 719
:WGEN:OUTPut / 721
:WGEN:OUTPut:LOAD / 722
:WGEN:OUTPut:POLarity / 723
:WGEN:PERiod / 724
:WGEN:RST / 725
:WGEN:VOLTage / 726
:WGEN:VOLTage:HIGH / 727
:WGEN:VOLTage:LOW / 728
:WGEN:VOLTage:OFFSet / 729

31 :WMEMory<r> Commands

:WMEMory<r>:CLEar / 733
:WMEMory<r>:DISPlay / 734
:WMEMory<r>:LABel / 735
:WMEMory<r>:SAVE / 736
:WMEMory<r>:SKEW / 737
:WMEMory<r>:YOFFset / 738
:WMEMory<r>:YRANge / 739
:WMEMory<r>:YSCale / 740

32 Obsolete and Discontinued Commands

:CHANnel:LABel / 746
:CHANnel2:SKEW / 747
:CHANnel<n>:INPut / 748

:CHANnel<n>:PMODe / 749
:DISPlay:CONNect / 750
:ERASe / 751
:EXTernal:PMODe / 752
:FRANalysis:PPDecade / 753
:FUNCtion:SOURce / 754
:FUNCtion:VIEW / 755
:HARDcopy:DESTination / 756
:HARDcopy:FILename / 757
:HARDcopy:GRAYscale / 758
:HARDcopy:IGColors / 759
:HARDcopy:PDRiver / 760
:MEASure:LOWer / 761
:MEASure:SCRatch / 762
:MEASure:TDELta / 763
:MEASure:THResholds / 764
:MEASure:TMAX / 765
:MEASure:TMIN / 766
:MEASure:TSTArt / 767
:MEASure:TSTOp / 768
:MEASure:TVOLt / 769
:MEASure:UPPer / 770
:MEASure:VDELta / 771
:MEASure:VSTArt / 772
:MEASure:VSTOp / 773
:MTESt:AMASk:{SAVE | STORe} / 774
:MTESt:AVERage / 775
:MTESt:AVERage:COUNt / 776
:MTESt:LOAD / 777
:MTESt:RUMode / 778
:MTESt:RUMode:SOFailure / 779
:MTESt:{STARt | STOP} / 780
:MTESt:TRIGger:SOURce / 781
:PRINt? / 782
:SAVE:IMAGe:AREA / 784
:TIMebase:DELay / 785
:TRIGger:TV:TVMode / 786

33 Error Messages

34 Status Reporting

Status Reporting Data Structures / 797

Status Byte Register (STB) / 800

Service Request Enable Register (SRE) / 802

Trigger Event Register (TER) / 803

Output Queue / 804

Message Queue / 805

(Standard) Event Status Register (ESR) / 806

(Standard) Event Status Enable Register (ESE) / 807

Error Queue / 808

Operation Status Event Register (:OPERegister[:EVENt]) / 809

Operation Status Condition Register (:OPERegister:CONDition) / 810

Arm Event Register (AER) / 811

Overload Event Register (:OVLRegister) / 812

Mask Test Event Event Register (:MTERegister[:EVENt]) / 813

Clearing Registers and Queues / 814

Status Reporting Decision Chart / 815

35 Synchronizing Acquisitions

Synchronization in the Programming Flow / 818

Set Up the Oscilloscope / 818

Acquire a Waveform / 818

Retrieve Results / 818

Blocking Synchronization / 819

Polling Synchronization With Timeout / 820

Synchronizing with a Single-Shot Device Under Test (DUT) / 822

Synchronization with an Averaging Acquisition / 824

36 More About Oscilloscope Commands

Command Classifications / 828
Core Commands / 828
Non-Core Commands / 828
Obsolete Commands / 828

Valid Command/Query Strings / 829
Program Message Syntax / 829
Duplicate Mnemonics / 833
Tree Traversal Rules and Multiple Commands / 833

Query Return Values / 835

All Oscilloscope Commands Are Sequential / 836

37 Programming Examples

VISA COM Examples / 838
VISA COM Example in Visual Basic / 838
VISA COM Example in C# / 847
VISA COM Example in Visual Basic .NET / 856
VISA COM Example in Python 3 / 864

VISA Examples / 871
VISA Example in C / 871
VISA Example in Visual Basic / 880
VISA Example in C# / 890
VISA Example in Visual Basic .NET / 901
VISA Example in Python 3 / 911

VISA.NET Examples / 918
VISA.NET Example in C# / 918
VISA.NET Example in Visual Basic .NET / 924

SICL Examples / 931
SICL Example in C / 931
SICL Example in Visual Basic / 940

SCPI.NET Examples / 951

Index

1 What's New

What's New in Version 2.12 / 26
What's New in Version 2.10 / 27
What's New in Version 2.01 / 30
Version 2.00 at Introduction / 31
Command Differences From 1000 X-Series Oscilloscopes / 32

What's New in Version 2.12

New features in version 2.12 of the InfiniiVision 1200 X-Series and EDUX11052A/G oscilloscope software are:

- Measurement statistics.

More detailed descriptions of the new and changed commands appear below.

New Commands

Command	Description
:MEASure:STATistics (see page 401)	Determines the type of information returned by the :MEASure:RESults? query.
:MEASure:STATistics:DISPlay (see page 402)	Specifies whether the display of measurement statistics is on or off.
:MEASure:STATistics:INCRement (see page 403)	Updates the statistics once (incrementing the count by one) using the current measurement values.
:MEASure:STATistics:MCOunt (see page 404)	Specifies the maximum number of values used when calculating measurement statistics.
:MEASure:STATistics:RESet (see page 405)	Resets the measurement statistics, zeroing the counts.
:MEASure:STATistics:RSDeviation (see page 406)	Disables or enables relative standard deviations, that is, standard deviation/mean, in the measurement statistics.

Changed Commands

Command	Differences
:MEASure:RESults (see page 393)	Now returns more information if :MEASurement:STATistics is ON.

What's New in Version 2.10

New features in version 2.10 of the InfiniiVision 1200 X-Series and EDUX11052A/G oscilloscope software are:

- Support for the new DSOX1202A/G and EDUX1052A/G 2-channel oscilloscope models has been added. On these new 2-channel models:
  - The Ext Trig input that can be used like a single digital input channel.
  - The Ext Trig input can be included in a bus made up of analog channels.
  - The Ext Trig input can be included in a pattern trigger.
  - The Ext Trig input can be a source for serial bus decodes.
- The serial bus decode Lister feature has been added.

More detailed descriptions of the new and changed commands appear below.

New Commands

Command	Description
:DISPlay:TRANsparent (see page 250)	Enables or disables transparent mode for dialog box backgrounds in the front panel graphical user interface.
:LISTer:DATA? (see page 338)	Returns the lister data.
:LISTer:DISPlay (see page 339)	Turns the serial bus Lister display on or off.
:LISTer:REFerence (see page 340)	Selects whether the time value for a Lister row is relative to the trigger ot the previous Lister row.
:SAVE:LISTer[:STARt] (see page 474)	Saves the Lister display data to a file.
:SBUS<n>:SPI:SOURce:DATA (see page 540)	On 2-channel DSOX1200-Series oscilloscopes (that support 3-wire SPI), this command sets the source for the SPI serial data.
:SBUS<n>:SPI:TRIGger:PATTern:DATA (see page 544)	On 2-channel DSOX1200-Series oscilloscopes (that support 3-wire SPI), this command defines the SPI data pattern.
:SBUS<n>:SPI:TRIGger:PATTern:WIDTh (see page 549)	On 2-channel DSOX1200-Series oscilloscopes (that support 3-wire SPI), this command sets the width of the SPI data pattern.
:SYSTem:TZONe (see page 600)	Sets the system time zone based on the specified offset from UTC.

Changed Commands

Command	Differences
:ABUS:BIT<m> (see page 179)	On 2-channel oscilloscopes, analog channel buses have bits for channels 1, 2, and the Ext Trig input.
:ABUS:BITS (see page 180)	On 2-channel oscilloscopes, analog channel buses have bits for channels 1, 2, and the Ext Trig input.

Command	Differences
:BLANk (see page 152)	On 2-channel oscilloscopes, the EXT source is available.
:DEMO:FUNCtion (see page 234)	The UART demo signal has been removed.
:DIGitize (see page 153)	On 2-channel oscilloscopes, the EXT source is available.
:EXTernal:DISPlay (see page 264)	On 2-channel oscilloscopes, the Ext Trig input can be displayed as a digital waveform.
:EXTernal:LABel (see page 265)	On 2-channel oscilloscopes, the Ext Trig input can be displayed as a digital waveform.
:EXTernal:POSition (see page 267)	On 2-channel oscilloscopes, the Ext Trig input can be displayed as a digital waveform.
:MARKer:X1Y1source (see page 346)	On 2-channel oscilloscopes, the EXTernal source is available.
:MEASure:DUTYcycle (see page 378)	On 2-channel oscilloscopes, the EXTernal source is available.
:MEASure:FREQuency (see page 380)	On 2-channel oscilloscopes, the EXTernal source is available.
:MEASure:NDUTy (see page 381)	On 2-channel oscilloscopes, the EXTernal source is available.
:MEASure:NWIDth (see page 384)	On 2-channel oscilloscopes, the EXTernal source is available.
:MEASure:PERiod (see page 388)	On 2-channel oscilloscopes, the EXTernal source is available.
:MEASure:PWIDth (see page 392)	On 2-channel oscilloscopes, the EXTernal source is available.
:MEASure:TEDGe (see page 407)	On 2-channel oscilloscopes, the EXTernal source is available.
:MEASure:VTIMe (see page 418)	On 2-channel oscilloscopes, the EXTernal source is available.
:SBUS<n>:CAN:SOURce (see page 502)	On 2-channel DSOX1200-Series oscilloscopes, EXTernal can be specified as the source.
:SBUS<n>:IIC[:SOURce]:CLOCk (see page 511)	On 2-channel DSOX1200-Series oscilloscopes, EXTernal can be specified as the source.
:SBUS<n>:IIC[:SOURce]:DATA (see page 512)	On 2-channel DSOX1200-Series oscilloscopes, EXTernal can be specified as the source.
:SBUS<n>:LIN:SOURce (see page 524)	On 2-channel DSOX1200-Series oscilloscopes, EXTernal can be specified as the source.
:SBUS<n>:SPI:SOURce:CLOCk (see page 539)	On 2-channel DSOX1200-Series oscilloscopes, EXTernal can be specified as the source.

Command	Differences
:SBUS<n>:SPI:SOURce:FRAMe (see page 541)	On 2-channel DSOX1200-Series oscilloscopes, EXTernal can be specified as the source.
:SBUS<n>:UART:SOURce:RX (see page 565)	On 2-channel DSOX1200-Series oscilloscopes, EXTernal can be specified as the source.
:SBUS<n>:UART:SOURce:TX (see page 566)	On 2-channel DSOX1200-Series oscilloscopes, EXTernal can be specified as the source.
:STATus (see page 173)	On 2-channel oscilloscopes, the EXT source is available.
:SYSTem:MENU (see page 583)	The LISTer option has been added so that the command can now display the Lister menu.
:TRIGger:PATTern (see page 642)	On 2-channel oscilloscopes, pattern triggers have bits for channels 1, 2, and the Ext Trig input, EXTernal can be used as an edge source.
:VIEW (see page 176)	On 2-channel oscilloscopes, the EXT source is available.
:WAVeform:SOURce (see page 684)	On 2-channel oscilloscopes, the EXT source is available.
:WGEN:FUNCtion:SQUare:DCYCle (see page 708)	The square wave duty cycle can now be adjusted from 1% to 99%.

What's New in Version 2.01

New features in version 2.01 of the InfiniiVision DSOX1204A/G oscilloscope software are:

- Frequency Response Analysis (FRA) now supports more flexible frequency ranges in the sweep analysis.

More detailed descriptions of the new and changed commands appear below.

New Commands

Command	Description
:FRANalysis:SWEep:POINts (see page 296)	Specifies the total number of points in the frequency response analysis.

Changed Commands

Command	Differences
:FRANalysis:FREQuency:SINGle (see page 290)	You can now specify precise frequency values between 10 Hz and 20 MHz with a resolution of 0.1 Hz.
:FRANalysis:FREQuency:STARt (see page 291)	You can now specify precise start frequency values between 10 Hz and 19.99 MHz with a resolution of 0.1 Hz.
:FRANalysis:FREQuency:STOP (see page 292)	You can now specify precise stop frequency values between 10.1 Hz and 20 MHz with a resolution of 0.1 Hz.

Obsolete Commands

Obsolete Command	Current Command Equivalent	Behavior Differences
:FRANalysis:PPDecade (see page 753)	:FRANalysis:SWEep:POINts (see page 296)	Instead of points-per-decade, the :FRANalysis:SWEep:POINts command lets you specify the total number of points in the frequency response analysis.

Version 2.00 at Introduction

The Keysight InfiniiVision DSOX1204A/G oscilloscopes were introduced with version 2.00 of oscilloscope operating software.

The command set is most closely related to the InfiniiVision 1000 X-Series oscilloscopes (and the 2000/3000 X-Series, 7000 Series, 6000 Series, and 54620/54640 Series oscilloscopes before them). For more information, see "Command Differences From 1000 X-Series Oscilloscopes" on page 32.

Command Differences From 1000 X-Series Oscilloscopes

The Keysight InfiniiVision DSOX1204A/G oscilloscopes command set is most closely related to the InfiniiVision 1000 X-Series oscilloscopes (and the 2000/3000 X-Series, 7000 Series, 6000 Series, and 54620/54640 Series oscilloscopes before them).

The main differences between the version 2.00 programming command set for the InfiniiVision DSOX1204A/G oscilloscopes and the 1.10 programming command set for the InfiniiVision 1000 X-Series oscilloscopes are related to:

- The DSOX1204A/G oscilloscopes have 4 analog input channels, the previous 1000 X-Series oscilloscopes have 2 analog input channels and an Ext Trig input that can be used like a single digital input channel.
- The Ext Trig input cannot be included in a bus made up of analog channels.
- The Ext Trig input cannot be included in a pattern trigger.
- The Ext Trig input cannot be a source for serial bus decodes.
- The DSOX1204A/G oscilloscopes have a LAN interface in addition to the USB device interface.
- Four count measurements are added to the DSOX1204A/G oscilloscopes: positive pulse count, negative pulse count, rising edge count, and falling edge count.

More detailed descriptions of the new, changed, obsolete, and discontinued commands appear below.

New Commands

Command	Description
:HARDcopy:NETWork:ADDRess (see page 331)	Sets the address for a network printer slot.
:HARDcopy:NETWork:APPLy (see page 332)	Applies the network printer settings and makes the printer connection.
:HARDcopy:NETWork:SLOT (see page 333)	Selects the network printer slot used for the address and apply commands.
:MEASure:NEDGes (see page 382)	Counts the number of falling edges.
:MEASure:NPULses (see page 383)	Counts the number of negative pulses.
:MEASure:PEDGes (see page 387)	Counts the number of rising edges.
:MEASure:PPULses (see page 390)	Counts the number of positive pulses.
:SYSTem:DIDentifier? (see page 579)	Returns the oscilloscope's Host ID string.

Command	Description
:SYSTem:USB:EJECt (see page 601)	Ejects connected USB storage devices.
:SYSTem:USB:PLISt? (see page 602)	Returns the root path for all connected USB storage devices, delimited by a newline character ("\n").

Changed Commands

Command	Differences From InfiniiVision 1000 X-Series Oscilloscopes
:ABUS:BIT<m> (see page 179)	Analog channel buses have bits for channels 3 and 4 but not for the Ext Trig input.
:ABUS:BITS (see page 180)	Analog channel buses have bits for channels 3 and 4 but not for the Ext Trig input.
:BLANk (see page 152)	EXT source is not available.
:DIGitize (see page 153)	EXT source is not available.
:EXTernal:DISPlay (see page 264)	OFF (or 0) is the only valid setting.
:MARKer:X1Y1source (see page 346)	EXTernal source is not available.
:MEASure:DUTYcycle (see page 378)	EXTernal source is not available.
:MEASure:FREQuency (see page 380)	EXTernal source is not available.
:MEASure:NDUTy (see page 381)	EXTernal source is not available.
:MEASure:NWIDth (see page 384)	EXTernal source is not available.
:MEASure:PERiod (see page 388)	EXTernal source is not available.
:MEASure:PWIDth (see page 392)	EXTernal source is not available.
:MEASure:TEDGe (see page 407)	EXTernal source is not available.
:MEASure:VTIMe (see page 418)	EXTernal source is not available.
:SBUS<n>:CAN:SOURce (see page 502)	EXTernal cannot be specified as the source.
:SBUS<n>:IIC[:SOURce]:CLOCk (see page 511)	EXTernal cannot be specified as the source.

Command	Differences From InfiniiVision 1000 X-Series Oscilloscopes
:SBUS<n>:IIC[:SOURce]:DATA (see page 512)	EXTernal cannot be specified as the source.
:SBUS<n>:LIN:SOURce (see page 524)	EXTernal cannot be specified as the source.
:SBUS<n>:SPI:SOURce:CLOCk (see page 539)	EXTernal cannot be specified as the source.
:SBUS<n>:SPI:SOURce:FRAMe (see page 541)	EXTernal cannot be specified as the source.
:SBUS<n>:SPI:SOURce:MISO (see page 542)	EXTernal cannot be specified as the source.
:SBUS<n>:SPI:SOURce:MOSI (see page 543)	EXTernal cannot be specified as the source.
:SBUS<n>:UART:SOURce:RX (see page 565)	EXTernal cannot be specified as the source.
:SBUS<n>:UART:SOURce:TX (see page 566)	EXTernal cannot be specified as the source.
:STATus (see page 173)	EXT source is not available.
:TRIGger:PATTern (see page 642)	Pattern triggers have bits for channels 3 and 4 but not for the Ext Trig input, EXTernal cannot be used as an edge source.
:VIEW (see page 176)	EXT source is not available.
:WAVeform:SOURce (see page 684)	EXT source is not available.

Discontinued Commands

Command	Description
:EXTernal:DISPlay (see page 264)	The Ext Trig input cannot be displayed as a digital waveform.
:EXTernal:LABel (see page 265)	
:EXTernal:POSition (see page 267)	

2 Setting Up

Step 1. Install Keysight IO Libraries Suite software / 36
Step 2. Connect and set up the oscilloscope / 37
Step 3. Verify the oscilloscope connection / 39

This chapter explains how to install the Keysight IO Libraries Suite software, connect the oscilloscope to the controller PC, set up the oscilloscope, and verify the oscilloscope connection.

Step 1. Install Keysight IO Libraries Suite software

1. Download the Keysight IO Libraries Suite software from the Keysight web site at:
   - http://www.keysight.com/find/iolib
2. Run the setup file, and follow its installation instructions.

Step 2. Connect and set up the oscilloscope

The 1200 X-Series and EDUX11052A/G oscilloscopes have two interfaces you can use for programming:

- USB (device port).
- LAN. To configure the LAN interface, press the **[Utility]** key on the front panel, then press the **I/O** softkey, then press the **Configure** softkey.

These interfaces are always active.



Figure 1 Control Connectors on Rear Panel

Using the USB (Device) Interface

1 Connect a USB cable from the controller PC's USB port to the "USB DEVICE" port on the back of the oscilloscope.

This is a USB 2.0 high-speed port.

Using the LAN Interface

1 If the controller PC is not already connected to the local area network (LAN), do that first.

2 Contact your network administrator about adding the oscilloscope to the network.

Find out if automatic configuration via DHCP or AutoIP can be used. Also, find out whether your network supports Dynamic DNS or Multicast DNS.

If automatic configuration is not supported, get the oscilloscope's network parameters (hostname, domain, IP address, subnet mask, gateway IP, DNS IP, etc.).

3 Connect the oscilloscope to the local area network (LAN) by inserting LAN cable into the "LAN" port on the back of the oscilloscope.

4 Configure the oscilloscope's LAN interface:

   a Press the **Configure** softkey until "LAN" is selected.

   b Press the **LAN Settings** softkey.

   c Press the **Config** softkey, and enable all the configuration options supported by your network.

   d If automatic configuration is not supported, press the **Addresses** softkey.

   Use the **Modify** softkey (and the other softkeys and the Entry knob) to enter the IP Address, Subnet Mask, Gateway IP, and DNS IP values.

   When you are done, press the **[Back up]** key.

   e Press the **Host name** softkey. Use the softkeys and the Entry knob to enter the Host name.

   When you are done, press the **[Back up]** key.

Step 3. Verify the oscilloscope connection

1 On the controller PC, click on the Keysight IO Control icon in the taskbar and choose **Connection Expert** from the popup menu.



2 In the Keysight Connection Expert application, instruments connected to the controller's USB interface should automatically appear in the Instruments tab.



3 Test some commands on the instrument:

a In the Details for the selected instrument, click **Send Commands To This Instrument**.



b In the Keysight Interactive IO application, enter commands in the **Command** field and press **Send Command**, **Read Response**, or **Send & Read**.



c Choose **Connect > Exit** from the menu to exit the Keysight Interactive IO application.

4 In the Keysight Connection Expert application, choose **File > Exit** from the menu to exit the application.

3 Getting Started

Basic Oscilloscope Program Structure / 42
Programming the Oscilloscope / 44
Other Ways of Sending Commands / 53

This chapter gives you an overview of programming the InfiniiVision 1200 X-Series and EDUX11052A/G oscilloscopes. It describes basic oscilloscope program structure and shows how to program the oscilloscope using a few simple examples.

The getting started examples show how to send oscilloscope setup, data capture, and query commands, and they show how to read query results.

NOTE

Language for Program Examples

The programming examples in this guide are written in Visual Basic using the Keysight VISA COM library.

Basic Oscilloscope Program Structure

The following figure shows the basic structure of every program you will write for the oscilloscope.



Initializing

To ensure consistent, repeatable performance, you need to start the program, controller, and oscilloscope in a known state. Without correct initialization, your program may run correctly in one instance and not in another. This might be due to changes made in configuration by previous program runs or from the front panel of the oscilloscope.

- Program initialization defines and initializes variables, allocates memory, or tests system configuration.
- Controller initialization ensures that the interface to the oscilloscope is properly set up and ready for data transfer.
- Oscilloscope initialization sets the channel configuration, channel labels, threshold voltages, trigger specification, trigger mode, timebase, and acquisition type.

Capturing Data

Once you initialize the oscilloscope, you can begin capturing data for analysis. Remember that while the oscilloscope is responding to commands from the controller, it is not performing acquisitions. Also, when you change the oscilloscope configuration, any data already captured will most likely be rendered.

To collect data, you use the :DIGitize command. This command clears the waveform buffers and starts the acquisition process. Acquisition continues until acquisition memory is full, then stops. The acquired data is displayed by the oscilloscope, and the captured data can be measured, stored in acquisition memory in the oscilloscope, or transferred to the controller for further analysis. Any additional commands sent while :DIGitize is working are buffered until :DIGitize is complete.

You could also put the oscilloscope into run mode, then use a wait loop in your program to ensure that the oscilloscope has completed at least one acquisition before you make a measurement. Keysight does not recommend this because the needed length of the wait loop may vary, causing your program to fail. :DIGitize, on the other hand, ensures that data capture is complete. Also, :DIGitize, when complete, stops the acquisition process so that all measurements are on displayed data, not on a constantly changing data set.

Analyzing Captured Data

After the oscilloscope has completed an acquisition, you can find out more about the data, either by using the oscilloscope measurements or by transferring the data to the controller for manipulation by your program. Built-in measurements include: frequency, duty cycle, period, positive pulse width, and negative pulse width.

Using the :WAVeform commands, you can transfer the data to your controller. You may want to display the data, compare it to a known good measurement, or simply check logic patterns at various time intervals in the acquisition.

Programming the Oscilloscope

- "Referencing the IO Library" on page 44
- "Opening the Oscilloscope Connection via the IO Library" on page 45
- "Using :AUToscale to Automate Oscilloscope Setup" on page 46
- "Using Other Oscilloscope Setup Commands" on page 46
- "Capturing Data with the :DIGitize Command" on page 47
- "Reading Query Responses from the Oscilloscope" on page 49
- "Reading Query Results into String Variables" on page 50
- "Reading Query Results into Numeric Variables" on page 50
- "Reading Definite-Length Block Query Response Data" on page 50
- "Sending Multiple Queries and Reading Results" on page 51
- "Checking Instrument Status" on page 52

Referencing the IO Library

No matter which instrument programming library you use (SICL, VISA, or VISA COM), you must reference the library from your program.

In C/C++, you must tell the compiler where to find the include and library files (see the Keysight IO Libraries Suite documentation for more information).

To reference the Keysight VISA COM library in Visual Basic for Applications (VBA, which comes with Microsoft Office products like Excel):

1 Choose **Tools > References...** from the main menu.

2 In the References dialog, check the "VISA COM 5.9 Type Library".



3 Click **OK**.

To reference the Keysight VISA COM library in Microsoft Visual Basic 6.0:

1 Choose **Project > References...** from the main menu.

2 In the References dialog, check the "VISA COM 5.9 Type Library".

3 Click **OK**.

Opening the Oscilloscope Connection via the IO Library

PC controllers communicate with the oscilloscope by sending and receiving messages over a remote interface. Once you have opened a connection to the oscilloscope over the remote interface, programming instructions normally appear as ASCII character strings embedded inside write statements of the programing language. Read statements are used to read query responses from the oscilloscope.

For example, when using the Keysight VISA COM library in Visual Basic (after opening the connection to the instrument using the ResourceManager object's Open method), the FormattedIO488 object's WriteString, WriteNumber, WriteList, or WriteIEEEBlock methods are used for sending commands and queries. After a query is sent, the response is read using the ReadString, ReadNumber, ReadList, or ReadIEEEBlock methods.

The following Visual Basic statements open the connection and send a command that turns on the oscilloscope's label display.

```
Dim myMgr As VisaComLib.ResourceManager
Dim myScope As VisaComLib.FormattedIO488

Set myMgr = New VisaComLib.ResourceManager
Set myScope = New VisaComLib.FormattedIO488

' Open the connection to the oscilloscope. Get the VISA Address from the
' Keysight Connection Expert (installed with Keysight IO Libraries Suite
).
Set myScope.IO = myMgr.Open("<VISA Address>")

' Send a command.
myScope.WriteString ":DISPlay:LABel ON"
```

The ":DISPLAY:LABEL ON" in the above example is called a *program message*. Program messages are explained in more detail in "Program Message Syntax" on page 829.

Initializing the Interface and the Oscilloscope

To make sure the bus and all appropriate interfaces are in a known state, begin every program with an initialization statement. When using the Keysight VISA COM library, you can use the resource session object's Clear method to clears the interface buffer:

```
Dim myMgr As VisaComLib.ResourceManager
Dim myScope As VisaComLib.FormattedIO488

Set myMgr = New VisaComLib.ResourceManager
Set myScope = New VisaComLib.FormattedIO488

' Open the connection to the oscilloscope. Get the VISA Address from the
' Keysight Connection Expert (installed with Keysight IO Libraries Suite
).
Set myScope.IO = myMgr.Open("<VISA Address>")

' Clear the interface buffer and set the interface timeout to 10 seconds
.
myScope.IO.Clear
myScope.IO.Timeout = 10000
```

When you are using GPIB, CLEAR also resets the oscilloscope's parser. The parser is the program which reads in the instructions which you send it.

After clearing the interface, initialize the instrument to a preset state:

```
myScope.WriteString "*RST"
```

NOTE

Information for Initializing the Instrument

The actual commands and syntax for initializing the instrument are discussed in Chapter 5, "Common (*) Commands," starting on page 117.

Refer to the Keysight IO Libraries Suite documentation for information on initializing the interface.

Using :AUToscale to Automate Oscilloscope Setup

The :AUToscale command performs a very useful function for unknown waveforms by setting up the vertical channel, time base, and trigger level of the instrument.

The syntax for the autoscale command is:

```
myScope.WriteString ":AUToscale"
```

Using Other Oscilloscope Setup Commands

A typical oscilloscope setup would set the vertical range and offset voltage, the horizontal range, delay time, delay reference, trigger mode, trigger level, and slope. An example of the commands that might be sent to the oscilloscope are:

```
myScope.WriteString ":CHANnel1:PROBe 10"
myScope.WriteString ":CHANnel1:RANGe 16"
myScope.WriteString ":CHANnel1:OFFSet 1.00"
myScope.WriteString ":TIMebase:MODE MAIN"
myScope.WriteString ":TIMebase:RANGe 1E-3"
myScope.WriteString ":TIMebase:DELay 100E-6"
```

Vertical is set to 16 V full-scale (2 V/div) with center of screen at 1 V and probe attenuation set to 10. This example sets the time base at 1 ms full-scale (100 ms/div) with a delay of 100 µs.

Example Oscilloscope Setup Code

This program demonstrates the basic command structure used to program the oscilloscope.

```
' Initialize the instrument interface to a known state.
myScope.IO.Clear
myScope.IO.Timeout = 10000   ' Set interface timeout to 10 seconds.

' Initialize the instrument to a preset state.
myScope.WriteString "*RST"

' Set the time base mode to normal with the horizontal time at
' 50 ms/div with 0 s of delay referenced at the center of the
' graticule.
myScope.WriteString ":TIMebase:RANGe 5E-4"   ' Time base to 50 us/div.
myScope.WriteString ":TIMebase:DELay 0"      ' Delay to zero.
myScope.WriteString ":TIMebase:REFerence CENTer"   ' Display ref. at
                                                   ' center.

' Set the vertical range to 1.6 volts full scale with center screen
' at -0.4 volts with 10:1 probe attenuation and DC coupling.
myScope.WriteString ":CHANnel1:PROBe 10"     ' Probe attenuation
                                              ' to 10:1.
myScope.WriteString ":CHANnel1:RANGe 1.6"    ' Vertical range
                                              ' 1.6 V full scale.
myScope.WriteString ":CHANnel1:OFFSet -0.4"  ' Offset to -0.4.
myScope.WriteString ":CHANnel1:COUPling DC"  ' Coupling to DC.

' Configure the instrument to trigger at -0.4 volts with normal
' triggering.
myScope.WriteString ":TRIGger:SWEep NORMal"   ' Normal triggering.
myScope.WriteString ":TRIGger:LEVel -0.4"     ' Trigger level to -0.4.
myScope.WriteString ":TRIGger:SLOPe POSitive" ' Trigger on pos. slope.

' Configure the instrument for normal acquisition.
myScope.WriteString ":ACQuire:TYPE NORMal"   ' Normal acquisition.
```

Capturing Data with the :DIGitize Command

The :DIGitize command captures data that meets the specifications set up by the :ACQuire subsystem. When the digitize process is complete, the acquisition is stopped. The captured data can then be measured by the instrument or transferred to the controller for further analysis. The captured data consists of two parts: the waveform data record, and the preamble.

NOTE

Ensure New Data is Collected

When you change the oscilloscope configuration, the waveform buffers are cleared. Before doing a measurement, send the :DIGitize command to the oscilloscope to ensure new data has been collected.

When you send the :DIGitize command to the oscilloscope, the specified channel signal is digitized with the current :ACQuire parameters. To obtain waveform data, you must specify the :WAVeform parameters for the SOURce channel, the FORMat type, and the number of POINts prior to sending the :WAVeform:DATA? query.

NOTE

Set :TIMebase:MODE to MAIN when using :DIGitize

:TIMebase:MODE must be set to MAIN to perform a :DIGitize command or to perform any :WAVeform subsystem query. A "Settings conflict" error message will be returned if these commands are executed when MODE is set to ROLL, XY, or WINDow (zoomed). Sending the *RST (reset) command will also set the time base mode to normal.

The number of data points comprising a waveform varies according to the number requested in the :ACQuire subsystem. The :ACQuire subsystem determines the number of data points, type of acquisition, and number of averages used by the :DIGitize command. This allows you to specify exactly what the digitized information contains.

The following program example shows a typical setup:

```
myScope.WriteString ":ACQuire:TYPE AVERage"
myScope.WriteString ":ACQuire:COMPlete 100"
myScope.WriteString ":ACQuire:COUNt 8"
myScope.WriteString ":DIGitize CHANnel1"
myScope.WriteString ":WAVeform:SOURce CHANnel1"
myScope.WriteString ":WAVeform:FORMat BYTE"
myScope.WriteString ":WAVeform:POINts 500"
myScope.WriteString ":WAVeform:DATA?"
```

This setup places the instrument into the averaged mode with eight averages. This means that when the :DIGitize command is received, the command will execute until the signal has been averaged at least eight times.

After receiving the :WAVeform:DATA? query, the instrument will start passing the waveform information.

Digitized waveforms are passed from the instrument to the controller by sending a numerical representation of each digitized point. The format of the numerical representation is controlled with the :WAVeform:FORMat command and may be selected as BYTE, WORD, or ASCii.

The easiest method of transferring a digitized waveform depends on data structures, formatting available and I/O capabilities. You must scale the integers to determine the voltage value of each point. These integers are passed starting with the left most point on the instrument's display.

For more information, see the waveform subsystem commands and corresponding program code examples in Chapter 29, ":WAVeform Commands," starting on page 663.

NOTE

Aborting a Digitize Operation Over the Programming Interface

When using the programming interface, you can abort a digitize operation by sending a Device Clear over the bus (for example, myScope.IO.Clear).

Reading Query Responses from the Oscilloscope

After receiving a query (command header followed by a question mark), the instrument interrogates the requested function and places the answer in its output queue. The answer remains in the output queue until it is read or another command is issued. When read, the answer is transmitted across the interface to the designated listener (typically a controller).

The statement for reading a query response message from an instrument's output queue typically has a format specification for handling the response message.

When using the VISA COM library in Visual Basic, you use different read methods (ReadString, ReadNumber, ReadList, or ReadIEEEBlock) for the various query response formats. For example, to read the result of the query command :CHANnel1:COUPling? you would execute the statements:

```
myScope.WriteString ":CHANnel1:COUPling?"
Dim strQueryResult As String
strQueryResult = myScope.ReadString
```

This reads the current setting for the channel one coupling into the string variable strQueryResult.

All results for queries (sent in one program message) must be read before another program message is sent.

Sending another command before reading the result of the query clears the output buffer and the current response. This also causes an error to be placed in the error queue.

Executing a read statement before sending a query causes the controller to wait indefinitely.

The format specification for handling response messages depends on the programming language.

Reading Query Results into String Variables

The output of the instrument may be numeric or character data depending on what is queried. Refer to the specific command descriptions for the formats and types of data returned from queries.

NOTE

Express String Variables Using Exact Syntax

In Visual Basic, string variables are case sensitive and must be expressed exactly the same each time they are used.

The following example shows numeric data being returned to a string variable:

```
myScope.WriteString ":CHANnel1:RANGe?"
Dim strQueryResult As String
strQueryResult = myScope.ReadString
MsgBox "Range (string):" + strQueryResult
```

After running this program, the controller displays:

Range (string): +40.0E+00

Reading Query Results into Numeric Variables

The following example shows numeric data being returned to a numeric variable:

```
myScope.WriteString ":CHANnel1:RANGe?"
Dim varQueryResult As Variant
varQueryResult = myScope.ReadNumber
MsgBox "Range (variant):" + CStr(varQueryResult)
```

After running this program, the controller displays:

Range (variant): 40

Reading Definite-Length Block Query Response Data

Definite-length block query response data allows any type of device-dependent data to be transmitted over the system interface as a series of 8-bit binary data bytes. This is particularly useful for sending large quantities of data or 8-bit extended ASCII codes. The syntax is a pound sign (#) followed by a non-zero digit representing the number of digits in the decimal integer. After the non-zero digit is the decimal integer that states the number of 8-bit data bytes being sent. This is followed by the actual data.

For example, for transmitting 1000 bytes of data, the syntax would be:



Figure 2 Definite-length block response data

The "8" states the number of digits that follow, and "00001000" states the number of bytes to be transmitted.

The VISA COM library's ReadIEEEBlock and WriteIEEEBlock methods understand the definite-length block syntax, so you can simply use variables that contain the data:

```
' Read oscilloscope setup using ":SYSTem:SETup?" query.
myScope.WriteString ":SYSTem:SETup?"
Dim varQueryResult As Variant
varQueryResult = myScope.ReadIEEEBlock(BinaryType_UI1)

' Write learn string back to oscilloscope using ":SYSTem:SETup" command:
myScope.WriteIEEEBlock ":SYSTem:SETup ", varQueryResult
```

Sending Multiple Queries and Reading Results

You can send multiple queries to the instrument within a single command string, but you must also read them back as a single query result. This can be accomplished by reading them back into a single string variable, multiple string variables, or multiple numeric variables.

For example, to read the :TIMebase:RANGe?;DELay? query result into a single string variable, you could use the commands:

```
myScope.WriteString ":TIMebase:RANGe?;DELay?"
Dim strQueryResult As String
strQueryResult = myScope.ReadString
MsgBox "Timebase range; delay:" + strQueryResult
```

When you read the result of multiple queries into a single string variable, each response is separated by a semicolon. For example, the output of the previous example would be:

```
Timebase range; delay: <range_value>;<delay_value>
```

To read the :TIMebase:RANGe?;DELay? query result into multiple string variables, you could use the ReadList method to read the query results into a string array variable using the commands:

```
myScope.WriteString ":TIMebase:RANGe?;DELay?"
Dim strResults() As String
strResults() = myScope.ReadList(ASCIIType_BSTR)
MsgBox "Timebase range: " + strResults(0) + ", delay: " + strResults(1)
```

To read the :TIMebase:RANGe?;DELay? query result into multiple numeric variables, you could use the ReadList method to read the query results into a variant array variable using the commands:

```
myScope.WriteString ":TIMebase:RANGe?;DELay?"
Dim varResults() As Variant
varResults() = myScope.ReadList
MsgBox "Timebase range: " + FormatNumber(varResults(0) * 1000, 4) + _
       " ms, delay: " + FormatNumber(varResults(1) * 1000000, 4) + " us"
```

Checking Instrument Status

Status registers track the current status of the instrument. By checking the instrument status, you can find out whether an operation has been completed, whether the instrument is receiving triggers, and more.

For more information, see Chapter 34, “Status Reporting,” starting on page 795 which explains how to check the status of the instrument.

Other Ways of Sending Commands

Standard Commands for Programmable Instrumentation (SCPI) can also be sent via a Telnet socket or through the Browser Web Control:

- "Telnet Sockets" on page 53
- "Sending SCPI Commands Using Browser Web Control" on page 53

Telnet Sockets

The following information is provided for programmers who wish to control the oscilloscope with SCPI commands in a Telnet session.

To connect to the oscilloscope via a telnet socket, issue the following command:

```
telnet <hostname> 5024
```

where <hostname> is the hostname of the oscilloscope. This will give you a command line with prompt.

For a command line without a prompt, use port 5025. For example:

```
telnet <hostname> 5025
```

Sending SCPI Commands Using Browser Web Control

To send SCPI commands using the Web Interface feature, establish a connection to the oscilloscope via LAN as described in the *User's Guide*. When you make the connection to the oscilloscope via LAN and the instrument's welcome page is displayed, select the **Control Instrument** tab, then select the **Use Instrument IO** link.

4 Commands Quick Reference

Command Summary / 56
Syntax Elements / 113

Command Summary

- Common (*) Commands Summary (see page 57)
- Root (:) Commands Summary (see page 60)
- :ABUS Commands Summary (see page 62)
- :ACQuire Commands Summary (see page 63)
- :CALibrate Commands Summary (see page 63)
- :CHANnel<n> Commands Summary (see page 64)
- :DEMO Commands Summary (see page 66)
- :DISPlay Commands Summary (see page 66)
- :DVM Commands Summary (see page 67)
- :EXTernal Trigger Commands Summary (see page 68)
- :FFT Commands Summary (see page 69)
- :FRANalysis Commands Summary (see page 69)
- :FUNCtion Commands Summary (see page 71)
- :HARDcopy Commands Summary (see page 72)
- :LISTer Commands Summary (see page 74)
- :MARKer Commands Summary (see page 74)
- :MEASure Commands Summary (see page 76)
- :MTESt Commands Summary (see page 86)
- :RECall Commands Summary (see page 88)
- :SAVE Commands Summary (see page 89)
- General :SBUS<n> Commands Summary (see page 91)
- :SBUS<n>:CAN Commands Summary (see page 91)
- :SBUS<n>:IIC Commands Summary (see page 93)
- :SBUS<n>:LIN Commands Summary (see page 94)
- :SBUS<n>:SPI Commands Summary (see page 95)
- :SBUS<n>:UART Commands Summary (see page 97)
- :SYSTem Commands Summary (see page 99)
- :TIMebase Commands Summary (see page 101)
- General :TRIGger Commands Summary (see page 102)
- :TRIGger[:EDGE] Commands Summary (see page 103)
- :TRIGger:GLITch Commands Summary (see page 103)
- :TRIGger:PATTern Commands Summary (see page 105)
- :TRIGger:SHOLd Commands Summary (see page 105)

- :TRIGger:TRANsition Commands Summary (see page 106)
- :TRIGger:TV Commands Summary (see page 106)
- :WAVeform Commands Summary (see page 107)
- :WGEN Commands Summary (see page 109)
- :WMEMory<r> Commands Summary (see page 111)

Table 2 Common (*) Commands Summary

Command	Query	Options and Query Returns
*CLS (see page 121)	n/a	n/a
*ESE <mask> (see page 122)	*ESE? (see page 123)	<mask> ::= 0 to 255; an integer in NR1 format: Bit Weight Name Enables --- ------ ---- ---------- 7 128 PON Power On 6 64 URQ User Request 5 32 CME Command Error 4 16 EXE Execution Error 3 8 DDE Dev. Dependent Error 2 4 QYE Query Error 1 2 RQL Request Control 0 1 OPC Operation Complete
n/a	*ESR? (see page 124)	<status> ::= 0 to 255; an integer in NR1 format
n/a	*IDN? (see page 124)	KEYSIGHT TECHNOLOGIES,<model>,<serial number>,X.XX.XX <model> ::= the model number of the instrument <serial number> ::= the serial number of the instrument <X.XX.XX> ::= the software revision of the instrument
n/a	*LRN? (see page 127)	<learn_string> ::= current instrument setup as a block of data in IEEE 488.2 # format
*OPC (see page 128)	*OPC? (see page 128)	ASCII "1" is placed in the output queue when all pending device operations have completed.

Table 2 Common (*) Commands Summary (continued)

Command	Query	Options and Query Returns
n/a	*OPT? (see page 129)	<return_value> ::= 0,0,<license info> <license info> ::= <All field>, <reserved>, <reserved>, <reserved>, <Memory>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <Segmented Memory>, <Mask Test>, <reserved>, <Bandwidth>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <Educator's Kit>, <Waveform Generator>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <Digital Voltmeter>, <reserved>, <reserved>, <reserved>, <Remote Command Logging>, <reserved>, <reserved>, <reserved> <All field> ::= {0 | All} <reserved> ::= 0 <Memory> ::= {0 | MEMUP} <Low Speed Serial> ::= {0 | EMBD} <Automotive Serial> ::= {0 | AUTO} <Segmented Memory> ::= {0 | SGM} <Mask Test> ::= {0 | MASK} <Bandwidth> ::= {0 | BW10 | BW20} <Educator's Kit> ::= {0 | EDK} <Waveform Generator> ::= {0 | WAVEGEN} <Digital Voltmeter> ::= {0 | DVM} <Remote Command Logging> ::= {0 | RML}
*RCL <value> (see page 130)	n/a	<value> ::= {0 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9}
*RST (see page 131)	n/a	See *RST (Reset) (see page 131)

Table 2 Common (*) Commands Summary (continued)

Command	Query	Options and Query Returns
*SAV <value> (see page 134)	n/a	<value> ::= {0 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9}
*SRE <mask> (see page 135)	*SRE? (see page 136)	<mask> ::= sum of all bits that are set, 0 to 255; an integer in NR1 format. <mask> ::= following values: Bit Weight Name Enables --- ------ ---- ---------- 7 128 OPER Operation Status Reg 6 64 ---- (Not used.) 5 32 ESB Event Status Bit 4 16 MAV Message Available 3 8 ---- (Not used.) 2 4 MSG Message 1 2 USR User 0 1 TRG Trigger
n/a	*STB? (see page 137)	<value> ::= 0 to 255; an integer in NR1 format, as shown in the following: Bit Weight Name "1" Indicates --- ------ ---- --------------- 7 128 OPER Operation status condition occurred. 6 64 RQS/ MSS Instrument is requesting service. 5 32 ESB Enabled event status condition occurred. 4 16 MAV Message available. 3 8 ---- (Not used.) 2 4 MSG Message displayed. 1 2 USR User event condition occurred. 0 1 TRG A trigger occurred.
*TRG (see page 139)	n/a	n/a
n/a	*TST? (see page 140)	<result> ::= 0 or non-zero value; an integer in NR1 format
*WAI (see page 141)	n/a	n/a

Table 3 Root (:) Commands Summary

Command	Query	Options and Query Returns
n/a	:AER? (see page 146)	{0 | 1}; an integer in NR1 format
:AUTOscale [<source>[,..,<source>]] (see page 147)	n/a	<source> ::= CHANnel<n> <source> can be repeated up to 5 times <n> ::= 1 to (# analog channels) in NR1 format
:AUTOscale:AMODE <value> (see page 149)	:AUTOscale:AMODE? (see page 149)	<value> ::= {NORMal | CURRent}}
:AUTOscale:CHANnels <value> (see page 150)	:AUTOscale:CHANnels? (see page 150)	<value> ::= {ALL | DISPlayed}}
:AUTOscale:FDEBug {{0 | OFF} | {1 | ON}} (see page 151)	:AUTOscale:FDEBug? (see page 151)	{0 | 1}
:BLANk [<source>] (see page 152)	n/a	<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r> | ABUS | EXT} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format EXT available on 2-channel oscilloscopes only
:DIGitize [<source>[,..,<source>]] (see page 153)	n/a	<source> ::= {CHANnel<n> | FUNCtion | MATH | SBUS{1} | FFT | ABUS | EXT} <source> can be repeated up to 5 times <n> ::= 1 to (# analog channels) in NR1 format EXT available on 2-channel oscilloscopes only
:MTEenable <n> (see page 155)	:MTEenable? (see page 155)	<n> ::= 16-bit integer in NR1 format
n/a	:MTERegister[:EVENt]? (see page 157)	<n> ::= 16-bit integer in NR1 format
:OPEE <n> (see page 159)	:OPEE? (see page 160)	<n> ::= 15-bit integer in NR1 format
n/a	:OPERregister:CONDition? (see page 161)	<n> ::= 15-bit integer in NR1 format

Table 3 Root (:) Commands Summary (continued)

Command	Query	Options and Query Returns
n/a	:OPERegister[:EVENt]? (see page 163)	<n> ::= 15-bit integer in NR1 format
:OVLenable <mask> (see page 165)	:OVLenable? (see page 165)	<mask> ::= 16-bit integer in NR1 format as shown: Bit Weight Input --- ------ ---------- 10 1024 Ext Trigger Fault 9 512 Channel 4 Fault 8 256 Channel 3 Fault 7 128 Channel 2 Fault 6 64 Channel 1 Fault 4 16 Ext Trigger OVL 3 8 Channel 4 OVL 2 4 Channel 3 OVL 1 2 Channel 2 OVL 0 1 Channel 1 OVL
n/a	:OVLRegister? (see page 167)	<value> ::= integer in NR1 format. See OVLenable for <value>
:PRINt [<options>] (see page 169)	n/a	<options> ::= [<print option>][,..,<print option>] <print option> ::= {COLor | GRAYscale | PRINter0 | PRINter1 | BMP8bit | BMP | PNG | NOFactors | FACTors} <print option> can be repeated up to 5 times.
:RUN (see page 170)	n/a	n/a
n/a	:SERial (see page 171)	<return value> ::= unquoted string containing serial number
:SINGle (see page 172)	n/a	n/a
n/a	:STATus? <display> (see page 173)	{0 | 1} <display> ::= {CHANnel<n> | FUNCtion | MATH | SBUS{1} | FFT | WMEMory<r> | ABUS | EXT} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format EXT available on 2-channel oscilloscopes only
:STOP (see page 174)	n/a	n/a

Table 3 Root (:) Commands Summary (continued)

Command	Query	Options and Query Returns
n/a	:TER? (see page 175)	{0 | 1}
:VIEW <source> (see page 176)	n/a	<source> ::= {CHANnel<n> | FUNCtion | MATH | SBUS{1} | FFT | WMEMory<r> | ABUS | EXT} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format EXT available on 2-channel oscilloscopes only

Table 4 :ABUS Commands Summary

Command	Query	Options and Query Returns
:ABUS:BIT<m> {{0 | OFF} | {1 | ON}} (see page 179)	:ABUS:BIT<m>? (see page 179)	{0 | 1} <m> ::= an integer in NR1 format
:ABUS:BITS <channel_list>, {{0 | OFF} | {1 | ON}} (see page 180)	:ABUS:BITS? (see page 180)	<channel_list>, {0 | 1} <channel_list> ::= (@<m>,<m>:<m> ...) where "," is separator and ":" is range <m> ::= an integer in NR1 format
:ABUS:CLEar (see page 182)	n/a	n/a
:ABUS:DISPlay {{0 | OFF} | {1 | ON}} (see page 183)	:ABUS:DISPlay? (see page 183)	{0 | 1}
:ABUS:LABel <string> (see page 184)	:ABUS:LABel? (see page 184)	<string> ::= quoted ASCII string up to 10 characters
:ABUS:MASK <mask> (see page 185)	:ABUS:MASK? (see page 185)	<mask> ::= 32-bit integer in decimal, <nondecimal>, or <string> <nondecimal> ::= #Hnn...n where n ::= {0,..,9 | A,..,F} for hexadecimal <nondecimal> ::= #Bnn...n where n ::= {0 | 1} for binary <string> ::= "0xnn...n" where n ::= {0,..,9 | A,..,F} for hexadecimal

Table 5 :ACQuire Commands Summary

Command	Query	Options and Query Returns
:ACQuire:COMPlete <complete> (see page 189)	:ACQuire:COMPlete? (see page 189)	<complete> ::= 100; an integer in NR1 format
:ACQuire:COUNt <count> (see page 190)	:ACQuire:COUNt? (see page 190)	<count> ::= an integer from 2 to 65536 in NR1 format
:ACQuire:MODE <mode> (see page 191)	:ACQuire:MODE? (see page 191)	<mode> ::= {RTIMe | SEGMented}
n/a	:ACQuire:POINts? (see page 192)	<# points> ::= an integer in NR1 format
:ACQuire:SEGMented:ANALyze (see page 193)	n/a	n/a (with SGM license)
:ACQuire:SEGMented:COUNt <count> (see page 194)	:ACQuire:SEGMented:COUNt? (see page 194)	<count> ::= an integer from 2 to 500 in NR1 format (with SGM license)
:ACQuire:SEGMented:INDex <index> (see page 195)	:ACQuire:SEGMented:INDex? (see page 195)	<index> ::= an integer from 1 to 500 in NR1 format (with SGM license)
n/a	:ACQuire:SRATe? (see page 198)	<sample_rate> ::= sample rate (samples/s) in NR3 format
:ACQuire:TYPE <type> (see page 199)	:ACQuire:TYPE? (see page 199)	<type> ::= {NORMal | AVERage | HRESolution | PEAK}

Table 6 :CALibrate Commands Summary

Command	Query	Options and Query Returns
n/a	:CALibrate:DATE? (see page 203)	<return value> ::= <year>,<month>,<day>; all in NR1 format
:CALibrate:LABel <string> (see page 204)	:CALibrate:LABel? (see page 204)	<string> ::= quoted ASCII string up to 32 characters
:CALibrate:OUTPut <signal> (see page 205)	:CALibrate:OUTPut? (see page 205)	<signal> ::= {TRIGgers | MASK | WAVEgen}
n/a	:CALibrate:PROTected? (see page 206)	{"PROTected" | "UNPRotected"}
:CALibrate:STARt (see page 207)	n/a	n/a

Table 6 :CALibrate Commands Summary (continued)

Command	Query	Options and Query Returns
n/a	:CALibrate:STATus? (see page 208)	<return value> ::= <status_code>,<status_string> <status_code> ::= an integer status code <status_string> ::= an ASCII status string
n/a	:CALibrate:TEMPerature? (see page 209)	<return value> ::= degrees C delta since last cal in NR3 format
n/a	:CALibrate:TIME? (see page 210)	<return value> ::= <hours>,<minutes>,<seconds>; all in NR1 format

Table 7 :CHANnel<n> Commands Summary

Command	Query	Options and Query Returns
:CHANnel<n>:BANDwidth <limit> (see page 214)	:CHANnel<n>:BANDwidth? [MAXimum] (see page 214)	<limit> ::= 25E6 in NR3 format <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:BWLimit {{0 | OFF} | {1 | ON}} (see page 215)	:CHANnel<n>:BWLimit? (see page 215)	{0 | 1} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:COUPling <coupling> (see page 216)	:CHANnel<n>:COUPling? (see page 216)	<coupling> ::= {AC | DC} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:DISPlay {{0 | OFF} | {1 | ON}} (see page 217)	:CHANnel<n>:DISPlay? (see page 217)	{0 | 1} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:IMPedance <impedance> (see page 218)	:CHANnel<n>:IMPedance? (see page 218)	<impedance> ::= ONEMeg <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:INVert {{0 | OFF} | {1 | ON}} (see page 219)	:CHANnel<n>:INVert? (see page 219)	{0 | 1} <n> ::= 1 to (# analog channels) in NR1 format

Table 7 :CHANnel<n> Commands Summary (continued)

Command	Query	Options and Query Returns
:CHANnel<n>:LABel <string> (see page 220)	:CHANnel<n>:LABel? (see page 220)	<string> ::= any series of 10 or less ASCII characters enclosed in quotation marks <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:OFFSet <offset>[suffix] (see page 221)	:CHANnel<n>:OFFSet? (see page 221)	<offset> ::= Vertical offset value in NR3 format [suffix] ::= {V | mV} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:PROBe <attenuation> (see page 222)	:CHANnel<n>:PROBe? (see page 222)	<attenuation> ::= Probe attenuation ratio in NR3 format <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:PROBe:HEAD[:TYPE] <head_param> (see page 223)	:CHANnel<n>:PROBe:HEAD[:TYPE]? (see page 223)	<head_param> ::= {SEND0 | SEND6 | SEND12 | SEND20 | DIFF0 | DIFF6 | DIFF12 | DIFF20 | NONE} <n> ::= 1 to (# analog channels) in NR1 format
n/a	:CHANnel<n>:PROBe:ID? (see page 224)	<probe id> ::= unquoted ASCII string up to 11 characters <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:PROBe:SKEW <skew_value> (see page 225)	:CHANnel<n>:PROBe:SKEW? (see page 225)	<skew_value> ::= -100 ns to +100 ns in NR3 format <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:PROBe:STYPe <signal type> (see page 226)	:CHANnel<n>:PROBe:STYPe? (see page 226)	<signal type> ::= {DIFFerential | SINGle} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:PROTection (see page 227)	:CHANnel<n>:PROTection? (see page 227)	NORM <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:RANGe <range>[suffix] (see page 228)	:CHANnel<n>:RANGe? (see page 228)	<range> ::= Vertical full-scale range value in NR3 format [suffix] ::= {V | mV} <n> ::= 1 to (# analog channels) in NR1 format

Table 7 :CHANnel<n> Commands Summary (continued)

Command	Query	Options and Query Returns
:CHANnel<n>:SCALe <scale>[suffix] (see page 229)	:CHANnel<n>:SCALe? (see page 229)	<scale> ::= Vertical units per division value in NR3 format [suffix] ::= {V | mV} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:UNITs <units> (see page 230)	:CHANnel<n>:UNITs? (see page 230)	<units> ::= {VOLT | AMPere} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:VERNier {{0 | OFF} | {1 | ON}} (see page 231)	:CHANnel<n>:VERNier? (see page 231)	{0 | 1} <n> ::= 1 to (# analog channels) in NR1 format

Table 8 :DEMO Commands Summary

Command	Query	Options and Query Returns
:DEMO:FUNCtion <signal> (see page 234)	:DEMO:FUNCtion? (see page 235)	<signal> ::= {SINusoid | NOISy | LFSine | AM | RFBurst | FMBurst | HARMonics | COUPling | RINGing | SINGle | CLK | TRANsition | BURSt | GLITch | CAN | LIN}
:DEMO:OUTPut {{0 | OFF} | {1 | ON}} (see page 236)	:DEMO:OUTPut? (see page 236)	{0 | 1}

Table 9 :DISPlay Commands Summary

Command	Query	Options and Query Returns
:DISPlay:ANNotation {{0 | OFF} | {1 | ON}} (see page 239)	:DISPlay:ANNotation? (see page 239)	{0 | 1}
:DISPlay:ANNotation:BACKground <mode> (see page 240)	:DISPlay:ANNotation:BACKground? (see page 240)	<mode> ::= {OPAQue | INVerted | TRANsparent}
:DISPlay:ANNotation:COLor <color> (see page 241)	:DISPlay:ANNotation:COLor? (see page 241)	<color> ::= {CH1 | CH2 | CH3 | CH4 | DIG | MATH | REF | MARKer | WHITe | RED}
:DISPlay:ANNotation:TEXT <string> (see page 242)	:DISPlay:ANNotation:TEXT? (see page 242)	<string> ::= quoted ASCII string (up to 254 characters)

Table 9 :DISPlay Commands Summary (continued)

Command	Query	Options and Query Returns
:DISPlay:CLEar (see page 243)	n/a	n/a
n/a	:DISPlay:DATA? [<format>][,][<palette>] (see page 244)	<format> ::= {BMP | BMP8bit | PNG} <palette> ::= {COLor | GRAYscale} <display data> ::= data in IEEE 488.2 # format
:DISPlay:INTensity:WAVeform <value> (see page 245)	:DISPlay:INTensity:WAVeform? (see page 245)	<value> ::= an integer from 0 to 100 in NR1 format.
:DISPlay:LABel {{0 | OFF} | {1 | ON}} (see page 246)	:DISPlay:LABel? (see page 246)	{0 | 1}
:DISPlay:LABList <binary block> (see page 247)	:DISPlay:LABList? (see page 247)	<binary block> ::= an ordered list of up to 75 labels, each 10 characters maximum, separated by newline characters
:DISPlay:PERSistence <value> (see page 249)	:DISPlay:PERSistence? (see page 249)	<value> ::= {MINimum | INFinite | <time>} <time> ::= seconds in in NR3 format from 100E-3 to 60E0
:DISPlay:VECTors {1 | ON} (see page 251)	:DISPlay:VECTors? (see page 251)	1

Table 10 :DVM Commands Summary

Command	Query	Options and Query Returns
:DVM:ARANge {{0 | OFF} | {1 | ON}} (see page 254)	:DVM:ARANge? (see page 254)	{0 | 1}
n/a	:DVM:CURRent? (see page 255)	<dvm_value> ::= floating-point number in NR3 format
:DVM:ENABle {{0 | OFF} | {1 | ON}} (see page 256)	:DVM:ENABle? (see page 256)	{0 | 1}
n/a	:DVM:FREQuency? (see page 255)	<freq_value> ::= floating-point number in NR3 format

Table 10 :DVM Commands Summary (continued)

Command	Query	Options and Query Returns
:DVM:MODE <mode> (see page 258)	:DVM:MODE? (see page 258)	<dvm_mode> ::= {ACRMs | DC | DCRMs | FREQuency}
:DVM:SOURce <source> (see page 259)	:DVM:SOURce? (see page 259)	<source> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format

Table 11 :EXTernal Trigger Commands Summary

Command	Query	Options and Query Returns
:EXTernal:BWLimit <bwlimit> (see page 263)	:EXTernal:BWLimit? (see page 263)	<bwlimit> ::= {0 | OFF}
:EXTernal:DISPlay {{0 | OFF} | {1 | ON}} (see page 264)	:EXTernal:DISPlay? (see page 264)	<setting> ::= {0 | 1} On DSOX1204A/G oscilloscopes, the :EXTernal:DISPlay command can be set to OFF only.
:EXTernal:LABel <string> (see page 265)	:EXTernal:LABel? (see page 265)	<string> ::= quoted ASCII string.
:EXTernal:LEVel <level>[<suffix>] (see page 266)	:EXTernal:LEVel? (see page 266)	<value> ::= external trigger level value in NR3 format. <suffix> ::= {V | mV}
:EXTernal:POSition <value> (see page 267)	:EXTernal:POSition? (see page 267)	<value> ::= Ext Trig waveform vertical position in divisions in NR3 format. On DSOX1204A/G oscilloscopes, the :EXTernal:POSition value can be zero only.
:EXTernal:PROBe <attenuation> (see page 268)	:EXTernal:PROBe? (see page 268)	<attenuation> ::= probe attenuation ratio in NR3 format
:EXTernal:RANGe <range>[<suffix>] (see page 269)	:EXTernal:RANGe? (see page 269)	<range> ::= vertical full-scale range value in NR3 format <suffix> ::= {V | mV}
:EXTernal:UNITs <units> (see page 270)	:EXTernal:UNITs? (see page 270)	<units> ::= {VOLT | AMPere}

Table 12 :FFT Commands Summary

Command	Query	Options and Query Returns
:FFT:CENTer <frequency> (see page 273)	:FFT:CENTer? (see page 273)	<frequency> ::= the current center frequency in NR3 format. The range of legal values is from -25 GHz to 25 GHz.
:FFT:DISPlay {{0 | OFF} | {1 | ON}} (see page 274)	:FFT:DISPlay? (see page 274)	<s> ::= 1-6, in NR1 format. {0 | 1}
:FFT:OFFSet <offset> (see page 275)	:FFT:OFFSet? (see page 275)	<offset> ::= the value at center screen in NR3 format.
:FFT:RANGe <range> (see page 276)	:FFT:RANGe? (see page 276)	<range> ::= the full-scale vertical axis value in NR3 format.
:FFT:REFerence <level> (see page 277)	:FFT:REFerence? (see page 277)	<level> ::= the current reference level in NR3 format.
:FFT:SCALe <scale_value>[<suffix>] (see page 278)	:FFT:SCALe? (see page 278)	<scale_value> ::= integer in NR1 format. <suffix> ::= dB
:FFT:SOURce1 <source> (see page 279)	:FFT:SOURce1? (see page 279)	<source> ::= {CHANnel<n> | FUNCtion<c> | MATH<c>} <n> ::= 1 to (# analog channels) in NR1 format. <c> ::= {1 | 2}
:FFT:SPAN (see page 280)	:FFT:SPAN? (see page 280)	::= the current frequency span in NR3 format. Legal values are 1 Hz to 100 GHz.
:FFT:VTYPe <units> (see page 281)	:FFT:VTYPe? (see page 281)	<units> ::= {DECibel | VRMS}
:FFT:WINDow <window> (see page 282)	:FFT:WINDow? (see page 282)	<window> ::= {RECTangular | HANNing | FLATtop | BHARris}

Table 13 :FRANalysis Commands Summary

Command	Query	Options and Query Returns
n/a	:FRANalysis:DATA? (see page 287)	<binary_block> ::= comma-separated data with newlines at the end of each row
:FRANalysis:ENABle {{0 | OFF} | {1 | ON}} (see page 288)	:FRANalysis:ENABle? (see page 288)	{0 | 1}

Table 13 :FRANalysis Commands Summary (continued)

Command	Query	Options and Query Returns
:FRANalysis:FREQuency :MODE <setting> (see page 289)	:FRANalysis:FREQuency :MODE? (see page 289)	<setting> ::= {SWEep | SINGle}
:FRANalysis:FREQuency :SINGle <value>[suffix] (see page 290)	:FRANalysis:FREQuency :SINGle? (see page 290)	<value> ::= between 10 Hz and 20 MHz with a resolution of 0.1 Hz in NR3 format [suffix] ::= {Hz | kHz| MHz}
:FRANalysis:FREQuency :STARt <value>[suffix] (see page 291)	:FRANalysis:FREQuency :STARt? (see page 291)	<value> ::= between 10 Hz and 19.99 MHz with a resolution of 0.1 Hz in NR3 format [suffix] ::= {Hz | kHz| MHz}
:FRANalysis:FREQuency :STOP <value>[suffix] (see page 292)	:FRANalysis:FREQuency :STOP? (see page 292)	<value> ::= between 10.1 Hz and 20 MHz with a resolution of 0.1 Hz in NR3 format [suffix] ::= {Hz | kHz| MHz}
:FRANalysis:RUN (see page 293)	n/a	n/a
:FRANalysis:SOURce:INPut <source> (see page 294)	:FRANalysis:SOURce:INPut? (see page 294)	<source> ::= CHANnel<n> <n> ::= 1 to (# analog channels) in NR1 format
:FRANalysis:SOURce:OUTPut <source> (see page 295)	:FRANalysis:SOURce:OUTPut? (see page 295)	<source> ::= CHANnel<n> <n> ::= 1 to (# analog channels) in NR1 format
:FRANalysis:SWEep:POINts <pts> (see page 296)	:FRANalysis:SWEep:POINts? (see page 296)	<pts> ::= number of points from 1 to 1000 in NR1 format
:FRANalysis:TRACe <selection> (see page 297)	:FRANalysis:TRACe? (see page 297)	<selection> ::= {NONE | ALL | GAIN | PHASe}[,{GAIN | PHASe}]
:FRANalysis:WGEN:LOAD <impedance> (see page 298)	:FRANalysis:WGEN:LOAD? (see page 298)	<impedance> ::= {ONEMeg | FIFTy}
:FRANalysis:WGEN:VOLTage <amplitude> (see page 299)	:FRANalysis:WGEN:VOLTage? (see page 299)	<amplitude> ::= amplitude in volts in NR3 format

Table 14 :FUNCtion Commands Summary

Command	Query	Options and Query Returns
:FUNCtion:DISPlay {{0 | OFF} | {1 | ON}} (see page 304)	:FUNCtion:DISPlay? (see page 304)	{0 | 1}
:FUNCtion[:FFT]:CENTer <frequency> (see page 305)	:FUNCtion[:FFT]:CENTer? (see page 305)	<frequency> ::= the current center frequency in NR3 format. The range of legal values is from 0 Hz to 25 GHz.
:FUNCtion[:FFT]:PHASe :REFerence <ref_point> (see page 306)	:FUNCtion[:FFT]:PHASe :REFerence? (see page 306)	<ref_point> ::= {TRIGger | DISPlay}
:FUNCtion[:FFT]:SPAN (see page 307)	:FUNCtion[:FFT]:SPAN? (see page 307)	::= the current frequency span in NR3 format. Legal values are 1 Hz to 100 GHz.
:FUNCtion[:FFT]:VTYPe <units> (see page 308)	:FUNCtion[:FFT]:VTYPe? (see page 308)	<units> ::= {DECibel | VRMS} for the FFT (magnitude) operation <units> ::= {DEGRees | RADians} for the FFTPhase operation
:FUNCtion[:FFT]:WINDow <window> (see page 309)	:FUNCtion[:FFT]:WINDow? (see page 309)	<window> ::= {RECTangular | HANNing | FLATtop | BHARris}
:FUNCtion:FREQuency:LOWPass <3dB_freq> (see page 310)	:FUNCtion:FREQuency:LOWPass? (see page 310)	<3dB_freq> ::= 3dB cutoff frequency value in NR3 format
:FUNCtion:GOFT:OPERation <operation> (see page 311)	:FUNCtion:GOFT:OPERation? (see page 311)	<operation> ::= {ADD | SUBTract | MULTiply}
:FUNCtion:GOFT:SOURce1 <source> (see page 312)	:FUNCtion:GOFT:SOURce1? (see page 312)	<source> ::= CHANnel<n> <n> ::= 1 to (# analog channels) in NR1 format
:FUNCtion:GOFT:SOURce2 <source> (see page 313)	:FUNCtion:GOFT:SOURce2? (see page 313)	<source> ::= CHANnel<n> <n> ::= 1 to (# analog channels) in NR1 format
:FUNCtion:OFFSet <offset> (see page 314)	:FUNCtion:OFFSet? (see page 314)	<offset> ::= the value at center screen in NR3 format. The range of legal values is +/-10 times the current sensitivity of the selected function.

Table 14 :FUNCtion Commands Summary (continued)

Command	Query	Options and Query Returns
:FUNCtion:OPERation <operation> (see page 315)	:FUNCtion:OPERation? (see page 315)	<operation> ::= {ADD | SUBTract | MULTiply | DIVide | FFT | FFTPhase | LOWPass}
:FUNCtion:RANGe <range> (see page 317)	:FUNCtion:RANGe? (see page 317)	<range> ::= the full-scale vertical axis value in NR3 format. The range for ADD, SUBT, MULT is 8E-6 to 800E+3. The range for the FFT function is 8 to 800 dBV.
:FUNCtion:REFerence <level> (see page 318)	:FUNCtion:REFerence? (see page 318)	<level> ::= the value at center screen in NR3 format. The range of legal values is +/-10 times the current sensitivity of the selected function.
:FUNCtion:SCALe <scale value>[<suffix>] (see page 319)	:FUNCtion:SCALe? (see page 319)	<scale value> ::= integer in NR1 format <suffix> ::= {V | dB}
:FUNCtion:SOURce1 <source> (see page 320)	:FUNCtion:SOURce1? (see page 320)	<source> ::= {CHANnel<n> | GOFT} <n> ::= 1 to (# analog channels) in NR1 format GOFT is only for FFT operation.
:FUNCtion:SOURce2 <source> (see page 321)	:FUNCtion:SOURce2? (see page 321)	<source> ::= {CHANnel<n> | NONE} <n> ::= 1 to (# analog channels) in NR1 format, depending on SOURce1 selection

Table 15 :HARDcopy Commands Summary

Command	Query	Options and Query Returns
:HARDcopy:AREA <area> (see page 325)	:HARDcopy:AREA? (see page 325)	<area> ::= SCReen
:HARDcopy:APRinter <active_printer> (see page 326)	:HARDcopy:APRinter? (see page 326)	<active_printer> ::= {<index> | <name>} <index> ::= integer index of printer in list <name> ::= name of printer in list

Table 15 :HARDcopy Commands Summary (continued)

Command	Query	Options and Query Returns
:HARDcopy:FACTors {{0 | OFF} | {1 | ON}} (see page 327)	:HARDcopy:FACTors? (see page 327)	{0 | 1}
:HARDcopy:FFEed {{0 | OFF} | {1 | ON}} (see page 328)	:HARDcopy:FFEed? (see page 328)	{0 | 1}
:HARDcopy:INKSaver {{0 | OFF} | {1 | ON}} (see page 329)	:HARDcopy:INKSaver? (see page 329)	{0 | 1}
:HARDcopy:LAYout <layout> (see page 330)	:HARDcopy:LAYout? (see page 330)	<layout> ::= {LANDscape | PORTrait}
:HARDcopy:NETWork:ADDRess <address> (see page 331)	:HARDcopy:NETWork:ADDRess? (see page 331)	<address> ::= quoted ASCII string
:HARDcopy:NETWork:APPLy (see page 332)	n/a	n/a
:HARDcopy:NETWork:SLOT <slot> (see page 333)	:HARDcopy:NETWork:SLOT? (see page 333)	<slot> ::= {NET0 | NET1}
:HARDcopy:PALette <palette> (see page 334)	:HARDcopy:PALette? (see page 334)	<palette> ::= {COLor | GRAYscale | NONE}
n/a	:HARDcopy:PRINter:LIST? (see page 335)	<list> ::= [<printer_spec>] ... [printer_spec>] <printer_spec> ::= "<index>,<active>,<name>;" <index> ::= integer index of printer <active> ::= {Y | N} <name> ::= name of printer
:HARDcopy:STARt (see page 336)	n/a	n/a

Table 16 :LISTer Commands Summary

Command	Query	Options and Query Returns
n/a	:LISTer:DATA? (see page 338)	<binary_block> ::= comma-separated data with newlines at the end of each row
:LISTer:DISPlay {{OFF | 0} | {SBUS1 | ON | 1}} (see page 339)	:LISTer:DISPlay? (see page 339)	{OFF | SBUS1}
:LISTer:REFerence <time_ref> (see page 340)	:LISTer:REFerence? (see page 340)	<time_ref> ::= {TRIGger | PREVious}

Table 17 :MARKer Commands Summary

Command	Query	Options and Query Returns
:MARKer:MODE <mode> (see page 344)	:MARKer:MODE? (see page 344)	<mode> ::= {OFF | MEASurement | MANual | WAVeform}
:MARKer:X1Position <position>[suffix] (see page 345)	:MARKer:X1Position? (see page 345)	<position> ::= X1 cursor position value in NR3 format [suffix] ::= {s | ms | us | ns | ps | Hz | kHz | MHz} <return_value> ::= X1 cursor position value in NR3 format
:MARKer:X1Y1source <source> (see page 346)	:MARKer:X1Y1source? (see page 346)	<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format On 2-channel oscilloscopes, EXTernal available for MANUAL mode only <return_value> ::= <source>
:MARKer:X2Position <position>[suffix] (see page 347)	:MARKer:X2Position? (see page 347)	<position> ::= X2 cursor position value in NR3 format [suffix] ::= {s | ms | us | ns | ps | Hz | kHz | MHz} <return_value> ::= X2 cursor position value in NR3 format

Table 17 :MARKer Commands Summary (continued)

Command	Query	Options and Query Returns
:MARKer:X2Y2source <source> (see page 348)	:MARKer:X2Y2source? (see page 348)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= <source>
n/a	:MARKer:XDELta? (see page 349)	<return_value> ::= X cursors delta value in NR3 format
:MARKer:XUNits <mode> (see page 350)	:MARKer:XUNits? (see page 350)	<units> ::= {SEConds | HERTz | DEGRees | PERCent}
:MARKer:XUNits:USE (see page 351)	n/a	n/a
:MARKer:Y1Position <position>[suffix] (see page 352)	:MARKer:Y1Position? (see page 352)	<position> ::= Y1 cursor position value in NR3 format [suffix] ::= {V | mV | dB} <return_value> ::= Y1 cursor position value in NR3 format
:MARKer:Y2Position <position>[suffix] (see page 353)	:MARKer:Y2Position? (see page 353)	<position> ::= Y2 cursor position value in NR3 format [suffix] ::= {V | mV | dB} <return_value> ::= Y2 cursor position value in NR3 format
n/a	:MARKer:YDELta? (see page 354)	<return_value> ::= Y cursors delta value in NR3 format
:MARKer:YUNits <mode> (see page 355)	:MARKer:YUNits? (see page 355)	<units> ::= {BASE | PERCent}
:MARKer:YUNits:USE (see page 356)	n/a	n/a

Table 18 :MEASure Commands Summary

Command	Query	Options and Query Returns
:MEASure:ALL (see page 369)	n/a	n/a
:MEASure:BRATe [<source>] (see page 370)	:MEASure:BRATe? [<source>] (see page 370)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# of analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format <return_value> ::= bit rate in Hz, NR3 format
:MEASure:CLEar (see page 371)	n/a	n/a
:MEASure:COUNter [<source>] (see page 372)	:MEASure:COUNter? [<source>] (see page 372)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <return_value> ::= counter frequency in Hertz in NR3 format
:MEASure:DEFine DELay, <delay spec>[,<source>] (see page 373)	:MEASure:DEFine? DELay[,<source>] (see page 374)	<delay spec> ::= <edge_spec1>,<edge_spec2> edge_spec1 ::= [<slope>]<occurrence> edge_spec2 ::= [<slope>]<occurrence> <slope> ::= {+ | -} <occurrence> ::= integer <source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}
:MEASure:DEFine THResholds, <threshold spec>[,<source>] (see page 373)	:MEASure:DEFine? THResholds[,<source>] (see page 374)	<threshold spec> ::= {STANdard} | {<threshold mode>,<upper>, <middle>,<lower>} <threshold mode> ::= {PERCent | ABSolute} <source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>}

Table 18 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:DELay [<source1>] [,<source2>] (see page 376)	:MEASure:DELay? [<source1>] [,<source2>] (see page 376)	<source1,2> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= floating-point number delay time in seconds in NR3 format
:MEASure:DUTYcycle [<source>] (see page 378)	:MEASure:DUTYcycle? [<source>] (see page 378)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= ratio of positive pulse width to period in NR3 format
:MEASure:FALLtime [<source>] (see page 379)	:MEASure:FALLtime? [<source>] (see page 379)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= time in seconds between the lower and upper thresholds in NR3 format
:MEASure:FREQuency [<source>] (see page 380)	:MEASure:FREQuency? [<source>] (see page 380)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= frequency in Hertz in NR3 format

Table 18 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:NDUTy [<source>] (see page 381)	:MEASure:NDUTy? [<source>] (see page 381)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= ratio of negative pulse width to period in NR3 format
:MEASure:NEDGes [<source>] (see page 382)	:MEASure:NEDGes? [<source>] (see page 382)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the falling edge count in NR3 format
:MEASure:NPULses [<source>] (see page 383)	:MEASure:NPULses? [<source>] (see page 383)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the falling pulse count in NR3 format
:MEASure:NWIDth [<source>] (see page 384)	:MEASure:NWIDth? [<source>] (see page 384)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= negative pulse width in seconds in NR3 format

Table 18 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:OVERshoot [<source>] (see page 385)	:MEASure:OVERshoot? [<source>] (see page 385)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the percent of the overshoot of the selected waveform in NR3 format
:MEASure:PEDGes [<source>] (see page 387)	:MEASure:PEDGes? [<source>] (see page 387)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the rising edge count in NR3 format
:MEASure:PERiod [<source>] (see page 388)	:MEASure:PERiod? [<source>] (see page 388)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= waveform period in seconds in NR3 format
:MEASure:PHASe [<source1>] [,<source2>] (see page 389)	:MEASure:PHASe? [<source1>] [,<source2>] (see page 389)	<source1,2> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the phase angle value in degrees in NR3 format
:MEASure:PPULses [<source>] (see page 390)	:MEASure:PPULses? [<source>] (see page 390)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the rising pulse count in NR3 format

Table 18 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:PREShoot [<source>] (see page 391)	:MEASure:PREShoot? [<source>] (see page 391)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the percent of preshoot of the selected waveform in NR3 format
:MEASure:PWIDth [<source>] (see page 392)	:MEASure:PWIDth? [<source>] (see page 392)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= width of positive pulse in seconds in NR3 format
n/a	:MEASure:RESults? <result_list> (see page 393)	<result_list> ::= comma-separated list of measurement results
:MEASure:RISetime [<source>] (see page 396)	:MEASure:RISetime? [<source>] (see page 396)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= rise time in seconds in NR3 format
:MEASure:SDEViation [<source>] (see page 397)	:MEASure:SDEViation? [<source>] (see page 397)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format <return_value> ::= calculated std deviation in NR3 format
:MEASure:SHOW {1 | ON} (see page 398)	:MEASure:SHOW? (see page 398)	{1}

Table 18 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:SOURce <source1> [,<source2>] (see page 399)	:MEASure:SOURce? (see page 399)	<source1,2> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= {<source> | NONE}
:MEASure:STATistics <type> (see page 401)	:MEASure:STATistics? (see page 401)	<type> ::= {{ON | 1} | CURRent | MEAN | MINimum | MAXimum | STDDev | COUNt} ON ::= all statistics returned
:MEASure:STATistics:DISPlay {{0 | OFF} | {1 | ON}} (see page 402)	:MEASure:STATistics:DISPlay? (see page 402)	{0 | 1}
:MEASure:STATistics:INCRement (see page 403)	n/a	n/a
:MEASure:STATistics:MCOunt <setting> (see page 404)	:MEASure:STATistics:MCOunt? (see page 404)	<setting> ::= {INFinite | <count>} <count> ::= 2 to 2000 in NR1 format
:MEASure:STATistics:RESet (see page 405)	n/a	n/a
:MEASure:STATistics:RSDeviation {{0 | OFF} | {1 | ON}} (see page 406)	:MEASure:STATistics:RSDeviation? (see page 406)	{0 | 1}

Table 18 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
n/a	:MEASure:TEDGe? <slope><occurrence>[,<source>] (see page 407)	<slope> ::= direction of the waveform <occurrence> ::= the transition to be reported <source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} for DSO models <source> ::= {CHANnel<n> | DIGital<d> | FUNCtion | MATH | WMEMory<r>} for MSO models <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <d> ::= 0 to (# digital channels - 1) in NR1 format <return_value> ::= time in seconds of the specified transition
n/a	:MEASure:TEDGe? <slope><occurrence>[,<source>] (see page 407)	<slope> ::= direction of the waveform <occurrence> ::= the transition to be reported <source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= time in seconds of the specified transition

Table 18 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
n/a	:MEASure:TVALue? <value>, [<slope>]<occurrence> [,<source>] (see page 409)	<value> ::= voltage level that the waveform must cross. <slope> ::= direction of the waveform when <value> is crossed. <occurrence> ::= transitions reported. <source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= time in seconds of specified voltage crossing in NR3 format
:MEASure:VAMPlitude [<source>] (see page 411)	:MEASure:VAMPlitude? [<source>] (see page 411)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the amplitude of the selected waveform in volts in NR3 format
:MEASure:VAVerage [<interval>][,][<source>] (see page 412)	:MEASure:VAVerage? [<interval>][,][<source>] (see page 412)	<interval> ::= {CYCLe | DISPlay} <source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= calculated average voltage in NR3 format
:MEASure:VBASe [<source>] (see page 413)	:MEASure:VBASe? [<source>] (see page 413)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <base_voltage> ::= voltage at the base of the selected waveform in NR3 format

Table 18 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:VMAX [<source>] (see page 414)	:MEASure:VMAX? [<source>] (see page 414)	<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= maximum voltage of the selected waveform in NR3 format
:MEASure:VMIN [<source>] (see page 415)	:MEASure:VMIN? [<source>] (see page 415)	<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= minimum voltage of the selected waveform in NR3 format
:MEASure:VPP [<source>] (see page 416)	:MEASure:VPP? [<source>] (see page 416)	<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= voltage peak-to-peak of the selected waveform in NR3 format
:MEASure:VRMS [<interval>][,] [<type>][,] [<source>] (see page 417)	:MEASure:VRMS? [<interval>][,] [<type>][,] [<source>] (see page 417)	<interval> ::= {CYCLe | DISPlay} <type> ::= {AC | DC} <source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= calculated dc RMS voltage in NR3 format

Table 18 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
n/a	:MEASure:VTIMe? <vtime>[,<source>] (see page 418)	<vtime> ::= displayed time from trigger in seconds in NR3 format <source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= voltage at the specified time in NR3 format
:MEASure:VTOP [<source>] (see page 419)	:MEASure:VTOP? [<source>] (see page 419)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= voltage at the top of the waveform in NR3 format
:MEASure:WINDow <type> (see page 420)	:MEASure:WINDow? (see page 420)	<type> ::= {MAIN | ZOOM | AUTO}

Table 18 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:XMAX [<source>] (see page 421)	:MEASure:XMAX? [<source>] (see page 421)	<source> ::= {CHANnel<n> | FUNCtion | FFT | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format <return_value> ::= horizontal value of the maximum in NR3 format
:MEASure:XMIN [<source>] (see page 422)	:MEASure:XMIN? [<source>] (see page 422)	<source> ::= {CHANnel<n> | FUNCtion | FFT | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format <return_value> ::= horizontal value of the maximum in NR3 format

Table 19 :MTESt Commands Summary

Command	Query	Options and Query Returns
:MTESt:ALL {{0 | OFF} | {1 | ON}} (see page 428)	:MTESt:ALL? (see page 428)	{0 | 1}
:MTESt:AMASk:CREate (see page 429)	n/a	n/a
:MTESt:AMASk:SOURce <source> (see page 430)	:MTESt:AMASk:SOURce? (see page 430)	<source> ::= CHANnel<n> <n> ::= {1 | 2 | 3 | 4} for 4ch models <n> ::= {1 | 2} for 2ch models
:MTESt:AMASk:UNITs <units> (see page 431)	:MTESt:AMASk:UNITs? (see page 431)	<units> ::= {CURRent | DIVisions}
:MTESt:AMASk:XDELta <value> (see page 432)	:MTESt:AMASk:XDELta? (see page 432)	<value> ::= X delta value in NR3 format
:MTESt:AMASk:YDELta <value> (see page 433)	:MTESt:AMASk:YDELta? (see page 433)	<value> ::= Y delta value in NR3 format

Table 19 :MTESt Commands Summary (continued)

Command	Query	Options and Query Returns
n/a	:MTESt:COUNt:FWAVeforms? [CHANnel<n>] (see page 434)	<failed> ::= number of failed waveforms in NR1 format
:MTESt:COUNt:RESet (see page 435)	n/a	n/a
n/a	:MTESt:COUNt:TIME? (see page 436)	<time> ::= elapsed seconds in NR3 format
n/a	:MTESt:COUNt:WAVeforms? (see page 437)	<count> ::= number of waveforms in NR1 format
:MTESt:DATA <mask> (see page 438)	:MTESt:DATA? (see page 438)	<mask> ::= data in IEEE 488.2 # format.
:MTESt:DELete (see page 439)	n/a	n/a
:MTESt:ENABle {{0 | OFF} | {1 | ON}} (see page 440)	:MTESt:ENABle? (see page 440)	{0 | 1}
:MTESt:LOCK {{0 | OFF} | {1 | ON}} (see page 441)	:MTESt:LOCK? (see page 441)	{0 | 1}
:MTESt:RMODe <rmode> (see page 442)	:MTESt:RMODe? (see page 442)	<rmode> ::= {FOREver | TIME | SIGMa | WAVeforms}
:MTESt:RMODe:FACTion:MEASure {{0 | OFF} | {1 | ON}} (see page 443)	:MTESt:RMODe:FACTion:MEASure? (see page 443)	{0 | 1}
:MTESt:RMODe:FACTion:PRINt {{0 | OFF} | {1 | ON}} (see page 444)	:MTESt:RMODe:FACTion:PRINt? (see page 444)	{0 | 1}
:MTESt:RMODe:FACTion:SAVE {{0 | OFF} | {1 | ON}} (see page 445)	:MTESt:RMODe:FACTion:SAVE? (see page 445)	{0 | 1}
:MTESt:RMODe:FACTion:STOP {{0 | OFF} | {1 | ON}} (see page 446)	:MTESt:RMODe:FACTion:STOP? (see page 446)	{0 | 1}
:MTESt:RMODe:SIGMa <level> (see page 447)	:MTESt:RMODe:SIGMa? (see page 447)	<level> ::= from 0.1 to 9.3 in NR3 format
:MTESt:RMODe:TIME <seconds> (see page 448)	:MTESt:RMODe:TIME? (see page 448)	<seconds> ::= from 1 to 86400 in NR3 format

Table 19 :MTESt Commands Summary (continued)

Command	Query	Options and Query Returns
:MTESt:RMODe:WAVeforms <count> (see page 449)	:MTESt:RMODe:WAVeforms? (see page 449)	<count> ::= number of waveforms in NR1 format
:MTESt:SCALe:BIND {{0 | OFF} | {1 | ON}} (see page 450)	:MTESt:SCALe:BIND? (see page 450)	{0 | 1}
:MTESt:SCALe:X1 <x1_value> (see page 451)	:MTESt:SCALe:X1? (see page 451)	<x1_value> ::= X1 value in NR3 format
:MTESt:SCALe:XDELta <xdelta_value> (see page 452)	:MTESt:SCALe:XDELta? (see page 452)	<xdelta_value> ::= X delta value in NR3 format
:MTESt:SCALe:Y1 <y1_value> (see page 453)	:MTESt:SCALe:Y1? (see page 453)	<y1_value> ::= Y1 value in NR3 format
:MTESt:SCALe:Y2 <y2_value> (see page 454)	:MTESt:SCALe:Y2? (see page 454)	<y2_value> ::= Y2 value in NR3 format
:MTESt:SOURce <source> (see page 455)	:MTESt:SOURce? (see page 455)	<source> ::= {CHANnel<n> | NONE} <n> ::= {1 | 2 | 3 | 4} for 4ch models <n> ::= {1 | 2} for 2ch models
n/a	:MTESt:TITLe? (see page 456)	<title> ::= a string of up to 128 ASCII characters

Table 20 :RECall Commands Summary

Command	Query	Options and Query Returns
:RECall:FILename <base_name> (see page 459)	:RECall:FILename? (see page 459)	<base_name> ::= quoted ASCII string
:RECall:MASK[:STARt] [<file_spec>] (see page 460)	n/a	<file_spec> ::= {<internal_loc> | <file_name>} <internal_loc> ::= 0-3; an integer in NR1 format <file_name> ::= quoted ASCII string
:RECall:PWD <path_name> (see page 461)	:RECall:PWD? (see page 461)	<path_name> ::= quoted ASCII string

Table 20 :RECall Commands Summary (continued)

Command	Query	Options and Query Returns
:RECall:SETup[:STARt] [<file_spec>] (see page 462)	n/a	<file_spec> ::= {<internal_loc> | <file_name>} <internal_loc> ::= 0-9; an integer in NR1 format <file_name> ::= quoted ASCII string
:RECall:WMEMory<r>[:STARt] [<file_name>] (see page 463)	n/a	<r> ::= 1-2 in NR1 format <file_name> ::= quoted ASCII string If extension included in file name, it must be ".h5".

Table 21 :SAVE Commands Summary

Command	Query	Options and Query Returns
:SAVE:FILename <base_name> (see page 468)	:SAVE:FILename? (see page 468)	<base_name> ::= quoted ASCII string
:SAVE:IMAGe[:STARt] [<file_name>] (see page 469)	n/a	<file_name> ::= quoted ASCII string
:SAVE:IMAGe:FACTors {{0 | OFF} | {1 | ON}} (see page 470)	:SAVE:IMAGe:FACTors? (see page 470)	{0 | 1}
:SAVE:IMAGe:FORMat <format> (see page 471)	:SAVE:IMAGe:FORMat? (see page 471)	<format> ::= {{BMP | BMP24bit} | BMP8bit | PNG | NONE}
:SAVE:IMAGe:INKSaver {{0 | OFF} | {1 | ON}} (see page 472)	:SAVE:IMAGe:INKSaver? (see page 472)	{0 | 1}
:SAVE:IMAGe:PALette <palette> (see page 473)	:SAVE:IMAGe:PALette? (see page 473)	<palette> ::= {COLor | GRAYscale}
:SAVE:LISTer[:STARt] [<file_name>] (see page 474)	n/a	<file_name> ::= quoted ASCII string

Table 21 :SAVE Commands Summary (continued)

Command	Query	Options and Query Returns
:SAVE:MASK[:STARt] [<file_spec>] (see page 475)	n/a	<file_spec> ::= {<internal_loc> | <file_name>} <internal_loc> ::= 0-3; an integer in NR1 format <file_name> ::= quoted ASCII string
:SAVE:MULTi[:STARt] [<file_name>] (see page 476)	n/a	<file_name> ::= quoted ASCII string
:SAVE:PWD <path_name> (see page 477)	:SAVE:PWD? (see page 477)	<path_name> ::= quoted ASCII string
:SAVE:SETup[:STARt] [<file_spec>] (see page 478)	n/a	<file_spec> ::= {<internal_loc> | <file_name>} <internal_loc> ::= 0-9; an integer in NR1 format <file_name> ::= quoted ASCII string
:SAVE:WAVeform[:STARt] [<file_name>] (see page 479)	n/a	<file_name> ::= quoted ASCII string
:SAVE:WAVeform:FORMat <format> (see page 480)	:SAVE:WAVeform:FORMat? (see page 480)	<format> ::= {ASCiixy | CSV | BINary | NONE}
:SAVE:WAVeform:LENGth <length> (see page 481)	:SAVE:WAVeform:LENGth? (see page 481)	<length> ::= 100 to max. length; an integer in NR1 format
:SAVE:WAVeform:LENGth:MAX {{0 | OFF} | {1 | ON}} (see page 482)	:SAVE:WAVeform:LENGth:MAX? (see page 482)	{0 | 1}
:SAVE:WAVeform:SEGMented <option> (see page 483)	:SAVE:WAVeform:SEGMented? (see page 483)	<option> ::= {ALL | CURRent}

Table 21 :SAVE Commands Summary (continued)

Command	Query	Options and Query Returns
:SAVE:WMEMory:SOURce <source> (see page 484)	:SAVE:WMEMory:SOURce? (see page 484)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format NOTE: Only ADD or SUBtract math operations can be saved as reference waveforms. <return_value> ::= <source>
:SAVE:WMEMory[:STARt] [<file_name>] (see page 485)	n/a	<file_name> ::= quoted ASCII string If extension included in file name, it must be ".h5".

Table 22 General :SBUS<n> Commands Summary

Command	Query	Options and Query Returns
:SBUS<n>:DISPlay {{0 | OFF} | {1 | ON}} (see page 490)	:SBUS<n>:DISPlay? (see page 490)	{0 | 1}
:SBUS<n>:MODE <mode> (see page 491)	:SBUS<n>:MODE? (see page 491)	<mode> ::= {CAN | IIC | LIN | SPI | UART}

Table 23 :SBUS<n>:CAN Commands Summary

Command	Query	Options and Query Returns
n/a	:SBUS<n>:CAN:COUNt:ERRor? (see page 494)	<frame_count> ::= integer in NR1 format
n/a	:SBUS<n>:CAN:COUNt:OVERload? (see page 495)	<frame_count> ::= integer in NR1 format
:SBUS<n>:CAN:COUNt:RESet (see page 496)	n/a	n/a
n/a	:SBUS<n>:CAN:COUNt:TOTal? (see page 497)	<frame_count> ::= integer in NR1 format
n/a	:SBUS<n>:CAN:COUNt:UTILization? (see page 498)	<percent> ::= floating-point in NR3 format

Table 23 :SBUS<n>:CAN Commands Summary (continued)

Command	Query	Options and Query Returns
:SBUS<n>:CAN:SAMPlepoint <value> (see page 499)	:SBUS<n>:CAN:SAMPlepoint? (see page 499)	<value> ::= {60 | 62.5 | 68 | 70 | 75 | 80 | 87.5} in NR3 format
:SBUS<n>:CAN:SIGNal:BAUDrate <baudrate> (see page 500)	:SBUS<n>:CAN:SIGNal:BAUDrate? (see page 500)	<baudrate> ::= integer from 10000 to 4000000 in 100 b/s increments, or 5000000
:SBUS<n>:CAN:SIGNal:DEFinition <value> (see page 501)	:SBUS<n>:CAN:SIGNal:DEFinition? (see page 501)	<value> ::= {CANH | CANL | RX | TX | DIFFerential | DIFL | DIFH}
:SBUS<n>:CAN:SOURce <source> (see page 502)	:SBUS<n>:CAN:SOURce? (see page 502)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:CAN:TRIGger <condition> (see page 503)	:SBUS<n>:CAN:TRIGger? (see page 504)	<condition> ::= {SOF | DATA | ERRor | IDData | IDEither | IDRemote | ALLerrors | OVERload | ACKerror}
:SBUS<n>:CAN:TRIGger:PATTern:DATA <string> (see page 505)	:SBUS<n>:CAN:TRIGger:PATTern:DATA? (see page 505)	<string> ::= "nn...n" where n ::= {0 | 1 | X | $} <string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
:SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth <length> (see page 506)	:SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth? (see page 506)	<length> ::= integer from 1 to 8 in NR1 format
:SBUS<n>:CAN:TRIGger:PATTern:ID <string> (see page 507)	:SBUS<n>:CAN:TRIGger:PATTern:ID? (see page 507)	<string> ::= "nn...n" where n ::= {0 | 1 | X | $} <string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
:SBUS<n>:CAN:TRIGger:PATTern:ID:MODE <value> (see page 508)	:SBUS<n>:CAN:TRIGger:PATTern:ID:MODE? (see page 508)	<value> ::= {STANdard | EXTended}

Table 24 :SBUS<n>:IIC Commands Summary

Command	Query	Options and Query Returns
:SBUS<n>:IIC:ASIZe <size> (see page 510)	:SBUS<n>:IIC:ASIZe? (see page 510)	<size> ::= {BIT7 | BIT8}
:SBUS<n>:IIC[:SOURce]:CLOCk <source> (see page 511)	:SBUS<n>:IIC[:SOURce]:CLOCk? (see page 511)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:IIC[:SOURce]:DATA <source> (see page 512)	:SBUS<n>:IIC[:SOURce]:DATA? (see page 512)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:IIC:TRIGger:PATTern:ADDRess <value> (see page 513)	:SBUS<n>:IIC:TRIGger:PATTern:ADDRess? (see page 513)	<value> ::= integer or <string> <string> ::= "0xnn" n ::= {0,..,9 | A,..,F}
:SBUS<n>:IIC:TRIGger:PATTern:DATA <value> (see page 514)	:SBUS<n>:IIC:TRIGger:PATTern:DATA? (see page 514)	<value> ::= integer or <string> <string> ::= "0xnn" n ::= {0,..,9 | A,..,F}
:SBUS<n>:IIC:TRIGger:PATTern:DATa2 <value> (see page 515)	:SBUS<n>:IIC:TRIGger:PATTern:DATa2? (see page 515)	<value> ::= integer or <string> <string> ::= "0xnn" n ::= {0,..,9 | A,..,F}
:SBUS<n>:IIC:TRIGger:QUALifier <value> (see page 516)	:SBUS<n>:IIC:TRIGger:QUALifier? (see page 516)	<value> ::= {EQUal | NOTequal | LESSthan | GREaterthan}
:SBUS<n>:IIC:TRIGger[:TYPE] <type> (see page 517)	:SBUS<n>:IIC:TRIGger[:TYPE]? (see page 517)	<type> ::= {STARt | STOP | READ7 | READEprom | WRITe7 | WRITe10 | NACKnowledge | ANACk | R7Data2 | W7Data2 | RESTart}

Table 25 :SBUS<n>:LIN Commands Summary

Command	Query	Options and Query Returns
:SBUS<n>:LIN:PARity {{0 | OFF} | {1 | ON}} (see page 521)	:SBUS<n>:LIN:PARity? (see page 521)	{0 | 1}
:SBUS<n>:LIN:SAMPlepoint <value> (see page 522)	:SBUS<n>:LIN:SAMPlepoint? (see page 522)	<value> ::= {60 | 62.5 | 68 | 70 | 75 | 80 | 87.5} in NR3 format
:SBUS<n>:LIN:SIGNal:BAUDrate <baudrate> (see page 523)	:SBUS<n>:LIN:SIGNal:BAUDrate? (see page 523)	<baudrate> ::= integer from 2400 to 625000 in 100 b/s increments
:SBUS<n>:LIN:SOURce <source> (see page 524)	:SBUS<n>:LIN:SOURce? (see page 524)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:LIN:STANdard <std> (see page 525)	:SBUS<n>:LIN:STANdard? (see page 525)	<std> ::= {LIN13 | LIN20}
:SBUS<n>:LIN:SYNCbreak <value> (see page 526)	:SBUS<n>:LIN:SYNCbreak? (see page 526)	<value> ::= integer = {11 | 12 | 13}
:SBUS<n>:LIN:TRIGger <condition> (see page 527)	:SBUS<n>:LIN:TRIGger? (see page 527)	<condition> ::= {SYNCbreak | ID | DATA}
:SBUS<n>:LIN:TRIGger:ID <value> (see page 528)	:SBUS<n>:LIN:TRIGger:ID? (see page 528)	<value> ::= 7-bit integer in decimal, <nondecimal>, or <string> from 0-63 or 0x00-0x3f <nondecimal> ::= #Hnn where n ::= {0,..,9 | A,..,F} for hexadecimal <nondecimal> ::= #Bnn...n where n ::= {0 | 1} for binary <string> ::= "0xnn" where n ::= {0,..,9 | A,..,F} for hexadecimal

Table 25 :SBUS<n>:LIN Commands Summary (continued)

Command	Query	Options and Query Returns
:SBUS<n>:LIN:TRIGger:PATTern:DATA <string> (see page 529)	:SBUS<n>:LIN:TRIGger:PATTern:DATA? (see page 529)	<string> ::= "n" where n ::= 32-bit integer in unsigned decimal when <base> = DECimal <string> ::= "nn...n" where n ::= {0 | 1 | X | $} when <base> = BINary <string> ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $} when <base> = HEX
:SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth <length> (see page 531)	:SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth? (see page 531)	<length> ::= integer from 1 to 8 in NR1 format
:SBUS<n>:LIN:TRIGger:PATTern:FORMat <base> (see page 532)	:SBUS<n>:LIN:TRIGger:PATTern:FORMat? (see page 532)	<base> ::= {BINary | HEX | DECimal}

Table 26 :SBUS<n>:SPI Commands Summary

Command	Query	Options and Query Returns
:SBUS<n>:SPI:BITorder <order> (see page 535)	:SBUS<n>:SPI:BITorder? (see page 535)	<order> ::= {LSBFirst | MSBFirst}
:SBUS<n>:SPI:CLOCk:SLOPe <slope> (see page 536)	:SBUS<n>:SPI:CLOCk:SLOPe? (see page 536)	<slope> ::= {NEGative | POSitive}
:SBUS<n>:SPI:CLOCk:TIMeout <time_value> (see page 537)	:SBUS<n>:SPI:CLOCk:TIMeout? (see page 537)	<time_value> ::= time in seconds in NR3 format
:SBUS<n>:SPI:FRAMing <value> (see page 538)	:SBUS<n>:SPI:FRAMing? (see page 538)	<value> ::= {CHIPselect | {NCHipselect | NOTC} | TIMeout}
:SBUS<n>:SPI:SOURce:CLOCk <source> (see page 539)	:SBUS<n>:SPI:SOURce:CLOCk? (see page 539)	<value> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only

Table 26 :SBUS<n>:SPI Commands Summary (continued)

Command	Query	Options and Query Returns
:SBUS<n>:SPI:SOURce:DATA <source> (see page 540)	:SBUS<n>:SPI:SOURce:DATA? (see page 540)	<value> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:SPI:SOURce:FRAMe <source> (see page 541)	:SBUS<n>:SPI:SOURce:FRAMe? (see page 541)	<value> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:SPI:SOURce:MISO <source> (see page 542)	:SBUS<n>:SPI:SOURce:MISO? (see page 542)	<value> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format
:SBUS<n>:SPI:SOURce:MOSI <source> (see page 543)	:SBUS<n>:SPI:SOURce:MOSI? (see page 543)	<value> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format
:SBUS<n>:SPI:TRIGger:PATTern:DATA <string> (see page 544)	:SBUS<n>:SPI:TRIGger:PATTern:DATA? (see page 544)	<string> ::= "nn...n" where n ::= {0 | 1 | X | $} <string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
:SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA <string> (see page 545)	:SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA? (see page 545)	<string> ::= "nn...n" where n ::= {0 | 1 | X | $} <string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
:SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh <width> (see page 546)	:SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh? (see page 546)	<width> ::= integer from 4 to 64 in NR1 format
:SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA <string> (see page 547)	:SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA? (see page 547)	<string> ::= "nn...n" where n ::= {0 | 1 | X | $} <string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
:SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh <width> (see page 548)	:SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh? (see page 548)	<width> ::= integer from 4 to 64 in NR1 format

Table 26 :SBUS<n>:SPI Commands Summary (continued)

Command	Query	Options and Query Returns
:SBUS<n>:SPI:TRIGger:PATTern:WIDTh <width> (see page 549)	:SBUS<n>:SPI:TRIGger:PATTern:WIDTh? (see page 549)	<width> ::= integer from 4 to 64 in NR1 format
:SBUS<n>:SPI:TRIGger:TYPE <value> (see page 550)	:SBUS<n>:SPI:TRIGger:TYPE? (see page 550)	<value> ::= {MOSI | MISO}
:SBUS<n>:SPI:WIDTh <word_width> (see page 551)	:SBUS<n>:SPI:WIDTh? (see page 551)	<word_width> ::= integer 4-16 in NR1 format

Table 27 :SBUS<n>:UART Commands Summary

Command	Query	Options and Query Returns
:SBUS<n>:UART:BASE <base> (see page 555)	:SBUS<n>:UART:BASE? (see page 555)	<base> ::= {ASCii | BINary | HEX}
:SBUS<n>:UART:BAUDrate <baudrate> (see page 556)	:SBUS<n>:UART:BAUDrate? (see page 556)	<baudrate> ::= integer from 100 to 8000000
:SBUS<n>:UART:BITorder <bitorder> (see page 557)	:SBUS<n>:UART:BITorder? (see page 557)	<bitorder> ::= {LSBFirst | MSBFirst}
n/a	:SBUS<n>:UART:COUNt:ERRor? (see page 558)	<frame_count> ::= integer in NR1 format
:SBUS<n>:UART:COUNt:RESet (see page 559)	n/a	n/a
n/a	:SBUS<n>:UART:COUNt:RXFRames? (see page 560)	<frame_count> ::= integer in NR1 format
n/a	:SBUS<n>:UART:COUNt:TXFRames? (see page 561)	<frame_count> ::= integer in NR1 format
:SBUS<n>:UART:FRAMing <value> (see page 562)	:SBUS<n>:UART:FRAMing? (see page 562)	<value> ::= {OFF | <decimal> | <nondecimal>} <decimal> ::= 8-bit integer from 0-255 (0x00-0xff) <nondecimal> ::= #Hnn where n ::= {0,..,9 | A,..,F} for hexadecimal <nondecimal> ::= #Bnn...n where n ::= {0 | 1} for binary

Table 27 :SBUS<n>:UART Commands Summary (continued)

Command	Query	Options and Query Returns
:SBUS<n>:UART:PARity <parity> (see page 563)	:SBUS<n>:UART:PARity? (see page 563)	<parity> ::= {EVEN | ODD | NONE}
:SBUS<n>:UART:POLarity <polarity> (see page 564)	:SBUS<n>:UART:POLarity? (see page 564)	<polarity> ::= {HIGH | LOW}
:SBUS<n>:UART:SOURce:RX <source> (see page 565)	:SBUS<n>:UART:SOURce:RX? (see page 565)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:UART:SOURce:TX <source> (see page 566)	:SBUS<n>:UART:SOURce:TX? (see page 566)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:UART:TRIGger:BASE <base> (see page 567)	:SBUS<n>:UART:TRIGger:BASE? (see page 567)	<base> ::= {ASCii | HEX}
:SBUS<n>:UART:TRIGger:BURSt <value> (see page 568)	:SBUS<n>:UART:TRIGger:BURSt? (see page 568)	<value> ::= {OFF | 1 to 4096 in NR1 format}
:SBUS<n>:UART:TRIGger:DATA <value> (see page 569)	:SBUS<n>:UART:TRIGger:DATA? (see page 569)	<value> ::= 8-bit integer from 0-255 (0x00-0xff) in decimal, <hexadecimal>, <binary>, or <quoted_string> format <hexadecimal> ::= #Hnn where n ::= {0,..,9 | A,..,F} for hexadecimal <binary> ::= #Bnn...n where n ::= {0 | 1} for binary <quoted_string> ::= any of the 128 valid 7-bit ASCII characters (or standard abbreviations)
:SBUS<n>:UART:TRIGger:IDLE <time_value> (see page 570)	:SBUS<n>:UART:TRIGger:IDLE? (see page 570)	<time_value> ::= time from 1 us to 10 s in NR3 format

Table 27 :SBUS<n>:UART Commands Summary (continued)

Command	Query	Options and Query Returns
:SBUS<n>:UART:TRIGger :QUALifier <value> (see page 571)	:SBUS<n>:UART:TRIGger :QUALifier? (see page 571)	<value> ::= {EQUal | NOTequal | GREaterthan | LESSthan}
:SBUS<n>:UART:TRIGger :TYPE <value> (see page 572)	:SBUS<n>:UART:TRIGger :TYPE? (see page 572)	<value> ::= {RSTArt | RSTOp | RDATa | RD1 | RD0 | RDX | PARityerror | TSTArt | TSTOp | TDATa | TD1 | TD0 | TDX}
:SBUS<n>:UART:WIDTh <width> (see page 573)	:SBUS<n>:UART:WIDTh? (see page 573)	<width> ::= {5 | 6 | 7 | 8 | 9}

Table 28 :SYSTem Commands Summary

Command	Query	Options and Query Returns
:SYSTem:DATE <date> (see page 578)	:SYSTem:DATE? (see page 578)	<date> ::= <year>,<month>,<day> <year> ::= 4-digit year in NR1 format <month> ::= {1,..,12 | JANuary | FEBruary | MARch | APRil | MAY | JUNe | JULy | AUGust | SEPtember | OCTober | NOVember | DECember} <day> ::= {1,..31}
n/a	:SYSTem:DIDentifier? (see page 579)	n/a
:SYSTem:DSP <string> (see page 580)	n/a	<string> ::= up to 75 characters as a quoted ASCII string
n/a	:SYSTem:ERRor? (see page 581)	<error> ::= an integer error code <error string> ::= quoted ASCII string. See Error Messages (see page 787).
:SYSTem:LOCK <value> (see page 582)	:SYSTem:LOCK? (see page 582)	<value> ::= {{1 | ON} | {0 | OFF}}
:SYSTem:MENU <menu> (see page 583)	n/a	<menu> ::= {MASK | MEASure | SEGMented}
:SYSTem:PERSona[:MANufacturer] <manufacturer_string> (see page 584)	:SYSTem:PERSona[:MANufacturer]? (see page 584)	<manufacturer_string> ::= quoted ASCII string, up to 63 characters

Table 28 :SYSTem Commands Summary (continued)

Command	Query	Options and Query Returns
:SYSTem:PERSona[:MANufacturer]:DEFault (see page 585)	n/a	Sets manufacturer string to "KEYSIGHT TECHNOLOGIES"
:SYSTem:PRESet (see page 586)	n/a	See :SYSTem:PRESet (see page 586)
:SYSTem:PROTection:LOCK <value> (see page 589)	:SYSTem:PROTection:LOCK? (see page 589)	<value> ::= {{1 | ON} | {0 | OFF}}
:SYSTem:RLOGger <setting>[,<file_name>[,<write_mode>]] (see page 590)	n/a	<setting> ::= {{0 | OFF} | {1 | ON}} <file_name> ::= quoted ASCII string <write_mode> ::= {CREate | APPend}
:SYSTem:RLOGger:DESTination <dest> (see page 591)	:SYSTem:RLOGger:DESTination? (see page 591)	<dest> ::= {FILE | SCReen | BOTH}
:SYSTem:RLOGger:DISPlay {{0 | OFF} | {1 | ON}} (see page 592)	:SYSTem:RLOGger:DISPlay? (see page 592)	<setting> ::= {0 | 1}
:SYSTem:RLOGger:FNAMe <file_name> (see page 593)	:SYSTem:RLOGger:FNAMe? (see page 593)	<file_name> ::= quoted ASCII string
:SYSTem:RLOGger:STATe {{0 | OFF} | {1 | ON}} (see page 594)	:SYSTem:RLOGger:STATe? (see page 594)	<setting> ::= {0 | 1}
:SYSTem:RLOGger:TRANsparent {{0 | OFF} | {1 | ON}} (see page 595)	:SYSTem:RLOGger:TRANsparent? (see page 595)	<setting> ::= {0 | 1}
:SYSTem:RLOGger:WMODe <write_mode> (see page 596)	:SYSTem:RLOGger:WMODe? (see page 596)	<write_mode> ::= {CREate | APPend}
:SYSTem:SETup <setup_data> (see page 597)	:SYSTem:SETup? (see page 597)	<setup_data> ::= data in IEEE 488.2 # format.
:SYSTem:TIME <time> (see page 599)	:SYSTem:TIME? (see page 599)	<time> ::= hours,minutes,seconds in NR1 format

Table 28 :SYSTem Commands Summary (continued)

Command	Query	Options and Query Returns
:SYSTem:TZONe <UTC_offset> (see page 600)	:SYSTem:TZONe? (see page 600)	<UTC_offset> ::= integer offset from UTC in the form HHMM, for example, 1000 for UTC+1000 or -230 for UTC-0230
:SYSTem:USB:EJECt [<usb_path>] (see page 601)	n/a	<usb_path> ::= path of USB storage device
n/a	:SYSTem:USB:PLISt? (see page 602)	n/a

Table 29 :TIMebase Commands Summary

Command	Query	Options and Query Returns
:TIMebase:MODE <value> (see page 605)	:TIMebase:MODE? (see page 605)	<value> ::= {MAIN | WINDow | XY | ROLL}
:TIMebase:POSition <pos> (see page 606)	:TIMebase:POSition? (see page 606)	<pos> ::= time from the trigger event to the display reference point in NR3 format
:TIMebase:RANGe <range_value> (see page 607)	:TIMebase:RANGe? (see page 607)	<range_value> ::= time for 10 div in seconds in NR3 format
:TIMebase:REFerence {LEFT | CENTer | RIGHt} (see page 608)	:TIMebase:REFerence? (see page 608)	<return_value> ::= {LEFT | CENTer | RIGHt}
:TIMebase:SCALe <scale_value> (see page 609)	:TIMebase:SCALe? (see page 609)	<scale_value> ::= time/div in seconds in NR3 format
:TIMebase:VERNier {{0 | OFF} | {1 | ON}} (see page 610)	:TIMebase:VERNier? (see page 610)	{0 | 1}
:TIMebase:WINDow:POSition <pos> (see page 611)	:TIMebase:WINDow:POSition? (see page 611)	<pos> ::= time from the trigger event to the zoomed view reference point in NR3 format
:TIMebase:WINDow:RANGe <range_value> (see page 612)	:TIMebase:WINDow:RANGe? (see page 612)	<range value> ::= range value in seconds in NR3 format for the zoomed window
:TIMebase:WINDow:SCALe <scale_value> (see page 613)	:TIMebase:WINDow:SCALe? (see page 613)	<scale_value> ::= scale value in seconds in NR3 format for the zoomed window

Table 30 General :TRIGger Commands Summary

Command	Query	Options and Query Returns
:TRIGger:FORCe (see page 618)	n/a	n/a
:TRIGger:HFReject {{0 | OFF} | {1 | ON}} (see page 619)	:TRIGger:HFReject? (see page 619)	{0 | 1}
:TRIGger:HOLDoff <holdoff_time> (see page 620)	:TRIGger:HOLDoff? (see page 620)	<holdoff_time> ::= 60 ns to 10 s in NR3 format
:TRIGger:LEVel:ASETup (see page 621)	n/a	n/a
:TRIGger:LEVel:HIGH <level>, <source> (see page 622)	:TRIGger:LEVel:HIGH? <source> (see page 622)	<level> ::= .75 x full-scale voltage from center screen in NR3 format. <source> ::= CHANnel<n> <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:LEVel:LOW <level>, <source> (see page 623)	:TRIGger:LEVel:LOW? <source> (see page 623)	<level> ::= .75 x full-scale voltage from center screen in NR3 format. <source> ::= CHANnel<n> <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:MODE <mode> (see page 624)	:TRIGger:MODE? (see page 624)	<mode> ::= {EDGE | GLITch | PATTern | SHOLd | TRANsition | TV | SBUS1} <return_value> ::= {<mode> | <none>} <none> ::= query returns "NONE" if the :TIMebase:MODE is ROLL or XY
:TRIGger:NREJect {{0 | OFF} | {1 | ON}} (see page 625)	:TRIGger:NREJect? (see page 625)	{0 | 1}
:TRIGger:SWEep <sweep> (see page 626)	:TRIGger:SWEep? (see page 626)	<sweep> ::= {AUTO | NORMal}

Table 31 :TRIGger[:EDGE] Commands Summary

Command	Query	Options and Query Returns
:TRIGger[:EDGE]:COUPling {AC | DC | LFReject} (see page 628)	:TRIGger[:EDGE]:COUPling? (see page 628)	{AC | DC | LFReject}
:TRIGger[:EDGE]:LEVel <level> [,<source>] (see page 629)	:TRIGger[:EDGE]:LEVel? [<source>] (see page 629)	For internal triggers, <level> ::= .75 x full-scale voltage from center screen in NR3 format. For external triggers, <level> ::= ±(external range setting) in NR3 format. <source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger[:EDGE]:REJect {OFF | LFReject | HFReject} (see page 630)	:TRIGger[:EDGE]:REJect? (see page 630)	{OFF | LFReject | HFReject}
:TRIGger[:EDGE]:SLOPe <polarity> (see page 631)	:TRIGger[:EDGE]:SLOPe? (see page 631)	<polarity> ::= {POSitive | NEGative | EITHer | ALTernate}
:TRIGger[:EDGE]:SOURce <source> (see page 632)	:TRIGger[:EDGE]:SOURce? (see page 632)	<source> ::= {CHANnel<n> | EXTernal | LINE | WGEN} <n> ::= 1 to (# analog channels) in NR1 format

Table 32 :TRIGger:GLITch Commands Summary

Command	Query	Options and Query Returns
:TRIGger:GLITch:GREaterthan <greater_than_time>[suffix] (see page 634)	:TRIGger:GLITch:GREaterthan? (see page 634)	<greater_than_time> ::= floating-point number in NR3 format [suffix] ::= {s | ms | us | ns | ps}
:TRIGger:GLITch:LESSthan <less_than_time>[suffix] (see page 635)	:TRIGger:GLITch:LESSthan? (see page 635)	<less_than_time> ::= floating-point number in NR3 format [suffix] ::= {s | ms | us | ns | ps}

Table 32 :TRIGger:GLITch Commands Summary (continued)

Command	Query	Options and Query Returns
:TRIGger:GLITch:LEVel <level> [<source>] (see page 636)	:TRIGger:GLITch:LEVel? (see page 636)	For internal triggers, <level> ::= .75 x full-scale voltage from center screen in NR3 format. For external triggers, <level> ::= ±(external range setting) in NR3 format. <source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:GLITch:POLarity <polarity> (see page 637)	:TRIGger:GLITch:POLarity? (see page 637)	<polarity> ::= {POSitive | NEGative}
:TRIGger:GLITch:QUALifier <qualifier> (see page 638)	:TRIGger:GLITch:QUALifier? (see page 638)	<qualifier> ::= {GREaterthan | LESSthan | RANGe}
:TRIGger:GLITch:RANGe <less_than_time>[suffix], <greater_than_time>[suffix] (see page 639)	:TRIGger:GLITch:RANGe? (see page 639)	<less_than_time> ::= 15 ns to 10 seconds in NR3 format <greater_than_time> ::= 10 ns to 9.99 seconds in NR3 format [suffix] ::= {s | ms | us | ns | ps}
:TRIGger:GLITch:SOURce <source> (see page 640)	:TRIGger:GLITch:SOURce? (see page 640)	<source> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format

Table 33 :TRIGger:PATTern Commands Summary

Command	Query	Options and Query Returns
:TRIGger:PATTern <string>[,<edge_source>,<edge>] (see page 642)	:TRIGger:PATTern? (see page 643)	<string> ::= "nn...n" where n ::= {0 | 1 | X | R | F} when <base> = ASCii <string> ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $} when <base> = HEX <edge_source> ::= {CHANnel<n> | EXTernal | NONE} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel oscilloscopes only <edge> ::= {POSitive | NEGative}
:TRIGger:PATTern:FORMat <base> (see page 644)	:TRIGger:PATTern:FORMat? (see page 644)	<base> ::= {ASCii | HEX}
:TRIGger:PATTern:QUALifier <qualifier> (see page 645)	:TRIGger:PATTern:QUALifier? (see page 645)	<qualifier> ::= ENTered

Table 34 :TRIGger:SHOLd Commands Summary

Command	Query	Options and Query Returns
:TRIGger:SHOLd:SLOPe <slope> (see page 647)	:TRIGger:SHOLd:SLOPe? (see page 647)	<slope> ::= {NEGative | POSitive}
:TRIGger:SHOLd:SOURce:CLOCk <source> (see page 648)	:TRIGger:SHOLd:SOURce:CLOCk? (see page 648)	<source> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:SHOLd:SOURce:DATA <source> (see page 649)	:TRIGger:SHOLd:SOURce:DATA? (see page 649)	<source> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:SHOLd:TIME:HOLD <time>[suffix] (see page 650)	:TRIGger:SHOLd:TIME:HOLD? (see page 650)	<time> ::= floating-point number in NR3 format [suffix] ::= {s | ms | us | ns | ps}
:TRIGger:SHOLd:TIME:SETup <time>[suffix] (see page 651)	:TRIGger:SHOLd:TIME:SETup? (see page 651)	<time> ::= floating-point number in NR3 format [suffix] ::= {s | ms | us | ns | ps}

Table 35 :TRIGger:TRANsition Commands Summary

Command	Query	Options and Query Returns
:TRIGger:TRANsition:QUALifier <qualifier> (see page 653)	:TRIGger:TRANsition:QUALifier? (see page 653)	<qualifier> ::= {GREaterthan | LESSthan}
:TRIGger:TRANsition:SLOPe <slope> (see page 654)	:TRIGger:TRANsition:SLOPe? (see page 654)	<slope> ::= {NEGative | POSitive}
:TRIGger:TRANsition:SOURce <source> (see page 655)	:TRIGger:TRANsition:SOURce? (see page 655)	<source> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:TRANsition:TIME <time>[suffix] (see page 656)	:TRIGger:TRANsition:TIME? (see page 656)	<time> ::= floating-point number in NR3 format [suffix] ::= {s | ms | us | ns | ps}

Table 36 :TRIGger:TV Commands Summary

Command	Query	Options and Query Returns
:TRIGger:TV:LINE <line number> (see page 658)	:TRIGger:TV:LINE? (see page 658)	<line number> ::= integer in NR1 format
:TRIGger:TV:MODE <tv mode> (see page 659)	:TRIGger:TV:MODE? (see page 659)	<tv mode> ::= {FIEld1 | FIEld2 | AFIelds | ALINes | LFIeld1 | LFIeld2 | LALTernate}
:TRIGger:TV:POLarity <polarity> (see page 660)	:TRIGger:TV:POLarity? (see page 660)	<polarity> ::= {POSitive | NEGative}
:TRIGger:TV:SOURce <source> (see page 661)	:TRIGger:TV:SOURce? (see page 661)	<source> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:TV:STANdard <standard> (see page 662)	:TRIGger:TV:STANdard? (see page 662)	<standard> ::= {NTSC | PAL | PALM | SECam}

Table 37 :WAVeform Commands Summary

Command	Query	Options and Query Returns
:WAVeform:BYTeorder <value> (see page 670)	:WAVeform:BYTeorder? (see page 670)	<value> ::= {LSBFirst | MSBFirst}
n/a	:WAVeform:COUNt? (see page 671)	<count> ::= an integer from 1 to 65536 in NR1 format
n/a	:WAVeform:DATA? (see page 672)	<binary block length bytes>, <binary data> For example, to transmit 1000 bytes of data, the syntax would be: #800001000<1000 bytes of data><NL> 8 is the number of digits that follow 00001000 is the number of bytes to be transmitted <1000 bytes of data> is the actual data
:WAVeform:FORMat <value> (see page 674)	:WAVeform:FORMat? (see page 674)	<value> ::= {WORD | BYTE | ASCII}
:WAVeform:POINts <# points> (see page 675)	:WAVeform:POINts? (see page 675)	<# points> ::= {100 | 250 | 500 | 1000 | <points_mode>} if waveform points mode is NORMal <# points> ::= {100 | 250 | 500 | 1000 | 2000 ... 2000000 in 1-2-5 sequence | <points_mode>} if waveform points mode is MAXimum or RAW <points_mode> ::= {NORMal | MAXimum | RAW}
:WAVeform:POINts:MODE <points_mode> (see page 677)	:WAVeform:POINts:MODE? (see page 677)	<points_mode> ::= {NORMal | MAXimum | RAW}

Table 37 :WAVeform Commands Summary (continued)

Command	Query	Options and Query Returns
n/a	:WAVeform:PREamble? (see page 679)	<preamble_block> ::= <format NR1>, <type NR1>,<points NR1>,<count NR1>, <xincrement NR3>, <xorigin NR3>, <xreference NR1>,<yincrement NR3>, <yorigin NR3>, <yreference NR1> <format> ::= an integer in NR1 format: • 0 for BYTE format • 1 for WORD format • 2 for ASCii format <type> ::= an integer in NR1 format: • 0 for NORMal type • 1 for PEAK detect type • 3 for AVERage type • 4 for HRESolution type <count> ::= Average count, or 1 if PEAK detect type or NORMal; an integer in NR1 format
n/a	:WAVeform:SEGMented:COUNt? (see page 682)	<count> ::= an integer from 2 to 500 in NR1 format (with SGM license)
n/a	:WAVeform:SEGMented:TTAG? (see page 683)	<time_tag> ::= in NR3 format (with SGM license)
:WAVeform:SOURce <source> (see page 684)	:WAVeform:SOURce? (see page 684)	<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r> | SBUS1 | ABUS | EXT} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format EXT available on 2-channel oscilloscopes only
:WAVeform:SOURce:SUBSource <subsource> (see page 688)	:WAVeform:SOURce:SUBSource? (see page 688)	<subsource> ::= {{SUB0 | RX | MOSI} | {SUB1 | TX | MISO}}
n/a	:WAVeform:TYPE? (see page 689)	<return_mode> ::= {NORM | PEAK | AVER | HRES}
:WAVeform:UNSigned {{0 | OFF} | {1 | ON}} (see page 690)	:WAVeform:UNSigned? (see page 690)	{0 | 1}

Table 37 :WAVeform Commands Summary (continued)

Command	Query	Options and Query Returns
:WAVeform:VIEW <view> (see page 691)	:WAVeform:VIEW? (see page 691)	<view> ::= {MAIN}
n/a	:WAVeform:XINCrement? (see page 692)	<return_value> ::= x-increment in the current preamble in NR3 format
n/a	:WAVeform:XORigin? (see page 693)	<return_value> ::= x-origin value in the current preamble in NR3 format
n/a	:WAVeform:XREFerence? (see page 694)	<return_value> ::= 0 (x-reference value in the current preamble in NR1 format)
n/a	:WAVeform:YINCrement? (see page 695)	<return_value> ::= y-increment value in the current preamble in NR3 format
n/a	:WAVeform:YORigin? (see page 696)	<return_value> ::= y-origin in the current preamble in NR3 format
n/a	:WAVeform:YREFerence? (see page 697)	<return_value> ::= y-reference value in the current preamble in NR1 format

Table 38 :WGEN Commands Summary

Command	Query	Options and Query Returns
:WGEN:FREQuency <frequency> (see page 702)	:WGEN:FREQuency? (see page 702)	<frequency> ::= frequency in Hz in NR3 format
:WGEN:FUNCtion <signal> (see page 703)	:WGEN:FUNCtion? (see page 704)	<signal> ::= {SINusoid | SQUare | RAMP | PULSe | NOISe | DC}
:WGEN:FUNCtion:PULSe:WIDTh <width> (see page 706)	:WGEN:FUNCtion:PULSe:WIDTh? (see page 706)	<width> ::= pulse width in seconds in NR3 format
:WGEN:FUNCtion:RAMP:SYMMetry <percent> (see page 707)	:WGEN:FUNCtion:RAMP:SYMMetry? (see page 707)	<percent> ::= symmetry percentage from 0% to 100% in NR1 format
:WGEN:FUNCtion:SQUare:DCYCle <percent> (see page 708)	:WGEN:FUNCtion:SQUare:DCYCle? (see page 708)	<percent> ::= duty cycle percentage from 1% to 99% in NR1 format

Table 38 :WGEN Commands Summary (continued)

Command	Query	Options and Query Returns
:WGEN:MODulation:AM:DEPTh <percent> (see page 709)	:WGEN:MODulation:AM:DEPTh? (see page 709)	<percent> ::= AM depth percentage from 0% to 100% in NR1 format
:WGEN:MODulation:AM:FREQuency <frequency> (see page 710)	:WGEN:MODulation:AM:FREQuency? (see page 710)	<frequency> ::= modulating waveform frequency in Hz in NR3 format
:WGEN:MODulation:FM:DEViation <frequency> (see page 711)	:WGEN:MODulation:FM:DEViation? (see page 711)	<frequency> ::= frequency deviation in Hz in NR3 format
:WGEN:MODulation:FM:FREQuency <frequency> (see page 712)	:WGEN:MODulation:FM:FREQuency? (see page 712)	<frequency> ::= modulating waveform frequency in Hz in NR3 format
:WGEN:MODulation:FSKey:FREQuency <percent> (see page 713)	:WGEN:MODulation:FSKey:FREQuency? (see page 713)	<frequency> ::= hop frequency in Hz in NR3 format
:WGEN:MODulation:FSKey:RATE <rate> (see page 714)	:WGEN:MODulation:FSKey:RATE? (see page 714)	<rate> ::= FSK modulation rate in Hz in NR3 format
:WGEN:MODulation:FUNCtion <shape> (see page 715)	:WGEN:MODulation:FUNCtion? (see page 715)	<shape> ::= {SINusoid | SQUare| RAMP}
:WGEN:MODulation:FUNCtion:RAMP:SYMMetry <percent> (see page 716)	:WGEN:MODulation:FUNCtion:RAMP:SYMMetry? (see page 716)	<percent> ::= symmetry percentage from 0% to 100% in NR1 format
:WGEN:MODulation:NOISe <percent> (see page 717)	:WGEN:MODulation:NOISe? (see page 717)	<percent> ::= 0 to 100
:WGEN:MODulation:STATe {{0 | OFF} | {1 | ON}} (see page 718)	:WGEN:MODulation:STATe? (see page 718)	{0 | 1}
:WGEN:MODulation:TYPE <type> (see page 719)	:WGEN:MODulation:TYPE? (see page 719)	<type> ::= {AM | FM | FSK}
:WGEN:OUTPut {{0 | OFF} | {1 | ON}} (see page 721)	:WGEN:OUTPut? (see page 721)	{0 | 1}
:WGEN:OUTPut:LOAD <impedance> (see page 722)	:WGEN:OUTPut:LOAD? (see page 722)	<impedance> ::= {ONEMeg | FIFTy}

Table 38 :WGEN Commands Summary (continued)

Command	Query	Options and Query Returns
:WGEN:OUTPut:POLarity <polarity> (see page 723)	:WGEN:OUTPut:POLarity? (see page 723)	<polarity> ::= {NORMal | INVerted}
:WGEN:PERiod <period> (see page 724)	:WGEN:PERiod? (see page 724)	<period> ::= period in seconds in NR3 format
:WGEN:RST (see page 725)	n/a	n/a
:WGEN:VOLTage <amplitude> (see page 726)	:WGEN:VOLTage? (see page 726)	<amplitude> ::= amplitude in volts in NR3 format
:WGEN:VOLTage:HIGH <high> (see page 727)	:WGEN:VOLTage:HIGH? (see page 727)	<high> ::= high-level voltage in volts, in NR3 format
:WGEN:VOLTage:LOW <low> (see page 728)	:WGEN:VOLTage:LOW? (see page 728)	<low> ::= low-level voltage in volts, in NR3 format
:WGEN:VOLTage:OFFSet <offset> (see page 729)	:WGEN:VOLTage:OFFSet? (see page 729)	<offset> ::= offset in volts in NR3 format

Table 39 :WMEMory<r> Commands Summary

Command	Query	Options and Query Returns
:WMEMory<r>:CLEar (see page 733)	n/a	<r> ::= 1-2 in NR1 format
:WMEMory<r>:DISPlay {{0 | OFF} | {1 | ON}} (see page 734)	:WMEMory<r>:DISPlay? (see page 734)	<r> ::= 1-2 in NR1 format {0 | 1}
:WMEMory<r>:LABel <string> (see page 735)	:WMEMory<r>:LABel? (see page 735)	<r> ::= 1-2 in NR1 format <string> ::= any series of 10 or less ASCII characters enclosed in quotation marks
:WMEMory<r>:SAVE <source> (see page 736)	n/a	<r> ::= 1-2 in NR1 format <source> ::= {CHANnel<n> | FUNCtion | MATH} <n> ::= 1 to (# analog channels) in NR1 format NOTE: Only ADD or SUBtract math operations can be saved as reference waveforms.

Table 39 :WMEMory<r> Commands Summary (continued)

Command	Query	Options and Query Returns
:WMEMory<r>:SKEW <skew> (see page 737)	:WMEMory<r>:SKEW? (see page 737)	<r> ::= 1-2 in NR1 format <skew> ::= time in seconds in NR3 format
:WMEMory<r>:YOFFset <offset>[suffix] (see page 738)	:WMEMory<r>:YOFFset? (see page 738)	<r> ::= 1-2 in NR1 format <offset> ::= vertical offset value in NR3 format [suffix] ::= {V | mV}
:WMEMory<r>:YRANge <range>[suffix] (see page 739)	:WMEMory<r>:YRANge? (see page 739)	<r> ::= 1-2 in NR1 format <range> ::= vertical full-scale range value in NR3 format [suffix] ::= {V | mV}
:WMEMory<r>:YSCale <scale>[suffix] (see page 740)	:WMEMory<r>:YSCale? (see page 740)	<r> ::= 1-2 in NR1 format <scale> ::= vertical units per division value in NR3 format [suffix] ::= {V | mV}

Syntax Elements

- "Number Format" on page 113
- "<NL> (Line Terminator)" on page 113
- "[ ] (Optional Syntax Terms)" on page 113
- "{ } (Braces)" on page 113
- "::= (Defined As)" on page 113
- "< > (Angle Brackets)" on page 114
- "... (Ellipsis)" on page 114
- "n,..,p (Value Ranges)" on page 114
- "d (Digits)" on page 114
- "Quoted ASCII String" on page 114
- "Definite-Length Block Response Data" on page 114

Number Format

NR1 specifies integer data.

NR3 specifies exponential data in floating point format (for example, -1.0E-3).

<NL> (Line Terminator)

<NL> = new line or linefeed (ASCII decimal 10).

The line terminator, or a leading colon, will send the parser to the "root" of the command tree.

[ ] (Optional Syntax Terms)

Items enclosed in square brackets, [ ], are optional.

{ } (Braces)

When several items are enclosed by braces, { }, only one of these elements may be selected. Vertical line (|) indicates "or". For example, {ON | OFF} indicates that only ON or OFF may be selected, not both.

::= (Defined As)

::= means "defined as".

For example, <A> ::= <B> indicates that <A> can be replaced by <B> in any statement containing <A>.

< > (Angle Brackets)

< > Angle brackets enclose words or characters that symbolize a program code parameter or an interface command.

... (Ellipsis)

... An ellipsis (trailing dots) indicates that the preceding element may be repeated one or more times.

n,..,p (Value Ranges)

n,..,p ::= all integers between n and p inclusive.

d (Digits)

d ::= A single ASCII numeric character 0 - 9.

Quoted ASCII String

A quoted ASCII string is a string delimited by either double quotes (") or single quotes ('). Some command parameters require a quoted ASCII string. For example, when using the Keysight VISA COM library in Visual Basic, the command:

```
myScope.WriteString ":CHANNEL1:LABEL 'One'"
```

has a quoted ASCII string of:

```
'One'
```

In order to read quoted ASCII strings from query return values, some programming languages require special handling or syntax.

Definite-Length Block Response Data

Definite-length block response data allows any type of device-dependent data to be transmitted over the system interface as a series of 8-bit binary data bytes. This is particularly useful for sending large quantities of data or 8-bit extended ASCII codes. This syntax is a pound sign (#) followed by a non-zero digit representing the number of digits in the decimal integer. After the non-zero digit is the decimal integer that states the number of 8-bit data bytes being sent. This is followed by the actual data.

For example, for transmitting 1000 bytes of data, the syntax would be

```
#800001000<1000 bytes of data> <NL>
```

8 is the number of digits that follow

00001000 is the number of bytes to be transmitted

<1000 bytes of data> is the actual data

5 Common (*) Commands

Commands defined by IEEE 488.2 standard that are common to all instruments.
See "Introduction to Common (*) Commands" on page 119.

Table 40 Common (*) Commands Summary

Command	Query	Options and Query Returns
*CLS (see page 121)	n/a	n/a
*ESE <mask> (see page 122)	*ESE? (see page 123)	<mask> ::= 0 to 255; an integer in NR1 format: Bit Weight Name Enables --- ------ ---- ---------- 7 128 PON Power On 6 64 URQ User Request 5 32 CME Command Error 4 16 EXE Execution Error 3 8 DDE Dev. Dependent Error 2 4 QYE Query Error 1 2 RQL Request Control 0 1 OPC Operation Complete
n/a	*ESR? (see page 124)	<status> ::= 0 to 255; an integer in NR1 format
n/a	*IDN? (see page 124)	KEYSIGHT TECHNOLOGIES,<model>,<serial number>,X.XX.XX <model> ::= the model number of the instrument <serial number> ::= the serial number of the instrument <X.XX.XX> ::= the software revision of the instrument
n/a	*LRN? (see page 127)	<learn_string> ::= current instrument setup as a block of data in IEEE 488.2 # format

Table 40 Common (*) Commands Summary (continued)

Command	Query	Options and Query Returns
*OPC (see page 128)	*OPC? (see page 128)	ASCII "1" is placed in the output queue when all pending device operations have completed.
n/a	*OPT? (see page 129)	<return_value> ::= 0,0,<license info> <license info> ::= <All field>, <reserved>, <reserved>, <reserved>, <Memory>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <Segmented Memory>, <Mask Test>, <reserved>, <Bandwidth>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <Educator's Kit>, <Waveform Generator>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <reserved>, <Digital Voltmeter>, <reserved>, <reserved>, <reserved>, <Remote Command Logging>, <reserved>, <reserved>, <reserved> <All field> ::= {0 | All} <reserved> ::= 0 <Memory> ::= {0 | MEMUP} <Low Speed Serial> ::= {0 | EMBD} <Automotive Serial> ::= {0 | AUTO} <Segmented Memory> ::= {0 | SGM} <Mask Test> ::= {0 | MASK} <Bandwidth> ::= {0 | BW10 | BW20} <Educator's Kit> ::= {0 | EDK} <Waveform Generator> ::= {0 | WAVEGEN} <Digital Voltmeter> ::= {0 | DVM} <Remote Command Logging> ::= {0 | RML}
*RCL <value> (see page 130)	n/a	<value> ::= {0 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9}

Table 40 Common (*) Commands Summary (continued)

Command	Query	Options and Query Returns
*RST (see page 131)	n/a	See *RST (Reset) (see page 131)
*SAV <value> (see page 134)	n/a	<value> ::= {0 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9}
*SRE <mask> (see page 135)	*SRE? (see page 136)	<mask> ::= sum of all bits that are set, 0 to 255; an integer in NR1 format. <mask> ::= following values: Bit Weight Name Enables --- ------ ---- ---------- 7 128 OPER Operation Status Reg 6 64 ---- (Not used.) 5 32 ESB Event Status Bit 4 16 MAV Message Available 3 8 ---- (Not used.) 2 4 MSG Message 1 2 USR User 0 1 TRG Trigger
n/a	*STB? (see page 137)	<value> ::= 0 to 255; an integer in NR1 format, as shown in the following: Bit Weight Name "1" Indicates --- ------ ---- --------------- 7 128 OPER Operation status condition occurred. 6 64 RQS/ MSS Instrument is requesting service. 5 32 ESB Enabled event status condition occurred. 4 16 MAV Message available. 3 8 ---- (Not used.) 2 4 MSG Message displayed. 1 2 USR User event condition occurred. 0 1 TRG A trigger occurred.
*TRG (see page 139)	n/a	n/a
n/a	*TST? (see page 140)	<result> ::= 0 or non-zero value; an integer in NR1 format
*WAI (see page 141)	n/a	n/a

Introduction to Common (*) Commands

The common commands are defined by the IEEE 488.2 standard. They are implemented by all instruments that comply with the IEEE 488.2 standard. They provide some of the basic instrument functions, such as instrument identification and reset, reading the instrument setup, and determining how status is read and cleared.

Common commands can be received and processed by the instrument whether they are sent over the interface as separate program messages or within other program messages. If an instrument subsystem has been selected and a common command is received by the instrument, the instrument remains in the selected subsystem. For example, if the program message ":ACQuire:TYPE AVERage; *CLS; COUNt 256" is received by the instrument, the instrument sets the acquire type, then clears the status information and sets the average count.

In contrast, if a root level command or some other subsystem command is within the program message, you must re-enter the original subsystem after the command. For example, the program message ":ACQuire:TYPE AVERage; :AUToscale; :ACQuire:COUNt 256" sets the acquire type, completes the autoscale, then sets the acquire count. In this example, :ACQuire must be sent again after the :AUToscale command in order to re-enter the ACQuire subsystem and set the count.

NOTE Each of the status registers has an enable (mask) register. By setting the bits in the enable register, you can select the status information you want to use.

*CLS (Clear Status)

(see page 828)

Command Syntax `*CLS`

The *CLS common command clears the status data structures, the device-defined error queue, and the Request-for-OPC flag.

NOTE **If the *CLS command immediately follows a program message terminator, the output queue and the MAV (message available) bit are cleared.**

See Also

- "Introduction to Common (*) Commands" on page 119
- "*STB (Read Status Byte)" on page 137
- "*ESE (Standard Event Status Enable)" on page 122
- "*ESR (Standard Event Status Register)" on page 124
- "*SRE (Service Request Enable)" on page 135
- ":SYSTem:ERRor" on page 581

*ESE (Standard Event Status Enable)

(see page 828)

Command Syntax

```
*ESE <mask_argument>

<mask_argument> ::= integer from 0 to 255
```

The *ESE common command sets the bits in the Standard Event Status Enable Register. The Standard Event Status Enable Register contains a mask value for the bits to be enabled in the Standard Event Status Register. A "1" in the Standard Event Status Enable Register enables the corresponding bit in the Standard Event Status Register. A zero disables the bit.



Table 41 Standard Event Status Enable (ESE)

Bit	Name	Description	When Set (1 = High = True), Enables:
7	PON	Power On	Event when an OFF to ON transition occurs.
6	URQ	User Request	Event when a front-panel key is pressed.
5	CME	Command Error	Event when a command error is detected.
4	EXE	Execution Error	Event when an execution error is detected.
3	DDE	Device Dependent Error	Event when a device-dependent error is detected.
2	QYE	Query Error	Event when a query error is detected.
1	RQL	Request Control	Event when the device is requesting control. (Not used.)
0	OPC	Operation Complete	Event when an operation is complete.

Query Syntax

```
*ESE?
```

The *ESE? query returns the current contents of the Standard Event Status Enable Register.

Return Format

```
<mask_argument><NL>

<mask_argument> ::= 0,..,255; an integer in NR1 format.
```

See Also

- "Introduction to Common (*) Commands" on page 119
- "*ESR (Standard Event Status Register)" on page 124
- "*OPC (Operation Complete)" on page 128
- "*CLS (Clear Status)" on page 121

*ESR (Standard Event Status Register)

(see page 828)

Query Syntax `*ESR?`

The *ESR? query returns the contents of the Standard Event Status Register. When you read the Event Status Register, the value returned is the total bit weights of all of the bits that are high at the time you read the byte. Reading the register clears the Event Status Register.

The following table shows bit weight, name, and condition for each bit.



Table 42 Standard Event Status Register (ESR)

Bit	Name	Description	When Set (1 = High = True), Indicates:
7	PON	Power On	An OFF to ON transition has occurred.
6	URQ	User Request	A front-panel key has been pressed.
5	CME	Command Error	A command error has been detected.
4	EXE	Execution Error	An execution error has been detected.
3	DDE	Device Dependent Error	A device-dependent error has been detected.
2	QYE	Query Error	A query error has been detected.
1	RQL	Request Control	The device is requesting control. (Not used.)
0	OPC	Operation Complete	Operation is complete.

Return Format

```
<status><NL>

<status> ::= 0,..,255; an integer in NR1 format.
```

NOTE Reading the Standard Event Status Register clears it. High or 1 indicates the bit is true.

See Also

- "Introduction to Common (*) Commands" on page 119
- "*ESE (Standard Event Status Enable)" on page 122
- "*OPC (Operation Complete)" on page 128
- "*CLS (Clear Status)" on page 121
- ":SYSTem:ERRor" on page 581

*IDN (Identification Number)

(see page 828)

Query Syntax `*IDN?`

The *IDN? query identifies the instrument type and software version.

Return Format

```
<manufacturer_string>,<model>,<serial_number>,X.XX.XX <NL>
<manufacturer_string> ::= KEYSIGHT TECHNOLOGIES
<model> ::= the model number of the instrument
<serial_number> ::= the serial number of the instrument
X.XX.XX ::= the software revision of the instrument
```

See Also

- "Introduction to Common (*) Commands" on page 119
- "*OPT (Option Identification)" on page 129
- ":SYSTem:PERSona[:MANufacturer]" on page 584
- ":SYSTem:PERSona[:MANufacturer]:DEFault" on page 585

*LRN (Learn Device Setup)

(see page 828)

Query Syntax

```
*LRN?
```

The *LRN? query result contains the current state of the instrument. This query is similar to the :SYSTem:SETup? (see page 597) query, except that it contains ":SYST:SET " before the binary block data. The query result is a valid command that can be used to restore instrument settings at a later time.

Return Format

```
<learn_string><NL>

<learn_string> ::= :SYST:SET <setup_data>

<setup_data> ::= binary block data in IEEE 488.2 # format
```

<learn string> specifies the current instrument setup. The block size is subject to change with different firmware revisions.

NOTE The *LRN? query return format has changed from previous Keysight oscilloscopes to match the IEEE 488.2 specification which says that the query result must contain ":SYST:SET " before the binary block data.

See Also

- "Introduction to Common (*) Commands" on page 119
- "*RCL (Recall)" on page 130
- "*SAV (Save)" on page 134
- ":SYSTem:SETup" on page 597

*OPC (Operation Complete)

(see page 828)

Command Syntax

```
*OPC
```

The *OPC command sets the operation complete bit in the Standard Event Status Register when all pending device operations have finished.

Query Syntax

```
*OPC?
```

The *OPC? query places an ASCII "1" in the output queue when all pending device operations have completed. The interface hangs until this query returns.

Return Format

```
<complete><NL>

<complete> ::= 1
```

See Also

- "Introduction to Common (*) Commands" on page 119
- "*ESE (Standard Event Status Enable)" on page 122
- "*ESR (Standard Event Status Register)" on page 124
- "*CLS (Clear Status)" on page 121

*OPT (Option Identification)

(see page 828)

Query Syntax

```
*OPT?
```

The *OPT? query reports the options installed in the instrument. This query returns a string that identifies the module and its software revision level.

Return Format

```
0,0,<license info>

<license info> ::= <All field>, <reserved>, <reserved>, <reserved>,
   <Memory>, <Low Speed Serial>, <Automotive Serial>, <reserved>,
   <reserved>, <reserved>, <Segmented Memory>, <Mask Test>, <reserved>,
   <Bandwidth>, <reserved>, <reserved>, <reserved>, <reserved>,
   <reserved>, <reserved>, <Educator's Kit>, <Waveform Generator>,
   <reserved>, <reserved>, <reserved>, <reserved>, <reserved>,
   <reserved>, <reserved>, <Digital Voltmeter>, <reserved>, <reserved>,
   <reserved>, <Remote Command Logging>, <reserved>, <reserved>,
   <reserved>

<All field> ::= {0 | All}

<reserved> ::= 0

<Memory> ::= {0 | MEMUP}

<Low Speed Serial> ::= {0 | EMBD}

<Automotive Serial> ::= {0 | AUTO}

<Segmented Memory> ::= {0 | SGM}

<Mask Test> ::= {0 | MASK}

<Bandwidth> ::= {0 | BW10 | BW20}

<Educator's Kit> ::= {0 | EDK}

<Waveform Generator> ::= {0 | WAVEGEN}

<Digital Voltmeter> ::= {0 | DVM}

<Remote Command Logging> ::= {0 | RML}
```

The *OPT? query returns the following:

Module	Module Id
No modules attached	0,0,0,0,0,0,0,0,0,0,0,0,0,SGM,MASK,0,0,0,0,0,0,0,0,EDK,WAVEGEN,0,0,0,0,0,0,0,0,0,0,0,0,RML,0,0,0

See Also

- "Introduction to Common (*) Commands" on page 119
- "*IDN (Identification Number)" on page 126

*RCL (Recall)

(see page 828)

Command Syntax

```
*RCL <value>

<value> ::= {0 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9}
```

The *RCL command restores the state of the instrument from the specified save/recall register.

See Also

- "Introduction to Common (*) Commands" on page 119
- "*SAV (Save)" on page 134

*RST (Reset)

C (see page 828)

Command Syntax `*RST`

The *RST command places the instrument in a known state. This is the same as pressing **[Save/Recall] > Default/Erase > Factory Default** on the front panel.

When you perform a factory default setup, there are no user settings that remain unchanged. To perform the equivalent of the front panel's **[Default Setup]** key, where some user settings (like preferences) remain unchanged, use the :SYSTem:PRESet command.

Reset conditions are:

Acquire Menu	
Mode	Normal
Averaging	Off
# Averages	8

Analog Channel Menu	
Channel 1	On
Channel 2	Off
Volts/division	5.00 V
Offset	0.00
Coupling	DC
Probe attenuation	10:1
Vernier	Off
Invert	Off
BW limit	Off
Impedance	1 M Ohm (cannot be changed)
Units	Volts
Skew	0

Cursor Menu	
Source	Channel 1

Display Menu	
Persistence	Off
Grid	20%

Quick Meas Menu	
Source	Channel 1

Run Control	
	Scope is running

Time Base Menu	
Main time/division	100 us
Main time base delay	0.00 s
Delay time/division	500 ns
Delay time base delay	0.00 s
Reference	center
Mode	main
Vernier	Off

Trigger Menu	
Type	Edge
Mode	Auto
Coupling	dc
Source	Channel 1
Level	0.0 V
Slope	Positive
HF Reject and noise reject	Off
Holdoff	60 ns
External probe attenuation	10:1
External Units	Volts
External Impedance	1 M Ohm (cannot be changed)

See Also
- "Introduction to Common (*) Commands" on page 119
- ":SYSTem:PRESet" on page 586

Example Code

```
' RESET - This command puts the oscilloscope into a known state.
' This statement is very important for programs to work as expected.
' Most of the following initialization commands are initialized by
' *RST.  It is not necessary to reinitialize them unless the default
' setting is not suitable for your application.
myScope.WriteString "*RST"  ' Reset the oscilloscope to the defaults.
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

*SAV (Save)

(see page 828)

Command Syntax

```
*SAV <value>

<value> ::= {0 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9}
```

The *SAV command stores the current state of the instrument in a save register. The data parameter specifies the register where the data will be saved.

See Also

- "Introduction to Common (*) Commands" on page 119
- "*RCL (Recall)" on page 130

*SRE (Service Request Enable)

(see page 828)

Command Syntax

```
*SRE <mask>

<mask> ::= integer with values defined in the following table.
```

The *SRE command sets the bits in the Service Request Enable Register. The Service Request Enable Register contains a mask value for the bits to be enabled in the Status Byte Register. A one in the Service Request Enable Register enables the corresponding bit in the Status Byte Register. A zero disables the bit.



Table 43 Service Request Enable Register (SRE)

Bit	Name	Description	When Set (1 = High = True), Enables:
7	OPER	Operation Status Register	Interrupts when enabled conditions in the Operation Status Register (OPER) occur.
6	---	---	(Not used.)
5	ESB	Event Status Bit	Interrupts when enabled conditions in the Standard Event Status Register (ESR) occur.
4	MAV	Message Available	Interrupts when messages are in the Output Queue.
3	---	---	(Not used.)
2	MSG	Message	Interrupts when an advisory has been displayed on the oscilloscope.
1	USR	User Event	Interrupts when enabled user event conditions occur.
0	TRG	Trigger	Interrupts when a trigger occurs.

Query Syntax

```
*SRE?
```

The *SRE? query returns the current value of the Service Request Enable Register.

Return Format

```
<mask><NL>

<mask> ::= sum of all bits that are set, 0,..,255;
           an integer in NR1 format
```

See Also

- "Introduction to Common (*) Commands" on page 119
- "*STB (Read Status Byte)" on page 137
- "*CLS (Clear Status)" on page 121

*STB (Read Status Byte)

(see page 828)

Query Syntax `*STB?`

The *STB? query returns the current value of the instrument's status byte. The MSS (Master Summary Status) bit is reported on bit 6 instead of the RQS (request service) bit. The MSS indicates whether or not the device has at least one reason for requesting service.

Return Format `<value><NL>`

`<value> ::= 0,..,255; an integer in NR1 format`



Table 44 Status Byte Register (STB)

Bit	Name	Description	When Set (1 = High = True), Indicates:
7	OPER	Operation Status Register	An enabled condition in the Operation Status Register (OPER) has occurred.
6	RQS	Request Service	When polled, that the device is requesting service.
	MSS	Master Summary Status	When read (by *STB?), whether the device has a reason for requesting service.
5	ESB	Event Status Bit	An enabled condition in the Standard Event Status Register (ESR) has occurred.
4	MAV	Message Available	There are messages in the Output Queue.
3	---	---	(Not used, always 0.)
2	MSG	Message	An advisory has been displayed on the oscilloscope.
1	USR	User Event	An enabled user event condition has occurred.
0	TRG	Trigger	A trigger has occurred.

NOTE To read the instrument's status byte with RQS reported on bit 6, use the interface Serial Poll.

See Also
- "Introduction to Common (*) Commands" on page 119
- "*SRE (Service Request Enable)" on page 135

*TRG (Trigger)

(see page 828)

Command Syntax `*TRG`

The *TRG command has the same effect as the :DIGitize command with no parameters.

See Also

- "Introduction to Common (*) Commands" on page 119
- ":DIGitize" on page 153
- ":RUN" on page 170
- ":STOP" on page 174

*TST (Self Test)

(see page 828)

Query Syntax `*TST?`

The *TST? query performs a self-test on the instrument. The result of the test is placed in the output queue. A zero indicates the test passed and a non-zero indicates the test failed. If the test fails, refer to the troubleshooting section of the *Service Guide*.

Return Format `<result><NL>`

`<result> ::= 0 or non-zero value; an integer in NR1 format`

See Also

- "Introduction to Common (*) Commands" on page 119

*WAI (Wait To Continue)

(see page 828)

Command Syntax `*WAI`

The *WAI command has no function in the oscilloscope, but is parsed for compatibility with other instruments.

See Also

- "Introduction to Common (*) Commands" on page 119

6 Root (:) Commands

Control many of the basic functions of the oscilloscope and reside at the root level of the command tree. See "Introduction to Root (:) Commands" on page 145.

Table 45 Root (:) Commands Summary

Command	Query	Options and Query Returns
n/a	:AER? (see page 146)	{0 | 1}; an integer in NR1 format
:AUToscale [<source>[,..,<source>]] (see page 147)	n/a	<source> ::= CHANnel<n> <source> can be repeated up to 5 times <n> ::= 1 to (# analog channels) in NR1 format
:AUToscale:AMODE <value> (see page 149)	:AUToscale:AMODE? (see page 149)	<value> ::= {NORMal | CURRent}}
:AUToscale:CHANnels <value> (see page 150)	:AUToscale:CHANnels? (see page 150)	<value> ::= {ALL | DISPlayed}}
:AUToscale:FDEBug {{0 | OFF} | {1 | ON}} (see page 151)	:AUToscale:FDEBug? (see page 151)	{0 | 1}
:BLANk [<source>] (see page 152)	n/a	<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r> | ABUS | EXT} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format EXT available on 2-channel oscilloscopes only

Table 45 Root (:) Commands Summary (continued)

Command	Query	Options and Query Returns
:DIGitize [<source>[,..,<source>]] (see page 153)	n/a	<source> ::= {CHANnel<n> | FUNCtion | MATH | SBUS{1} | FFT | ABUS | EXT} <source> can be repeated up to 5 times <n> ::= 1 to (# analog channels) in NR1 format EXT available on 2-channel oscilloscopes only
:MTEenable <n> (see page 155)	:MTEenable? (see page 155)	<n> ::= 16-bit integer in NR1 format
n/a	:MTERegister[:EVENt]? (see page 157)	<n> ::= 16-bit integer in NR1 format
:OPEE <n> (see page 159)	:OPEE? (see page 160)	<n> ::= 15-bit integer in NR1 format
n/a	:OPERregister:CONDition? (see page 161)	<n> ::= 15-bit integer in NR1 format
n/a	:OPERegister[:EVENt]? (see page 163)	<n> ::= 15-bit integer in NR1 format
:OVLenable <mask> (see page 165)	:OVLenable? (see page 165)	<mask> ::= 16-bit integer in NR1 format as shown: Bit Weight Input --- ------ ---------- 10 1024 Ext Trigger Fault 9 512 Channel 4 Fault 8 256 Channel 3 Fault 7 128 Channel 2 Fault 6 64 Channel 1 Fault 4 16 Ext Trigger OVL 3 8 Channel 4 OVL 2 4 Channel 3 OVL 1 2 Channel 2 OVL 0 1 Channel 1 OVL
n/a	:OVLRegister? (see page 167)	<value> ::= integer in NR1 format. See OVLenable for <value>

Table 45 Root (:) Commands Summary (continued)

Command	Query	Options and Query Returns
:PRINt [<options>] (see page 169)	n/a	<options> ::= [<print option>][,..,<print option>] <print option> ::= {COLor | GRAYscale | PRINter0 | PRINter1 | BMP8bit | BMP | PNG | NOFactors | FACTors} <print option> can be repeated up to 5 times.
:RUN (see page 170)	n/a	n/a
n/a	:SERial (see page 171)	<return value> ::= unquoted string containing serial number
:SINGle (see page 172)	n/a	n/a
n/a	:STATus? <display> (see page 173)	{0 | 1} <display> ::= {CHANnel<n> | FUNCtion | MATH | SBUS{1} | FFT | WMEMory<r> | ABUS | EXT} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format EXT available on 2-channel oscilloscopes only
:STOP (see page 174)	n/a	n/a
n/a	:TER? (see page 175)	{0 | 1}
:VIEW <source> (see page 176)	n/a	<source> ::= {CHANnel<n> | FUNCtion | MATH | SBUS{1} | FFT | WMEMory<r> | ABUS | EXT} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format EXT available on 2-channel oscilloscopes only

Introduction to Root (:) Commands

Root level commands control many of the basic operations of the instrument. These commands are always recognized by the parser if they are prefixed with a colon, regardless of current command tree position. After executing a root-level command, the parser is positioned at the root of the command tree.

:AER (Arm Event Register)

(see page 828)

Query Syntax `:AER?`

The AER query reads the Arm Event Register. After the Arm Event Register is read, it is cleared. A "1" indicates the trigger system is in the armed state, ready to accept a trigger.

The Armed Event Register is summarized in the Wait Trig bit of the Operation Status Event Register. A Service Request can be generated when the Wait Trig bit transitions and the appropriate enable bits have been set in the Operation Status Enable Register (OPEE) and the Service Request Enable Register (SRE).

Return Format `<value><NL>`

`<value> ::= {0 | 1}; an integer in NR1 format.`

See Also

- "Introduction to Root (:) Commands" on page 145
- ":OPEE (Operation Status Enable Register)" on page 159
- ":OPERegister:CONDition (Operation Status Condition Register)" on page 161
- ":OPERegister[:EVENt] (Operation Status Event Register)" on page 163
- "*STB (Read Status Byte)" on page 137
- "*SRE (Service Request Enable)" on page 135

:AUToscale

(see page 828)

Command Syntax

```
:AUToscale

:AUToscale [<source>[,..,<source>]]

<source> ::= CHANnel<n>

<n> ::= 1 to (# analog channels) in NR1 format

The <source> parameter may be repeated up to 5 times.
```

The :AUToscale command evaluates all input signals and sets the correct conditions to display the signals. This is the same as pressing the **[Auto Scale]** key on the front panel.

If one or more sources are specified, those specified sources will be enabled and all others blanked. The autoscale channels mode (see ":AUToscale:CHANnels" on page 150) is set to DISPlayed channels. Then, the autoscale is performed.

When the :AUToscale command is sent, the following conditions are affected and actions are taken:

- Thresholds.
- Channels with activity around the trigger point are turned on, others are turned off.
- Channels are reordered on screen; analog channel 1 first, followed by the remaining analog channels.
- Delay is set to 0 seconds.
- Time/Div.

The :AUToscale command does not affect the following conditions:

- Label names.
- Trigger conditioning.

The :AUToscale command turns off the following items:

- Cursors.
- Measurements.
- Math waveforms.
- Reference waveforms.
- Zoomed (delayed) time base mode.

For further information on :AUToscale, see the *User's Guide*.

See Also

- "Introduction to Root (:) Commands" on page 145
- ":AUToscale:CHANnels" on page 150

- ":AUToscale:AMODE" on page 149

Example Code

```
' AUTOSCALE - This command evaluates all the input signals and sets
' the correct conditions to display all of the active signals.
myScope.WriteString ":AUToscale"    ' Same as pressing Auto Scale key.
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:AUToscale:AMODE

(see page 828)

Command Syntax

```
:AUToscale:AMODE <value>

<value> ::= {NORMal | CURRent}
```

The :AUTOscale:AMODE command specifies the acquisition mode that is set by subsequent :AUToscales.

- When NORMal is selected, an :AUToscale command sets the NORMal acquisition type and the RTIMe (real-time) acquisition mode.
- When CURRent is selected, the current acquisition type and mode are kept on subsequent :AUToscales.

Use the :ACQuire:TYPE and :ACQuire:MODE commands to set the acquisition type and mode.

Query Syntax

```
:AUToscale:AMODE?
```

The :AUToscale:AMODE? query returns the autoscale acquire mode setting.

Return Format

```
<value><NL>

<value> ::= {NORM | CURR}
```

See Also

- "Introduction to Root (:) Commands" on page 145
- ":AUToscale" on page 147
- ":AUToscale:CHANnels" on page 150
- ":ACQuire:TYPE" on page 199
- ":ACQuire:MODE" on page 191

:AUToscale:CHANnels

(see page 828)

Command Syntax

```
:AUToscale:CHANnels <value>

<value> ::= {ALL | DISPlayed}
```

The :AUTOscale:CHANnels command specifies which channels will be displayed on subsequent :AUToscales.

- When ALL is selected, all channels that meet the requirements of :AUToscale will be displayed.
- When DISPlayed is selected, only the channels that are turned on are autoscaled.

Use the :VIEW or :BLANk root commands to turn channels on or off.

Query Syntax

```
:AUToscale:CHANnels?
```

The :AUToscale:CHANnels? query returns the autoscale channels setting.

Return Format

```
<value><NL>

<value> ::= {ALL | DISP}
```

See Also

- "Introduction to Root (:) Commands" on page 145
- ":AUToscale" on page 147
- ":AUToscale:AMODE" on page 149
- ":VIEW" on page 176
- ":BLANk" on page 152

:AUToscale:FDEBug

N (see page 828)

Command Syntax

```
:AUToscale:FDEBug <on_off>

<on_off> ::= {{1 | ON} | {0 | OFF}}
```

The :AUToscale:FDEBug command turns fast debug auto scaling on or off.

The Fast Debug option changes the behavior of :AUToscale to let you make quick visual comparisons to determine whether the signal being probed is a DC voltage, ground, or an active AC signal.

Channel coupling is maintained for easy viewing of oscillating signals.

Query Syntax

```
:AUToscale:FDEBug?
```

The :AUToscale:FDEBug? query returns the current autoscale fast debug setting.

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- "Introduction to Root (:) Commands" on page 145
- ":AUToscale" on page 147

:BLANk

(see page 828)

Command Syntax

```
:BLANk [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | SBUS{1} | FFT
   | WMEMory<r> | ABUS | EXT}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1 to (# ref waveforms) in NR1 format
```

The :BLANk command turns off (stops displaying) the specified channel, math function, or serial decode bus. The :BLANk command with no parameter turns off all sources.

NOTE To turn on (start displaying) a channel, etc., use the :VIEW command. The DISPlay commands, :CHANnel<n>:DISPlay, :FUNCtion:DISPlay, or :WMEMory<r>:DISPlay, are the preferred method to turn on/off a channel, etc.

NOTE MATH is an alias for FUNCtion.

NOTE The EXT source is available on 2-channel oscilloscopes only.

See Also

- "Introduction to Root (:) Commands" on page 145
- ":DISPlay:CLEar" on page 243
- ":CHANnel<n>:DISPlay" on page 217
- ":FUNCtion:DISPlay" on page 304
- ":WMEMory<r>:DISPlay" on page 734
- ":STATus" on page 173
- ":VIEW" on page 176

Example Code

- "Example Code" on page 176

:DIGitize

(see page 828)

Command Syntax

```
:DIGitize [<source>[,..,<source>]]

<source> ::= {CHANnel<n> | FUNCtion | MATH | SBUS{1} | FFT | ABUS
   | EXT}

<n> ::= 1 to (# analog channels) in NR1 format

The <source> parameter may be repeated up to 5 times.
```

The :DIGitize command is a specialized RUN command. It causes the instrument to acquire waveforms according to the settings of the :ACQuire commands subsystem. When the acquisition is complete, the instrument is stopped.

If no argument is given, :DIGitize acquires the channels currently displayed. If no channels are displayed, all channels are acquired.

NOTE The :DIGitize command is only executed when the :TIMebase:MODE is MAIN or WINDow.

NOTE To halt a :DIGitize in progress, use the device clear command.

NOTE MATH is an alias for FUNCtion.

NOTE The EXT source is available on 2-channel oscilloscopes only.

See Also

- "Introduction to Root (:) Commands" on page 145
- ":RUN" on page 170
- ":SINGle" on page 172
- ":STOP" on page 174
- ":TIMebase:MODE" on page 605
- Chapter 8, ":ACQuire Commands," starting on page 187
- Chapter 29, ":WAVeform Commands," starting on page 663

Example Code

```
' Capture an acquisition using :DIGitize.
' ------------------------------------------------------------------
myScope.WriteString ":DIGitize CHANnel1"
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:MTEenable (Mask Test Event Enable Register)

N (see page 828)

Command Syntax

```
:MTEenable <mask>

<mask> ::= 16-bit integer
```

The :MTEenable command sets a mask in the Mask Test Event Enable register. Set any of the following bits to "1" to enable bit 9 in the Operation Status Condition Register and potentially cause an SRQ (Service Request interrupt to be generated.



Table 46 Mask Test Event Enable Register (MTEenable)

Bit	Name	Description	When Set (1 = High = True), Enables:
15-11	---	---	(Not used.)
10	Auto Mask	Auto Mask Created	Auto mask creation completed.
9	---	---	(Not used.)
8	Started	Mask Testing Started	Mask testing started.
7-2	---	---	(Not used.)
1	Fail	Mask Test Fail	Mask test failed.
0	Complete	Mask Test Complete	Mask test is complete.

Query Syntax

```
:MTEenable?
```

The :MTEenable? query returns the current value contained in the Mask Test Event Enable register as an integer number.

Return Format

```
<value><NL>

<value> ::= integer in NR1 format.
```

See Also
- "Introduction to Root (:) Commands" on page 145
- ":AER (Arm Event Register)" on page 146
- ":CHANnel<n>:PROTection" on page 227
- ":OPERegister[:EVENt] (Operation Status Event Register)" on page 163
- ":OVLenable (Overload Event Enable Register)" on page 165
- ":OVLRegister (Overload Event Register)" on page 167
- "*STB (Read Status Byte)" on page 137
- "*SRE (Service Request Enable)" on page 135

:MTERegister[:EVENt] (Mask Test Event Event Register)

N (see page 828)

Query Syntax `:MTERegister[:EVENt]?`

The :MTERegister[:EVENt]? query returns the integer value contained in the Mask Test Event Event Register and clears the register.



Table 47 Mask Test Event Event Register

Bit	Name	Description	When Set (1 = High = True), Indicates:
15-11	---	---	(Not used.)
10	Auto Mask	Auto Mask Created	Auto mask creation completed.
9	---	---	(Not used.)
8	Started	Mask Testing Started	Mask testing started.
7-2	---	---	(Not used.)
1	Fail	Mask Test Fail	The mask test failed.
0	Complete	Mask Test Complete	The mask test is complete.

Return Format `<value><NL>`

`<value> ::= integer in NR1 format.`

See Also
- "Introduction to Root (:) Commands" on page 145
- ":CHANnel<n>:PROTection" on page 227
- ":OPEE (Operation Status Enable Register)" on page 159
- ":OPERegister:CONDition (Operation Status Condition Register)" on page 161

- ":OVLenable (Overload Event Enable Register)" on page 165
- ":OVLRegister (Overload Event Register)" on page 167
- "*STB (Read Status Byte)" on page 137
- "*SRE (Service Request Enable)" on page 135

:OPEE (Operation Status Enable Register)

(see page 828)

Command Syntax

```
:OPEE <mask>

<mask> ::= 15-bit integer
```

The :OPEE command sets a mask in the Operation Status Enable register. Set any of the following bits to "1" to enable bit 7 in the Status Byte Register and potentially cause an SRQ (Service Request interrupt to be generated.



Table 48 Operation Status Enable Register (OPEE)

Bit	Name	Description	When Set (1 = High = True), Enables:
14-12	---	---	(Not used.)
11	OVLR	Overload	Event when 50Ω input overload occurs.
10	---	---	(Not used.)
9	MTE	Mask Test Event	Event when mask test event occurs.
8-6	---	---	(Not used.)
5	Wait Trig	Wait Trig	Event when the trigger is armed.
4	---	---	(Not used.)

Table 48 Operation Status Enable Register (OPEE) (continued)

Bit	Name	Description	When Set (1 = High = True), Enables:
3	Run	Running	Event when the oscilloscope is running (not stopped).
2-0	---	---	(Not used.)

Query Syntax

```
:OPEE?
```

The :OPEE? query returns the current value contained in the Operation Status Enable register as an integer number.

Return Format

```
<value><NL>

<value> ::= integer in NR1 format.
```

See Also

- "Introduction to Root (:) Commands" on page 145
- ":AER (Arm Event Register)" on page 146
- ":CHANnel<n>:PROTection" on page 227
- ":OPERegister[:EVENt] (Operation Status Event Register)" on page 163
- ":OVLenable (Overload Event Enable Register)" on page 165
- ":OVLRegister (Overload Event Register)" on page 167
- "*STB (Read Status Byte)" on page 137
- "*SRE (Service Request Enable)" on page 135

:OPERegister:CONDition (Operation Status Condition Register)

(see page 828)

Query Syntax `:OPERegister:CONDition?`

The :OPERegister:CONDition? query returns the integer value contained in the Operation Status Condition Register.



Table 49 Operation Status Condition Register

Bit	Name	Description	When Set (1 = High = True), Indicates:
14-12	---	---	(Not used.)
11	OVLR	Overload	A 50Ω input overload has occurred.
10	---	---	(Not used.)
9	MTE	Mask Test Event	A mask test event has occurred.
8-6	---	---	(Not used.)
5	Wait Trig	Wait Trig	The trigger is armed (set by the Trigger Armed Event Register (TER)).
4	---	---	(Not used.)
3	Run	Running	The oscilloscope is running (not stopped).
2-0	---	---	(Not used.)

Return Format `<value><NL>`

```
<value> ::= integer in NR1 format.
```

See Also

- "Introduction to Root (:) Commands" on page 145
- ":CHANnel<n>:PROTection" on page 227
- ":OPEE (Operation Status Enable Register)" on page 159
- ":OPERegister[:EVENt] (Operation Status Event Register)" on page 163
- ":OVLenable (Overload Event Enable Register)" on page 165
- ":OVLRegister (Overload Event Register)" on page 167
- "*STB (Read Status Byte)" on page 137
- "*SRE (Service Request Enable)" on page 135
- ":MTERegister[:EVENt] (Mask Test Event Event Register)" on page 157
- ":MTEenable (Mask Test Event Enable Register)" on page 155

:OPERegister[:EVENt] (Operation Status Event Register)

(see page 828)

Query Syntax `:OPERegister[:EVENt]?`

The :OPERegister[:EVENt]? query returns the integer value contained in the Operation Status Event Register.



Table 50 Operation Status Event Register

Bit	Name	Description	When Set (1 = High = True), Indicates:
14-12	---	---	(Not used.)
11	OVLR	Overload	A 50Ω input overload has occurred.
10	---	---	(Not used.)
9	MTE	Mask Test Event	A mask test event has occurred.
8-6	---	---	(Not used.)
5	Wait Trig	Wait Trig	The trigger is armed (set by the Trigger Armed Event Register (TER)).
4	---	---	(Not used.)
3	Run	Running	The oscilloscope has gone from a stop state to a single or running state.
2-0	---	---	(Not used.)

Return Format

```
<value><NL>

<value> ::= integer in NR1 format.
```

See Also

- "Introduction to Root (:) Commands" on page 145
- ":CHANnel<n>:PROTection" on page 227
- ":OPEE (Operation Status Enable Register)" on page 159
- ":OPERegister:CONDition (Operation Status Condition Register)" on page 161
- ":OVLenable (Overload Event Enable Register)" on page 165
- ":OVLRegister (Overload Event Register)" on page 167
- "*STB (Read Status Byte)" on page 137
- "*SRE (Service Request Enable)" on page 135
- ":MTERegister[:EVENt] (Mask Test Event Event Register)" on page 157
- ":MTEenable (Mask Test Event Enable Register)" on page 155

:OVLenable (Overload Event Enable Register)

(see page 828)

Command Syntax

```
:OVLenable <enable_mask>

<enable_mask> ::= 16-bit integer
```

The overload enable mask is an integer representing an input as described in the following table.

The :OVLenable command sets the mask in the Overload Event Enable Register and enables the reporting of the Overload Event Register. If enabled, such an event will set bit 11 in the Operation Status Register.



Table 51 Overload Event Enable Register (OVL)

Bit	Description	When Set (1 = High = True), Enables:
15-8	---	(Not used.)
7	Channel 2 Fault	Event when fault occurs on Channel 2 input.
6	Channel 1 Fault	Event when fault occurs on Channel 1 input.
5-2	---	(Not used.)
1	Channel 2 OVL	Event when overload occurs on Channel 2 input.
0	Channel 1 OVL	Event when overload occurs on Channel 1 input.

Query Syntax

```
:OVLenable?
```

The :OVLenable query returns the current enable mask value contained in the Overload Event Enable Register.

Return Format

```
<enable_mask><NL>

<enable_mask> ::= integer in NR1 format.
```

See Also

- "Introduction to Root (:) Commands" on page 145
- ":CHANnel<n>:PROTection" on page 227
- ":OPEE (Operation Status Enable Register)" on page 159
- ":OPERegister:CONDition (Operation Status Condition Register)" on page 161
- ":OPERegister[:EVENt] (Operation Status Event Register)" on page 163
- ":OVLRegister (Overload Event Register)" on page 167
- "*STB (Read Status Byte)" on page 137
- "*SRE (Service Request Enable)" on page 135

:OVLRegister (Overload Event Register)

(see page 828)

Query Syntax `:OVLRegister?`

The :OVLRegister query returns the overload protection value stored in the Overload Event Register (OVLR). A "1" indicates an overload has occurred.



Table 52 Overload Event Register (OVLR)

Bit	Description	When Set (1 = High = True), Indicates:
15-8	---	(Not used.)
7	Channel 2 Fault	Fault has occurred on Channel 2 input.
6	Channel 1 Fault	Fault has occurred on Channel 1 input.
5-2	---	(Not used.)
1	Channel 2 OVL	Overload has occurred on Channel 2 input.
0	Channel 1 OVL	Overload has occurred on Channel 1 input.

Return Format `<value><NL>`

`<value> ::= integer in NR1 format.`

See Also

- "Introduction to Root (:) Commands" on page 145
- ":CHANnel<n>:PROTection" on page 227
- ":OPEE (Operation Status Enable Register)" on page 159
- ":OVLenable (Overload Event Enable Register)" on page 165
- "*STB (Read Status Byte)" on page 137

- "*SRE (Service Request Enable)" on page 135

:PRINt

C (see page 828)

Command Syntax

```
:PRINt [<options>]

<options> ::= [<print option>][,..,<print option>]

<print option> ::= {COLor | GRAYscale | PRINter0 | PRINter1 | BMP8bit
                    | BMP | PNG | NOFactors | FACTors}

The <print option> parameter may be repeated up to 5 times.
```

The PRINt command formats the output according to the currently selected format (device). If an option is not specified, the value selected in the Print Config menu is used.

See Also

- "Introduction to Root (:) Commands" on page 145
- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:FACTors" on page 327
- ":HARDcopy:GRAYscale" on page 758
- ":DISPlay:DATA" on page 244

:RUN

(see page 828)

Command Syntax

```
:RUN
```

The :RUN command starts repetitive acquisitions. This is the same as pressing the Run key on the front panel.

See Also

- "Introduction to Root (:) Commands" on page 145
- ":SINGle" on page 172
- ":STOP" on page 174

Example Code

```
' RUN_STOP - (not executed in this example)
'   - RUN starts the data acquisition for the active waveform display.
'   - STOP stops the data acquisition and turns off AUTOSTORE.
' myScope.WriteString ":RUN"    ' Start data acquisition.
' myScope.WriteString ":STOP"    ' Stop the data acquisition.
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:SERial

N (see page 828)

Query Syntax `:SERial?`

The :SERial? query returns the serial number of the instrument.

Return Format: `Unquoted string<NL>`

See Also

- "Introduction to Root (:) Commands" on page 145

:SINGle

(see page 828)

Command Syntax `:SINGle`

The :SINGle command causes the instrument to acquire a single trigger of data. This is the same as pressing the Single key on the front panel.

See Also

- "Introduction to Root (:) Commands" on page 145
- ":RUN" on page 170
- ":STOP" on page 174

:STATus

N (see page 828)

Query Syntax

```
:STATus? <source>

<source> ::= {CHANnel<n> | FUNCtion | MATH | SBUS{1} | FFT
   | WMEMory<r> | ABUS | EXT}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1 to (# ref waveforms) in NR1 format
```

The :STATus? query reports whether the channel, function, or serial decode bus specified by <source> is displayed.

NOTE MATH is an alias for FUNCtion.

NOTE The EXT source is available on 2-channel oscilloscopes only.

Return Format

```
<value><NL>

<value> ::= {1 | 0}
```

See Also

- "Introduction to Root (:) Commands" on page 145
- ":BLANk" on page 152
- ":CHANnel<n>:DISPlay" on page 217
- ":FUNCtion:DISPlay" on page 304
- ":WMEMory<r>:DISPlay" on page 734
- ":VIEW" on page 176

:STOP

(see page 828)

Command Syntax `:STOP`

The :STOP command stops the acquisition. This is the same as pressing the Stop key on the front panel.

See Also

- "Introduction to Root (:) Commands" on page 145
- ":RUN" on page 170
- ":SINGle" on page 172

Example Code

- "Example Code" on page 170

:TER (Trigger Event Register)

(see page 828)

Query Syntax

```
:TER?
```

The :TER? query reads the Trigger Event Register. After the Trigger Event Register is read, it is cleared. A one indicates a trigger has occurred. A zero indicates a trigger has not occurred.

The Trigger Event Register is summarized in the TRG bit of the Status Byte Register (STB). A Service Request (SRQ) can be generated when the TRG bit of the Status Byte transitions, and the TRG bit is set in the Service Request Enable register. The Trigger Event Register must be cleared each time you want a new service request to be generated.

Return Format

```
<value><NL>

<value> ::= {1 | 0}; a 16-bit integer in NR1 format.
```

See Also

- "Introduction to Root (:) Commands" on page 145
- "*SRE (Service Request Enable)" on page 135
- "*STB (Read Status Byte)" on page 137

:VIEW

(see page 828)

Command Syntax

```
:VIEW <source>

<source> ::= {CHANnel<n> | FUNCtion | MATH | SBUS{1} | FFT
   | WMEMory<r> | ABUS | EXT}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1 to (# ref waveforms) in NR1 format
```

The :VIEW command turns on the specified channel, function, or serial decode bus.

NOTE MATH is an alias for FUNCtion.

NOTE The EXT source is available on 2-channel oscilloscopes only.

See Also

- "Introduction to Root (:) Commands" on page 145
- ":BLANk" on page 152
- ":CHANnel<n>:DISPlay" on page 217
- ":FUNCtion:DISPlay" on page 304
- ":WMEMory<r>:DISPlay" on page 734
- ":STATus" on page 173

Example Code

```
' VIEW_BLANK - (not executed in this example)
'  - VIEW turns on (starts displaying) a channel.
'  - BLANK turns off (stops displaying) a channel.
' myScope.WriteString ":BLANk CHANnel1"    ' Turn channel 1 off.
' myScope.WriteString ":VIEW CHANnel1"     ' Turn channel 1 on.
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

7 :ABUS Commands

Control all oscilloscope functions associated with a bus made up of analog channels. See "Introduction to :ABUS Commands" on page 178.

Table 53 :ABUS Commands Summary

Command	Query	Options and Query Returns
:ABUS:BIT<m> {{0 | OFF} | {1 | ON}} (see page 179)	:ABUS:BIT<m>? (see page 179)	{0 | 1} <m> ::= an integer in NR1 format
:ABUS:BITS <channel_list>, {{0 | OFF} | {1 | ON}} (see page 180)	:ABUS:BITS? (see page 180)	<channel_list>, {0 | 1} <channel_list> ::= (@<m>,<m>:<m> ...) where "," is separator and ":" is range <m> ::= an integer in NR1 format
:ABUS:CLEar (see page 182)	n/a	n/a
:ABUS:DISPlay {{0 | OFF} | {1 | ON}} (see page 183)	:ABUS:DISPlay? (see page 183)	{0 | 1}
:ABUS:LABel <string> (see page 184)	:ABUS:LABel? (see page 184)	<string> ::= quoted ASCII string up to 10 characters
:ABUS:MASK <mask> (see page 185)	:ABUS:MASK? (see page 185)	<mask> ::= 32-bit integer in decimal, <nondecimal>, or <string> <nondecimal> ::= #Hnn...n where n ::= {0,..,9 | A,..,F} for hexadecimal <nondecimal> ::= #Bnn...n where n ::= {0 | 1} for binary <string> ::= "0xnn...n" where n ::= {0,..,9 | A,..,F} for hexadecimal

Introduction to :ABUS Commands

The ABUS subsystem commands control the viewing, labeling, and analog channel bus makeup.

Reporting the Setup

Use :ABUS? to query setup information for the ABUS subsystem.

Return Format

The following is a sample response from the :ABUS? query. In this case, the query was issued following a *RST command.

```
:ABUS:DISP 0;LAB "ABUS1";MASK +0
```

:ABUS:BIT<m>

N (see page 828)

Command Syntax

```
:ABUS:BIT<m> <display>

<display> ::= {{1 | ON} | {0 | OFF}}

<m> ::= An integer is attached as a suffix to BIT
and defines the analog channel that is affected by the command.
```

The :ABUS:BIT<m> command includes or excludes the selected bit as part of the definition for the selected bus. If the parameter is a 1 (ON), the bit is included in the definition. If the parameter is a 0 (OFF), the bit is excluded from the definition.

On 2-channel oscillosccopes:		On 4-channel oscillosccopes:	
Bit	Channel	Bit	Channel
0	channel 1	0	channel 1
1	channel 2	1	channel 2
2	Ext Trig input	2	channel 3
		3	channel 4

Query Syntax

```
:ABUS:BIT<m>?
```

The :ABUS:BIT<m>? query returns the value indicating whether the specified bit is included or excluded from the specified bus definition.

Return Format

```
<display><NL>

<display> ::= {0 | 1}
```

See Also

- "Introduction to :ABUS Commands" on page 178
- ":ABUS:BITS" on page 180
- ":ABUS:CLEar" on page 182
- ":ABUS:DISPlay" on page 183
- ":ABUS:LABel" on page 184
- ":ABUS:MASK" on page 185

Example Code

```
' Include analog channel 2 in the bus:
myScope.WriteString ":ABUS:BIT1 ON"
```

:ABUS:BITS

N (see page 828)

Command Syntax

```
:ABUS:BITS <channel_list>, <display>

<channel_list> ::= (@<m>,<m>:<m>, ...) where commas separate bits and
colons define bit ranges.

<m> ::= An integer defines the channel affected by the command.

<display> ::= {{1 | ON} | {0 | OFF}}
```

The :ABUS:BITS command includes or excludes the selected bits in the channel list in the definition of the analog bus. If the parameter is a 1 (ON), then the bits in the channel list are included as part of the analog bus definition. If the parameter is a 0 (OFF), then the bits in the channel list are excluded from the definition of the analog bus.

The threshold voltage level for each channel is set using the trigger-level commands of the source. For analog channels, the trigger-level command to use depends on the current Trigger Mode. For the External Trigger channel, use :EXTernal:LEVel command.

The following table shows the bit definitions for <m> on the different oscilloscopes:

On 2-channel oscillosccopes:		On 4-channel oscillosccopes:	
Bit	Channel	Bit	Channel
0	channel 1	0	channel 1
1	channel 2	1	channel 2
2	Ext Trig input	2	channel 3
		3	channel 4

Query Syntax

```
:ABUS:BITS?
```

The :ABUS:BITS? query returns the definition for the specified bus.

Return Format

```
<channel_list>, <display><NL>

<channel_list> ::= (@<m>,<m>:<m>, ...) where commas separate bits and
colons define bit ranges.

<display> ::= {0 | 1}
```

See Also

- "Introduction to :ABUS Commands" on page 178
- ":ABUS:BIT<m>" on page 179
- ":ABUS:CLEar" on page 182
- ":ABUS:DISPlay" on page 183

- ":ABUS:LABel" on page 184
- ":ABUS:MASK" on page 185

Example Code

```
' Include the first and third channel in the bus:
myScope.WriteString ":ABUS:BITS (@0,2), ON"

' Include the first three channels in the bus:
myScope.WriteString ":ABUS:BITS (@0:2), ON"
```

:ABUS:CLEar

(see page 828)

Command Syntax `:ABUS:CLEar`

The :ABUS:CLEar command excludes all of the analog channels from the selected bus definition.

See Also

- "Introduction to :ABUS Commands" on page 178
- ":ABUS:BIT<m>" on page 179
- ":ABUS:BITS" on page 180
- ":ABUS:DISPlay" on page 183
- ":ABUS:LABel" on page 184
- ":ABUS:MASK" on page 185

:ABUS:DISPlay

(see page 828)

Command Syntax

```
:ABUS:DISPlay <value>

<value> ::= {{1 | ON} | {0 | OFF}}
```

The :ABUS:DISPlay command enables or disables the view of the selected bus.

Query Syntax

```
:ABUS:DISPlay?
```

The :ABUS:DISPlay? query returns the display value of the selected bus.

Return Format

```
<value><NL>

<value> ::= {0 | 1}
```

See Also

- "Introduction to :ABUS Commands" on page 178
- ":ABUS:BIT<m>" on page 179
- ":ABUS:BITS" on page 180
- ":ABUS:CLEar" on page 182
- ":ABUS:LABel" on page 184
- ":ABUS:MASK" on page 185

:ABUS:LABel

N (see page 828)

Command Syntax

```
:ABUS:LABel <quoted_string>

<quoted_string> ::= any series of 10 or less characters as a
quoted ASCII string.
```

The :ABUS:LABel command sets the bus label to the quoted string. Setting a label for a bus will also result in the name being added to the label list.

NOTE Label strings are 10 characters or less, and may contain any commonly used ASCII characters. Labels with more than 10 characters are truncated to 10 characters.

Query Syntax

```
:ABUS:LABel?
```

The :ABUS:LABel? query returns the name of the specified bus.

Return Format

```
<quoted_string><NL>

<quoted_string> ::= any series of 10 or less characters as a
quoted ASCII string.
```

See Also

- "Introduction to :ABUS Commands" on page 178
- ":ABUS:BIT<m>" on page 179
- ":ABUS:BITS" on page 180
- ":ABUS:CLEar" on page 182
- ":ABUS:DISPlay" on page 183
- ":ABUS:MASK" on page 185
- ":CHANnel:LABel" on page 746
- ":DISPlay:LABList" on page 247

Example Code

```
' Set the analog channel bus label to "DATA":
myScope.WriteString ":ABUS:LABel 'Data'"
```

:ABUS:MASK

N (see page 828)

Command Syntax

```
:ABUS:MASK <mask>

<mask> ::= 32-bit integer in decimal, <nondecimal>, or <string>

<nondecimal> ::= #Hnn...n where n ::= {0,..,9 | A,..,F} for hexadecimal

<nondecimal> ::= #Bnn...n where n ::= {0 | 1} for binary

<string> ::= "0xnn...n" where n ::= {0,..,9 | A,..,F} for hexadecimal
```

The :ABUS:MASK command defines the bits included and excluded in the selected bus according to the mask. Set a mask bit to a "1" to include that bit in the selected bus, and set a mask bit to a "0" to exclude it.

Query Syntax

```
:ABUS:MASK?
```

The :ABUS:MASK? query returns the mask value for the specified bus.

Return Format

```
<mask><NL> in decimal format
```

See Also

- "Introduction to :ABUS Commands" on page 178
- ":ABUS:BIT<m>" on page 179
- ":ABUS:BITS" on page 180
- ":ABUS:CLEar" on page 182
- ":ABUS:DISPlay" on page 183
- ":ABUS:LABel" on page 184

8 :ACQuire Commands

Set the parameters for acquiring and storing data. See "Introduction to :ACQuire Commands" on page 187.

Table 54 :ACQuire Commands Summary

Command	Query	Options and Query Returns
:ACQuire:COMPlete <complete> (see page 189)	:ACQuire:COMPlete? (see page 189)	<complete> ::= 100; an integer in NR1 format
:ACQuire:COUNt <count> (see page 190)	:ACQuire:COUNt? (see page 190)	<count> ::= an integer from 2 to 65536 in NR1 format
:ACQuire:MODE <mode> (see page 191)	:ACQuire:MODE? (see page 191)	<mode> ::= {RTIMe | SEGMented}
n/a	:ACQuire:POINts? (see page 192)	<# points> ::= an integer in NR1 format
:ACQuire:SEGMented:ANALyze (see page 193)	n/a	n/a (with SGM license)
:ACQuire:SEGMented:COUNt <count> (see page 194)	:ACQuire:SEGMented:COUNt? (see page 194)	<count> ::= an integer from 2 to 500 in NR1 format (with SGM license)
:ACQuire:SEGMented:INDex <index> (see page 195)	:ACQuire:SEGMented:INDex? (see page 195)	<index> ::= an integer from 1 to 500 in NR1 format (with SGM license)
n/a	:ACQuire:SRATe? (see page 198)	<sample_rate> ::= sample rate (samples/s) in NR3 format
:ACQuire:TYPE <type> (see page 199)	:ACQuire:TYPE? (see page 199)	<type> ::= {NORMal | AVERage | HRESolution | PEAK}

Introduction to :ACQuire Commands

The ACQuire subsystem controls the way in which waveforms are acquired. These acquisition types are available: normal, averaging, peak detect, and high resolution.

Normal

The :ACQuire:TYPE NORMal command sets the oscilloscope in the normal acquisition mode. For the majority of user models and signals, NORMal mode yields the best oscilloscope picture of the waveform.

Averaging

The :ACQuire:TYPE AVERage command sets the oscilloscope in the averaging mode. You can set the count by sending the :ACQuire:COUNt command followed by the number of averages. In this mode, the value for averages is an integer from 2 to 65536. The COUNt value determines the number of averages that must be acquired.

High-Resolution

The :ACQuire:TYPE HRESolution command sets the oscilloscope in the high-resolution mode (also known as *smoothing*). This mode is used to reduce noise at slower sweep speeds where the digitizer samples faster than needed to fill memory for the displayed time range. Instead of decimating samples, they are averaged together to provide the value for one display point. The slower the sweep speed, the greater the number of samples that are averaged together for each display point.

Peak Detect

The :ACQuire:TYPE PEAK command sets the oscilloscope in the peak detect mode. In this mode, :ACQuire:COUNt has no meaning.

Reporting the Setup

Use :ACQuire? to query setup information for the ACQuire subsystem.

Return Format

The following is a sample response from the :ACQuire? query. In this case, the query was issued following a *RST command.

```
:ACQ:MODE RTIM;TYPE NORM;COMP 100;COUNT 8;SEGM:COUN 2
```

:ACQuire:COMPlete

(see page 828)

Command Syntax

```
:ACQuire:COMPlete <complete>

<complete> ::= 100; an integer in NR1 format
```

The :ACQuire:COMPlete command affects the operation of the :DIGitize command. It specifies the minimum completion criteria for an acquisition. The parameter determines the percentage of the time buckets that must be "full" before an acquisition is considered complete. If :ACQuire:TYPE is NORMal, it needs only one sample per time bucket for that time bucket to be considered full.

The only legal value for the :COMPlete command is 100. All time buckets must contain data for the acquisition to be considered complete.

Query Syntax

```
:ACQuire:COMPlete?
```

The :ACQuire:COMPlete? query returns the completion criteria (100) for the currently selected mode.

Return Format

```
<completion_criteria><NL>

<completion_criteria> ::= 100; an integer in NR1 format
```

See Also

- "Introduction to :ACQuire Commands" on page 187
- ":ACQuire:TYPE" on page 199
- ":DIGitize" on page 153
- ":WAVeform:POINts" on page 675

Example Code

```
' AQUIRE_COMPLETE - Specifies the minimum completion criteria for
' an acquisition.  The parameter determines the percentage of time
' buckets needed to be "full" before an acquisition is considered
' to be complete.
myScope.WriteString ":ACQuire:COMPlete 100"
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:ACQuire:COUNt

(see page 828)

Command Syntax

```
:ACQuire:COUNt <count>

<count> ::= integer in NR1 format
```

In averaging mode, the :ACQuire:COUNt command specifies the number of values to be averaged for each time bucket before the acquisition is considered to be complete for that time bucket. When :ACQuire:TYPE is set to AVERage, the count can be set to any value from 2 to 65536.

NOTE

The :ACQuire:COUNt 1 command has been deprecated. The AVERage acquisition type with a count of 1 is functionally equivalent to the HRESolution acquisition type; however, you should select the high-resolution acquisition mode with the :ACQuire:TYPE HRESolution command instead.

Query Syntax

```
:ACQuire:COUNT?
```

The :ACQuire:COUNT? query returns the currently selected count value for averaging mode.

Return Format

```
<count_argument><NL>

<count_argument> ::= an integer from 2 to 65536 in NR1 format
```

See Also

- "Introduction to :ACQuire Commands" on page 187
- ":ACQuire:TYPE" on page 199
- ":DIGitize" on page 153
- ":WAVeform:COUNt" on page 671

:ACQuire:MODE

(see page 828)

Command Syntax

```
:ACQuire:MODE <mode>

<mode> ::= {RTIMe | SEGMented}
```

The :ACQuire:MODE command sets the acquisition mode of the oscilloscope.

- The :ACQuire:MODE RTIMe command sets the oscilloscope in real time mode.

NOTE **The obsolete command ACQuire:TYPE:REALtime is functionally equivalent to sending ACQuire:MODE RTIMe; TYPE NORMal.**

- The :ACQuire:MODE SEGMented command sets the oscilloscope in segmented memory mode.

  Segmented memory is available on the DSOX1200-Series oscilloscope models.

Query Syntax

```
:ACQuire:MODE?
```

The :ACQuire:MODE? query returns the acquisition mode of the oscilloscope.

Return Format

```
<mode_argument><NL>

<mode_argument> ::= {RTIM | SEGM}
```

See Also

- "Introduction to :ACQuire Commands" on page 187
- ":ACQuire:TYPE" on page 199

:ACQuire:POINts

(see page 828)

Query Syntax `:ACQuire:POINts?`

The :ACQuire:POINts? query returns the number of data points that the hardware will acquire from the input signal. The number of points acquired is not directly controllable. To set the number of points to be transferred from the oscilloscope, use the command :WAVeform:POINts. The :WAVeform:POINts? query will return the number of points available to be transferred from the oscilloscope.

Return Format `<points_argument><NL>`

`<points_argument> ::= an integer in NR1 format`

See Also

- "Introduction to :ACQuire Commands" on page 187
- ":DIGitize" on page 153
- ":WAVeform:POINts" on page 675

:ACQuire:SEGMented:ANALyze

(see page 828)

Command Syntax `:ACQuire:SEGMented:ANALyze`

NOTE Segmented memory is available on the DSOX1200-Series oscilloscope models that have the SGM license.

This command calculates measurement statistics and/or infinite persistence over all segments that have been acquired. It corresponds to the front panel **Analyze Segments** softkey which appears in the Segmented Memory menu.

In order to use this command, the oscilloscope must be stopped and in segmented acquisition mode, with either quick measurements or infinite persistence on.

See Also
- ":ACQuire:MODE" on page 191
- ":ACQuire:SEGMented:COUNt" on page 194
- "Introduction to :ACQuire Commands" on page 187

:ACQuire:SEGMented:COUNt

(see page 828)

Command Syntax

```
:ACQuire:SEGMented:COUNt <count>

<count> ::= an integer from 2 to 500 in NR1 format
```

NOTE Segmented memory is available on the DSOX1200-Series oscilloscope models that have the SGM license.

The :ACQuire:SEGMented:COUNt command sets the number of memory segments to acquire.

The segmented memory acquisition mode is enabled with the :ACQuire:MODE command, and data is acquired using the :DIGitize, :SINGle, or :RUN commands. The number of memory segments in the current acquisition is returned by the :WAVeform:SEGMented:COUNt? query.

Query Syntax

```
:ACQuire:SEGMented:COUNt?
```

The :ACQuire:SEGMented:COUNt? query returns the current count setting.

Return Format

```
<count><NL>

<count> ::= an integer from 2 to 500 in NR1 format
```

See Also

- ":ACQuire:MODE" on page 191
- ":DIGitize" on page 153
- ":SINGle" on page 172
- ":RUN" on page 170
- ":WAVeform:SEGMented:COUNt" on page 682
- ":ACQuire:SEGMented:ANALyze" on page 193
- "Introduction to :ACQuire Commands" on page 187

Example Code

- "Example Code" on page 195

:ACQuire:SEGMented:INDex

(see page 828)

Command Syntax

```
:ACQuire:SEGMented:INDex <index>

<index> ::= an integer from 1 to 500 in NR1 format
```

NOTE Segmented memory is available on the DSOX1200-Series oscilloscope models that have the SGM license.

The :ACQuire:SEGMented:INDex command sets the index into the memory segments that have been acquired.

The segmented memory acquisition mode is enabled with the :ACQuire:MODE command. The number of segments to acquire is set using the :ACQuire:SEGMented:COUNt command, and data is acquired using the :DIGitize, :SINGle, or :RUN commands. The number of memory segments that have been acquired is returned by the :WAVeform:SEGMented:COUNt? query. The time tag of the currently indexed memory segment is returned by the :WAVeform:SEGMented:TTAG? query.

Query Syntax

```
:ACQuire:SEGMented:INDex?
```

The :ACQuire:SEGMented:INDex? query returns the current segmented memory index setting.

Return Format

```
<index><NL>

<index> ::= an integer from 1 to 500 in NR1 format
```

See Also

- ":ACQuire:MODE" on page 191
- ":ACQuire:SEGMented:COUNt" on page 194
- ":DIGitize" on page 153
- ":SINGle" on page 172
- ":RUN" on page 170
- ":WAVeform:SEGMented:COUNt" on page 682
- ":WAVeform:SEGMented:TTAG" on page 683
- ":ACQuire:SEGMented:ANALyze" on page 193
- "Introduction to :ACQuire Commands" on page 187

Example Code

```
' Segmented memory commands example.
' ------------------------------------------------------------------

Option Explicit

Public myMgr As VisaComLib.ResourceManager
```

```
Public myScope As VisaComLib.FormattedIO488
Public varQueryResult As Variant
Public strQueryResult As String

Private Declare Sub Sleep Lib "kernel32" (ByVal dwMilliseconds As Long)

Sub Main()

  On Error GoTo VisaComError

  ' Create the VISA COM I/O resource.
  Set myMgr = New VisaComLib.ResourceManager
  Set myScope = New VisaComLib.FormattedIO488
  Set myScope.IO = _
        myMgr.Open("USB0::0x0957::0x17A6::US50210029::0::INSTR")
  myScope.IO.Clear   ' Clear the interface.

  ' Turn on segmented memory acquisition mode.
  myScope.WriteString ":ACQuire:MODE SEGMented"
  myScope.WriteString ":ACQuire:MODE?"
  strQueryResult = myScope.ReadString
  Debug.Print "Acquisition mode: " + strQueryResult

  ' Set the number of segments to 25.
  myScope.WriteString ":ACQuire:SEGMented:COUNt 25"
  myScope.WriteString ":ACQuire:SEGMented:COUNt?"
  strQueryResult = myScope.ReadString
  Debug.Print "Acquisition memory segments: " + strQueryResult

  ' If data will be acquired within the IO timeout:
  'myScope.IO.Timeout = 10000
  'myScope.WriteString ":DIGitize"
  'Debug.Print ":DIGitize blocks until all segments acquired."
  'myScope.WriteString ":WAVeform:SEGMented:COUNt?"
  'varQueryResult = myScope.ReadNumber

  ' Or, to poll until the desired number of segments acquired:
  myScope.WriteString ":SINGle"
  Debug.Print ":SINGle does not block until all segments acquired."
  Do
    Sleep 100   ' Small wait to prevent excessive queries.
    myScope.WriteString ":WAVeform:SEGMented:COUNt?"
    varQueryResult = myScope.ReadNumber
  Loop Until varQueryResult = 25

  Debug.Print "Number of segments in acquired data: " _
      + FormatNumber(varQueryResult)

  Dim lngSegments As Long
  lngSegments = varQueryResult

  ' For each segment:
  Dim dblTimeTag As Double
  Dim lngI As Long

  For lngI = lngSegments To 1 Step -1
```

```
    ' Set the segmented memory index.
    myScope.WriteString ":ACQuire:SEGMented:INDex " + CStr(lngI)
    myScope.WriteString ":ACQuire:SEGMented:INDex?"
    strQueryResult = myScope.ReadString
    Debug.Print "Acquisition memory segment index: " + strQueryResult

    ' Display the segment time tag.
    myScope.WriteString ":WAVeform:SEGMented:TTAG?"
    dblTimeTag = myScope.ReadNumber
    Debug.Print "Segment " + CStr(lngI) + " time tag: " _
        + FormatNumber(dblTimeTag, 12)

  Next lngI

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error:" + vbCrLf + Err.Description

End Sub
```

:ACQuire:SRATe

(see page 828)

Query Syntax `:ACQuire:SRATe?`

The :ACQuire:SRATe? query returns the current oscilloscope acquisition sample rate. The sample rate is not directly controllable.

Return Format `<sample_rate><NL>`

`<sample_rate> ::= sample rate in NR3 format`

See Also

- "Introduction to :ACQuire Commands" on page 187
- ":ACQuire:POINts" on page 192

:ACQuire:TYPE

(see page 828)

Command Syntax `:ACQuire:TYPE <type>`

`<type> ::= {NORMal | AVERage | HRESolution | PEAK}`

The :ACQuire:TYPE command selects the type of data acquisition that is to take place. The acquisition types are:

- NORMal — sets the oscilloscope in the normal mode.
- AVERage — sets the oscilloscope in the averaging mode. You can set the count by sending the :ACQuire:COUNt command followed by the number of averages. In this mode, the value for averages is an integer from 1 to 65536. The COUNt value determines the number of averages that must be acquired.

  The AVERage type is not available when in segmented memory mode (:ACQuire:MODE SEGMented).
- HRESolution — sets the oscilloscope in the high-resolution mode (also known as *smoothing*). This mode is used to reduce noise at slower sweep speeds where the digitizer samples faster than needed to fill memory for the displayed time range.

  For example, if the digitizer samples at 200 MSa/s, but the effective sample rate is 1 MSa/s (because of a slower sweep speed), only 1 out of every 200 samples needs to be stored. Instead of storing one sample (and throwing others away), the 200 samples are averaged together to provide the value for one display point. The slower the sweep speed, the greater the number of samples that are averaged together for each display point.
- PEAK — sets the oscilloscope in the peak detect mode. In this mode, :ACQuire:COUNt has no meaning.

The AVERage and HRESolution types can give you extra bits of vertical resolution. See the *User's Guide* for an explanation. When getting waveform data acquired using the AVERage and HRESolution types, be sure to use the WORD or ASCii waveform data formats to get the extra bits of vertical resolution.

NOTE **The obsolete command ACQuire:TYPE:REALtime is functionally equivalent to sending ACQuire:MODE RTIME; TYPE NORMal.**

Query Syntax `:ACQuire:TYPE?`

The :ACQuire:TYPE? query returns the current acquisition type.

Return Format `<acq_type><NL>`

`<acq_type> ::= {NORM | AVER | HRES | PEAK}`

See Also
- "Introduction to :ACQuire Commands" on page 187
- ":ACQuire:COUNt" on page 190
- ":ACQuire:MODE" on page 191
- ":DIGitize" on page 153
- ":WAVeform:FORMat" on page 674
- ":WAVeform:TYPE" on page 689
- ":WAVeform:PREamble" on page 679

Example Code

```
' AQUIRE_TYPE - Sets the acquisition mode, which can be NORMAL,
' PEAK, or AVERAGE.
myScope.WriteString ":ACQuire:TYPE NORMal"
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

9 :CALibrate Commands

Utility commands for viewing calibration status and for starting the user calibration procedure. See "Introduction to :CALibrate Commands" on page 202.

Table 55 :CALibrate Commands Summary

Command	Query	Options and Query Returns
n/a	:CALibrate:DATE? (see page 203)	<return value> ::= <year>,<month>,<day>; all in NR1 format
:CALibrate:LABel <string> (see page 204)	:CALibrate:LABel? (see page 204)	<string> ::= quoted ASCII string up to 32 characters
:CALibrate:OUTPut <signal> (see page 205)	:CALibrate:OUTPut? (see page 205)	<signal> ::= {TRIGgers | MASK | WAVEgen}
n/a	:CALibrate:PROTected? (see page 206)	{"PROTected" | "UNPRotected"}
:CALibrate:STARt (see page 207)	n/a	n/a
n/a	:CALibrate:STATus? (see page 208)	<return value> ::= <status_code>,<status_string> <status_code> ::= an integer status code <status_string> ::= an ASCII status string
n/a	:CALibrate:TEMPerature? (see page 209)	<return value> ::= degrees C delta since last cal in NR3 format
n/a	:CALibrate:TIME? (see page 210)	<return value> ::= <hours>,<minutes>,<seconds>; all in NR1 format

Introduction to :CALibrate Commands

The CALibrate subsystem provides utility commands for:

- Determining the state of the calibration factor protection switch (CAL PROTECT).
- Saving and querying the calibration label string.
- Reporting the calibration time and date.
- Reporting changes in the temperature since the last calibration.
- Starting the user calibration procedure.

:CALibrate:DATE

N (see page 828)

Query Syntax `:CALibrate:DATE?`

The :CALibrate:DATE? query returns the date of the last calibration.

Return Format `<date><NL>`

`<date> ::= year,month,day in NR1 format<NL>`

See Also

- "Introduction to :CALibrate Commands" on page 202

:CALibrate:LABel

(see page 828)

Command Syntax

```
:CALibrate:LABel <string>

<string> ::= quoted ASCII string of up to 32 characters in length,
not including the quotes
```

The CALibrate:LABel command saves a string that is up to 32 characters in length into the instrument's non-volatile memory. The string may be used to record calibration dates or other information as needed.

Query Syntax

```
:CALibrate:LABel?
```

The :CALibrate:LABel? query returns the contents of the calibration label string.

Return Format

```
<string><NL>

<string>::= unquoted ASCII string of up to 32 characters in length
```

See Also

- "Introduction to :CALibrate Commands" on page 202

:CALibrate:OUTPut

N (see page 828)

Command Syntax

```
:CALibrate:OUTPut <signal>

<signal> ::= {TRIGgers | MASK | OFF}
```

For oscilloscopes that have a built-in waveform generator (G-suffix models), the :CALibrate:OUTPut command sets the signal that is available on the Gen Out BNC:

- TRIGgers – pulse when a trigger event occurs.
- MASK – signal from mask test indicating a failure.
- OFF – either no signal or the waveform generator output signal when :WGEN:OUTPut is ON.

Query Syntax

```
:CALibrate:OUTPut?
```

The :CALibrate:OUTPut query returns the Gen Out BNC signal selection.

Return Format

```
<signal><NL>

<signal> ::= {TRIG | MASK | OFF}
```

See Also

- "Introduction to :CALibrate Commands" on page 202
- ":WGEN:OUTPut" on page 721

:CALibrate:PROTected

(see page 828)

Query Syntax `:CALibrate:PROTected?`

The :CALibrate:PROTected? query returns the rear-panel calibration protect (CAL PROTECT) button state. The value "PROTected" indicates calibration is disabled, and "UNPRotected" indicates calibration is enabled.

Return Format `<switch><NL>`

`<switch> ::= {"PROTected" | "UNPRotected"}`

See Also

- "Introduction to :CALibrate Commands" on page 202

:CALibrate:STARt

(see page 828)

Command Syntax `:CALibrate:STARt`

The CALibrate:STARt command starts the user calibration procedure.

NOTE Before starting the user calibration procedure, you must set the rear panel CALIBRATION switch to UNPROTECTED, and you must connect BNC cables from the TRIG OUT connector to the analog channel inputs. See the *User's Guide* for details.

See Also
- "Introduction to :CALibrate Commands" on page 202
- ":CALibrate:PROTected" on page 206

:CALibrate:STATus

(see page 828)

Query Syntax

```
:CALibrate:STATus?
```

The :CALibrate:STATus? query returns the summary results of the last user calibration procedure.

Return Format

```
<return value><NL>

<return value> ::= <status_code>,<status_string>

<status_code> ::= an integer status code

<status_string> ::= an ASCII status string
```

See Also

- "Introduction to :CALibrate Commands" on page 202

:CALibrate:TEMPerature

N (see page 828)

Query Syntax `:CALibrate:TEMPerature?`

The :CALibrate:TEMPerature? query returns the change in temperature since the last user calibration procedure.

Return Format `<return value><NL>`

`<return value> ::= degrees C delta since last cal in NR3 format`

See Also

- "Introduction to :CALibrate Commands" on page 202

:CALibrate:TIME

(see page 828)

Query Syntax `:CALibrate:TIME?`

The :CALibrate:TIME? query returns the time of the last calibration.

Return Format `<date><NL>`

`<date> ::= hour,minutes,seconds in NR1 format`

See Also

- "Introduction to :CALibrate Commands" on page 202

10 :CHANnel<n> Commands

Control all oscilloscope functions associated with individual analog channels or groups of channels. See "Introduction to :CHANnel<n> Commands" on page 213.

Table 56 :CHANnel<n> Commands Summary

Command	Query	Options and Query Returns
:CHANnel<n>:BANDwidth <limit> (see page 214)	:CHANnel<n>:BANDwidth? [MAXimum] (see page 214)	<limit> ::= 25E6 in NR3 format <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:BWLimit {{0 | OFF} | {1 | ON}} (see page 215)	:CHANnel<n>:BWLimit? (see page 215)	{0 | 1} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:COUPling <coupling> (see page 216)	:CHANnel<n>:COUPling? (see page 216)	<coupling> ::= {AC | DC} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:DISPlay {{0 | OFF} | {1 | ON}} (see page 217)	:CHANnel<n>:DISPlay? (see page 217)	{0 | 1} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:IMPedance <impedance> (see page 218)	:CHANnel<n>:IMPedance? (see page 218)	<impedance> ::= ONEMeg <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:INVert {{0 | OFF} | {1 | ON}} (see page 219)	:CHANnel<n>:INVert? (see page 219)	{0 | 1} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:LABel <string> (see page 220)	:CHANnel<n>:LABel? (see page 220)	<string> ::= any series of 10 or less ASCII characters enclosed in quotation marks <n> ::= 1 to (# analog channels) in NR1 format

Table 56 :CHANnel<n> Commands Summary (continued)

Command	Query	Options and Query Returns
:CHANnel<n>:OFFSet <offset>[suffix] (see page 221)	:CHANnel<n>:OFFSet? (see page 221)	<offset> ::= Vertical offset value in NR3 format [suffix] ::= {V | mV} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:PROBe <attenuation> (see page 222)	:CHANnel<n>:PROBe? (see page 222)	<attenuation> ::= Probe attenuation ratio in NR3 format <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:PROBe:HEAD[:TYPE] <head_param> (see page 223)	:CHANnel<n>:PROBe:HEAD[:TYPE]? (see page 223)	<head_param> ::= {SEND0 | SEND6 | SEND12 | SEND20 | DIFF0 | DIFF6 | DIFF12 | DIFF20 | NONE} <n> ::= 1 to (# analog channels) in NR1 format
n/a	:CHANnel<n>:PROBe:ID? (see page 224)	<probe id> ::= unquoted ASCII string up to 11 characters <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:PROBe:SKEW <skew_value> (see page 225)	:CHANnel<n>:PROBe:SKEW? (see page 225)	<skew_value> ::= -100 ns to +100 ns in NR3 format <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:PROBe:STYPe <signal type> (see page 226)	:CHANnel<n>:PROBe:STYPe? (see page 226)	<signal type> ::= {DIFFerential | SINGle} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:PROTection (see page 227)	:CHANnel<n>:PROTection? (see page 227)	NORM <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:RANGe <range>[suffix] (see page 228)	:CHANnel<n>:RANGe? (see page 228)	<range> ::= Vertical full-scale range value in NR3 format [suffix] ::= {V | mV} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:SCALe <scale>[suffix] (see page 229)	:CHANnel<n>:SCALe? (see page 229)	<scale> ::= Vertical units per division value in NR3 format [suffix] ::= {V | mV} <n> ::= 1 to (# analog channels) in NR1 format

Table 56 :CHANnel<n> Commands Summary (continued)

Command	Query	Options and Query Returns
:CHANnel<n>:UNITs <units> (see page 230)	:CHANnel<n>:UNITs? (see page 230)	<units> ::= {VOLT | AMPere} <n> ::= 1 to (# analog channels) in NR1 format
:CHANnel<n>:VERNier {{0 | OFF} | {1 | ON}} (see page 231)	:CHANnel<n>:VERNier? (see page 231)	{0 | 1} <n> ::= 1 to (# analog channels) in NR1 format

Introduction to :CHANnel<n> Commands

<n> ::= 1 to (# analog channels) in NR1 format

The CHANnel<n> subsystem commands control an analog channel (vertical or Y-axis of the oscilloscope). Channels are independently programmable for all offset, probe, coupling, bandwidth limit, inversion, vernier, and range (scale) functions. The channel number (1 or 2) specified in the command selects the analog channel that is affected by the command.

A label command provides identifying annotations of up to 10 characters.

You can toggle the channel displays on and off with the :CHANnel<n>:DISPlay command as well as with the root level commands :VIEW and :BLANk.

NOTE The obsolete CHANnel subsystem is supported.

Reporting the Setup

Use :CHANnel1? or :CHANnel2? to query setup information for the CHANnel<n> subsystem.

Return Format

The following are sample responses from the :CHANnel<n>? query. In this case, the query was issued following a *RST command.

```
:CHAN1:RANG +40.0E+00;OFFS +0.00000E+00;COUP DC;IMP ONEM;DISP 1;BWL 0;
INV 0;LAB "1";UNIT VOLT;PROB +10E+00;PROB:SKEW +0.00E+00;STYP SING
```

:CHANnel<n>:BANDwidth

N (see page 828)

Command Syntax

```
:CHANnel<n>:BANDwidth <limit>

<limit> ::= 25E6 in NR3 format

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:BANDwidth command sets the bandwidth limit value and turns on bandwidth limiting (see the :CHANnel<n>:BWLimit command).

For waveforms with frequencies below the bandwidth limit, turning the bandwidth limit on removes unwanted high frequency noise from the waveform.

Bandwidth limit also limits the trigger signal path of the channel.

While you can request any limit; the oscilloscope will choose the only bandwidth limit available, 25 MHz.

Query Syntax

```
:CHANnel<n>:BANDwidth? [MAXimum]
```

The :CHANnel<n>:BANDwidth? query returns the current setting of the low-pass filter.

If the bandwidth limit is off, the query returns the full bandwidth of the oscilloscope.

When the MAXimum parameter is used, the oscilloscope's maximum possible bandwidth is returned.

Return Format

```
<limit><NL>

<limit> ::= 25E6 or full bandwidth in NR3 format
```

See Also

- ":CHANnel<n>:BWLimit" on page 215

:CHANnel<n>:BWLimit

(see page 828)

Command Syntax

```
:CHANnel<n>:BWLimit <bwlimit>

<bwlimit> ::= {{1 | ON} | {0 | OFF}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:BWLimit command controls an internal low-pass filter. When the filter is on, the bandwidth of the specified channel is limited to approximately 25 MHz.

Query Syntax

```
:CHANnel<n>:BWLimit?
```

The :CHANnel<n>:BWLimit? query returns the current setting of the low-pass filter.

Return Format

```
<bwlimit><NL>

<bwlimit> ::= {1 | 0}
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213

:CHANnel<n>:COUPling

(see page 828)

Command Syntax

```
:CHANnel<n>:COUPling <coupling>

<coupling> ::= {AC | DC}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:COUPling command selects the input coupling for the specified channel. The coupling for each analog channel can be set to AC or DC.

Query Syntax

```
:CHANnel<n>:COUPling?
```

The :CHANnel<n>:COUPling? query returns the current coupling for the specified channel.

Return Format

```
<coupling value><NL>

<coupling value> ::= {AC | DC}
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213

:CHANnel<n>:DISPlay

(see page 828)

Command Syntax

```
:CHANnel<n>:DISPlay <display value>

<display value> ::= {{1 | ON} | {0 | OFF}}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:DISPlay command turns the display of the specified channel on or off.

Query Syntax

```
:CHANnel<n>:DISPlay?
```

The :CHANnel<n>:DISPlay? query returns the current display setting for the specified channel.

Return Format

```
<display value><NL>

<display value> ::= {1 | 0}
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213
- ":VIEW" on page 176
- ":BLANk" on page 152
- ":STATus" on page 173

:CHANnel<n>:IMPedance

(see page 828)

Command Syntax

```
:CHANnel<n>:IMPedance <impedance>

<impedance> ::= ONEMeg

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:IMPedance command selects the input impedance setting for the specified analog channel. The only legal value for this command is ONEMeg (1 MΩ).

Query Syntax

```
:CHANnel<n>:IMPedance?
```

The :CHANnel<n>:IMPedance? query returns the current input impedance setting for the specified channel.

Return Format

```
<impedance value><NL>

<impedance value> ::= ONEM
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213

:CHANnel<n>:INVert

(see page 828)

Command Syntax

```
:CHANnel<n>:INVert <invert value>

<invert value> ::= {{1 | ON} | {0 | OFF}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:INVert command selects whether or not to invert the input signal for the specified channel. The inversion may be 1 (ON/inverted) or 0 (OFF/not inverted).

Query Syntax

```
:CHANnel<n>:INVert?
```

The :CHANnel<n>:INVert? query returns the current state of the channel inversion.

Return Format

```
<invert value><NL>

<invert value> ::= {0 | 1}
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213

:CHANnel<n>:LABel

N (see page 828)

Command Syntax

```
:CHANnel<n>:LABel <string>

<string> ::= quoted ASCII string

<n> ::= 1 to (# analog channels) in NR1 format
```

NOTE Label strings are 10 characters or less, and may contain any commonly used ASCII characters. Labels with more than 10 characters are truncated to 10 characters. Lower case characters are converted to upper case.

The :CHANnel<n>:LABel command sets the analog channel label to the string that follows. Setting a label for a channel also adds the name to the label list in non-volatile memory (replacing the oldest label in the list).

Query Syntax

```
:CHANnel<n>:LABel?
```

The :CHANnel<n>:LABel? query returns the label associated with a particular analog channel.

Return Format

```
<string><NL>

<string> ::= quoted ASCII string
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213
- ":DISPlay:LABel" on page 246
- ":DISPlay:LABList" on page 247

Example Code

```
' LABEL - This command allows you to write a name (10 characters
' maximum) next to the channel number.  It is not necessary, but
' can be useful for organizing the display.
myScope.WriteString ":CHANnel1:LABel ""CAL 1"""  ' Label ch1 "CAL 1".
myScope.WriteString ":CHANnel2:LABel ""CAL2"""   ' Label ch1 "CAL2".
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:CHANnel<n>:OFFSet

(see page 828)

Command Syntax

```
:CHANnel<n>:OFFSet <offset> [<suffix>]

<offset> ::= Vertical offset value in NR3 format

<suffix> ::= {V | mV}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:OFFSet command sets the value that is represented at center screen for the selected channel. The range of legal values varies with the value set by the :CHANnel<n>:RANGe and :CHANnel<n>:SCALe commands. If you set the offset to a value outside of the legal range, the offset value is automatically set to the nearest legal value. Legal values are affected by the probe attenuation setting.

Query Syntax

```
:CHANnel<n>:OFFSet?
```

The :CHANnel<n>:OFFSet? query returns the current offset value for the selected channel.

Return Format

```
<offset><NL>

<offset> ::= Vertical offset value in NR3 format
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213
- ":CHANnel<n>:RANGe" on page 228
- ":CHANnel<n>:SCALe" on page 229
- ":CHANnel<n>:PROBe" on page 222

:CHANnel<n>:PROBe

(see page 828)

Command Syntax

```
:CHANnel<n>:PROBe <attenuation>

<attenuation> ::= probe attenuation ratio in NR3 format

<n> ::= 1 to (# analog channels) in NR1 format

The obsolete attenuation values X1, X10, X20, X100 are also supported.
```

The :CHANnel<n>:PROBe command specifies the probe attenuation factor for the selected channel. The probe attenuation factor may be 0.1 to 10000. This command does not change the actual input sensitivity of the oscilloscope. It changes the reference constants for scaling the display factors, for making automatic measurements, and for setting trigger levels.

Query Syntax

```
:CHANnel<n>:PROBe?
```

The :CHANnel<n>:PROBe? query returns the current probe attenuation factor for the selected channel.

Return Format

```
<attenuation><NL>

<attenuation> ::= probe attenuation ratio in NR3 format
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213
- ":CHANnel<n>:RANGe" on page 228
- ":CHANnel<n>:SCALe" on page 229
- ":CHANnel<n>:OFFSet" on page 221

Example Code

```
' CHANNEL_PROBE - Sets the probe attenuation factor for the selected
' channel.  The probe attenuation factor may be set from 0.1 to 10000
.
myScope.WriteString ":CHANnel1:PROBe 10"   ' Set Probe to 10:1.
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:CHANnel<n>:PROBe:HEAD[:TYPE]

(see page 828)

Command Syntax

NOTE This command is valid only for the 113xA Series probes.

```
:CHANnel<n>:PROBe:HEAD[:TYPE] <head_param>

<head_param> ::= {SEND0 | SEND6 | SEND12 | SEND20 | DIFF0 | DIFF6
                 | DIFF12 | DIFF20 | NONE}

<n> ::= {1 | 2 | 3 | 4}
```

The :CHANnel<n>:PROBe:HEAD[:TYPE] command sets an analog channel probe head type and dB value. You can choose from:

- SEND0 – Single-ended, 0dB.
- SEND6 – Single-ended, 6dB.
- SEND12 – Single-ended, 12dB.
- SEND20 – Single-ended, 20dB.
- DIFF0 – Differential, 0dB.
- DIFF6 – Differential, 6dB.
- DIFF12 – Differential, 12dB.
- DIFF20 – Differential, 20dB.

Query Syntax

```
:CHANnel<n>:PROBe:HEAD[:TYPE]?
```

The :CHANnel<n>:PROBe:HEAD[:TYPE]? query returns the current probe head type setting for the selected channel.

Return Format

```
<head_param><NL>

<head_param> ::= {SEND0 | SEND6 | SEND12 | SEND20 | DIFF0 | DIFF6
                 | DIFF12 | DIFF20 | NONE}
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213
- ":CHANnel<n>:PROBe" on page 222
- ":CHANnel<n>:PROBe:ID" on page 224
- ":CHANnel<n>:PROBe:SKEW" on page 225
- ":CHANnel<n>:PROBe:STYPe" on page 226

:CHANnel<n>:PROBe:ID

(see page 828)

Query Syntax

```
:CHANnel<n>:PROBe:ID?

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:PROBe:ID? query returns the type of probe attached to the specified oscilloscope channel.

Return Format

```
<probe id><NL>

<probe id> ::= unquoted ASCII string up to 11 characters
```

Some of the possible returned values are:

- 1131A
- 1132A
- 1134A
- 1147A
- 1153A
- 1154A
- 1156A
- 1157A
- 1158A
- 1159A
- AutoProbe
- E2621A
- E2622A
- E2695A
- E2697A
- HP1152A
- HP1153A
- NONE
- Probe
- Unknown
- Unsupported

See Also

- "Introduction to :CHANnel<n> Commands" on page 213

:CHANnel<n>:PROBe:SKEW

(see page 828)

Command Syntax

```
:CHANnel<n>:PROBe:SKEW <skew value>

<skew value> ::= skew time in NR3 format

<skew value> ::= -100 ns to +100 ns

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:PROBe:SKEW command sets the channel-to-channel skew factor for the specified channel. Each analog channel can be adjusted + or -100 ns for a total of 200 ns difference between channels. You can use the oscilloscope's probe skew control to remove cable-delay errors between channels.

Query Syntax

```
:CHANnel<n>:PROBe:SKEW?
```

The :CHANnel<n>:PROBe:SKEW? query returns the current probe skew setting for the selected channel.

Return Format

```
<skew value><NL>

<skew value> ::= skew value in NR3 format
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213

:CHANnel<n>:PROBe:STYPe

(see page 828)

Command Syntax

NOTE This command is valid only for the 113xA Series probes.

```
:CHANnel<n>:PROBe:STYPe <signal type>

<signal type> ::= {DIFFerential | SINGle}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:PROBe:STYPe command sets the channel probe signal type (STYPe) to differential or single-ended when using the 113xA Series probes and determines how offset is applied.

When single-ended is selected, the :CHANnel<n>:OFFset command changes the offset value of the probe amplifier. When differential is selected, the :CHANnel<n>:OFFset command changes the offset value of the channel amplifier.

Query Syntax

```
:CHANnel<n>:PROBe:STYPe?
```

The :CHANnel<n>:PROBe:STYPe? query returns the current probe signal type setting for the selected channel.

Return Format

```
<signal type><NL>

<signal type> ::= {DIFF | SING}
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213
- ":CHANnel<n>:OFFSet" on page 221

:CHANnel<n>:PROTection

N (see page 828)

Command Syntax

```
:CHANnel<n>:PROTection[:CLEar]

<n> ::= 1 to (# analog channels) in NR1 format
```

With the InfiniiVision 1200 X-Series and EDUX11052A/G oscilloscopes, the analog channel input impedance is always 1 MΩ, so automatic overvoltage protection is not necessary (as it is for channels with 50Ω input impedance). There are no protection settings to clear, so the :CHANnel<n>:PROTection[:CLEar] command does nothing.

Query Syntax

```
:CHANnel<n>:PROTection?
```

The :CHANnel<n>:PROTection query always returns NORM (normal).

Return Format

```
NORM<NL>
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213
- ":CHANnel<n>:COUPling" on page 216
- ":CHANnel<n>:PROBe" on page 222

:CHANnel<n>:RANGe

(see page 828)

Command Syntax

```
:CHANnel<n>:RANGe <range>[<suffix>]

<range> ::= vertical full-scale range value in NR3 format

<suffix> ::= {V | mV}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:RANGe command defines the full-scale vertical axis of the selected channel. When using 1:1 probe attenuation, legal values for the range are from 8 mV to 40 V.

If the probe attenuation is changed, the range value is multiplied by the probe attenuation factor.

Query Syntax

```
:CHANnel<n>:RANGe?
```

The :CHANnel<n>:RANGe? query returns the current full-scale range setting for the specified channel.

Return Format

```
<range_argument><NL>

<range_argument> ::= vertical full-scale range value in NR3 format
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213
- ":CHANnel<n>:SCALe" on page 229
- ":CHANnel<n>:PROBe" on page 222

Example Code

```
' CHANNEL_RANGE - Sets the full scale vertical range in volts.  The
' range value is 8 times the volts per division.
myScope.WriteString ":CHANnel1:RANGe 8"   ' Set the vertical range to
8 volts.
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:CHANnel<n>:SCALe

(see page 828)

Command Syntax

```
:CHANnel<n>:SCALe <scale>[<suffix>]

<scale> ::= vertical units per division in NR3 format

<suffix> ::= {V | mV}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:SCALe command sets the vertical scale, or units per division, of the selected channel.

If the probe attenuation is changed, the scale value is multiplied by the probe's attenuation factor.

Query Syntax

```
:CHANnel<n>:SCALe?
```

The :CHANnel<n>:SCALe? query returns the current scale setting for the specified channel.

Return Format

```
<scale value><NL>

<scale value> ::= vertical units per division in NR3 format
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213
- ":CHANnel<n>:RANGe" on page 228
- ":CHANnel<n>:PROBe" on page 222

:CHANnel<n>:UNITs

(see page 828)

Command Syntax

```
:CHANnel<n>:UNITs <units>

<units> ::= {VOLT | AMPere}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:UNITs command sets the measurement units for the connected probe. Select VOLT for a voltage probe and select AMPere for a current probe. Measurement results, channel sensitivity, and trigger level will reflect the measurement units you select.

Query Syntax

```
:CHANnel<n>:UNITs?
```

The :CHANnel<n>:UNITs? query returns the current units setting for the specified channel.

Return Format

```
<units><NL>

<units> ::= {VOLT | AMP}
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213
- ":CHANnel<n>:RANGe" on page 228
- ":CHANnel<n>:PROBe" on page 222
- ":EXTernal:UNITs" on page 270

:CHANnel<n>:VERNier

(see page 828)

Command Syntax

```
:CHANnel<n>:VERNier <vernier value>

<vernier value> ::= {{1 | ON} | {0 | OFF}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:VERNier command specifies whether the channel's vernier (fine vertical adjustment) setting is ON (1) or OFF (0).

Query Syntax

```
:CHANnel<n>:VERNier?
```

The :CHANnel<n>:VERNier? query returns the current state of the channel's vernier setting.

Return Format

```
<vernier value><NL>

<vernier value> ::= {0 | 1}
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213

11 :DEMO Commands

You can output demonstration/training signals on the oscilloscope's Demo terminal. See "Introduction to :DEMO Commands" on page 233.

Table 57 :DEMO Commands Summary

Command	Query	Options and Query Returns
`:DEMO:FUNCtion <signal>` (see page 234)	`:DEMO:FUNCtion?` (see page 235)	`<signal> ::= {SINusoid | NOISy | LFSine | AM | RFBurst | FMBurst | HARMonics | COUPling | RINGing | SINGle | CLK | TRANsition | BURSt | GLITch | CAN | LIN}`
`:DEMO:OUTPut {{0 | OFF} | {1 | ON}}` (see page 236)	`:DEMO:OUTPut?` (see page 236)	`{0 | 1}`

Introduction to :DEMO Commands

The :DEMO subsystem provides commands to output demonstration signals on the oscillosope's Demo terminal.

Reporting the Setup

Use :DEMO? to query setup information for the DEMO subsystem.

Return Format

The following is a sample response from the :DEMO? query. In this case, the query was issued following the *RST command.

```
:DEMO:FUNC SIN;OUTP 0
```

:DEMO:FUNCtion

N (see page 828)

Command Syntax

```
:DEMO:FUNCtion <signal>

<signal> ::= {SINusoid | NOISy | LFSine | AM | RFBurst | FMBurst
   | HARMonics | COUPling | RINGing | SINGle | CLK | TRANsition
   | BURSt | GLITch | CAN | LIN}
```

The :DEMO:FUNCtion command selects the type of demo signal:

Demo Signal Function	Demo Terminal
SINusoid	250 kHz sine wave @ ~ 6 Vpp, 0 V offset
NOISy	1 kHz sine wave @ ~ 2.4 Vpp, 0.0 V offset, with ~ 0.5 Vpp of random noise added
LFSine	30 Hz sine wave @ ~2.7 Vpp, 0 V offset, with very narrow glitch near each positive peak
AM	Amplitude modulated signal, ~ 3 Vpp, 0 V offset, with ~260 kHz carrier and sine envelope
RFBurst	5-cycle burst of a 10 MHz amplitude modulated sine wave @ ~ 2.6 Vpp, 0 V offset occurring once every 4 ms
FMBurst	FM burst, modulated from ~100 kHz to ~1 MHz, ~5.0 Vpp, ~600 mV offset.
HARMonics	1 kHz sine wave @ ~3.5 Vpp, 0.0 V offset, with a ~2 kHz sine wave coupled in
COUPling	1 kHz square wave @ ~1 Vpp, 0.0 V offset, with a ~90 kHz sine wave with ~180 mVpp riding on top
RINGing	10 kHz digital pulse @ ~ 3 Vpp, 1.5 V offset, and ~24 µs pulse width with ringing
SINGle	~24 µs wide digital pulse with ringing @ ~ 3 Vpp, 1.5 V offset Press the front panel **Set Off Single-Shot** softkey to cause the selected single-shot signal to be output.
CLK	50 kHz clock @ ~2 Vpp, 1 V offset, with infrequent glitch (1 glitch per 50,000 clocks)
TRANsition	Digital pulse train with two different edge speeds @ ~ 3.5 Vpp, 1.75 V offset
BURSt	Burst of digital pulses that occur every 50 µs @ ~ 3.6 Vpp, ~1.5 V offset
GLITch	Burst of 6 digital pulses (plus infrequent glitch) that occurs once every 80 µs @ ~3.6 Vpp, ~1.8 V offset

Demo Signal Function	Demo Terminal
CAN	CAN_L, 125 kbps dominant-low, ~2.8 Vpp, ~1.4 V offset, available in DSOX1200-Series oscilloscope models only
LIN	LIN, 19.2 kbs, ~2.8 Vpp, ~1.4 V offset, available in DSOX1200-Series oscilloscope models only

Query Syntax

```
:DEMO:FUNCtion?
```

The :DEMO:FUNCtion? query returns the currently selected demo signal type.

Return Format

```
<signal><NL>

<signal> ::= {SIN | NOIS | LFS | AM | RFB | FMB | HARM | COUP | RING
    | SING | CLK | TRAN | BURS | GLIT | CAN | LIN}
```

See Also

- "Introduction to :DEMO Commands" on page 233

:DEMO:OUTPut

(see page 828)

Command Syntax

```
:DEMO:OUTPut <on_off>

<on_off> ::= {{1 | ON} | {0 | OFF}
```

The :DEMO:OUTPut command specifies whether the demo signal output is ON (1) or OFF (0).

Query Syntax

```
:DEMO:OUTPut?
```

The :DEMO:OUTPut? query returns the current state of the demo signal output setting.

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- "Introduction to :DEMO Commands" on page 233
- ":DEMO:FUNCtion" on page 234

12 :DISPlay Commands

Control how waveforms, graticule, and text are displayed and written on the screen. See "Introduction to :DISPlay Commands" on page 238.

Table 58 :DISPlay Commands Summary

Command	Query	Options and Query Returns
:DISPlay:ANNotation {{0 | OFF} | {1 | ON}} (see page 239)	:DISPlay:ANNotation? (see page 239)	{0 | 1}
:DISPlay:ANNotation:BACKground <mode> (see page 240)	:DISPlay:ANNotation:BACKground? (see page 240)	<mode> ::= {OPAQue | INVerted | TRANsparent}
:DISPlay:ANNotation:COLor <color> (see page 241)	:DISPlay:ANNotation:COLor? (see page 241)	<color> ::= {CH1 | CH2 | CH3 | CH4 | DIG | MATH | REF | MARKer | WHITe | RED}
:DISPlay:ANNotation:TEXT <string> (see page 242)	:DISPlay:ANNotation:TEXT? (see page 242)	<string> ::= quoted ASCII string (up to 254 characters)
:DISPlay:CLEar (see page 243)	n/a	n/a
n/a	:DISPlay:DATA? [<format>][,][<palette>] (see page 244)	<format> ::= {BMP | BMP8bit | PNG} <palette> ::= {COLor | GRAYscale} <display data> ::= data in IEEE 488.2 # format
:DISPlay:INTensity:WAVeform <value> (see page 245)	:DISPlay:INTensity:WAVeform? (see page 245)	<value> ::= an integer from 0 to 100 in NR1 format.
:DISPlay:LABel {{0 | OFF} | {1 | ON}} (see page 246)	:DISPlay:LABel? (see page 246)	{0 | 1}

Table 58 :DISPlay Commands Summary (continued)

Command	Query	Options and Query Returns
:DISPlay:LABList <binary block> (see page 247)	:DISPlay:LABList? (see page 247)	<binary block> ::= an ordered list of up to 75 labels, each 10 characters maximum, separated by newline characters
:DISPlay:MENU:TIMeout {<value> | {OFF | MAX}} (see page 248)	:DISPlay:MENU:TIMeout? (see page 248)	<value> ::= an integer from 5 to 60 in NR1 format.
:DISPlay:PERSistence <value> (see page 249)	:DISPlay:PERSistence? (see page 249)	<value> ::= {MINimum | INFinite | <time>} <time> ::= seconds in in NR3 format from 100E-3 to 60E0
:DISPlay:TRANsparent {{0 | OFF} | {1 | ON}} (see page 250)	:DISPlay:TRANsparent? (see page 250)	{0 | 1}
:DISPlay:VECTors {1 | ON} (see page 251)	:DISPlay:VECTors? (see page 251)	1

Introduction to :DISPlay Commands

The DISPlay subsystem is used to control the display storage and retrieval of waveform data, labels, and text. This subsystem allows the following actions:

- Clear the waveform area on the display.
- Turn vectors on or off.
- Set waveform persistence.
- Specify labels.
- Save and Recall display data.

Reporting the Setup

Use :DISPlay? to query the setup information for the DISPlay subsystem.

Return Format

The following is a sample response from the :DISPlay? query. In this case, the query was issued following a *RST command.

```
:DISP:LAB 0;VECT 1;PERS MIN
```

:DISPlay:ANNotation

(see page 828)

Command Syntax

```
:DISPlay:ANNotation <setting>

<setting> ::= {{1 | ON} | {0 | OFF}}
```

The :DISPlay:ANNotation command turns the annotation on and off. When on, the annotation appears in the upper left corner of the oscilloscope's display.

The annotation is useful for documentation purposes, to add notes before capturing screens.

Query Syntax

```
:DISPlay:ANNotation?
```

The :DISPlay:ANNotation? query returns the annotation setting.

Return Format

```
<value><NL>

<value> ::= {0 | 1}
```

See Also

- ":DISPlay:ANNotation:TEXT" on page 242
- ":DISPlay:ANNotation:COLor" on page 241
- ":DISPlay:ANNotation:BACKground" on page 240
- "Introduction to :DISPlay Commands" on page 238

:DISPlay:ANNotation:BACKground

(see page 828)

Command Syntax

```
:DISPlay:ANNotation:BACKground <mode>

<mode> ::= {OPAQue | INVerted | TRANsparent}
```

The :DISPlay:ANNotation:BACKground command specifies the background of the annotation:

- OPAQue – the annotation has a solid background.
- INVerted – the annotation's foreground and background colors are switched.
- TRANsparent – the annotation has a transparent background.

Query Syntax

```
:DISPlay:ANNotation:BACKground?
```

The :DISPlay:ANNotation:BACKground? query returns the specified annotation background mode.

Return Format

```
<mode><NL>

<mode> ::= {OPAQ | INV | TRAN}
```

See Also

- ":DISPlay:ANNotation" on page 239
- ":DISPlay:ANNotation:TEXT" on page 242
- ":DISPlay:ANNotation:COLor" on page 241
- "Introduction to :DISPlay Commands" on page 238

:DISPlay:ANNotation:COLor

(see page 828)

Command Syntax

```
:DISPlay:ANNotation:COLor <color>

<color> ::= {CH1 | CH2 | CH3 | CH4 | DIG | MATH | REF | MARKer | WHITe
            | RED}
```

The :DISPlay:ANNotation:COLor command specifies the annotation color. You can choose white, red, or colors that match analog channels, digital channels, math waveforms, reference waveforms, or markers.

Query Syntax

```
:DISPlay:ANNotation:COLor?
```

The :DISPlay:ANNotation:COLor? query returns the specified annotation color.

Return Format

```
<color><NL>

<color> ::= {CH1 | CH2 | CH3 | CH4 | DIG | MATH | REF | MARK | WHIT
            | RED}
```

See Also

- ":DISPlay:ANNotation" on page 239
- ":DISPlay:ANNotation:TEXT" on page 242
- ":DISPlay:ANNotation:BACKground" on page 240
- "Introduction to :DISPlay Commands" on page 238

:DISPlay:ANNotation:TEXT

N (see page 828)

Command Syntax

```
:DISPlay:ANNotation:TEXT <string>

<string> ::= quoted ASCII string (up to 254 characters)
```

The :DISPlay:ANNotation:TEXT command specifies the annotation string. The annotation string can contain as many characters as will fit in the Edit Annotation box on the oscilloscope's screen, up to 254 characters.

You can include a carriage return in the annotation string using the characters "\n". Note that this is not a new line character but the actual "\" (backslash) and "n" characters in the string. Carriage returns lessen the number of characters available for the annotation string.

Use :DISPlay:ANNotation:TEXT "" to remotely clear the annotation text. (Two sets of quote marks without a space between them creates a NULL string.)

Query Syntax

```
:DISPlay:ANNotation:TEXT?
```

The :DISPlay:ANNotation:TEXT? query returns the specified annotation text.

When carriage returns are present in the annotation text, they are returned as the actual carriage return character (ASCII 0x0D).

Return Format

```
<string><NL>

<string> ::= quoted ASCII string
```

See Also

- ":DISPlay:ANNotation" on page 239
- ":DISPlay:ANNotation:COLor" on page 241
- ":DISPlay:ANNotation:BACKground" on page 240
- "Introduction to :DISPlay Commands" on page 238

:DISPlay:CLEar

(see page 828)

Command Syntax `:DISPlay:CLEar`

The :DISPlay:CLEar command clears the display and resets all associated measurements. If the oscilloscope is stopped, all currently displayed data is erased. If the oscilloscope is running, all of the data for active channels and functions is erased; however, new data is displayed on the next acquisition.

See Also

- "Introduction to :DISPlay Commands" on page 238

:DISPlay:DATA

N (see page 828)

Query Syntax

```
:DISPlay:DATA? [<format>][,][<palette>]

<format> ::= {BMP | BMP8bit | PNG}

<palette> ::= {COLor | GRAYscale}
```

The :DISPlay:DATA? query reads screen image data. You can choose 24-bit BMP, 8-bit BMP8bit, or 24-bit PNG formats in color or grayscale.

You can invert the screen image graticule colors (before reading the data) by using the ":HARDcopy:INKSaver ON" command.

If no format or palette option is specified, the screen image is returned in BMP, COLor format.

Return Format

```
<display data><NL>

<display data> ::= binary block data in IEEE-488.2 # format.
```

Screen image data is returned in the IEEE-488.2 # binary block data format.

See Also

- "Introduction to :DISPlay Commands" on page 238
- ":HARDcopy:INKSaver" on page 329
- ":PRINt" on page 169
- "*RCL (Recall)" on page 130
- "*SAV (Save)" on page 134
- ":VIEW" on page 176

Example Code

```
' IMAGE_TRANSFER - In this example, we will query for the image data
' with ":DISPlay:DATA?", read the data, and then save it to a file.
Dim byteData() As Byte
myScope.IO.Timeout = 15000
myScope.WriteString ":DISPlay:DATA? BMP, COLOR"
byteData = myScope.ReadIEEEBlock(BinaryType_UI1)
' Output display data to a file:
strPath = "c:\scope\data\screen.bmp"
' Remove file if it exists.
If Len(Dir(strPath)) Then
  Kill strPath
End If
Close #1   ' If #1 is open, close it.
Open strPath For Binary Access Write Lock Write As #1   ' Open file f
or output.
Put #1, , byteData   ' Write data.
Close #1   ' Close file.
myScope.IO.Timeout = 5000
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:DISPlay:INTensity:WAVeform

N (see page 828)

Command Syntax

```
:DISPlay:INTensity:WAVeform <value>
<value> ::= an integer from 0 to 100 in NR1 format.
```

The :DISPlay:INTensity:WAVeform command sets the waveform intensity.

This is the same as adjusting the front panel **[Intensity]** knob.

Query Syntax

```
:DISPlay:INTensity:WAVeform?
```

The :DISPlay:INTensity:WAVeform? query returns the waveform intensity setting.

Return Format

```
<value><NL>
<value> ::= an integer from 0 to 100 in NR1 format.
```

See Also

- "Introduction to :DISPlay Commands" on page 238

:DISPlay:LABel

(see page 828)

Command Syntax

```
:DISPlay:LABel <value>

<value> ::= {{1 | ON} | {0 | OFF}}
```

The :DISPlay:LABel command turns the analog channel labels on and off.

Query Syntax

```
:DISPlay:LABel?
```

The :DISPlay:LABel? query returns the display mode of the analog channel labels.

Return Format

```
<value><NL>

<value> ::= {0 | 1}
```

See Also

- "Introduction to :DISPlay Commands" on page 238
- ":CHANnel<n>:LABel" on page 220

Example Code

```
' DISP_LABEL
'  - Turns label names ON or OFF on the analyzer display.
myScope.WriteString ":DISPlay:LABel ON"    ' Turn on labels.
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:DISPlay:LABList

N (see page 828)

Command Syntax

```
:DISPlay:LABList <binary block data>

<binary block> ::= an ordered list of up to 75 labels, a maximum of 10
                   characters each, separated by newline characters.
```

The :DISPlay:LABList command adds labels to the label list. Labels are added in alphabetical order.

NOTE Labels that begin with the same alphabetic base string followed by decimal digits are considered duplicate labels. Duplicate labels are not added to the label list. For example, if label "A0" is in the list and you try to add a new label called "A123456789", the new label is not added.

Query Syntax

```
:DISPlay:LABList?
```

The :DISPlay:LABList? query returns the label list.

Return Format

```
<binary block><NL>

<binary block> ::= an ordered list of up to 75 labels, a maximum of 10
                   characters each, separated by newline characters.
```

See Also

- "Introduction to :DISPlay Commands" on page 238
- ":DISPlay:LABel" on page 246
- ":CHANnel<n>:LABel" on page 220

:DISPlay:MENU:TIMeout

(see page 828)

Command Syntax

```
:DISPlay:MENU:TIMeout {<value> | {OFF | MAX}}

<value> ::= an integer from 5 to 60 in NR1 format.
```

The :DISPlay:MENU:TIMeout command sets the softkey menu timeout period. OFF and MAX are equivalent.

Query Syntax

```
:DISPlay:MENU:TIMeout?
```

The :DISPlay:MENU:TIMeout? query returns the softkey menu timeout period setting.

Return Format

```
<value><NL>

<value> ::= an integer from 5 to 60 in NR1 format or OFF.
```

:DISPlay:PERSistence

(see page 828)

Command Syntax

```
:DISPlay:PERSistence <value>

<value> ::= {MINimum | INFinite | <time>}

<time> ::= seconds in in NR3 format from 100E-3 to 60E0
```

The :DISPlay:PERSistence command specifies the persistence setting:

- MINimum – indicates zero persistence.
- INFinite – indicates infinite persistence.
- <time> – for variable persistence, that is, you can specify how long acquisitions remain on the screen.

Use the :DISPlay:CLEar command to erase points stored by persistence.

Query Syntax

```
:DISPlay:PERSistence?
```

The :DISPlay:PERSistence? query returns the specified persistence value.

Return Format

```
<value><NL>

<value> ::= {MIN | INF | <time>}
```

See Also

- "Introduction to :DISPlay Commands" on page 238
- ":DISPlay:CLEar" on page 243

:DISPlay:TRANsparent

(see page 828)

Command Syntax

```
:DISPlay:TRANsparent <setting>

<setting> ::= {{0 | OFF} | {1 | ON}}
```

The :DISPlay:TRANsparent command enables or disables transparent mode for DVM, mask test statistics, and waveform memory readouts in the front panel graphical user interface.

This command maps to the **Transparent** softkey that appears in the front panel user interface under **[Utility] > Options > Preferences** and in the menus for DVM, mask testing, and waveform memory.

Note that annotations and remote logging have separate transparency controls (:DISPlay:ANNotation:BACKground and :SYSTem:RLOGger:TRANsparent).

Query Syntax

```
:DISPlay:TRANsparent?
```

The :DISPlay:TRANsparent? query returns the transparent setting.

Return Format

```
<setting><NL>

<setting> ::= {0 | 1}
```

See Also

- "Introduction to :DISPlay Commands" on page 238
- ":DISPlay:ANNotation:BACKground" on page 240
- ":SYSTem:RLOGger:TRANsparent" on page 595

:DISPlay:VECTors

(see page 828)

Command Syntax

```
:DISPlay:VECTors <vectors>

<vectors> ::= {1 | ON}
```

The only legal value for the :DISPlay:VECTors command is ON (or 1). This specifies that lines are drawn between acquired data points on the screen.

Query Syntax

```
:DISPlay:VECTors?
```

The :DISPlay:VECTors? query returns the vectors setting.

Return Format

```
<vectors><NL>

<vectors> ::= 1
```

See Also

- "Introduction to :DISPlay Commands" on page 238

13 :DVM Commands

These commands control the digital voltmeter (DVM) feature.

Table 59 :DVM Commands Summary

Command	Query	Options and Query Returns
:DVM:ARANge {{0 | OFF} | {1 | ON}} (see page 254)	:DVM:ARANge? (see page 254)	{0 | 1}
n/a	:DVM:CURRent? (see page 255)	<dvm_value> ::= floating-point number in NR3 format
:DVM:ENABle {{0 | OFF} | {1 | ON}} (see page 256)	:DVM:ENABle? (see page 256)	{0 | 1}
n/a	:DVM:FREQuency? (see page 255)	<freq_value> ::= floating-point number in NR3 format
:DVM:MODE <mode> (see page 258)	:DVM:MODE? (see page 258)	<dvm_mode> ::= {ACRMs | DC | DCRMs | FREQuency}
:DVM:SOURce <source> (see page 259)	:DVM:SOURce? (see page 259)	<source> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format

:DVM:ARANge

(see page 828)

Command Syntax

```
:DVM:ARANge <setting>

<setting> ::= {{OFF | 0} | {ON | 1}}
```

If the selected digital voltmeter (DVM) source channel is not used in oscilloscope triggering, the :DVM:ARANge command turns the digital voltmeter's Auto Range capability on or off.

- When on, the DVM channel's vertical scale, vertical (ground level) position, and trigger (threshold voltage) level (used for the counter frequency measurement) are automatically adjusted.

  The Auto Range capability overrides attempted adjustments of the channel's vertical scale and position.
- When off, you can adjust the channel's vertical scale and position normally.

Query Syntax

```
:DVM:ARANge?
```

The :DVM:ARANge? query returns a flag indicating whether the digital voltmeter's Auto Range capability is on or off.

Return Format

```
<setting><NL>

<setting> ::= {0 | 1}
```

See Also

- ":DVM:SOURce" on page 259
- ":DVM:ENABle" on page 256
- ":DVM:MODE" on page 258

:DVM:CURRent

(see page 828)

Query Syntax `:DVM:CURRent?`

The :DVM:CURRent? query returns the displayed 3-digit DVM value based on the current mode.

NOTE It can take up to a few seconds after DVM analysis is enabled before this query starts to produce good results, that is, results other than +9.9E+37. To wait for good values after DVM analysis is enabled, programs should loop until a value less than +9.9E+37 is returned.

Return Format `<dvm_value><NL>`

`<dvm_value> ::= floating-point number in NR3 format`

See Also
- ":DVM:SOURce" on page 259
- ":DVM:ENABle" on page 256
- ":DVM:MODE" on page 258
- ":DVM:FREQuency" on page 257

:DVM:ENABle

(see page 828)

Command Syntax

```
:DVM:ENABle <setting>

<setting> ::= {{OFF | 0} | {ON | 1}}
```

The :DVM:ENABle command turns the digital voltmeter (DVM) analysis feature on or off.

Query Syntax

```
:DVM:ENABle?
```

The :DVM:ENABle? query returns a flag indicating whether the digital voltmeter (DVM) analysis feature is on or off.

Return Format

```
<setting><NL>

<setting> ::= {0 | 1}
```

See Also

- ":DVM:SOURce" on page 259
- ":DVM:MODE" on page 258
- ":DVM:ARANge" on page 254

:DVM:FREQuency

(see page 828)

Query Syntax `:DVM:FREQuency?`

The :DVM:FREQuency? query returns the displayed 5-digit frequency value that is displayed below the main DVM value.

If the requirements for the DVM FREQuency mode are not met (see ":DVM:MODE" on page 258), this query will return 9.9E+37.

Return Format `<freq_value><NL>`

`<freq_value> ::= floating-point number in NR3 format`

See Also

- ":DVM:SOURce" on page 259
- ":DVM:ENABle" on page 256
- ":DVM:MODE" on page 258
- ":DVM:CURRent" on page 255

:DVM:MODE

(see page 828)

Command Syntax

```
:DVM:MODE <dvm_mode>

<dvm_mode> ::= {ACRMs | DC | DCRMs | FREQuency}
```

The :DVM:MODE command sets the digital voltmenter (DVM) mode:

- ACRMs – displays the root-mean-square value of the acquired data, with the DC component removed.
- DC – displays the DC value of the acquired data.
- DCRMs – displays the root-mean-square value of the acquired data.
- FREQuency – displays the frequency counter measurement. Requires the EDGE or GLITch trigger mode, and the DVM source and the trigger source must be the same analog channel.

Query Syntax

```
:DVM:MODE?
```

The :DVM:MODE? query returns the selected DVM mode.

Return Format

```
<dvm_mode><NL>

<dvm_mode> ::= {ACRM | DC | DCRM | FREQ}
```

See Also

- ":DVM:ENABle" on page 256
- ":DVM:SOURce" on page 259
- ":DVM:ARANge" on page 254
- ":DVM:CURRent" on page 255
- ":DVM:FREQuency" on page 257
- ":TRIGger:MODE" on page 624

:DVM:SOURce

(see page 828)

Command Syntax

```
:DVM:SOURce <source>

<source> ::= {CHANnel<n>}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :DVM:SOURce command sets the select the analog channel on which digital voltmeter (DVM) measurements are made.

The selected channel does not have to be on (displaying a waveform) in order for DVM measurements to be made.

Query Syntax

```
:DVM:SOURce?
```

The :DVM:SOURce? query returns the selected DVM input source.

Return Format

```
<source><NL>

<source> ::= {CHAN<n>}

<n> ::= 1 to (# analog channels) in NR1 format
```

See Also

- ":DVM:ENABle" on page 256
- ":DVM:MODE" on page 258
- ":DVM:ARANge" on page 254
- ":DVM:CURRent" on page 255
- ":DVM:FREQuency" on page 257

14 :EXTernal Trigger Commands

Control the input characteristics of the external trigger input. See "Introduction to :EXTernal Trigger Commands" on page 262.

Table 60 :EXTernal Trigger Commands Summary

Command	Query	Options and Query Returns
:EXTernal:BWLimit <bwlimit> (see page 263)	:EXTernal:BWLimit? (see page 263)	<bwlimit> ::= {0 | OFF}
:EXTernal:DISPlay {{0 | OFF} | {1 | ON}} (see page 264)	:EXTernal:DISPlay? (see page 264)	<setting> ::= {0 | 1} On DSOX1204A/G oscilloscopes, the :EXTernal:DISPlay command can be set to OFF only.
:EXTernal:LABel <string> (see page 265)	:EXTernal:LABel? (see page 265)	<string> ::= quoted ASCII string.
:EXTernal:LEVel <level>[<suffix>] (see page 266)	:EXTernal:LEVel? (see page 266)	<value> ::= external trigger level value in NR3 format. <suffix> ::= {V | mV}
:EXTernal:POSition <value> (see page 267)	:EXTernal:POSition? (see page 267)	<value> ::= Ext Trig waveform vertical position in divisions in NR3 format. On DSOX1204A/G oscilloscopes, the :EXTernal:POSition value can be zero only.
:EXTernal:PROBe <attenuation> (see page 268)	:EXTernal:PROBe? (see page 268)	<attenuation> ::= probe attenuation ratio in NR3 format
:EXTernal:RANGe <range>[<suffix>] (see page 269)	:EXTernal:RANGe? (see page 269)	<range> ::= vertical full-scale range value in NR3 format <suffix> ::= {V | mV}
:EXTernal:UNITs <units> (see page 270)	:EXTernal:UNITs? (see page 270)	<units> ::= {VOLT | AMPere}

Introduction to :EXTernal Trigger Commands

The EXTernal trigger subsystem commands control the input characteristics of the external trigger input. The probe factor, impedance, input range, input protection state, units, and bandwidth limit settings may all be queried. Depending on the instrument type, some settings may be changeable.

Reporting the Setup

Use :EXTernal? to query setup information for the EXTernal subsystem.

Return Format

The following is a sample response from the :EXTernal query. In this case, the query was issued following a *RST command.

```
:EXT:BWL 0;RANG +8E+00;UNIT VOLT;PROB +1.000E+00
```

:EXTernal:BWLimit

(see page 828)

Command Syntax

```
:EXTernal:BWLimit <bwlimit>

<bwlimit> ::= {0 | OFF}
```

The :EXTernal:BWLimit command is provided for product compatibility. The only legal value is 0 or OFF. Use the :TRIGger:HFReject command to limit bandwidth on the external trigger input.

Query Syntax

```
:EXTernal:BWLimit?
```

The :EXTernal:BWLimit? query returns the current setting of the low-pass filter (always 0).

Return Format

```
<bwlimit><NL>

<bwlimit> ::= 0
```

See Also

- "Introduction to :EXTernal Trigger Commands" on page 262
- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:HFReject" on page 619

:EXTernal:DISPlay

(see page 828)

Command Syntax `:EXTernal:DISPlay {{0 | OFF} | {1 | ON}}`

In the InfiniiVision DSOX1204A/G oscilloscopes, the :EXTernal:DISPlay command can be set to OFF only.

Query Syntax `:EXTernal:DISPlay?`

The :EXTernal:DISPlay? query returns the external trigger input display setting.

Return Format `<setting><NL>`

`<setting> ::= {0 | 1}`

See Also

- ":EXTernal:LEVel" on page 266

:EXTernal:LABel

(see page 828)

Command Syntax

```
:EXTernal:LABel <string>

<string> ::= quoted ASCII string.
```

NOTE

Label strings are 10 characters or less, and may contain any commonly used ASCII characters. Labels with more than 10 characters are truncated to 10 characters. Lower case characters are converted to upper case.

The :EXTernal:LABel command sets the external trigger input's label.

Setting a label for the external waveform also adds the name to the label list in non-volatile memory (replacing the oldest label in the list).

Query Syntax

```
:EXTernal:LABel?
```

The :EXTernal:LABel? query returns the label associated with the external trigger input.

Return Format

```
<string><NL>

<string> ::= quoted ASCII string.
```

See Also

- ":EXTernal:DISPlay" on page 264
- ":DISPlay:LABel" on page 246

:EXTernal:LEVel

(see page 828)

Command Syntax

```
:EXTernal:LEVel <level>[<suffix>]

<value> ::= external trigger level value in NR3 format.

<suffix> ::= {V | mV}
```

The :EXTernal:LEVel command sets the external trigger input threshold (trigger) voltage level.

Query Syntax

```
:EXTernal:LEVel?
```

The :EXTernal:LEVel? query returns the external trigger input threshold voltage setting.

Return Format

```
<value><NL>
```

See Also

- ":EXTernal:DISPlay" on page 264

:EXTernal:POSition

N (see page 828)

Command Syntax `:EXTernal:POSition <value>`

`<value> ::= Ext Trig waveform vertical position in divisions in NR3 form at.`

The :EXTernal:POSition command sets the external trigger input waveform's veritical position on the oscilloscope display.

When the external trigger input's waveform is displayed (see :EXTernal:DISPlay), a cyan digital waveform, based on the :EXTernal:LEVel threshold voltage, appears on the oscilloscope display. This waveform is one division tall, and the base of the waveform can be positioned from -3.5 divisions to 2.5 divisions.

In the InfiniiVision DSOX1204A/G oscilloscopes, the :EXTernal:POSition command can be set to zero only (since the Ext Trig input cannot be displayed as a digital waveform).

Query Syntax `:EXTernal:POSition?`

The :EXTernal:POSition? query returns, in vertical divisions, the position of the external trigger input waveform.

In the InfiniiVision DSOX1204A/G oscilloscopes, the :EXTernal:POSition? query returns zero.

Return Format `<value><NL>`

See Also

- ":EXTernal:DISPlay" on page 264
- ":EXTernal:LEVel" on page 266

:EXTernal:PROBe

(see page 828)

Command Syntax

```
:EXTernal:PROBe <attenuation>

<attenuation> ::= probe attenuation ratio in NR3 format
```

The :EXTernal:PROBe command specifies the probe attenuation factor for the external trigger. The probe attenuation factor may be 0.1 to 10000. This command does not change the actual input sensitivity of the oscilloscope. It changes the reference constants for scaling the display factors and for setting trigger levels.

If an AutoProbe probe is connected to the oscilloscope, the attenuation value cannot be changed from the sensed value. Attempting to set the oscilloscope to an attenuation value other than the sensed value produces an error.

Query Syntax

```
:EXTernal:PROBe?
```

The :EXTernal:PROBe? query returns the current probe attenuation factor for the external trigger.

Return Format

```
<attenuation><NL>

<attenuation> ::= probe attenuation ratio in NR3 format
```

See Also

- "Introduction to :EXTernal Trigger Commands" on page 262
- ":EXTernal:RANGe" on page 269
- "Introduction to :TRIGger Commands" on page 615
- ":CHANnel<n>:PROBe" on page 222

:EXTernal:RANGe

(see page 828)

Command Syntax

```
:EXTernal:RANGe <range>[<suffix>]

<range> ::= vertical full-scale range value in NR3 format

<suffix> ::= {V | mV}
```

The :EXTernal:RANGe command sets the external trigger input signal range.

When using DSOX1200-Series oscilloscopes, this range is either 1.6 V or 8 V when you are using a 1:1 probe.

When using EDUX1000-Series oscilloscopes, this range is 8 V when you are using a 1:1 probe and cannot be changed.

If the probe attenuation is changed, the range value is multiplied by the probe attenuation factor.

Query Syntax

```
:EXTernal:RANGe?
```

The :EXTernal:RANGe? query returns the current full-scale range setting for the external trigger.

Return Format

```
<range_argument><NL>

<range_argument> ::= external trigger range value in NR3 format
```

See Also

- "Introduction to :EXTernal Trigger Commands" on page 262
- ":EXTernal:PROBe" on page 268
- "Introduction to :TRIGger Commands" on page 615

:EXTernal:UNITs

(see page 828)

Command Syntax

```
:EXTernal:UNITs <units>

<units> ::= {VOLT | AMPere}
```

The :EXTernal:UNITs command sets the measurement units for the probe connected to the external trigger input. Select VOLT for a voltage probe and select AMPere for a current probe. Measurement results, channel sensitivity, and trigger level will reflect the measurement units you select.

Query Syntax

```
:EXTernal:UNITs?
```

The :CHANnel<n>:UNITs? query returns the current units setting for the external trigger.

Return Format

```
<units><NL>

<units> ::= {VOLT | AMP}
```

See Also

- "Introduction to :EXTernal Trigger Commands" on page 262
- "Introduction to :TRIGger Commands" on page 615
- ":EXTernal:RANGe" on page 269
- ":EXTernal:PROBe" on page 268
- ":CHANnel<n>:UNITs" on page 230

15 :FFT Commands

Control functions in the measurement/storage module. See "Introduction to :FFT Commands" on page 272.

Table 61 :FFT Commands Summary

Command	Query	Options and Query Returns
:FFT:CENTer <frequency> (see page 273)	:FFT:CENTer? (see page 273)	<frequency> ::= the current center frequency in NR3 format. The range of legal values is from -25 GHz to 25 GHz.
:FFT:DISPlay {{0 | OFF} | {1 | ON}} (see page 274)	:FFT:DISPlay? (see page 274)	<s> ::= 1-6, in NR1 format. {0 | 1}
:FFT:OFFSet <offset> (see page 275)	:FFT:OFFSet? (see page 275)	<offset> ::= the value at center screen in NR3 format.
:FFT:RANGe <range> (see page 276)	:FFT:RANGe? (see page 276)	<range> ::= the full-scale vertical axis value in NR3 format.
:FFT:REFerence <level> (see page 277)	:FFT:REFerence? (see page 277)	<level> ::= the current reference level in NR3 format.
:FFT:SCALe <scale_value>[<suffix>] (see page 278)	:FFT:SCALe? (see page 278)	<scale_value> ::= integer in NR1 format. <suffix> ::= dB
:FFT:SOURce1 <source> (see page 279)	:FFT:SOURce1? (see page 279)	<source> ::= {CHANnel<n> | FUNCtion<c> | MATH<c>} <n> ::= 1 to (# analog channels) in NR1 format. <c> ::= {1 | 2}
:FFT:SPAN (see page 280)	:FFT:SPAN? (see page 280)	::= the current frequency span in NR3 format. Legal values are 1 Hz to 100 GHz.

Table 61 :FFT Commands Summary (continued)

Command	Query	Options and Query Returns
:FFT:VTYPe <units> (see page 281)	:FFT:VTYPe? (see page 281)	<units> ::= {DECibel | VRMS}
:FFT:WINDow <window> (see page 282)	:FFT:WINDow? (see page 282)	<window> ::= {RECTangular | HANNing | FLATtop | BHARris}

Introduction to :FFT Commands

The FFT subsystem controls the FFT function in the oscilloscope.

Reporting the Setup

Use :FFT? to query setup information for the FFT subsystem.

Return Format

The following is a sample response from the :FFT? query. In this case, the query was issued following a *RST command.

```
:FFT:DISP 0;SOUR1 CHAN1;RANG +160E+00;OFFS -60.0000E+00;SPAN
+100.0000E+03;CENT +50.000000E+03;WIND HANN;VTYP DEC;DMODE
NORM;AVER:COUN 8
```

:FFT:CENTer

N (see page 828)

Command Syntax

```
:FFT:CENTer <frequency>

<frequency> ::= the current center frequency in NR3 format. The range
                of legal values is from -25 GHz to 25 GHz.
```

The :FFT:CENTer command sets the center frequency when FFT (Fast Fourier Transform) is selected.

Query Syntax

```
:FFT:CENTer?
```

The :FFT:CENTer? query returns the current center frequency in Hertz.

Return Format

```
<frequency><NL>

<frequency> ::= the current center frequency in NR3 format. The range
                of legal values is from -25 GHz to 25 GHz.
```

NOTE After a *RST (Reset) or :AUToscale command, the values returned by the :FFT:CENTer? and :FFT:SPAN? queries depend on the current :TIMebase:RANGe value. Once you change either the :FFT:CENTer or :FFT:SPAN value, they no longer track the :TIMebase:RANGe value.

See Also

- ":FFT:DISPlay" on page 274
- ":FFT:OFFSet" on page 275
- ":FFT:RANGe" on page 276
- ":FFT:REFerence" on page 277
- ":FFT:SCALe" on page 278
- ":FFT:SOURce1" on page 279
- ":FFT:SPAN" on page 280
- ":FFT:VTYPe" on page 281
- ":FFT:WINDow" on page 282

:FFT:DISPlay

(see page 828)

Command Syntax

```
:FFT:DISPlay {{0 | OFF} | {1 | ON}}
```

The :FFT:DISPlay command turns the display of the FFT function on or off.

When ON is selected, the FFT function is calculated and displayed.

When OFF is selected, the FFT function is neither calculated nor displayed.

Query Syntax

```
:FFT:DISPlay?
```

The :FFT:DISPlay? query returns whether the function display is on or off.

Return Format

```
<display><NL>

<display> ::= {0 | 1}
```

See Also

- ":FFT:CENTer" on page 273
- ":FFT:OFFSet" on page 275
- ":FFT:RANGe" on page 276
- ":FFT:REFerence" on page 277
- ":FFT:SCALe" on page 278
- ":FFT:SOURce1" on page 279
- ":FFT:SPAN" on page 280
- ":FFT:VTYPe" on page 281
- ":FFT:WINDow" on page 282

:FFT:OFFSet

(see page 828)

Command Syntax

```
:FFT:OFFSet <offset>

<offset> ::= the value at center screen in NR3 format.
```

The :FFT:OFFSet command specifies the FFT vertical value represented at center screen.

If you set the offset to a value outside of the legal range, the offset value is automatically set to the nearest legal value.

NOTE **The :FFT:OFFSet command is equivalent to the :FFT:REFerence command.**

Query Syntax

```
:FFT:OFFSet?
```

The :FFT:OFFSet? query returns the current offset value for the FFT function.

Return Format

```
<offset><NL>

<offset> ::= the value at center screen in NR3 format.
```

See Also

- ":FFT:CENTer" on page 273
- ":FFT:DISPlay" on page 274
- ":FFT:RANGe" on page 276
- ":FFT:REFerence" on page 277
- ":FFT:SCALe" on page 278
- ":FFT:SOURce1" on page 279
- ":FFT:SPAN" on page 280
- ":FFT:VTYPe" on page 281
- ":FFT:WINDow" on page 282

:FFT:RANGe

(see page 828)

Command Syntax

```
:FFT:RANGe <range>

<range> ::= the full-scale vertical axis value in NR3 format.
```

The :FFT:RANGe command defines the full-scale vertical axis for the FFT function.

Query Syntax

```
:FFT:RANGe?
```

The :FFT:RANGe? query returns the current full-scale range value for the FFT function.

Return Format

```
<range><NL>

<range> ::= the full-scale vertical axis value in NR3 format.
```

See Also

- ":FFT:CENTer" on page 273
- ":FFT:DISPlay" on page 274
- ":FFT:OFFSet" on page 275
- ":FFT:REFerence" on page 277
- ":FFT:SCALe" on page 278
- ":FFT:SOURce1" on page 279
- ":FFT:SPAN" on page 280
- ":FFT:VTYPe" on page 281
- ":FFT:WINDow" on page 282

:FFT:REFerence

N (see page 828)

Command Syntax

```
:FFT:REFerence <level>

<level> ::= the current reference level in NR3 format.
```

The :FFT:REFerence command specifies the FFT vertical value represented at center screen.

If you set the reference level to a value outside of the legal range, the level is automatically set to the nearest legal value.

NOTE **The :FFT:REFerence command is equivalent to the :FFT:OFFSet command.**

Query Syntax

```
:FFT:REFerence?
```

The :FFT:REFerence? query returns the current reference level value for the FFT function.

Return Format

```
<level><NL>

<level> ::= the current reference level in NR3 format.
```

See Also

- ":FFT:CENTer" on page 273
- ":FFT:DISPlay" on page 274
- ":FFT:OFFSet" on page 275
- ":FFT:RANGe" on page 276
- ":FFT:SCALe" on page 278
- ":FFT:SOURce1" on page 279
- ":FFT:SPAN" on page 280
- ":FFT:VTYPe" on page 281
- ":FFT:WINDow" on page 282

:FFT:SCALe

N (see page 828)

Command Syntax

```
:FFT:SCALe <scale_value>[<suffix>]

<scale_value> ::= floating-point value in NR3 format.

<suffix> ::= dB
```

The :FFT:SCALe command sets the vertical scale, or units per division, of the FFT function. Legal values for the scale depend on the selected function.

Query Syntax

```
:FFT:SCALe?
```

The :FFT:SCALe? query returns the current scale value for the FFT function.

Return Format

```
<scale_value><NL>

<scale_value> ::= floating-point value in NR3 format.
```

See Also

- ":FFT:CENTer" on page 273
- ":FFT:DISPlay" on page 274
- ":FFT:OFFSet" on page 275
- ":FFT:RANGe" on page 276
- ":FFT:REFerence" on page 277
- ":FFT:SOURce1" on page 279
- ":FFT:SPAN" on page 280
- ":FFT:VTYPe" on page 281
- ":FFT:WINDow" on page 282

:FFT:SOURce1

N (see page 828)

Command Syntax

```
:FFT:SOURce1 <offset>
<source> ::= {CHANnel<n>}
<n> ::= 1 to (# analog channels) in NR1 format.
```

The :FFT:SOURce1 command selects the source for the FFT function.

NOTE Another shorthand notation for SOURce1 in this command/query (besides SOUR1) is SOUR.

Query Syntax

```
:FFT:SOURce1?
```

The :FFT:SOURce1? query returns the current source1 for the FFT function.

Return Format

```
<source><NL>
<source> ::= {CHAN<n>}
```

See Also

- ":FFT:CENTer" on page 273
- ":FFT:DISPlay" on page 274
- ":FFT:OFFSet" on page 275
- ":FFT:RANGe" on page 276
- ":FFT:REFerence" on page 277
- ":FFT:SCALe" on page 278
- ":FFT:SPAN" on page 280
- ":FFT:VTYPe" on page 281
- ":FFT:WINDow" on page 282

:FFT:SPAN

(see page 828)

Command Syntax

```
:FFT:SPAN <span>

<span> ::= the current frequency span in NR3 format. Legal values are
           1 Hz to 100 GHz.

If you set the frequency span to a value outside of the legal range, the
step size is automatically set to the nearest legal value.
```

The :FFT:SPAN command sets the frequency span of the display (left graticule to right graticule) when FFT (Fast Fourier Transform) is selected.

Query Syntax

```
:FFT:SPAN?
```

The :FFT:SPAN? query returns the current frequency span in Hertz.

NOTE After a *RST (Reset) or :AUToscale command, the values returned by the :FFT:CENTer? and :FFT:SPAN? queries depend on the current :TIMebase:RANGe value. Once you change either the :FFT:CENTer or :FFT:SPAN value, they no longer track the :TIMebase:RANGe value.

Return Format

```
<span><NL>

<span> ::= the current frequency span in NR3 format. Legal values are 1
Hz to 100 GHz.
```

See Also

- ":FFT:CENTer" on page 273
- ":FFT:DISPlay" on page 274
- ":FFT:OFFSet" on page 275
- ":FFT:RANGe" on page 276
- ":FFT:REFerence" on page 277
- ":FFT:SCALe" on page 278
- ":FFT:SOURce1" on page 279
- ":FFT:VTYPe" on page 281
- ":FFT:WINDow" on page 282

:FFT:VTYPe

N (see page 828)

Command Syntax

```
:FFT:VTYPe <units>

<units> ::= {DECibel | VRMS}
```

The :FFT:VTYPe command specifies FFT vertical units as DECibel or VRMS.

Query Syntax

```
:FFT:VTYPe?
```

The :FFT:VTYPe? query returns the current FFT vertical units.

Return Format

```
<units><NL>

<units> ::= {DEC | VRMS}
```

See Also

- ":FFT:CENTer" on page 273
- ":FFT:DISPlay" on page 274
- ":FFT:OFFSet" on page 275
- ":FFT:RANGe" on page 276
- ":FFT:REFerence" on page 277
- ":FFT:SCALe" on page 278
- ":FFT:SOURce1" on page 279
- ":FFT:SPAN" on page 280
- ":FFT:WINDow" on page 282

:FFT:WINDow

N (see page 828)

Command Syntax

```
:FFT:WINDow <window>

<window> ::= {RECTangular | HANNing | FLATtop | BHARris}
```

The :FFT:WINDow command allows the selection of four different windowing transforms or operations for the FFT (Fast Fourier Transform) function.

The FFT operation assumes that the time record repeats. Unless an integral number of sampled waveform cycles exist in the record, a discontinuity is created between the end of one record and the beginning of the next. This discontinuity introduces additional frequency components about the peaks into the spectrum. This is referred to as leakage. To minimize leakage, windows that approach zero smoothly at the start and end of the record are employed as filters to the FFTs. Each window is useful for certain classes of input signals.

- RECTangular – useful for transient signals, and signals where there are an integral number of cycles in the time record.
- HANNing – useful for frequency resolution and general purpose use. It is good for resolving two frequencies that are close together, or for making frequency measurements. This is the default window.
- FLATtop – best for making accurate amplitude measurements of frequency peaks.
- BHARris (Blackman-Harris) – reduces time resolution compared to the rectangular window, but it improves the capacity to detect smaller impulses due to lower secondary lobes (provides minimal spectral leakage).

Query Syntax

```
:FFT:WINDow?
```

The :FFT:WINDow? query returns the value of the window selected for the FFT function.

Return Format

```
<window><NL>

<window> ::= {RECT | HANN | FLAT | BHAR}
```

See Also

- ":FFT:CENTer" on page 273
- ":FFT:DISPlay" on page 274
- ":FFT:OFFSet" on page 275
- ":FFT:RANGe" on page 276
- ":FFT:REFerence" on page 277
- ":FFT:SCALe" on page 278
- ":FFT:SOURce1" on page 279
- ":FFT:SPAN" on page 280

- ":FFT:VTYPe" on page 281

16 :FRANalysis Commands

Control oscilloscope functions associated with the Frequency Response Analysis (FRA) feature, which is available in G-suffix oscilloscope models (that have a built-in waveform generator). See "Introduction to :FRANalysis Commands" on page 286.

Table 62 :FRANalysis Commands Summary

Command	Query	Options and Query Returns
n/a	:FRANalysis:DATA? (see page 287)	<binary_block> ::= comma-separated data with newlines at the end of each row
:FRANalysis:ENABle {{0 | OFF} | {1 | ON}} (see page 288)	:FRANalysis:ENABle? (see page 288)	{0 | 1}
:FRANalysis:FREQuency :MODE <setting> (see page 289)	:FRANalysis:FREQuency :MODE? (see page 289)	<setting> ::= {SWEep | SINGle}
:FRANalysis:FREQuency :SINGle <value>[suffix] (see page 290)	:FRANalysis:FREQuency :SINGle? (see page 290)	<value> ::= between 10 Hz and 20 MHz with a resolution of 0.1 Hz in NR3 format [suffix] ::= {Hz | kHz| MHz}
:FRANalysis:FREQuency :STARt <value>[suffix] (see page 291)	:FRANalysis:FREQuency :STARt? (see page 291)	<value> ::= between 10 Hz and 19.99 MHz with a resolution of 0.1 Hz in NR3 format [suffix] ::= {Hz | kHz| MHz}
:FRANalysis:FREQuency :STOP <value>[suffix] (see page 292)	:FRANalysis:FREQuency :STOP? (see page 292)	<value> ::= between 10.1 Hz and 20 MHz with a resolution of 0.1 Hz in NR3 format [suffix] ::= {Hz | kHz| MHz}
:FRANalysis:RUN (see page 293)	n/a	n/a

Table 62 :FRANalysis Commands Summary (continued)

Command	Query	Options and Query Returns
:FRANalysis:SOURce:INPut <source> (see page 294)	:FRANalysis:SOURce:INPut? (see page 294)	<source> ::= CHANnel<n> <n> ::= 1 to (# analog channels) in NR1 format
:FRANalysis:SOURce:OUTPut <source> (see page 295)	:FRANalysis:SOURce:OUTPut? (see page 295)	<source> ::= CHANnel<n> <n> ::= 1 to (# analog channels) in NR1 format
:FRANalysis:SWEep:POINts <pts> (see page 296)	:FRANalysis:SWEep:POINts? (see page 296)	<pts> ::= number of points from 1 to 1000 in NR1 format
:FRANalysis:TRACe <selection> (see page 297)	:FRANalysis:TRACe? (see page 297)	<selection> ::= {NONE | ALL | GAIN | PHASe}[,{GAIN | PHASe}]
:FRANalysis:WGEN:LOAD <impedance> (see page 298)	:FRANalysis:WGEN:LOAD? (see page 298)	<impedance> ::= {ONEMeg | FIFTy}
:FRANalysis:WGEN:VOLTage <amplitude> (see page 299)	:FRANalysis:WGEN:VOLTage? (see page 299)	<amplitude> ::= amplitude in volts in NR3 format

Introduction to :FRANalysis Commands

The FRANalysis subsystem controls the Frequency Response Analysis feature in the oscilloscope.

The Frequency Response Analysis (FRA) feature controls the built-in waveform generator to sweep a sine wave across a range of frequencies while measuring the input to and output from a device under test (DUT). At each frequency, gain (A) and phase are measured and plotted on a frequency response chart.

Reporting the Setup

Use :FRANalysis? to query setup information for the FRANalysis subsystem.

Return Format

The following is a sample response from the :FRANalysis? query. In this case, the query was issued following a *RST command.

```
:FRAN:SOUR:INP CHAN1;OUTP CHAN2;:FRAN:FREQ:STAR +100E+00;
STOP +20.000000E+06;:FRAN:WGEN:VOLT +200.0E-03;LOAD FIFT
```

:FRANalysis:DATA

(see page 828)

Query Syntax

```
:FRANalysis:DATA?
```

The :FRANalysis:DATA? query returns the frequency response analysis data.

The data is returned in four comma-separated columns of data for each step in the sweep: Frequency (Hz), Amplitude (Vpp), Gain (dB), and Phase (°).

Return Format

```
<binary_block><NL>

<binary_block> ::= comma-separated data with newlines at the end of each
 row
```

See Also

- ":FRANalysis:ENABle" on page 288
- ":FRANalysis:FREQuency:STARt" on page 291
- ":FRANalysis:FREQuency:STOP" on page 292
- ":FRANalysis:RUN" on page 293
- ":FRANalysis:SOURce:INPut" on page 294
- ":FRANalysis:SOURce:OUTPut" on page 295
- ":FRANalysis:TRACe" on page 297
- ":FRANalysis:WGEN:LOAD" on page 298
- ":FRANalysis:WGEN:VOLTage" on page 299

:FRANalysis:ENABle

(see page 828)

Command Syntax

```
:FRANalysis:ENABle <setting>

<setting> ::= {{0 | OFF} | {1 | ON}}
```

The :FRANalysis:ENABle command turns the Frequency Response Analysis (FRA) feature on or off.

Query Syntax

```
:FRANalysis:ENABle?
```

The :FRANalysis:ENABle? query returns a flag indicating whether the Frequency Response Analysis (FRA) feature is on or off.

Return Format

```
<setting><NL>

<setting> ::= {0 | 1}
```

See Also

- ":FRANalysis:DATA" on page 287
- ":FRANalysis:FREQuency:STARt" on page 291
- ":FRANalysis:FREQuency:STOP" on page 292
- ":FRANalysis:RUN" on page 293
- ":FRANalysis:SOURce:INPut" on page 294
- ":FRANalysis:SOURce:OUTPut" on page 295
- ":FRANalysis:WGEN:LOAD" on page 298
- ":FRANalysis:WGEN:VOLTage" on page 299

:FRANalysis:FREQuency:MODE

N (see page 828)

Command Syntax

```
:FRANalysis:FREQuency:MODE <setting>

<setting> ::= {SWEep | SINGle}
```

The :FRANalysis:FREQuency:MODE command lets you select between the normal swept frequency response analysis or analysis at a single frequency, which can be useful when debugging.

NOTE The SINGle mode is available through the remote programming interface only and is not available when using the front panel graphical user interface (GUI).

Query Syntax

```
:FRANalysis:FREQuency:MODE?
```

The :FRANalysis:FREQuency:MODE? query returns the frequency mode setting.

Return Format

```
<setting><NL>

<setting> ::= {SWEep | SINGle}
```

See Also

- ":FRANalysis:RUN" on page 293
- ":FRANalysis:FREQuency:SINGle" on page 290
- ":FRANalysis:FREQuency:STARt" on page 291
- ":FRANalysis:FREQuency:STOP" on page 292
- ":FRANalysis:SWEep:POINts" on page 296

:FRANalysis:FREQuency:SINGle

(see page 828)

Command Syntax

```
:FRANalysis:FREQuency:SINGle <value>[suffix]

<value> ::= between 10 Hz and 20 MHz with a resolution of 0.1 Hz
   in NR3 format

[suffix] ::= {Hz | kHz| MHz}
```

The :FRANalysis:FREQuency:SINGle command command sets the single frequency value.

NOTE The SINGle mode is available through the remote programming interface only and is not available when using the front panel graphical user interface (GUI).

Query Syntax

```
:FRANalysis:FREQuency:SINGle?
```

The :FRANalysis:FREQuency:SINGle? query returns the single frequency setting.

Return Format

```
<value><NL>
```

See Also

- ":FRANalysis:DATA" on page 287
- ":FRANalysis:ENABle" on page 288
- ":FRANalysis:SWEep:POINts" on page 296
- ":FRANalysis:FREQuency:MODE" on page 289
- ":FRANalysis:RUN" on page 293
- ":FRANalysis:SOURce:INPut" on page 294
- ":FRANalysis:SOURce:OUTPut" on page 295
- ":FRANalysis:WGEN:LOAD" on page 298
- ":FRANalysis:WGEN:VOLTage" on page 299

:FRANalysis:FREQuency:STARt

(see page 828)

Command Syntax

```
:FRANalysis:FREQuency:STARt <value>[suffix]

<value> ::= between 10 Hz and 19.99 MHz with a resolution of 0.1 Hz
   in NR3 format

[suffix] ::= {Hz | kHz| MHz}
```

The :FRANalysis:FREQuency:STARt command command sets the frequency sweep start value.

Query Syntax

```
:FRANalysis:FREQuency:STARt?
```

The :FRANalysis:FREQuency:STARt? query returns the frequency sweep start setting.

Return Format

```
<value><NL>
```

See Also

- ":FRANalysis:DATA" on page 287
- ":FRANalysis:ENABle" on page 288
- ":FRANalysis:FREQuency:STOP" on page 292
- ":FRANalysis:SWEep:POINts" on page 296
- ":FRANalysis:FREQuency:MODE" on page 289
- ":FRANalysis:RUN" on page 293
- ":FRANalysis:SOURce:INPut" on page 294
- ":FRANalysis:SOURce:OUTPut" on page 295
- ":FRANalysis:WGEN:LOAD" on page 298
- ":FRANalysis:WGEN:VOLTage" on page 299

:FRANalysis:FREQuency:STOP

(see page 828)

Command Syntax

```
:FRANalysis:FREQuency:STOP <value>[suffix]

<value> ::= between 10.1 Hz and 20 MHz with a resolution of 0.1 Hz
   in NR3 format

[suffix] ::= {Hz | kHz| MHz}
```

The :FRANalysis:FREQuency:STOP command sets the frequency sweep stop value.

Query Syntax

```
:FRANalysis:FREQuency:STOP?
```

The :FRANalysis:FREQuency:STOP? query returns the frequency sweep stop setting.

Return Format

```
<value><NL>
```

See Also

- ":FRANalysis:DATA" on page 287
- ":FRANalysis:ENABle" on page 288
- ":FRANalysis:FREQuency:STARt" on page 291
- ":FRANalysis:SWEep:POINts" on page 296
- ":FRANalysis:FREQuency:MODE" on page 289
- ":FRANalysis:RUN" on page 293
- ":FRANalysis:SOURce:INPut" on page 294
- ":FRANalysis:SOURce:OUTPut" on page 295
- ":FRANalysis:WGEN:LOAD" on page 298
- ":FRANalysis:WGEN:VOLTage" on page 299

:FRANalysis:RUN

N (see page 828)

Command Syntax `:FRANalysis:RUN`

The :FRANalysis:RUN command performs the Frequency Response Analysis. This analysis controls the built-in waveform generator to sweep a sine wave across a range of frequencies while measuring the input to and output from a device under test (DUT). At each frequency, gain (A) and phase are measured and plotted on a Bode frequency response chart.

The :FRANalysis:APPLy command is a valid compatible alias for the :FRANalysis:RUN command.

When the frequency response analysis completes, you can use the :FRANalysis:DATA? query to get four comma-separated columns of data for each step in the sweep: Frequency (Hz), Amplitude (Vpp), Gain (dB), and Phase (°).

It takes some time for the frequency sweep analysis to complete. You can query bit 0 of the Standard Event Status Register (*ESR?) to find out when the analysis is complete.

See Also

- ":FRANalysis:DATA" on page 287
- ":FRANalysis:ENABle" on page 288
- ":FRANalysis:FREQuency:MODE" on page 289
- ":FRANalysis:FREQuency:SINGle" on page 290
- ":FRANalysis:FREQuency:STARt" on page 291
- ":FRANalysis:FREQuency:STOP" on page 292
- ":FRANalysis:SOURce:INPut" on page 294
- ":FRANalysis:SOURce:OUTPut" on page 295
- ":FRANalysis:TRACe" on page 297
- ":FRANalysis:WGEN:LOAD" on page 298
- ":FRANalysis:WGEN:VOLTage" on page 299
- "*ESR (Standard Event Status Register)" on page 124

:FRANalysis:SOURce:INPut

(see page 828)

Command Syntax

```
:FRANalysis:SOURce:INPut <source>

<source> ::= CHANnel<n>

<n> ::= 1 to (# analog channels) in NR1 format
```

The :FRANalysis:SOURce:INPut command specifies the analog input channel that is probing the input voltage to the device under test (DUT) in the frequency response analysis.

Query Syntax

```
:FRANalysis:SOURce:INPut?
```

The :FRANalysis:SOURce:INPut? query returns the currently selected channel probing the input voltage.

Return Format

```
<source><NL>

<source> ::= CHAN<n>
```

See Also

- ":FRANalysis:DATA" on page 287
- ":FRANalysis:ENABle" on page 288
- ":FRANalysis:FREQuency:STARt" on page 291
- ":FRANalysis:FREQuency:STOP" on page 292
- ":FRANalysis:RUN" on page 293
- ":FRANalysis:SOURce:OUTPut" on page 295
- ":FRANalysis:WGEN:LOAD" on page 298
- ":FRANalysis:WGEN:VOLTage" on page 299

:FRANalysis:SOURce:OUTPut

(see page 828)

Command Syntax

```
:FRANalysis:SOURce:OUTPut <source>

<source> ::= CHANnel<n>

<n> ::= 1 to (# analog channels) in NR1 format
```

The :FRANalysis:SOURce:OUTPut command specifies the analog input channel that is probing the output voltage from the device under test (DUT) in the frequency response analysis.

Query Syntax

```
:FRANalysis:SOURce:OUTPut?
```

The :FRANalysis:SOURce:OUTPut? query returns the currently selected channel probing the output voltage.

Return Format

```
<source><NL>

<source> ::= CHAN<n>
```

See Also

- ":FRANalysis:DATA" on page 287
- ":FRANalysis:ENABle" on page 288
- ":FRANalysis:FREQuency:STARt" on page 291
- ":FRANalysis:FREQuency:STOP" on page 292
- ":FRANalysis:RUN" on page 293
- ":FRANalysis:SOURce:INPut" on page 294
- ":FRANalysis:WGEN:LOAD" on page 298
- ":FRANalysis:WGEN:VOLTage" on page 299

:FRANalysis:SWEep:POINts

(see page 828)

Command Syntax

```
:FRANalysis:SWEep:POINts <pts>

<pts> ::= number of points from 1 to 1000 in NR1 format
```

The :FRANalysis:SWEep:POINts command specifies the total number of points in the frequency response analysis.

Query Syntax

```
:FRANalysis:SWEep:POINts?
```

The :FRANalysis:SWEep:POINts? query returns the number of points setting.

Return Format

```
<pts><NL>
```

See Also

- ":FRANalysis:FREQuency:STARt" on page 291
- ":FRANalysis:FREQuency:STOP" on page 292

:FRANalysis:TRACe

(see page 828)

Command Syntax

```
:FRANalysis:TRACe <selection>

<selection> ::= {NONE | ALL | GAIN | PHASe}[,{GAIN | PHASe}]
```

The :FRANalysis:TRACe command specifies whether to include gain, phase, both gain and phase, or neither in the frequency response analysis results.

NOTE This command affects the oscilloscope's front panel graphical user interface (plot and table) as well as when saving analysis data.

Query Syntax

```
:FRANalysis:TRACe?
```

The :FRANalysis:TRACe? query returns a comma-separated list of the types of data that are currently included in the frequency response analysis results, or "NONE" if neither gain nor phase data is included.

Return Format

```
<selection_list><NL>

<selection_list> ::= {"NONE" | "GAIN" | "PHASe" | "GAIN,PHASe"}
```

See Also

- ":FRANalysis:RUN" on page 293
- ":FRANalysis:DATA" on page 287

:FRANalysis:WGEN:LOAD

(see page 828)

Command Syntax

```
:FRANalysis:WGEN:LOAD <impedance>

<impedance> ::= {ONEMeg | FIFTy}
```

The :FRANalysis:WGEN:LOAD command selects the expected output load impedance.

The output impedance of the Gen Out BNC is fixed at 50 ohms. However, the output load selection lets the waveform generator display the correct amplitude and offset levels for the expected output load.

If the actual load impedance is different than the selected value, the displayed amplitude and offset levels will be incorrect.

Query Syntax

```
:FRANalysis:WGEN:LOAD?
```

The :FRANalysis:WGEN:LOAD? query returns the current expected output load impedance.

Return Format

```
<impedance><NL>

<impedance> ::= {ONEM | FIFT}
```

See Also

- ":FRANalysis:DATA" on page 287
- ":FRANalysis:ENABle" on page 288
- ":FRANalysis:FREQuency:STARt" on page 291
- ":FRANalysis:FREQuency:STOP" on page 292
- ":FRANalysis:RUN" on page 293
- ":FRANalysis:SOURce:INPut" on page 294
- ":FRANalysis:SOURce:OUTPut" on page 295
- ":FRANalysis:WGEN:VOLTage" on page 299

:FRANalysis:WGEN:VOLTage

(see page 828)

Command Syntax

```
:FRANalysis:WGEN:VOLTage <amplitude>

<amplitude> ::= amplitude in volts in NR3 format
```

The :FRANalysis:WGEN:VOLTage command specifies the waveform generator's output sine wave amplitude.

Use the :WGEN:VOLTage:OFFSet command to specify the offset voltage or DC level.

You can also specify the amplitude and offset indirectly using the :WGEN:VOLTage:HIGH and :WGEN:VOLTage:LOW commands. For example, an amplitude of 5 V and an offset of 1 V is the same as a high-level voltage of 4 V and a low-level voltage of -1 V.

Query Syntax

```
:FRANalysis:WGEN:VOLTage?
```

The :FRANalysis:WGEN:VOLTage? query returns the currently specified waveform generator amplitude.

Return Format

```
<amplitude><NL>

<amplitude> ::= amplitude in volts in NR3 format
```

See Also

- ":FRANalysis:DATA" on page 287
- ":FRANalysis:ENABle" on page 288
- ":FRANalysis:FREQuency:STARt" on page 291
- ":FRANalysis:FREQuency:STOP" on page 292
- ":FRANalysis:SWEep:POINts" on page 296
- ":FRANalysis:RUN" on page 293
- ":FRANalysis:SOURce:INPut" on page 294
- ":FRANalysis:SOURce:OUTPut" on page 295
- ":FRANalysis:WGEN:LOAD" on page 298

17 :FUNCtion Commands

Control functions in the measurement/storage module. See "Introduction to :FUNCtion Commands" on page 303.

Table 63 :FUNCtion Commands Summary

Command	Query	Options and Query Returns
:FUNCtion:DISPlay {{0 | OFF} | {1 | ON}} (see page 304)	:FUNCtion:DISPlay? (see page 304)	{0 | 1}
:FUNCtion[:FFT]:CENTer <frequency> (see page 305)	:FUNCtion[:FFT]:CENTer? (see page 305)	<frequency> ::= the current center frequency in NR3 format. The range of legal values is from 0 Hz to 25 GHz.
:FUNCtion[:FFT]:PHASe :REFerence <ref_point> (see page 306)	:FUNCtion[:FFT]:PHASe :REFerence? (see page 306)	<ref_point> ::= {TRIGger | DISPlay}
:FUNCtion[:FFT]:SPAN (see page 307)	:FUNCtion[:FFT]:SPAN? (see page 307)	::= the current frequency span in NR3 format. Legal values are 1 Hz to 100 GHz.
:FUNCtion[:FFT]:VTYPe <units> (see page 308)	:FUNCtion[:FFT]:VTYPe? (see page 308)	<units> ::= {DECibel | VRMS} for the FFT (magnitude) operation <units> ::= {DEGRees | RADians} for the FFTPhase operation
:FUNCtion[:FFT]:WINDow <window> (see page 309)	:FUNCtion[:FFT]:WINDow? (see page 309)	<window> ::= {RECTangular | HANNing | FLATtop | BHARris}
:FUNCtion:FREQuency:LOWPass <3dB_freq> (see page 310)	:FUNCtion:FREQuency:LOWPass? (see page 310)	<3dB_freq> ::= 3dB cutoff frequency value in NR3 format
:FUNCtion:GOFT:OPERation <operation> (see page 311)	:FUNCtion:GOFT:OPERation? (see page 311)	<operation> ::= {ADD | SUBTract | MULTiply}

Table 63 :FUNCtion Commands Summary (continued)

Command	Query	Options and Query Returns
:FUNCtion:GOFT:SOURce1 <source> (see page 312)	:FUNCtion:GOFT:SOURce1? (see page 312)	<source> ::= CHANnel<n> <n> ::= 1 to (# analog channels) in NR1 format
:FUNCtion:GOFT:SOURce2 <source> (see page 313)	:FUNCtion:GOFT:SOURce2? (see page 313)	<source> ::= CHANnel<n> <n> ::= 1 to (# analog channels) in NR1 format
:FUNCtion:OFFSet <offset> (see page 314)	:FUNCtion:OFFSet? (see page 314)	<offset> ::= the value at center screen in NR3 format. The range of legal values is +/-10 times the current sensitivity of the selected function.
:FUNCtion:OPERation <operation> (see page 315)	:FUNCtion:OPERation? (see page 315)	<operation> ::= {ADD | SUBTract | MULTiply | DIVide | FFT | FFTPhase | LOWPass}
:FUNCtion:RANGe <range> (see page 317)	:FUNCtion:RANGe? (see page 317)	<range> ::= the full-scale vertical axis value in NR3 format. The range for ADD, SUBT, MULT is 8E-6 to 800E+3. The range for the FFT function is 8 to 800 dBV.
:FUNCtion:REFerence <level> (see page 318)	:FUNCtion:REFerence? (see page 318)	<level> ::= the value at center screen in NR3 format. The range of legal values is +/-10 times the current sensitivity of the selected function.
:FUNCtion:SCALe <scale value>[<suffix>] (see page 319)	:FUNCtion:SCALe? (see page 319)	<scale value> ::= integer in NR1 format <suffix> ::= {V | dB}
:FUNCtion:SOURce1 <source> (see page 320)	:FUNCtion:SOURce1? (see page 320)	<source> ::= {CHANnel<n> | GOFT} <n> ::= 1 to (# analog channels) in NR1 format GOFT is only for FFT operation.
:FUNCtion:SOURce2 <source> (see page 321)	:FUNCtion:SOURce2? (see page 321)	<source> ::= {CHANnel<n> | NONE} <n> ::= 1 to (# analog channels) in NR1 format, depending on SOURce1 selection

Introduction to :FUNCtion Commands

The FUNCtion subsystem controls the math functions in the oscilloscope. Add, subtract, multiply, and FFT (Fast Fourier Transform) operations are available. These math operations only use the analog (vertical) channels.

The SOURce1, DISPlay, RANGe, and OFFSet commands apply to any function.

The SPAN, CENTer, VTYPe, and WINDow commands are only useful for FFT functions. When FFT is selected, the horizontal cursors change from time to frequency (Hz), and the vertical cursors change from volts to decibel (dB).

Reporting the Setup

Use :FUNCtion? to query setup information for the FUNCtion subsystem.

Return Format

The following is a sample response from the :FUNCtion? queries. In this case, the query was issued following a *RST command.

```
:FUNC:OPER ADD;DISP 0;SOUR1 CHAN1;SOUR2 CHAN2;RANG +8.00E+00;OFFS
+0.0E+00;:FUNC:GOFT:OPER ADD;SOUR1 CHAN1;SOUR2 CHAN2
```

:FUNCtion:DISPlay

(see page 828)

Command Syntax

```
:FUNCtion:DISPlay <display>

<display> ::= {{1 | ON} | {0 | OFF}}
```

The :FUNCtion:DISPlay command turns the display of the function on or off. When ON is selected, the function performs as specified using the other FUNCtion commands. When OFF is selected, function is neither calculated nor displayed.

Query Syntax

```
:FUNCtion:DISPlay?
```

The :FUNCtion:DISPlay? query returns whether the function display is on or off.

Return Format

```
<display><NL>

<display> ::= {1 | 0}
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":VIEW" on page 176
- ":BLANk" on page 152
- ":STATus" on page 173

:FUNCtion[:FFT]:CENTer

(see page 828)

Command Syntax

```
:FUNCtion[:FFT]:CENTer <frequency>

<frequency> ::= the current center frequency in NR3 format.  The range
                of legal values is from 0 Hz to 25 GHz.
```

The :FUNCtion[:FFT]:CENTer command sets the center frequency when FFT (Fast Fourier Transform) is selected.

Query Syntax

```
:FUNCtion[:FFT]:CENTer?
```

The :FUNCtion[:FFT]:CENTer? query returns the current center frequency in Hertz.

Return Format

```
<frequency><NL>

<frequency> ::= the current center frequency in NR3 format.  The range
                of legal values is from 0 Hz to 25 GHz.
```

NOTE After a *RST (Reset) or :AUToscale command, the values returned by the :FUNCtion[:FFT]:CENTer? and :FUNCtion:SPAN? queries depend on the current :TIMebase:RANGe value. Once you change either the :FUNCtion[:FFT]:CENTer or :FUNCtion:SPAN value, they no longer track the :TIMebase:RANGe value.

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion[:FFT]:SPAN" on page 307
- ":TIMebase:RANGe" on page 607
- ":TIMebase:SCALe" on page 609

:FUNCtion[:FFT]:PHASe:REFerence

(see page 828)

Command Syntax

```
:FUNCtion[:FFT]:PHASe:REFerence <ref_point>

<ref_point> ::= {TRIGger | DISPlay}
```

The :FUNCtion[:FFT]:PHASe:REFerence command sets the reference point for calculating the FFT Phase function to either the trigger point or beginning of the displayed waveform.

Query Syntax

```
:FUNCtion[:FFT]:PHASe:REFerence?
```

The :FUNCtion[:FFT]:PHASe:REFerence? query returns the selected reference point.

Return Format

```
<ref_point><NL>

<ref_point> ::= {TRIGger | DISPlay}
```

See Also

- ":FUNCtion:OPERation" on page 315
- "Introduction to :FUNCtion Commands" on page 303

:FUNCtion[:FFT]:SPAN

(see page 828)

Command Syntax

```
:FUNCtion[:FFT]:SPAN <span>

<span> ::= the current frequency span in NR3 format. Legal values are
           1 Hz to 100 GHz.

If you set the frequency span to a value outside of the legal range, the
step size is automatically set to the nearest legal value.
```

The :FUNCtion[:FFT]:SPAN command sets the frequency span of the display (left graticule to right graticule) when FFT (Fast Fourier Transform) is selected.

Query Syntax

```
:FUNCtion[:FFT]:SPAN?
```

The :FUNCtion[:FFT]:SPAN? query returns the current frequency span in Hertz.

NOTE

After a *RST (Reset) or :AUToscale command, the values returned by the :FUNCtion[:FFT]:CENTer? and :FUNCtion:SPAN? queries depend on the current :TIMebase:RANGe value. Once you change either the :FUNCtion[:FFT]:CENTer or :FUNCtion:SPAN value, they no longer track the :TIMebase:RANGe value.

Return Format

```
<span><NL>

<span> ::= the current frequency span in NR3 format. Legal values are 1
Hz to 100 GHz.
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion[:FFT]:CENTer" on page 305
- ":TIMebase:RANGe" on page 607
- ":TIMebase:SCALe" on page 609

:FUNCtion[:FFT]:VTYPe

N (see page 828)

Command Syntax

```
:FUNCtion[:FFT]:VTYPe <units>
<units> ::= {DECibel | VRMS} for the FFT (magnitude) operation
<units> ::= {DEGRees | RADians} for the FFTPhase operation
```

The :FUNCtion[:FFT]:VTYPe command specifies FFT vertical units.

Query Syntax

```
:FUNCtion[:FFT]:VTYPe?
```

The :FUNCtion[:FFT]:VTYPe? query returns the current FFT vertical units.

Return Format

```
<units><NL>
<units> ::= {DEC | VRMS} for the FFT (magnitude) operation
<units> ::= {DEGR | RAD} for the FFTPhase operation
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion:OPERation" on page 315

:FUNCtion[:FFT]:WINDow

N (see page 828)

Command Syntax

```
:FUNCtion[:FFT]:WINDow <window>

<window> ::= {RECTangular | HANNing | FLATtop | BHARris}
```

The :FUNCtion[:FFT]:WINDow command allows the selection of four different windowing transforms or operations for the FFT (Fast Fourier Transform) function.

The FFT operation assumes that the time record repeats. Unless an integral number of sampled waveform cycles exist in the record, a discontinuity is created between the end of one record and the beginning of the next. This discontinuity introduces additional frequency components about the peaks into the spectrum. This is referred to as leakage. To minimize leakage, windows that approach zero smoothly at the start and end of the record are employed as filters to the FFTs. Each window is useful for certain classes of input signals.

- RECTangular – useful for transient signals, and signals where there are an integral number of cycles in the time record.
- HANNing – useful for frequency resolution and general purpose use. It is good for resolving two frequencies that are close together, or for making frequency measurements. This is the default window.
- FLATtop – best for making accurate amplitude measurements of frequency peaks.
- BHARris (Blackman-Harris) – reduces time resolution compared to the rectangular window, but it improves the capacity to detect smaller impulses due to lower secondary lobes (provides minimal spectral leakage).

Query Syntax

```
:FUNCtion[:FFT]:WINDow?
```

The :FUNCtion[:FFT]:WINDow? query returns the value of the window selected for the FFT function.

Return Format

```
<window><NL>

<window> ::= {RECT | HANN | FLAT | BHAR}
```

See Also

- "Introduction to :FUNCtion Commands" on page 303

:FUNCtion:FREQuency:LOWPass

(see page 828)

Command Syntax

```
:FUNCtion:FREQuency:LOWPass <3dB_freq>

<3dB_freq> ::= -3dB cutoff frequency value in NR3 format
```

The :FUNCtion:FREQuency:LOWPass command sets the low-pass filter's -3 dB cutoff frequency.

The low-pass filter is a 4th order Bessel-Thompson filter.

Query Syntax

```
:FUNCtion:FREQuency:LOWPass?
```

The :FUNCtion:FREQuency:LOWPass query returns the low-pass filter's cutoff frequency.

Return Format

```
<3dB_freq><NL>

<3dB_freq> ::= -3dB cutoff frequency value in NR3 format
```

See Also

- ":FUNCtion:OPERation" on page 315

:FUNCtion:GOFT:OPERation

(see page 828)

Command Syntax

```
:FUNCtion:GOFT:OPERation <operation>

<operation> ::= {ADD | SUBTract | MULTiply}
```

The :FUNCtion:GOFT:OPERation command sets the math operation for the g(t) source that can be used as the input to the FFT function:

- ADD – Source1 + source2.
- SUBTract – Source1 - source2.
- MULTiply – Source1 * source2.

The :FUNCtion:GOFT:SOURce1 and :FUNCtion:GOFT:SOURce2 commands are used to select source1 and source2.

Query Syntax

```
:FUNCtion:GOFT:OPERation?
```

The :FUNCtion:GOFT:OPERation? query returns the current g(t) source operation setting.

Return Format

```
<operation><NL>

<operation> ::= {ADD | SUBT | MULT}
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion:GOFT:SOURce1" on page 312
- ":FUNCtion:GOFT:SOURce2" on page 313
- ":FUNCtion:SOURce1" on page 320

:FUNCtion:GOFT:SOURce1

(see page 828)

Command Syntax

```
:FUNCtion:GOFT:SOURce1 <value>

<value> ::= CHANnel<n>

<n> ::= 1 to (# analog channels) in NR1 format
```

The :FUNCtion:GOFT:SOURce1 command selects the first input channel for the g(t) source that can be used as the input to the FFT function.

Query Syntax

```
:FUNCtion:GOFT:SOURce1?
```

The :FUNCtion:GOFT:SOURce1? query returns the current selection for the first input channel for the g(t) source.

Return Format

```
<value><NL>

<value> ::= CHAN<n>

<n> ::= 1 to (# analog channels) in NR1 format
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion:GOFT:SOURce2" on page 313
- ":FUNCtion:GOFT:OPERation" on page 311

:FUNCtion:GOFT:SOURce2

(see page 828)

Command Syntax

```
:FUNCtion:GOFT:SOURce2 <value>

<value> ::= CHANnel<n>

<n> ::= 1 to (# analog channels) in NR1 format
```

The :FUNCtion:GOFT:SOURce2 command selects the second input channel for the g(t) source that can be used as the input to the FFT function.

Query Syntax

```
:FUNCtion:GOFT:SOURce2?
```

The :FUNCtion:GOFT:SOURce2? query returns the current selection for the second input channel for the g(t) source.

Return Format

```
<value><NL>

<value> ::= CHAN<n>

<n> ::= 1 to (# analog channels) in NR1 format
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion:GOFT:SOURce1" on page 312
- ":FUNCtion:GOFT:OPERation" on page 311

:FUNCtion:OFFSet

(see page 828)

Command Syntax

```
:FUNCtion:OFFSet <offset>

<offset> ::= the value at center screen in NR3 format.
```

The :FUNCtion:OFFSet command sets the voltage or vertical value represented at center screen for the selected function. The range of legal values is generally +/-10 times the current scale of the selected function, but will vary by function. If you set the offset to a value outside of the legal range, the offset value is automatically set to the nearest legal value.

NOTE **The :FUNCtion:OFFset command is equivalent to the :FUNCtion:REFerence command.**

Query Syntax

```
:FUNCtion:OFFSet?
```

The :FUNCtion:OFFSet? query outputs the current offset value for the selected function.

Return Format

```
<offset><NL>

<offset> ::= the value at center screen in NR3 format.
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion:RANGe" on page 317
- ":FUNCtion:REFerence" on page 318
- ":FUNCtion:SCALe" on page 319

:FUNCtion:OPERation

N (see page 828)

Command Syntax

```
:FUNCtion:OPERation <operation>

<operation> ::= {ADD | SUBTract | MULTiply | DIVide | FFT
   | FFTPhase | LOWPass}
```

The :FUNCtion:OPERation command sets the desired waveform math operation:

- ADD – Source1 + source2.
- SUBTract – Source1 - source2.
- MULTiply – Source1 * source2.
- DIVide – Source1 / source2.
- FFT (magnitude) – Using the Fast Fourier Transform (FFT), this operation displays the magnitudes of the frequency content that makes up the source waveform. The FFT takes the digitized time record of the specified source and transforms it to the frequency domain.

  The SPAN, CENTer, VTYPe, and WINDow commands are used for FFT functions. When FFT is selected, the horizontal cursors change from time to frequency (Hz), and the vertical cursors change from volts to decibels or V RMS.
- FFTPhase – Using the Fast Fourier Transform (FFT), this operation shows the phase relationships of the frequency content that makes up the source waveform. The FFT takes the digitized time record of the specified source and transforms it to the frequency domain.

  The SPAN, CENTer, VTYPe, and WINDow commands are used for FFT functions. When FFTPhase is selected, the horizontal cursors change from time to frequency (Hz), and the vertical cursors change from volts to degrees or radians.
- LOWPass – Low pass filter – The FREQuency:LOWPass command sets the -3 dB cutoff frequency.

When the operation is ADD, SUBTract, MULTiply, or DIVide, the :FUNCtion:SOURce1 and :FUNCtion:SOURce2 commands are used to select source1 and source2. For FFT, the :FUNCtion:SOURce1 command selects the waveform source.

Query Syntax

```
:FUNCtion:OPERation?
```

The :FUNCtion:OPERation? query returns the current operation for the selected function.

Return Format

```
<operation><NL>

<operation> ::= {ADD | SUBT | MULT | DIV | FFT | FFTP | LOWP}
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion:SOURce1" on page 320
- ":FUNCtion:SOURce2" on page 321

:FUNCtion:RANGe

(see page 828)

Command Syntax

```
:FUNCtion:RANGe <range>

<range> ::= the full-scale vertical axis value in NR3 format.
```

The :FUNCtion:RANGe command defines the full-scale vertical axis for the selected function.

Query Syntax

```
:FUNCtion:RANGe?
```

The :FUNCtion:RANGe? query returns the current full-scale range value for the selected function.

Return Format

```
<range><NL>

<range> ::= the full-scale vertical axis value in NR3 format.
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion:SCALe" on page 319

:FUNCtion:REFerence

(see page 828)

Command Syntax

```
:FUNCtion:REFerence <level>

<level> ::= the current reference level in NR3 format.
```

The :FUNCtion:REFerence command sets the voltage or vertical value represented at center screen for the selected function. The range of legal values is generally +/-10 times the current scale of the selected function, but will vary by function. If you set the reference level to a value outside of the legal range, the level is automatically set to the nearest legal value.

NOTE The FUNCtion:REFerence command is equivalent to the :FUNCtion:OFFSet command.

Query Syntax

```
:FUNCtion:REFerence?
```

The :FUNCtion:REFerence? query outputs the current reference level value for the selected function.

Return Format

```
<level><NL>

<level> ::= the current reference level in NR3 format.
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion:OFFSet" on page 314
- ":FUNCtion:RANGe" on page 317
- ":FUNCtion:SCALe" on page 319

:FUNCtion:SCALe

(see page 828)

Command Syntax

```
:FUNCtion:SCALe <scale value>[<suffix>]

<scale value> ::= integer in NR1 format

<suffix> ::= {V | dB}
```

The :FUNCtion:SCALe command sets the vertical scale, or units per division, of the selected function. Legal values for the scale depend on the selected function.

Query Syntax

```
:FUNCtion:SCALe?
```

The :FUNCtion:SCALe? query returns the current scale value for the selected function.

Return Format

```
<scale value><NL>

<scale value> ::= integer in NR1 format
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion:RANGe" on page 317

:FUNCtion:SOURce1

(see page 828)

Command Syntax

```
:FUNCtion:SOURce1 <value>

<value> ::= {CHANnel<n> | GOFT}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :FUNCtion:SOURce1 command is used for any :FUNCtion:OPERation selection (including the ADD, SUBTract, or MULTiply channel math operations and the FFT transform). This command selects the first source for channel math operations or the single source for the transforms.

The GOFT parameter is only available for the FFT function. It lets you specify, as the function input source, the addition, subtraction, or multiplication of two channels. When GOFT is used, the g(t) source is specified by the :FUNCtion:GOFT:OPERation, :FUNCtion:GOFT:SOURce1, and :FUNCtion:GOFT:SOURce2 commands.

NOTE Another shorthand notation for SOURce1 in this command/query (besides SOUR1) is SOUR.

Query Syntax

```
:FUNCtion:SOURce1?
```

The :FUNCtion:SOURce1? query returns the current source1 for function operations.

Return Format

```
<value><NL>

<value> ::= {CHAN<n> | GOFT}

<n> ::= 1 to (# analog channels) in NR1 format
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion:OPERation" on page 315
- ":FUNCtion:GOFT:OPERation" on page 311
- ":FUNCtion:GOFT:SOURce1" on page 312
- ":FUNCtion:GOFT:SOURce2" on page 313

:FUNCtion:SOURce2

(see page 828)

Command Syntax

```
:FUNCtion:SOURce2 <value>

<value> ::= {CHANnel<n> | NONE}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :FUNCtion:SOURce2 command specifies the second source for math operations that have two sources (see the :FUNCtion:OPERation command), in other words, ADD, SUBTract, or MULTiply. (The :FUNCtion:SOURce1 command specifies the first source.)

If CHANnel1 or CHANnel2 is selected for :FUNCtion:SOURce1, the SOURce2 selection can be CHANnel1 or CHANnel2.

The :FUNCtion:SOURce2 setting is not used when the :FUNCtion:OPERation is FFT (Fast Fourier Transform).

Query Syntax

```
:FUNCtion:SOURce2?
```

The :FUNCtion:SOURce2? query returns the currently specified second source for math operations.

Return Format

```
<value><NL>

<value> ::= {CHAN<n> | NONE}

<n> ::= 1 to (# analog channels) in NR1 format
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion:OPERation" on page 315
- ":FUNCtion:SOURce1" on page 320

18 :HARDcopy Commands

Set and query the selection of hardcopy device and formatting options. See "Introduction to :HARDcopy Commands" on page 324.

Table 64 :HARDcopy Commands Summary

Command	Query	Options and Query Returns
:HARDcopy:AREA <area> (see page 325)	:HARDcopy:AREA? (see page 325)	<area> ::= SCReen
:HARDcopy:APRinter <active_printer> (see page 326)	:HARDcopy:APRinter? (see page 326)	<active_printer> ::= {<index> | <name>} <index> ::= integer index of printer in list <name> ::= name of printer in list
:HARDcopy:FACTors {{0 | OFF} | {1 | ON}} (see page 327)	:HARDcopy:FACTors? (see page 327)	{0 | 1}
:HARDcopy:FFEed {{0 | OFF} | {1 | ON}} (see page 328)	:HARDcopy:FFEed? (see page 328)	{0 | 1}
:HARDcopy:INKSaver {{0 | OFF} | {1 | ON}} (see page 329)	:HARDcopy:INKSaver? (see page 329)	{0 | 1}
:HARDcopy:LAYout <layout> (see page 330)	:HARDcopy:LAYout? (see page 330)	<layout> ::= {LANDscape | PORTrait}
:HARDcopy:NETWork:ADDRess <address> (see page 331)	:HARDcopy:NETWork:ADDRess? (see page 331)	<address> ::= quoted ASCII string
:HARDcopy:NETWork:APPLy (see page 332)	n/a	n/a

Table 64 :HARDcopy Commands Summary (continued)

Command	Query	Options and Query Returns
:HARDcopy:NETWork:SLOT <slot> (see page 333)	:HARDcopy:NETWork:SLOT? (see page 333)	<slot> ::= {NET0 | NET1}
:HARDcopy:PALette <palette> (see page 334)	:HARDcopy:PALette? (see page 334)	<palette> ::= {COLor | GRAYscale | NONE}
n/a	:HARDcopy:PRINter:LIST? (see page 335)	<list> ::= [<printer_spec>] ... [printer_spec>] <printer_spec> ::= "<index>,<active>,<name>;" <index> ::= integer index of printer <active> ::= {Y | N} <name> ::= name of printer
:HARDcopy:STARt (see page 336)	n/a	n/a

Introduction to :HARDcopy Commands

The HARDcopy subsystem provides commands to set and query the selection of hardcopy device and formatting options such as inclusion of instrument settings (FACTors) and generation of formfeed (FFEed).

:HARDC is an acceptable short form for :HARDcopy.

Reporting the Setup

Use :HARDcopy? to query setup information for the HARDcopy subsystem.

Return Format

The following is a sample response from the :HARDcopy? query. In this case, the query was issued following the *RST command.

```
:HARD:APR "";AREA SCR;FACT 0;FFE 0;INKS 1;PAL NONE;LAY PORT
```

:HARDcopy:AREA

(see page 828)

Command Syntax

```
:HARDcopy:AREA <area>

<area> ::= SCReen
```

The :HARDcopy:AREA command controls what part of the display area is printed. Currently, the only legal choice is SCReen.

Query Syntax

```
:HARDcopy:AREA?
```

The :HARDcopy:AREA? query returns the selected display area.

Return Format

```
<area><NL>

<area> ::= SCR
```

See Also

- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:STARt" on page 336
- ":HARDcopy:APRinter" on page 326
- ":HARDcopy:PRINter:LIST" on page 335
- ":HARDcopy:FACTors" on page 327
- ":HARDcopy:FFEed" on page 328
- ":HARDcopy:INKSaver" on page 329
- ":HARDcopy:LAYout" on page 330
- ":HARDcopy:PALette" on page 334

:HARDcopy:APRinter

(see page 828)

Command Syntax

```
:HARDcopy:APRinter <active_printer>

<active_printer> ::= {<index> | <name>}

<index> ::= integer index of printer in list

<name> ::= name of printer in list
```

The :HARDcopy:APRinter command sets the active printer.

Query Syntax

```
:HARDcopy:APRinter?
```

The :HARDcopy:APRinter? query returns the name of the active printer.

Return Format

```
<name><NL>

<name> ::= name of printer in list
```

See Also

- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:PRINter:LIST" on page 335
- ":HARDcopy:STARt" on page 336

:HARDcopy:FACTors

N (see page 828)

Command Syntax

```
:HARDcopy:FACTors <factors>

<factors> ::= {{OFF | 0} | {ON | 1}}
```

The HARDcopy:FACTors command controls whether the scale factors are output on the hardcopy dump.

Query Syntax

```
:HARDcopy:FACTors?
```

The :HARDcopy:FACTors? query returns a flag indicating whether oscilloscope instrument settings are output on the hardcopy.

Return Format

```
<factors><NL>

<factors> ::= {0 | 1}
```

See Also

- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:STARt" on page 336
- ":HARDcopy:FFEed" on page 328
- ":HARDcopy:INKSaver" on page 329
- ":HARDcopy:LAYout" on page 330
- ":HARDcopy:PALette" on page 334

:HARDcopy:FFEed

N (see page 828)

Command Syntax

```
:HARDcopy:FFEed <ffeed>

<ffeed> ::= {{OFF | 0} | {ON | 1}}
```

The HARDcopy:FFEed command controls whether a formfeed is output between the screen image and factors of a hardcopy dump.

Query Syntax

```
:HARDcopy:FFEed?
```

The :HARDcopy:FFEed? query returns a flag indicating whether a formfeed is output at the end of the hardcopy dump.

Return Format

```
<ffeed><NL>

<ffeed> ::= {0 | 1}
```

See Also

- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:STARt" on page 336
- ":HARDcopy:FACTors" on page 327
- ":HARDcopy:INKSaver" on page 329
- ":HARDcopy:LAYout" on page 330
- ":HARDcopy:PALette" on page 334

:HARDcopy:INKSaver

(see page 828)

Command Syntax

```
:HARDcopy:INKSaver <value>

<value> ::= {{OFF | 0} | {ON | 1}}
```

The HARDcopy:INKSaver command controls whether the graticule colors are inverted or not.

Query Syntax

```
:HARDcopy:INKSaver?
```

The :HARDcopy:INKSaver? query returns a flag indicating whether graticule colors are inverted or not.

Return Format

```
<value><NL>

<value> ::= {0 | 1}
```

See Also

- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:STARt" on page 336
- ":HARDcopy:FACTors" on page 327
- ":HARDcopy:FFEed" on page 328
- ":HARDcopy:LAYout" on page 330
- ":HARDcopy:PALette" on page 334

:HARDcopy:LAYout

N (see page 828)

Command Syntax

```
:HARDcopy:LAYout <layout>

<layout> ::= {LANDscape | PORTrait}
```

The :HARDcopy:LAYout command sets the hardcopy layout mode.

Query Syntax

```
:HARDcopy:LAYout?
```

The :HARDcopy:LAYout? query returns the selected hardcopy layout mode.

Return Format

```
<layout><NL>

<layout> ::= {LAND | PORT}
```

See Also

- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:STARt" on page 336
- ":HARDcopy:FACTors" on page 327
- ":HARDcopy:PALette" on page 334
- ":HARDcopy:FFEed" on page 328
- ":HARDcopy:INKSaver" on page 329

:HARDcopy:NETWork:ADDRess

(see page 828)

Command Syntax

```
:HARDcopy:NETWork:ADDRess <address>

<address> ::= quoted ASCII string
```

The :HARDcopy:NETWork:ADDRess command sets the address for a network printer slot.

The address is the printer or print server's address in one of the following formats:

- IP address of a network-enabled printer (for example: 192.168.1.100 or 192.168.1.100:650). Optionally, a non-standard port number can be specified following a colon.
- IP address of a print server followed by the path to the printer (for example: 192.168.1.100/printers/printer-name or 192.168.1.100:650/printers/printer-name).

The network printer slot is selected by the :HARDcopy:NETWork:SLOT command.

To apply the entered address, use the :HARDcopy:NETWork:APPLy command.

Query Syntax

```
:HARDcopy:NETWork:ADDRess?
```

The :HARDcopy:NETWork:ADDRess? query returns the specified address for the currently selected network printer slot.

Return Format

```
<address><NL>

<address> ::= quoted ASCII string
```

See Also

- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:NETWork:SLOT" on page 333
- ":HARDcopy:NETWork:APPLy" on page 332

:HARDcopy:NETWork:APPLy

(see page 828)

Command Syntax `:HARDcopy:NETWork:APPLy`

The :HARDcopy:NETWork:APPLy command applies the network printer settings and makes the printer connection.

See Also

- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:NETWork:SLOT" on page 333
- ":HARDcopy:NETWork:ADDRess" on page 331

:HARDcopy:NETWork:SLOT

(see page 828)

Command Syntax

```
:HARDcopy:NETWork:SLOT <slot>

<slot> ::= {NET0 | NET1}
```

The :HARDcopy:NETWork:SLOT command selects the network printer slot used for the address and apply commands. There are two network printer slots to choose from.

Query Syntax

```
:HARDcopy:NETWork:SLOT?
```

The :HARDcopy:NETWork:SLOT? query returns the currently selected network printer slot.

Return Format

```
<slot><NL>

<slot> ::= {NET0 | NET1}
```

See Also

- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:NETWork:APPLy" on page 332
- ":HARDcopy:NETWork:ADDRess" on page 331

:HARDcopy:PALette

N (see page 828)

Command Syntax

```
:HARDcopy:PALette <palette>

<palette> ::= {COLor | GRAYscale | NONE}
```

The :HARDcopy:PALette command sets the hardcopy palette color.

The oscilloscope's print driver cannot print color images to color laser printers, so the COLor option is not available when connected to laser printers.

Query Syntax

```
:HARDcopy:PALette?
```

The :HARDcopy:PALette? query returns the selected hardcopy palette color.

Return Format

```
<palette><NL>

<palette> ::= {COL | GRAY | NONE}
```

See Also

- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:STARt" on page 336
- ":HARDcopy:FACTors" on page 327
- ":HARDcopy:LAYout" on page 330
- ":HARDcopy:FFEed" on page 328
- ":HARDcopy:INKSaver" on page 329

:HARDcopy:PRINter:LIST

N (see page 828)

Query Syntax `:HARDcopy:PRINter:LIST?`

The :HARDcopy:PRINter:LIST? query returns a list of available printers. The list can be empty.

Return Format

```
<list><NL>

<list> ::= [<printer_spec>] ... [printer_spec>]

<printer_spec> ::= "<index>,<active>,<name>;"

<index> ::= integer index of printer

<active> ::= {Y | N}

<name> ::= name of printer (for example "DESKJET 950C")
```

See Also

- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:APRinter" on page 326
- ":HARDcopy:STARt" on page 336

:HARDcopy:STARt

(see page 828)

Command Syntax `:HARDcopy:STARt`

The :HARDcopy:STARt command starts a print job.

See Also

- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:APRinter" on page 326
- ":HARDcopy:PRINter:LIST" on page 335
- ":HARDcopy:FACTors" on page 327
- ":HARDcopy:FFEed" on page 328
- ":HARDcopy:INKSaver" on page 329
- ":HARDcopy:LAYout" on page 330
- ":HARDcopy:PALette" on page 334

19 :LISTer Commands

Table 65 :LISTer Commands Summary

Command	Query	Options and Query Returns
n/a	:LISTer:DATA? (see page 338)	<binary_block> ::= comma-separated data with newlines at the end of each row
:LISTer:DISPlay {{OFF | 0} | {SBUS1 | ON | 1}} (see page 339)	:LISTer:DISPlay? (see page 339)	{OFF | SBUS1}
:LISTer:REFerence <time_ref> (see page 340)	:LISTer:REFerence? (see page 340)	<time_ref> ::= {TRIGger | PREVious}

Introduction to :LISTer Commands

The LISTer subsystem is used to turn on/off the serial decode Lister display and return data from the Lister display.

:LISTer:DATA

(see page 828)

Query Syntax `:LISTer:DATA?`

The :LISTer:DATA? query returns the lister data.

Return Format `<binary block><NL>`

```
<binary_block> ::= comma-separated data with newlines at the
                   end of each row
```

See Also

- "Introduction to :LISTer Commands" on page 337
- ":LISTer:DISPlay" on page 339
- "Definite-Length Block Response Data" on page 114

:LISTer:DISPlay

N (see page 828)

Command Syntax

```
:LISTer:DISPlay <value>

<value> ::= {{OFF | 0} | {SBUS1 | ON | 1}}
```

The :LISTer:DISPlay command turns the serial bus Lister display on or off. "ON" or "1" is the same as "SBUS1".

Serial bus decode must be on before it can be displayed in the Lister.

Query Syntax

```
:LISTer:DISPlay?
```

The :LISTer:DISPlay? query returns the Lister display setting.

Return Format

```
<value><NL>

<value> ::= {OFF | SBUS1}
```

See Also

- "Introduction to :LISTer Commands" on page 337
- ":SBUS<n>:DISPlay" on page 490
- ":LISTer:DATA" on page 338

:LISTer:REFerence

N (see page 828)

Command Syntax

```
:LISTer:REFerence <time_ref>

<time_ref> ::= {TRIGger | PREVious}
```

The :LISTer:REFerence command selects whether the time value for a Lister row is relative to the trigger ot the previous Lister row.

Query Syntax

```
:LISTer:REFerence?
```

The :LISTer:REFerence? query returns the Lister time reference setting.

Return Format

```
<time_ref><NL>

<time_ref> ::= {TRIGger | PREVious}
```

See Also

- "Introduction to :LISTer Commands" on page 337
- ":SBUS<n>:DISPlay" on page 490
- ":LISTer:DATA" on page 338
- ":LISTer:DISPlay" on page 339

20 :MARKer Commands

Set and query the settings of X-axis markers (X1 and X2 cursors) and the Y-axis markers (Y1 and Y2 cursors). See "Introduction to :MARKer Commands" on page 342.

Table 66 :MARKer Commands Summary

Command	Query	Options and Query Returns
:MARKer:MODE <mode> (see page 344)	:MARKer:MODE? (see page 344)	<mode> ::= {OFF | MEASurement | MANual | WAVeform}
:MARKer:X1Position <position>[suffix] (see page 345)	:MARKer:X1Position? (see page 345)	<position> ::= X1 cursor position value in NR3 format [suffix] ::= {s | ms | us | ns | ps | Hz | kHz | MHz} <return_value> ::= X1 cursor position value in NR3 format
:MARKer:X1Y1source <source> (see page 346)	:MARKer:X1Y1source? (see page 346)	<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format On 2-channel oscilloscopes, EXTernal available for MANUAL mode only <return_value> ::= <source>
:MARKer:X2Position <position>[suffix] (see page 347)	:MARKer:X2Position? (see page 347)	<position> ::= X2 cursor position value in NR3 format [suffix] ::= {s | ms | us | ns | ps | Hz | kHz | MHz} <return_value> ::= X2 cursor position value in NR3 format

Table 66 :MARKer Commands Summary (continued)

Command	Query	Options and Query Returns
:MARKer:X2Y2source <source> (see page 348)	:MARKer:X2Y2source? (see page 348)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= <source>
n/a	:MARKer:XDELta? (see page 349)	<return_value> ::= X cursors delta value in NR3 format
:MARKer:XUNits <mode> (see page 350)	:MARKer:XUNits? (see page 350)	<units> ::= {SEConds | HERTz | DEGRees | PERCent}
:MARKer:XUNits:USE (see page 351)	n/a	n/a
:MARKer:Y1Position <position>[suffix] (see page 352)	:MARKer:Y1Position? (see page 352)	<position> ::= Y1 cursor position value in NR3 format [suffix] ::= {V | mV | dB} <return_value> ::= Y1 cursor position value in NR3 format
:MARKer:Y2Position <position>[suffix] (see page 353)	:MARKer:Y2Position? (see page 353)	<position> ::= Y2 cursor position value in NR3 format [suffix] ::= {V | mV | dB} <return_value> ::= Y2 cursor position value in NR3 format
n/a	:MARKer:YDELta? (see page 354)	<return_value> ::= Y cursors delta value in NR3 format
:MARKer:YUNits <mode> (see page 355)	:MARKer:YUNits? (see page 355)	<units> ::= {BASE | PERCent}
:MARKer:YUNits:USE (see page 356)	n/a	n/a

Introduction to :MARKer Commands

The MARKer subsystem commands set and query the settings of X-axis markers (X1 and X2 cursors) and the Y-axis markers (Y1 and Y2 cursors). You can set and query the marker mode and source, the position of the X and Y cursors, and query delta X and delta Y cursor values.

Reporting the Setup

Use :MARKer? to query setup information for the MARKer subsystem.

Return Format

The following is a sample response from the :MARKer? query. In this case, the query was issued following a *RST and ":MARKer:MODE MANual" command.

```
:MARK:X1Y1 CHAN1;X2Y2 CHAN1;MODE MAN
```

:MARKer:MODE

(see page 828)

Command Syntax

```
:MARKer:MODE <mode>

<mode> ::= {OFF | MEASurement | MANual | WAVeform}
```

The :MARKer:MODE command sets the cursors mode:

- OFF – removes the cursor information from the display.
- MANual – enables manual placement of the X and Y cursors.

  If the front-panel cursors are off, or are set to the front-panel Hex or Binary mode, setting :MARKer:MODE MANual will put the cursors in the front-panel Normal mode.
- MEASurement – cursors track the most recent measurement.

  Setting the mode to MEASurement sets the marker sources (:MARKer:X1Y1source and :MARKer:X2Y2source) to the measurement source (:MEASure:SOURce). Setting the measurement source remotely always sets the marker sources.
- WAVeform – the Y1 cursor tracks the voltage value at the X1 cursor of the waveform specified by the X1Y1source, and the Y2 cursor does the same for the X2 cursor and its X2Y2source.

Query Syntax

```
:MARKer:MODE?
```

The :MARKer:MODE? query returns the current cursors mode.

Return Format

```
<mode><NL>

<mode> ::= {OFF | MEAS | MAN | WAV}
```

See Also

- "Introduction to :MARKer Commands" on page 342
- ":MARKer:X1Y1source" on page 346
- ":MARKer:X2Y2source" on page 348
- ":MEASure:SOURce" on page 399
- ":MARKer:X1Position" on page 345
- ":MARKer:X2Position" on page 347
- ":MARKer:Y1Position" on page 352
- ":MARKer:Y2Position" on page 353

:MARKer:X1Position

(see page 828)

Command Syntax

```
:MARKer:X1Position <position> [suffix]

<position> ::= X1 cursor position in NR3 format

<suffix> ::= {s | ms | us | ns | ps | Hz | kHz | MHz}
```

The :MARKer:X1Position command:

- Sets :MARKer:MODE to MANual if it is not currently set to WAVeform (see ":MARKer:MODE" on page 344).
- Sets the X1 cursor position to the specified value.

X cursor units are set by the :MARKer:XUNits command.

Query Syntax

```
:MARKer:X1Position?
```

The :MARKer:X1Position? query returns the current X1 cursor position. This is functionally equivalent to the obsolete :MEASure:TSTArt command/query.

NOTE If the front-panel cursors are off, the marker position values are not defined and an error is generated. Make sure to set :MARKer:MODE to MANual or WAVeform to put the cursors in the front-panel Normal mode.

Return Format

```
<position><NL>

<position> ::= X1 cursor position in NR3 format
```

See Also

- "Introduction to :MARKer Commands" on page 342
- ":MARKer:MODE" on page 344
- ":MARKer:X2Position" on page 347
- ":MARKer:X1Y1source" on page 346
- ":MARKer:X2Y2source" on page 348
- ":MARKer:XUNits" on page 350
- ":MEASure:TSTArt" on page 767

:MARKer:X1Y1source

(see page 828)

Command Syntax

```
:MARKer:X1Y1source <source>

<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>
   | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= {1 | 2}

On 2-channel oscilloscopes, EXTernal available for MANUAL mode only
```

The :MARKer:X1Y1source command sets the source for the cursors. The channel you specify must be enabled for cursors to be displayed. If the channel or function is not on, an error message is issued.

If the marker mode is not currently WAVeform (see ":MARKer:MODE" on page 344):

- Sending a :MARKer:X1Y1source command will put the cursors in the MANual mode.
- Setting the source for one pair of markers (for example, X1Y1) sets the source for the other (for example, X2Y2).

If the marker mode is currently WAVeform, the X1Y1 source can be set separate from the X2Y2 source.

If :MARKer:MODE is set to OFF or MANual, setting :MEASure:SOURce to CHANnel<n>, FUNCtion, MATH, or WMEMory<r> will also set :MARKer:X1Y1source and :MARKer:X2Y2source to this value.

NOTE MATH is an alias for FUNCtion. The query will return FUNC if the source is FUNCtion or MATH.

Query Syntax

```
:MARKer:X1Y1source?
```

The :MARKer:X1Y1source? query returns the current source for the cursors. If all channels are off or if :MARKer:MODE is set to OFF, the query returns NONE.

Return Format

```
<source><NL>

<source> ::= {CHAN<n> | FUNC | FFT | WMEM<r> | EXT | NONE}
```

See Also

- "Introduction to :MARKer Commands" on page 342
- ":MARKer:MODE" on page 344
- ":MARKer:X2Y2source" on page 348
- ":MEASure:SOURce" on page 399

:MARKer:X2Position

(see page 828)

Command Syntax

```
:MARKer:X2Position <position> [suffix]

<position> ::= X2 cursor position in NR3 format

<suffix> ::= {s | ms | us | ns | ps | Hz | kHz | MHz}
```

The :MARKer:X2Position command:

- Sets :MARKer:MODE to MANual if it is not currently set to WAVeform (see ":MARKer:MODE" on page 344).
- Sets the X2 cursor position to the specified value.

X cursor units are set by the :MARKer:XUNits command.

Query Syntax

```
:MARKer:X2Position?
```

The :MARKer:X2Position? query returns current X2 cursor position. This is functionally equivalent to the obsolete :MEASure:TSTOp command/query.

NOTE If the front-panel cursors are off, the marker position values are not defined and an error is generated. Make sure to set :MARKer:MODE to MANual or WAVeform to put the cursors in the front-panel Normal mode.

Return Format

```
<position><NL>

<position> ::= X2 cursor position in NR3 format
```

See Also

- "Introduction to :MARKer Commands" on page 342
- ":MARKer:MODE" on page 344
- ":MARKer:X1Position" on page 345
- ":MARKer:X2Y2source" on page 348
- ":MARKer:XUNits" on page 350
- ":MEASure:TSTOp" on page 768

:MARKer:X2Y2source

N (see page 828)

Command Syntax

```
:MARKer:X2Y2source <source>

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= {1 | 2}
```

The :MARKer:X2Y2source command sets the source for the cursors. The channel you specify must be enabled for cursors to be displayed. If the channel or function is not on, an error message is issued.

If the marker mode is not currently WAVeform (see ":MARKer:MODE" on page 344):

- Sending a :MARKer:X2Y2source command will put the cursors in the MANual mode.
- Setting the source for one pair of markers (for example, X2Y2) sets the source for the other (for example, X1Y1).

If the marker mode is currently WAVeform, the X2Y2 source can be set separate from the X1Y1 source.

If :MARKer:MODE is set to OFF or MANual, setting :MEASure:SOURce to CHANnel<n>, FUNCtion, MATH, or WMEMory<r> will also set :MARKer:X1Y1source and :MARKer:X2Y2source to this value.

NOTE MATH is an alias for FUNCtion. The query will return FUNC if the source is FUNCtion or MATH.

Query Syntax

```
:MARKer:X2Y2source?
```

The :MARKer:X2Y2source? query returns the current source for the cursors. If all channels are off or if :MARKer:MODE is set to OFF, the query returns NONE.

Return Format

```
<source><NL>

<source> ::= {CHAN<n> | FUNC | WMEM<r> | NONE}
```

See Also

- "Introduction to :MARKer Commands" on page 342
- ":MARKer:MODE" on page 344
- ":MARKer:X1Y1source" on page 346
- ":MEASure:SOURce" on page 399

:MARKer:XDELta

(see page 828)

Query Syntax `:MARKer:XDELta?`

The MARKer:XDELta? query returns the value difference between the current X1 and X2 cursor positions.

Xdelta = (Value at X2 cursor) - (Value at X1 cursor)

X cursor units are set by the :MARKer:XUNits command.

NOTE If the front-panel cursors are off, the marker position values are not defined. Make sure to set :MARKer:MODE to MANual or WAVeform to put the cursors in the front-panel Normal mode.

Return Format `<value><NL>`

`<value> ::= difference value in NR3 format.`

See Also
- "Introduction to :MARKer Commands" on page 342
- ":MARKer:MODE" on page 344
- ":MARKer:X1Position" on page 345
- ":MARKer:X2Position" on page 347
- ":MARKer:X1Y1source" on page 346
- ":MARKer:X2Y2source" on page 348
- ":MARKer:XUNits" on page 350

:MARKer:XUNits

(see page 828)

Command Syntax

```
:MARKer:XUNits <units>

<units> ::= {SEConds | HERTz | DEGRees | PERCent}
```

The :MARKer:XUNits command sets the X cursors units:

- SEConds – for making time measurements.
- HERTz – for making frequency measurements.
- DEGRees – for making phase measurements. Use the :MARKer:XUNits:USE command to set the current X1 location as 0 degrees and the current X2 location as 360 degrees.
- PERCent – for making ratio measurements. Use the :MARKer:XUNits:USE command to set the current X1 location as 0 percent and the current X2 location as 100 percent.

Changing X units affects the input and output values of the :MARKer:X1Position, :MARKer:X2Position, and :MARKer:XDELta commands/queries.

Query Syntax

```
:MARKer:XUNits?
```

The :MARKer:XUNits? query returns the current X cursors units.

Return Format

```
<units><NL>

<units> ::= {SEC | HERT | DEGR | PERC}
```

See Also

- "Introduction to :MARKer Commands" on page 342
- ":MARKer:XUNits:USE" on page 351
- ":MARKer:X1Y1source" on page 346
- ":MARKer:X2Y2source" on page 348
- ":MEASure:SOURce" on page 399
- ":MARKer:X1Position" on page 345
- ":MARKer:X2Position" on page 347

:MARKer:XUNits:USE

(see page 828)

Command Syntax `:MARKer:XUNits:USE`

When DEGRees is selected for :MARKer:XUNits, the :MARKer:XUNits:USE command sets the current X1 location as 0 degrees and the current X2 location as 360 degrees.

When PERCent is selected for :MARKer:XUNits, the :MARKer:XUNits:USE command sets the current X1 location as 0 percent and the current X2 location as 100 percent.

Once the 0 and 360 degree or 0 and 100 percent locations are set, inputs to and outputs from the :MARKer:X1Position, :MARKer:X2Position, and :MARKer:XDELta commands/queries are relative to the set locations.

See Also

- "Introduction to :MARKer Commands" on page 342
- ":MARKer:XUNits" on page 350
- ":MARKer:X1Y1source" on page 346
- ":MARKer:X2Y2source" on page 348
- ":MEASure:SOURce" on page 399
- ":MARKer:X1Position" on page 345
- ":MARKer:X2Position" on page 347
- ":MARKer:XDELta" on page 349

:MARKer:Y1Position

(see page 828)

Command Syntax

```
:MARKer:Y1Position <position> [suffix]

<position> ::= Y1 cursor position in NR3 format

<suffix> ::= {mV | V | dB}
```

If the :MARKer:MODE is not currently set to WAVeform (see ":MARKer:MODE" on page 344), the :MARKer:Y1Position command:

- Sets :MARKer:MODE to MANual.
- Sets the Y1 cursor position to the specified value.

Y cursor units are set by the :MARKer:YUNits command.

When the :MARKer:MODE is set to WAVeform, Y positions cannot be set.

Query Syntax

```
:MARKer:Y1Position?
```

The :MARKer:Y1Position? query returns current Y1 cursor position. This is functionally equivalent to the obsolete :MEASure:VSTArt command/query.

NOTE

If the front-panel cursors are off or are set to Binary or Hex Mode, the marker position values are not defined and an error is generated. Make sure to set :MARKer:MODE to MANual or WAVeform to put the cursors in the front-panel Normal mode.

Return Format

```
<position><NL>

<position> ::= Y1 cursor position in NR3 format
```

See Also

- "Introduction to :MARKer Commands" on page 342
- ":MARKer:MODE" on page 344
- ":MARKer:X1Y1source" on page 346
- ":MARKer:X2Y2source" on page 348
- ":MARKer:Y2Position" on page 353
- ":MARKer:YUNits" on page 355
- ":MEASure:VSTArt" on page 772

:MARKer:Y2Position

(see page 828)

Command Syntax

```
:MARKer:Y2Position <position> [suffix]

<position> ::= Y2 cursor position in NR3 format

<suffix> ::= {mV | V | dB}
```

If the :MARKer:MODE is not currently set to WAVeform (see ":MARKer:MODE" on page 344), the :MARKer:Y1Position command:

- Sets :MARKer:MODE to MANual.
- Sets the Y2 cursor position to the specified value.

Y cursor units are set by the :MARKer:YUNits command.

When the :MARKer:MODE is set to WAVeform, Y positions cannot be set.

Query Syntax

```
:MARKer:Y2Position?
```

The :MARKer:Y2Position? query returns current Y2 cursor position. This is functionally equivalent to the obsolete :MEASure:VSTOp command/query.

NOTE If the front-panel cursors are off or are set to Binary or Hex Mode, the marker position values are not defined and an error is generated. Make sure to set :MARKer:MODE to MANual or WAVeform to put the cursors in the front-panel Normal mode.

Return Format

```
<position><NL>

<position> ::= Y2 cursor position in NR3 format
```

See Also

- "Introduction to :MARKer Commands" on page 342
- ":MARKer:MODE" on page 344
- ":MARKer:X1Y1source" on page 346
- ":MARKer:X2Y2source" on page 348
- ":MARKer:Y1Position" on page 352
- ":MARKer:YUNits" on page 355
- ":MEASure:VSTOp" on page 773

:MARKer:YDELta

(see page 828)

Query Syntax `:MARKer:YDELta?`

The :MARKer:YDELta? query returns the value difference between the current Y1 and Y2 cursor positions.

Ydelta = (Value at Y2 cursor) - (Value at Y1 cursor)

NOTE **If the front-panel cursors are off or are set to Binary or Hex Mode, the marker position values are not defined. Make sure to set :MARKer:MODE to MANual or WAVeform to put the cursors in the front-panel Normal mode.**

Y cursor units are set by the :MARKer:YUNits command.

Return Format `<value><NL>`

`<value> ::= difference value in NR3 format`

See Also

- "Introduction to :MARKer Commands" on page 342
- ":MARKer:MODE" on page 344
- ":MARKer:X1Y1source" on page 346
- ":MARKer:X2Y2source" on page 348
- ":MARKer:Y1Position" on page 352
- ":MARKer:Y2Position" on page 353
- ":MARKer:YUNits" on page 355

:MARKer:YUNits

(see page 828)

Command Syntax

```
:MARKer:YUNits <units>

<units> ::= {BASE | PERCent}
```

The :MARKer:YUNits command sets the Y cursors units:

- BASE – for making measurements in the units associated with the cursors source.
- PERCent – for making ratio measurements. Use the :MARKer:YUNits:USE command to set the current Y1 location as 0 percent and the current Y2 location as 100 percent.

Changing Y units affects the input and output values of the :MARKer:Y1Position, :MARKer:Y2Position, and :MARKer:YDELta commands/queries.

Query Syntax

```
:MARKer:YUNits?
```

The :MARKer:YUNits? query returns the current Y cursors units.

Return Format

```
<units><NL>

<units> ::= {BASE | PERC}
```

See Also

- "Introduction to :MARKer Commands" on page 342
- ":MARKer:YUNits:USE" on page 356
- ":MARKer:X1Y1source" on page 346
- ":MARKer:X2Y2source" on page 348
- ":MEASure:SOURce" on page 399
- ":MARKer:Y1Position" on page 352
- ":MARKer:Y2Position" on page 353
- ":MARKer:YDELta" on page 354

:MARKer:YUNits:USE

(see page 828)

Command Syntax `:MARKer:YUNits:USE`

When PERCent is selected for :MARKer:YUNits, the :MARKer:YUNits:USE command sets the current Y1 location as 0 percent and the current Y2 location as 100 percent.

Once the 0 and 100 percent locations are set, inputs to and outputs from the :MARKer:Y1Position, :MARKer:Y2Position, and :MARKer:YDELta commands/queries are relative to the set locations.

See Also

- "Introduction to :MARKer Commands" on page 342
- ":MARKer:YUNits" on page 355
- ":MARKer:X1Y1source" on page 346
- ":MARKer:X2Y2source" on page 348
- ":MEASure:SOURce" on page 399
- ":MARKer:Y1Position" on page 352
- ":MARKer:Y2Position" on page 353
- ":MARKer:YDELta" on page 354

21 :MEASure Commands

Select automatic measurements to be made and control time markers. See "Introduction to :MEASure Commands" on page 367.

Table 67 :MEASure Commands Summary

Command	Query	Options and Query Returns
:MEASure:ALL (see page 369)	n/a	n/a
:MEASure:BRATe [<source>] (see page 370)	:MEASure:BRATe? [<source>] (see page 370)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# of analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format <return_value> ::= bit rate in Hz, NR3 format
:MEASure:CLEar (see page 371)	n/a	n/a
:MEASure:COUNter [<source>] (see page 372)	:MEASure:COUNter? [<source>] (see page 372)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <return_value> ::= counter frequency in Hertz in NR3 format

Table 67 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:DEFine DELay, <delay spec>[,<source>] (see page 373)	:MEASure:DEFine? DELay[,<source>] (see page 374)	<delay spec> ::= <edge_spec1>,<edge_spec2> edge_spec1 ::= [<slope>]<occurrence> edge_spec2 ::= [<slope>]<occurrence> <slope> ::= {+ | -} <occurrence> ::= integer <source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}
:MEASure:DEFine THResholds, <threshold spec>[,<source>] (see page 373)	:MEASure:DEFine? THResholds[,<source>] (see page 374)	<threshold spec> ::= {STANdard} | {<threshold mode>,<upper>, <middle>,<lower>} <threshold mode> ::= {PERCent | ABSolute} <source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>}
:MEASure:DELay [<source1>] [,<source2>] (see page 376)	:MEASure:DELay? [<source1>] [,<source2>] (see page 376)	<source1,2> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= floating-point number delay time in seconds in NR3 format
:MEASure:DUTYcycle [<source>] (see page 378)	:MEASure:DUTYcycle? [<source>] (see page 378)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= ratio of positive pulse width to period in NR3 format

Table 67 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:FALLtime [<source>] (see page 379)	:MEASure:FALLtime? [<source>] (see page 379)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= time in seconds between the lower and upper thresholds in NR3 format
:MEASure:FREQuency [<source>] (see page 380)	:MEASure:FREQuency? [<source>] (see page 380)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= frequency in Hertz in NR3 format
:MEASure:NDUTy [<source>] (see page 381)	:MEASure:NDUTy? [<source>] (see page 381)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= ratio of negative pulse width to period in NR3 format
:MEASure:NEDGes [<source>] (see page 382)	:MEASure:NEDGes? [<source>] (see page 382)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the falling edge count in NR3 format

Table 67 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:NPULses [<source>] (see page 383)	:MEASure:NPULses? [<source>] (see page 383)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the falling pulse count in NR3 format
:MEASure:NWIDth [<source>] (see page 384)	:MEASure:NWIDth? [<source>] (see page 384)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= negative pulse width in seconds in NR3 format
:MEASure:OVERshoot [<source>] (see page 385)	:MEASure:OVERshoot? [<source>] (see page 385)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the percent of the overshoot of the selected waveform in NR3 format
:MEASure:PEDGes [<source>] (see page 387)	:MEASure:PEDGes? [<source>] (see page 387)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the rising edge count in NR3 format

Table 67 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:PERiod [<source>] (see page 388)	:MEASure:PERiod? [<source>] (see page 388)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= waveform period in seconds in NR3 format
:MEASure:PHASe [<source1>] [,<source2>] (see page 389)	:MEASure:PHASe? [<source1>] [,<source2>] (see page 389)	<source1,2> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the phase angle value in degrees in NR3 format
:MEASure:PPULses [<source>] (see page 390)	:MEASure:PPULses? [<source>] (see page 390)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the rising pulse count in NR3 format
:MEASure:PREShoot [<source>] (see page 391)	:MEASure:PREShoot? [<source>] (see page 391)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the percent of preshoot of the selected waveform in NR3 format

Table 67 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:PWIDth [<source>] (see page 392)	:MEASure:PWIDth? [<source>] (see page 392)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= width of positive pulse in seconds in NR3 format
n/a	:MEASure:RESults? <result_list> (see page 393)	<result_list> ::= comma-separated list of measurement results
:MEASure:RISetime [<source>] (see page 396)	:MEASure:RISetime? [<source>] (see page 396)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= rise time in seconds in NR3 format
:MEASure:SDEViation [<source>] (see page 397)	:MEASure:SDEViation? [<source>] (see page 397)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format <return_value> ::= calculated std deviation in NR3 format
:MEASure:SHOW {1 | ON} (see page 398)	:MEASure:SHOW? (see page 398)	{1}
:MEASure:SOURce <source1> [,<source2>] (see page 399)	:MEASure:SOURce? (see page 399)	<source1,2> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= {<source> | NONE}

Table 67 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:STATistics <type> (see page 401)	:MEASure:STATistics? (see page 401)	<type> ::= {{ON | 1} | CURRent | MEAN | MINimum | MAXimum | STDDev | COUNt} ON ::= all statistics returned
:MEASure:STATistics:DISPlay {{0 | OFF} | {1 | ON}} (see page 402)	:MEASure:STATistics:DISPlay? (see page 402)	{0 | 1}
:MEASure:STATistics:INCRement (see page 403)	n/a	n/a
:MEASure:STATistics:MCOunt <setting> (see page 404)	:MEASure:STATistics:MCOunt? (see page 404)	<setting> ::= {INFinite | <count>} <count> ::= 2 to 2000 in NR1 format
:MEASure:STATistics:RESet (see page 405)	n/a	n/a
:MEASure:STATistics:RSDeviation {{0 | OFF} | {1 | ON}} (see page 406)	:MEASure:STATistics:RSDeviation? (see page 406)	{0 | 1}
n/a	:MEASure:TEDGe? <slope><occurrence>[,<source>] (see page 407)	<slope> ::= direction of the waveform <occurrence> ::= the transition to be reported <source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} for DSO models <source> ::= {CHANnel<n> | DIGital<d> | FUNCtion | MATH | WMEMory<r>} for MSO models <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <d> ::= 0 to (# digital channels - 1) in NR1 format <return_value> ::= time in seconds of the specified transition

Table 67 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
n/a	:MEASure:TEDGe? <slope><occurrence>[,<source>] (see page 407)	<slope> ::= direction of the waveform <occurrence> ::= the transition to be reported <source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= time in seconds of the specified transition
n/a	:MEASure:TVALue? <value>,[<slope>]<occurrence>[,<source>] (see page 409)	<value> ::= voltage level that the waveform must cross. <slope> ::= direction of the waveform when <value> is crossed. <occurrence> ::= transitions reported. <source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= time in seconds of specified voltage crossing in NR3 format
:MEASure:VAMPlitude [<source>] (see page 411)	:MEASure:VAMPlitude? [<source>] (see page 411)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= the amplitude of the selected waveform in volts in NR3 format

Table 67 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:VAVerage [<interval>][,][<source>] (see page 412)	:MEASure:VAVerage? [<interval>][,][<source>] (see page 412)	<interval> ::= {CYCLe | DISPlay} <source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= calculated average voltage in NR3 format
:MEASure:VBASe [<source>] (see page 413)	:MEASure:VBASe? [<source>] (see page 413)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <base_voltage> ::= voltage at the base of the selected waveform in NR3 format
:MEASure:VMAX [<source>] (see page 414)	:MEASure:VMAX? [<source>] (see page 414)	<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= maximum voltage of the selected waveform in NR3 format
:MEASure:VMIN [<source>] (see page 415)	:MEASure:VMIN? [<source>] (see page 415)	<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= minimum voltage of the selected waveform in NR3 format

Table 67 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:VPP [<source>] (see page 416)	:MEASure:VPP? [<source>] (see page 416)	<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= voltage peak-to-peak of the selected waveform in NR3 format
:MEASure:VRMS [<interval>][,] [<type>][,] [<source>] (see page 417)	:MEASure:VRMS? [<interval>][,] [<type>][,] [<source>] (see page 417)	<interval> ::= {CYCLe | DISPlay} <type> ::= {AC | DC} <source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= calculated dc RMS voltage in NR3 format
n/a	:MEASure:VTIMe? <vtime>[,<source>] (see page 418)	<vtime> ::= displayed time from trigger in seconds in NR3 format <source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format EXTernal available on 2-channel oscilloscopes only <return_value> ::= voltage at the specified time in NR3 format
:MEASure:VTOP [<source>] (see page 419)	:MEASure:VTOP? [<source>] (see page 419)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format <return_value> ::= voltage at the top of the waveform in NR3 format
:MEASure:WINDow <type> (see page 420)	:MEASure:WINDow? (see page 420)	<type> ::= {MAIN | ZOOM | AUTO}

Table 67 :MEASure Commands Summary (continued)

Command	Query	Options and Query Returns
:MEASure:XMAX [<source>] (see page 421)	:MEASure:XMAX? [<source>] (see page 421)	<source> ::= {CHANnel<n> | FUNCtion | FFT | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format <return_value> ::= horizontal value of the maximum in NR3 format
:MEASure:XMIN [<source>] (see page 422)	:MEASure:XMIN? [<source>] (see page 422)	<source> ::= {CHANnel<n> | FUNCtion | FFT | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format <return_value> ::= horizontal value of the maximum in NR3 format

Introduction to :MEASure Commands

The commands in the MEASure subsystem are used to make parametric measurements on displayed waveforms.

Measurement Setup

To make a measurement, the portion of the waveform required for that measurement must be displayed on the oscilloscope screen.

Measurement Type	Portion of waveform that must be displayed
period, duty cycle, or frequency	at least one complete cycle
pulse width	the entire pulse
rise time	rising edge, top and bottom of pulse
fall time	falling edge, top and bottom of pulse

Measurement Error

If a measurement cannot be made (typically because the proper portion of the waveform is not displayed), the value +9.9E+37 is returned for that measurement.

Making Measurements

If more than one waveform, edge, or pulse is displayed, time measurements are made on the portion of the displayed waveform closest to the trigger reference (left, center, or right).

When making measurements in the zoomed (delayed) time base mode (:TIMebase:MODE WINDow), the oscilloscope will attempt to make the measurement inside the zoomed sweep window. If the measurement is an average and there are not three edges, the oscilloscope will revert to the mode of making the measurement at the start of the main sweep.

When the command form is used, the measurement result is displayed on the instrument. When the query form of these measurements is used, the measurement is made one time, and the measurement result is returned over the bus.

Measurements are made on the displayed waveforms specified by the :MEASure:SOURce command. The MATH source is an alias for the FUNCtion source.

Not all measurements are available on the FFT (Fast Fourier Transform).

Reporting the Setup

Use the :MEASure? query to obtain setup information for the MEASure subsystem. (Currently, this is only :MEASure:SOURce.)

Return Format

The following is a sample response from the :MEASure? query. In this case, the query was issued following a *RST command.

```
:MEAS:SOUR CHAN1,CHAN2;STAT ON
```

:MEASure:ALL

(see page 828)

Command Syntax `:MEASure:ALL`

This command installs a Snapshot All measurement on the screen.

See Also

- "Introduction to :MEASure Commands" on page 367

:MEASure:BRATe

(see page 828)

Command Syntax

```
:MEASure:BRATe [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal}

<n> ::= 1 to (# of analog channels) in NR1 format

<r> ::= 1 to (# ref waveforms) in NR1 format
```

The :MEASure:BRATe command installs a screen measurement and starts the bit rate measurement. If the optional source parameter is specified, the currently specified source is modified.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

Query Syntax

```
:MEASure:BRATe? [<source>]
```

The :MEASure:BRATe? query measures all positive and negative pulse widths on the waveform, takes the minimum value found of either width type and inverts that minimum width to give a value in Hertz.

Return Format

```
<value><NL>

<value> ::= the bit rate value in Hertz
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:FREQuency" on page 380
- ":MEASure:PERiod" on page 388

:MEASure:CLEar

(see page 828)

Command Syntax `:MEASure:CLEar`

This command clears all selected measurements and markers from the screen.

See Also

- "Introduction to :MEASure Commands" on page 367

:MEASure:COUNter

(see page 828)

Command Syntax

```
:MEASure:COUNter [<source>]

<source> ::= {CHANnel<n> | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :MEASure:COUNter command installs a screen measurement and starts a counter measurement. If the optional source parameter is specified, the current source is modified. Any channel except Math may be selected for the source.

The counter measurement counts trigger level crossings at the selected trigger slope and displays the results in Hz. The gate time for the measurement is automatically adjusted to be 100 ms or twice the current time window, whichever is longer, up to 1 second. The counter measurement can measure frequencies up to 125 MHz. The minimum frequency supported is 1/(2 X gate time).

The Y cursor shows the the edge threshold level used in the measurement.

Only one counter measurement may be displayed at a time.

NOTE This command is not available if the source is MATH.

Query Syntax

```
:MEASure:COUNter? [<source>]
```

The :MEASure:COUNter? query measures and outputs the counter frequency of the specified source.

NOTE The :MEASure:COUNter? query times out if the counter measurement is installed on the front panel. Use :MEASure:CLEar to remove the front-panel measurement before executing the :MEASure:COUNter? query.

Return Format

```
<source><NL>

<source> ::= count in Hertz in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:FREQuency" on page 380
- ":MEASure:CLEar" on page 371

:MEASure:DEFine

N (see page 828)

Command Syntax

```
:MEASure:DEFine <meas_spec>[,<source>]

<meas_spec> ::= {DELay | THResholds}

<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= {1 | 2}
```

The :MEASure:DEFine command sets up the definition for measurements by specifying the delta time or threshold values. Changing these values may affect the results of other measure commands. The table below identifies which measurement results that can be affected by redefining the DELay specification or the THResholds values. For example, changing the THResholds definition from the default 10%, 50%, and 90% values may change the returned measurement result.

MEASure Command	DELay	THResholds
DUTYcycle		x
DELay	x	x
FALLtime		x
FREQuency		x
NWIDth		x
OVERshoot		x
PERiod		x
PHASe		x
PREShoot		x
PWIDth		x
RISetime		x
VAVerage		x
VRMS		x

:MEASure:DEFine DELay Command Syntax

```
:MEASure:DEFine DELay,<delay spec>[,<source>]

<delay spec> ::= <edge_spec1>,<edge_spec2>

<edge_spec1> ::= [<slope>]<occurrence>

<edge_spec2> ::= [<slope>]<occurrence>

<slope> ::= {+ | -}
```

```
<occurrence> ::= integer
```

This command defines the behavior of the :MEASure:DELay? query by specifying the start and stop edge to be used. <edge_spec1> specifies the slope and edge number on source1. <edge_spec2> specifies the slope and edge number on source2. The measurement is taken as:

delay = t(<edge_spec2>) - t(<edge_spec1>)

NOTE The :MEASure:DELay command and the front-panel delay measurement use an auto-edge selection method to determine the actual edge used for the measurement. The :MEASure:DEFine command has no effect on these delay measurements. The edges specified by the :MEASure:DEFine command only define the edges used by the :MEASure:DELay? query.

:MEASure:DEFine THResholds Command Syntax

```
:MEASure:DEFine THResholds,<threshold spec>[,<source>]

<threshold spec> ::= {STANdard}
                   | {<threshold mode>,<upper>,<middle>,<lower>}

<threshold mode> ::= {PERCent | ABSolute}
```

for <threshold mode> = PERCent:

```
<upper>, <middle>, <lower> ::= A number specifying the upper, middle,
                               and lower threshold percentage values
                               between Vbase and Vtop in NR3 format.
```

for <threshold mode> = ABSolute:

```
<upper>, <middle>, <lower> ::= A number specifying the upper, middle,
                               and lower threshold absolute values in
                               NR3 format.
```

- STANdard threshold specification sets the lower, middle, and upper measurement thresholds to 10%, 50%, and 90% values between Vbase and Vtop.
- Threshold mode PERCent sets the measurement thresholds to any user-defined percentages between 5% and 95% of values between Vbase and Vtop.
- Threshold mode ABSolute sets the measurement thresholds to absolute values. ABSolute thresholds are dependent on channel scaling (:CHANnel<n>:RANGe or ":CHANnel<n>:SCALe" on page 229:CHANnel<n>:SCALe), probe attenuation (:CHANnel<n>:PROBe), and probe units (:CHANnel<n>:UNITs). Always set these values first before setting ABSolute thresholds.

Query Syntax

```
:MEASure:DEFine? <meas_spec>[,<source>]

<meas_spec> ::= {DELay | THResholds}
```

The :MEASure:DEFine? query returns the current edge specification for the delay measurements setup or the current specification for the thresholds setup.

Return Format

for <meas_spec> = DELay:

```
{ <edge_spec1> | <edge_spec2> | <edge_spec1>,<edge_spec2>} <NL>
```

for <meas_spec> = THResholds and <threshold mode> = PERCent:

```
THR,PERC,<upper>,<middle>,<lower><NL>

<upper>, <middle>, <lower> ::= A number specifying the upper, middle,
                               and lower threshold percentage values
                               between Vbase and Vtop in NR3 format.
```

for <meas_spec> = THResholds and <threshold mode> = ABSolute:

```
THR,ABS,<upper>,<middle>,<lower><NL>

<upper>, <middle>, <lower> ::= A number specifying the upper, middle,
                               and lower threshold voltages in NR3
                               format.
```

for <threshold spec> = STANdard:

```
THR,PERC,+90.0,+50.0,+10.0
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:DELay" on page 376
- ":MEASure:SOURce" on page 399
- ":CHANnel<n>:RANGe" on page 228
- ":CHANnel<n>:SCALe" on page 229
- ":CHANnel<n>:PROBe" on page 222
- ":CHANnel<n>:UNITs" on page 230

:MEASure:DELay

N (see page 828)

Command Syntax

```
:MEASure:DELay [<source1>][,<source2>]

<source1>, <source2> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:DELay command places the instrument in the continuous measurement mode and starts a delay measurement.

The measurement is taken as:

delay = t(<edge spec 2>) - t(<edge spec 1>)

where the <edge spec> definitions are set by the :MEASure:DEFine command

NOTE

The :MEASure:DELay command and the front-panel delay measurement differ from the :MEASure:DELay? query.

The delay command or front-panel measurement run the delay measurement in auto-edge select mode. In this mode, you can select the edge polarity, but the instrument will select the edges that will make the best possible delay measurement. The source1 edge chosen will be the edge that meets the polarity specified and is closest to the trigger reference point. The source2 edge selected will be that edge of the specified polarity that gives the first of the following criteria:

- **The smallest positive delay value that is less than source1 period.**
- **The smallest negative delay that is less than source1 period.**
- **The smallest absolute value of delay.**

The :MEASure:DELay? query will make the measurement using the edges specified by the :MEASure:DEFine command.

Query Syntax

```
:MEASure:DELay? [<source1>][,<source2>]
```

The :MEASure:DELay? query measures and returns the delay between source1 and source2. The delay measurement is made from the user-defined slope and edge count of the signal connected to source1, to the defined slope and edge count of the signal connected to source2. Delay measurement slope and edge parameters are selected using the :MEASure:DEFine command.

Also in the :MEASure:DEFine command, you can set upper, middle, and lower threshold values. *It is the middle threshold value that is used when performing the delay query.* The standard upper, middle, and lower measurement thresholds are

90%, 50%, and 10% values between Vbase and Vtop. If you want to move the delay measurement point nearer to Vtop or Vbase, you must change the threshold values with the :MEASure:DEFine THResholds command.

Return Format

```
<value><NL>

<value> ::= floating-point number delay time in seconds in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:DEFine" on page 373
- ":MEASure:PHASe" on page 389

:MEASure:DUTYcycle

(see page 828)

Command Syntax

```
:MEASure:DUTYcycle [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal}

<n> ::= 1 to (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:DUTYcycle command installs a screen measurement and starts a duty cycle measurement on the current :MEASure:SOURce. If the optional source parameter is specified, the current source is modified.

NOTE The signal must be displayed to make the measurement. This command is not available if the source is FFT (Fast Fourier Transform).

NOTE The EXTernal source is available on 2-channel oscilloscopes only.

Query Syntax

```
:MEASure:DUTYcycle? [<source>]
```

The :MEASure:DUTYcycle? query measures and outputs the duty cycle of the signal specified by the :MEASure:SOURce command. The value returned for the duty cycle is the ratio of the positive pulse width to the period. The positive pulse width and the period of the specified signal are measured, then the duty cycle is calculated with the following formula:

duty cycle = (+pulse width/period)*100

Return Format

```
<value><NL>

<value> ::= ratio of positive pulse width to period in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:PERiod" on page 388
- ":MEASure:PWIDth" on page 392
- ":MEASure:SOURce" on page 399

Example Code

- "Example Code" on page 399

:MEASure:FALLtime

(see page 828)

Command Syntax

```
:MEASure:FALLtime [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:FALLtime command installs a screen measurement and starts a fall-time measurement. For highest measurement accuracy, set the sweep speed as fast as possible, while leaving the falling edge of the waveform on the display. If the optional source parameter is specified, the current source is modified.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

Query Syntax

```
:MEASure:FALLtime? [<source>]
```

The :MEASure:FALLtime? query measures and outputs the fall time of the displayed falling (negative-going) edge closest to the trigger reference. The fall time is determined by measuring the time at the upper threshold of the falling edge, then measuring the time at the lower threshold of the falling edge, and calculating the fall time with the following formula:

fall time = time at lower threshold - time at upper threshold

Return Format

```
<value><NL>

<value> ::= time in seconds between the lower threshold and upper
            threshold in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:RISetime" on page 396
- ":MEASure:SOURce" on page 399

:MEASure:FREQuency

(see page 828)

Command Syntax

```
:MEASure:FREQuency [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal}

<n> ::= 1 to (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:FREQuency command installs a screen measurement and starts a frequency measurement. If the optional source parameter is specified, the current source is modified.

IF the edge on the screen closest to the trigger reference is rising:

THEN frequency = 1/(time at trailing rising edge - time at leading rising edge)

ELSE frequency = 1/(time at trailing falling edge - time at leading falling edge)

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

NOTE The EXTernal source is available on 2-channel oscilloscopes only.

Query Syntax

```
:MEASure:FREQuency? [<source>]
```

The :MEASure:FREQuency? query measures and outputs the frequency of the cycle on the screen closest to the trigger reference.

Return Format

```
<source><NL>

<source> ::= frequency in Hertz in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:PERiod" on page 388

Example Code

- "Example Code" on page 399

:MEASure:NDUTy

N (see page 828)

Command Syntax

```
:MEASure:NDUTy [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal}

<n> ::= 1 to (# of analog channels) in NR1 format

<r> ::= 1 to (# ref waveforms) in NR1 format
```

The :MEASure:NDUTy command installs a screen measurement and starts a negative duty cycle measurement on the current :MEASure:SOURce. If the optional source parameter is specified, the current source is modified.

NOTE The signal must be displayed to make the measurement. This command is not available if the source is FFT (Fast Fourier Transform).

NOTE The EXTernal source is available on 2-channel oscilloscopes only.

Query Syntax

```
:MEASure:NDUTy? [<source>]
```

The :MEASure:NDUTy? query measures and outputs the negative duty cycle of the signal specified by the :MEASure:SOURce command. The value returned for the duty cycle is the ratio of the negative pulse width to the period. The negative pulse width and the period of the specified signal are measured, then the duty cycle is calculated with the following formula:

-duty cycle = (-pulse width/period)*100

Return Format

```
<value><NL>

<value> ::= ratio of negative pulse width to period in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:PERiod" on page 388
- ":MEASure:NWIDth" on page 384
- ":MEASure:SOURce" on page 399
- ":MEASure:DUTYcycle" on page 378

:MEASure:NEDGes

(see page 828)

Command Syntax

```
:MEASure:NEDGes [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:NEDGes command installs a falling edge count measurement on screen. If the optional source parameter is not specified, the current source is measured.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

Query Syntax

```
:MEASure:NEDGes? [<source>]
```

The :MEASure:NEDGes? query measures and returns the on-screen falling edge count.

Return Format

```
<value><NL>

<value> ::= the falling edge count in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399

:MEASure:NPULses

(see page 828)

Command Syntax

```
:MEASure:NPULses [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:NPULses command installs a falling pulse count measurement on screen. If the optional source parameter is not specified, the current source is measured.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

Query Syntax

```
:MEASure:NPULses? [<source>]
```

The :MEASure:NPULses? query measures and returns the on-screen falling pulse count.

Return Format

```
<value><NL>

<value> ::= the falling pulse count in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399

:MEASure:NWIDth

(see page 828)

Command Syntax

```
:MEASure:NWIDth [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal}

<n> ::= 1 to (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:NWIDth command installs a screen measurement and starts a negative pulse width measurement. If the optional source parameter is not specified, the current source is modified.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

NOTE The EXTernal source is available on 2-channel oscilloscopes only.

Query Syntax

```
:MEASure:NWIDth? [<source>]
```

The :MEASure:NWIDth? query measures and outputs the width of the negative pulse on the screen closest to the trigger reference using the midpoint between the upper and lower thresholds.

FOR the negative pulse closest to the trigger point:

width = (time at trailing rising edge - time at leading falling edge)

Return Format

```
<value><NL>

<value> ::= negative pulse width in seconds in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:PWIDth" on page 392
- ":MEASure:PERiod" on page 388

:MEASure:OVERshoot

(see page 828)

Command Syntax

```
:MEASure:OVERshoot [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:OVERshoot command installs a screen measurement and starts an overshoot measurement. If the optional source parameter is specified, the current source is modified.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

Query Syntax

```
:MEASure:OVERshoot? [<source>]
```

The :MEASure:OVERshoot? query measures and returns the overshoot of the edge closest to the trigger reference, displayed on the screen. The method used to determine overshoot is to make three different vertical value measurements: Vtop, Vbase, and either Vmax or Vmin, depending on whether the edge is rising or falling.

For a rising edge:

overshoot = ((Vmax-Vtop) / (Vtop-Vbase)) x 100

For a falling edge:

overshoot = ((Vbase-Vmin) / (Vtop-Vbase)) x 100

Vtop and Vbase are taken from the normal histogram of all waveform vertical values. The extremum of Vmax or Vmin is taken from the waveform interval right after the chosen edge, halfway to the next edge. This more restricted definition is used instead of the normal one, because it is conceivable that a signal may have more preshoot than overshoot, and the normal extremum would then be dominated by the preshoot of the following edge.

Return Format

```
<overshoot><NL>

<overshoot>::= the percent of the overshoot of the selected waveform in
NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:PREShoot" on page 391
- ":MEASure:SOURce" on page 399
- ":MEASure:VMAX" on page 414

- ":MEASure:VTOP" on page 419
- ":MEASure:VBASe" on page 413
- ":MEASure:VMIN" on page 415

:MEASure:PEDGes

(see page 828)

Command Syntax

```
:MEASure:PEDGes [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:PEDGes command installs a rising edge count measurement on screen. If the optional source parameter is not specified, the current source is measured.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

Query Syntax

```
:MEASure:PEDGes? [<source>]
```

The :MEASure:NEDGes? query measures and returns the on-screen rising edge count.

Return Format

```
<value><NL>

<value> ::= the rising edge count in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399

:MEASure:PERiod

(see page 828)

Command Syntax

```
:MEASure:PERiod [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal}

<n> ::= 1 to (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:PERiod command installs a screen measurement and starts the period measurement. If the optional source parameter is specified, the current source is modified.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

NOTE The EXTernal source is available on 2-channel oscilloscopes only.

Query Syntax

```
:MEASure:PERiod? [<source>]
```

The :MEASure:PERiod? query measures and outputs the period of the cycle closest to the trigger reference on the screen. The period is measured at the midpoint of the upper and lower thresholds.

IF the edge closest to the trigger reference on screen is rising:

THEN period = (time at trailing rising edge - time at leading rising edge)

ELSE period = (time at trailing falling edge - time at leading falling edge)

Return Format

```
<value><NL>

<value> ::= waveform period in seconds in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:NWIDth" on page 384
- ":MEASure:PWIDth" on page 392
- ":MEASure:FREQuency" on page 380

Example Code

- "Example Code" on page 399

:MEASure:PHASe

(see page 828)

Command Syntax

```
:MEASure:PHASe [<source1>][,<source2>]

<source1>, <source2> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:PHASe command places the instrument in the continuous measurement mode and starts a phase measurement.

Query Syntax

```
:MEASure:PHASe? [<source1>][,<source2>]
```

The :MEASure:PHASe? query measures and returns the phase between the specified sources.

A phase measurement is a combination of the period and delay measurements. First, the period is measured on source1. Then the delay is measured between source1 and source2. The edges used for delay are the source1 rising edge used for the period measurement closest to the horizontal reference and the rising edge on source 2. See :MEASure:DELay for more detail on selecting the 2nd edge.

The phase is calculated as follows:

phase = (delay / period of input 1) x 360

Return Format

```
<value><NL>

<value> ::= the phase angle value in degrees in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:DELay" on page 376
- ":MEASure:PERiod" on page 388
- ":MEASure:SOURce" on page 399

:MEASure:PPULses

(see page 828)

Command Syntax

```
:MEASure:PPULses [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:PPULses command installs a rising pulse count measurement on screen. If the optional source parameter is not specified, the current source is measured.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

Query Syntax

```
:MEASure:PPULses? [<source>]
```

The :MEASure:PPULses? query measures and returns the on-screen rising pulse count.

Return Format

```
<value><NL>

<value> ::= the rising pulse count in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399

:MEASure:PREShoot

(see page 828)

Command Syntax

```
:MEASure:PREShoot [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:PREShoot command installs a screen measurement and starts a preshoot measurement. If the optional source parameter is specified, the current source is modified.

Query Syntax

```
:MEASure:PREShoot? [<source>]
```

The :MEASure:PREShoot? query measures and returns the preshoot of the edge closest to the trigger, displayed on the screen. The method used to determine preshoot is to make three different vertical value measurements: Vtop, Vbase, and either Vmin or Vmax, depending on whether the edge is rising or falling.

For a rising edge:

preshoot = ((Vmin-Vbase) / (Vtop-Vbase)) x 100

For a falling edge:

preshoot = ((Vmax-Vtop) / (Vtop-Vbase)) x 100

Vtop and Vbase are taken from the normal histogram of all waveform vertical values. The extremum of Vmax or Vmin is taken from the waveform interval right before the chosen edge, halfway back to the previous edge. This more restricted definition is used instead of the normal one, because it is likely that a signal may have more overshoot than preshoot, and the normal extremum would then be dominated by the overshoot of the preceding edge.

Return Format

```
<value><NL>

<value> ::= the percent of preshoot of the selected waveform
            in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:VMIN" on page 415
- ":MEASure:VMAX" on page 414
- ":MEASure:VTOP" on page 419
- ":MEASure:VBASe" on page 413

:MEASure:PWIDth

(see page 828)

Command Syntax

```
:MEASure:PWIDth [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal}

<n> ::= 1 to (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:PWIDth command installs a screen measurement and starts the positive pulse width measurement. If the optional source parameter is specified, the current source is modified.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

NOTE The EXTernal source is available on 2-channel oscilloscopes only.

Query Syntax

```
:MEASure:PWIDth? [<source>]
```

The :MEASure:PWIDth? query measures and outputs the width of the displayed positive pulse closest to the trigger reference. Pulse width is measured at the midpoint of the upper and lower thresholds.

IF the edge on the screen closest to the trigger is falling:

THEN width = (time at trailing falling edge - time at leading rising edge)

ELSE width = (time at leading falling edge - time at leading rising edge)

Return Format

```
<value><NL>

<value> ::= width of positive pulse in seconds in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:NWIDth" on page 384
- ":MEASure:PERiod" on page 388

:MEASure:RESults

N (see page 828)

Query Syntax

```
:MEASure:RESults?
```

The :MEASure:RESults? query returns the results of the continuously displayed measurements. The response to the MEASure:RESults? query is a list of comma-separated values.

If more than one measurement is running continuously, the :MEASure:RESults return values are duplicated for each continuous measurement from the first to last (left to right) result displayed. Each result returned is separated from the previous result by a comma. There is a maximum of four continuous measurements that can be continuously displayed at a time.

When no quick measurements are installed, the :MEASure:RESults? query returns nothing (empty string). When the count for any of the measurements is 0, the value of infinity (9.9E+37) is returned for the min, max, mean, and standard deviation.

Return Format

```
<result_list><NL>

<result_list> ::= comma-separated list of measurement results
```

The following shows the order of values received for a single measurement if :MEASure:STATistics is set to ON.

Measurement label	current	min	max	mean	std dev	count

Measurement label, current, min, max, mean, std dev, and count are only returned if :MEASure:STATistics is ON.

If :MEASure:STATistics is set to CURRent, MIN, MAX, MEAN, STDDev, or COUNt only that particular statistic value is returned for each measurement that is on.

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:STATistics" on page 401

Example Code

```
' This program shows the InfiniiVision oscilloscopes' measurement
' statistics commands.
' ----------------------------------------------------------------------

Option Explicit

Public myMgr As VisaComLib.ResourceManager
Public myScope As VisaComLib.FormattedIO488
Public varQueryResult As Variant
Public strQueryResult As String
```

```
Private Declare Sub Sleep Lib "kernel32" (ByVal dwMilliseconds As Long)

Sub Main()

  On Error GoTo VisaComError

  ' Create the VISA COM I/O resource.
  Set myMgr = New VisaComLib.ResourceManager
  Set myScope = New VisaComLib.FormattedIO488
  Set myScope.IO = myMgr.Open("TCPIP0::130.29.70.228::inst0::INSTR")

  ' Initialize.
  myScope.IO.Clear   ' Clear the interface.
  myScope.WriteString "*RST"   ' Reset to the defaults.
  myScope.WriteString "*CLS"   ' Clear the status data structures.
  myScope.WriteString ":AUToscale"

  ' Install some measurements.
  myScope.WriteString ":MEASure:SOURce CHANnel1"   ' Input source.

  Dim MeasurementArray(3) As String
  MeasurementArray(0) = "FREQuency"
  MeasurementArray(1) = "DUTYcycle"
  MeasurementArray(2) = "VAMPlitude"
  MeasurementArray(3) = "VPP"
  Dim Measurement As Variant

  For Each Measurement In MeasurementArray
    myScope.WriteString ":MEASure:" + Measurement
    myScope.WriteString ":MEASure:" + Measurement + "?"
    varQueryResult = myScope.ReadNumber   ' Read measurement value.
    Debug.Print Measurement + ": " + FormatNumber(varQueryResult, 4)
  Next

  myScope.WriteString ":MEASure:STATistics:RESet"   ' Reset stats.
  Sleep 5000   ' Wait for 5 seconds.

  ' Select the statistics results type.
  Dim ResultsTypeArray(6) As String
  ResultsTypeArray(0) = "CURRent"
  ResultsTypeArray(1) = "MINimum"
  ResultsTypeArray(2) = "MAXimum"
  ResultsTypeArray(3) = "MEAN"
  ResultsTypeArray(4) = "STDDev"
  ResultsTypeArray(5) = "COUNt"
  ResultsTypeArray(6) = "ON"   ' All results.
  Dim ResultType As Variant

  Dim ResultsList()

  Dim ValueColumnArray(6) As String
  ValueColumnArray(0) = "Meas_Lbl"
  ValueColumnArray(1) = "Current"
  ValueColumnArray(2) = "Min"
  ValueColumnArray(3) = "Max"
  ValueColumnArray(4) = "Mean"
  ValueColumnArray(5) = "Std_Dev"
```

```
  ValueColumnArray(6) = "Count"
  Dim ValueColumn As Variant

  For Each ResultType In ResultsTypeArray
    myScope.WriteString ":MEASure:STATistics " + ResultType

    ' Get the statistics results.
    Dim intCounter As Integer
    intCounter = 0
    myScope.WriteString ":MEASure:RESults?"
    ResultsList() = myScope.ReadList

    For Each Measurement In MeasurementArray

      If ResultType = "ON" Then   ' All statistics.

        For Each ValueColumn In ValueColumnArray
          If VarType(ResultsList(intCounter)) <> vbString Then
            Debug.Print "Measure statistics result CH1, " + _
                Measurement + ", "; ValueColumn + ": " + _
                FormatNumber(ResultsList(intCounter), 4)

          Else   ' Result is a string (e.g., measurement label).
            Debug.Print "Measure statistics result CH1, " + _
                Measurement + ", "; ValueColumn + ": " + _
                ResultsList(intCounter)

          End If

          intCounter = intCounter + 1

        Next

      Else   ' Specific statistic (e.g., Current, Max, Min, etc.).

        Debug.Print "Measure statistics result CH1, " + _
            Measurement + ", "; ResultType + ": " + _
            FormatNumber(ResultsList(intCounter), 4)

        intCounter = intCounter + 1

      End If

    Next

  Next

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error:" + vbCrLf + Err.Description

End Sub
```

:MEASure:RISetime

(see page 828)

Command Syntax

```
:MEASure: RISetime [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:RISetime command installs a screen measurement and starts a rise-time measurement. If the optional source parameter is specified, the current source is modified.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

Query Syntax

```
:MEASure: RISetime? [<source>]
```

The :MEASure:RISetime? query measures and outputs the rise time of the displayed rising (positive-going) edge closest to the trigger reference. For maximum measurement accuracy, set the sweep speed as fast as possible while leaving the leading edge of the waveform on the display. The rise time is determined by measuring the time at the lower threshold of the rising edge and the time at the upper threshold of the rising edge, then calculating the rise time with the following formula:

rise time = time at upper threshold - time at lower threshold

Return Format

```
<value><NL>

<value> ::= rise time in seconds in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:FALLtime" on page 379

:MEASure:SDEViation

(see page 828)

Command Syntax

```
:MEASure:SDEViation [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1-2 or 1-4 (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

NOTE This ":MEASure:VRMS DISPlay, AC" command is the preferred syntax for making standard deviation measurements.

The :MEASure:SDEViation command installs a screen measurement and starts std deviation measurement. If the optional source parameter is specified, the current source is modified.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

Query Syntax

```
:MEASure:SDEViation? [<source>]
```

The :MEASure:SDEViation? query measures and outputs the std deviation of the selected waveform. The oscilloscope computes the std deviation on all displayed data points.

Return Format

```
<value><NL>

<value> ::= calculated std deviation value in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:VRMS" on page 417
- ":MEASure:SOURce" on page 399

:MEASure:SHOW

(see page 828)

Command Syntax

```
:MEASure:SHOW <show>

<show> ::= {1 | ON}
```

The :MEASure:SHOW command enables markers for tracking measurements on the display. This feature is always on.

Query Syntax

```
:MEASure:SHOW?
```

The :MEASure:SHOW? query returns the current state of the markers.

Return Format

```
<show><NL>

<show> ::= 1
```

See Also

- "Introduction to :MEASure Commands" on page 367

:MEASure:SOURce

(see page 828)

Command Syntax

```
:MEASure:SOURce <source1>[,<source2>]

<source1>,<source2> ::= {CHANnel<n> | FUNCtion
                         | MATH | WMEMory<r> | EXTernal}

<n> ::= 1 to (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:SOURce command sets the default sources for measurements. The specified sources are used as the sources for the MEASure subsystem commands if the sources are not explicitly set with the command.

If a source is specified for any measurement, the current source is changed to this new value.

If :MARKer:MODE is set to OFF or MANual, setting :MEASure:SOURce to CHANnel<n>, FUNCtion, or MATH will also set :MARKer:X1Y1source to source1 and :MARKer:X2Y2source to source2.

EXTernal is only a valid source for the counter measurement (and <source1>).

Query Syntax

```
:MEASure:SOURce?
```

The :MEASure:SOURce? query returns the current source selections. Source2 applies only to :MEASure:DELay and :MEASure:PHASe measurements.

NOTE MATH is an alias for FUNCtion. The query will return FUNC if the source is FUNCtion or MATH.

Return Format

```
<source1>,<source2><NL>

<source1>,<source2> ::= {CHAN<n> | FUNC | WMWM<r>
                         | EXT}
```

See Also:

- "Introduction to :MEASure Commands" on page 367
- ":MARKer:MODE" on page 344
- ":MARKer:X1Y1source" on page 346
- ":MARKer:X2Y2source" on page 348
- ":MEASure:DELay" on page 376
- ":MEASure:PHASe" on page 389

Example Code

```
' MEASURE - The commands in the MEASURE subsystem are used to make
' measurements on displayed waveforms.
myScope.WriteString ":MEASURE:SOURCE CHANNEL1"    ' Source to measure.
myScope.WriteString ":MEASURE:FREQUENCY?"    ' Query for frequency.
```

```
varQueryResult = myScope.ReadNumber   ' Read frequency.
MsgBox "Frequency:" + vbCrLf _
      + FormatNumber(varQueryResult / 1000, 4) + " kHz"
myScope.WriteString ":MEASURE:DUTYCYCLE?"   ' Query for duty cycle.
varQueryResult = myScope.ReadNumber   ' Read duty cycle.
MsgBox "Duty cycle:" + vbCrLf _
      + FormatNumber(varQueryResult, 3) + "%"
myScope.WriteString ":MEASURE:RISETIME?"   ' Query for risetime.
varQueryResult = myScope.ReadNumber   ' Read risetime.
MsgBox "Risetime:" + vbCrLf _
      + FormatNumber(varQueryResult * 1000000, 4) + " us"
myScope.WriteString ":MEASURE:VPP?"   ' Query for Pk to Pk voltage.
varQueryResult = myScope.ReadNumber   ' Read VPP.
MsgBox "Peak to peak voltage:" + vbCrLf _
      + FormatNumber(varQueryResult, 4) + " V"
myScope.WriteString ":MEASURE:VMAX?"   ' Query for Vmax.
varQueryResult = myScope.ReadNumber   ' Read Vmax.
MsgBox "Maximum voltage:" + vbCrLf _
      + FormatNumber(varQueryResult, 4) + " V"
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:MEASure:STATistics

(see page 828)

Command Syntax

```
:MEASure:STATistics <type>

<type> ::= {{ON | 1} | CURRent | MINimum | MAXimum | MEAN | STDDev
           | COUNt}
```

The :MEASure:STATistics command determines the type of information returned by the :MEASure:RESults? query. ON means all the statistics are on.

Query Syntax

```
:MEASure:STATistics?
```

The :MEASure:STATistics? query returns the current statistics mode.

Return Format

```
<type><NL>

<type> ::= {ON | CURR | MIN | MAX | MEAN | STDD | COUN}
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:RESults" on page 393
- ":MEASure:STATistics:DISPlay" on page 402
- ":MEASure:STATistics:RESet" on page 405
- ":MEASure:STATistics:INCRement" on page 403

Example Code

- "Example Code" on page 393

:MEASure:STATistics:DISPlay

(see page 828)

Command Syntax `:MEASure:STATistics:DISPlay {{0 | OFF} | {1 | ON}}`

The :MEASure:STATistics:DISPlay command disables or enables the display of the measurement statistics.

Query Syntax `:MEASure:STATistics:DISPlay?`

The :MEASure:STATistics:DISPlay? query returns the state of the measurement statistics display.

Return Format `{0 | 1}<NL>`

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:RESults" on page 393
- ":MEASure:STATistics" on page 401
- ":MEASure:STATistics:MCOunt" on page 404
- ":MEASure:STATistics:RESet" on page 405
- ":MEASure:STATistics:INCRement" on page 403
- ":MEASure:STATistics:RSDeviation" on page 406

:MEASure:STATistics:INCRement

(see page 828)

Command Syntax `:MEASure:STATistics:INCRement`

This command updates the statistics once (incrementing the count by one) using the current measurement values. It corresponds to the front panel **Increment Statistics** softkey in the Measurement Statistics Menu. This command lets you, for example, gather statistics over multiple pulses captured in a single acquisition. To do this, change the horizontal position and enter the command for each new pulse that is measured.

This command is only allowed when the oscilloscope is stopped and quick measurements are on.

The command is allowed in segmented acquisition mode even though the corresponding front panel softkey is not available.

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:STATistics" on page 401
- ":MEASure:STATistics:DISPlay" on page 402
- ":MEASure:STATistics:RESet" on page 405
- ":MEASure:RESults" on page 393

:MEASure:STATistics:MCOunt

(see page 828)

Command Syntax

```
:MEASure:STATistics:MCOunt <setting>

<setting> ::= {INFinite | <count>}

<count> ::= 2 to 2000 in NR1 format
```

The :MEASure:STATistics:MCOunt command specifies the maximum number of values used when calculating measurement statistics.

Query Syntax

```
:MEASure:STATistics:MCOunt?
```

The :MEASure:STATistics:MCOunt? query returns the current measurement statistics max count setting.

Return Format

```
<setting><NL>

<setting> ::= {INF | <count>}

<count> ::= 2 to 2000
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:RESults" on page 393
- ":MEASure:STATistics" on page 401
- ":MEASure:STATistics:DISPlay" on page 402
- ":MEASure:STATistics:RSDeviation" on page 406
- ":MEASure:STATistics:RESet" on page 405
- ":MEASure:STATistics:INCRement" on page 403

:MEASure:STATistics:RESet

(see page 828)

Command Syntax `:MEASure:STATistics:RESet`

This command resets the measurement statistics, zeroing the counts.

Note that the measurement (statistics) configuration is not deleted.

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:STATistics" on page 401
- ":MEASure:STATistics:DISPlay" on page 402
- ":MEASure:RESults" on page 393
- ":MEASure:STATistics:INCRement" on page 403

Example Code

- "Example Code" on page 393

:MEASure:STATistics:RSDeviation

(see page 828)

Command Syntax `:MEASure:STATistics:RSDeviation {{0 | OFF} | {1 | ON}}`

The :MEASure:STATistics:RSDeviation command disables or enables relative standard deviations, that is, standard deviation/mean, in the measurement statistics.

Query Syntax `:MEASure:STATistics:RSDeviation?`

The :MEASure:STATistics:RSDeviation? query returns the current relative standard deviation setting.

Return Format `{0 | 1}<NL>`

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:RESults" on page 393
- ":MEASure:STATistics" on page 401
- ":MEASure:STATistics:DISPlay" on page 402
- ":MEASure:STATistics:MCOunt" on page 404
- ":MEASure:STATistics:RESet" on page 405
- ":MEASure:STATistics:INCRement" on page 403

:MEASure:TEDGe

N (see page 828)

Query Syntax

```
:MEASure:TEDGe? <slope><occurrence>[,<source>]

<slope> ::= direction of the waveform. A rising slope is indicated by a
            space or plus sign (+). A falling edge is indicated by a
            minus sign (-).

<occurrence> ::= the transition to be reported. If the occurrence number
                 is one, the first crossing from the left screen edge is
                 reported.  If the number is two, the second crossing is
                 reported, etc.

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal}

<n> ::= 1 to (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

When the :MEASure:TEDGe query is sent, the displayed signal is searched for the specified transition. The time interval between the trigger event and this occurrence is returned as the response to the query. The sign of the slope selects a rising (+) or falling (-) edge. If no sign is specified for the slope, it is assumed to be the rising edge.

The magnitude of occurrence defines the occurrence to be reported. For example, +3 returns the time for the third time the waveform crosses the midpoint threshold in the positive direction. Once this crossing is found, the oscilloscope reports the time at that crossing in seconds, with the trigger point (time zero) as the reference.

If the specified crossing cannot be found, the oscilloscope reports +9.9E+37. This value is returned if the waveform does not cross the specified vertical value, or if the waveform does not cross the specified vertical value for the specific number of times in the direction specified.

You can make delay and phase measurements using the MEASure:TEDGe command:

Delay = time at the nth rising or falling edge of the channel - time at the same edge of another channel

Phase = (delay between channels / period of channel) x 360

For an example of making a delay and phase measurement, see ":MEASure:TEDGe Code" on page 408.

If the optional source parameter is specified, the current source is modified.

NOTE This query is not available if the source is FFT (Fast Fourier Transform).

NOTE The EXTernal source is available on 2-channel oscilloscopes only.

Return Format

```
<value><NL>

<value> ::= time in seconds of the specified transition in NR3 format
```

:MEASure:TEDGe Code

```
' Make a delay measurement between channel 1 and 2.
Dim dblChan1Edge1 As Double
Dim dblChan2Edge1 As Double
Dim dblChan1Edge2 As Double
Dim dblDelay As Double
Dim dblPeriod As Double
Dim dblPhase As Double

' Query time at 1st rising edge on ch1.
myScope.WriteString ":MEASURE:TEDGE? +1, CHAN1"

' Read time at edge 1 on ch 1.
dblChan1Edge1 = myScope.ReadNumber

' Query time at 1st rising edge on ch2.
myScope.WriteString ":MEASURE:TEDGE? +1, CHAN2"

' Read time at edge 1 on ch 2.
dblChan2Edge1 = myScope.ReadNumber

' Calculate delay time between ch1 and ch2.
dblDelay = dblChan2Edge1 - dblChan1Edge1

' Write calculated delay time to screen.
MsgBox "Delay = " + vbCrLf + CStr(dblDelay)

' Make a phase difference measurement between channel 1 and 2.
' Query time at 1st rising edge on ch1.
myScope.WriteString ":MEASURE:TEDGE? +2, CHAN1"

' Read time at edge 2 on ch 1.
dblChan1Edge2 = myScope.ReadNumber

' Calculate period of ch 1.
dblPeriod = dblChan1Edge2 - dblChan1Edge1

' Calculate phase difference between ch1 and ch2.
dblPhase = (dblDelay / dblPeriod) * 360
MsgBox "Phase = " + vbCrLf + CStr(dblPhase)
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:TVALue" on page 409
- ":MEASure:VTIMe" on page 418

:MEASure:TVALue

(see page 828)

Query Syntax

```
:MEASure:TVALue? <value>, [<slope>]<occurrence>[,<source>]

<value> ::= the vertical value that the waveform must cross.  The
            value can be volts or a math function value such as dB,
            Vs, or V/s.

<slope> ::= direction of the waveform.  A rising slope is indicated
            by a plus sign (+).  A falling edge is indicated by a
            minus sign (-).

<occurrence> ::= the transition to be reported. If the occurrence
                 number is one, the first crossing is reported.  If
                 the number is two, the second crossing is reported,
                 etc.

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

When the :MEASure:TVALue? query is sent, the displayed signal is searched for the specified value level and transition. The time interval between the trigger event and this defined occurrence is returned as the response to the query.

The specified value can be negative or positive. To specify a negative value, use a minus sign (-). The sign of the slope selects a rising (+) or falling (-) edge. If no sign is specified for the slope, it is assumed to be the rising edge.

The magnitude of the occurrence defines the occurrence to be reported. For example, +3 returns the time for the third time the waveform crosses the specified value level in the positive direction. Once this value crossing is found, the oscilloscope reports the time at that crossing in seconds, with the trigger point (time zero) as the reference.

If the specified crossing cannot be found, the oscilloscope reports +9.9E+37. This value is returned if the waveform does not cross the specified value, or if the waveform does not cross the specified value for the specified number of times in the direction specified.

If the optional source parameter is specified, the current source is modified.

NOTE This query is not available if the source is FFT (Fast Fourier Transform).

Return Format

```
<value><NL>

<value> ::= time in seconds of the specified value crossing in
            NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:TEDGe" on page 407
- ":MEASure:VTIMe" on page 418

:MEASure:VAMPlitude

(see page 828)

Command Syntax

```
:MEASure:VAMPlitude [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:VAMPlitude command installs a screen measurement and starts a vertical amplitude measurement. If the optional source parameter is specified, the current source is modified.

Query Syntax

```
:MEASure:VAMPlitude? [<source>]
```

The :MEASure:VAMPlitude? query measures and returns the vertical amplitude of the waveform. To determine the amplitude, the instrument measures Vtop and Vbase, then calculates the amplitude as follows:

vertical amplitude = Vtop - Vbase

Return Format

```
<value><NL>

<value> ::= the amplitude of the selected waveform in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:VBASe" on page 413
- ":MEASure:VTOP" on page 419
- ":MEASure:VPP" on page 416

:MEASure:VAVerage

(see page 828)

Command Syntax

```
:MEASure:VAVerage [<interval>][,][<source>]

<interval> ::= {CYCLe | DISPlay}

<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>}

<n> ::= 1 to (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:VAVerage command installs a screen measurement and starts an average value measurement. If the optional source parameter is specified, the current source is modified.

The <interval> option lets you specify the measurement interval: either an integral number of cycles, or the full screen. If <interval> is not specified, DISPlay is implied.

Query Syntax

```
:MEASure:VAVerage? [<interval>][,][<source>]
```

The :MEASure:VAVerage? query returns the average value of an integral number of periods of the signal. If at least three edges are not present, the oscilloscope averages all data points.

Return Format

```
<value><NL>

<value> ::= calculated average value in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399

:MEASure:VBASe

(see page 828)

Command Syntax

```
:MEASure:VBASe [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:VBASe command installs a screen measurement and starts a waveform base value measurement. If the optional source parameter is specified, the current source is modified.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

Query Syntax

```
:MEASure:VBASe? [<source>]
```

The :MEASure:VBASe? query returns the vertical value at the base of the waveform. The base value of a pulse is normally not the same as the minimum value.

Return Format

```
<base_voltage><NL>

<base_voltage> ::= value at the base of the selected waveform in
                   NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:VTOP" on page 419
- ":MEASure:VAMPlitude" on page 411
- ":MEASure:VMIN" on page 415

:MEASure:VMAX

(see page 828)

Command Syntax

```
:MEASure:VMAX [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>}

<n> ::= 1 to (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:VMAX command installs a screen measurement and starts a maximum vertical value measurement. If the optional source parameter is specified, the current source is modified.

Query Syntax

```
:MEASure:VMAX? [<source>]
```

The :MEASure:VMAX? query measures and outputs the maximum vertical value present on the selected waveform.

Return Format

```
<value><NL>

<value> ::= maximum vertical value of the selected waveform in
            NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:VMIN" on page 415
- ":MEASure:VPP" on page 416
- ":MEASure:VTOP" on page 419

:MEASure:VMIN

(see page 828)

Command Syntax

```
:MEASure:VMIN [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:VMIN command installs a screen measurement and starts a minimum vertical value measurement. If the optional source parameter is specified, the current source is modified.

Query Syntax

```
:MEASure:VMIN? [<source>]
```

The :MEASure:VMIN? query measures and outputs the minimum vertical value present on the selected waveform.

Return Format

```
<value><NL>

<value> ::= minimum vertical value of the selected waveform in
            NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:VBASe" on page 413
- ":MEASure:VMAX" on page 414
- ":MEASure:VPP" on page 416

:MEASure:VPP

(see page 828)

Command Syntax

```
:MEASure:VPP [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:VPP command installs a screen measurement and starts a vertical peak-to-peak measurement. If the optional source parameter is specified, the current source is modified.

Query Syntax

```
:MEASure:VPP? [<source>]
```

The :MEASure:VPP? query measures the maximum and minimum vertical value for the selected source, then calculates the vertical peak-to-peak value and returns that value. The peak-to-peak value (Vpp) is calculated with the following formula:

Vpp = Vmax - Vmin

Vmax and Vmin are the vertical maximum and minimum values present on the selected source.

Return Format

```
<value><NL>

<value> ::= vertical peak to peak value in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:VMAX" on page 414
- ":MEASure:VMIN" on page 415
- ":MEASure:VAMPlitude" on page 411

:MEASure:VRMS

(see page 828)

Command Syntax

```
:MEASure:VRMS [<interval>][,<type>][,<source>]

<interval> ::= {CYCLe | DISPlay}

<type> ::= {AC | DC}

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:VRMS command installs a screen measurement and starts an RMS value measurement. If the optional source parameter is specified, the current source is modified.

The <interval> option lets you specify the measurement interval: either an integral number of cycles, or the full screen. If <interval> is not specified, DISPlay is implied.

The <type> option lets you choose between a DC RMS measurement and an AC RMS measurement. If <type> is not specified, DC is implied.

NOTE This command is not available if the source is FFT (Fast Fourier Transform).

Query Syntax

```
:MEASure:VRMS? [<interval>][,<type>][,<source>]
```

The :MEASure:VRMS? query measures and outputs the dc RMS value of the selected waveform. The dc RMS value is measured on an integral number of periods of the displayed signal. If at least three edges are not present, the oscilloscope computes the RMS value on all displayed data points.

Return Format

```
<value><NL>

<value> ::= calculated dc RMS value in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399

:MEASure:VTIMe

(see page 828)

Query Syntax

```
:MEASure:VTIMe? <vtime_argument>[,<source>]

<vtime_argument> ::= time from trigger in seconds

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r> | EXTernal}

<n> ::= 1 to (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:VTIMe? query returns the value at a specified time on the source specified with :MEASure:SOURce. The specified time must be on the screen and is referenced to the trigger event. If the optional source parameter is specified, the current source is modified.

For the EXT digital waveform source, the returned value is either 1 or 0, based on the threshold voltage setting.

NOTE This query is not available if the source is FFT (Fast Fourier Transform).

NOTE The EXTernal source is available on 2-channel oscilloscopes only.

Return Format

```
<value><NL>

<value> ::= value at the specified time in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:TEDGe" on page 407
- ":MEASure:TVALue" on page 409

:MEASure:VTOP

(see page 828)

Command Syntax

```
:MEASure:VTOP [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:VTOP command installs a screen measurement and starts a waveform top value measurement.

NOTE This query is not available if the source is FFT (Fast Fourier Transform).

Query Syntax

```
:MEASure:VTOP? [<source>]
```

The :MEASure:VTOP? query returns the vertical value at the top of the waveform. The top value of the pulse is normally not the same as the maximum value.

Return Format

```
<value><NL>

<value> ::= vertical value at the top of the waveform in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399
- ":MEASure:VMAX" on page 414
- ":MEASure:VAMPlitude" on page 411
- ":MEASure:VBASe" on page 413

:MEASure:WINDow

(see page 828)

Command Syntax

```
:MEASure:WINDow <type>

<type> ::= {MAIN | ZOOM | AUTO}
```

When the zoomed time base is displayed, the :MEASure:WINDow command lets you specify the measurement window:

- MAIN – the measurement window is the upper, Main window.
- ZOOM – the measurement window is the lower, Zoom window.
- AUTO – the measurement is attempted in the lower, Zoom window; if it cannot be made there, the upper, Main window is used.

Query Syntax

```
:MEASure:WINDow?
```

The :MEASure:WINDow? query returns the current measurement window setting.

Return Format

```
<type><NL>

<type> ::= {MAIN | ZOOM | AUTO}
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:SOURce" on page 399

:MEASure:XMAX

(see page 828)

Command Syntax

```
:MEASure:XMAX [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1-2 or 1-4 (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:XMAX command installs a screen measurement and starts an X-at-Max-Y measurement on the selected window. If the optional source parameter is specified, the current source is modified.

NOTE :MEASure:XMAX is an alias for :MEASure:TMAX.

Query Syntax

```
:MEASure:XMAX? [<source>]
```

The :MEASure:XMAX? query measures and returns the horizontal axis value at which the maximum vertical value occurs. If the optional source is specified, the current source is modified.

Return Format

```
<value><NL>

<value> ::= horizontal value of the maximum in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:XMIN" on page 422
- ":MEASure:TMAX" on page 765

:MEASure:XMIN

N (see page 828)

Command Syntax

```
:MEASure:XMIN [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1-2 or 1-4 (# of analog channels) in NR1 format

<r> ::= 1-2 in NR1 format
```

The :MEASure:XMIN command installs a screen measurement and starts an X-at-Min-Y measurement on the selected window. If the optional source parameter is specified, the current source is modified.

NOTE :MEASure:XMIN is an alias for :MEASure:TMIN.

Query Syntax

```
:MEASure:XMIN? [<source>]
```

The :MEASure:XMIN? query measures and returns the horizontal axis value at which the minimum vertical value occurs. If the optional source is specified, the current source is modified.

Return Format

```
<value><NL>

<value> ::= horizontal value of the minimum in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:XMAX" on page 421
- ":MEASure:TMIN" on page 766

22 :MTESt Commands

Mask testing is available on the DSOX1200-Series oscilloscope models.

The MTESt subsystem commands and queries control the mask test features. See "Introduction to :MTESt Commands" on page 425.

Table 68 :MTESt Commands Summary

Command	Query	Options and Query Returns
:MTESt:ALL {{0 | OFF} | {1 | ON}} (see page 428)	:MTESt:ALL? (see page 428)	{0 | 1}
:MTESt:AMASk:CREate (see page 429)	n/a	n/a
:MTESt:AMASk:SOURce <source> (see page 430)	:MTESt:AMASk:SOURce? (see page 430)	<source> ::= CHANnel<n> <n> ::= {1 | 2 | 3 | 4} for 4ch models <n> ::= {1 | 2} for 2ch models
:MTESt:AMASk:UNITs <units> (see page 431)	:MTESt:AMASk:UNITs? (see page 431)	<units> ::= {CURRent | DIVisions}
:MTESt:AMASk:XDELta <value> (see page 432)	:MTESt:AMASk:XDELta? (see page 432)	<value> ::= X delta value in NR3 format
:MTESt:AMASk:YDELta <value> (see page 433)	:MTESt:AMASk:YDELta? (see page 433)	<value> ::= Y delta value in NR3 format
n/a	:MTESt:COUNt:FWAVeforms? [CHANnel<n>] (see page 434)	<failed> ::= number of failed waveforms in NR1 format
:MTESt:COUNt:RESet (see page 435)	n/a	n/a
n/a	:MTESt:COUNt:TIME? (see page 436)	<time> ::= elapsed seconds in NR3 format
n/a	:MTESt:COUNt:WAVeforms? (see page 437)	<count> ::= number of waveforms in NR1 format

Table 68 :MTESt Commands Summary (continued)

Command	Query	Options and Query Returns
:MTESt:DATA <mask> (see page 438)	:MTESt:DATA? (see page 438)	<mask> ::= data in IEEE 488.2 # format.
:MTESt:DELete (see page 439)	n/a	n/a
:MTESt:ENABle {{0 | OFF} | {1 | ON}} (see page 440)	:MTESt:ENABle? (see page 440)	{0 | 1}
:MTESt:LOCK {{0 | OFF} | {1 | ON}} (see page 441)	:MTESt:LOCK? (see page 441)	{0 | 1}
:MTESt:RMODe <rmode> (see page 442)	:MTESt:RMODe? (see page 442)	<rmode> ::= {FOREver | TIME | SIGMa | WAVeforms}
:MTESt:RMODe:FACTion:MEASure {{0 | OFF} | {1 | ON}} (see page 443)	:MTESt:RMODe:FACTion:MEASure? (see page 443)	{0 | 1}
:MTESt:RMODe:FACTion:PRINt {{0 | OFF} | {1 | ON}} (see page 444)	:MTESt:RMODe:FACTion:PRINt? (see page 444)	{0 | 1}
:MTESt:RMODe:FACTion:SAVE {{0 | OFF} | {1 | ON}} (see page 445)	:MTESt:RMODe:FACTion:SAVE? (see page 445)	{0 | 1}
:MTESt:RMODe:FACTion:STOP {{0 | OFF} | {1 | ON}} (see page 446)	:MTESt:RMODe:FACTion:STOP? (see page 446)	{0 | 1}
:MTESt:RMODe:SIGMa <level> (see page 447)	:MTESt:RMODe:SIGMa? (see page 447)	<level> ::= from 0.1 to 9.3 in NR3 format
:MTESt:RMODe:TIME <seconds> (see page 448)	:MTESt:RMODe:TIME? (see page 448)	<seconds> ::= from 1 to 86400 in NR3 format
:MTESt:RMODe:WAVeforms <count> (see page 449)	:MTESt:RMODe:WAVeforms? (see page 449)	<count> ::= number of waveforms in NR1 format
:MTESt:SCALe:BIND {{0 | OFF} | {1 | ON}} (see page 450)	:MTESt:SCALe:BIND? (see page 450)	{0 | 1}
:MTESt:SCALe:X1 <x1_value> (see page 451)	:MTESt:SCALe:X1? (see page 451)	<x1_value> ::= X1 value in NR3 format

Table 68 :MTESt Commands Summary (continued)

Command	Query	Options and Query Returns
:MTESt:SCALe:XDELta <xdelta_value> (see page 452)	:MTESt:SCALe:XDELta? (see page 452)	<xdelta_value> ::= X delta value in NR3 format
:MTESt:SCALe:Y1 <y1_value> (see page 453)	:MTESt:SCALe:Y1? (see page 453)	<y1_value> ::= Y1 value in NR3 format
:MTESt:SCALe:Y2 <y2_value> (see page 454)	:MTESt:SCALe:Y2? (see page 454)	<y2_value> ::= Y2 value in NR3 format
:MTESt:SOURce <source> (see page 455)	:MTESt:SOURce? (see page 455)	<source> ::= {CHANnel<n> | NONE} <n> ::= {1 | 2 | 3 | 4} for 4ch models <n> ::= {1 | 2} for 2ch models
n/a	:MTESt:TITLe? (see page 456)	<title> ::= a string of up to 128 ASCII characters

Introduction to :MTESt Commands

Mask testing automatically compares the current displayed waveform with the boundaries of a set of polygons that you define. Any waveform or sample that falls within the boundaries of one or more polygons is recorded as a failure.

Reporting the Setup

Use :MTESt? to query setup information for the MTESt subsystem.

Return Format

The following is a sample response from the :MTESt? query. In this case, the query was issued following a *RST command.

```
:MTES:SOUR CHAN1;ENAB 0;LOCK 1;:MTES:AMAS:SOUR CHAN1;UNIT DIV;XDEL
+2.50000000E-001;YDEL +2.50000000E-001;:MTES:SCAL:X1 +200.000E-06;XDEL
+400.000E-06;Y1 -3.00000E+00;Y2 +3.00000E+00;BIND 0;:MTES:RMOD
FOR;RMOD:TIME +1E+00;WAV 1000;SIGM +6.0E+00;:MTES:RMOD:FACT:STOP
0;PRIN 0;SAVE 0
```

Example Code

```
' Mask testing commands example.
' ----------------------------------------------------------------------

Option Explicit

Public myMgr As VisaComLib.ResourceManager
Public myScope As VisaComLib.FormattedIO488
Public varQueryResult As Variant
Public strQueryResult As String
```

```
Private Declare Sub Sleep Lib "kernel32" (ByVal dwMilliseconds As Long)

Sub Main()

  On Error GoTo VisaComError

  ' Create the VISA COM I/O resource.
  Set myMgr = New VisaComLib.ResourceManager
  Set myScope = New VisaComLib.FormattedIO488
  Set myScope.IO = _
        myMgr.Open("USB0::0x0957::0x17A6::US50210029::0::INSTR")
  myScope.IO.Clear   ' Clear the interface.

  ' Make sure oscilloscope is running.
  myScope.WriteString ":RUN"

  ' Set mask test termination conditions.
  myScope.WriteString ":MTESt:RMODe SIGMa"
  myScope.WriteString ":MTESt:RMODe?"
  strQueryResult = myScope.ReadString
  Debug.Print "Mask test termination mode: " + strQueryResult

  myScope.WriteString ":MTESt:RMODe:SIGMa 4.2"
  myScope.WriteString ":MTESt:RMODe:SIGMa?"
  varQueryResult = myScope.ReadNumber
  Debug.Print "Mask test termination 'test sigma': " + _
      FormatNumber(varQueryResult)

  ' Use auto-mask to create mask.
  myScope.WriteString ":MTESt:AMASk:SOURce CHANnel1"
  myScope.WriteString ":MTESt:AMASk:SOURce?"
  strQueryResult = myScope.ReadString
  Debug.Print "Mask test auto-mask source: " + strQueryResult

  myScope.WriteString ":MTESt:AMASk:UNITs DIVisions"
  myScope.WriteString ":MTESt:AMASk:UNITs?"
  strQueryResult = myScope.ReadString
  Debug.Print "Mask test auto-mask units: " + strQueryResult

  myScope.WriteString ":MTESt:AMASk:XDELta 0.1"
  myScope.WriteString ":MTESt:AMASk:XDELta?"
  varQueryResult = myScope.ReadNumber
  Debug.Print "Mask test auto-mask X delta: " + _
      FormatNumber(varQueryResult)

  myScope.WriteString ":MTESt:AMASk:YDELta 0.1"
  myScope.WriteString ":MTESt:AMASk:YDELta?"
  varQueryResult = myScope.ReadNumber
  Debug.Print "Mask test auto-mask Y delta: " + _
      FormatNumber(varQueryResult)

  ' Enable "Auto Mask Created" event (bit 10, &H400)
  myScope.WriteString "*CLS"
  myScope.WriteString ":MTEenable " + CStr(CInt("&H400"))

  ' Create mask.
```

```
  myScope.WriteString ":MTESt:AMASk:CREate"
  Debug.Print "Auto-mask created, mask test automatically enabled."

  ' Set up timeout variables.
  Dim lngTimeout As Long   ' Max millisecs to wait.
  Dim lngElapsed As Long
  lngTimeout = 60000   ' 60 seconds.

  ' Wait until mask is created.
  lngElapsed = 0
  Do While lngElapsed <= lngTimeout
    myScope.WriteString ":OPERegister:CONDition?"
    varQueryResult = myScope.ReadNumber
    ' Operation Status Condition Register MTE bit (bit 9, &H200).
    If (varQueryResult And &H200) <> 0 Then
      Exit Do
    Else
      Sleep 100   ' Small wait to prevent excessive queries.
      lngElapsed = lngElapsed + 100
    End If
  Loop

  ' Look for RUN bit = stopped (mask test termination).
  lngElapsed = 0
  Do While lngElapsed <= lngTimeout
    myScope.WriteString ":OPERegister:CONDition?"
    varQueryResult = myScope.ReadNumber
    ' Operation Status Condition Register RUN bit (bit 3, &H8).
    If (varQueryResult And &H8) = 0 Then
      Exit Do
    Else
      Sleep 100   ' Small wait to prevent excessive queries.
      lngElapsed = lngElapsed + 100
    End If
  Loop

  ' Get total waveforms, failed waveforms, and test time.
  myScope.WriteString ":MTESt:COUNt:WAVeforms?"
  strQueryResult = myScope.ReadString
  Debug.Print "Mask test total waveforms: " + strQueryResult

  myScope.WriteString ":MTESt:COUNt:FWAVeforms?"
  strQueryResult = myScope.ReadString
  Debug.Print "Mask test failed waveforms: " + strQueryResult

  myScope.WriteString ":MTESt:COUNt:TIME?"
  strQueryResult = myScope.ReadString
  Debug.Print "Mask test elapsed seconds: " + strQueryResult

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error:" + vbCrLf + Err.Description

End Sub
```

:MTESt:ALL

(see page 828)

Command Syntax

```
:MTESt:ALL <on_off>

<on_off> ::= {{1 | ON} | {0 | OFF}}
```

The :MTESt:ALL command specifies the channel(s) that are included in the mask test:

- ON – All displayed analog channels are included in the mask test.
- OFF – Just the selected source channel is included in the test.

Query Syntax

```
:MTESt:ENABle?
```

The :MTESt:ENABle? query returns the current setting.

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- "Introduction to :MTESt Commands" on page 425

:MTESt:AMASk:CREate

(see page 828)

Command Syntax `:MTESt:AMASk:CREate`

The :MTESt:AMASk:CREate command automatically constructs a mask around the current selected channel, using the tolerance parameters defined by the :MTESt:AMASk:XDELta, :MTESt:AMASk:YDELta, and :MTESt:AMASk:UNITs commands. The mask only encompasses the portion of the waveform visible on the display, so you must ensure that the waveform is acquired and displayed consistently to obtain repeatable results.

The :MTESt:SOURce command selects the channel and should be set before using this command.

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:AMASk:XDELta" on page 432
- ":MTESt:AMASk:YDELta" on page 433
- ":MTESt:AMASk:UNITs" on page 431
- ":MTESt:AMASk:SOURce" on page 430
- ":MTESt:SOURce" on page 455

Example Code

- "Example Code" on page 425

:MTESt:AMASk:SOURce

(see page 828)

Command Syntax

```
:MTESt:AMASk:SOURce <source>

<source> ::= CHANnel<n>

<n> ::= 1 to (# analog channels) in NR1 format
```

The :MTESt:AMASk:SOURce command selects the source for the interpretation of the :MTESt:AMASk:XDELta and :MTESt:AMASk:YDELta parameters when :MTESt:AMASk:UNITs is set to CURRent.

When UNITs are CURRent, the XDELta and YDELta parameters are defined in terms of the channel units, as set by the :CHANnel<n>:UNITs command, of the selected source.

Suppose that UNITs are CURRent and that you set SOURce to CHANNEL1, which is using units of volts. Then you can define AMASk:XDELta in terms of volts and AMASk:YDELta in terms of seconds.

This command is the same as the :MTESt:SOURce command.

Query Syntax

```
:MTESt:AMASk:SOURce?
```

The :MTESt:AMASk:SOURce? query returns the currently set source.

Return Format

```
<source> ::= CHAN<n>

<n> ::= 1 to (# analog channels) in NR1 format
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:AMASk:XDELta" on page 432
- ":MTESt:AMASk:YDELta" on page 433
- ":MTESt:AMASk:UNITs" on page 431
- ":MTESt:SOURce" on page 455

Example Code

- "Example Code" on page 425

:MTESt:AMASk:UNITs

N (see page 828)

Command Syntax

```
:MTESt:AMASk:UNITs <units>

<units> ::= {CURRent | DIVisions}
```

The :MTESt:AMASk:UNITs command alters the way the mask test subsystem interprets the tolerance parameters for automasking as defined by :MTESt:AMASk:XDELta and :MTESt:AMASk:YDELta commands.

- CURRent – the mask test subsystem uses the units as set by the :CHANnel<n>:UNITs command, usually time for ΔX and voltage for ΔY.
- DIVisions – the mask test subsystem uses the graticule as the measurement system, so tolerance settings are specified as parts of a screen division. The mask test subsystem maintains separate XDELta and YDELta settings for CURRent and DIVisions. Thus, XDELta and YDELta are not converted to new values when the UNITs setting is changed.

Query Syntax

```
:MTESt:AMASk:UNITs?
```

The :MTESt:AMASk:UNITs query returns the current measurement units setting for the mask test automask feature.

Return Format

```
<units><NL>

<units> ::= {CURR | DIV}
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:AMASk:XDELta" on page 432
- ":MTESt:AMASk:YDELta" on page 433
- ":CHANnel<n>:UNITs" on page 230
- ":MTESt:AMASk:SOURce" on page 430
- ":MTESt:SOURce" on page 455

Example Code

- "Example Code" on page 425

:MTESt:AMASk:XDELta

(see page 828)

Command Syntax

```
:MTESt:AMASk:XDELta <value>

<value> ::= X delta value in NR3 format
```

The :MTESt:AMASk:XDELta command sets the tolerance in the X direction around the waveform for the automasking feature. The absolute value of the tolerance will be added and subtracted to horizontal values of the waveform to determine the boundaries of the mask.

The horizontal tolerance value is interpreted based on the setting specified by the :MTESt:AMASk:UNITs command; thus, if you specify 250-E3, the setting for :MTESt:AMASk:UNITs is CURRent, and the current setting specifies time in the horizontal direction, the tolerance will be ±250 ms. If the setting for :MTESt:AMASk:UNITs is DIVisions, the same X delta value will set the tolerance to ±250 millidivisions, or 1/4 of a division.

Query Syntax

```
:MTESt:AMASk:XDELta?
```

The :MTEST:AMASk:XDELta? query returns the current setting of the ΔX tolerance for automasking. If your computer program will interpret this value, it should also request the current measurement system using the :MTESt:AMASk:UNITs query.

Return Format

```
<value><NL>

<value> ::= X delta value in NR3 format
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:AMASk:UNITs" on page 431
- ":MTESt:AMASk:YDELta" on page 433
- ":MTESt:AMASk:SOURce" on page 430
- ":MTESt:SOURce" on page 455

Example Code

- "Example Code" on page 425

:MTESt:AMASk:YDELta

(see page 828)

Command Syntax

```
:MTESt:AMASk:YDELta <value>

<value> ::= Y delta value in NR3 format
```

The :MTESt:AMASk:YDELta command sets the vertical tolerance around the waveform for the automasking feature. The absolute value of the tolerance will be added and subtracted to vertical values of the waveform to determine the boundaries of the mask.

The vertical tolerance value is interpreted based on the setting specified by the :MTESt:AMASk:UNITs command; thus, if you specify 250-E3, the setting for :MTESt:AMASk:UNITs is CURRent, and the current setting specifies voltage in the vertical direction, the tolerance will be ±250 mV. If the setting for :MTESt:AMASk:UNITs is DIVisions, the same Y delta value will set the tolerance to ±250 millidivisions, or 1/4 of a division.

Query Syntax

```
:MTESt:AMASk:YDELta?
```

The :MTESt:AMASk:YDELta? query returns the current setting of the ΔY tolerance for automasking. If your computer program will interpret this value, it should also request the current measurement system using the :MTESt:AMASk:UNITs query.

Return Format

```
<value><NL>

<value> ::= Y delta value in NR3 format
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:AMASk:UNITs" on page 431
- ":MTESt:AMASk:XDELta" on page 432
- ":MTESt:AMASk:SOURce" on page 430
- ":MTESt:SOURce" on page 455

Example Code

- "Example Code" on page 425

:MTESt:COUNt:FWAVeforms

(see page 828)

Query Syntax

```
:MTESt:COUNt:FWAVeforms? [CHANnel<n>]

<n> ::= 1 to (# analog channels) in NR1 format
```

The :MTESt:COUNt:FWAVeforms? query returns the total number of failed waveforms in the current mask test run. This count is for all regions and all waveforms collected on the channel specified by the optional parameter or collected on the currently specified source channel (:MTESt:SOURce) if there is no parameter.

Return Format

```
<failed><NL>

<failed> ::= number of failed waveforms in NR1 format.
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:COUNt:WAVeforms" on page 437
- ":MTESt:COUNt:TIME" on page 436
- ":MTESt:COUNt:RESet" on page 435
- ":MTESt:SOURce" on page 455

Example Code

- "Example Code" on page 425

:MTESt:COUNt:RESet

(see page 828)

Command Syntax `:MTESt:COUNt:RESet`

The :MTESt:COUNt:RESet command resets the mask statistics.

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:COUNt:WAVeforms" on page 437
- ":MTESt:COUNt:FWAVeforms" on page 434
- ":MTESt:COUNt:TIME" on page 436

:MTESt:COUNt:TIME

(see page 828)

Query Syntax

```
:MTESt:COUNt:TIME?
```

The :MTESt:COUNt:TIME? query returns the elapsed time in the current mask test run.

Return Format

```
<time><NL>

<time> ::= elapsed seconds in NR3 format.
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:COUNt:WAVeforms" on page 437
- ":MTESt:COUNt:FWAVeforms" on page 434
- ":MTESt:COUNt:RESet" on page 435

Example Code

- "Example Code" on page 425

:MTESt:COUNt:WAVeforms

(see page 828)

Query Syntax

```
:MTESt:COUNt:WAVeforms?
```

The :MTESt:COUNt:WAVeforms? query returns the total number of waveforms acquired in the current mask test run.

Return Format

```
<count><NL>

<count> ::= number of waveforms in NR1 format.
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:COUNt:FWAVeforms" on page 434
- ":MTESt:COUNt:TIME" on page 436
- ":MTESt:COUNt:RESet" on page 435

Example Code

- "Example Code" on page 425

:MTESt:DATA

(see page 828)

Command Syntax

```
:MTESt:DATA <mask>

<mask> ::= binary block data in IEEE 488.2 # format.
```

The :MTESt:DATA command loads a mask from binary block data. These are the data bytes found in a *.msk file.

Query Syntax

```
:MTESt:DATA?
```

The :MTESt:DATA? query returns a mask in binary block data format. The format for the data transmission is the # definite-length format defined in the IEEE 488.2 specification.

Return Format

```
<mask><NL>

<mask> ::= binary block data in IEEE 488.2 # format
```

See Also

- ":SAVE:MASK[:STARt]" on page 475
- ":RECall:MASK[:STARt]" on page 460

:MTESt:DELete

(see page 828)

Command Syntax `:MTESt:DELete`

The :MTESt:DELete command clears the currently loaded mask.

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:AMASk:CREate" on page 429

:MTESt:ENABle

(see page 828)

Command Syntax

```
:MTESt:ENABle <on_off>
<on_off> ::= {{1 | ON} | {0 | OFF}}
```

The :MTESt:ENABle command enables or disables the mask test features.

- ON – Enables the mask test features.
- OFF – Disables the mask test features.

Query Syntax

```
:MTESt:ENABle?
```

The :MTESt:ENABle? query returns the current state of mask test features.

Return Format

```
<on_off><NL>
<on_off> ::= {1 | 0}
```

See Also

- "Introduction to :MTESt Commands" on page 425

:MTESt:LOCK

(see page 828)

Command Syntax

```
:MTESt:LOCK <on_off>

<on_off> ::= {{1 | ON} | {0 | OFF}}
```

The :MTESt:LOCK command enables or disables the mask lock feature:

- ON – Locks a mask to the SOURce. As the vertical or horizontal scaling or position of the SOURce changes, the mask is redrawn accordingly.
- OFF – The mask is static and does not move.

Query Syntax

```
:MTESt:LOCK?
```

The :MTESt:LOCK? query returns the current mask lock setting.

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:SOURce" on page 455

:MTESt:RMODe

(see page 828)

Command Syntax

```
:MTESt:RMODe <rmode>

<rmode> ::= {FORever | SIGMa | TIME | WAVeforms}
```

The :MTESt:RMODe command specifies the termination conditions for the mask test:

- FORever – the mask test runs until it is turned off.
- SIGMa – the mask test runs until the Sigma level is reached. This level is set by the ":MTESt:RMODe:SIGMa" on page 447 command.
- TIME – the mask test runs for a fixed amount of time. The amount of time is set by the ":MTESt:RMODe:TIME" on page 448 command.
- WAVeforms – the mask test runs until a fixed number of waveforms are acquired. The number of waveforms is set by the ":MTESt:RMODe:WAVeforms" on page 449 command.

Query Syntax

```
:MTESt:RMODe?
```

The :MTESt:RMODe? query returns the currently set termination condition.

Return Format

```
<rmode><NL>

<rmode> ::= {FOR | SIGM | TIME | WAV}
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:RMODe:SIGMa" on page 447
- ":MTESt:RMODe:TIME" on page 448
- ":MTESt:RMODe:WAVeforms" on page 449

Example Code

- "Example Code" on page 425

:MTESt:RMODe:FACTion:MEASure

(see page 828)

Command Syntax

```
:MTESt:RMODe:FACTion:MEASure <on_off>

<on_off> ::= {{1 | ON} | {0 | OFF}}
```

The :MTESt:RMODe:FACTion:MEASure command sets measuring only mask failures on or off.

When ON, measurements and measurement statistics run only on waveforms that contain a mask violation; passing waveforms do not affect measurements and measurement statistics.

This mode is not available when the acquisition mode is set to Averaging.

Query Syntax

```
:MTESt:RMODe:FACTion:MEASure?
```

The :MTESt:RMODe:FACTion:MEASure? query returns the current mask failure measure setting.

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:RMODe:FACTion:PRINt" on page 444
- ":MTESt:RMODe:FACTion:SAVE" on page 445
- ":MTESt:RMODe:FACTion:STOP" on page 446

:MTESt:RMODe:FACTion:PRINt

(see page 828)

Command Syntax

```
:MTESt:RMODe:FACTion:PRINt <on_off>

<on_off> ::= {{1 | ON} | {0 | OFF}}
```

The :MTESt:RMODe:FACTion:PRINt command sets printing on mask failures on or off.

NOTE **Setting :MTESt:RMODe:FACTion:PRINt ON automatically sets :MTESt:RMODe:FACTion:SAVE OFF.**

See Chapter 18, ":HARDcopy Commands," starting on page 323 for more information on setting the hardcopy device and formatting options.

Query Syntax

```
:MTESt:RMODe:FACTion:PRINt?
```

The :MTESt:RMODe:FACTion:PRINt? query returns the current mask failure print setting.

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:RMODe:FACTion:MEASure" on page 443
- ":MTESt:RMODe:FACTion:SAVE" on page 445
- ":MTESt:RMODe:FACTion:STOP" on page 446

:MTESt:RMODe:FACTion:SAVE

(see page 828)

Command Syntax

```
:MTESt:RMODe:FACTion:SAVE <on_off>

<on_off> ::= {{1 | ON} | {0 | OFF}}
```

The :MTESt:RMODe:FACTion:SAVE command sets saving on mask failures on or off.

NOTE **Setting :MTESt:RMODe:FACTion:SAVE ON automatically sets :MTESt:RMODe:FACTion:PRINt OFF.**

See Chapter 24, ":SAVE Commands," starting on page 465 for more information on save options.

Query Syntax

```
:MTESt:RMODe:FACTion:SAVE?
```

The :MTESt:RMODe:FACTion:SAVE? query returns the current mask failure save setting.

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:RMODe:FACTion:MEASure" on page 443
- ":MTESt:RMODe:FACTion:PRINt" on page 444
- ":MTESt:RMODe:FACTion:STOP" on page 446

:MTESt:RMODe:FACTion:STOP

(see page 828)

Command Syntax

```
:MTESt:RMODe:FACTion:STOP <on_off>

<on_off> ::= {{1 | ON} | {0 | OFF}}
```

The :MTESt:RMODe:FACTion:STOP command sets stopping on a mask failure on or off. When this setting is ON and a mask violation is detected, the mask test is stopped and the acquisition system is stopped.

Query Syntax

```
:MTESt:RMODe:FACTion:STOP?
```

The :MTESt:RMODe:FACTion:STOP? query returns the current mask failure stop setting.

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:RMODe:FACTion:MEASure" on page 443
- ":MTESt:RMODe:FACTion:PRINt" on page 444
- ":MTESt:RMODe:FACTion:SAVE" on page 445

:MTESt:RMODe:SIGMa

(see page 828)

Command Syntax

```
:MTESt:RMODe:SIGMa <level>

<level> ::= from 0.1 to 9.3 in NR3 format
```

When the :MTESt:RMODe command is set to SIGMa, the :MTESt:RMODe:SIGMa command sets the *test sigma* level to which a mask test runs. *Test sigma* is the best achievable process sigma, assuming no failures. (*Process sigma* is calculated using the number of failures per test.) The *test sigma* level indirectly specifies the number of waveforms that must be tested (in order to reach the sigma level).

Query Syntax

```
:MTESt:RMODe:SIGMa?
```

The :MTESt:RMODe:SIGMa? query returns the current Sigma level setting.

Return Format

```
<level><NL>

<level> ::= from 0.1 to 9.3 in NR3 format
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:RMODe" on page 442

Example Code

- "Example Code" on page 425

:MTESt:RMODe:TIME

(see page 828)

Command Syntax

```
:MTESt:RMODe:TIME <seconds>

<seconds> ::= from 1 to 86400 in NR3 format
```

When the :MTESt:RMODe command is set to TIME, the :MTESt:RMODe:TIME command sets the number of seconds for a mask test to run.

Query Syntax

```
:MTESt:RMODe:TIME?
```

The :MTESt:RMODe:TIME? query returns the number of seconds currently set.

Return Format

```
<seconds><NL>

<seconds> ::= from 1 to 86400 in NR3 format
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:RMODe" on page 442

:MTESt:RMODe:WAVeforms

(see page 828)

Command Syntax

```
:MTESt:RMODe:WAVeforms <count>

<count> ::= number of waveforms in NR1 format
            from 1 to 2,000,000,000
```

When the :MTESt:RMODe command is set to WAVeforms, the :MTESt:RMODe:WAVeforms command sets the number of waveform acquisitions that are mask tested.

Query Syntax

```
:MTESt:RMODe:WAVeforms?
```

The :MTESt:RMODe:WAVeforms? query returns the number of waveforms currently set.

Return Format

```
<count><NL>

<count> ::= number of waveforms in NR1 format
            from 1 to 2,000,000,000
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:RMODe" on page 442

:MTESt:SCALe:BIND

(see page 828)

Command Syntax

```
:MTESt:SCALe:BIND <on_off>

<on_off> ::= {{1 | ON} | {0 | OFF}}
```

The :MTESt:SCALe:BIND command enables or disables Bind 1 & 0 Levels (Bind -1 & 0 Levels for inverted masks) control:

- ON –

  If the Bind 1 & 0 Levels control is enabled, the 1 Level and the 0 Level controls track each other. Adjusting either the 1 Level or the 0 Level control shifts the position of the mask up or down without changing its size.

  If the Bind -1 & 0 Levels control is enabled, the -1 Level and the 0 Level controls track each other. Adjusting either the -1 Level or the 0 Level control shifts the position of the mask up or down without changing its size.

- OFF –

  If the Bind 1 & 0 Levels control is disabled, adjusting either the 1 Level or the 0 Level control changes the vertical height of the mask.

  If the Bind -1 & 0 Levels control is disabled, adjusting either the -1 Level or the 0 Level control changes the vertical height of the mask.

Query Syntax

```
:MTESt:SCALe:BIND?
```

The :MTESt:SCALe:BIND? query returns the value of the Bind 1&0 control (Bind -1&0 for inverted masks).

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:SCALe:X1" on page 451
- ":MTESt:SCALe:XDELta" on page 452
- ":MTESt:SCALe:Y1" on page 453
- ":MTESt:SCALe:Y2" on page 454

:MTESt:SCALe:X1

N (see page 828)

Command Syntax

```
:MTESt:SCALe:X1 <x1_value>

<x1_value> ::= X1 value in NR3 format
```

The :MTESt:SCALe:X1 command defines where X=0 in the base coordinate system used for mask testing. The other X-coordinate is defined by the :MTESt:SCALe:XDELta command. Once the X1 and XDELta coordinates are set, all X values of vertices in the mask regions are defined with respect to this value, according to the equation:

$$X = (X * \Delta X) + X1$$

Thus, if you set X1 to 100 ms, and XDELta to 100 ms, an X value of 0.100 is a vertex at 110 ms.

The oscilloscope uses this equation to normalize vertices. This simplifies reprogramming to handle different data rates. For example, if you halve the period of the waveform of interest, you need only to adjust the XDELta value to set up the mask for the new waveform.

The X1 value is a time value specifying the location of the X1 coordinate, which will then be treated as X=0 for mask regions coordinates.

Query Syntax

```
:MTESt:SCALe:X1?
```

The :MTESt:SCALe:X1? query returns the current X1 coordinate setting.

Return Format

```
<x1_value><NL>

<x1_value> ::= X1 value in NR3 format
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:SCALe:BIND" on page 450
- ":MTESt:SCALe:XDELta" on page 452
- ":MTESt:SCALe:Y1" on page 453
- ":MTESt:SCALe:Y2" on page 454

:MTESt:SCALe:XDELta

(see page 828)

Command Syntax

```
:MTESt:SCALe:XDELta <xdelta_value>

<xdelta_value> ::= X delta value in NR3 format
```

The :MTESt:SCALe:XDELta command defines the position of the X2 marker with respect to the X1 marker. In the mask test coordinate system, the X1 marker defines where X=0; thus, the X2 marker defines where X=1.

Because all X vertices of the regions defined for mask testing are normalized with respect to X1 and ΔX, redefining ΔX also moves those vertices to stay in the same locations with respect to X1 and ΔX. Thus, in many applications, it is best if you define XDELta as a pulse width or bit period. Then, a change in data rate without corresponding changes in the waveform can easily be handled by changing ΔX.

The X-coordinate of polygon vertices is normalized using this equation:

```
X = (X * ΔX) + X1
```

The X delta value is a time value specifying the distance of the X2 marker with respect to the X1 marker.

For example, if the period of the waveform you wish to test is 1 ms, setting ΔX to 1 ms ensures that the waveform's period is between the X1 and X2 markers.

Query Syntax

```
:MTESt:SCALe:XDELta?
```

The :MTESt:SCALe:XDELta? query returns the current value of ΔX.

Return Format

```
<xdelta_value><NL>

<xdelta_value> ::= X delta value in NR3 format
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:SCALe:BIND" on page 450
- ":MTESt:SCALe:X1" on page 451
- ":MTESt:SCALe:Y1" on page 453
- ":MTESt:SCALe:Y2" on page 454

:MTESt:SCALe:Y1

(see page 828)

Command Syntax

```
:MTESt:SCALe:Y1 <y1_value>

<y1_value> ::= Y1 value in NR3 format
```

The :MTESt:SCALe:Y1 command defines where Y=0 in the coordinate system for mask testing. All Y values of vertices in the coordinate system are defined with respect to the boundaries set by SCALe:Y1 and SCALe:Y2 according to the equation:

```
Y = (Y * (Y2 - Y1)) + Y1
```

Thus, if you set Y1 to 100 mV, and Y2 to 1 V, a Y value of 0.100 in a vertex is at 190 mV.

The Y1 value is a voltage value specifying the point at which Y=0.

Query Syntax

```
:MTESt:SCALe:Y1?
```

The :MTESt:SCALe:Y1? query returns the current setting of the Y1 marker.

Return Format

```
<y1_value><NL>

<y1_value> ::= Y1 value in NR3 format
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:SCALe:BIND" on page 450
- ":MTESt:SCALe:X1" on page 451
- ":MTESt:SCALe:XDELta" on page 452
- ":MTESt:SCALe:Y2" on page 454

:MTESt:SCALe:Y2

(see page 828)

Command Syntax

```
:MTESt:SCALe:Y2 <y2_value>

<y2_value> ::= Y2 value in NR3 format
```

The :MTESt:SCALe:Y2 command defines the Y2 marker in the coordinate system for mask testing. All Y values of vertices in the coordinate system are defined with respect to the boundaries defined by SCALe:Y1 and SCALe:Y2 according to the following equation:

```
Y = (Y * (Y2 - Y1)) + Y1
```

Thus, if you set Y1 to 100 mV, and Y2 to 1 V, a Y value of 0.100 in a vertex is at 190 mV.

The Y2 value is a voltage value specifying the location of the Y2 marker.

Query Syntax

```
:MTESt:SCALe:Y2?
```

The :MTESt:SCALe:Y2? query returns the current setting of the Y2 marker.

Return Format

```
<y2_value><NL>

<y2_value> ::= Y2 value in NR3 format
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:SCALe:BIND" on page 450
- ":MTESt:SCALe:X1" on page 451
- ":MTESt:SCALe:XDELta" on page 452
- ":MTESt:SCALe:Y1" on page 453

:MTESt:SOURce

N (see page 828)

Command Syntax

```
:MTESt:SOURce <source>

<source> ::= CHANnel<n>

<n> ::= 1 to (# analog channels) in NR1 format
```

The :MTESt:SOURce command selects the channel which is configured by the commands contained in a mask file when it is loaded.

Query Syntax

```
:MTESt:SOURce?
```

The :MTESt:SOURce? query returns the channel which is configured by the commands contained in the current mask file.

Return Format

```
<source><NL>

<source> ::= {CHAN<n> | NONE}

<n> ::= 1 to (# analog channels) in NR1 format
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:AMASk:SOURce" on page 430

:MTESt:TITLe

N (see page 828)

Query Syntax `:MTESt:TITLe?`

The :MTESt:TITLe? query returns the mask title which is a string of up to 128 characters. The title is displayed in the mask test dialog box and mask test tab when a mask file is loaded.

Return Format `<title><NL>`

`<title> ::= a string of up to 128 ASCII characters.`

See Also

- "Introduction to :MTESt Commands" on page 425

23 :RECall Commands

Recall previously saved oscilloscope setups, reference waveforms, and masks.

Table 69 :RECall Commands Summary

Command	Query	Options and Query Returns
:RECall:FILename <base_name> (see page 459)	:RECall:FILename? (see page 459)	<base_name> ::= quoted ASCII string
:RECall:MASK[:STARt] [<file_spec>] (see page 460)	n/a	<file_spec> ::= {<internal_loc> | <file_name>} <internal_loc> ::= 0-3; an integer in NR1 format <file_name> ::= quoted ASCII string
:RECall:PWD <path_name> (see page 461)	:RECall:PWD? (see page 461)	<path_name> ::= quoted ASCII string
:RECall:SETup[:STARt] [<file_spec>] (see page 462)	n/a	<file_spec> ::= {<internal_loc> | <file_name>} <internal_loc> ::= 0-9; an integer in NR1 format <file_name> ::= quoted ASCII string
:RECall:WMEMory<r>[:STARt] [<file_name>] (see page 463)	n/a	<r> ::= 1-2 in NR1 format <file_name> ::= quoted ASCII string If extension included in file name, it must be ".h5".

Introduction to :RECall Commands

The :RECall subsystem provides commands to recall previously saved oscilloscope setups, reference waveforms, and masks.

Reporting the Setup

Use :RECall? to query setup information for the RECall subsystem.

Return Format

The following is a sample response from the :RECall? query. In this case, the query was issued following the *RST command.

```
:REC:FIL "scope_0"
```

:RECall:FILename

N (see page 828)

Command Syntax

```
:RECall:FILename <base_name>
<base_name> ::= quoted ASCII string
```

The :RECall:FILename command specifies the source for any RECall operations.

NOTE This command specifies a file's base name only, without path information or an extension.

Query Syntax

```
:RECall:FILename?
```

The :RECall:FILename? query returns the current RECall filename.

Return Format

```
<base_name><NL>
<base_name> ::= quoted ASCII string
```

See Also

- "Introduction to :RECall Commands" on page 457
- ":RECall:SETup[:STARt]" on page 462
- ":SAVE:FILename" on page 468

:RECall:MASK[:STARt]

(see page 828)

Command Syntax

```
:RECall:MASK[:STARt] [<file_spec>]
<file_spec> ::= {<internal_loc> | <file_name>}
<internal_loc> ::= 0-3; an integer in NR1 format
<file_name> ::= quoted ASCII string
```

The :RECall:MASK[:STARt] command recalls a mask.

NOTE If a file extension is provided as part of a specified <file_name>, it must be ".msk".

See Also

- "Introduction to :RECall Commands" on page 457
- ":RECall:FILename" on page 459
- ":SAVE:MASK[:STARt]" on page 475
- ":MTESt:DATA" on page 438

:RECall:PWD

(see page 828)

Command Syntax

```
:RECall:PWD <path_name>

<path_name> ::= quoted ASCII string
```

The :RECall:PWD command sets the present working directory for recall operations.

Query Syntax

```
:RECall:PWD?
```

The :RECall:PWD? query returns the currently set working directory for recall operations.

Return Format

```
<path_name><NL>

<path_name> ::= quoted ASCII string
```

See Also

- "Introduction to :RECall Commands" on page 457
- ":SAVE:PWD" on page 477

:RECall:SETup[:STARt]

(see page 828)

Command Syntax

```
:RECall:SETup[:STARt] [<file_spec>]
<file_spec> ::= {<internal_loc> | <file_name>}
<internal_loc> ::= 0-9; an integer in NR1 format
<file_name> ::= quoted ASCII string
```

The :RECall:SETup[:STARt] command recalls an oscilloscope setup.

NOTE If a file extension is provided as part of a specified <file_name>, it must be ".scp".

See Also

- "Introduction to :RECall Commands" on page 457
- ":RECall:FILename" on page 459
- ":SAVE:SETup[:STARt]" on page 478

:RECall:WMEMory<r>[:STARt]

(see page 828)

Command Syntax

```
:RECall:WMEMory<r>[:STARt] [<file_name>]
<r> ::= 1-2 in NR1 format
<file_name> ::= quoted ASCII string
```

The :RECall:WMEMory<r>[:STARt] command recalls a reference waveform.

NOTE If a file extension is provided as part of a specified <file_name>, it must be ".h5".

See Also

- "Introduction to :RECall Commands" on page 457
- ":RECall:FILename" on page 459
- ":SAVE:WMEMory[:STARt]" on page 485

24 :SAVE Commands

Save oscilloscope setups, screen images, and data. See "Introduction to :SAVE Commands" on page 467.

Table 70 :SAVE Commands Summary

Command	Query	Options and Query Returns
:SAVE:FILename <base_name> (see page 468)	:SAVE:FILename? (see page 468)	<base_name> ::= quoted ASCII string
:SAVE:IMAGe[:STARt] [<file_name>] (see page 469)	n/a	<file_name> ::= quoted ASCII string
:SAVE:IMAGe:FACTors {{0 | OFF} | {1 | ON}} (see page 470)	:SAVE:IMAGe:FACTors? (see page 470)	{0 | 1}
:SAVE:IMAGe:FORMat <format> (see page 471)	:SAVE:IMAGe:FORMat? (see page 471)	<format> ::= {{BMP | BMP24bit} | BMP8bit | PNG | NONE}
:SAVE:IMAGe:INKSaver {{0 | OFF} | {1 | ON}} (see page 472)	:SAVE:IMAGe:INKSaver? (see page 472)	{0 | 1}
:SAVE:IMAGe:PALette <palette> (see page 473)	:SAVE:IMAGe:PALette? (see page 473)	<palette> ::= {COLor | GRAYscale}
:SAVE:LISTer[:STARt] [<file_name>] (see page 474)	n/a	<file_name> ::= quoted ASCII string
:SAVE:MASK[:STARt] [<file_spec>] (see page 475)	n/a	<file_spec> ::= {<internal_loc> | <file_name>} <internal_loc> ::= 0-3; an integer in NR1 format <file_name> ::= quoted ASCII string

Table 70 :SAVE Commands Summary (continued)

Command	Query	Options and Query Returns
:SAVE:MULTi[:STARt] [<file_name>] (see page 476)	n/a	<file_name> ::= quoted ASCII string
:SAVE:PWD <path_name> (see page 477)	:SAVE:PWD? (see page 477)	<path_name> ::= quoted ASCII string
:SAVE:SETup[:STARt] [<file_spec>] (see page 478)	n/a	<file_spec> ::= {<internal_loc> | <file_name>} <internal_loc> ::= 0-9; an integer in NR1 format <file_name> ::= quoted ASCII string
:SAVE:WAVeform[:STARt] [<file_name>] (see page 479)	n/a	<file_name> ::= quoted ASCII string
:SAVE:WAVeform:FORMat <format> (see page 480)	:SAVE:WAVeform:FORMat? (see page 480)	<format> ::= {ASCiixy | CSV | BINary | NONE}
:SAVE:WAVeform:LENGth <length> (see page 481)	:SAVE:WAVeform:LENGth? (see page 481)	<length> ::= 100 to max. length; an integer in NR1 format
:SAVE:WAVeform:LENGth:MAX {{0 | OFF} | {1 | ON}} (see page 482)	:SAVE:WAVeform:LENGth:MAX? (see page 482)	{0 | 1}
:SAVE:WAVeform:SEGMented <option> (see page 483)	:SAVE:WAVeform:SEGMented? (see page 483)	<option> ::= {ALL | CURRent}
:SAVE:WMEMory:SOURce <source> (see page 484)	:SAVE:WMEMory:SOURce? (see page 484)	<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1-2 in NR1 format NOTE: Only ADD or SUBtract math operations can be saved as reference waveforms. <return_value> ::= <source>
:SAVE:WMEMory[:STARt] [<file_name>] (see page 485)	n/a	<file_name> ::= quoted ASCII string If extension included in file name, it must be ".h5".

Introduction to :SAVE Commands

The :SAVE subsystem provides commands to save oscilloscope setups, screen images, and data.

:SAV is an acceptable short form for :SAVE.

Reporting the Setup

Use :SAVE? to query setup information for the SAVE subsystem.

Return Format

The following is a sample response from the :SAVE? query. In this case, the query was issued following the *RST command.

```
:SAVE:FIL "";:SAVE:IMAG:AREA GRAT;FACT 0;FORM TIFF;INKS 0;PAL
MON;:SAVE:PWD "C:/setups/";:SAVE:WAV:FORM NONE;LENG 1000;SEGM CURR
```

:SAVE:FILename

(see page 828)

Command Syntax

```
:SAVE:FILename <base_name>
<base_name> ::= quoted ASCII string
```

The :SAVE:FILename command specifies the source for any SAVE operations.

NOTE This command specifies a file's base name only, without path information or an extension.

Query Syntax

```
:SAVE:FILename?
```

The :SAVE:FILename? query returns the current SAVE filename.

Return Format

```
<base_name><NL>
<base_name> ::= quoted ASCII string
```

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:IMAGe[:STARt]" on page 469
- ":SAVE:SETup[:STARt]" on page 478
- ":SAVE:WAVeform[:STARt]" on page 479
- ":SAVE:PWD" on page 477
- ":RECall:FILename" on page 459

:SAVE:IMAGe[:STARt]

(see page 828)

Command Syntax

```
:SAVE:IMAGe[:STARt] [<file_name>]

<file_name> ::= quoted ASCII string
```

The :SAVE:IMAGe[:STARt] command saves an image.

NOTE Be sure to set the :SAVE:IMAGe:FORMat before saving an image. If the format is NONE, the save image command will not succeed.

NOTE If a file extension is provided as part of a specified <file_name>, and it does not match the extension expected by the format specified in :SAVE:IMAGe:FORMat, the format will be changed if the extension is a valid image file extension.

NOTE If the extension ".bmp" is used and the current :SAVE:IMAGe:FORMat is not BMP or BMP8, the format will be changed to BMP.

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:IMAGe:FACTors" on page 470
- ":SAVE:IMAGe:FORMat" on page 471
- ":SAVE:IMAGe:INKSaver" on page 472
- ":SAVE:IMAGe:PALette" on page 473
- ":SAVE:FILename" on page 468

:SAVE:IMAGe:FACTors

(see page 828)

Command Syntax

```
:SAVE:IMAGe:FACTors <factors>

<factors> ::= {{OFF | 0} | {ON | 1}}
```

The :SAVE:IMAGe:FACTors command controls whether the oscilloscope factors are output along with the image.

NOTE Factors are written to a separate file with the same path and base name but with the ".txt" extension.

Query Syntax

```
:SAVE:IMAGe:FACTors?
```

The :SAVE:IMAGe:FACTors? query returns a flag indicating whether oscilloscope factors are output along with the image.

Return Format

```
<factors><NL>

<factors> ::= {0 | 1}
```

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:IMAGe[:STARt]" on page 469
- ":SAVE:IMAGe:FORMat" on page 471
- ":SAVE:IMAGe:INKSaver" on page 472
- ":SAVE:IMAGe:PALette" on page 473

:SAVE:IMAGe:FORMat

(see page 828)

Command Syntax

```
:SAVE:IMAGe:FORMat <format>

<format> ::= {{BMP | BMP24bit} | BMP8bit | PNG}
```

The :SAVE:IMAGe:FORMat command sets the image format type.

Query Syntax

```
:SAVE:IMAGe:FORMat?
```

The :SAVE:IMAGe:FORMat? query returns the selected image format type.

Return Format

```
<format><NL>

<format> ::= {BMP | BMP8 | PNG | NONE}
```

When NONE is returned, it indicates that a waveform data file format is currently selected.

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:IMAGe[:STARt]" on page 469
- ":SAVE:IMAGe:FACTors" on page 470
- ":SAVE:IMAGe:INKSaver" on page 472
- ":SAVE:IMAGe:PALette" on page 473
- ":SAVE:WAVeform:FORMat" on page 480

:SAVE:IMAGe:INKSaver

(see page 828)

Command Syntax

```
:SAVE:IMAGe:INKSaver <value>

<value> ::= {{OFF | 0} | {ON | 1}}
```

The :SAVE:IMAGe:INKSaver command controls whether the graticule colors are inverted or not.

Query Syntax

```
:SAVE:IMAGe:INKSaver?
```

The :SAVE:IMAGe:INKSaver? query returns a flag indicating whether graticule colors are inverted or not.

Return Format

```
<value><NL>

<value> ::= {0 | 1}
```

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:IMAGe[:STARt]" on page 469
- ":SAVE:IMAGe:FACTors" on page 470
- ":SAVE:IMAGe:FORMat" on page 471
- ":SAVE:IMAGe:PALette" on page 473

:SAVE:IMAGe:PALette

(see page 828)

Command Syntax

```
:SAVE:IMAGe:PALette <palette>

<palette> ::= {COLor | GRAYscale}
```

The :SAVE:IMAGe:PALette command sets the image palette color.

Query Syntax

```
:SAVE:IMAGe:PALette?
```

The :SAVE:IMAGe:PALette? query returns the selected image palette color.

Return Format

```
<palette><NL>

<palette> ::= {COL | GRAY}
```

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:IMAGe[:STARt]" on page 469
- ":SAVE:IMAGe:FACTors" on page 470
- ":SAVE:IMAGe:FORMat" on page 471
- ":SAVE:IMAGe:INKSaver" on page 472

:SAVE:LISTer[:STARt]

(see page 828)

Command Syntax

```
:SAVE:LISTer[:STARt] [<file_name>]
<file_name> ::= quoted ASCII string
```

The :SAVE:LISTer[:STARt] command saves the Lister display data to a file.

NOTE If a file extension is provided as part of a specified <file_name>, it must be ".csv".

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:FILename" on page 468
- Chapter 19, ":LISTer Commands," starting on page 337

:SAVE:MASK[:STARt]

(see page 828)

Command Syntax

```
:SAVE:MASK[:STARt] [<file_spec>]
<file_spec> ::= {<internal_loc> | <file_name>}
<internal_loc> ::= 0-3; an integer in NR1 format
<file_name> ::= quoted ASCII string
```

The :SAVE:MASK[:STARt] command saves a mask.

NOTE If a file extension is provided as part of a specified <file_name>, it must be ".msk".

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:FILename" on page 468
- ":RECall:MASK[:STARt]" on page 460
- ":MTESt:DATA" on page 438

:SAVE:MULTi[:STARt]

(see page 828)

Command Syntax

```
:SAVE:MULTi[:STARt] [<file_name>]

<file_name> ::= quoted ASCII string
```

The :SAVE:MULTi[:STARt] command saves multi-channel waveform data to a file. This file can be opened by the N8900A InfiniiView oscilloscope analysis software.

NOTE If a file extension is provided as part of a specified <file_name>, it must be ".h5".

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:FILename" on page 468
- ":SAVE:PWD" on page 477

:SAVE:PWD

(see page 828)

Command Syntax

```
:SAVE:PWD <path_name>

<path_name> ::= quoted ASCII string
```

The :SAVE:PWD command sets the present working directory for save operations.

Query Syntax

```
:SAVE:PWD?
```

The :SAVE:PWD? query returns the currently set working directory for save operations.

Return Format

```
<path_name><NL>

<path_name> ::= quoted ASCII string
```

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:FILename" on page 468
- ":RECall:PWD" on page 461

:SAVE:SETup[:STARt]

N (see page 828)

Command Syntax

```
:SAVE:SETup[:STARt] [<file_spec>]
<file_spec> ::= {<internal_loc> | <file_name>}
<internal_loc> ::= 0-9; an integer in NR1 format
<file_name> ::= quoted ASCII string
```

The :SAVE:SETup[:STARt] command saves an oscilloscope setup.

NOTE If a file extension is provided as part of a specified <file_name>, it must be ".scp".

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:FILename" on page 468
- ":RECall:SETup[:STARt]" on page 462

:SAVE:WAVeform[:STARt]

(see page 828)

Command Syntax

```
:SAVE:WAVeform[:STARt] [<file_name>]

<file_name> ::= quoted ASCII string
```

The :SAVE:WAVeform[:STARt] command saves oscilloscope waveform data to a file.

NOTE Be sure to set the :SAVE:WAVeform:FORMat before saving waveform data. If the format is NONE, the save waveform command will not succeed.

NOTE If a file extension is provided as part of a specified <file_name>, and it does not match the extension expected by the format specified in :SAVE:WAVeform:FORMat, the format will be changed if the extension is a valid waveform file extension.

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:WAVeform:FORMat" on page 480
- ":SAVE:WAVeform:LENGth" on page 481
- ":SAVE:FILename" on page 468
- ":RECall:SETup[:STARt]" on page 462

:SAVE:WAVeform:FORMat

(see page 828)

Command Syntax

```
:SAVE:WAVeform:FORMat <format>

<format> ::= {ASCiixy | CSV | BINary}
```

The :SAVE:WAVeform:FORMat command sets the waveform data format type:

- ASCiixy – creates comma-separated value files for each analog channel that is displayed (turned on). The proper file extension for this format is ".csv".
- CSV – creates one comma-separated value file that contains information for all analog channels that are displayed (turned on). The proper file extension for this format is ".csv".
- BINary – creates an oscilloscope binary data format file. See the *User's Guide* for a description of this format. The proper file extension for this format is ".bin".

Query Syntax

```
:SAVE:WAVeform:FORMat?
```

The :SAVE:WAVeform:FORMat? query returns the selected waveform data format type.

Return Format

```
<format><NL>

<format> ::= {ASC | CSV | BIN | NONE}
```

When NONE is returned, it indicates that an image file format is currently selected.

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:WAVeform[:STARt]" on page 479
- ":SAVE:WAVeform:LENGth" on page 481
- ":SAVE:IMAGe:FORMat" on page 471

:SAVE:WAVeform:LENGth

(see page 828)

Command Syntax

```
:SAVE:WAVeform:LENGth <length>

<length> ::= 100 to max. length; an integer in NR1 format
```

When the :SAVE:WAVeform:LENGth:MAX setting is OFF, the :SAVE:WAVeform:LENGth command sets the waveform data length (that is, the number of points saved).

When the :SAVE:WAVeform:LENGth:MAX setting is ON, the :SAVE:WAVeform:LENGth setting has no effect.

Query Syntax

```
:SAVE:WAVeform:LENGth?
```

The :SAVE:WAVeform:LENGth? query returns the current waveform data length setting.

Return Format

```
<length><NL>

<length> ::= 100 to max. length; an integer in NR1 format
```

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:WAVeform:LENGth:MAX" on page 482
- ":SAVE:WAVeform[:STARt]" on page 479
- ":WAVeform:POINts" on page 675
- ":SAVE:WAVeform:FORMat" on page 480

:SAVE:WAVeform:LENGth:MAX

(see page 828)

Command Syntax

```
:SAVE:WAVeform:LENGth:MAX <setting>

<setting> ::= {{OFF | 0} | {ON | 1}}
```

The :SAVE:WAVeform:LENGth:MAX command specifies whether maximum number of waveform data points is saved.

When OFF, the :SAVE:WAVeform:LENGth command specifies the number of waveform data points saved.

Query Syntax

```
:SAVE:WAVeform:LENGth:MAX?
```

The :SAVE:WAVeform:LENGth:MAX? query returns the current setting.

Return Format

```
<setting><NL>

<setting> ::= {0 | 1}
```

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:WAVeform[:STARt]" on page 479
- ":SAVE:WAVeform:LENGth" on page 481

:SAVE:WAVeform:SEGMented

(see page 828)

Command Syntax

```
:SAVE:WAVeform:SEGMented <option>

<option> ::= {ALL | CURRent}
```

When segmented memory is used for acquisitions, the :SAVE:WAVeform:SEGMented command specifies which segments are included when the waveform is saved:

- ALL – all acquired segments are saved.
- CURRent – only the currently selected segment is saved.

Query Syntax

```
:SAVE:WAVeform:SEGMented?
```

The :SAVE:WAVeform:SEGMented? query returns the current segmented waveform save option setting.

Return Format

```
<option><NL>

<option> ::= {ALL | CURR}
```

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:WAVeform[:STARt]" on page 479
- ":SAVE:WAVeform:FORMat" on page 480
- ":SAVE:WAVeform:LENGth" on page 481

:SAVE:WMEMory:SOURce

(see page 828)

Command Syntax

```
:SAVE:WMEMory:SOURce <source>

<source> ::= {CHANnel<n> | FUNCtion | MATH | WMEMory<r>}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= {1 | 2}
```

The :SAVE:WMEMory:SOURce command selects the source to be saved as a reference waveform file.

NOTE Only ADD or SUBtract math operations can be saved as reference waveforms.

NOTE MATH is an alias for FUNCtion. The query will return FUNC if the source is FUNCtion or MATH.

Query Syntax

```
:SAVE:WMEMory:SOURce?
```

The :SAVE:WMEMory:SOURce? query returns the source to be saved as a reference waveform file.

Return Format

```
<source><NL>

<source> ::= {CHAN<n> | FUNC | WMEM<r> | NONE}
```

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:WMEMory[:STARt]" on page 485
- ":RECall:WMEMory<r>[:STARt]" on page 463

:SAVE:WMEMory[:STARt]

(see page 828)

Command Syntax

```
:SAVE:WMEMory[:STARt] [<file_name>]

<file_name> ::= quoted ASCII string
```

The :SAVE:WMEMory[:STARt] command saves oscilloscope waveform data to a reference waveform file.

NOTE If a file extension is provided as part of a specified <file_name>, it must be ".h5".

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:WMEMory:SOURce" on page 484
- ":RECall:WMEMory<r>[:STARt]" on page 463

25 :SBUS<n> Commands

Control the modes and parameters for each serial bus decode/trigger type. See:

- "Introduction to :SBUS<n> Commands" on page 487
- "General :SBUS<n> Commands" on page 489
- ":SBUS<n>:CAN Commands" on page 492
- ":SBUS<n>:IIC Commands" on page 509
- ":SBUS<n>:LIN Commands" on page 519
- ":SBUS<n>:SPI Commands" on page 533
- ":SBUS<n>:UART Commands" on page 552

Introduction to :SBUS<n> Commands

The :SBUS subsystem commands control the serial decode bus viewing, mode, and other options.

NOTE

These commands are only valid on oscilloscope models when a serial decode option has been licensed. The CAN, LIN, and SPI serial decode and triggering options are available on the DSOX1200-Series oscilloscope models only.

The following serial bus decode/trigger types are available (see ":TRIGger:MODE" on page 624).

- **CAN (Controller Area Network) triggering**— will trigger on CAN version 2.0A and 2.0B signals. Setup consists of connecting the oscilloscope to a CAN signal. Baud rate, signal source, and signal polarity, and type of data to trigger on can be specified. You can trigger on CAN data and identifier patterns and you can set the bit sample point.
- **IIC (Inter-IC bus) triggering**— consists of connecting the oscilloscope to the serial data (SDA) line and the serial clock (SCL) line, then triggering on a stop/start condition, a restart, a missing acknowledge, or on a read/write frame with a specific device address and data value.
- **LIN (Local Interconnect Network) triggering**— will trigger on LIN sync break at the beginning of a message frame.You can trigger on Sync Break, Frame IDs, or Frame IDs and Data.

- **SPI (Serial Peripheral Interface) triggering**— consists of connecting the oscilloscope to a clock, data (MOSI or MISO), and framing signal. You can then trigger on a data pattern during a specific framing period. The serial data string can be specified to be from 4 to 64 bits long.
- **UART/RS-232 triggering** (with Option 232) — lets you trigger on RS-232 serial data.

Reporting the Setup

Use :SBUS<n>? to query setup information for the :SBUS<n> subsystem.

Return Format

The following is a sample response from the :SBUS1? query. In this case, the query was issued following a *RST command.

```
:SBUS1:DISP 0;MODE IIC;:SBUS1:IIC:ASIZ BIT7;:SBUS1:IIC:TRIG:TYPE
STAR;QUAL EQU;:SBUS1:IIC:SOUR:CLOC CHAN1;DATA
CHAN2;:SBUS1:IIC:TRIG:PATT:ADDR -1;DATA -1;DATA2 -1
```

General :SBUS<n> Commands

Table 71 General :SBUS<n> Commands Summary

Command	Query	Options and Query Returns
:SBUS<n>:DISPlay {{0 | OFF} | {1 | ON}} (see page 490)	:SBUS<n>:DISPlay? (see page 490)	{0 | 1}
:SBUS<n>:MODE <mode> (see page 491)	:SBUS<n>:MODE? (see page 491)	<mode> ::= {CAN | IIC | LIN | SPI | UART}

:SBUS<n>:DISPlay

N (see page 828)

Command Syntax

```
:SBUS<n>:DISPlay <display>

<display> ::= {{1 | ON} | {0 | OFF}}
```

The :SBUS<n>:DISPlay command turns displaying of the serial decode bus on or off.

NOTE This command is only valid when a serial decode option has been licensed.

Query Syntax

```
:SBUS<n>:DISPlay?
```

The :SBUS<n>:DISPlay? query returns the current display setting of the serial decode bus.

Return Format

```
<display><NL>

<display> ::= {0 | 1}
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :SBUS<n> Commands" on page 487
- ":CHANnel<n>:DISPlay" on page 217
- ":VIEW" on page 176
- ":BLANk" on page 152
- ":STATus" on page 173

:SBUS<n>:MODE

(see page 828)

Command Syntax

```
:SBUS<n>:MODE <mode>

<mode> ::= {CAN | IIC | LIN | SPI | UART}
```

The :SBUS<n>:MODE command determines the decode mode for the serial bus.

NOTE This command is only valid when a serial decode option has been licensed. The CAN, LIN, and SPI serial decode and triggering options are available on the DSOX1200-Series oscilloscope models.

Query Syntax

```
:SBUS<n>:MODE?
```

The :SBUS<n>:MODE? query returns the current serial bus decode mode setting.

Return Format

```
<mode><NL>

<mode> ::= {CAN | IIC | LIN | SPI | UART | NONE}
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:CAN Commands" on page 492
- ":SBUS<n>:IIC Commands" on page 509
- ":SBUS<n>:LIN Commands" on page 519
- ":SBUS<n>:SPI Commands" on page 533
- ":SBUS<n>:UART Commands" on page 552

:SBUS<n>:CAN Commands

NOTE These commands are valid on DSOX1200-Series oscilloscopes when the automotive CAN and LIN serial decode license (AUTO) is enabled.

Table 72 :SBUS<n>:CAN Commands Summary

Command	Query	Options and Query Returns
n/a	:SBUS<n>:CAN:COUNt:ERRor? (see page 494)	<frame_count> ::= integer in NR1 format
n/a	:SBUS<n>:CAN:COUNt:OVERload? (see page 495)	<frame_count> ::= integer in NR1 format
:SBUS<n>:CAN:COUNt:RESet (see page 496)	n/a	n/a
n/a	:SBUS<n>:CAN:COUNt:TOTal? (see page 497)	<frame_count> ::= integer in NR1 format
n/a	:SBUS<n>:CAN:COUNt:UTILization? (see page 498)	<percent> ::= floating-point in NR3 format
:SBUS<n>:CAN:SAMPlepoint <value> (see page 499)	:SBUS<n>:CAN:SAMPlepoint? (see page 499)	<value> ::= {60 | 62.5 | 68 | 70 | 75 | 80 | 87.5} in NR3 format
:SBUS<n>:CAN:SIGNal:BAUDrate <baudrate> (see page 500)	:SBUS<n>:CAN:SIGNal:BAUDrate? (see page 500)	<baudrate> ::= integer from 10000 to 4000000 in 100 b/s increments, or 5000000
:SBUS<n>:CAN:SIGNal:DEFinition <value> (see page 501)	:SBUS<n>:CAN:SIGNal:DEFinition? (see page 501)	<value> ::= {CANH | CANL | RX | TX | DIFFerential | DIFL | DIFH}
:SBUS<n>:CAN:SOURce <source> (see page 502)	:SBUS<n>:CAN:SOURce? (see page 502)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:CAN:TRIGger <condition> (see page 503)	:SBUS<n>:CAN:TRIGger? (see page 504)	<condition> ::= {SOF | DATA | ERRor | IDData | IDEither | IDRemote | ALLerrors | OVERload | ACKerror}

Table 72 :SBUS<n>:CAN Commands Summary (continued)

Command	Query	Options and Query Returns
:SBUS<n>:CAN:TRIGger:PATTern:DATA <string> (see page 505)	:SBUS<n>:CAN:TRIGger:PATTern:DATA? (see page 505)	<string> ::= "nn...n" where n ::= {0 | 1 | X | $} <string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
:SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth <length> (see page 506)	:SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth? (see page 506)	<length> ::= integer from 1 to 8 in NR1 format
:SBUS<n>:CAN:TRIGger:PATTern:ID <string> (see page 507)	:SBUS<n>:CAN:TRIGger:PATTern:ID? (see page 507)	<string> ::= "nn...n" where n ::= {0 | 1 | X | $} <string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
:SBUS<n>:CAN:TRIGger:PATTern:ID:MODE <value> (see page 508)	:SBUS<n>:CAN:TRIGger:PATTern:ID:MODE? (see page 508)	<value> ::= {STANdard | EXTended}

:SBUS<n>:CAN:COUNt:ERRor

(see page 828)

Query Syntax `:SBUS<n>:CAN:COUNt:ERRor?`

Returns the error frame count.

Return Format `<frame_count><NL>`

`<frame_count> ::= integer in NR1 format`

Errors

- "-241, Hardware missing" on page 789

See Also

- ":SBUS<n>:CAN:COUNt:RESet" on page 496
- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:CAN Commands" on page 492

:SBUS<n>:CAN:COUNt:OVERload

N (see page 828)

Query Syntax `:SBUS<n>:CAN:COUNt:OVERload?`

Returns the overload frame count.

Return Format `<frame_count><NL>`

`<frame_count> ::= integer in NR1 format`

Errors

- "-241, Hardware missing" on page 789

See Also

- ":SBUS<n>:CAN:COUNt:RESet" on page 496
- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:CAN Commands" on page 492

:SBUS<n>:CAN:COUNt:RESet

(see page 828)

Command Syntax `:SBUS<n>:CAN:COUNt:RESet`

Resets the frame counters.

Errors

- "-241, Hardware missing" on page 789

See Also

- ":SBUS<n>:CAN:COUNt:ERRor" on page 494
- ":SBUS<n>:CAN:COUNt:OVERload" on page 495
- ":SBUS<n>:CAN:COUNt:TOTal" on page 497
- ":SBUS<n>:CAN:COUNt:UTILization" on page 498
- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:CAN Commands" on page 492

:SBUS<n>:CAN:COUNt:TOTal

N (see page 828)

Query Syntax `:SBUS<n>:CAN:COUNt:TOTal?`

Returns the total frame count.

Return Format `<frame_count><NL>`

`<frame_count> ::= integer in NR1 format`

Errors

- "-241, Hardware missing" on page 789

See Also

- ":SBUS<n>:CAN:COUNt:RESet" on page 496
- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:CAN Commands" on page 492

:SBUS<n>:CAN:COUNt:UTILization

(see page 828)

Query Syntax `:SBUS<n>:CAN:COUNt:UTILization?`

Returns the percent utilization.

Return Format `<percent><NL>`

`<percent> ::= floating-point in NR3 format`

Errors

- "-241, Hardware missing" on page 789

See Also

- ":SBUS<n>:CAN:COUNt:RESet" on page 496
- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:CAN Commands" on page 492

:SBUS<n>:CAN:SAMPlepoint

(see page 828)

Command Syntax

```
:SBUS<n>:CAN:SAMPlepoint <value>

<value><NL>

<value> ::= {60 | 62.5 | 68 | 70 | 75 | 80 | 87.5} in NR3 format
```

The :SBUS<n>:CAN:SAMPlepoint command sets the point during the bit time where the bit level is sampled to determine whether the bit is dominant or recessive. The sample point represents the percentage of time between the beginning of the bit time to the end of the bit time.

Query Syntax

```
:SBUS<n>:CAN:SAMPlepoint?
```

The :SBUS<n>:CAN:SAMPlepoint? query returns the current CAN sample point setting.

Return Format

```
<value><NL>

<value> ::= {60 | 62.5 | 68 | 70 | 75 | 80 | 87.5} in NR3 format
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:CAN:TRIGger" on page 503

:SBUS<n>:CAN:SIGNal:BAUDrate

(see page 828)

Command Syntax

```
:SBUS<n>:CAN:SIGNal:BAUDrate <baudrate>

<baudrate> ::= integer from 10000 to 4000000 in 100 b/s increments,
               or 5000000
```

The :SBUS<n>:CAN:SIGNal:BAUDrate command sets the standard baud rate of the CAN signal from 10 kb/s to 4 Mb/s in 100 b/s increments. If you enter a baud rate that is not divisible by 100 b/s, the baud rate is set to the nearest baud rate divisible by 100 b/s.

You can also set the baud rate of the CAN signal to 5 Mb/s. Fractional baud rates between 4 Mb/s and 5 Mb/s are not allowed.

If the baud rate you select does not match the system baud rate, false triggers may occur.

Query Syntax

```
:SBUS<n>:CAN:SIGNal:BAUDrate?
```

The :SBUS<n>:CAN:SIGNal:BAUDrate? query returns the current CAN baud rate setting.

Return Format

```
<baudrate><NL>

<baudrate> ::= integer from 10000 to 4000000 in 100 b/s increments,
               or 5000000
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:CAN:TRIGger" on page 503
- ":SBUS<n>:CAN:SIGNal:DEFinition" on page 501
- ":SBUS<n>:CAN:SOURce" on page 502

:SBUS<n>:CAN:SIGNal:DEFinition

N (see page 828)

Command Syntax

```
:SBUS<n>:CAN:SIGNal:DEFinition <value>

<value> ::= {CANH | CANL | RX | TX | DIFFerential | DIFL | DIFH}
```

The :SBUS<n>:CAN:SIGNal:DEFinition command sets the CAN signal type when :SBUS<n>:CAN:TRIGger is set to SOF (start of frame). These signals can be set to:

Dominant high signals:

- CANH – the actual CAN_H differential bus signal.
- DIFH – the CAN differential (H-L) bus signal connected to an analog source channel using a differential probe.

Dominant low signals:

- CANL – the actual CAN_L differential bus signal.
- RX – the Receive signal from the CAN bus transceiver.
- TX – the Transmit signal to the CAN bus transceiver.
- DIFL – the CAN differential (L-H) bus signal connected to an analog source channel using a differential probe.
- DIFFerential – the CAN differential bus signal connected to an analog source channel using a differential probe. This is the same as DIFL.

Query Syntax

```
:SBUS<n>:CAN:SIGNal:DEFinition?
```

The :SBUS<n>:CAN:SIGNal:DEFinition? query returns the current CAN signal type.

Return Format

```
<value><NL>

<value> ::= {CANH | CANL | RX | TX | DIFL | DIFH}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:CAN:SIGNal:BAUDrate" on page 500
- ":SBUS<n>:CAN:SOURce" on page 502
- ":SBUS<n>:CAN:TRIGger" on page 503

:SBUS<n>:CAN:SOURce

N (see page 828)

Command Syntax

```
:SBUS<n>:CAN:SOURce <source>
<source> ::= {CHANnel<n> | EXTernal}
<n> ::= 1 to (# analog channels) in NR1 format
```

The :SBUS<n>:CAN:SOURce command sets the source for the CAN signal.

NOTE EXTernal can be specified as the source on 2-channel DSOX1200-Series oscilloscopes only.

Query Syntax

```
:SBUS<n>:CAN:SOURce?
```

The :SBUS<n>:CAN:SOURce? query returns the current source for the CAN signal.

Return Format

```
<source><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:CAN:TRIGger" on page 503
- ":SBUS<n>:CAN:SIGNal:DEFinition" on page 501

:SBUS<n>:CAN:TRIGger

N (see page 828)

Command Syntax

```
:SBUS<n>:CAN:TRIGger <condition>

<condition> ::= {SOF | DATA | ERRor | IDData | IDEither | IDRemote |
                 ALLerrors | OVERload | ACKerror}
```

The :SBUS<n>:CAN:TRIGger command sets the CAN trigger on condition:

- SOF - will trigger on the Start of Frame (SOF) bit of a Data frame, Remote Transfer Request (RTR) frame, or an Overload frame.
- DATA - will trigger on CAN Data frames matching the specified Id, Data, and the DLC (Data length code).
- ERRor - will trigger on CAN Error frame.
- IDData - will trigger on CAN frames matching the specified Id of a Data frame.
- IDEither - will trigger on the specified Id, regardless if it is a Remote frame or a Data frame.
- IDRemote - will trigger on CAN frames matching the specified Id of a Remote frame.
- ALLerrors - will trigger on CAN active error frames and unknown bus conditions.
- OVERload - will trigger on CAN overload frames.
- ACKerror - will trigger on a data or remote frame acknowledge bit that is recessive.

The table below shows the programming parameter and the corresponding front-panel softkey selection:

Remote <condition> parameter	Front-panel Trigger on: softkey selection (softkey text - softkey popup text)
SOF	SOF - Start of Frame
DATA	ID & Data - Data Frame ID and Data
ERRor	Error - Error frame
IDData	ID & ~RTR - Data Frame ID (~RTR)
IDEither	ID - Remote or Data Frame ID
IDRemote	ID & RTR - Remote Frame ID (RTR)
ALLerrors	All Errors - All Errors
OVERload	Overload - Overload Frame
ACKerror	Ack Error - Acknowledge Error

CAN Id specification is set by the :SBUS<n>:CAN:TRIGger:PATTern:ID and:SBUS<n>:CAN:TRIGger:PATTern:ID:MODE commands.

CAN Data specification is set by the :SBUS<n>:CAN:TRIGger:PATTern:DATA command.

CAN Data Length Code is set by the :SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth command.

Query Syntax

```
:SBUS<n>:CAN:TRIGger?
```

The :SBUS<n>:CAN:TRIGger? query returns the current CAN trigger on condition.

Return Format

```
<condition><NL>

<condition> ::= {SOF | DATA | ERR | IDD | IDE | IDR | ALL | OVER | ACK}
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:CAN:TRIGger:PATTern:DATA" on page 505
- ":SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth" on page 506
- ":SBUS<n>:CAN:TRIGger:PATTern:ID" on page 507
- ":SBUS<n>:CAN:TRIGger:PATTern:ID:MODE" on page 508
- ":SBUS<n>:CAN:SIGNal:DEFinition" on page 501
- ":SBUS<n>:CAN:SOURce" on page 502

:SBUS<n>:CAN:TRIGger:PATTern:DATA

N (see page 828)

Command Syntax

```
:SBUS<n>:CAN:TRIGger:PATTern:DATA <string>

<string> ::= "nn...n" where n ::= {0 | 1 | X | $}

<string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
```

The :SBUS<n>:CAN:TRIGger:PATTern:DATA command defines the CAN data pattern resource according to the string parameter. This pattern, along with the data length (set by the :SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth command), control the data pattern searched for in each CAN message.

If the string parameter starts with "0x", it is a hexadecimal string made up of hexadecimal and X (don't care) characters; otherwise, it is a binary string made up of 0, 1, and X (don't care) characters.

NOTE

If more bits are sent for <string> than specified by the :SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth command, the most significant bits will be truncated. If the data length is changed after the <string> is programmed, the added or deleted bits will be added to or deleted from the least significant bits.

Query Syntax

```
:SBUS<n>:CAN:TRIGger:PATTern:DATA?
```

The :SBUS<n>:CAN:TRIGger:PATTern:DATA? query returns the current settings of the specified CAN data pattern resource in the binary string format.

Return Format

```
<string><NL> in nondecimal format
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth" on page 506
- ":SBUS<n>:CAN:TRIGger:PATTern:ID" on page 507

:SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth

N (see page 828)

Command Syntax

```
:SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth <length>

<length> ::= integer from 1 to 8 in NR1 format
```

The :SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth command sets the number of 8-bit bytes in the CAN data string. The number of bytes in the string can be anywhere from 1 bytes to 8 bytes (64 bits). The value for these bytes is set by the :SBUS<n>:CAN:TRIGger:PATTern:DATA command.

Query Syntax

```
:SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth?
```

The :SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth? query returns the current CAN data pattern length setting.

Return Format

```
<count><NL>

<count> ::= integer from 1 to 8 in NR1 format
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:CAN:TRIGger:PATTern:DATA" on page 505
- ":SBUS<n>:CAN:SOURce" on page 502

:SBUS<n>:CAN:TRIGger:PATTern:ID

N (see page 828)

Command Syntax

```
:SBUS<n>:CAN:TRIGger:PATTern:ID <string>

<string> ::= "nn...n" where n ::= {0 | 1 | X | $}

<string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
```

The :SBUS<n>:CAN:TRIGger:PATTern:ID command defines the CAN identifier pattern resource according to the string parameter. This pattern, along with the identifier mode (set by the :SBUS<n>:CAN:TRIGger:PATTern:ID:MODE command), control the identifier pattern searched for in each CAN message.

If the string parameter starts with "0x", it is a hexadecimal string made up of hexadecimal and X (don't care) characters; otherwise, it is a binary string made up of 0, 1, and X (don't care) characters.

NOTE

The ID pattern resource string is always 29 bits. Only 11 of these bits are used when the :SBUS<n>:CAN:TRIGger:PATTern:ID:MODE is STANdard.

A string longer than 29 bits is truncated to 29 bits when setting the ID pattern resource.

Query Syntax

```
:SBUS<n>:CAN:TRIGger:PATTern:ID?
```

The :SBUS<n>:CAN:TRIGger:PATTern:ID? query returns the current settings of the specified CAN identifier pattern resource in the 29-bit binary string format.

Return Format

```
<string><NL> in 29-bit binary string format
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:CAN:TRIGger:PATTern:ID:MODE" on page 508
- ":SBUS<n>:CAN:TRIGger:PATTern:DATA" on page 505

:SBUS<n>:CAN:TRIGger:PATTern:ID:MODE

(see page 828)

Command Syntax

```
:SBUS<n>:CAN:TRIGger:PATTern:ID:MODE <value>

<value> ::= {STANdard | EXTended}
```

The :SBUS<n>:CAN:TRIGger:PATTern:ID:MODE command sets the CAN identifier mode. STANdard selects the standard 11-bit identifier. EXTended selects the extended 29-bit identifier. The CAN identifier is set by the :SBUS<n>:CAN:TRIGger:PATTern:ID command.

Query Syntax

```
:SBUS<n>:CAN:TRIGger:PATTern:ID:MODE?
```

The :SBUS<n>:CAN:TRIGger:PATTern:ID:MODE? query returns the current setting of the CAN identifier mode.

Return Format

```
<value><NL>

<value> ::= {STAN | EXT}
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:CAN:TRIGger:PATTern:DATA" on page 505
- ":SBUS<n>:CAN:TRIGger:PATTern:DATA:LENGth" on page 506
- ":SBUS<n>:CAN:TRIGger:PATTern:ID" on page 507

:SBUS<n>:IIC Commands

NOTE These commands are valid when the low-speed IIC and SPI serial decode license (EMBD) is enabled.

Table 73 :SBUS<n>:IIC Commands Summary

Command	Query	Options and Query Returns
:SBUS<n>:IIC:ASIZe <size> (see page 510)	:SBUS<n>:IIC:ASIZe? (see page 510)	<size> ::= {BIT7 | BIT8}
:SBUS<n>:IIC[:SOURce]:CLOCk <source> (see page 511)	:SBUS<n>:IIC[:SOURce]:CLOCk? (see page 511)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:IIC[:SOURce]:DATA <source> (see page 512)	:SBUS<n>:IIC[:SOURce]:DATA? (see page 512)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:IIC:TRIGger:PATTern:ADDRess <value> (see page 513)	:SBUS<n>:IIC:TRIGger:PATTern:ADDRess? (see page 513)	<value> ::= integer or <string> <string> ::= "0xnn" n ::= {0,..,9 | A,..,F}
:SBUS<n>:IIC:TRIGger:PATTern:DATA <value> (see page 514)	:SBUS<n>:IIC:TRIGger:PATTern:DATA? (see page 514)	<value> ::= integer or <string> <string> ::= "0xnn" n ::= {0,..,9 | A,..,F}
:SBUS<n>:IIC:TRIGger:PATTern:DATa2 <value> (see page 515)	:SBUS<n>:IIC:TRIGger:PATTern:DATa2? (see page 515)	<value> ::= integer or <string> <string> ::= "0xnn" n ::= {0,..,9 | A,..,F}
:SBUS<n>:IIC:TRIGger:QUALifier <value> (see page 516)	:SBUS<n>:IIC:TRIGger:QUALifier? (see page 516)	<value> ::= {EQUal | NOTequal | LESSthan | GREaterthan}
:SBUS<n>:IIC:TRIGger[:TYPE] <type> (see page 517)	:SBUS<n>:IIC:TRIGger[:TYPE]? (see page 517)	<type> ::= {STARt | STOP | READ7 | READEprom | WRITe7 | WRITe10 | NACKnowledge | ANACk | R7Data2 | W7Data2 | RESTart}

:SBUS<n>:IIC:ASIZe

N (see page 828)

Command Syntax

```
:SBUS<n>:IIC:ASIZe <size>

<size> ::= {BIT7 | BIT8}
```

The :SBUS<n>:IIC:ASIZe command determines whether the Read/Write bit is included as the LSB in the display of the IIC address field of the decode bus.

Query Syntax

```
:SBUS<n>:IIC:ASIZe?
```

The :SBUS<n>:IIC:ASIZe? query returns the current IIC address width setting.

Return Format

```
<mode><NL>

<mode> ::= {BIT7 | BIT8}
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:IIC Commands" on page 509

:SBUS<n>:IIC[:SOURce]:CLOCk

N (see page 828)

Command Syntax

```
:SBUS<n>:IIC[:SOURce]:CLOCk <source>

<source> ::= {CHANnel<n> | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :SBUS<n>:IIC[:SOURce]:CLOCk command sets the source for the IIC serial clock (SCL).

NOTE EXTernal can be specified as the source on 2-channel DSOX1200-Series oscilloscopes only.

Query Syntax

```
:SBUS<n>:IIC[:SOURce]:CLOCk?
```

The :SBUS<n>:IIC[:SOURce]:CLOCk? query returns the current source for the IIC serial clock.

Return Format

```
<source><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:IIC[:SOURce]:DATA" on page 512

:SBUS<n>:IIC[:SOURce]:DATA

N (see page 828)

Command Syntax

```
:SBUS<n>:IIC[:SOURce]:DATA <source>

<source> ::= {CHANnel<n> | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :SBUS<n>:IIC[:SOURce]:DATA command sets the source for IIC serial data (SDA).

NOTE EXTernal can be specified as the source on 2-channel DSOX1200-Series oscilloscopes only.

Query Syntax

```
:SBUS<n>:IIC[:SOURce]:DATA?
```

The :SBUS<n>:IIC[:SOURce]:DATA? query returns the current source for IIC serial data.

Return Format

```
<source><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:IIC[:SOURce]:CLOCk" on page 511

:SBUS<n>:IIC:TRIGger:PATTern:ADDRess

N (see page 828)

Command Syntax

```
:SBUS<n>:IIC:TRIGger:PATTern:ADDRess <value>

<value> ::= integer or <string>

<string> ::= "0xnn" where n ::= {0,..,9 | A,..,F}
```

The :SBUS<n>:IIC:TRIGger:PATTern:ADDRess command sets the address for IIC data.The address can range from 0x00 to 0x7F (7-bit) or 0x3FF (10-bit) hexadecimal. Use the don't care address (-1 or 0xFFFFFFFF) to ignore the address value.

Query Syntax

```
:SBUS<n>:IIC:TRIGger:PATTern:ADDRess?
```

The :SBUS<n>:IIC:TRIGger:PATTern:ADDRess? query returns the current address for IIC data.

Return Format

```
<value><NL>

<value> ::= integer
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:IIC:TRIGger:PATTern:DATA" on page 514
- ":SBUS<n>:IIC:TRIGger:PATTern:DATa2" on page 515
- ":SBUS<n>:IIC:TRIGger[:TYPE]" on page 517

:SBUS<n>:IIC:TRIGger:PATTern:DATA

(see page 828)

Command Syntax

```
:SBUS<n>:IIC:TRIGger:PATTern:DATA <value>

<value> ::= integer or <string>

<string> ::= "0xnn" where n ::= {0,..,9 | A,..,F}
```

The :SBUS<n>:IIC:TRIGger:PATTern:DATA command sets IIC data. The data value can range from 0x00 to 0x0FF (hexadecimal). Use the don't care data pattern (-1 or 0xFFFFFFFF) to ignore the data value.

Query Syntax

```
:SBUS<n>:IIC:TRIGger:PATTern:DATA?
```

The :SBUS<n>:IIC:TRIGger:PATTern:DATA? query returns the current pattern for IIC data.

Return Format

```
<value><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:IIC:TRIGger:PATTern:ADDRess" on page 513
- ":SBUS<n>:IIC:TRIGger:PATTern:DATa2" on page 515
- ":SBUS<n>:IIC:TRIGger[:TYPE]" on page 517

:SBUS<n>:IIC:TRIGger:PATTern:DATa2

N (see page 828)

Command Syntax

```
:SBUS<n>:IIC:TRIGger:PATTern:DATa2 <value>

<value> ::= integer or <string>

<string> ::= "0xnn" where n ::= {0,..,9 | A,..,F}
```

The :SBUS<n>:IIC:TRIGger:PATTern:DATa2 command sets IIC data 2. The data value can range from 0x00 to 0x0FF (hexadecimal). Use the don't care data pattern (-1 or 0xFFFFFFFF) to ignore the data value.

Query Syntax

```
:SBUS<n>:IIC:TRIGger:PATTern:DATa2?
```

The :SBUS<n>:IIC:TRIGger:PATTern:DATa2? query returns the current pattern for IIC data 2.

Return Format

```
<value><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:IIC:TRIGger:PATTern:ADDRess" on page 513
- ":SBUS<n>:IIC:TRIGger:PATTern:DATA" on page 514
- ":SBUS<n>:IIC:TRIGger[:TYPE]" on page 517

:SBUS<n>:IIC:TRIGger:QUALifier

N (see page 828)

Command Syntax

```
:SBUS<n>:IIC:TRIGger:QUALifier <value>

<value> ::= {EQUal | NOTequal | LESSthan | GREaterthan}
```

The :SBUS<n>:IIC:TRIGger:QUALifier command sets the IIC data qualifier when TRIGger:IIC:TRIGger[:TYPE] is set to READEprom.

Query Syntax

```
:SBUS<n>:IIC:TRIGger:QUALifier?
```

The :SBUS<n>:IIC:TRIGger:QUALifier? query returns the current IIC data qualifier value.

Return Format

```
<value><NL>

<value> ::= {EQUal | NOTequal | LESSthan | GREaterthan}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:IIC:TRIGger[:TYPE]" on page 517

:SBUS<n>:IIC:TRIGger[:TYPE]

N (see page 828)

Command Syntax

```
:SBUS<n>:IIC:TRIGger[:TYPE] <value>

<value> ::= {STARt | STOP | READ7 | READEprom | WRITe7 | WRITe10
| NACKnowledge | ANACk | R7Data2 | W7Data2 | RESTart}
```

The :SBUS<n>:IIC:TRIGger[:TYPE] command sets the IIC trigger type:

- STARt – Start condition.
- STOP – Stop condition.
- READ7 – 7-bit address frame containing (Start:Address7:Read:Ack:Data). The value READ is also accepted for READ7.
- R7Data2 – 7-bit address frame containing (Start:Address7:Read:Ack:Data:Ack:Data2).
- READEprom – EEPROM data read.
- WRITe7 – 7-bit address frame containing (Start:Address7:Write:Ack:Data). The value WRITe is also accepted for WRITe7.
- W7Data2 – 7-bit address frame containing (Start:Address7:Write:Ack:Data:Ack:Data2).
- WRITe10 – 10-bit address frame containing (Start:Address byte1:Write:Ack:Address byte 2:Data).
- NACKnowledge – Missing acknowledge.
- ANACk – Address with no acknowledge.
- RESTart – Another start condition occurs before a stop condition.

NOTE **The short form of READ7 (READ7), READEprom (READE), WRITe7 (WRIT7), and WRITe10 (WRIT10) do not follow the defined Long Form to Short Form Truncation Rules (see page 830).**

Query Syntax

```
:SBUS<n>:IIC:TRIGger[:TYPE]?
```

The :SBUS<n>:IIC:TRIGger[:TYPE]? query returns the current IIC trigger type value.

Return Format

```
<value><NL>

<value> ::= {STAR | STOP | READ7 | READE | WRIT7 | WRIT10 | NACK | ANAC
            | R7D2 | W7D2 | REST}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:IIC:TRIGger:PATTern:ADDRess" on page 513
- ":SBUS<n>:IIC:TRIGger:PATTern:DATA" on page 514

- ":SBUS<n>:IIC:TRIGger:PATTern:DATa2" on page 515
- ":SBUS<n>:IIC:TRIGger:QUALifier" on page 516
- "Long Form to Short Form Truncation Rules" on page 830

:SBUS<n>:LIN Commands

NOTE These commands are valid on DSOX1200-Series oscilloscopes when the automotive CAN and LIN serial decode license (AUTO) is enabled.

Table 74 :SBUS<n>:LIN Commands Summary

Command	Query	Options and Query Returns
:SBUS<n>:LIN:PARity {{0 | OFF} | {1 | ON}} (see page 521)	:SBUS<n>:LIN:PARity? (see page 521)	{0 | 1}
:SBUS<n>:LIN:SAMPlepoint <value> (see page 522)	:SBUS<n>:LIN:SAMPlepoint? (see page 522)	<value> ::= {60 | 62.5 | 68 | 70 | 75 | 80 | 87.5} in NR3 format
:SBUS<n>:LIN:SIGNal:BAUDrate <baudrate> (see page 523)	:SBUS<n>:LIN:SIGNal:BAUDrate? (see page 523)	<baudrate> ::= integer from 2400 to 625000 in 100 b/s increments
:SBUS<n>:LIN:SOURce <source> (see page 524)	:SBUS<n>:LIN:SOURce? (see page 524)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:LIN:STANdard <std> (see page 525)	:SBUS<n>:LIN:STANdard? (see page 525)	<std> ::= {LIN13 | LIN20}
:SBUS<n>:LIN:SYNCbreak <value> (see page 526)	:SBUS<n>:LIN:SYNCbreak? (see page 526)	<value> ::= integer = {11 | 12 | 13}
:SBUS<n>:LIN:TRIGger <condition> (see page 527)	:SBUS<n>:LIN:TRIGger? (see page 527)	<condition> ::= {SYNCbreak | ID | DATA}
:SBUS<n>:LIN:TRIGger:ID <value> (see page 528)	:SBUS<n>:LIN:TRIGger:ID? (see page 528)	<value> ::= 7-bit integer in decimal, <nondecimal>, or <string> from 0-63 or 0x00-0x3f <nondecimal> ::= #Hnn where n ::= {0,..,9 | A,..,F} for hexadecimal <nondecimal> ::= #Bnn...n where n ::= {0 | 1} for binary <string> ::= "0xnn" where n ::= {0,..,9 | A,..,F} for hexadecimal

Table 74 :SBUS<n>:LIN Commands Summary (continued)

Command	Query	Options and Query Returns
:SBUS<n>:LIN:TRIGger:PATTern:DATA <string> (see page 529)	:SBUS<n>:LIN:TRIGger:PATTern:DATA? (see page 529)	<string> ::= "n" where n ::= 32-bit integer in unsigned decimal when <base> = DECimal <string> ::= "nn...n" where n ::= {0 | 1 | X | $} when <base> = BINary <string> ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $} when <base> = HEX
:SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth <length> (see page 531)	:SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth? (see page 531)	<length> ::= integer from 1 to 8 in NR1 format
:SBUS<n>:LIN:TRIGger:PATTern:FORMat <base> (see page 532)	:SBUS<n>:LIN:TRIGger:PATTern:FORMat? (see page 532)	<base> ::= {BINary | HEX | DECimal}

:SBUS<n>:LIN:PARity

N (see page 828)

Command Syntax

```
:SBUS<n>:LIN:PARity <display>

<display> ::= {{1 | ON} | {0 | OFF}}
```

The :SBUS<n>:LIN:PARity command determines whether the parity bits are included as the most significant bits (MSB) in the display of the Frame Id field in the LIN decode bus.

Query Syntax

```
:SBUS<n>:LIN:PARity?
```

The :SBUS<n>:LIN:PARity? query returns the current LIN parity bits display setting of the serial decode bus.

Return Format

```
<display><NL>

<display> ::= {0 | 1}
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:LIN Commands" on page 519

:SBUS<n>:LIN:SAMPlepoint

(see page 828)

Command Syntax

```
:SBUS<n>:LIN:SAMPlepoint <value>

<value><NL>

<value> ::= {60 | 62.5 | 68 | 70 | 75 | 80 | 87.5} in NR3 format
```

The :SBUS<n>:LIN:SAMPlepoint command sets the point during the bit time where the bit level is sampled to determine whether the bit is dominant or recessive. The sample point represents the percentage of time between the beginning of the bit time to the end of the bit time.

NOTE The sample point values are not limited by the baud rate.

Query Syntax

```
:SBUS<n>:LIN:SAMPlepoint?
```

The :SBUS<n>:LIN:SAMPlepoint? query returns the current LIN sample point setting.

Return Format

```
<value><NL>

<value> ::= {60 | 62.5 | 68 | 70 | 75 | 80 | 87.5} in NR3 format
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:LIN:TRIGger" on page 527

:SBUS<n>:LIN:SIGNal:BAUDrate

N (see page 828)

Command Syntax

```
:SBUS<n>:LIN:SIGNal:BAUDrate <baudrate>

<baudrate> ::= integer from 2400 to 625000 in 100 b/s increments
```

The :SBUS<n>:LIN:SIGNal:BAUDrate command sets the standard baud rate of the LIN signal from 2400 b/s to 625 kb/s in 100 b/s increments. If you enter a baud rate that is not divisible by 100 b/s, the baud rate is set to the nearest baud rate divisible by 100 b/s.

Query Syntax

```
:SBUS<n>:LIN:SIGNal:BAUDrate?
```

The :SBUS<n>:LIN:SIGNal:BAUDrate? query returns the current LIN baud rate setting.

Return Format

```
<baudrate><NL>

<baudrate> ::= integer from 2400 to 625000 in 100 b/s increments
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:LIN:TRIGger" on page 527
- ":SBUS<n>:LIN:SOURce" on page 524

:SBUS<n>:LIN:SOURce

(see page 828)

Command Syntax

```
:SBUS<n>:LIN:SOURce <source>
<source> ::= {CHANnel<n> | EXTernal}
<n> ::= 1 to (# analog channels) in NR1 format
```

The :SBUS<n>:LIN:SOURce command sets the source for the LIN signal.

NOTE EXTernal can be specified as the source on 2-channel DSOX1200-Series oscilloscopes only.

Query Syntax

```
:SBUS<n>:LIN:SOURce?
```

The :SBUS<n>:LIN:SOURce? query returns the current source for the LIN signal.

Return Format

```
<source><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:LIN:TRIGger" on page 527

:SBUS<n>:LIN:STANdard

N (see page 828)

Command Syntax

```
:SBUS<n>:LIN:STANdard <std>

<std> ::= {LIN13 | LIN20}
```

The :SBUS<n>:LIN:STANdard command sets the LIN standard in effect for triggering and decoding to be LIN1.3 or LIN2.0.

Query Syntax

```
:SBUS<n>:LIN:STANdard?
```

The :SBUS<n>:LIN:STANdard? query returns the current LIN standard setting.

Return Format

```
<std><NL>

<std> ::= {LIN13 | LIN20}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:LIN:SOURce" on page 524

:SBUS<n>:LIN:SYNCbreak

(see page 828)

Command Syntax

```
:SBUS<n>:LIN:SYNCbreak <value>

<value> ::= integer = {11 | 12 | 13}
```

The :SBUS<n>:LIN:SYNCbreak command sets the length of the LIN sync break to be greater than or equal to 11, 12, or 13 clock lengths. The sync break is the idle period in the bus activity at the beginning of each packet that distinguishes one information packet from the previous one.

Query Syntax

```
:SBUS<n>:LIN:SYNCbreak?
```

The :SBUS<n>:LIN:SYNCbreak? query returns the current LIN sync break setting.

Return Format

```
<value><NL>

<value> ::= {11 | 12 | 13}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:LIN:SOURce" on page 524

:SBUS<n>:LIN:TRIGger

N (see page 828)

Command Syntax

```
:SBUS<n>:LIN:TRIGger <condition>

<condition> ::= {SYNCbreak | ID | DATA}
```

The :SBUS<n>:LIN:TRIGger command sets the LIN trigger condition to be:

- SYNCbreak — Sync Break.
- ID — Frame ID.

  Use the :SBUS<n>:LIN:TRIGger:ID command to specify the frame ID.
- DATA — Frame ID and Data.

  Use the :SBUS<n>:LIN:TRIGger:ID command to specify the frame ID.

  Use the :SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth and :SBUS<n>:LIN:TRIGger:PATTern:DATA commands to specify the data string length and value.

Query Syntax

```
:SBUS<n>:LIN:TRIGger?
```

The :SBUS<n>:LIN:TRIGger? query returns the current LIN trigger value.

Return Format

```
<condition><NL>

<condition> ::= {SYNC | ID | DATA}
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:LIN:TRIGger:ID" on page 528
- ":SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth" on page 531
- ":SBUS<n>:LIN:TRIGger:PATTern:DATA" on page 529
- ":SBUS<n>:LIN:SOURce" on page 524

:SBUS<n>:LIN:TRIGger:ID

(see page 828)

Command Syntax

```
:SBUS<n>:LIN:TRIGger:ID <value>

<value> ::= 7-bit integer in decimal, <nondecimal>, or <string>
            from 0-63 or 0x00-0x3f

<nondecimal> ::= #Hnn where n ::= {0,..,9 | A,..,F} for hexadecimal

<nondecimal> ::= #Bnn...n where n ::= {0 | 1} for binary

<string> ::= "0xnn" where n ::= {0,..,9 | A,..,F} for hexadecimal
```

The :SBUS<n>:LIN:TRIGger:ID command defines the LIN identifier searched for in each CAN message when the LIN trigger mode is set to frame ID.

Setting the ID to a value of "-1" results in "0xXX" which is equivalent to all IDs.

Query Syntax

```
:SBUS<n>:LIN:TRIGger:ID?
```

The :SBUS<n>:LIN:TRIGger:ID? query returns the current LIN identifier setting.

Return Format

```
<value><NL>

<value> ::= integer in decimal
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:LIN:TRIGger" on page 527
- ":SBUS<n>:LIN:SOURce" on page 524

:SBUS<n>:LIN:TRIGger:PATTern:DATA

N (see page 828)

Command Syntax

```
:SBUS<n>:LIN:TRIGger:PATTern:DATA <string>

<string> ::= "n" where n ::= 32-bit integer in unsigned decimal when
             <base> = DECimal

<string> ::= "nn...n" where n ::= {0 | 1 | X | $} when
             <base> = BINary

<string> ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $} when
             <base> = HEX
```

NOTE <base> is specified with the :SBUS<n>:LIN:TRIGger:PATTern:FORMat command. The default <base> is BINary.

The :SBUS<n>:LIN:TRIGger:PATTern:DATA command specifies the LIN trigger data pattern searched for in each LIN data field.

Set a <string> bit to "0" or "1" to set the corresponding bit in the data pattern to low or high, respectively.

Set a <string> bit to "X" to ignore (mask off) that bit in the data pattern.

Use the "$" character to indicate that the value of the corresponding bit will not be changed (the existing bit value is used).

When <base> = DECimal, the "X" and "$" characters cannot be entered. When queried, the "$" character is returned when any bits in the pattern have the value of "X" and <base> = DECimal. When any bits in a given nibble have the value of "X" and <base> = HEX, the "$" character is returned for the corresponding nibble.

NOTE The length of the trigger data value is determined by the :SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth command.

NOTE If more bits are sent for <string> than the specified trigger pattern data length, the most significant bits will be truncated. If the data length size is changed after the <string> is programmed, the added or deleted bits will be added to or deleted from the least significant bits.

Query Syntax

```
:SBUS<n>:LIN:TRIGger:PATTern:DATA?
```

The :SBUS<n>:LIN:TRIGger:PATTern:DATA? query returns the currently specified LIN trigger data pattern.

Return Format

```
<string><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:LIN:TRIGger:PATTern:FORMat" on page 532
- ":SBUS<n>:LIN:TRIGger" on page 527
- ":SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth" on page 531

:SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth

N (see page 828)

Command Syntax

```
:SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth <length>

<length> ::= integer from 1 to 8 in NR1 format
```

The :SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth command sets the number of 8-bit bytes in the LIN data string. The number of bytes in the string can be anywhere from 1 bytes to 8 bytes (64 bits). The value for these bytes is set by the :SBUS<n>:LIN:TRIGger:PATTern:DATA command.

Query Syntax

```
:SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth?
```

The :SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth? query returns the current LIN data pattern length setting.

Return Format

```
<count><NL>

<count> ::= integer from 1 to 8 in NR1 format
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:LIN:TRIGger:PATTern:DATA" on page 529
- ":SBUS<n>:LIN:SOURce" on page 524

:SBUS<n>:LIN:TRIGger:PATTern:FORMat

N (see page 828)

Command Syntax

```
:SBUS<n>:LIN:TRIGger:PATTern:FORMat <base>

<base> ::= {BINary | HEX | DECimal}
```

The :SBUS<n>:LIN:TRIGger:PATTern:FORMat command sets the entry (and query) number base used by the :SBUS<n>:LIN:TRIGger:PATTern:DATA command. The default <base> is BINary.

Query Syntax

```
:SBUS<n>:LIN:TRIGger:PATTern:FORMat?
```

The :SBUS<n>:LIN:TRIGger:PATTern:FORMat? query returns the currently set number base for LIN pattern data.

Return Format

```
<base><NL>

<base> ::= {BIN | HEX | DEC}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:LIN:TRIGger:PATTern:DATA" on page 529
- ":SBUS<n>:LIN:TRIGger:PATTern:DATA:LENGth" on page 531

:SBUS<n>:SPI Commands

NOTE These commands are valid on DSOX1200-Series oscilloscopes when the low-speed IIC and SPI serial decode license (EMBD) is enabled.

Table 75 :SBUS<n>:SPI Commands Summary

Command	Query	Options and Query Returns
:SBUS<n>:SPI:BITorder <order> (see page 535)	:SBUS<n>:SPI:BITorder? (see page 535)	<order> ::= {LSBFirst | MSBFirst}
:SBUS<n>:SPI:CLOCk:SLOPe <slope> (see page 536)	:SBUS<n>:SPI:CLOCk:SLOPe? (see page 536)	<slope> ::= {NEGative | POSitive}
:SBUS<n>:SPI:CLOCk:TIMeout <time_value> (see page 537)	:SBUS<n>:SPI:CLOCk:TIMeout? (see page 537)	<time_value> ::= time in seconds in NR3 format
:SBUS<n>:SPI:FRAMing <value> (see page 538)	:SBUS<n>:SPI:FRAMing? (see page 538)	<value> ::= {CHIPselect | {NCHipselect | NOTC} | TIMeout}
:SBUS<n>:SPI:SOURce:CLOCk <source> (see page 539)	:SBUS<n>:SPI:SOURce:CLOCk? (see page 539)	<value> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:SPI:SOURce:DATA <source> (see page 540)	:SBUS<n>:SPI:SOURce:DATA? (see page 540)	<value> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:SPI:SOURce:FRAMe <source> (see page 541)	:SBUS<n>:SPI:SOURce:FRAMe? (see page 541)	<value> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only

Table 75 :SBUS<n>:SPI Commands Summary (continued)

Command	Query	Options and Query Returns
:SBUS<n>:SPI:SOURce:MISO <source> (see page 542)	:SBUS<n>:SPI:SOURce:MISO? (see page 542)	<value> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format
:SBUS<n>:SPI:SOURce:MOSI <source> (see page 543)	:SBUS<n>:SPI:SOURce:MOSI? (see page 543)	<value> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format
:SBUS<n>:SPI:TRIGger:PATTern:DATA <string> (see page 544)	:SBUS<n>:SPI:TRIGger:PATTern:DATA? (see page 544)	<string> ::= "nn...n" where n ::= {0 | 1 | X | $} <string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
:SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA <string> (see page 545)	:SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA? (see page 545)	<string> ::= "nn...n" where n ::= {0 | 1 | X | $} <string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
:SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh <width> (see page 546)	:SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh? (see page 546)	<width> ::= integer from 4 to 64 in NR1 format
:SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA <string> (see page 547)	:SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA? (see page 547)	<string> ::= "nn...n" where n ::= {0 | 1 | X | $} <string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
:SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh <width> (see page 548)	:SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh? (see page 548)	<width> ::= integer from 4 to 64 in NR1 format
:SBUS<n>:SPI:TRIGger:PATTern:WIDTh <width> (see page 549)	:SBUS<n>:SPI:TRIGger:PATTern:WIDTh? (see page 549)	<width> ::= integer from 4 to 64 in NR1 format
:SBUS<n>:SPI:TRIGger:TYPE <value> (see page 550)	:SBUS<n>:SPI:TRIGger:TYPE? (see page 550)	<value> ::= {MOSI | MISO}
:SBUS<n>:SPI:WIDTh <word_width> (see page 551)	:SBUS<n>:SPI:WIDTh? (see page 551)	<word_width> ::= integer 4-16 in NR1 format

:SBUS<n>:SPI:BITorder

(see page 828)

Command Syntax

```
:SBUS<n>:SPI:BITorder <order>

<order> ::= {LSBFirst | MSBFirst}
```

The :SBUS<n>:SPI:BITorder command selects the bit order, most significant bit first (MSB) or least significant bit first (LSB), used when displaying data in the serial decode waveform and in the Lister.

Query Syntax

```
:SBUS<n>:SPI:BITorder?
```

The :SBUS<n>:SPI:BITorder? query returns the current SPI decode bit order.

Return Format

```
<order><NL>

<order> ::= {LSBF | MSBF}
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:SPI Commands" on page 533

:SBUS<n>:SPI:CLOCk:SLOPe

N (see page 828)

Command Syntax

```
:SBUS<n>:SPI:CLOCk:SLOPe <slope>

<slope> ::= {NEGative | POSitive}
```

The :SBUS<n>:SPI:CLOCk:SLOPe command specifies the rising edge (POSitive) or falling edge (NEGative) of the SPI clock source that will clock in the data.

Query Syntax

```
:SBUS<n>:SPI:CLOCk:SLOPe?
```

The :SBUS<n>:SPI:CLOCk:SLOPe? query returns the current SPI clock source slope.

Return Format

```
<slope><NL>

<slope> ::= {NEG | POS}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:CLOCk:TIMeout" on page 537
- ":SBUS<n>:SPI:SOURce:CLOCk" on page 539

:SBUS<n>:SPI:CLOCk:TIMeout

(see page 828)

Command Syntax

```
:SBUS<n>:SPI:CLOCk:TIMeout <time_value>

<time_value> ::= time in seconds in NR3 format
```

The :SBUS<n>:SPI:CLOCk:TIMeout command sets the SPI signal clock timeout resource in seconds from 100 ns to 10 s when the :SBUS<n>:SPI:FRAMing command is set to TIMeout. The timer is used to frame a signal by a clock timeout.

Query Syntax

```
:SBUS<n>:SPI:CLOCk:TIMeout?
```

The :SBUS<n>:SPI:CLOCk:TIMeout? query returns current SPI clock timeout setting.

Return Format

```
<time value><NL>

<time_value> ::= time in seconds in NR3 format
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:CLOCk:SLOPe" on page 536
- ":SBUS<n>:SPI:SOURce:CLOCk" on page 539
- ":SBUS<n>:SPI:FRAMing" on page 538

:SBUS<n>:SPI:FRAMing

(see page 828)

Command Syntax

```
:SBUS<n>:SPI:FRAMing <value>

<value> ::= {CHIPselect | {NCHipselect | NOTC} | TIMeout}
```

The :SBUS<n>:SPI:FRAMing command sets the SPI trigger framing value. If TIMeout is selected, the timeout value is set by the :SBUS<n>:SPI:CLOCk:TIMeout command.

NOTE The NOTC value is deprecated. It is the same as NCHipselect.

Query Syntax

```
:SBUS<n>:SPI:FRAMing?
```

The :SBUS<n>:SPI:FRAMing? query returns the current SPI framing value.

Return Format

```
<value><NL>

<value> ::= {CHIP | NCH | TIM}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:SPI:CLOCk:TIMeout" on page 537
- ":SBUS<n>:SPI:SOURce:FRAMe" on page 541

:SBUS<n>:SPI:SOURce:CLOCk

N (see page 828)

Command Syntax

```
:SBUS<n>:SPI:SOURce:CLOCk <source>

<source> ::= {CHANnel<n> | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :SBUS<n>:SPI:SOURce:CLOCk command sets the source for the SPI serial clock.

NOTE EXTernal can be specified as the source on 2-channel DSOX1200-Series oscilloscopes only.

Query Syntax

```
:SBUS<n>:SPI:SOURce:CLOCk?
```

The :SBUS<n>:SPI:SOURce:CLOCk? query returns the current source for the SPI serial clock.

Return Format

```
<source><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:CLOCk:SLOPe" on page 536
- ":SBUS<n>:SPI:CLOCk:TIMeout" on page 537
- ":SBUS<n>:SPI:SOURce:FRAMe" on page 541
- ":SBUS<n>:SPI:SOURce:MOSI" on page 543
- ":SBUS<n>:SPI:SOURce:MISO" on page 542

:SBUS<n>:SPI:SOURce:DATA

(see page 828)

Command Syntax

```
:SBUS<n>:SPI:SOURce:DATA <source>

<source> ::= {CHANnel<n> | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format
```

On 2-channel DSOX1200-Series oscilloscopes (that support 3-wire SPI), the :SBUS<n>:SPI:SOURce:DATA command sets the source for the SPI serial data.

NOTE EXTernal can be specified as the source on 2-channel DSOX1200-Series oscilloscopes only.

Query Syntax

```
:SBUS<n>:SPI:SOURce:DATA?
```

The :SBUS<n>:SPI:SOURce:DATA? query returns the current source for the SPI serial data.

Return Format

```
<source><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:SOURce:CLOCk" on page 539
- ":SBUS<n>:SPI:SOURce:FRAMe" on page 541
- ":SBUS<n>:SPI:TRIGger:PATTern:DATA" on page 544
- ":SBUS<n>:SPI:TRIGger:PATTern:WIDTh" on page 549

:SBUS<n>:SPI:SOURce:FRAMe

N (see page 828)

Command Syntax

```
:SBUS<n>:SPI:SOURce:FRAMe <source>

<source> ::= {CHANnel<n> | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :SBUS<n>:SPI:SOURce:FRAMe command sets the frame source when :SBUS<n>:SPI:FRAMing is set to CHIPselect or NOTChipselect.

NOTE EXTernal can be specified as the source on 2-channel DSOX1200-Series oscilloscopes only.

Query Syntax

```
:SBUS<n>:SPI:SOURce:FRAMe?
```

The :SBUS<n>:SPI:SOURce:FRAMe? query returns the current frame source for the SPI serial frame.

Return Format

```
<source><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:SOURce:CLOCk" on page 539
- ":SBUS<n>:SPI:SOURce:MOSI" on page 543
- ":SBUS<n>:SPI:SOURce:MISO" on page 542
- ":SBUS<n>:SPI:FRAMing" on page 538

:SBUS<n>:SPI:SOURce:MISO

(see page 828)

Command Syntax

```
:SBUS<n>:SPI:SOURce:MISO <source>

<source> ::= {CHANnel<n>}

<n> ::= 1 to (# analog channels) in NR1 format
```

On 4-channel DSOX1200-Series oscilloscopes (that support 4-wire SPI), the :SBUS<n>:SPI:SOURce:MISO command sets the source for the SPI serial MISO data.

Query Syntax

```
:SBUS<n>:SPI:SOURce:MISO?
```

The :SBUS<n>:SPI:SOURce:MISO? query returns the current source for the SPI serial MISO data.

Return Format

```
<source><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:SOURce:MOSI" on page 543
- ":SBUS<n>:SPI:SOURce:CLOCk" on page 539
- ":SBUS<n>:SPI:SOURce:FRAMe" on page 541
- ":SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA" on page 545
- ":SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA" on page 547
- ":SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh" on page 546
- ":SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh" on page 548

:SBUS<n>:SPI:SOURce:MOSI

N (see page 828)

Command Syntax

```
:SBUS<n>:SPI:SOURce:MOSI <source>

<source> ::= {CHANnel<n>}

<n> ::= 1 to (# analog channels) in NR1 format
```

On 4-channel DSOX1200-Series oscilloscopes (that support 4-wire SPI), the :SBUS<n>:SPI:SOURce:MOSI command sets the source for the SPI serial MOSI data.

You can also use the equivalent :SBUS<n>:SPI:SOURce:DATA command to set the MOSI data source.

Query Syntax

```
:SBUS<n>:SPI:SOURce:MOSI?
```

The :SBUS<n>:SPI:SOURce:MOSI? query returns the current source for the SPI serial MOSI data.

Return Format

```
<source><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:SOURce:MISO" on page 542
- ":SBUS<n>:SPI:SOURce:CLOCk" on page 539
- ":SBUS<n>:SPI:SOURce:FRAMe" on page 541
- ":SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA" on page 545
- ":SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA" on page 547
- ":SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh" on page 546
- ":SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh" on page 548

:SBUS<n>:SPI:TRIGger:PATTern:DATA

(see page 828)

Command Syntax

```
:SBUS<n>:SPI:TRIGger:PATTern:DATA <string>

<string> ::= "nn...n" where n ::= {0 | 1 | X | $}

<string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
```

On 2-channel DSOX1200-Series oscilloscopes (that support 3-wire SPI), the :SBUS<n>:SPI:TRIGger:PATTern:DATA command defines the SPI data pattern resource according to the string parameter. This pattern, along with the data width, control the data pattern searched for in the data stream.

If the string parameter starts with "0x", it is a hexadecimal string made up of hexadecimal and X (don't care) characters; otherwise, it is a binary string made up of 0, 1, and X (don't care) characters.

NOTE **The :SBUS<n>:SPI:TRIGger:PATTern:WIDTh should be set before :SBUS<n>:SPI:TRIGger:PATTern:DATA.**

Query Syntax

```
:SBUS<n>:SPI:TRIGger:PATTern:DATA?
```

The :SBUS<n>:SPI:TRIGger:PATTern:DATA? query returns the current settings of the specified SPI data pattern resource in the binary string format.

Return Format

```
<string><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:TRIGger:PATTern:WIDTh" on page 549
- ":SBUS<n>:SPI:SOURce:DATA" on page 540

:SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA

N (see page 828)

Command Syntax

```
:SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA <string>

<string> ::= "nn...n" where n ::= {0 | 1 | X | $}

<string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
```

On 4-channel DSOX1200-Series oscilloscopes (that support 4-wire SPI), the :SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA command defines the SPI MISO data pattern resource according to the string parameter. This pattern, along with the data width, control the data pattern searched for in the data stream.

If the string parameter starts with "0x", it is a hexadecimal string made up of hexadecimal and X (don't care) characters; otherwise, it is a binary string made up of 0, 1, and X (don't care) characters.

NOTE The :SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh should be set before :SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA.

Query Syntax

```
:SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA?
```

The :SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA? query returns the current settings of the specified SPI MISO data pattern resource in the binary string format.

Return Format

```
<string><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh" on page 546
- ":SBUS<n>:SPI:SOURce:MISO" on page 542

:SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh

N (see page 828)

Command Syntax

```
:SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh <width>

<width> ::= integer from 4 to 64 in NR1 format
```

On 4-channel DSOX1200-Series oscilloscopes (that support 4-wire SPI), the :SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh command sets the width of the SPI MISO data pattern anywhere from 4 bits to 64 bits.

NOTE **The :SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh should be set before :SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA.**

Query Syntax

```
:SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh?
```

The :SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh? query returns the current SPI MISO data pattern width setting.

Return Format

```
<width><NL>

<width> ::= integer from 4 to 64 in NR1 format
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA" on page 545
- ":SBUS<n>:SPI:SOURce:MISO" on page 542

:SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA

N (see page 828)

Command Syntax

```
:SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA <string>

<string> ::= "nn...n" where n ::= {0 | 1 | X | $}

<string ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $}
```

On 4-channel DSOX1200-Series oscilloscopes (that support 4-wire SPI), the :SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA command defines the SPI MOSI data pattern resource according to the string parameter. This pattern, along with the data width, control the data pattern searched for in the data stream.

If the string parameter starts with "0x", it is a hexadecimal string made up of hexadecimal and X (don't care) characters; otherwise, it is a binary string made up of 0, 1, and X (don't care) characters.

NOTE The :SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh should be set before :SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA.

Query Syntax

```
:SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA?
```

The :SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA? query returns the current settings of the specified SPI MOSI data pattern resource in the binary string format.

Return Format

```
<string><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh" on page 548
- ":SBUS<n>:SPI:SOURce:MOSI" on page 543

:SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh

N (see page 828)

Command Syntax

```
:SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh <width>

<width> ::= integer from 4 to 64 in NR1 format
```

On 4-channel DSOX1200-Series oscilloscopes (that support 4-wire SPI), the :SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh command sets the width of the SPI MOSI data pattern anywhere from 4 bits to 64 bits.

NOTE **The :SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh should be set before :SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA.**

Query Syntax

```
:SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh?
```

The :SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh? query returns the current SPI MOSI data pattern width setting.

Return Format

```
<width><NL>

<width> ::= integer from 4 to 64 in NR1 format
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA" on page 547
- ":SBUS<n>:SPI:SOURce:MOSI" on page 543

:SBUS<n>:SPI:TRIGger:PATTern:WIDTh

N (see page 828)

Command Syntax

```
:SBUS<n>:SPI:TRIGger:PATTern:WIDTh <width>

<width> ::= integer from 4 to 64 in NR1 format
```

On 2-channel DSOX1200-Series oscilloscopes (that support 3-wire SPI), the :SBUS<n>:SPI:TRIGger:PATTern:WIDTh command sets the width of the SPI data pattern anywhere from 4 bits to 64 bits.

NOTE **The :SBUS<n>:SPI:TRIGger:PATTern:WIDTh should be set before :SBUS<n>:SPI:TRIGger:PATTern:DATA.**

Query Syntax

```
:SBUS<n>:SPI:TRIGger:PATTern:WIDTh?
```

The :SBUS<n>:SPI:TRIGger:PATTern:WIDTh? query returns the current SPI data pattern width setting.

Return Format

```
<width><NL>

<width> ::= integer from 4 to 64 in NR1 format
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:TRIGger:PATTern:DATA" on page 544
- ":SBUS<n>:SPI:SOURce:DATA" on page 540

:SBUS<n>:SPI:TRIGger:TYPE

(see page 828)

Command Syntax

```
:SBUS<n>:SPI:TRIGger:TYPE <value>

<value> ::= {MOSI | MISO}
```

The :SBUS<n>:SPI:TRIGger:TYPE command specifies whether the SPI trigger will be on the MOSI data or the MISO data.

When triggering on MOSI data, the data value is specified by the :SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA and :SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh commands.

When triggering on MISO data, the data value is specified by the :SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA and :SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh commands.

Query Syntax

```
:SBUS<n>:SPI:TRIGger:TYPE?
```

The :SBUS<n>:SPI:TRIGger:TYPE? query returns the current SPI trigger type setting.

Return Format

```
<value><NL>

<value> ::= {MOSI | MISO}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":SBUS<n>:SPI:SOURce:MOSI" on page 543
- ":SBUS<n>:SPI:SOURce:MISO" on page 542
- ":SBUS<n>:SPI:TRIGger:PATTern:MISO:DATA" on page 545
- ":SBUS<n>:SPI:TRIGger:PATTern:MOSI:DATA" on page 547
- ":SBUS<n>:SPI:TRIGger:PATTern:MISO:WIDTh" on page 546
- ":SBUS<n>:SPI:TRIGger:PATTern:MOSI:WIDTh" on page 548
- ":TRIGger:MODE" on page 624

:SBUS<n>:SPI:WIDTh

N (see page 828)

Command Syntax

```
:SBUS<n>:SPI:WIDTh <word_width>

<word_width> ::= integer 4-16 in NR1 format
```

The :SBUS<n>:SPI:WIDTh command determines the number of bits in a word of data for SPI.

Query Syntax

```
:SBUS<n>:SPI:WIDTh?
```

The :SBUS<n>:SPI:WIDTh? query returns the current SPI decode word width.

Return Format

```
<word_width><NL>

<word_width> ::= integer 4-16 in NR1 format
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:SPI Commands" on page 533

:SBUS<n>:UART Commands

NOTE These commands are valid when the UART/RS-232 triggering and serial decode license (EMBD) is enabled.

Table 76 :SBUS<n>:UART Commands Summary

Command	Query	Options and Query Returns
:SBUS<n>:UART:BASE <base> (see page 555)	:SBUS<n>:UART:BASE? (see page 555)	<base> ::= {ASCii | BINary | HEX}
:SBUS<n>:UART:BAUDrate <baudrate> (see page 556)	:SBUS<n>:UART:BAUDrate? (see page 556)	<baudrate> ::= integer from 100 to 8000000
:SBUS<n>:UART:BITorder <bitorder> (see page 557)	:SBUS<n>:UART:BITorder? (see page 557)	<bitorder> ::= {LSBFirst | MSBFirst}
n/a	:SBUS<n>:UART:COUNt:ERRor? (see page 558)	<frame_count> ::= integer in NR1 format
:SBUS<n>:UART:COUNt:RESet (see page 559)	n/a	n/a
n/a	:SBUS<n>:UART:COUNt:RXFRames? (see page 560)	<frame_count> ::= integer in NR1 format
n/a	:SBUS<n>:UART:COUNt:TXFRames? (see page 561)	<frame_count> ::= integer in NR1 format
:SBUS<n>:UART:FRAMing <value> (see page 562)	:SBUS<n>:UART:FRAMing? (see page 562)	<value> ::= {OFF | <decimal> | <nondecimal>} <decimal> ::= 8-bit integer from 0-255 (0x00-0xff) <nondecimal> ::= #Hnn where n ::= {0,..,9 | A,..,F} for hexadecimal <nondecimal> ::= #Bnn...n where n ::= {0 | 1} for binary
:SBUS<n>:UART:PARity <parity> (see page 563)	:SBUS<n>:UART:PARity? (see page 563)	<parity> ::= {EVEN | ODD | NONE}
:SBUS<n>:UART:POLarity <polarity> (see page 564)	:SBUS<n>:UART:POLarity? (see page 564)	<polarity> ::= {HIGH | LOW}

Table 76 :SBUS<n>:UART Commands Summary (continued)

Command	Query	Options and Query Returns
:SBUS<n>:UART:SOURce:RX <source> (see page 565)	:SBUS<n>:UART:SOURce:RX? (see page 565)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:UART:SOURce:TX <source> (see page 566)	:SBUS<n>:UART:SOURce:TX? (see page 566)	<source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel DSOX1200-Series oscilloscopes only
:SBUS<n>:UART:TRIGger:BASE <base> (see page 567)	:SBUS<n>:UART:TRIGger:BASE? (see page 567)	<base> ::= {ASCii | HEX}
:SBUS<n>:UART:TRIGger:BURSt <value> (see page 568)	:SBUS<n>:UART:TRIGger:BURSt? (see page 568)	<value> ::= {OFF | 1 to 4096 in NR1 format}
:SBUS<n>:UART:TRIGger:DATA <value> (see page 569)	:SBUS<n>:UART:TRIGger:DATA? (see page 569)	<value> ::= 8-bit integer from 0-255 (0x00-0xff) in decimal, <hexadecimal>, <binary>, or <quoted_string> format <hexadecimal> ::= #Hnn where n ::= {0,..,9 | A,..,F} for hexadecimal <binary> ::= #Bnn...n where n ::= {0 | 1} for binary <quoted_string> ::= any of the 128 valid 7-bit ASCII characters (or standard abbreviations)
:SBUS<n>:UART:TRIGger:IDLE <time_value> (see page 570)	:SBUS<n>:UART:TRIGger:IDLE? (see page 570)	<time_value> ::= time from 1 us to 10 s in NR3 format
:SBUS<n>:UART:TRIGger:QUALifier <value> (see page 571)	:SBUS<n>:UART:TRIGger:QUALifier? (see page 571)	<value> ::= {EQUal | NOTequal | GREaterthan | LESSthan}

Table 76 :SBUS<n>:UART Commands Summary (continued)

Command	Query	Options and Query Returns
:SBUS<n>:UART:TRIGger:TYPE <value> (see page 572)	:SBUS<n>:UART:TRIGger:TYPE? (see page 572)	<value> ::= {RSTArt | RSTOp | RDATa | RD1 | RD0 | RDX | PARityerror | TSTArt | TSTOp | TDATa | TD1 | TD0 | TDX}
:SBUS<n>:UART:WIDTh <width> (see page 573)	:SBUS<n>:UART:WIDTh? (see page 573)	<width> ::= {5 | 6 | 7 | 8 | 9}

:SBUS<n>:UART:BASE

(see page 828)

Command Syntax

```
:SBUS<n>:UART:BASE <base>

<base> ::= {ASCii | BINary | HEX}
```

The :SBUS<n>:UART:BASE command determines the base to use for the UART decode and Lister display.

Query Syntax

```
:SBUS<n>:UART:BASE?
```

The :SBUS<n>:UART:BASE? query returns the current UART decode and Lister base setting.

Return Format

```
<base><NL>

<base> ::= {ASCii | BINary | HEX}
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:UART Commands" on page 552

:SBUS<n>:UART:BAUDrate

(see page 828)

Command Syntax

```
:SBUS<n>:UART:BAUDrate <baudrate>

<baudrate> ::= integer from 100 to 8000000
```

The :SBUS<n>:UART:BAUDrate command selects the bit rate (in bps) for the serial decoder and/or trigger when in UART mode. The baud rate can be set from 100 b/s to 8 Mb/s.

If the baud rate you select does not match the system baud rate, false triggers may occur.

Query Syntax

```
:SBUS<n>:UART:BAUDrate?
```

The :SBUS<n>:UART:BAUDrate? query returns the current UART baud rate setting.

Return Format

```
<baudrate><NL>

<baudrate> ::= integer from 100 to 8000000
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:TYPE" on page 572

:SBUS<n>:UART:BITorder

(see page 828)

Command Syntax

```
:SBUS<n>:UART:BITorder <bitorder>

<bitorder> ::= {LSBFirst | MSBFirst}
```

The :SBUS<n>:UART:BITorder command specifies the order of transmission used by the physical Tx and Rx input signals for the serial decoder and/or trigger when in UART mode. LSBFirst sets the least significant bit of each message "byte" as transmitted first. MSBFirst sets the most significant bit as transmitted first.

Query Syntax

```
:SBUS<n>:UART:BITorder?
```

The :SBUS<n>:UART:BITorder? query returns the current UART bit order setting.

Return Format

```
<bitorder><NL>

<bitorder> ::= {LSBF | MSBF}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:TYPE" on page 572
- ":SBUS<n>:UART:SOURce:RX" on page 565
- ":SBUS<n>:UART:SOURce:TX" on page 566

:SBUS<n>:UART:COUNt:ERRor

(see page 828)

Query Syntax `:SBUS<n>:UART:COUNt:ERRor?`

Returns the UART error frame count.

Return Format `<frame_count><NL>`

`<frame_count> ::= integer in NR1 format`

Errors

- "-241, Hardware missing" on page 789

See Also

- ":SBUS<n>:UART:COUNt:RESet" on page 559
- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:UART Commands" on page 552

:SBUS<n>:UART:COUNt:RESet

(see page 828)

Command Syntax `:SBUS<n>:UART:COUNt:RESet`

Resets the UART frame counters.

Errors
- "-241, Hardware missing" on page 789

See Also
- ":SBUS<n>:UART:COUNt:ERRor" on page 558
- ":SBUS<n>:UART:COUNt:RXFRames" on page 560
- ":SBUS<n>:UART:COUNt:TXFRames" on page 561
- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:UART Commands" on page 552

:SBUS<n>:UART:COUNt:RXFRames

(see page 828)

Query Syntax `:SBUS<n>:UART:COUNt:RXFRames?`

Returns the UART Rx frame count.

Return Format `<frame_count><NL>`

`<frame_count> ::= integer in NR1 format`

Errors

- "-241, Hardware missing" on page 789

See Also

- ":SBUS<n>:UART:COUNt:RESet" on page 559
- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:UART Commands" on page 552

:SBUS<n>:UART:COUNt:TXFRames

N (see page 828)

Query Syntax `:SBUS<n>:UART:COUNt:TXFRames?`

Returns the UART Tx frame count.

Return Format `<frame_count><NL>`

`<frame_count> ::= integer in NR1 format`

Errors

- "-241, Hardware missing" on page 789

See Also

- ":SBUS<n>:UART:COUNt:RESet" on page 559
- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:MODE" on page 491
- ":SBUS<n>:UART Commands" on page 552

:SBUS<n>:UART:FRAMing

N (see page 828)

Command Syntax

```
:SBUS<n>:UART:FRAMing <value>

<value> ::= {OFF | <decimal> | <nondecimal>}

<decimal> ::= 8-bit integer in decimal from 0-255 (0x00-0xff)

<nondecimal> ::= #Hnn where n ::= {0,..,9 | A,..,F} for hexadecimal

<nondecimal> ::= #Bnn...n where n ::= {0 | 1} for binary
```

The :SBUS<n>:UART:FRAMing command determines the byte value to use for framing (end of packet) or to turn off framing for UART decode.

Query Syntax

```
:SBUS<n>:UART:FRAMing?
```

The :SBUS<n>:UART:FRAMing? query returns the current UART decode base setting.

Return Format

```
<value><NL>

<value> ::= {OFF | <decimal>}

<decimal> ::= 8-bit integer in decimal from 0-255
```

Errors

- "-241, Hardware missing" on page 789

See Also

- "Introduction to :SBUS<n> Commands" on page 487
- ":SBUS<n>:UART Commands" on page 552

:SBUS<n>:UART:PARity

N (see page 828)

Command Syntax

```
:SBUS<n>:UART:PARity <parity>

<parity> ::= {EVEN | ODD | NONE}
```

The :SBUS<n>:UART:PARity command selects the parity to be used with each message "byte" for the serial decoder and/or trigger when in UART mode.

Query Syntax

```
:SBUS<n>:UART:PARity?
```

The :SBUS<n>:UART:PARity? query returns the current UART parity setting.

Return Format

```
<parity><NL>

<parity> ::= {EVEN | ODD | NONE}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:TYPE" on page 572

:SBUS<n>:UART:POLarity

N (see page 828)

Command Syntax

```
:SBUS<n>:UART:POLarity <polarity>

<polarity> ::= {HIGH | LOW}
```

The :SBUS<n>:UART:POLarity command selects the polarity as idle low or idle high for the serial decoder and/or trigger when in UART mode.

Query Syntax

```
:SBUS<n>:UART:POLarity?
```

The :SBUS<n>:UART:POLarity? query returns the current UART polarity setting.

Return Format

```
<polarity><NL>

<polarity> ::= {HIGH | LOW}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:TYPE" on page 572

:SBUS<n>:UART:SOURce:RX

N (see page 828)

Command Syntax

```
:SBUS<n>:UART:SOURce:RX <source>

<source> ::= {CHANnel<n> | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :SBUS<n>:UART:SOURce:RX command controls which signal is used as the Rx source by the serial decoder and/or trigger when in UART mode.

NOTE EXTernal can be specified as the source on 2-channel DSOX1200-Series oscilloscopes only.

Query Syntax

```
:SBUS<n>:UART:SOURce:RX?
```

The :SBUS<n>:UART:SOURce:RX? query returns the current source for the UART Rx signal.

Return Format

```
<source><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:TYPE" on page 572
- ":SBUS<n>:UART:BITorder" on page 557

:SBUS<n>:UART:SOURce:TX

N (see page 828)

Command Syntax

```
:SBUS<n>:UART:SOURce:TX <source>

<source> ::= {CHANnel<n> | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :SBUS<n>:UART:SOURce:TX command controls which signal is used as the Tx source by the serial decoder and/or trigger when in UART mode.

NOTE EXTernal can be specified as the source on 2-channel DSOX1200-Series oscilloscopes only.

Query Syntax

```
:SBUS<n>:UART:SOURce:TX?
```

The :SBUS<n>:UART:SOURce:TX? query returns the current source for the UART Tx signal.

Return Format

```
<source><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:TYPE" on page 572
- ":SBUS<n>:UART:BITorder" on page 557

:SBUS<n>:UART:TRIGger:BASE

(see page 828)

Command Syntax

```
:SBUS<n>:UART:TRIGger:BASE <base>

<base> ::= {ASCii | HEX}
```

The :SBUS<n>:UART:TRIGger:BASE command sets the front panel UART/RS232 trigger setup data selection option:

- ASCii – front panel data selection is from ASCII values.
- HEX – front panel data selection is from hexadecimal values.

The :SBUS<n>:UART:TRIGger:BASE setting does not affect the :SBUS<n>:UART:TRIGger:DATA command which can always set data values using ASCII or hexadecimal values.

NOTE **The :SBUS<n>:UART:TRIGger:BASE command is independent of the :SBUS<n>:UART:BASE command which affects decode and Lister only.**

Query Syntax

```
:SBUS<n>:UART:TRIGger:BASE?
```

The :SBUS<n>:UART:TRIGger:BASE? query returns the current UART base setting.

Return Format

```
<base><NL>

<base> ::= {ASC | HEX}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:DATA" on page 569

:SBUS<n>:UART:TRIGger:BURSt

N (see page 828)

Command Syntax

```
:SBUS<n>:UART:TRIGger:BURSt <value>

<value> ::= {OFF | 1 to 4096 in NR1 format}
```

The :SBUS<n>:UART:TRIGger:BURSt command selects the burst value (Nth frame after idle period) in the range 1 to 4096 or OFF, for the trigger when in UART mode.

Query Syntax

```
:SBUS<n>:UART:TRIGger:BURSt?
```

The :SBUS<n>:UART:TRIGger:BURSt? query returns the current UART trigger burst value.

Return Format

```
<value><NL>

<value> ::= {OFF | 1 to 4096 in NR1 format}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:IDLE" on page 570
- ":SBUS<n>:UART:TRIGger:TYPE" on page 572

:SBUS<n>:UART:TRIGger:DATA

N (see page 828)

Command Syntax

```
:SBUS<n>:UART:TRIGger:DATA <value>

<value> ::= 8-bit integer from 0-255 (0x00-0xff) in decimal,
            <hexadecimal>, <binary>, or <quoted_string> format

<hexadecimal> ::= #Hnn where n ::= {0,..,9 | A,..,F} for hexadecimal

<binary> ::= #Bnn...n where n ::= {0 | 1} for binary

<quoted_string> ::= any of the 128 valid 7-bit ASCII characters
                    (or standard abbreviations)
```

The :SBUS<n>:UART:TRIGger:DATA command selects the data byte value (0x00 to 0xFF) for the trigger QUALifier when in UART mode. The data value is used when one of the RD or TD trigger types is selected.

When entering an ASCII character via the quoted string, it must be one of the 128 valid characters (case-sensitive): "NUL", "SOH", "STX", "ETX", "EOT", "ENQ", "ACK", "BEL", "BS", "HT", "LF", "VT", "FF", "CR", "SO","SI", "DLE", "DC1", "DC2", "DC3", "DC4", "NAK", "SYN", "ETB", "CAN", "EM", "SUB", "ESC", "FS","GS", "RS", "US", "SP", "!", "\"", "#", "$", "%","&", "\'", "(", ")", "*", "+", ",", "-", ".", "/","0", "1", "2", "3", "4", "5", "6", "7", "8", "9",":", ";", "<", "=", ">", "?", "@", "A", "B", "C","D", "E", "F", "G", "H", "I", "J", "K", "L", "M","N", "O", "P", "Q", "R", "S", "T", "U", "V", "W", "X", "Y", "Z","[", "\\", "]", "^", "_", "`", "a", "b", "c", "d", "e", "f", "g", "h", "i", "j", "k", "l", "m", "n", "o", "p", "q", "r", "s", "t", "u", "v", "w", "x", "y", "z", "{", "|", "}", "~", or "DEL".

Query Syntax

```
:SBUS<n>:UART:TRIGger:DATA?
```

The :SBUS<n>:UART:TRIGger:DATA? query returns the current UART trigger data value.

Return Format

```
<value><NL>

<value> ::= 8-bit integer in decimal from 0-255
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:BASE" on page 567
- ":SBUS<n>:UART:TRIGger:TYPE" on page 572

:SBUS<n>:UART:TRIGger:IDLE

(see page 828)

Command Syntax

```
:SBUS<n>:UART:TRIGger:IDLE <time_value>

<time_value> ::= time from 1 us to 10 s in NR3 format
```

The :SBUS<n>:UART:TRIGger:IDLE command selects the value of the idle period for burst trigger in the range from 1 us to 10 s when in UART mode.

Query Syntax

```
:SBUS<n>:UART:TRIGger:IDLE?
```

The :SBUS<n>:UART:TRIGger:IDLE? query returns the current UART trigger idle period time.

Return Format

```
<time_value><NL>

<time_value> ::= time from 1 us to 10 s in NR3 format
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:BURSt" on page 568
- ":SBUS<n>:UART:TRIGger:TYPE" on page 572

:SBUS<n>:UART:TRIGger:QUALifier

N (see page 828)

Command Syntax

```
:SBUS<n>:UART:TRIGger:QUALifier <value>

<value> ::= {EQUal | NOTequal | GREaterthan | LESSthan}
```

The :SBUS<n>:UART:TRIGger:QUALifier command selects the data qualifier when :TYPE is set to RDATa, RD1, RD0, RDX, TDATa, TD1, TD0, or TDX for the trigger when in UART mode.

Query Syntax

```
:SBUS<n>:UART:TRIGger:QUALifier?
```

The :SBUS<n>:UART:TRIGger:QUALifier? query returns the current UART trigger qualifier.

Return Format

```
<value><NL>

<value> ::= {EQU | NOT | GRE | LESS}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:TYPE" on page 572

:SBUS<n>:UART:TRIGger:TYPE

(see page 828)

Command Syntax

```
:SBUS<n>:UART:TRIGger:TYPE <value>

<value> ::= {RSTArt | RSTOp | RDATa | RD1 | RD0 | RDX | PARityerror
             | TSTArt | TSTOp | TDATa | TD1 | TD0 | TDX}
```

The :SBUS<n>:UART:TRIGger:TYPE command selects the UART trigger type.

When one of the RD or TD types is selected, the :SBUS<n>:UART:TRIGger:DATA and :SBUS<n>:UART:TRIGger:QUALifier commands are used to specify the data value and comparison operator.

The RD1, RD0, RDX, TD1, TD0, and TDX types (for triggering on data and alert bit values) are only valid when a 9-bit width has been selected.

Query Syntax

```
:SBUS<n>:UART:TRIGger:TYPE?
```

The :SBUS<n>:UART:TRIGger:TYPE? query returns the current UART trigger data value.

Return Format

```
<value><NL>

<value> ::= {RSTA | RSTO | RDAT | RD1 | RD0 | RDX | PAR | TSTA |
             TSTO | TDAT | TD1 | TD0 | TDX}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:DATA" on page 569
- ":SBUS<n>:UART:TRIGger:QUALifier" on page 571
- ":SBUS<n>:UART:WIDTh" on page 573

:SBUS<n>:UART:WIDTh

(see page 828)

Command Syntax

```
:SBUS<n>:UART:WIDTh <width>

<width> ::= {5 | 6 | 7 | 8 | 9}
```

The :SBUS<n>:UART:WIDTh command determines the number of bits (5-9) for each message "byte" for the serial decoder and/or trigger when in UART mode.

Query Syntax

```
:SBUS<n>:UART:WIDTh?
```

The :SBUS<n>:UART:WIDTh? query returns the current UART width setting.

Return Format

```
<width><NL>

<width> ::= {5 | 6 | 7 | 8 | 9}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":SBUS<n>:UART:TRIGger:TYPE" on page 572

26 :SYSTem Commands

Control basic system functions of the oscilloscope. See "Introduction to :SYSTem Commands" on page 577.

Table 77 :SYSTem Commands Summary

Command	Query	Options and Query Returns
:SYSTem:DATE <date> (see page 578)	:SYSTem:DATE? (see page 578)	<date> ::= <year>,<month>,<day> <year> ::= 4-digit year in NR1 format <month> ::= {1,..,12 | JANuary | FEBruary | MARch | APRil | MAY | JUNe | JULy | AUGust | SEPtember | OCTober | NOVember | DECember} <day> ::= {1,..31}
n/a	:SYSTem:DIDentifier? (see page 579)	n/a
:SYSTem:DSP <string> (see page 580)	n/a	<string> ::= up to 75 characters as a quoted ASCII string
n/a	:SYSTem:ERRor? (see page 581)	<error> ::= an integer error code <error string> ::= quoted ASCII string. See Error Messages (see page 787).
:SYSTem:LOCK <value> (see page 582)	:SYSTem:LOCK? (see page 582)	<value> ::= {{1 | ON} | {0 | OFF}}
:SYSTem:MENU <menu> (see page 583)	n/a	<menu> ::= {MASK | MEASure | SEGMented}
:SYSTem:PERSona[:MANufacturer] <manufacturer_string> (see page 584)	:SYSTem:PERSona[:MANufacturer]? (see page 584)	<manufacturer_string> ::= quoted ASCII string, up to 63 characters
:SYSTem:PERSona[:MANufacturer]:DEFault (see page 585)	n/a	Sets manufacturer string to "KEYSIGHT TECHNOLOGIES"

Table 77 :SYSTem Commands Summary (continued)

Command	Query	Options and Query Returns
:SYSTem:PRESet (see page 586)	n/a	See :SYSTem:PRESet (see page 586)
:SYSTem:PROTection:LOCK <value> (see page 589)	:SYSTem:PROTection:LOCK? (see page 589)	<value> ::= {{1 | ON} | {0 | OFF}}
:SYSTem:RLOGger <setting>[,<file_name>[,<write_mode>]] (see page 590)	n/a	<setting> ::= {{0 | OFF} | {1 | ON}} <file_name> ::= quoted ASCII string <write_mode> ::= {CREate | APPend}
:SYSTem:RLOGger:DESTination <dest> (see page 591)	:SYSTem:RLOGger:DESTination? (see page 591)	<dest> ::= {FILE | SCReen | BOTH}
:SYSTem:RLOGger:DISPlay {{0 | OFF} | {1 | ON}} (see page 592)	:SYSTem:RLOGger:DISPlay? (see page 592)	<setting> ::= {0 | 1}
:SYSTem:RLOGger:FNAMe <file_name> (see page 593)	:SYSTem:RLOGger:FNAMe? (see page 593)	<file_name> ::= quoted ASCII string
:SYSTem:RLOGger:STATe {{0 | OFF} | {1 | ON}} (see page 594)	:SYSTem:RLOGger:STATe? (see page 594)	<setting> ::= {0 | 1}
:SYSTem:RLOGger:TRANsparent {{0 | OFF} | {1 | ON}} (see page 595)	:SYSTem:RLOGger:TRANsparent? (see page 595)	<setting> ::= {0 | 1}
:SYSTem:RLOGger:WMODe <write_mode> (see page 596)	:SYSTem:RLOGger:WMODe? (see page 596)	<write_mode> ::= {CREate | APPend}
:SYSTem:SETup <setup_data> (see page 597)	:SYSTem:SETup? (see page 597)	<setup_data> ::= data in IEEE 488.2 # format.
:SYSTem:TIME <time> (see page 599)	:SYSTem:TIME? (see page 599)	<time> ::= hours,minutes,seconds in NR1 format
:SYSTem:TZONe <UTC_offset> (see page 600)	:SYSTem:TZONe? (see page 600)	<UTC_offset> ::= integer offset from UTC in the form HHMM, for example, 1000 for UTC+1000 or -230 for UTC-0230

Table 77 :SYSTem Commands Summary (continued)

Command	Query	Options and Query Returns
:SYSTem:USB:EJECt [<usb_path>] (see page 601)	n/a	<usb_path> ::= path of USB storage device
n/a	:SYSTem:USB:PLISt? (see page 602)	n/a

Introduction to :SYSTem Commands

SYSTem subsystem commands enable writing messages to the display, setting and reading both the time and the date, querying for errors, and saving and recalling setups.

:SYSTem:DATE

(see page 828)

Command Syntax

```
:SYSTem:DATE <date>

<date> ::= <year>,<month>,<day>

<year> ::= 4-digit year in NR1 format

<month> ::= {1,..,12 | JANuary | FEBruary | MARch | APRil | MAY | JUNe
             | JULy | AUGust | SEPtember | OCTober | NOVember | DECember}

<day> ::= {1,..,31}
```

The :SYSTem:DATE command sets the date. Validity checking is performed to ensure that the date is valid.

Query Syntax

```
:SYSTem:DATE?
```

The SYSTem:DATE? query returns the date.

Return Format

```
<year>,<month>,<day><NL>
```

See Also

- "Introduction to :SYSTem Commands" on page 577
- ":SYSTem:TIME" on page 599

:SYSTem:DIDentifier

(see page 828)

Query Syntax `:SYSTem:DIDentifier?`

The :SYSTem:DIDentifier? query returns the oscilloscope's Host ID as (part of) a quoted string.

The oscilloscope's Host ID is needed when redeeming licenses for oscilloscope upgrades or other licensed features.

The exact format of returned string are product-specific. This example returns the model number, serial number, and host ID in a comma-separated format:

```
"X12345A,US12345678,G1EFDNLPAF2YPLRN"
```

Portable programs should not attempt to parse the contents of the returned string. Use the *IDN? query instead to get the model number and/or serial number in a defined portable format.

Return Format `<host_id><NL>`

`<host_id> ::= quoted ASCII string`

See Also

- "*IDN (Identification Number)" on page 126

:SYSTem:DSP

(see page 828)

Command Syntax

```
:SYSTem:DSP <string>

<string> ::= quoted ASCII string (up to 75 characters)
```

The :SYSTem:DSP command writes the quoted string (excluding quotation marks) to a text box in the center of the display. Use :SYStem:DSP "" to remotely remove the message from the display. (Two sets of quote marks without a space between them creates a NULL string.) Press any menu key to manually remove the message from the display.

See Also

- "Introduction to :SYSTem Commands" on page 577

:SYSTem:ERRor

(see page 828)

Query Syntax

```
:SYSTem:ERRor?
```

The :SYSTem:ERRor? query outputs the next error number and text from the error queue. The instrument has an error queue that is 30 errors deep and operates on a first-in, first-out basis. Repeatedly sending the :SYSTem:ERRor? query returns the errors in the order that they occurred until the queue is empty. Any further queries then return zero until another error occurs.

Return Format

```
<error number>,<error string><NL>

<error number> ::= an integer error code in NR1 format

<error string> ::= quoted ASCII string containing the error message
```

Error messages are listed in Chapter 33, “Error Messages,” starting on page 787.

See Also

- "Introduction to :SYSTem Commands" on page 577
- "*ESR (Standard Event Status Register)" on page 124
- "*CLS (Clear Status)" on page 121

:SYSTem:LOCK

(see page 828)

Command Syntax

```
:SYSTem:LOCK <value>

<value> ::= {{1 | ON} | {0 | OFF}}
```

The :SYSTem:LOCK command disables the front panel. LOCK ON is the equivalent of sending a local lockout message over the programming interface.

Query Syntax

```
:SYSTem:LOCK?
```

The :SYSTem:LOCK? query returns the lock status of the front panel.

Return Format

```
<value><NL>

<value> ::= {1 | 0}
```

See Also

- "Introduction to :SYSTem Commands" on page 577

:SYSTem:MENU

(see page 828)

Command Syntax `:SYSTem:MENU <menu>`

`<menu> ::= {MASK | MEASure | SEGMented | LISTer}`

The :SYSTem:MENU command changes the front panel softkey menu.

:SYSTem:PERSona[:MANufacturer]

(see page 828)

Command Syntax

```
:SYSTem:PERSona[:MANufacturer] <manufacturer_string>

<manufacturer_string> ::= ::= quoted ASCII string, up to 63 characters
```

The :SYSTem:PERSona[:MANufacturer] command lets you change the manufacturer string portion of the identification string returned by the *IDN? query.

The default manufacturer string is "KEYSIGHT TECHNOLOGIES".

If your remote programs depend on a legacy manufacturer string, for example, you could use this command to set the manufacturer string to "AGILENT TECHNOLOGIES".

Query Syntax

```
:SYSTem:PERSona[:MANufacturer]?
```

The :SYSTem:PERSona[:MANufacturer]? query returns the currently set manufacturer string.

Return Format

```
<manufacturer_string><NL>
```

See Also

- "*IDN (Identification Number)" on page 126
- ":SYSTem:PERSona[:MANufacturer]:DEFault" on page 585
- "Introduction to :SYSTem Commands" on page 577

:SYSTem:PERSona[:MANufacturer]:DEFault

(see page 828)

Command Syntax `:SYSTem:PERSona[:MANufacturer]:DEFault`

The :SYSTem:PERSona[:MANufacturer]:DEFault command sets the manufacturer string to "KEYSIGHT TECHNOLOGIES".

See Also

- "*IDN (Identification Number)" on page 126
- ":SYSTem:PERSona[:MANufacturer]" on page 584
- "Introduction to :SYSTem Commands" on page 577

:SYSTem:PRESet

C (see page 828)

Command Syntax `:SYSTem:PRESet`

The :SYSTem:PRESet command places the instrument in a known state. This is the same as pressing the **[Default Setup]** key or **[Save/Recall] > Default/Erase > Default Setup** on the front panel.

When you perform a default setup, some user settings (like preferences) remain unchanged. To reset all user settings to their factory defaults, use the *RST command.

Reset conditions are:

Acquire Menu	
Mode	Normal
Averaging	Off
# Averages	8

Analog Channel Menu	
Channel 1	On
Channel 2	Off
Volts/division	5.00 V
Offset	0.00
Coupling	DC
Probe attenuation	10:1
Vernier	Off
Invert	Off
BW limit	Off
Impedance	1 M Ohm (cannot be changed)
Units	Volts
Skew	0

Cursor Menu	
Source	Channel 1

Display Menu	
Persistence	Off
Grid	20%

Quick Meas Menu	
Source	Channel 1

Run Control	
	Scope is running

Time Base Menu	
Main time/division	100 us
Main time base delay	0.00 s
Delay time/division	500 ns
Delay time base delay	0.00 s
Reference	center
Mode	main
Vernier	Off

Trigger Menu	
Type	Edge
Mode	Auto
Coupling	dc
Source	Channel 1
Level	0.0 V
Slope	Positive
HF Reject and noise reject	Off
Holdoff	60 ns
External probe attenuation	10:1
External Units	Volts
External Impedance	1 M Ohm (cannot be changed)

See Also

- "Introduction to Common (*) Commands" on page 119
- "*RST (Reset)" on page 131

:SYSTem:PROTection:LOCK

(see page 828)

Command Syntax

```
:SYSTem:PROTection:LOCK <value>

<value> ::= {{1 | ON} | {0 | OFF}}
```

The :SYSTem:PROTection:LOCK command disables the fifty ohm impedance setting for all analog channels.

Query Syntax

```
:SYSTem:PROTection:LOCK?
```

The :SYSTem:PROTection:LOCK? query returns the analog channel protection lock status.

Return Format

```
<value><NL>

<value> ::= {1 | 0}
```

See Also

- "Introduction to :SYSTem Commands" on page 577

:SYSTem:RLOGger

(see page 828)

Command Syntax

```
:SYSTem:RLOGger <setting>[,<file_name>[,<write_mode>]]

<setting> ::= {{0 | OFF} | {1 | ON}}

<file_name> ::= quoted ASCII string

<write_mode> ::= {CREate | APPend}
```

The :SYSTem:RLOGger command enables or disables remote command logging, optionally specifying the log file name and write mode.

See Also

- ":SYSTem:RLOGger:DESTination" on page 591
- ":SYSTem:RLOGger:DISPlay" on page 592
- ":SYSTem:RLOGger:FNAMe" on page 593
- ":SYSTem:RLOGger:STATe" on page 594
- ":SYSTem:RLOGger:TRANsparent" on page 595
- ":SYSTem:RLOGger:WMODe" on page 596

:SYSTem:RLOGger:DESTination

(see page 828)

Command Syntax

```
:SYSTem:RLOGger:DESTination <dest>

<dest> ::= {FILE | SCReen | BOTH}
```

The :SYSTem:RLOGger:DESTination command specifies whether remote commands are logged to a text file (on a connected USB storage device), logged to the screen, or both.

NOTE **If the destination is changed while remote command logging is running, remote command logging is turned off.**

Query Syntax

```
:SYSTem:RLOGger:DESTination?
```

The :SYSTem:RLOGger:DESTination? query returns the remote command logging destination.

Return Format

```
<dest><NL>

<dest> ::= {FILE | SCR | BOTH}
```

See Also

- ":SYSTem:RLOGger" on page 590
- ":SYSTem:RLOGger:DISPlay" on page 592
- ":SYSTem:RLOGger:FNAMe" on page 593
- ":SYSTem:RLOGger:STATe" on page 594
- ":SYSTem:RLOGger:TRANsparent" on page 595
- ":SYSTem:RLOGger:WMODe" on page 596

:SYSTem:RLOGger:DISPlay

(see page 828)

Command Syntax

```
:SYSTem:RLOGger:DISPlay {{0 | OFF} | {1 | ON}}
```

The :SYSTem:RLOGger:DISPlay command enables or disables the screen display of logged remote commands and their return values (if applicable).

Query Syntax

```
:SYSTem:RLOGger:DISPlay?
```

The :SYSTem:RLOGger:DISPlay? query returns whether the screen display for remote command logging is enabled or disabled.

Return Format

```
<setting><NL>

<setting> ::= {0 | 1}
```

See Also

- ":SYSTem:RLOGger" on page 590
- ":SYSTem:RLOGger:DESTination" on page 591
- ":SYSTem:RLOGger:FNAMe" on page 593
- ":SYSTem:RLOGger:STATe" on page 594
- ":SYSTem:RLOGger:TRANsparent" on page 595
- ":SYSTem:RLOGger:WMODe" on page 596

:SYSTem:RLOGger:FNAMe

(see page 828)

Command Syntax

```
:SYSTem:RLOGger:FNAMe <file_name>

<file_name> ::= quoted ASCII string
```

The :SYSTem:RLOGger:FNAMe command specifies the remote command log file name.

Because log files are ASCII text files, the ".txt" extension is automatically added to the name specified.

Query Syntax

```
:SYSTem:RLOGger:FNAMe?
```

The :SYSTem:RLOGger:FNAMe? query returns the remote command log file name.

Return Format

```
<file_name><NL>
```

See Also

- ":SYSTem:RLOGger" on page 590
- ":SYSTem:RLOGger:DESTination" on page 591
- ":SYSTem:RLOGger:DISPlay" on page 592
- ":SYSTem:RLOGger:STATe" on page 594
- ":SYSTem:RLOGger:TRANsparent" on page 595
- ":SYSTem:RLOGger:WMODe" on page 596

:SYSTem:RLOGger:STATe

(see page 828)

Command Syntax `:SYSTem:RLOGger:STATe {{0 | OFF} | {1 | ON}}`

The :SYSTem:RLOGger:STATe command enables or disables remote command logging.

Query Syntax `:SYSTem:RLOGger:STATe?`

The :SYSTem:RLOGger:STATe? query returns the remote command logging state.

Return Format `<setting><NL>`

`<setting> ::= {0 | 1}`

See Also

- ":SYSTem:RLOGger" on page 590
- ":SYSTem:RLOGger:DESTination" on page 591
- ":SYSTem:RLOGger:DISPlay" on page 592
- ":SYSTem:RLOGger:FNAMe" on page 593
- ":SYSTem:RLOGger:TRANsparent" on page 595
- ":SYSTem:RLOGger:WMODe" on page 596

:SYSTem:RLOGger:TRANsparent

N (see page 828)

Command Syntax `:SYSTem:RLOGger:TRANsparent {{0 | OFF} | {1 | ON}}`

The :SYSTem:RLOGger:TRANsparent command specifies whether the screen display background for remote command logging is transparent or solid.

Query Syntax `:SYSTem:RLOGger:TRANsparent?`

The :SYSTem:RLOGger:TRANsparent? query returns the setting for transparent screen display background.

Return Format `<setting><NL>`

`<setting> ::= {0 | 1}`

See Also

- ":SYSTem:RLOGger" on page 590
- ":SYSTem:RLOGger:DESTination" on page 591
- ":SYSTem:RLOGger:DISPlay" on page 592
- ":SYSTem:RLOGger:FNAMe" on page 593
- ":SYSTem:RLOGger:STATe" on page 594
- ":SYSTem:RLOGger:WMODe" on page 596

:SYSTem:RLOGger:WMODe

(see page 828)

Command Syntax

```
:SYSTem:RLOGger:WMODe <write_mode>

<write_mode> ::= {CREate | APPend}
```

The :SYSTem:RLOGger:WMODe command specifies the remote command logging write mode.

Query Syntax

```
:SYSTem:RLOGger:WMODe?
```

The :SYSTem:RLOGger:WMODe? query returns the remote command logging write mode.

Return Format

```
<write_mode><NL>

<write_mode> ::= {CRE | APP}
```

See Also

- ":SYSTem:RLOGger" on page 590
- ":SYSTem:RLOGger:DESTination" on page 591
- ":SYSTem:RLOGger:DISPlay" on page 592
- ":SYSTem:RLOGger:FNAMe" on page 593
- ":SYSTem:RLOGger:STATe" on page 594
- ":SYSTem:RLOGger:TRANsparent" on page 595

:SYSTem:SETup

(see page 828)

Command Syntax

```
:SYSTem:SETup <setup_data>

<setup_data> ::= binary block data in IEEE 488.2 # format.
```

The :SYSTem:SETup command sets the oscilloscope as defined by the data in the setup (learn) string sent from the controller. The setup string does not change the interface mode or interface address.

Query Syntax

```
:SYSTem:SETup?
```

The :SYSTem:SETup? query operates the same as the *LRN? query. It outputs the current oscilloscope setup in the form of a learn string to the controller. The setup (learn) string is sent and received as a binary block of data. The format for the data transmission is the # format defined in the IEEE 488.2 specification.

Return Format

```
<setup_data><NL>

<setup_data> ::= binary block data in IEEE 488.2 # format
```

See Also

- "Introduction to :SYSTem Commands" on page 577
- "*LRN (Learn Device Setup)" on page 127

Example Code

```
' SAVE_SYSTEM_SETUP - The :SYSTEM:SETUP? query returns a program
' message that contains the current state of the instrument.  Its
' format is a definite-length binary block, for example,
' #800075595<setup string><NL>
' where the setup string is 75595 bytes in length.
myScope.WriteString ":SYSTEM:SETUP?"
varQueryResult = myScope.ReadIEEEBlock(BinaryType_UI1)
CheckForInstrumentErrors   ' After reading query results.

' Output setup string to a file:
Dim strPath As String
strPath = "c:\scope\config\setup.dat"

' Open file for output.
Close #1   ' If #1 is open, close it.
Open strPath For Binary Access Write Lock Write As #1
Put #1, , varQueryResult   ' Write data.
Close #1   ' Close file.

' RESTORE_SYSTEM_SETUP - Read the setup string from a file and
' write it back to the oscilloscope.
Dim varSetupString As Variant
strPath = "c:\scope\config\setup.dat"

' Open file for input.
Open strPath For Binary Access Read As #1
Get #1, , varSetupString   ' Read data.
Close #1   ' Close file.
```

```
' Write setup string back to oscilloscope using ":SYSTEM:SETUP"
' command:
myScope.WriteIEEEBlock ":SYSTEM:SETUP ", varSetupString
CheckForInstrumentErrors
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:SYSTem:TIME

(see page 828)

Command Syntax

```
:SYSTem:TIME <time>

<time> ::= hours,minutes,seconds in NR1 format
```

The :SYSTem:TIME command sets the system time, using a 24-hour format. Commas are used as separators. Validity checking is performed to ensure that the time is valid.

Query Syntax

```
:SYSTem:TIME? <time>
```

The :SYSTem:TIME? query returns the current system time.

Return Format

```
<time><NL>

<time> ::= hours,minutes,seconds in NR1 format
```

See Also

- "Introduction to :SYSTem Commands" on page 577
- ":SYSTem:TZONe" on page 600
- ":SYSTem:DATE" on page 578

:SYSTem:TZONe

(see page 828)

Command Syntax

```
:SYSTem:TZONe <UTC_offset>

<UTC_offset> ::=  integer offset from UTC in the form HHMM,
   for example, 1000 for UTC+1000 or -230 for UTC-0230
```

The :SYSTem:TZONe command sets the system time zone based on the specified offset from UTC. This keeps local time constant and moves the UTC by setting the system clock to match the displayed oscilloscope clock.

Supported time zone offsets are: -1200, -1100, -1000, -900, -800, -700, -600, -500, -400, -330, -300, -230, -200, -100, 0, 100, 200, 300, 330, 400, 430, 500, 530, 600, 700, 800, 845, 900, 930, 1000, 1030, 1100, 1200

Because licenses are based on Coordinated Universal Time (UTC), the proper time zone setting allows licenses to work immediately after they are generated.

Query Syntax

```
:SYSTem:TZONe?
```

The :SYSTem:TZONe? query returns the time zone offset setting.

Return Format

```
<UTC_offset><NL>

<UTC_offset> ::=  integer offset from UTC in the form HHMM
```

See Also

- ":SYSTem:TIME" on page 599

:SYSTem:USB:EJECt

(see page 828)

Command Syntax

```
:SYSTem:USB:EJECt {ALL | <usb_path>}

<usb_path> ::= path of USB storage device
```

The :SYSTem:USB:EJECt command ejects connected USB storage devices.

NOTE **You must "eject" a USB mass storage device before unplugging it; otherwise, the device will be marked as needing repair when connecting to a computer with the Windows operating system (even though there are no harmful effects to the device).**

When the ALL parameter is given, the command will dismount/eject all connected USB storage devices.

The paths of connected USB storage devices are returned by the :SYSTem:USB:PLISt? query.

See Also

- ":SYSTem:USB:PLISt" on page 602

:SYSTem:USB:PLISt

(see page 828)

Query Syntax `:SYSTem:USB:PLISt?`

The :SYSTem:USB:PLISt? query returns the root path for all connected USB storage devices, delimited by a newline character ("\n").

Return Format `<string><NL>`

`<string> ::= a string of up to 256 ASCII characters.`

See Also

- ":SYSTem:USB:EJECt" on page 601

27 :TIMebase Commands

Control all horizontal sweep functions. See "Introduction to :TIMebase Commands" on page 604.

Table 78 :TIMebase Commands Summary

Command	Query	Options and Query Returns
:TIMebase:MODE <value> (see page 605)	:TIMebase:MODE? (see page 605)	<value> ::= {MAIN | WINDow | XY | ROLL}
:TIMebase:POSition <pos> (see page 606)	:TIMebase:POSition? (see page 606)	<pos> ::= time from the trigger event to the display reference point in NR3 format
:TIMebase:RANGe <range_value> (see page 607)	:TIMebase:RANGe? (see page 607)	<range_value> ::= time for 10 div in seconds in NR3 format
:TIMebase:REFerence {LEFT | CENTer | RIGHt} (see page 608)	:TIMebase:REFerence? (see page 608)	<return_value> ::= {LEFT | CENTer | RIGHt}
:TIMebase:SCALe <scale_value> (see page 609)	:TIMebase:SCALe? (see page 609)	<scale_value> ::= time/div in seconds in NR3 format
:TIMebase:VERNier {{0 | OFF} | {1 | ON}} (see page 610)	:TIMebase:VERNier? (see page 610)	{0 | 1}
:TIMebase:WINDow:POSition <pos> (see page 611)	:TIMebase:WINDow:POSition? (see page 611)	<pos> ::= time from the trigger event to the zoomed view reference point in NR3 format
:TIMebase:WINDow:RANGe <range_value> (see page 612)	:TIMebase:WINDow:RANGe? (see page 612)	<range value> ::= range value in seconds in NR3 format for the zoomed window
:TIMebase:WINDow:SCALe <scale_value> (see page 613)	:TIMebase:WINDow:SCALe? (see page 613)	<scale_value> ::= scale value in seconds in NR3 format for the zoomed window

Introduction to :TIMebase Commands

The TIMebase subsystem commands control the horizontal (X-axis) functions and set the oscilloscope to X-Y mode (where channel 1 becomes the X input and channel 2 becomes the Y input). The time per division, delay, vernier control, and reference can be controlled for the main and window (zoomed) time bases.

Reporting the Setup

Use :TIMebase? to query setup information for the TIMebase subsystem.

Return Format

The following is a sample response from the :TIMebase? query. In this case, the query was issued following a *RST command.

```
:TIM:MODE MAIN;REF CENT;MAIN:RANG +1.00E-03;POS +0.0E+00
```

:TIMebase:MODE

(see page 828)

Command Syntax

```
:TIMebase:MODE <value>

<value> ::= {MAIN | WINDow | XY | ROLL}
```

The :TIMebase:MODE command sets the current time base. There are four time base modes:

- MAIN — The normal time base mode is the main time base. It is the default time base mode after the *RST (Reset) command.
- WINDow — In the WINDow (zoomed or delayed) time base mode, measurements are made in the zoomed time base if possible; otherwise, the measurements are made in the main time base.
- XY — In the XY mode, the :TIMebase:RANGe, :TIMebase:POSition, and :TIMebase:REFerence commands are not available. No measurements are available in this mode.
- ROLL — In the ROLL mode, data moves continuously across the display from left to right. The oscilloscope runs continuously and is untriggered. The :TIMebase:REFerence selection changes to RIGHt.

Query Syntax

```
:TIMebase:MODE?
```

The :TIMebase:MODE query returns the current time base mode.

Return Format

```
<value><NL>

<value> ::= {MAIN | WIND | XY | ROLL}
```

See Also

- "Introduction to :TIMebase Commands" on page 604
- "*RST (Reset)" on page 131
- ":TIMebase:RANGe" on page 607
- ":TIMebase:POSition" on page 606
- ":TIMebase:REFerence" on page 608

Example Code

```
' TIMEBASE_MODE - (not executed in this example)
' Set the time base mode to MAIN, DELAYED, XY, or ROLL.

' Set time base mode to main.
myScope.WriteString ":TIMEBASE:MODE MAIN"
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:TIMebase:POSition

(see page 828)

Command Syntax

```
:TIMebase:POSition <pos>

<pos> ::= time in seconds from the trigger to the display reference
          in NR3 format
```

The :TIMebase:POSition command sets the time interval between the trigger event and the display reference point on the screen. The display reference point is either left, right, or center and is set with the :TIMebase:REFerence command. The maximum position value depends on the time/division settings.

NOTE This command is an alias for the :TIMebase:DELay command.

Query Syntax

```
:TIMebase:POSition?
```

The :TIMebase:POSition? query returns the current time from the trigger to the display reference in seconds.

Return Format

```
<pos><NL>

<pos> ::= time in seconds from the trigger to the display reference
          in NR3 format
```

See Also

- "Introduction to :TIMebase Commands" on page 604
- ":TIMebase:REFerence" on page 608
- ":TIMebase:RANGe" on page 607
- ":TIMebase:SCALe" on page 609
- ":TIMebase:WINDow:POSition" on page 611
- ":TIMebase:DELay" on page 785

:TIMebase:RANGe

(see page 828)

Command Syntax

```
:TIMebase:RANGe <range_value>

<range_value> ::= time for 10 div in seconds in NR3 format
```

The :TIMebase:RANGe command sets the full-scale horizontal time in seconds for the main window. The range is 10 times the current time-per-division setting.

Query Syntax

```
:TIMebase:RANGe?
```

The :TIMebase:RANGe query returns the current full-scale range value for the main window.

Return Format

```
<range_value><NL>

<range_value> ::= time for 10 div in seconds in NR3 format
```

See Also

- "Introduction to :TIMebase Commands" on page 604
- ":TIMebase:MODE" on page 605
- ":TIMebase:SCALe" on page 609
- ":TIMebase:WINDow:RANGe" on page 612

Example Code

```
   ' TIME_RANGE - Sets the full scale horizontal time in seconds.  The
   ' range value is 10 times the time per division.
   myScope.WriteString ":TIM:RANG 2e-3"   ' Set the time range to 0.002
seconds.
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:TIMebase:REFerence

(see page 828)

Command Syntax

```
:TIMebase:REFerence <reference>

<reference> ::= {LEFT | CENTer | RIGHt}
```

The :TIMebase:REFerence command sets the time reference to one division from the left side of the screen, to the center of the screen, or to one division from the right side of the screen. Time reference is the point on the display where the trigger point is referenced.

Query Syntax

```
:TIMebase:REFerence?
```

The :TIMebase:REFerence? query returns the current display reference for the main window.

Return Format

```
<reference><NL>

<reference> ::= {LEFT | CENT | RIGH}
```

See Also

- "Introduction to :TIMebase Commands" on page 604
- ":TIMebase:MODE" on page 605

Example Code

```
   ' TIME_REFERENCE - Possible values are LEFT, CENTer, or RIGHt.
   '  - LEFT sets the display reference one time division from the left.
   '  - CENTer sets the display reference to the center of the screen.
   '  - RIGHt sets the display reference one time division from the righ
t.
   myScope.WriteString ":TIMebase:REFerence CENTer"   ' Set reference to
 center.
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:TIMebase:SCALe

N (see page 828)

Command Syntax

```
:TIMebase:SCALe <scale_value>

<scale_value> ::= time/div in seconds in NR3 format
```

The :TIMebase:SCALe command sets the horizontal scale or units per division for the main window.

Query Syntax

```
:TIMebase:SCALe?
```

The :TIMebase:SCALe? query returns the current horizontal scale setting in seconds per division for the main window.

Return Format

```
<scale_value><NL>

<scale_value> ::= time/div in seconds in NR3 format
```

See Also

- "Introduction to :TIMebase Commands" on page 604
- ":TIMebase:RANGe" on page 607
- ":TIMebase:WINDow:SCALe" on page 613
- ":TIMebase:WINDow:RANGe" on page 612

:TIMebase:VERNier

(see page 828)

Command Syntax

```
:TIMebase:VERNier <vernier value>

<vernier value> ::= {{1 | ON} | {0 | OFF}
```

The :TIMebase:VERNier command specifies whether the time base control's vernier (fine horizontal adjustment) setting is ON (1) or OFF (0).

Query Syntax

```
:TIMebase:VERNier?
```

The :TIMebase:VERNier? query returns the current state of the time base control's vernier setting.

Return Format

```
<vernier value><NL>

<vernier value> ::= {0 | 1}
```

See Also

- "Introduction to :TIMebase Commands" on page 604

:TIMebase:WINDow:POSition

(see page 828)

Command Syntax

```
:TIMebase:WINDow:POSition <pos value>

<pos value> ::= time from the trigger event to the zoomed (delayed)
                view reference point in NR3 format
```

The :TIMebase:WINDow:POSition command sets the horizontal position in the zoomed (delayed) view of the main sweep. The main sweep range and the main sweep horizontal position determine the range for this command. The value for this command must keep the zoomed view window within the main sweep range.

Query Syntax

```
:TIMebase:WINDow:POSition?
```

The :TIMebase:WINDow:POSition? query returns the current horizontal window position setting in the zoomed view.

Return Format

```
<value><NL>

<value> ::= position value in seconds
```

See Also

- "Introduction to :TIMebase Commands" on page 604
- ":TIMebase:MODE" on page 605
- ":TIMebase:POSition" on page 606
- ":TIMebase:RANGe" on page 607
- ":TIMebase:SCALe" on page 609
- ":TIMebase:WINDow:RANGe" on page 612
- ":TIMebase:WINDow:SCALe" on page 613

:TIMebase:WINDow:RANGe

(see page 828)

Command Syntax

```
:TIMebase:WINDow:RANGe <range value>

<range value> ::= range value in seconds in NR3 format
```

The :TIMebase:WINDow:RANGe command sets the full-scale horizontal time in seconds for the zoomed (delayed) window. The range is 10 times the current zoomed view window seconds per division setting. The main sweep range determines the range for this command. The maximum value is one half of the :TIMebase:RANGe value.

Query Syntax

```
:TIMebase:WINDow:RANGe?
```

The :TIMebase:WINDow:RANGe? query returns the current window timebase range setting.

Return Format

```
<value><NL>

<value> ::= range value in seconds
```

See Also

- "Introduction to :TIMebase Commands" on page 604
- ":TIMebase:RANGe" on page 607
- ":TIMebase:POSition" on page 606
- ":TIMebase:SCALe" on page 609

:TIMebase:WINDow:SCALe

(see page 828)

Command Syntax

```
:TIMebase:WINDow:SCALe <scale_value>

<scale_value> ::= scale value in seconds in NR3 format
```

The :TIMebase:WINDow:SCALe command sets the zoomed (delayed) window horizontal scale (seconds/division). The main sweep scale determines the range for this command. The maximum value is one half of the :TIMebase:SCALe value.

Query Syntax

```
:TIMebase:WINDow:SCALe?
```

The :TIMebase:WINDow:SCALe? query returns the current zoomed window scale setting.

Return Format

```
<scale_value><NL>

<scale_value> ::= current seconds per division for the zoomed window
```

See Also

- "Introduction to :TIMebase Commands" on page 604
- ":TIMebase:RANGe" on page 607
- ":TIMebase:POSition" on page 606
- ":TIMebase:SCALe" on page 609
- ":TIMebase:WINDow:RANGe" on page 612

28 :TRIGger Commands

Control the trigger modes and parameters for each trigger type. See:

- "Introduction to :TRIGger Commands" on page 615
- "General :TRIGger Commands" on page 617
- ":TRIGger[:EDGE] Commands" on page 627
- ":TRIGger:GLITch Commands" on page 633 (Pulse Width trigger)
- ":TRIGger:PATTern Commands" on page 641 (DSOX1200-Series oscilloscopes only)
- ":TRIGger:SHOLd Commands" on page 646 (DSOX1200-Series oscilloscopes only)
- ":TRIGger:TRANsition Commands" on page 652 (DSOX1200-Series oscilloscopes only)
- ":TRIGger:TV Commands" on page 657

Introduction to :TRIGger Commands

The commands in the TRIGger subsystem define the conditions for an internal trigger. Many of these commands are valid in multiple trigger modes.

The default trigger mode is :EDGE.

The trigger subsystem controls the trigger sweep mode and the trigger specification. The trigger sweep (see ":TRIGger:SWEep" on page 626) can be AUTO or NORMal.

- **NORMal** mode — displays a waveform only if a trigger signal is present and the trigger conditions are met. Otherwise the oscilloscope does not trigger and the display is not updated. This mode is useful for low-repetitive-rate signals.
- **AUTO** trigger mode — generates an artificial trigger event if the trigger specification is not satisfied within a preset time, acquires unsynchronized data and displays it.

  AUTO mode is useful for signals other than low-repetitive-rate signals. You must use this mode to display a DC signal because there are no edges on which to trigger.

The following trigger types are available (see ":TRIGger:MODE" on page 624).

- **Edge triggering**— identifies a trigger by looking for a specified slope and voltage level on a waveform.

- **Pulse width triggering**— (:TRIGger:GLITch commands) sets the oscilloscope to trigger on a positive pulse or on a negative pulse of a specified width.
- **Pattern triggering**— identifies a trigger condition by looking for a specified pattern. This pattern is a logical AND combination of the channels. You can also trigger on a specified time duration of a pattern.
- **TV triggering**— is used to capture the complicated waveforms of television equipment. The trigger circuitry detects the vertical and horizontal interval of the waveform and produces triggers based on the TV trigger settings you selected. TV triggering requires greater than ¼ division of sync amplitude with any analog channel as the trigger source.

Reporting the Setup

Use :TRIGger? to query setup information for the TRIGger subsystem.

Return Format

The return format for the TRIGger? query varies depending on the current mode. The following is a sample response from the :TRIGger? query. In this case, the query was issued following a *RST command.

```
:TRIG:MODE EDGE;SWE AUTO;NREJ 0;HFR 0;HOLD +60.0000000000000E-09;
:TRIG:EDGE:SOUR CHAN1;LEV +0.00000E+00;SLOP POS;REJ OFF;COUP DC
```

General :TRIGger Commands

Table 79 General :TRIGger Commands Summary

Command	Query	Options and Query Returns
:TRIGger:FORCe (see page 618)	n/a	n/a
:TRIGger:HFReject {{0 | OFF} | {1 | ON}} (see page 619)	:TRIGger:HFReject? (see page 619)	{0 | 1}
:TRIGger:HOLDoff <holdoff_time> (see page 620)	:TRIGger:HOLDoff? (see page 620)	<holdoff_time> ::= 60 ns to 10 s in NR3 format
:TRIGger:LEVel:ASETup (see page 621)	n/a	n/a
:TRIGger:LEVel:HIGH <level>, <source> (see page 622)	:TRIGger:LEVel:HIGH? <source> (see page 622)	<level> ::= .75 x full-scale voltage from center screen in NR3 format. <source> ::= CHANnel<n> <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:LEVel:LOW <level>, <source> (see page 623)	:TRIGger:LEVel:LOW? <source> (see page 623)	<level> ::= .75 x full-scale voltage from center screen in NR3 format. <source> ::= CHANnel<n> <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:MODE <mode> (see page 624)	:TRIGger:MODE? (see page 624)	<mode> ::= {EDGE | GLITch | PATTern | SHOLd | TRANsition | TV | SBUS1} <return_value> ::= {<mode> | <none>} <none> ::= query returns "NONE" if the :TIMebase:MODE is ROLL or XY
:TRIGger:NREJect {{0 | OFF} | {1 | ON}} (see page 625)	:TRIGger:NREJect? (see page 625)	{0 | 1}
:TRIGger:SWEep <sweep> (see page 626)	:TRIGger:SWEep? (see page 626)	<sweep> ::= {AUTO | NORMal}

:TRIGger:FORCe

(see page 828)

Command Syntax `:TRIGger:FORCe`

The :TRIGger:FORCe command causes an acquisition to be captured even though the trigger condition has not been met. This command is equivalent to the front panel **[Force Trigger]** key.

See Also

- "Introduction to :TRIGger Commands" on page 615

:TRIGger:HFReject

(see page 828)

Command Syntax

```
:TRIGger:HFReject <value>

<value> ::= {{0 | OFF} | {1 | ON}}
```

The :TRIGger:HFReject command turns the high frequency reject filter off and on. The high frequency reject filter adds a 50 kHz low-pass filter in the trigger path to remove high frequency components from the trigger waveform. Use this filter to remove high-frequency noise, such as AM or FM broadcast stations, from the trigger path.

Query Syntax

```
:TRIGger:HFReject?
```

The :TRIGger:HFReject? query returns the current high frequency reject filter mode.

Return Format

```
<value><NL>

<value> ::= {0 | 1}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger[:EDGE]:REJect" on page 630

:TRIGger:HOLDoff

(see page 828)

Command Syntax

```
:TRIGger:HOLDoff <holdoff_time>

<holdoff_time> ::= 60 ns to 10 s in NR3 format
```

The :TRIGger:HOLDoff command defines the holdoff time value in seconds. Holdoff keeps a trigger from occurring until after a certain amount of time has passed since the last trigger. This feature is valuable when a waveform crosses the trigger level multiple times during one period of the waveform. Without holdoff, the oscilloscope could trigger on each of the crossings, producing a confusing waveform. With holdoff set correctly, the oscilloscope always triggers on the same crossing. The correct holdoff setting is typically slightly less than one period.

Query Syntax

```
:TRIGger:HOLDoff?
```

The :TRIGger:HOLDoff? query returns the holdoff time value for the current trigger mode.

Return Format

```
<holdoff_time><NL>

<holdoff_time> ::= the holdoff time value in seconds in NR3 format.
```

See Also

- "Introduction to :TRIGger Commands" on page 615

:TRIGger:LEVel:ASETup

(see page 828)

Command Syntax `:TRIGger:LEVel:ASETup`

The :TRIGger:LEVel:ASETup command automatically sets the trigger levels of all displayed analog channels to their waveforms' 50% values.

If AC coupling is used, the trigger levels are set to 0 V.

When High and Low (dual) trigger levels are used (as with Rise/Fall Time and Runt triggers, for example), this command has no effect.

See Also

- ":TRIGger[:EDGE]:LEVel" on page 629

:TRIGger:LEVel:HIGH

(see page 828)

Command Syntax

```
:TRIGger:LEVel:HIGH <level>, <source>

<level> ::= 0.75 x full-scale voltage from center screen in NR3 format
            for internal triggers

<source> ::= {CHANnel<n> | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :TRIGger:LEVel:HIGH command sets the high trigger voltage level voltage for the specified source.

Query Syntax

```
:TRIGger:LEVel:HIGH? <source>
```

The :TRIGger:LEVel:HIGH? query returns the high trigger voltage level for the specified source.

Return Format

```
<level><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:LEVel:LOW" on page 623
- ":TRIGger[:EDGE]:SOURce" on page 632

:TRIGger:LEVel:LOW

(see page 828)

Command Syntax

```
:TRIGger:LEVel:LOW <level>, <source>

<level> ::= 0.75 x full-scale voltage from center screen in NR3 format
            for internal triggers

<source> ::= {CHANnel<n> | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :TRIGger:LEVel:LOW command sets the low trigger voltage level voltage for the specified source.

Query Syntax

```
:TRIGger:LEVel:LOW? <source>
```

The :TRIGger:LEVel:LOW? query returns the low trigger voltage level for the specified source.

Return Format

```
<level><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:LEVel:HIGH" on page 622
- ":TRIGger[:EDGE]:SOURce" on page 632

:TRIGger:MODE

(see page 828)

Command Syntax

```
:TRIGger:MODE <mode>

<mode> ::= {EDGE | GLITch | PATTern | SHOLd | TRANsition | TV | SBUS1}
```

The :TRIGger:MODE command selects the trigger mode (trigger type).

NOTE The PATTern, SHOLd, and TRANsition modes are available on the DSOX1200-Series oscilloscopes only.

Query Syntax

```
:TRIGger:MODE?
```

The :TRIGger:MODE? query returns the current trigger mode. If the :TIMebase:MODE is ROLL or XY, the query returns "NONE".

Return Format

```
<mode><NL>

<mode> ::= {EDGE | GLIT | PATT | SHOL | TRAN | TV | SBUS1}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:SWEep" on page 626
- ":TIMebase:MODE" on page 605

Example Code

```
' TRIGGER_MODE - Set the trigger mode to EDGE.
myScope.WriteString ":TRIGger:MODE EDGE"
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:TRIGger:NREJect

(see page 828)

Command Syntax

```
:TRIGger:NREJect <value>

<value> ::= {{0 | OFF} | {1 | ON}}
```

The :TRIGger:NREJect command turns the noise reject filter off and on. When the noise reject filter is on, the trigger circuitry is less sensitive to noise but may require a greater amplitude waveform to trigger the oscilloscope. This command is not valid in TV trigger mode.

Query Syntax

```
:TRIGger:NREJect?
```

The :TRIGger:NREJect? query returns the current noise reject filter mode.

Return Format

```
<value><NL>

<value> ::= {0 | 1}
```

See Also

- "Introduction to :TRIGger Commands" on page 615

:TRIGger:SWEep

(see page 828)

Command Syntax

```
:TRIGger:SWEep <sweep>

<sweep> ::= {AUTO | NORMal}
```

The :TRIGger:SWEep command selects the trigger sweep mode.

When AUTO sweep mode is selected, a baseline is displayed in the absence of a signal. If a signal is present but the oscilloscope is not triggered, the unsynchronized signal is displayed instead of a baseline.

When NORMal sweep mode is selected and no trigger is present, the instrument does not sweep, and the data acquired on the previous trigger remains on the screen.

NOTE This feature is called "Mode" on the instrument's front panel.

Query Syntax

```
:TRIGger:SWEep?
```

The :TRIGger:SWEep? query returns the current trigger sweep mode.

Return Format

```
<sweep><NL>

<sweep> ::= current trigger sweep mode
```

See Also

- "Introduction to :TRIGger Commands" on page 615

:TRIGger[:EDGE] Commands

Table 80 :TRIGger[:EDGE] Commands Summary

Command	Query	Options and Query Returns
:TRIGger[:EDGE]:COUPling {AC | DC | LFReject} (see page 628)	:TRIGger[:EDGE]:COUPling? (see page 628)	{AC | DC | LFReject}
:TRIGger[:EDGE]:LEVel <level> [,<source>] (see page 629)	:TRIGger[:EDGE]:LEVel? [<source>] (see page 629)	For internal triggers, <level> ::= .75 x full-scale voltage from center screen in NR3 format. For external triggers, <level> ::= ±(external range setting) in NR3 format. <source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger[:EDGE]:REJect {OFF | LFReject | HFReject} (see page 630)	:TRIGger[:EDGE]:REJect? (see page 630)	{OFF | LFReject | HFReject}
:TRIGger[:EDGE]:SLOPe <polarity> (see page 631)	:TRIGger[:EDGE]:SLOPe? (see page 631)	<polarity> ::= {POSitive | NEGative | EITHer | ALTernate}
:TRIGger[:EDGE]:SOURce <source> (see page 632)	:TRIGger[:EDGE]:SOURce? (see page 632)	<source> ::= {CHANnel<n> | EXTernal | LINE | WGEN} <n> ::= 1 to (# analog channels) in NR1 format

:TRIGger[:EDGE]:COUPling

(see page 828)

Command Syntax

```
:TRIGger[:EDGE]:COUPling <coupling>

<coupling> ::= {AC | DC | LFReject}
```

The :TRIGger[:EDGE]:COUPling command sets the input coupling for the selected trigger sources. The coupling can be set to AC, DC, or LFReject.

- AC coupling places a high-pass filter (10 Hz for analog channels, and 3.5 Hz for all External trigger inputs) in the trigger path, removing dc offset voltage from the trigger waveform. Use AC coupling to get a stable edge trigger when your waveform has a large dc offset.
- LFReject coupling places a 50 KHz high-pass filter in the trigger path.
- DC coupling allows dc and ac signals into the trigger path.

NOTE **The :TRIGger[:EDGE]:COUPling and the :TRIGger[:EDGE]:REJect selections are coupled. Changing the setting of the :TRIGger[:EDGE]:REJect can change the COUPling setting.**

Query Syntax

```
:TRIGger[:EDGE]:COUPling?
```

The :TRIGger[:EDGE]:COUPling? query returns the current coupling selection.

Return Format

```
<coupling><NL>

<coupling> ::= {AC | DC | LFR}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":TRIGger[:EDGE]:REJect" on page 630

:TRIGger[:EDGE]:LEVel

(see page 828)

Command Syntax

```
:TRIGger[:EDGE]:LEVel <level>

<level> ::= <level>[,<source>]

<level> ::= 0.75 x full-scale voltage from center screen in NR3 format
            for internal triggers

<level> ::= ±(external range setting) in NR3 format
            for external triggers

<source> ::= {CHANnel<n> | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :TRIGger[:EDGE]:LEVel command sets the trigger level voltage for the active trigger source.

NOTE If the optional source is specified and is not the active source, the level on the active source is not affected and the active source is not changed.

Query Syntax

```
:TRIGger[:EDGE]:LEVel? [<source>]
```

The :TRIGger[:EDGE]:LEVel? query returns the trigger level of the current trigger source.

Return Format

```
<level><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger[:EDGE]:SOURce" on page 632
- ":EXTernal:RANGe" on page 269

:TRIGger[:EDGE]:REJect

(see page 828)

Command Syntax

```
:TRIGger[:EDGE]:REJect <reject>

<reject> ::= {OFF | LFReject | HFReject}
```

The :TRIGger[:EDGE]:REJect command turns the low-frequency or high-frequency reject filter on or off. You can turn on one of these filters at a time.

- The high frequency reject filter adds a 50 kHz low-pass filter in the trigger path to remove high frequency components from the trigger waveform. Use the high frequency reject filter to remove high-frequency noise, such as AM or FM broadcast stations, from the trigger path.
- The low frequency reject filter adds a 50 kHz high-pass filter in series with the trigger waveform to remove any unwanted low frequency components from a trigger waveform, such as power line frequencies, that can interfere with proper triggering.

NOTE **The :TRIGger[:EDGE]:REJect and the :TRIGger[:EDGE]:COUPling selections are coupled. Changing the setting of the :TRIGger[:EDGE]:COUPling can change the COUPling setting.**

Query Syntax

```
:TRIGger[:EDGE]:REJect?
```

The :TRIGger[:EDGE]:REJect? query returns the current status of the reject filter.

Return Format

```
<reject><NL>

<reject> ::= {OFF | LFR | HFR}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:HFReject" on page 619
- ":TRIGger[:EDGE]:COUPling" on page 628

:TRIGger[:EDGE]:SLOPe

(see page 828)

Command Syntax

```
:TRIGger[:EDGE]:SLOPe <slope>

<slope> ::= {NEGative | POSitive | EITHer | ALTernate}
```

The :TRIGger[:EDGE]:SLOPe command specifies the slope of the edge for the trigger. The SLOPe command is not valid in TV trigger mode. Instead, use :TRIGger:TV:POLarity to set the polarity in TV trigger mode.

Query Syntax

```
:TRIGger[:EDGE]:SLOPe?
```

The :TRIGger[:EDGE]:SLOPe? query returns the current trigger slope.

Return Format

```
<slope><NL>

<slope> ::= {NEG | POS | EITH | ALT}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":TRIGger:TV:POLarity" on page 660

Example Code

```
' TRIGGER_EDGE_SLOPE - Sets the slope of the edge for the trigger.

' Set the slope to positive.
myScope.WriteString ":TRIGGER:EDGE:SLOPE POSITIVE"
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:TRIGger[:EDGE]:SOURce

(see page 828)

Command Syntax

```
:TRIGger[:EDGE]:SOURce <source>

<source> ::= {CHANnel<n> | EXTernal | LINE | WGEN}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :TRIGger[:EDGE]:SOURce command selects the input that produces the trigger.

- EXTernal – triggers on the rear panel EXT TRIG IN signal.
- LINE – triggers at the 50% level of the rising or falling edge of the AC power source signal.
- WGEN – triggers at the 50% level of the rising edge of the waveform generator output signal. This option is not available when the DC or NOISe waveforms are selected. This option is also not available when serial decode is on due to hardware limitations.

Query Syntax

```
:TRIGger[:EDGE]:SOURce?
```

The :TRIGger[:EDGE]:SOURce? query returns the current source. If all channels are off, the query returns "NONE."

Return Format

```
<source><NL>

<source> ::= {CHAN<n> | EXT | LINE | WGEN | NONE}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624

Example Code

```
' TRIGGER_EDGE_SOURCE - Selects the channel that actually produces th
e
' edge trigger.  Any channel can be selected.
myScope.WriteString ":TRIGger:EDGE:SOURce CHANnel1"
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:TRIGger:GLITch Commands

Table 81 :TRIGger:GLITch Commands Summary

Command	Query	Options and Query Returns
:TRIGger:GLITch:GREaterthan <greater_than_time>[suffix] (see page 634)	:TRIGger:GLITch:GREaterthan? (see page 634)	<greater_than_time> ::= floating-point number in NR3 format [suffix] ::= {s | ms | us | ns | ps}
:TRIGger:GLITch:LESSthan <less_than_time>[suffix] (see page 635)	:TRIGger:GLITch:LESSthan? (see page 635)	<less_than_time> ::= floating-point number in NR3 format [suffix] ::= {s | ms | us | ns | ps}
:TRIGger:GLITch:LEVel <level> [<source>] (see page 636)	:TRIGger:GLITch:LEVel? (see page 636)	For internal triggers, <level> ::= .75 x full-scale voltage from center screen in NR3 format. For external triggers, <level> ::= ±(external range setting) in NR3 format. <source> ::= {CHANnel<n> | EXTernal} <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:GLITch:POLarity <polarity> (see page 637)	:TRIGger:GLITch:POLarity? (see page 637)	<polarity> ::= {POSitive | NEGative}
:TRIGger:GLITch:QUALifier <qualifier> (see page 638)	:TRIGger:GLITch:QUALifier? (see page 638)	<qualifier> ::= {GREaterthan | LESSthan | RANGe}
:TRIGger:GLITch:RANGe <less_than_time>[suffix], <greater_than_time>[suffix] (see page 639)	:TRIGger:GLITch:RANGe? (see page 639)	<less_than_time> ::= 15 ns to 10 seconds in NR3 format <greater_than_time> ::= 10 ns to 9.99 seconds in NR3 format [suffix] ::= {s | ms | us | ns | ps}
:TRIGger:GLITch:SOURce <source> (see page 640)	:TRIGger:GLITch:SOURce? (see page 640)	<source> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format

:TRIGger:GLITch:GREaterthan

(see page 828)

Command Syntax

```
:TRIGger:GLITch:GREaterthan <greater_than_time>[<suffix>]

<greater_than_time> ::= floating-point number in NR3 format

<suffix> ::= {s | ms | us | ns | ps}
```

The :TRIGger:GLITch:GREaterthan command sets the minimum pulse width duration for the selected :TRIGger:GLITch:SOURce.

Query Syntax

```
:TRIGger:GLITch:GREaterthan?
```

The :TRIGger:GLITch:GREaterthan? query returns the minimum pulse width duration time for :TRIGger:GLITch:SOURce.

Return Format

```
<greater_than_time><NL>

<greater_than_time> ::= floating-point number in NR3 format.
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:GLITch:SOURce" on page 640
- ":TRIGger:GLITch:QUALifier" on page 638
- ":TRIGger:MODE" on page 624

:TRIGger:GLITch:LESSthan

(see page 828)

Command Syntax

```
:TRIGger:GLITch:LESSthan <less_than_time>[<suffix>]

<less_than_time> ::= floating-point number in NR3 format

<suffix> ::= {s | ms | us | ns | ps}
```

The :TRIGger:GLITch:LESSthan command sets the maximum pulse width duration for the selected :TRIGger:GLITch:SOURce.

Query Syntax

```
:TRIGger:GLITch:LESSthan?
```

The :TRIGger:GLITch:LESSthan? query returns the pulse width duration time for :TRIGger:GLITch:SOURce.

Return Format

```
<less_than_time><NL>

<less_than_time> ::= floating-point number in NR3 format.
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:GLITch:SOURce" on page 640
- ":TRIGger:GLITch:QUALifier" on page 638
- ":TRIGger:MODE" on page 624

:TRIGger:GLITch:LEVel

(see page 828)

Command Syntax

```
:TRIGger:GLITch:LEVel <level_argument>

<level_argument> ::= <level>[, <source>]

<level> ::= .75 x full-scale voltage from center screen in NR3 format
            for internal triggers

<level> ::= ±(external range setting) in NR3 format
            for external triggers

<source> ::= {CHANnel<n> | EXTernal}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :TRIGger:GLITch:LEVel command sets the trigger level voltage for the active pulse width trigger.

Query Syntax

```
:TRIGger:GLITch:LEVel?
```

The :TRIGger:GLITch:LEVel? query returns the trigger level of the current pulse width trigger mode. If all channels are off, the query returns "NONE."

Return Format

```
<level_argument><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":TRIGger:GLITch:SOURce" on page 640
- ":EXTernal:RANGe" on page 269

:TRIGger:GLITch:POLarity

(see page 828)

Command Syntax

```
:TRIGger:GLITch:POLarity <polarity>

<polarity> ::= {POSitive | NEGative}
```

The :TRIGger:GLITch:POLarity command sets the polarity for the glitch pulse width trigger.

Query Syntax

```
:TRIGger:GLITch:POLarity?
```

The :TRIGger:GLITch:POLarity? query returns the glitch pulse width trigger polarity.

Return Format

```
<polarity><NL>

<polarity> ::= {POS | NEG}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":TRIGger:GLITch:SOURce" on page 640

:TRIGger:GLITch:QUALifier

N (see page 828)

Command Syntax

```
:TRIGger:GLITch:QUALifier <operator>

<operator> ::= {GREaterthan | LESSthan | RANGe}
```

This command sets the mode of operation of the glitch pulse width trigger. The oscilloscope can trigger on a pulse width that is greater than a time value, less than a time value, or within a range of time values.

Query Syntax

```
:TRIGger:GLITch:QUALifier?
```

The :TRIGger:GLITch:QUALifier? query returns the glitch pulse width qualifier.

Return Format

```
<operator><NL>

<operator> ::= {GRE | LESS | RANG}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:GLITch:SOURce" on page 640
- ":TRIGger:MODE" on page 624

:TRIGger:GLITch:RANGe

(see page 828)

Command Syntax

```
:TRIGger:GLITch:RANGe <less_than_time>[suffix],
                      <greater_than_time>[suffix]

<less_than_time> ::= (15 ns - 10 seconds) in NR3 format

<greater_than_time> ::= (10 ns - 9.99 seconds) in NR3 format

[suffix] ::= {s | ms | us | ns | ps}
```

The :TRIGger:GLITch:RANGe command sets the pulse width duration for the selected :TRIGger:GLITch:SOURce. You can enter the parameters in any order — the smaller value becomes the <greater_than_time> and the larger value becomes the <less_than_time>.

Query Syntax

```
:TRIGger:GLITch:RANGe?
```

The :TRIGger:GLITch:RANGe? query returns the pulse width duration time for :TRIGger:GLITch:SOURce.

Return Format

```
<less_than_time>,<greater_than_time><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:GLITch:SOURce" on page 640
- ":TRIGger:GLITch:QUALifier" on page 638
- ":TRIGger:MODE" on page 624

:TRIGger:GLITch:SOURce

N (see page 828)

Command Syntax

```
:TRIGger:GLITch:SOURce <source>

<source> ::= {DIGital<d> | CHANnel<n>}

<n> ::= 1 to (# analog channels) in NR1 format

<d> ::= 0 to (# digital channels - 1) in NR1 format
```

The :TRIGger:GLITch:SOURce command selects the channel that produces the pulse width trigger.

Query Syntax

```
:TRIGger:GLITch:SOURce?
```

The :TRIGger:GLITch:SOURce? query returns the current pulse width source. If all channels are off, the query returns "NONE".

Return Format

```
<source><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":TRIGger:GLITch:LEVel" on page 636
- ":TRIGger:GLITch:POLarity" on page 637
- ":TRIGger:GLITch:QUALifier" on page 638
- ":TRIGger:GLITch:RANGe" on page 639

Example Code

- "Example Code" on page 632

:TRIGger:PATTern Commands

NOTE The :TRIGger:PATTern commands are available on the DSOX1200-Series oscilloscopes only.

Table 82 :TRIGger:PATTern Commands Summary

Command	Query	Options and Query Returns
:TRIGger:PATTern <string>[,<edge_source>,<edge>] (see page 642)	:TRIGger:PATTern? (see page 643)	<string> ::= "nn...n" where n ::= {0 | 1 | X | R | F} when <base> = ASCii <string> ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $} when <base> = HEX <edge_source> ::= {CHANnel<n> | EXTernal | NONE} <n> ::= 1 to (# analog channels) in NR1 format EXTernal available on 2-channel oscilloscopes only <edge> ::= {POSitive | NEGative}
:TRIGger:PATTern:FORMat <base> (see page 644)	:TRIGger:PATTern:FORMat? (see page 644)	<base> ::= {ASCii | HEX}
:TRIGger:PATTern:QUALifier <qualifier> (see page 645)	:TRIGger:PATTern:QUALifier? (see page 645)	<qualifier> ::= ENTered

:TRIGger:PATTern

(see page 828)

Command Syntax

```
:TRIGger:PATTern <pattern>

<pattern> ::= <string>[,<edge_source>,<edge>]

<string> ::= "nn...n" where n ::= {0 | 1 | X | R | F} when
             <base> = ASCii

<string> ::= "0xnn...n" where n ::= {0,..,9 | A,..,F | X | $} when
             <base> = HEX

<edge_source> ::= {CHANnel<n> | EXTernal | NONE}

<n> ::= 1 to (# of analog channels) in NR1 format

<edge> ::= {POSitive | NEGative}
```

The :TRIGger:PATTern command specifies the channel values to be used in the pattern trigger.

In the <string> parameter, each bit corresponds to a channel as described in the following table:

Oscilloscope Models	Value and Mask Bit Assignments
2 analog + 1 external trigger input	Bit 0 - external trigger input. Bits 1 and 2 - analog channels 2 and 1.
4 analog channels only	Bits 0 through 3 - analog channels 4 through 1.

The format of the <string> parameter depends on the :TRIGger:PATTern:FORMat command setting:

- When the format is ASCii, the string looks just like the string you see on the oscilloscope's front panel, made up of 0, 1, X (don't care), R (rising edge), and F (falling edge) characters.
- When the format is HEX, the string begins with "0x" and contains hex digit characters or X (don't care for all four bits in the nibble).

  With the hex format string, you can use the <edge_source> and <edge> parameters to specify an edge on one of the channels.

NOTE The optional <edge_source> and <edge> parameters should be sent together or not at all. The edge can be specified in the ASCII <string> parameter. If the edge source and edge parameters are used, they take precedence.

NOTE EXTernal can be used as an edge source on 2-channel oscilloscopes only.

You can only specify an edge on one channel. When an edge is specified, the :TRIGger:PATTern:QUALifier does not apply.

Query Syntax

```
:TRIGger:PATTern?
```

The :TRIGger:PATTern? query returns the pattern string, edge source, and edge.

Return Format

```
<string>,<edge_source>,<edge><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:PATTern:FORMat" on page 644
- ":TRIGger:PATTern:QUALifier" on page 645
- ":TRIGger:MODE" on page 624

:TRIGger:PATTern:FORMat

(see page 828)

Command Syntax

```
:TRIGger:PATTern:FORMat <base>

<base> ::= {ASCii | HEX}
```

The :TRIGger:PATTern:FORMat command sets the entry (and query) number base used by the :TRIGger:PATTern command. The default <base> is ASCii.

Query Syntax

```
:TRIGger:PATTern:FORMat?
```

The :TRIGger:PATTern:FORMat? query returns the currently set number base for pattern trigger patterns.

Return Format

```
<base><NL>

<base> ::= {ASC | HEX}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:PATTern" on page 642

:TRIGger:PATTern:QUALifier

(see page 828)

Command Syntax

```
:TRIGger:PATTern:QUALifier <qualifier>

<qualifier> ::= ENTered
```

The :TRIGger:PATTern:QUALifier command qualifies when the trigger occurs.

In the InfiniiVision 1200 X-Series and EDUX11052A/G oscilloscopes, the trigger always occurs when the pattern is entered.

Query Syntax

```
:TRIGger:PATTern:QUALifier?
```

The :TRIGger:PATTern:QUALifier? query returns the trigger duration qualifier.

Return Format

```
<qualifier><NL>
```

See Also

- "Introduction to :TRIGger Commands" on page 615

:TRIGger:SHOLd Commands

NOTE The :TRIGger:SHOLd commands are available on the DSOX1200-Series oscilloscopes only.

Table 83 :TRIGger:SHOLd Commands Summary

Command	Query	Options and Query Returns
:TRIGger:SHOLd:SLOPe <slope> (see page 647)	:TRIGger:SHOLd:SLOPe? (see page 647)	<slope> ::= {NEGative | POSitive}
:TRIGger:SHOLd:SOURce:CLOCk <source> (see page 648)	:TRIGger:SHOLd:SOURce:CLOCk? (see page 648)	<source> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:SHOLd:SOURce:DATA <source> (see page 649)	:TRIGger:SHOLd:SOURce:DATA? (see page 649)	<source> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:SHOLd:TIME:HOLD <time>[suffix] (see page 650)	:TRIGger:SHOLd:TIME:HOLD? (see page 650)	<time> ::= floating-point number in NR3 format [suffix] ::= {s | ms | us | ns | ps}
:TRIGger:SHOLd:TIME:SETup <time>[suffix] (see page 651)	:TRIGger:SHOLd:TIME:SETup? (see page 651)	<time> ::= floating-point number in NR3 format [suffix] ::= {s | ms | us | ns | ps}

:TRIGger:SHOLd:SLOPe

(see page 828)

Command Syntax

```
:TRIGger:SHOLd:SLOPe <slope>

<slope> ::= {NEGative | POSitive}
```

The :TRIGger:SHOLd:SLOPe command specifies whether the rising edge or the falling edge of the clock signal is used.

Query Syntax

```
:TRIGger:SHOLd:SLOPe?
```

The :TRIGger:SHOLd:SLOPe? query returns the current rising or falling edge setting.

Return Format

```
<slope><NL>

<slope> ::= {NEG | POS}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":TRIGger:SHOLd:SOURce:CLOCk" on page 648
- ":TRIGger:SHOLd:SOURce:DATA" on page 649

:TRIGger:SHOLd:SOURce:CLOCk

(see page 828)

Command Syntax

```
:TRIGger:SHOLd:SOURce:CLOCk <source>

<source> ::= {CHANnel<n>}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :TRIGger:SHOLd:SOURce:CLOCk command selects the input channel probing the clock signal.

Query Syntax

```
:TRIGger:SHOLd:SOURce:CLOCk?
```

The :TRIGger:SHOLd:SOURce:CLOCk? query returns the currently set clock signal source.

Return Format

```
<source><NL>

<source> ::= {CHAN<n>}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":TRIGger:SHOLd:SLOPe" on page 647

:TRIGger:SHOLd:SOURce:DATA

(see page 828)

Command Syntax

```
:TRIGger:SHOLd:SOURce:DATA <source>

<source> ::= {CHANnel<n>}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :TRIGger:SHOLd:SOURce:DATA command selects the input channel probing the data signal.

Query Syntax

```
:TRIGger:SHOLd:SOURce:DATA?
```

The :TRIGger:SHOLd:SOURce:DATA? query returns the currently set data signal source.

Return Format

```
<source><NL>

<source> ::= {CHAN<n>}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":TRIGger:SHOLd:SLOPe" on page 647

:TRIGger:SHOLd:TIME:HOLD

(see page 828)

Command Syntax

```
:TRIGger:SHOLd:TIME:HOLD <time>[suffix]
<time> ::= floating-point number in NR3 format
[suffix] ::= {s | ms | us | ns | ps}
```

The :TRIGger:SHOLd:TIME:HOLD command sets the hold time.

Query Syntax

```
:TRIGger:SHOLd:TIME:HOLD?
```

The :TRIGger:SHOLd:TIME:HOLD? query returns the currently specified hold time.

Return Format

```
<time><NL>
<time> ::= floating-point number in NR3 format
```

See Also

- "Introduction to :TRIGger Commands" on page 615

:TRIGger:SHOLd:TIME:SETup

(see page 828)

Command Syntax

```
:TRIGger:SHOLd:TIME:SETup <time>[suffix]

<time> ::= floating-point number in NR3 format

[suffix] ::= {s | ms | us | ns | ps}
```

The :TRIGger:SHOLd:TIME:SETup command sets the setup time.

Query Syntax

```
:TRIGger:SHOLd:TIME:SETup?
```

The :TRIGger:SHOLd:TIME:SETup? query returns the currently specified setup time.

Return Format

```
<time><NL>

<time> ::= floating-point number in NR3 format
```

See Also

- "Introduction to :TRIGger Commands" on page 615

:TRIGger:TRANsition Commands

NOTE The :TRIGger:TRANsition commands are available on the DSOX1200-Series oscilloscopes only.

The :TRIGger:TRANsition commands set the rise/fall time trigger options.

Table 84 :TRIGger:TRANsition Commands Summary

Command	Query	Options and Query Returns
:TRIGger:TRANsition:QUALifier <qualifier> (see page 653)	:TRIGger:TRANsition:QUALifier? (see page 653)	<qualifier> ::= {GREaterthan | LESSthan}
:TRIGger:TRANsition:SLOPe <slope> (see page 654)	:TRIGger:TRANsition:SLOPe? (see page 654)	<slope> ::= {NEGative | POSitive}
:TRIGger:TRANsition:SOURce <source> (see page 655)	:TRIGger:TRANsition:SOURce? (see page 655)	<source> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:TRANsition:TIME <time>[suffix] (see page 656)	:TRIGger:TRANsition:TIME? (see page 656)	<time> ::= floating-point number in NR3 format [suffix] ::= {s | ms | us | ns | ps}

:TRIGger:TRANsition:QUALifier

(see page 828)

Command Syntax

```
:TRIGger:TRANsition:QUALifier <qualifier>

<qualifier> ::= {GREaterthan | LESSthan}
```

The :TRIGger:TRANsition:QUALifier command specifies whether you are looking for rise/fall times greater than or less than a certain time value. The time value is set using the :TRIGger:TRANsition:TIME command.

Query Syntax

```
:TRIGger:TRANsition:QUALifier?
```

The :TRIGger:TRANsition:QUALifier? query returns the current rise/fall time trigger qualifier setting.

Return Format

```
<qualifier><NL>

<qualifier> ::= {GRE | LESS}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:TRANsition:TIME" on page 656
- ":TRIGger:MODE" on page 624

:TRIGger:TRANsition:SLOPe

(see page 828)

Command Syntax

```
:TRIGger:TRANsition:SLOPe <slope>

<slope> ::= {NEGative | POSitive}
```

The :TRIGger:TRANsition:SLOPe command specifies a POSitive rising edge or a NEGative falling edge.

Query Syntax

```
:TRIGger:TRANsition:SLOPe?
```

The :TRIGger:TRANsition:SLOPe? query returns the current rise/fall time trigger slope setting.

Return Format

```
<slope><NL>

<slope> ::= {NEG | POS}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":TRIGger:TRANsition:SOURce" on page 655

:TRIGger:TRANsition:SOURce

(see page 828)

Command Syntax

```
:TRIGger:TRANsition:SOURce <source>

<source> ::= {CHANnel<n>}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :TRIGger:TRANsition:SOURce command selects the channel used to produce the trigger.

Query Syntax

```
:TRIGger:TRANsition:SOURce?
```

The :TRIGger:TRANsition:SOURce? query returns the current transition trigger source.

Return Format

```
<source><NL>

<source> ::= {CHAN<n>}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":TRIGger:TRANsition:SLOPe" on page 654

:TRIGger:TRANsition:TIME

(see page 828)

Command Syntax

```
:TRIGger:TRANsition:TIME <time>[suffix]

<time> ::= floating-point number in NR3 format

[suffix] ::= {s | ms | us | ns | ps}
```

The :TRIGger:TRANsition:TIME command sets the time value for rise/fall time triggers. You also use the :TRIGger:TRANsition:QUALifier command to specify whether you are triggering on times greater than or less than this time value.

Query Syntax

```
:TRIGger:TRANsition:TIME?
```

The :TRIGger:TRANsition:TIME? query returns the current rise/fall time trigger time value.

Return Format

```
<time><NL>

<time> ::= floating-point number in NR3 format
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:TRANsition:QUALifier" on page 653

:TRIGger:TV Commands

Table 85 :TRIGger:TV Commands Summary

Command	Query	Options and Query Returns
:TRIGger:TV:LINE <line number> (see page 658)	:TRIGger:TV:LINE? (see page 658)	<line number> ::= integer in NR1 format
:TRIGger:TV:MODE <tv mode> (see page 659)	:TRIGger:TV:MODE? (see page 659)	<tv mode> ::= {FIEld1 | FIEld2 | AFIelds | ALINes | LFIeld1 | LFIeld2 | LALTernate}
:TRIGger:TV:POLarity <polarity> (see page 660)	:TRIGger:TV:POLarity? (see page 660)	<polarity> ::= {POSitive | NEGative}
:TRIGger:TV:SOURce <source> (see page 661)	:TRIGger:TV:SOURce? (see page 661)	<source> ::= {CHANnel<n>} <n> ::= 1 to (# analog channels) in NR1 format
:TRIGger:TV:STANdard <standard> (see page 662)	:TRIGger:TV:STANdard? (see page 662)	<standard> ::= {NTSC | PAL | PALM | SECam}

:TRIGger:TV:LINE

N (see page 828)

Command Syntax

```
:TRIGger:TV:LINE <line_number>

<line_number> ::= integer in NR1 format
```

The :TRIGger:TV:LINE command allows triggering on a specific line of video. The line number limits vary with the standard and mode, as shown in the following table.

Table 86 TV Trigger Line Number Limits

TV Standard	Mode		
	LFIeld1	LFIeld2	LALTernate
NTSC	1 to 263	1 to 262	1 to 262
PAL	1 to 313	314 to 625	1 to 312
PAL-M	1 to 263	264 to 525	1 to 262
SECAM	1 to 313	314 to 625	1 to 312

Query Syntax

```
:TRIGger:TV:LINE?
```

The :TRIGger:TV:LINE? query returns the current TV trigger line number setting.

Return Format

```
<line_number><NL>

<line_number>::= integer in NR1 format
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:TV:STANdard" on page 662
- ":TRIGger:TV:MODE" on page 659

:TRIGger:TV:MODE

(see page 828)

Command Syntax

```
:TRIGger:TV:MODE <mode>

<mode> ::= {FIEld1 | FIEld2 | AFIelds | ALINes
           | LFIeld1 | LFIeld2 | LALTernate}
```

The :TRIGger:TV:MODE command selects the TV trigger mode and field.

Old forms for <mode> are accepted:

<mode>	Old Forms Accepted
FIEld1	F1
FIEld2	F2
AFIelds	ALLFields, ALLFLDS
ALINes	ALLLines
LFIeld1	LINEF1, LINEFIELD1
LFIeld2	LINEF2, LINEFIELD2
LALTernate	LINEAlt

Query Syntax

```
:TRIGger:TV:MODE?
```

The :TRIGger:TV:MODE? query returns the TV trigger mode.

Return Format

```
<value><NL>

<value> ::= {FIE1 | FIE2 | AFI | ALIN | LFI1 | LFI2 | LALT}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:TV:STANdard" on page 662
- ":TRIGger:MODE" on page 624

:TRIGger:TV:POLarity

(see page 828)

Command Syntax

```
:TRIGger:TV:POLarity <polarity>
<polarity> ::= {POSitive | NEGative}
```

The :TRIGger:TV:POLarity command sets the polarity for the TV trigger.

Query Syntax

```
:TRIGger:TV:POLarity?
```

The :TRIGger:TV:POLarity? query returns the TV trigger polarity.

Return Format

```
<polarity><NL>
<polarity> ::= {POS | NEG}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":TRIGger:TV:SOURce" on page 661

:TRIGger:TV:SOURce

(see page 828)

Command Syntax

```
:TRIGger:TV:SOURce <source>

<source> ::= {CHANnel<n>}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :TRIGger:TV:SOURce command selects the channel used to produce the trigger.

Query Syntax

```
:TRIGger:TV:SOURce?
```

The :TRIGger:TV:SOURce? query returns the current TV trigger source.

Return Format

```
<source><NL>

<source> ::= {CHAN<n>}
```

See Also

- "Introduction to :TRIGger Commands" on page 615
- ":TRIGger:MODE" on page 624
- ":TRIGger:TV:POLarity" on page 660

Example Code

- "Example Code" on page 632

:TRIGger:TV:STANdard

N (see page 828)

Command Syntax

```
:TRIGger:TV:STANdard <standard>

<standard> ::= {NTSC | PALM | PAL | SECam}
```

The :TRIGger:TV:STANdard command selects the video standard:

- NTSC
- PAL
- PAL-M
- SECAM

Query Syntax

```
:TRIGger:TV:STANdard?
```

The :TRIGger:TV:STANdard? query returns the current TV trigger standard setting.

Return Format

```
<standard><NL>

<standard> ::= {NTSC | PALM | PAL | SEC}
```

29 :WAVeform Commands

Provide access to waveform data. See "Introduction to :WAVeform Commands" on page 665.

Table 87 :WAVeform Commands Summary

Command	Query	Options and Query Returns
:WAVeform:BYTeorder <value> (see page 670)	:WAVeform:BYTeorder? (see page 670)	<value> ::= {LSBFirst | MSBFirst}
n/a	:WAVeform:COUNt? (see page 671)	<count> ::= an integer from 1 to 65536 in NR1 format
n/a	:WAVeform:DATA? (see page 672)	<binary block length bytes>, <binary data> For example, to transmit 1000 bytes of data, the syntax would be: #800001000<1000 bytes of data><NL> 8 is the number of digits that follow 00001000 is the number of bytes to be transmitted <1000 bytes of data> is the actual data
:WAVeform:FORMat <value> (see page 674)	:WAVeform:FORMat? (see page 674)	<value> ::= {WORD | BYTE | ASCII}
:WAVeform:POINts <# points> (see page 675)	:WAVeform:POINts? (see page 675)	<# points> ::= {100 | 250 | 500 | 1000 | <points_mode>} if waveform points mode is NORMal <# points> ::= {100 | 250 | 500 | 1000 | 2000 ... 2000000 in 1-2-5 sequence | <points_mode>} if waveform points mode is MAXimum or RAW <points_mode> ::= {NORMal | MAXimum | RAW}

Table 87 :WAVeform Commands Summary (continued)

Command	Query	Options and Query Returns
:WAVeform:POINts:MODE <points_mode> (see page 677)	:WAVeform:POINts:MODE? (see page 677)	<points_mode> ::= {NORMal | MAXimum | RAW}
n/a	:WAVeform:PREamble? (see page 679)	<preamble_block> ::= <format NR1>, <type NR1>,<points NR1>,<count NR1>, <xincrement NR3>, <xorigin NR3>, <xreference NR1>,<yincrement NR3>, <yorigin NR3>, <yreference NR1> <format> ::= an integer in NR1 format: • 0 for BYTE format • 1 for WORD format • 2 for ASCii format <type> ::= an integer in NR1 format: • 0 for NORMal type • 1 for PEAK detect type • 3 for AVERage type • 4 for HRESolution type <count> ::= Average count, or 1 if PEAK detect type or NORMal; an integer in NR1 format
n/a	:WAVeform:SEGMented:COUNt? (see page 682)	<count> ::= an integer from 2 to 500 in NR1 format (with SGM license)
n/a	:WAVeform:SEGMented:TTAG? (see page 683)	<time_tag> ::= in NR3 format (with SGM license)
:WAVeform:SOURce <source> (see page 684)	:WAVeform:SOURce? (see page 684)	<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r> | SBUS1 | ABUS | EXT} <n> ::= 1 to (# analog channels) in NR1 format <r> ::= 1 to (# ref waveforms) in NR1 format EXT available on 2-channel oscilloscopes only
:WAVeform:SOURce:SUBSource <subsource> (see page 688)	:WAVeform:SOURce:SUBSource? (see page 688)	<subsource> ::= {{SUB0 | RX | MOSI} | {SUB1 | TX | MISO}}
n/a	:WAVeform:TYPE? (see page 689)	<return_mode> ::= {NORM | PEAK | AVER | HRES}

Table 87 :WAVeform Commands Summary (continued)

Command	Query	Options and Query Returns
:WAVeform:UNSigned {{0 | OFF} | {1 | ON}} (see page 690)	:WAVeform:UNSigned? (see page 690)	{0 | 1}
:WAVeform:VIEW <view> (see page 691)	:WAVeform:VIEW? (see page 691)	<view> ::= {MAIN}
n/a	:WAVeform:XINCrement? (see page 692)	<return_value> ::= x-increment in the current preamble in NR3 format
n/a	:WAVeform:XORigin? (see page 693)	<return_value> ::= x-origin value in the current preamble in NR3 format
n/a	:WAVeform:XREFerence? (see page 694)	<return_value> ::= 0 (x-reference value in the current preamble in NR1 format)
n/a	:WAVeform:YINCrement? (see page 695)	<return_value> ::= y-increment value in the current preamble in NR3 format
n/a	:WAVeform:YORigin? (see page 696)	<return_value> ::= y-origin in the current preamble in NR3 format
n/a	:WAVeform:YREFerence? (see page 697)	<return_value> ::= y-reference value in the current preamble in NR1 format

Introduction to :WAVeform Commands

The WAVeform subsystem is used to transfer data to a controller from the oscilloscope waveform memories. The queries in this subsystem will only operate when the channel selected by :WAVeform:SOURce is on.

Waveform Data and Preamble

The waveform record is actually contained in two portions: the preamble and waveform data. The waveform record must be read from the oscilloscope by the controller using two separate commands, :WAVeform:DATA (see page 672) and :WAVeform:PREamble (see page 679). The waveform data is the actual data acquired for each point in the specified source. The preamble contains the information for interpreting the waveform data, which includes the number of points acquired, the format of acquired data, and the type of acquired data. The preamble also contains the X and Y increments, origins, and references for the acquired data, so that word and byte data can be translated to time and voltage values.

Data Acquisition Types

There are four types of waveform acquisitions that can be selected for analog channels with the :ACQuire:TYPE command (see page 199): NORMal, AVERage, PEAK, and HRESolution. When the data is acquired using the :DIGitize command (see page 153) or :RUN command (see page 170), the data is placed in the channel buffer of the specified source.

Once you have acquired data with the :DIGitize command, the instrument is stopped. If the instrument is restarted (via the programming interface or the front panel), or if any instrument setting is changed, the data acquired with the :DIGitize command may be overwritten.You should first acquire the data with the :DIGitize command, then immediately read the data with the :WAVeform:DATA? query (see page 672) before changing any instrument setup.

A waveform record consists of either all of the acquired points or a subset of the acquired points. The number of points acquired may be queried using :ACQuire:POINts? (see page 192).

Helpful Hints:

The number of points transferred to the computer is controlled using the :WAVeform:POINts command (see page 675). If :WAVeform:POINts MAXimum is specified and the instrument is not running (stopped, in other words), all of the points that are displayed are transferred. This can be the full oscilloscope acquisition memory in some operating modes. You can ask for fewer points to speed data transfers and minimize controller analysis time. The :WAVeform:POINts may be varied even after data on a channel is acquired. However, this decimation may result in lost pulses and transitions. The number of points selected for transfer using :WAVeform:POINts must be an even divisor of 1,000 or be set to MAXimum. :WAVeform:POINts determines the increment between time buckets that will be transferred. If POINts = MAXimum, the data cannot be decimated. For example:

- `:WAVeform:POINts 1000` — returns time buckets 0, 1, 2, 3, 4 ,.., 999.
- `:WAVeform:POINts 500` — returns time buckets 0, 2, 4, 6, 8 ,.., 998.
- `:WAVeform:POINts 250` — returns time buckets 0, 4, 8, 12, 16 ,.., 996.
- `:WAVeform:POINts 100` — returns time buckets 0, 10, 20, 30, 40 ,.., 990.

Analog Channel Data

NORMal Data

Normal data consists of the last data point (hit) in each time bucket. This data is transmitted over the programming interface in a linear fashion starting with time bucket 0 and going through time bucket n - 1, where n is the number returned by the :WAVeform:POINts? query (see page 675). Only the magnitude values of each data point are transmitted. The first voltage value corresponds to the first time bucket on the left side of the screen and the last value corresponds to the

next-to-last time bucket on the right side of the screen. Time buckets without data return 0. The time values for each data point correspond to the position of the data point in the data array. These time values are not transmitted.

AVERage Data

AVERage data consists of the average of the first n hits in a time bucket, where n is the value returned by the :ACQuire:COUNt query (see page 190). Time buckets that have fewer than n hits return the average of the data they do have. If a time bucket does not have any data in it, it returns 0.

This data is transmitted over the interface linearly, starting with time bucket 0 and proceeding through time bucket n-1, where n is the number returned by the :WAVeform:POINts? query (see page 675). The first value corresponds to a point at the left side of the screen and the last value corresponds to one point away from the right side of the screen. The maximum number of points that can be returned in average mode is 8192 unless ACQuire:COUNt has been set to 1.

PEAK Data

Peak detect display mode is used to detect glitches for time base settings of 500 us/div and slower. In this mode, the oscilloscope can sample more data than it can store and display. So, when peak detect is turned on, the oscilloscope scans through the extra data, picks up the minimum and maximum for each time bucket, then stores the data in an array. Each time bucket contains two data sample.

The array is transmitted over the interface bus linearly, starting with time bucket 0 proceeding through time bucket n-1, where n is the number returned by the :WAVeform:POINts? query (see page 675). In each time bucket, two values are transmitted, first the minimum, followed by the maximum. The first pair of values corresponds to the time bucket at the leftmost side of the screen. The last pair of values corresponds to the time bucket at the far right side of the screen. In :ACQuire:TYPE PEAK mode (see page 199), the value returned by the :WAVeform:XINCrement query (see page 692) should be doubled to find the time difference between the min-max pairs.

HRESolution Data

The high resolution (*smoothing*) mode is used to reduce noise at slower sweep speeds where the digitizer samples faster than needed to fill memory for the displayed time range.

Data Conversion

Word or byte data sent from the oscilloscope must be scaled for useful interpretation. The values used to interpret the data are the X and Y references, X and Y origins, and X and Y increments. These values are read from the waveform preamble. Each channel has its own waveform preamble.

In converting a data value to a voltage value, the following formula is used:

voltage = [(data value - yreference) * yincrement] + yorigin

If the :WAVeform:FORMat data format is ASCii (see page 674), the data values are converted internally and sent as floating point values separated by commas.

In converting a data value to time, the time value of a data point can be determined by the position of the data point. For example, the fourth data point sent with :WAVeform:XORigin = 16 ns, :WAVeform:XREFerence = 0, and :WAVeform:XINCrement = 2 ns, can be calculated using the following formula:

time = [(data point number - xreference) * xincrement] + xorigin

This would result in the following calculation for time bucket 3:

time = [(3 - 0) * 2 ns] + 16 ns = 22 ns

In :ACQuire:TYPE PEAK mode (see page 199), because data is acquired in max-min pairs, modify the previous time formula to the following:

time=[(data pair number - xreference) * xincrement * 2] + xorigin

Data Format for Transfer

There are three formats for transferring waveform data over the interface: BYTE, WORD and ASCii (see ":WAVeform:FORMat" on page 674). BYTE, WORD and ASCii formatted waveform records are transmitted using the arbitrary block program data format specified in IEEE 488.2.

When you use the block data format, the ASCII character string "#8<DD...D>" is sent prior to sending the actual data. The 8 indicates how many Ds follow. The Ds are ASCII numbers that indicate how many data bytes follow.

For example, if 1000 points will be transferred, and the WORD format was specified, the block header "#800001000" would be sent. The 8 indicates that eight length bytes follow, and 00001000 indicates that 1000 binary data bytes follow.

Use the :WAVeform:UNSigned command (see page 690) to control whether data values are sent as unsigned or signed integers. This command can be used to match the instrument's internal data type to the data type used by the programming language. This command has no effect if the data format is ASCii.

Data Format for Transfer - ASCii format

The ASCii format (see ":WAVeform:FORMat" on page 674) provides access to the waveform data as real Y-axis values without using Y origin, Y reference, and Y increment to convert the binary data. Values are transferred as ASCii digits in floating point format separated by commas. In ASCii format, holes are represented by the value 9.9e+37. The setting of :WAVeform:BYTeorder (see page 670) and :WAVeform:UNSigned (see page 690) have no effect when the format is ASCii.

Data Format for Transfer - WORD format

WORD format (see ":WAVeform:FORMat" on page 674) provides 16-bit access to the waveform data. In the WORD format, the number of data bytes is twice the number of data points. The number of data points is the value returned by the :WAVeform:POINts? query (see page 675). If the data intrinsically has less than 16 bits of resolution, the data is left-shifted to provide 16 bits of resolution and the least significant bits are set to 0. Currently, the greatest intrinsic resolution of any data is 12 bits, so at least the lowest 4 bits of data will be 0. If there is a hole in the data, the hole is represented by a 16 bit value equal to 0.

Use :WAVeform:BYTeorder (see page 670) to determine if the least significant byte or most significant byte is to be transferred first. The :BYTeorder command can be used to alter the transmit sequence to match the storage sequence of an integer in the programming language being used.

Data Format for Transfer - BYTE format

The BYTE format (see ":WAVeform:FORMat" on page 674) allows 8-bit access to the waveform data. If the data intrinsically has more than 8 bits of resolution (averaged data), the data is right-shifted (truncated) to fit into 8 bits. If there is a hole in the data, the hole is represented by a value of 0. The BYTE-formatted data transfers over the programming interface faster than ASCii or WORD-formatted data, because in ASCii format, as many as 13 bytes per point are transferred, in BYTE format one byte per point is transferred, and in WORD format two bytes per point are transferred.

The :WAVeform:BYTeorder command (see page 670) has no effect when the data format is BYTE.

Reporting the Setup

The following is a sample response from the :WAVeform? query. In this case, the query was issued following a *RST command.

```
:WAV:UNS 1;VIEW MAIN;BYT MSBF;FORM BYTE;POIN +1000;SOUR CHAN1;SOUR:SUBS
NONE
```

:WAVeform:BYTeorder

(see page 828)

Command Syntax

```
:WAVeform:BYTeorder <value>

<value> ::= {LSBFirst | MSBFirst}
```

The :WAVeform:BYTeorder command sets the output sequence of the WORD data.

- MSBFirst – sets the most significant byte to be transmitted first.
- LSBFirst – sets the least significant byte to be transmitted first.

This command affects the transmitting sequence only when :WAVeform:FORMat WORD is selected.

The default setting is MSBFirst.

Query Syntax

```
:WAVeform:BYTeorder?
```

The :WAVeform:BYTeorder query returns the current output sequence.

Return Format

```
<value><NL>

<value> ::= {LSBF | MSBF}
```

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:DATA" on page 672
- ":WAVeform:FORMat" on page 674
- ":WAVeform:PREamble" on page 679

Example Code

- "Example Code" on page 684
- "Example Code" on page 680

:WAVeform:COUNt

(see page 828)

Query Syntax `:WAVeform:COUNt?`

The :WAVeform:COUNT? query returns the count used to acquire the current waveform. This may differ from current values if the unit has been stopped and its configuration modified. For all acquisition types except average, this value is 1.

Return Format `<count_argument><NL>`

`<count_argument> ::= an integer from 1 to 65536 in NR1 format`

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":ACQuire:COUNt" on page 190
- ":ACQuire:TYPE" on page 199

:WAVeform:DATA

(see page 828)

Query Syntax

```
:WAVeform:DATA?
```

The :WAVeform:DATA query returns the binary block of sampled data points transmitted using the IEEE 488.2 arbitrary block data format. The binary data is formatted according to the settings of the :WAVeform:UNSigned, :WAVeform:BYTeorder, :WAVeform:FORMat, and :WAVeform:SOURce commands. The number of points returned is controlled by the :WAVeform:POINts command.

In BYTE or WORD waveform formats, these data values have special meaning:

- 0x00 or 0x0000 – Hole. Holes are locations where data has not yet been acquired.

  Another situation where there can be zeros in the data, incorrectly, is when programming over telnet port 5024. Port 5024 provides a command prompt and is intended for ASCII transfers. Use telnet port 5025 instead.
- 0x01 or 0x0001 – Clipped low. These are locations where the waveform is clipped at the bottom of the oscilloscope display.
- 0xFF or 0xFFFF – Clipped high. These are locations where the waveform is clipped at the top of the oscilloscope display.

Return Format

```
<binary block data><NL>
```

See Also

- For a more detailed description of the data returned for different acquisition types, see: "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:UNSigned" on page 690
- ":WAVeform:BYTeorder" on page 670
- ":WAVeform:FORMat" on page 674
- ":WAVeform:POINts" on page 675
- ":WAVeform:PREamble" on page 679
- ":WAVeform:SOURce" on page 684
- ":WAVeform:TYPE" on page 689

Example Code

```
' QUERY_WAVE_DATA - Outputs waveform data that is stored in a buffer.

' Query the oscilloscope for the waveform data.
myScope.WriteString ":WAV:DATA?"

' READ_WAVE_DATA - The wave data consists of two parts: the header,
' and the actual waveform data followed by a new line (NL) character.
' The query data has the following format:
'
'    <header><waveform_data><NL>
'
' Where:
```

```
'    <header> = #800001000 (This is an example header)
' The "#8" may be stripped off of the header and the remaining
' numbers are the size, in bytes, of the waveform data block.  The
' size can vary depending on the number of points acquired for the
' waveform.  You can then read that number of bytes from the
' oscilloscope and the terminating NL character.
'
Dim lngI As Long
Dim lngDataValue As Long

varQueryResult = myScope.ReadIEEEBlock(BinaryType_UI1)
' Unsigned integer bytes.
For lngI = 0 To UBound(varQueryResult) _
    Step (UBound(varQueryResult) / 20)   ' 20 points.
  If intBytesPerData = 2 Then
    lngDataValue = varQueryResult(lngI) * 256 _
        + varQueryResult(lngI + 1)   ' 16-bit value.
  Else
    lngDataValue = varQueryResult(lngI)   ' 8-bit value.
  End If
  strOutput = strOutput + "Data point " + _
    CStr(lngI / intBytesPerData) + ", " + _
    FormatNumber((lngDataValue - lngYReference) _
        * sngYIncrement + sngYOrigin) + " V, " + _
    FormatNumber(((lngI / intBytesPerData - lngXReference) _
        * sngXIncrement + dblXOrigin) * 1000000) + " us" + vbCrLf
Next lngI
MsgBox "Waveform data:" + vbCrLf + strOutput
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:WAVeform:FORMat

(see page 828)

Command Syntax

```
:WAVeform:FORMat <value>

<value> ::= {WORD | BYTE | ASCii}
```

The :WAVeform:FORMat command sets the data transmission mode for waveform data points. This command controls how the data is formatted when sent from the oscilloscope.

- ASCii formatted data converts the internal integer data values to real Y-axis values. Values are transferred as ASCii digits in floating point notation, separated by commas.

  ASCII formatted data is transferred ASCii text.
- WORD formatted data transfers 16-bit data as two bytes. The :WAVeform:BYTeorder command can be used to specify whether the upper or lower byte is transmitted first. The default (no command sent) is that the upper byte transmitted first.
- BYTE formatted data is transferred as 8-bit bytes.

Query Syntax

```
:WAVeform:FORMat?
```

The :WAVeform:FORMat query returns the current output format for the transfer of waveform data.

Return Format

```
<value><NL>

<value> ::= {WORD | BYTE | ASC}
```

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:BYTeorder" on page 670
- ":WAVeform:SOURce" on page 684
- ":WAVeform:DATA" on page 672
- ":WAVeform:PREamble" on page 679

Example Code

- "Example Code" on page 684

:WAVeform:POINts

(see page 828)

Command Syntax

```
:WAVeform:POINts <# points>

<# points> ::= {100 | 250 | 500 | 1000 | <points mode>}
               if waveform points mode is NORMal

<# points> ::= {100 | 250 | 500 | 1000 | 2000 | 5000 | 10000 | 20000
               | 50000 | 100000 | 200000 | 500000 | 1000000 | 2000000
               | <points mode>}
               if waveform points mode is MAXimum or RAW

<points mode> ::= {NORMal | MAXimum | RAW}
```

NOTE The <points_mode> option is deprecated. Use the :WAVeform:POINts:MODE command instead.

The :WAVeform:POINts command sets the number of waveform points to be transferred with the :WAVeform:DATA? query. This value represents the points contained in the waveform selected with the :WAVeform:SOURce command.

For the analog sources, the records that can be transferred depend on the waveform points mode. The maximum number of points returned for math (function) waveforms is determined by the NORMal waveform points mode. See the :WAVeform:POINts:MODE command (see page 677) for more information.

Only data visible on the display will be returned.

Query Syntax

```
:WAVeform:POINts?
```

The :WAVeform:POINts query returns the number of waveform points to be transferred when using the :WAVeform:DATA? query. Setting the points mode will affect what data is transferred (see the :WAVeform:POINts:MODE command (see page 677) for more information).

Return Format

```
<# points><NL>

<# points> ::= {100 | 250 | 500 | 1000 | <maximum # points>}
               if waveform points mode is NORMal

<# points> ::= {100 | 250 | 500 | 1000 | 2000 | 5000 | 10000 | 20000
               | 50000 | 100000 | 200000 | 500000 | 1000000 | 2000000
               | <maximum # points>}
               if waveform points mode is MAXimum or RAW
```

NOTE If a full screen of data is not displayed, the number of points returned will not be 1000 or an even divisor of it.

See Also
- "Introduction to :WAVeform Commands" on page 665
- ":ACQuire:POINts" on page 192
- ":WAVeform:DATA" on page 672
- ":WAVeform:SOURce" on page 684
- ":WAVeform:VIEW" on page 691
- ":WAVeform:PREamble" on page 679
- ":WAVeform:POINts:MODE" on page 677

Example Code

```
' WAVE_POINTS - Specifies the number of points to be transferred
' using the ":WAVeform:DATA?" query.
myScope.WriteString ":WAVeform:POINts 1000"
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:WAVeform:POINts:MODE

N (see page 828)

Command Syntax

```
:WAVeform:POINts:MODE <points_mode>

<points_mode> ::= {NORMal | MAXimum | RAW}
```

The :WAVeform:POINts:MODE command sets the data record to be transferred with the :WAVeform:DATA? query.

For the analog sources, there are two different records that can be transferred:

- The first is the raw acquisition record. The maximum number of points available in this record is returned by the :ACQuire:POINts? query. The raw acquisition record can only be transferred when the oscilloscope is not running and can only be retrieved from the analog sources.
- The second is referred to as the *measurement record* and is a 62,500-point (maximum) representation of the raw acquisition record. The measurement record can be retrieved from any source.

If the <points_mode> is NORMal the measurement record is retrieved.

If the <points_mode> is RAW, the raw acquisition record is used. Under some conditions, such as when the oscilloscope is running, this data record is unavailable.

If the <points_mode> is MAXimum, whichever record contains the maximum amount of points is used. Usually, this is the raw acquisition record. But, if the raw acquisition record is unavailable (for example, when the oscilloscope is running), the measurement record may have more data. If data is being retrieved as the oscilloscope is stopped and as the data displayed is changing, the data being retrieved can switch between the measurement and raw acquisition records.

Considerations for MAXimum or RAW data retrieval

- The instrument must be stopped (see the :STOP command (see page 174) or the :DIGitize command (see page 153) in the root subsystem) in order to return more than the *measurement record*.
- :TIMebase:MODE must be set to MAIN.
- :ACQuire:TYPE must be set to NORMal or HRESolution.
- MAXimum or RAW will allow up to 100,000 points to be returned. The number of points returned will vary as the instrument's configuration is changed. Use the :WAVeform:POINts? MAXimum query to determine the maximum number of points that can be retrieved at the current settings.

Query Syntax

```
:WAVeform:POINts:MODE?
```

The :WAVeform:POINts:MODE? query returns the current points mode. Setting the points mode will affect what data is transferred. See the discussion above.

Return Format

```
<points_mode><NL>
```

```
<points_mode> ::= {NORMal | MAXimum | RAW}
```

See Also
- "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:DATA" on page 672
- ":ACQuire:POINts" on page 192
- ":WAVeform:VIEW" on page 691
- ":WAVeform:PREamble" on page 679
- ":WAVeform:POINts" on page 675
- ":TIMebase:MODE" on page 605
- ":ACQuire:TYPE" on page 199
- ":ACQuire:COUNt" on page 190

:WAVeform:PREamble

(see page 828)

Query Syntax

```
:WAVeform:PREamble?
```

The :WAVeform:PREamble query requests the preamble information for the selected waveform source. The preamble data contains information concerning the vertical and horizontal scaling of the data of the corresponding channel.

Return Format

```
<preamble_block><NL>

<preamble_block> ::= <format 16-bit NR1>,
                     <type 16-bit NR1>,
                     <points 32-bit NR1>,
                     <count 32-bit NR1>,
                     <xincrement 64-bit floating point NR3>,
                     <xorigin 64-bit floating point NR3>,
                     <xreference 32-bit NR1>,
                     <yincrement 32-bit floating point NR3>,
                     <yorigin 32-bit floating point NR3>,
                     <yreference 32-bit NR1>

<format> ::= 0 for BYTE format, 1 for WORD format, 4 for ASCii format;
             an integer in NR1 format (format set by :WAVeform:FORMat).

<type> ::= 2 for AVERage type, 0 for NORMal type, 1 for PEAK detect
           type; an integer in NR1 format (type set by :ACQuire:TYPE).

<count> ::= Average count or 1 if PEAK or NORMal; an integer in NR1
            format (count set by :ACQuire:COUNt).
```



See Also

- "Introduction to :WAVeform Commands" on page 665

- ":ACQuire:COUNt" on page 190
- ":ACQuire:POINts" on page 192
- ":ACQuire:TYPE" on page 199
- ":DIGitize" on page 153
- ":WAVeform:COUNt" on page 671
- ":WAVeform:DATA" on page 672
- ":WAVeform:FORMat" on page 674
- ":WAVeform:POINts" on page 675
- ":WAVeform:TYPE" on page 689
- ":WAVeform:XINCrement" on page 692
- ":WAVeform:XORigin" on page 693
- ":WAVeform:XREFerence" on page 694
- ":WAVeform:YINCrement" on page 695
- ":WAVeform:YORigin" on page 696
- ":WAVeform:YREFerence" on page 697

Example Code

```
' GET_PREAMBLE - The preamble block contains all of the current
' WAVEFORM settings.  It is returned in the form <preamble_block><NL>
' where <preamble_block> is:
'    FORMAT        : int16 - 0 = BYTE, 1 = WORD, 4 = ASCII.
'    TYPE          : int16 - 0 = NORMAL, 1 = PEAK DETECT, 2 = AVERAGE
'    POINTS        : int32 - number of data points transferred.
'    COUNT         : int32 - 1 and is always 1.
'    XINCREMENT    : float64 - time difference between data points.
'    XORIGIN       : float64 - always the first data point in memory.
'    XREFERENCE    : int32 - specifies the data point associated with
'                            x-origin.
'    YINCREMENT    : float32 - voltage diff between data points.
'    YORIGIN       : float32 - value is the voltage at center screen.
'    YREFERENCE    : int32 - specifies the data point where y-origin
'                            occurs.
Dim Preamble()
Dim intFormat As Integer
Dim intType As Integer
Dim lngPoints As Long
Dim lngCount As Long
Dim dblXIncrement As Double
Dim dblXOrigin As Double
Dim lngXReference As Long
Dim sngYIncrement As Single
Dim sngYOrigin As Single
Dim lngYReference As Long
Dim strOutput As String

myScope.WriteString ":WAVEFORM:PREAMBLE?"    ' Query for the preamble.
Preamble() = myScope.ReadList    ' Read preamble information.
intFormat = Preamble(0)
intType = Preamble(1)
```

```
lngPoints = Preamble(2)
lngCount = Preamble(3)
dblXIncrement = Preamble(4)
dblXOrigin = Preamble(5)
lngXReference = Preamble(6)
sngYIncrement = Preamble(7)
sngYOrigin = Preamble(8)
lngYReference = Preamble(9)
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:WAVeform:SEGMented:COUNt

(see page 828)

Query Syntax `:WAVeform:SEGMented:COUNt?`

NOTE **Segmented memory is available on the DSOX1200-Series oscilloscope models that have the SGM license.**

The :WAVeform:SEGMented:COUNt query returns the number of memory segments in the acquired data. You can use the :WAVeform:SEGMented:COUNt? query while segments are being acquired (although :DIGitize blocks subsequent queries until the full segmented acquisition is complete).

The segmented memory acquisition mode is enabled with the :ACQuire:MODE command. The number of segments to acquire is set using the :ACQuire:SEGMented:COUNt command, and data is acquired using the :DIGitize, :SINGle, or :RUN commands.

Return Format

```
<count> ::= an integer from 2 to 500 in NR1 format (count set by
            :ACQuire:SEGMented:COUNt).
```

See Also

- ":ACQuire:MODE" on page 191
- ":ACQuire:SEGMented:COUNt" on page 194
- ":DIGitize" on page 153
- ":SINGle" on page 172
- ":RUN" on page 170
- "Introduction to :WAVeform Commands" on page 665

Example Code

- "Example Code" on page 195

:WAVeform:SEGMented:TTAG

(see page 828)

Query Syntax `:WAVeform:SEGMented:TTAG?`

NOTE Segmented memory is available on the DSOX1200-Series oscilloscope models that have the SGM license.

The :WAVeform:SEGMented:TTAG? query returns the time tag of the currently selected segmented memory index. The index is selected using the :ACQuire:SEGMented:INDex command.

Return Format `<time_tag> ::= in NR3 format`

See Also
- ":ACQuire:SEGMented:INDex" on page 195
- "Introduction to :WAVeform Commands" on page 665

Example Code
- "Example Code" on page 195

:WAVeform:SOURce

(see page 828)

Command Syntax

```
:WAVeform:SOURce <source>

<source> ::= {CHANnel<n> | FUNCtion | MATH | FFT | WMEMory<r> | SBUS1
   | ABUS | EXT}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= {1 | 2}
```

The :WAVeform:SOURce command selects the analog channel, function, or reference waveform to be used as the source for the :WAVeform commands.

Function capabilities include add, subtract, multiply, and FFT (Fast Fourier Transform) operations.

NOTE The EXT source is available on 2-channel oscilloscopes only.

Query Syntax

```
:WAVeform:SOURce?
```

The :WAVeform:SOURce? query returns the currently selected source for the WAVeform commands.

NOTE MATH is an alias for FUNCtion. The :WAVeform:SOURce? Query returns FUNC if the source is FUNCtion or MATH.

Return Format

```
<source><NL>

<source> ::= {CHAN<n> | FUNC | FFT | WMEM<r> | SBUS1 | ABUS | EXT}

<n> ::= 1 to (# analog channels) in NR1 format

<r> ::= {1 | 2}
```

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":DIGitize" on page 153
- ":WAVeform:FORMat" on page 674
- ":WAVeform:BYTeorder" on page 670
- ":WAVeform:DATA" on page 672
- ":WAVeform:PREamble" on page 679

Example Code

```
' WAVEFORM_DATA - To obtain waveform data, you must specify the
' WAVEFORM parameters for the waveform data prior to sending the
' ":WAVEFORM:DATA?" query.  Once these parameters have been sent,
```

```
' the waveform data and the preamble can be read.
'
' WAVE_SOURCE - Selects the channel to be used as the source for
' the waveform commands.
myScope.WriteString ":WAVEFORM:SOURCE CHAN1"

' WAVE_POINTS - Specifies the number of points to be transferred
' using the ":WAVEFORM:DATA?" query.
myScope.WriteString ":WAVEFORM:POINTS 1000"

' WAVE_FORMAT - Sets the data transmission mode for the waveform
' data output.  This command controls whether data is formatted in
' a word or byte format when sent from the oscilloscope.
Dim lngVSteps As Long
Dim intBytesPerData As Integer

' Data in range 0 to 65535.
myScope.WriteString ":WAVEFORM:FORMAT WORD"
lngVSteps = 65536
intBytesPerData = 2

' Data in range 0 to 255.
'myScope.WriteString ":WAVEFORM:FORMAT BYTE"
'lngVSteps = 256
'intBytesPerData = 1

' GET_PREAMBLE - The preamble block contains all of the current
' WAVEFORM settings.  It is returned in the form <preamble_block><NL>
' where <preamble_block> is:
'    FORMAT        : int16 - 0 = BYTE, 1 = WORD, 4 = ASCII.
'    TYPE          : int16 - 0 = NORMAL, 1 = PEAK DETECT, 2 = AVERAGE
'    POINTS        : int32 - number of data points transferred.
'    COUNT         : int32 - 1 and is always 1.
'    XINCREMENT    : float64 - time difference between data points.
'    XORIGIN       : float64 - always the first data point in memory.
'    XREFERENCE    : int32 - specifies the data point associated with
'                            x-origin.
'    YINCREMENT    : float32 - voltage diff between data points.
'    YORIGIN       : float32 - value is the voltage at center screen.
'    YREFERENCE    : int32 - specifies the data point where y-origin
'                            occurs.
Dim Preamble()
Dim intFormat As Integer
Dim intType As Integer
Dim lngPoints As Long
Dim lngCount As Long
Dim dblXIncrement As Double
Dim dblXOrigin As Double
Dim lngXReference As Long
Dim sngYIncrement As Single
Dim sngYOrigin As Single
Dim lngYReference As Long
Dim strOutput As String

myScope.WriteString ":WAVEFORM:PREAMBLE?"   ' Query for the preamble.
Preamble() = myScope.ReadList   ' Read preamble information.
intFormat = Preamble(0)
```

```
intType = Preamble(1)
lngPoints = Preamble(2)
lngCount = Preamble(3)
dblXIncrement = Preamble(4)
dblXOrigin = Preamble(5)
lngXReference = Preamble(6)
sngYIncrement = Preamble(7)
sngYOrigin = Preamble(8)
lngYReference = Preamble(9)
strOutput = ""
'strOutput = strOutput + "Format = " + CStr(intFormat) + vbCrLf
'strOutput = strOutput + "Type = " + CStr(intType) + vbCrLf
'strOutput = strOutput + "Points = " + CStr(lngPoints) + vbCrLf
'strOutput = strOutput + "Count = " + CStr(lngCount) + vbCrLf
'strOutput = strOutput + "X increment = " + _
'            FormatNumber(dblXIncrement * 1000000) + " us" + vbCrLf
'strOutput = strOutput + "X origin = " + _
'            FormatNumber(dblXOrigin * 1000000) + " us" + vbCrLf
'strOutput = strOutput + "X reference = " + _
'            CStr(lngXReference) + vbCrLf
'strOutput = strOutput + "Y increment = " + _
'            FormatNumber(sngYIncrement * 1000) + " mV" + vbCrLf
'strOutput = strOutput + "Y origin = " + _
'            FormatNumber(sngYOrigin) + " V" + vbCrLf
'strOutput = strOutput + "Y reference = " + _
'            CStr(lngYReference) + vbCrLf
strOutput = strOutput + "Volts/Div = " + _
            FormatNumber(lngVSteps * sngYIncrement / 8) + _
            " V" + vbCrLf
strOutput = strOutput + "Offset = " + _
            FormatNumber((lngVSteps / 2 - lngYReference) * _
            sngYIncrement + sngYOrigin) + " V" + vbCrLf
strOutput = strOutput + "Sec/Div = " + _
            FormatNumber(lngPoints * dblXIncrement / 10 * _
            1000000) + " us" + vbCrLf
strOutput = strOutput + "Delay = " + _
            FormatNumber(((lngPoints / 2 - lngXReference) * _
            dblXIncrement + dblXOrigin) * 1000000) + " us" + vbCrLf

' QUERY_WAVE_DATA - Outputs waveform data that is stored in a buffer.

' Query the oscilloscope for the waveform data.
myScope.WriteString ":WAV:DATA?"

' READ_WAVE_DATA - The wave data consists of two parts: the header,
' and the actual waveform data followed by a new line (NL) character.
' The query data has the following format:
'
'    <header><waveform_data><NL>
'
' Where:
'    <header> = #800001000 (This is an example header)
' The "#8" may be stripped off of the header and the remaining
' numbers are the size, in bytes, of the waveform data block.  The
' size can vary depending on the number of points acquired for the
' waveform.  You can then read that number of bytes from the
' oscilloscope and the terminating NL character.
```

```
'
Dim lngI As Long
Dim lngDataValue As Long

' Unsigned integer bytes.
varQueryResult = myScope.ReadIEEEBlock(BinaryType_UI1)

For lngI = 0 To UBound(varQueryResult) _
    Step (UBound(varQueryResult) / 20)   ' 20 points.
  If intBytesPerData = 2 Then
    lngDataValue = varQueryResult(lngI) * 256 _
        + varQueryResult(lngI + 1)   ' 16-bit value.
  Else
    lngDataValue = varQueryResult(lngI)   ' 8-bit value.
  End If
  strOutput = strOutput + "Data point " + _
    CStr(lngI / intBytesPerData) + ", " + _
    FormatNumber((lngDataValue - lngYReference) _
        * sngYIncrement + sngYOrigin) + " V, " + _
    FormatNumber(((lngI / intBytesPerData - lngXReference) _
        * sngXIncrement + dblXOrigin) * 1000000) + " us" + vbCrLf
Next lngI
MsgBox "Waveform data:" + vbCrLf + strOutput
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:WAVeform:SOURce:SUBSource

(see page 828)

Command Syntax

```
:WAVeform:SOURce:SUBSource <subsource>

<subsource> ::= {{SUB0 | RX | MOSI} | {SUB1 | TX | MISO}}
```

If the :WAVeform:SOURce is SBUS<n> (serial decode), more than one data set may be available, and this command lets you choose from the available data sets.

When using UART serial decode, this option lets you get "TX" data. (TX is an alias for SUB1.) The default, SUB0, specifies "RX" data. (RX is an alias for SUB0.)

When using SPI serial decode, this option lets you get "MISO" data. (MISO is an alias for SUB1.) The default, SUB0, specifies "MOSI" data. (MOSI is an alias for SUB0.)

If the :WAVeform:SOURce is not SBUS, or the :SBUS<n>:MODE is not UART or SPI, the only valid subsource is SUB0.

Query Syntax

```
:WAVeform:SOURce:SUBSource?
```

The :WAVeform:SOURce:SUBSource? query returns the current waveform subsource setting.

Return Format

```
<subsource><NL>

<subsource> ::= {SUB0 | SUB1}
```

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:SOURce" on page 684

:WAVeform:TYPE

(see page 828)

Query Syntax `:WAVeform:TYPE?`

The :WAVeform:TYPE? query returns the acquisition mode associated with the currently selected waveform. The acquisition mode is set by the :ACQuire:TYPE command.

Return Format `<mode><NL>`

`<mode> ::= {NORM | PEAK | AVER | HRES}`

NOTE If the :WAVeform:SOURce is POD1 or POD2, the type is always NORM.

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":ACQuire:TYPE" on page 199
- ":WAVeform:DATA" on page 672
- ":WAVeform:PREamble" on page 679
- ":WAVeform:SOURce" on page 684

:WAVeform:UNSigned

(see page 828)

Command Syntax

```
:WAVeform:UNSigned <unsigned>

<unsigned> ::= {{0 | OFF} | {1 | ON}}
```

The :WAVeform:UNSigned command turns unsigned mode on or off for the currently selected waveform. Use the WAVeform:UNSigned command to control whether data values are sent as unsigned or signed integers. This command can be used to match the instrument's internal data type to the data type used by the programming language. This command has no effect if the data format is ASCii.

If :WAVeform:SOURce is set to POD1, POD2, BUS1, or BUS2, WAVeform:UNSigned must be set to ON.

Query Syntax

```
:WAVeform:UNSigned?
```

The :WAVeform:UNSigned? query returns the status of unsigned mode for the currently selected waveform.

Return Format

```
<unsigned><NL>

<unsigned> ::= {0 | 1}
```

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:SOURce" on page 684

:WAVeform:VIEW

(see page 828)

Command Syntax

```
:WAVeform:VIEW <view>

<view> ::= {MAIN}
```

The :WAVeform:VIEW command sets the view setting associated with the currently selected waveform. Currently, the only legal value for the view setting is MAIN.

Query Syntax

```
:WAVeform:VIEW?
```

The :WAVeform:VIEW? query returns the view setting associated with the currently selected waveform.

Return Format

```
<view><NL>

<view> ::= {MAIN}
```

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:POINts" on page 675

:WAVeform:XINCrement

(see page 828)

Query Syntax

```
:WAVeform:XINCrement?
```

The :WAVeform:XINCrement? query returns the x-increment value for the currently specified source. This value is the time difference between consecutive data points in seconds.

Return Format

```
<value><NL>
```

```
<value> ::= x-increment in the current preamble in 64-bit
            floating point NR3 format
```

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:PREamble" on page 679

Example Code

- "Example Code" on page 680

:WAVeform:XORigin

(see page 828)

Query Syntax

```
:WAVeform:XORigin?
```

The :WAVeform:XORigin? query returns the x-origin value for the currently specified source. XORigin is the X-axis value of the data point specified by the :WAVeform:XREFerence value. In this product, that is always the X-axis value of the first data point (XREFerence = 0).

Return Format

```
<value><NL>

<value> ::= x-origin value in the current preamble in 64-bit
            floating point NR3 format
```

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:PREamble" on page 679
- ":WAVeform:XREFerence" on page 694

Example Code

- "Example Code" on page 680

:WAVeform:XREFerence

(see page 828)

Query Syntax

```
:WAVeform:XREFerence?
```

The :WAVeform:XREFerence? query returns the x-reference value for the currently specified source. This value specifies the index of the data point associated with the x-origin data value. In this product, the x-reference point is the first point displayed and XREFerence is always 0.

Return Format

```
<value><NL>
```

```
<value> ::= x-reference value = 0 in 32-bit NR1 format
```

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:PREamble" on page 679
- ":WAVeform:XORigin" on page 693

Example Code

- "Example Code" on page 680

:WAVeform:YINCrement

(see page 828)

Query Syntax

```
:WAVeform:YINCrement?
```

The :WAVeform:YINCrement? query returns the y-increment value in volts for the currently specified source. This value is the voltage difference between consecutive data values.

Return Format

```
<value><NL>

<value> ::= y-increment value in the current preamble in 32-bit
            floating point NR3 format
```

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:PREamble" on page 679

Example Code

- "Example Code" on page 680

:WAVeform:YORigin

(see page 828)

Query Syntax

```
:WAVeform:YORigin?
```

The :WAVeform:YORigin? query returns the y-origin value for the currently specified source. This value is the Y-axis value of the data value specified by the :WAVeform:YREFerence value. For this product, this is the Y-axis value of the center of the screen.

Return Format

```
<value><NL>

<value> ::= y-origin in the current preamble in 32-bit
            floating point NR3 format
```

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:PREamble" on page 679
- ":WAVeform:YREFerence" on page 697

Example Code

- "Example Code" on page 680

:WAVeform:YREFerence

(see page 828)

Query Syntax

```
:WAVeform:YREFerence?
```

The :WAVeform:YREFerence? query returns the y-reference value for the currently specified source. This value specifies the data point value where the y-origin occurs. In this product, this is the data point value of the center of the screen. It is undefined if the format is ASCii.

Return Format

```
<value><NL>

<value> ::= y-reference value in the current preamble in 32-bit
            NR1 format
```

See Also

- "Introduction to :WAVeform Commands" on page 665
- ":WAVeform:PREamble" on page 679
- ":WAVeform:YORigin" on page 696

Example Code

- "Example Code" on page 680

30 :WGEN Commands

On G-suffix oscilloscope models, a waveform generator is built into the oscilloscope. You can use the waveform generator to output sine, square, ramp, pulse, DC, and noise waveforms. The :WGEN commands are used to select the waveform function and parameters. See "Introduction to :WGEN Commands" on page 701.

Table 88 :WGEN Commands Summary

Command	Query	Options and Query Returns
:WGEN:FREQuency <frequency> (see page 702)	:WGEN:FREQuency? (see page 702)	<frequency> ::= frequency in Hz in NR3 format
:WGEN:FUNCtion <signal> (see page 703)	:WGEN:FUNCtion? (see page 704)	<signal> ::= {SINusoid | SQUare | RAMP | PULSe | NOISe | DC}
:WGEN:FUNCtion:PULSe:WIDTh <width> (see page 706)	:WGEN:FUNCtion:PULSe:WIDTh? (see page 706)	<width> ::= pulse width in seconds in NR3 format
:WGEN:FUNCtion:RAMP:SYMMetry <percent> (see page 707)	:WGEN:FUNCtion:RAMP:SYMMetry? (see page 707)	<percent> ::= symmetry percentage from 0% to 100% in NR1 format
:WGEN:FUNCtion:SQUare:DCYCle <percent> (see page 708)	:WGEN:FUNCtion:SQUare:DCYCle? (see page 708)	<percent> ::= duty cycle percentage from 1% to 99% in NR1 format
:WGEN:MODulation:AM:DEPTh <percent> (see page 709)	:WGEN:MODulation:AM:DEPTh? (see page 709)	<percent> ::= AM depth percentage from 0% to 100% in NR1 format
:WGEN:MODulation:AM:FREQuency <frequency> (see page 710)	:WGEN:MODulation:AM:FREQuency? (see page 710)	<frequency> ::= modulating waveform frequency in Hz in NR3 format
:WGEN:MODulation:FM:DEViation <frequency> (see page 711)	:WGEN:MODulation:FM:DEViation? (see page 711)	<frequency> ::= frequency deviation in Hz in NR3 format

Table 88 :WGEN Commands Summary (continued)

Command	Query	Options and Query Returns
:WGEN:MODulation:FM:FREQuency <frequency> (see page 712)	:WGEN:MODulation:FM:FREQuency? (see page 712)	<frequency> ::= modulating waveform frequency in Hz in NR3 format
:WGEN:MODulation:FSKey:FREQuency <percent> (see page 713)	:WGEN:MODulation:FSKey:FREQuency? (see page 713)	<frequency> ::= hop frequency in Hz in NR3 format
:WGEN:MODulation:FSKey:RATE <rate> (see page 714)	:WGEN:MODulation:FSKey:RATE? (see page 714)	<rate> ::= FSK modulation rate in Hz in NR3 format
:WGEN:MODulation:FUNCtion <shape> (see page 715)	:WGEN:MODulation:FUNCtion? (see page 715)	<shape> ::= {SINusoid | SQUare| RAMP}
:WGEN:MODulation:FUNCtion:RAMP:SYMMetry <percent> (see page 716)	:WGEN:MODulation:FUNCtion:RAMP:SYMMetry? (see page 716)	<percent> ::= symmetry percentage from 0% to 100% in NR1 format
:WGEN:MODulation:NOISe <percent> (see page 717)	:WGEN:MODulation:NOISe? (see page 717)	<percent> ::= 0 to 100
:WGEN:MODulation:STATe {{0 | OFF} | {1 | ON}} (see page 718)	:WGEN:MODulation:STATe? (see page 718)	{0 | 1}
:WGEN:MODulation:TYPE <type> (see page 719)	:WGEN:MODulation:TYPE? (see page 719)	<type> ::= {AM | FM | FSK}
:WGEN:OUTPut {{0 | OFF} | {1 | ON}} (see page 721)	:WGEN:OUTPut? (see page 721)	{0 | 1}
:WGEN:OUTPut:LOAD <impedance> (see page 722)	:WGEN:OUTPut:LOAD? (see page 722)	<impedance> ::= {ONEMeg | FIFTy}
:WGEN:OUTPut:POLarity <polarity> (see page 723)	:WGEN:OUTPut:POLarity? (see page 723)	<polarity> ::= {NORMal | INVerted}
:WGEN:PERiod <period> (see page 724)	:WGEN:PERiod? (see page 724)	<period> ::= period in seconds in NR3 format
:WGEN:RST (see page 725)	n/a	n/a
:WGEN:VOLTage <amplitude> (see page 726)	:WGEN:VOLTage? (see page 726)	<amplitude> ::= amplitude in volts in NR3 format

Table 88 :WGEN Commands Summary (continued)

Command	Query	Options and Query Returns
:WGEN:VOLTage:HIGH <high> (see page 727)	:WGEN:VOLTage:HIGH? (see page 727)	<high> ::= high-level voltage in volts, in NR3 format
:WGEN:VOLTage:LOW <low> (see page 728)	:WGEN:VOLTage:LOW? (see page 728)	<low> ::= low-level voltage in volts, in NR3 format
:WGEN:VOLTage:OFFSet <offset> (see page 729)	:WGEN:VOLTage:OFFSet? (see page 729)	<offset> ::= offset in volts in NR3 format

Introduction to :WGEN Commands

The :WGEN subsystem provides commands to select the waveform generator function and parameters.

Reporting the Setup

Use :WGEN? to query setup information for the WGEN subsystem.

Return Format

The following is a sample response from the :WGEN? query. In this case, the query was issued following the *RST command.

```
:WGEN:FUNC SIN;OUTP 0;FREQ +1.0000E+03;VOLT +500.0E-03;VOLT:OFFS
+0.0E+00;:WGEN:OUTP:LOAD ONEM
```

:WGEN:FREQuency

(see page 828)

Command Syntax

```
:WGEN:FREQuency <frequency>

<frequency> ::= frequency in Hz in NR3 format
```

For all waveforms except Noise and DC, the :WGEN:FREQuency command specifies the frequency of the waveform.

You can also specify the frequency indirectly using the :WGEN:PERiod command.

Query Syntax

```
:WGEN:FREQuency?
```

The :WGEN:FREQuency? query returns the currently set waveform generator frequency.

Return Format

```
<frequency><NL>

<frequency> ::= frequency in Hz in NR3 format
```

See Also

- "Introduction to :WGEN Commands" on page 701
- ":WGEN:FUNCtion" on page 703
- ":WGEN:PERiod" on page 724

:WGEN:FUNCtion

N (see page 828)

Command Syntax

```
:WGEN:FUNCtion <signal>
<signal> ::= {SINusoid | SQUare | RAMP | PULSe | NOISe | DC}
```

The :WGEN:FUNCtion command selects the type of waveform:

Waveform Type	Characteristics
SINusoid	Use these commands to set the sine signal parameters: ▪ ":WGEN:FREQuency" on page 702 ▪ ":WGEN:PERiod" on page 724 ▪ ":WGEN:VOLTage" on page 726 ▪ ":WGEN:VOLTage:OFFSet" on page 729 ▪ ":WGEN:VOLTage:HIGH" on page 727 ▪ ":WGEN:VOLTage:LOW" on page 728 The frequency can be adjusted from 100 mHz to 20 MHz.
SQUare	Use these commands to set the square wave signal parameters: ▪ ":WGEN:FREQuency" on page 702 ▪ ":WGEN:PERiod" on page 724 ▪ ":WGEN:VOLTage" on page 726 ▪ ":WGEN:VOLTage:OFFSet" on page 729 ▪ ":WGEN:VOLTage:HIGH" on page 727 ▪ ":WGEN:VOLTage:LOW" on page 728 ▪ ":WGEN:FUNCtion:SQUare:DCYCle" on page 708 The frequency can be adjusted from 100 mHz to 10 MHz. The duty cycle can be adjusted from 1% to 99% up to 500 kHz. At higher frequencies, the adjustment range narrows so as not to allow pulse widths less than 20 ns. For example: ▪ At 1 MHz, the duty cycle can be adjusted from 2% to 98%. ▪ At 5 MHz, the duty cycle can be adjusted from 10% to 90%. ▪ At 10 MHz, the duty cycle can be adjusted from 20% to 80%.

Waveform Type	Characteristics
RAMP	Use these commands to set the ramp signal parameters: ▪ ":WGEN:FREQuency" on page 702 ▪ ":WGEN:PERiod" on page 724 ▪ ":WGEN:VOLTage" on page 726 ▪ ":WGEN:VOLTage:OFFSet" on page 729 ▪ ":WGEN:VOLTage:HIGH" on page 727 ▪ ":WGEN:VOLTage:LOW" on page 728 ▪ ":WGEN:FUNCtion:RAMP:SYMMetry" on page 707 The frequency can be adjusted from 100 mHz to 100 kHz. Symmetry represents the amount of time per cycle that the ramp waveform is rising and can be adjusted from 0% to 100%.
PULSe	Use these commands to set the pulse signal parameters: ▪ ":WGEN:FREQuency" on page 702 ▪ ":WGEN:PERiod" on page 724 ▪ ":WGEN:VOLTage" on page 726 ▪ ":WGEN:VOLTage:OFFSet" on page 729 ▪ ":WGEN:VOLTage:HIGH" on page 727 ▪ ":WGEN:VOLTage:LOW" on page 728 ▪ ":WGEN:FUNCtion:PULSe:WIDTh" on page 706 The frequency can be adjusted from 100 mHz to 10 MHz. The pulse width can be adjusted from 20 ns to the period minus 20 ns.
DC	Use this command to set the DC level: ▪ ":WGEN:VOLTage:OFFSet" on page 729
NOISe	Use these commands to set the noise signal parameters: ▪ ":WGEN:VOLTage" on page 726 ▪ ":WGEN:VOLTage:OFFSet" on page 729 ▪ ":WGEN:VOLTage:HIGH" on page 727 ▪ ":WGEN:VOLTage:LOW" on page 728

For all waveform types, the output amplitude, into 50 Ω, can be adjusted from 10 mVpp to 2.5 Vpp (or from 20 mVpp to 5 Vpp into and open-circuit load).

Query Syntax

```
:WGEN:FUNCtion?
```

The :WGEN:FUNCtion? query returns the currently selected signal type.

Return Format

```
<signal><NL>

<signal> ::= {SIN | SQU | RAMP | PULS | NOIS | DC}
```

See Also • "Introduction to :WGEN Commands" on page 701

:WGEN:FUNCtion:PULSe:WIDTh

(see page 828)

Command Syntax

```
:WGEN:FUNCtion:PULSe:WIDTh <width>

<width> ::= pulse width in seconds in NR3 format
```

For Pulse waveforms, the :WGEN:FUNCtion:PULSe:WIDTh command specifies the width of the pulse.

The pulse width can be adjusted from 20 ns to the period minus 20 ns.

Query Syntax

```
:WGEN:FUNCtion:PULSe:WIDTh?
```

The :WGEN:FUNCtion:PULSe:WIDTh? query returns the currently set pulse width.

Return Format

```
<width><NL>

<width> ::= pulse width in seconds in NR3 format
```

See Also

- "Introduction to :WGEN Commands" on page 701
- ":WGEN:FUNCtion" on page 703

:WGEN:FUNCtion:RAMP:SYMMetry

(see page 828)

Command Syntax

```
:WGEN:FUNCtion:RAMP:SYMMetry <percent>

<percent> ::= symmetry percentage from 0% to 100% in NR1 format
```

For Ramp waveforms, the :WGEN:FUNCtion:RAMP:SYMMetry command specifies the symmetry of the waveform.

Symmetry represents the amount of time per cycle that the ramp waveform is rising.

Query Syntax

```
:WGEN:FUNCtion:RAMP:SYMMetry?
```

The :WGEN:FUNCtion:RAMP:SYMMetry? query returns the currently set ramp symmetry.

Return Format

```
<percent><NL>

<percent> ::= symmetry percentage from 0% to 100% in NR1 format
```

See Also

- "Introduction to :WGEN Commands" on page 701
- ":WGEN:FUNCtion" on page 703

:WGEN:FUNCtion:SQUare:DCYCle

(see page 828)

Command Syntax

```
:WGEN:FUNCtion:SQUare:DCYCle <percent>

<percent> ::= duty cycle percentage from 1% to 99% in NR1 format
```

For Square waveforms, the :WGEN:FUNCtion:SQUare:DCYCle command specifies the square wave duty cycle.

Duty cycle is the percentage of the period that the waveform is high.

The duty cycle can be adjusted from 1% to 99% up to 500 kHz. At higher frequencies, the adjustment range narrows to not allow pulse widths less than 20 ns. For example:

- At 1 MHz, the duty cycle can be adjusted from 2% to 98%.
- At 5 MHz, the duty cycle can be adjusted from 10% to 90%.
- At 10 MHz, the duty cycle can be adjusted from 20% to 80%.

Query Syntax

```
:WGEN:FUNCtion:SQUare:DCYCle?
```

The :WGEN:FUNCtion:SQUare:DCYCle? query returns the currently set square wave duty cycle.

Return Format

```
<percent><NL>

<percent> ::= duty cycle percentage from 1% to 99% in NR1 format
```

See Also

- "Introduction to :WGEN Commands" on page 701
- ":WGEN:FUNCtion" on page 703

:WGEN:MODulation:AM:DEPTh

N (see page 828)

Command Syntax

```
:WGEN:MODulation:AM:DEPTh <percent>

<percent> ::= AM depth percentage from 0% to 100% in NR1 format
```

The :WGEN:MODulation:AM:DEPTh command specifies the amount of amplitude modulation.

AM Depth refers to the portion of the amplitude range that will be used by the modulation. For example, a depth setting of 80% causes the output amplitude to vary from 10% to 90% (90% – 10% = 80%) of the original amplitude as the modulating signal goes from its minimum to maximum amplitude.

Query Syntax

```
:WGEN:MODulation:AM:DEPTh?
```

The :WGEN:MODulation:AM:DEPTh? query returns the AM depth percentage setting.

Return Format

```
<percent><NL>

<percent> ::= AM depth percentage from 0% to 100% in NR1 format
```

See Also

- ":WGEN:MODulation:AM:FREQuency" on page 710
- ":WGEN:MODulation:FM:DEViation" on page 711
- ":WGEN:MODulation:FM:FREQuency" on page 712
- ":WGEN:MODulation:FSKey:FREQuency" on page 713
- ":WGEN:MODulation:FSKey:RATE" on page 714
- ":WGEN:MODulation:FUNCtion" on page 715
- ":WGEN:MODulation:FUNCtion:RAMP:SYMMetry" on page 716
- ":WGEN:MODulation:STATe" on page 718
- ":WGEN:MODulation:TYPE" on page 719

:WGEN:MODulation:AM:FREQuency

N (see page 828)

Command Syntax

```
:WGEN:MODulation:AM:FREQuency <frequency>

<frequency> ::= modulating waveform frequency in Hz in NR3 format
```

The :WGEN:MODulation:AM:FREQuency command specifies the frequency of the modulating signal.

Query Syntax

```
:WGEN:MODulation:AM:FREQuency?
```

The :WGEN:MODulation:AM:FREQuency? query returns the frequency of the modulating signal.

Return Format

```
<frequency><NL>

<frequency> ::= modulating waveform frequency in Hz in NR3 format
```

See Also

- ":WGEN:MODulation:AM:DEPTh" on page 709
- ":WGEN:MODulation:FM:DEViation" on page 711
- ":WGEN:MODulation:FM:FREQuency" on page 712
- ":WGEN:MODulation:FSKey:FREQuency" on page 713
- ":WGEN:MODulation:FSKey:RATE" on page 714
- ":WGEN:MODulation:FUNCtion" on page 715
- ":WGEN:MODulation:FUNCtion:RAMP:SYMMetry" on page 716
- ":WGEN:MODulation:STATe" on page 718
- ":WGEN:MODulation:TYPE" on page 719

:WGEN:MODulation:FM:DEViation

N (see page 828)

Command Syntax

```
:WGEN:MODulation:FM:DEViation <frequency>

<frequency> ::= frequency deviation in Hz in NR3 format
```

The :WGEN:MODulation:FM:DEViation command specifies the frequency deviation from the original carrier signal frequency.

When the modulating signal is at its maximum amplitude, the output frequency is the carrier signal frequency plus the deviation amount, and when the modulating signal is at its minimum amplitude, the output frequency is the carrier signal frequency minus the deviation amount.

The frequency deviation cannot be greater than the original carrier signal frequency.

Also, the sum of the original carrier signal frequency and the frequency deviation must be less than or equal to the maximum frequency for the selected waveform generator function plus 100 kHz.

Query Syntax

```
:WGEN:MODulation:FM:DEViation?
```

The :WGEN:MODulation:FM:DEViation? query returns the frequency deviation setting.

Return Format

```
<frequency><NL>

<frequency> ::= frequency deviation in Hz in NR3 format
```

See Also

- ":WGEN:MODulation:AM:DEPTh" on page 709
- ":WGEN:MODulation:AM:FREQuency" on page 710
- ":WGEN:MODulation:FM:FREQuency" on page 712
- ":WGEN:MODulation:FSKey:FREQuency" on page 713
- ":WGEN:MODulation:FSKey:RATE" on page 714
- ":WGEN:MODulation:FUNCtion" on page 715
- ":WGEN:MODulation:FUNCtion:RAMP:SYMMetry" on page 716
- ":WGEN:MODulation:STATe" on page 718
- ":WGEN:MODulation:TYPE" on page 719

:WGEN:MODulation:FM:FREQuency

(see page 828)

Command Syntax

```
:WGEN:MODulation:FM:FREQuency <frequency>

<frequency> ::= modulating waveform frequency in Hz in NR3 format
```

The :WGEN:MODulation:FM:FREQuency command specifies the frequency of the modulating signal.

Query Syntax

```
:WGEN:MODulation:FM:FREQuency?
```

The :WGEN:MODulation:FM:FREQuency? query returns the frequency of the modulating signal.

Return Format

```
<frequency><NL>

<frequency> ::= modulating waveform frequency in Hz in NR3 format
```

See Also

- ":WGEN:MODulation:AM:DEPTh" on page 709
- ":WGEN:MODulation:AM:FREQuency" on page 710
- ":WGEN:MODulation:FM:DEViation" on page 711
- ":WGEN:MODulation:FSKey:FREQuency" on page 713
- ":WGEN:MODulation:FSKey:RATE" on page 714
- ":WGEN:MODulation:FUNCtion" on page 715
- ":WGEN:MODulation:FUNCtion:RAMP:SYMMetry" on page 716
- ":WGEN:MODulation:STATe" on page 718
- ":WGEN:MODulation:TYPE" on page 719

:WGEN:MODulation:FSKey:FREQuency

N (see page 828)

Command Syntax

```
:WGEN:MODulation:FSKey:FREQuency <frequency>

<frequency> ::= hop frequency in Hz in NR3 format
```

The :WGEN:MODulation:FSKey:FREQuency command specifies the "hop frequency".

The output frequency "shifts" between the original carrier frequency and this "hop frequency".

Query Syntax

```
:WGEN:MODulation:FSKey:FREQuency?
```

The :WGEN:MODulation:FSKey:FREQuency? query returns the "hop frequency" setting.

Return Format

```
<frequency><NL>

<frequency> ::= hop frequency in Hz in NR3 format
```

See Also

- ":WGEN:MODulation:AM:DEPTh" on page 709
- ":WGEN:MODulation:AM:FREQuency" on page 710
- ":WGEN:MODulation:FM:DEViation" on page 711
- ":WGEN:MODulation:FM:FREQuency" on page 712
- ":WGEN:MODulation:FSKey:RATE" on page 714
- ":WGEN:MODulation:FUNCtion" on page 715
- ":WGEN:MODulation:FUNCtion:RAMP:SYMMetry" on page 716
- ":WGEN:MODulation:STATe" on page 718
- ":WGEN:MODulation:TYPE" on page 719

:WGEN:MODulation:FSKey:RATE

(see page 828)

Command Syntax

```
:WGEN:MODulation:FSKey:RATE <rate>

<rate> ::= FSK modulation rate in Hz in NR3 format
```

The :WGEN:MODulation:FSKey:RATE command specifies the rate at which the output frequency "shifts".

The FSK rate specifies a digital square wave modulating signal.

Query Syntax

```
:WGEN:MODulation:FSKey:RATE?
```

The :WGEN:MODulation:FSKey:RATE? query returns the FSK rate setting.

Return Format

```
<rate><NL>

<rate> ::= FSK modulation rate in Hz in NR3 format
```

See Also

- ":WGEN:MODulation:AM:DEPTh" on page 709
- ":WGEN:MODulation:AM:FREQuency" on page 710
- ":WGEN:MODulation:FM:DEViation" on page 711
- ":WGEN:MODulation:FM:FREQuency" on page 712
- ":WGEN:MODulation:FSKey:FREQuency" on page 713
- ":WGEN:MODulation:FUNCtion" on page 715
- ":WGEN:MODulation:FUNCtion:RAMP:SYMMetry" on page 716
- ":WGEN:MODulation:STATe" on page 718
- ":WGEN:MODulation:TYPE" on page 719

:WGEN:MODulation:FUNCtion

(see page 828)

Command Syntax

```
:WGEN:MODulation:FUNCtion <shape>

<shape> ::= {SINusoid | SQUare| RAMP}
```

The :WGEN:MODulation:FUNCtion command specifies the shape of the modulating signal.

When the RAMP shape is selected, you can specify the amount of time per cycle that the ramp waveform is rising with the :WGEN:MODulation:FUNCtion:RAMP:SYMMetry command.

This command applies to AM and FM modulation. (The FSK modulation signal is a square wave shape.)

Query Syntax

```
:WGEN:MODulation:FUNCtion?
```

The :WGEN:MODulation:FUNCtion? query returns the specified modulating signal shape.

Return Format

```
<shape><NL>

<shape> ::= {SIN | SQU| RAMP}
```

See Also

- ":WGEN:MODulation:AM:DEPTh" on page 709
- ":WGEN:MODulation:AM:FREQuency" on page 710
- ":WGEN:MODulation:FM:DEViation" on page 711
- ":WGEN:MODulation:FM:FREQuency" on page 712
- ":WGEN:MODulation:FSKey:FREQuency" on page 713
- ":WGEN:MODulation:FSKey:RATE" on page 714
- ":WGEN:MODulation:FUNCtion:RAMP:SYMMetry" on page 716
- ":WGEN:MODulation:STATe" on page 718
- ":WGEN:MODulation:TYPE" on page 719

:WGEN:MODulation:FUNCtion:RAMP:SYMMetry

(see page 828)

Command Syntax

```
:WGEN:MODulation:FUNCtion:RAMP:SYMMetry <percent>

<percent> ::= symmetry percentage from 0% to 100% in NR1 format
```

The :WGEN:MODulation:FUNCtion:RAMP:SYMMetry command specifies the amount of time per cycle that the ramp waveform is rising. The ramp modulating waveform shape is specified with the :WGEN:MODulation:FUNCtion command.

Query Syntax

```
:WGEN:MODulation:FUNCtion:RAMP:SYMMetry?
```

The :WGEN:MODulation:FUNCtion:RAMP:SYMMetry? query returns ramp symmetry percentage setting.

Return Format

```
<percent><NL>

<percent> ::= symmetry percentage from 0% to 100% in NR1 format
```

See Also

- ":WGEN:MODulation:AM:DEPTh" on page 709
- ":WGEN:MODulation:AM:FREQuency" on page 710
- ":WGEN:MODulation:FM:DEViation" on page 711
- ":WGEN:MODulation:FM:FREQuency" on page 712
- ":WGEN:MODulation:FSKey:FREQuency" on page 713
- ":WGEN:MODulation:FSKey:RATE" on page 714
- ":WGEN:MODulation:FUNCtion" on page 715
- ":WGEN:MODulation:STATe" on page 718
- ":WGEN:MODulation:TYPE" on page 719

:WGEN:MODulation:NOISe

(see page 828)

Command Syntax

```
:WGEN:MODulation:NOISe <percent>

<percent> ::= 0 to 100
```

The :WGEN:MODulation:NOISe command adds noise to the currently selected signal. The sum of the amplitude between the original signal and injected noise is limited to the regular amplitude limit (for example, 5 Vpp in 1 MOhm), so the range for <percent> varies according to current amplitude.

Note that adding noise affects edge triggering on the waveform generator source as well as the waveform generator sync pulse output signal (which can be sent to TRIG OUT). This is because the trigger comparator is located after the noise source.

Query Syntax

```
:WGEN:MODulation:NOISe?
```

The :WGEN:MODulation:NOISe query returns the percent of added noise.

Return Format

```
<percent><NL>

<percent> ::= 0 to 100
```

See Also

- ":WGEN:FUNCtion" on page 703

:WGEN:MODulation:STATe

(see page 828)

Command Syntax

```
:WGEN:MODulation:STATe <setting>

<setting> ::= {{OFF | 0} | {ON | 1}}
```

The :WGEN:MODulation:STATe command enables or disables modulated waveform generator output.

You can enable modulation for all waveform generator function types except pulse, DC, and noise.

Query Syntax

```
:WGEN:MODulation:STATe?
```

The :WGEN:MODulation:STATe? query returns whether the modulated waveform generator output is enabled of disabled.

Return Format

```
<setting><NL>

<setting> ::= {0 | 1}
```

See Also

- ":WGEN:MODulation:AM:DEPTh" on page 709
- ":WGEN:MODulation:AM:FREQuency" on page 710
- ":WGEN:MODulation:FM:DEViation" on page 711
- ":WGEN:MODulation:FM:FREQuency" on page 712
- ":WGEN:MODulation:FSKey:FREQuency" on page 713
- ":WGEN:MODulation:FSKey:RATE" on page 714
- ":WGEN:MODulation:FUNCtion" on page 715
- ":WGEN:MODulation:FUNCtion:RAMP:SYMMetry" on page 716
- ":WGEN:MODulation:TYPE" on page 719

:WGEN:MODulation:TYPE

N (see page 828)

Command Syntax

```
:WGEN:MODulation:TYPE <type>

<type> ::= {AM | FM | FSK}
```

The :WGEN:MODulation:TYPE command selects the modulation type:

- AM (amplitude modulation) — the amplitude of the original carrier signal is modified according to the amplitude of the modulating signal.

  Use the :WGEN:MODulation:AM:FREQuency command to set the modulating signal frequency.

  Use the :WGEN:MODulation:AM:DEPTh command to specify the amount of amplitude modulation.

- FM (frequency modulation) — the frequency of the original carrier signal is modified according to the amplitude of the modulating signal.

  Use the :WGEN:MODulation:FM:FREQuency command to set the modulating signal frequency.

  Use the :WGEN:MODulation:FM:DEViation command to specify the frequency deviation from the original carrier signal frequency.

- FSK (frequency-shift keying modulation) — the output frequency "shifts" between the original carrier frequency and a "hop frequency" at the specified FSK rate.

  The FSK rate specifies a digital square wave modulating signal.

  Use the :WGEN:MODulation:FSKey:FREQuency command to specify the "hop frequency".

  Use the :WGEN:MODulation:FSKey:RATE command to specify the rate at which the output frequency "shifts".

Query Syntax

```
:WGEN:MODulation:TYPE?
```

The :WGEN:MODulation:TYPE? query returns the selected modulation type.

Return Format

```
<type><NL>

<type> ::= {AM | FM | FSK}
```

See Also

- ":WGEN:MODulation:AM:DEPTh" on page 709
- ":WGEN:MODulation:AM:FREQuency" on page 710
- ":WGEN:MODulation:FM:DEViation" on page 711
- ":WGEN:MODulation:FM:FREQuency" on page 712
- ":WGEN:MODulation:FSKey:FREQuency" on page 713

- ":WGEN:MODulation:FSKey:RATE" on page 714
- ":WGEN:MODulation:FUNCtion" on page 715
- ":WGEN:MODulation:FUNCtion:RAMP:SYMMetry" on page 716
- ":WGEN:MODulation:STATe" on page 718

:WGEN:OUTPut

N (see page 828)

Command Syntax

```
:WGEN:OUTPut <on_off>

<on_off> ::= {{1 | ON} | {0 | OFF}
```

The :WGEN:OUTPut command specifies whether the waveform generator signal output is ON (1) or OFF (0).

Query Syntax

```
:WGEN:OUTPut?
```

The :WGEN:OUTPut? query returns the current state of the waveform generator output setting.

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- "Introduction to :WGEN Commands" on page 701

:WGEN:OUTPut:LOAD

(see page 828)

Command Syntax

```
:WGEN:OUTPut:LOAD <impedance>

<impedance> ::= {ONEMeg | FIFTy}
```

The :WGEN:OUTPut:LOAD command selects the expected output load impedance.

The output impedance of the Gen Out BNC is fixed at 50 ohms. However, the output load selection lets the waveform generator display the correct amplitude and offset levels for the expected output load.

If the actual load impedance is different than the selected value, the displayed amplitude and offset levels will be incorrect.

Query Syntax

```
:WGEN:OUTPut:LOAD?
```

The :WGEN:OUTPut:LOAD? query returns the current expected output load impedance.

Return Format

```
<impedance><NL>

<impedance> ::= {ONEM | FIFT}
```

See Also

- "Introduction to :WGEN Commands" on page 701

:WGEN:OUTPut:POLarity

N (see page 828)

Command Syntax

```
:WGEN:OUTPut:POLarity <polarity>

<polarity> ::= {NORMal | INVerted}
```

The :WGEN:OUTPut:POLarity command specifies whether the waveform generator output is inverted..

Query Syntax

```
:WGEN:OUTPut:POLarity?
```

The :WGEN:OUTPut:POLarity? query returns the specified output polarity.

Return Format

```
<polarity><NL>

<polarity> ::= {NORM | INV}
```

See Also

- "Introduction to :WGEN Commands" on page 701

:WGEN:PERiod

(see page 828)

Command Syntax

```
:WGEN:PERiod <period>

<period> ::= period in seconds in NR3 format
```

For all waveforms except Noise and DC, the :WGEN:PERiod command specifies the period of the waveform.

You can also specify the period indirectly using the :WGEN:FREQuency command.

Query Syntax

```
:WGEN:PERiod?
```

The :WGEN:PERiod? query returns the currently set waveform generator period.

Return Format

```
<period><NL>

<period> ::= period in seconds in NR3 format
```

See Also

- "Introduction to :WGEN Commands" on page 701
- ":WGEN:FUNCtion" on page 703
- ":WGEN:FREQuency" on page 702

:WGEN:RST

(see page 828)

Command Syntax `:WGEN:RST`

The :WGEN:RST command restores the waveform generator factory default settings (1 kHz sine wave, 500 mVpp, 0 V offset).

See Also

- "Introduction to :WGEN Commands" on page 701
- ":WGEN:FUNCtion" on page 703
- ":WGEN:FREQuency" on page 702

:WGEN:VOLTage

(see page 828)

Command Syntax

```
:WGEN:VOLTage <amplitude>

<amplitude> ::= amplitude in volts in NR3 format
```

For all waveforms except DC, the :WGEN:VOLTage command specifies the waveform's amplitude. Use the :WGEN:VOLTage:OFFSet command to specify the offset voltage or DC level.

You can also specify the amplitude and offset indirectly using the :WGEN:VOLTage:HIGH and :WGEN:VOLTage:LOW commands. For example, an amplitude of 5 V and an offset of 1 V is the same as a high-level voltage of 4 V and a low-level voltage of -1 V.

Query Syntax

```
:WGEN:VOLTage?
```

The :WGEN:VOLTage? query returns the currently specified waveform amplitude.

Return Format

```
<amplitude><NL>

<amplitude> ::= amplitude in volts in NR3 format
```

See Also

- "Introduction to :WGEN Commands" on page 701
- ":WGEN:FUNCtion" on page 703
- ":WGEN:VOLTage:OFFSet" on page 729
- ":WGEN:VOLTage:HIGH" on page 727
- ":WGEN:VOLTage:LOW" on page 728

:WGEN:VOLTage:HIGH

(see page 828)

Command Syntax

```
:WGEN:VOLTage:HIGH <high>

<high> ::= high-level voltage in volts, in NR3 format
```

For all waveforms except DC, the :WGEN:VOLTage:HIGH command specifies the waveform's high-level voltage. Use the :WGEN:VOLTage:LOW command to specify the low-level voltage.

You can also specify the high-level and low-level voltages indirectly using the :WGEN:VOLTage and :WGEN:VOLTage:OFFSet commands. For example, a high-level voltage of 4 V and a low-level voltage of -1 V is the same as an amplitude of 5 V and an offset of 1 V.

Query Syntax

```
:WGEN:VOLTage:HIGH?
```

The :WGEN:VOLTage:HIGH? query returns the currently specified waveform high-level voltage.

Return Format

```
<high><NL>

<high> ::= high-level voltage in volts, in NR3 format
```

See Also

- "Introduction to :WGEN Commands" on page 701
- ":WGEN:FUNCtion" on page 703
- ":WGEN:VOLTage:LOW" on page 728
- ":WGEN:VOLTage" on page 726
- ":WGEN:VOLTage:OFFSet" on page 729

:WGEN:VOLTage:LOW

(see page 828)

Command Syntax

```
:WGEN:VOLTage:LOW <low>

<low> ::= low-level voltage in volts, in NR3 format
```

For all waveforms except DC, the :WGEN:VOLTage:LOW command specifies the waveform's low-level voltage. Use the :WGEN:VOLTage:HIGH command to specify the high-level voltage.

You can also specify the high-level and low-level voltages indirectly using the :WGEN:VOLTage and :WGEN:VOLTage:OFFSet commands. For example, a high-level voltage of 4 V and a low-level voltage of -1 V is the same as an amplitude of 5 V and an offset of 1 V.

Query Syntax

```
:WGEN:VOLTage:LOW?
```

The :WGEN:VOLTage:LOW? query returns the currently specified waveform low-level voltage.

Return Format

```
<low><NL>

<low> ::= low-level voltage in volts, in NR3 format
```

See Also

- "Introduction to :WGEN Commands" on page 701
- ":WGEN:FUNCtion" on page 703
- ":WGEN:VOLTage:LOW" on page 728
- ":WGEN:VOLTage" on page 726
- ":WGEN:VOLTage:OFFSet" on page 729

:WGEN:VOLTage:OFFSet

(see page 828)

Command Syntax

```
:WGEN:VOLTage:OFFSet <offset>

<offset> ::= offset in volts in NR3 format
```

The :WGEN:VOLTage:OFFSet command specifies the waveform's offset voltage or the DC level. Use the :WGEN:VOLTage command to specify the amplitude.

You can also specify the amplitude and offset indirectly using the :WGEN:VOLTage:HIGH and :WGEN:VOLTage:LOW commands. For example, an amplitude of 5 V and an offset of 1 V is the same as a high-level voltage of 4 V and a low-level voltage of -1 V.

Query Syntax

```
:WGEN:VOLTage:OFFSet?
```

The :WGEN:VOLTage:OFFSet? query returns the currently specified waveform offset voltage.

Return Format

```
<offset><NL>

<offset> ::= offset in volts in NR3 format
```

See Also

- "Introduction to :WGEN Commands" on page 701
- ":WGEN:FUNCtion" on page 703
- ":WGEN:VOLTage" on page 726
- ":WGEN:VOLTage:HIGH" on page 727
- ":WGEN:VOLTage:LOW" on page 728

31 :WMEMory<r> Commands

Control reference waveforms.

Table 89 :WMEMory<r> Commands Summary

Command	Query	Options and Query Returns
:WMEMory<r>:CLEar (see page 733)	n/a	<r> ::= 1-2 in NR1 format
:WMEMory<r>:DISPlay {{0 | OFF} | {1 | ON}} (see page 734)	:WMEMory<r>:DISPlay? (see page 734)	<r> ::= 1-2 in NR1 format {0 | 1}
:WMEMory<r>:LABel <string> (see page 735)	:WMEMory<r>:LABel? (see page 735)	<r> ::= 1-2 in NR1 format <string> ::= any series of 10 or less ASCII characters enclosed in quotation marks
:WMEMory<r>:SAVE <source> (see page 736)	n/a	<r> ::= 1-2 in NR1 format <source> ::= {CHANnel<n> | FUNCtion | MATH} <n> ::= 1 to (# analog channels) in NR1 format NOTE: Only ADD or SUBtract math operations can be saved as reference waveforms.
:WMEMory<r>:SKEW <skew> (see page 737)	:WMEMory<r>:SKEW? (see page 737)	<r> ::= 1-2 in NR1 format <skew> ::= time in seconds in NR3 format
:WMEMory<r>:YOFFset <offset>[suffix] (see page 738)	:WMEMory<r>:YOFFset? (see page 738)	<r> ::= 1-2 in NR1 format <offset> ::= vertical offset value in NR3 format [suffix] ::= {V | mV}

Table 89 :WMEMory<r> Commands Summary (continued)

Command	Query	Options and Query Returns
:WMEMory<r>:YRANge <range>[suffix] (see page 739)	:WMEMory<r>:YRANge? (see page 739)	<r> ::= 1-2 in NR1 format <range> ::= vertical full-scale range value in NR3 format [suffix] ::= {V | mV}
:WMEMory<r>:YSCale <scale>[suffix] (see page 740)	:WMEMory<r>:YSCale? (see page 740)	<r> ::= 1-2 in NR1 format <scale> ::= vertical units per division value in NR3 format [suffix] ::= {V | mV}

:WMEMory<r>:CLEar

(see page 828)

Command Syntax

```
:WMEMory<r>:CLEar

<r> ::= 1-2 in NR1 format
```

The :WMEMory<r>:CLEar command clears the specified reference waveform location.

See Also

- Chapter 31, ":WMEMory<r> Commands," starting on page 731
- ":WMEMory<r>:SAVE" on page 736
- ":WMEMory<r>:DISPlay" on page 734

:WMEMory<r>:DISPlay

(see page 828)

Command Syntax

```
:WMEMory<r>:DISPlay <on_off>

<r> ::= 1-2 in NR1 format

<on_off> ::= {{1 | ON} | {0 | OFF}}
```

The :WMEMory<r>:DISPlay command turns the display of the specified reference waveform on or off.

There are two reference waveform locations, but only one reference waveform can be displayed at a time. That means, if :WMEMory1:DISPlay is ON, sending the :WMEMory2:DISPlay ON command will automatically set :WMEMory1:DISPlay OFF.

Query Syntax

```
:WMEMory<r>:DISPlay?
```

The :WMEMory<r>:DISPlay? query returns the current display setting for the reference waveform.

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- Chapter 31, ":WMEMory<r> Commands," starting on page 731
- ":WMEMory<r>:CLEar" on page 733
- ":WMEMory<r>:LABel" on page 735

:WMEMory<r>:LABel

(see page 828)

Command Syntax

```
:WMEMory<r>:LABel <string>

<r> ::= 1-2 in NR1 format

<string> ::= quoted ASCII string
```

NOTE Label strings are 10 characters or less, and may contain any commonly used ASCII characters. Labels with more than 10 characters are truncated to 10 characters. Lower case characters are converted to upper case.

The :WMEMory<r>:LABel command sets the reference waveform label to the string that follows.

Setting a label for a reference waveform also adds the name to the label list in non-volatile memory (replacing the oldest label in the list).

Query Syntax

```
:WMEMory<r>:LABel?
```

The :WMEMory<r>:LABel? query returns the label associated with a particular reference waveform.

Return Format

```
<string><NL>

<string> ::= quoted ASCII string
```

See Also

- Chapter 31, ":WMEMory<r> Commands," starting on page 731
- ":WMEMory<r>:DISPlay" on page 734

:WMEMory<r>:SAVE

(see page 828)

Command Syntax

```
:WMEMory<r>:SAVE <source>

<r> ::= 1-2 in NR1 format

<source> ::= {CHANnel<n> | FUNCtion | MATH}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :WMEMory<r>:SAVE command copies the analog channel or math function waveform to the specified reference waveform location.

NOTE Only ADD or SUBtract math operations can be saved as reference waveforms.

See Also

- Chapter 31, ":WMEMory<r> Commands," starting on page 731
- ":WMEMory<r>:DISPlay" on page 734

:WMEMory<r>:SKEW

(see page 828)

Command Syntax

```
:WMEMory<r>:SKEW <skew>

<r> ::= 1-2 in NR1 format

<skew> ::= time in seconds in NR3 format
```

The :WMEMory<r>:SKEW command sets the skew factor for the specified reference waveform.

Query Syntax

```
:WMEMory<r>:SKEW?
```

The :WMEMory<r>:SKEW? query returns the current skew setting for the selected reference waveform.

Return Format

```
<skew><NL>

<skew> ::= time in seconds in NR3 format
```

See Also

- Chapter 31, ":WMEMory<r> Commands," starting on page 731
- ":WMEMory<r>:DISPlay" on page 734
- ":WMEMory<r>:YOFFset" on page 738
- ":WMEMory<r>:YRANge" on page 739
- ":WMEMory<r>:YSCale" on page 740

:WMEMory<r>:YOFFset

(see page 828)

Command Syntax

```
:WMEMory<r>:YOFFset <offset> [<suffix>]

<r> ::= 1-2 in NR1 format

<offset> ::= vertical offset value in NR3 format

<suffix> ::= {V | mV}
```

The :WMEMory<r>:YOFFset command sets the value that is represented at center screen for the selected reference waveform.

The range of legal values varies with the value set by the :WMEMory<r>:YRANge or :WMEMory<r>:YSCale commands. If you set the offset to a value outside of the legal range, the offset value is automatically set to the nearest legal value. Legal values are affected by the probe attenuation setting.

Query Syntax

```
:WMEMory<r>:YOFFset?
```

The :WMEMory<r>:YOFFset? query returns the current offset value for the selected reference waveform.

Return Format

```
<offset><NL>

<offset> ::= vertical offset value in NR3 format
```

See Also

- Chapter 31, ":WMEMory<r> Commands," starting on page 731
- ":WMEMory<r>:DISPlay" on page 734
- ":WMEMory<r>:YRANge" on page 739
- ":WMEMory<r>:YSCale" on page 740
- ":WMEMory<r>:SKEW" on page 737

:WMEMory<r>:YRANge

N (see page 828)

Command Syntax

```
:WMEMory<r>:YRANge <range>[<suffix>]

<r> ::= 1-2 in NR1 format

<range> ::= vertical full-scale range value in NR3 format

<suffix> ::= {V | mV}
```

The :WMEMory<r>:YRANge command defines the full-scale vertical axis of the selected reference waveform.

Legal values for the range are copied from the original source waveform (that is, the analog channel or math function waveform that was originally saved as a reference waveform).

Query Syntax

```
:WMEMory<r>:YRANge?
```

The :WMEMory<r>:YRANge? query returns the current full-scale range setting for the specified reference waveform.

Return Format

```
<range><NL>

<range> ::= vertical full-scale range value in NR3 format
```

See Also

- Chapter 31, ":WMEMory<r> Commands," starting on page 731
- ":WMEMory<r>:DISPlay" on page 734
- ":WMEMory<r>:YOFFset" on page 738
- ":WMEMory<r>:SKEW" on page 737
- ":WMEMory<r>:YSCale" on page 740

:WMEMory<r>:YSCale

N (see page 828)

Command Syntax

```
:WMEMory<r>:YSCale <scale>[<suffix>]

<r> ::= 1-2 in NR1 format

<scale> ::= vertical units per division in NR3 format

<suffix> ::= {V | mV}
```

The :WMEMory<r>:YSCale command sets the vertical scale, or units per division, of the selected reference waveform.

Legal values for the scale are copied from the original source waveform (that is, the analog channel or math function waveform that was originally saved as a reference waveform).

Query Syntax

```
:WMEMory<r>:YSCale?
```

The :WMEMory<r>:YSCale? query returns the current scale setting for the specified reference waveform.

Return Format

```
<scale><NL>

<scale> ::= vertical units per division in NR3 format
```

See Also

- Chapter 31, ":WMEMory<r> Commands," starting on page 731
- ":WMEMory<r>:DISPlay" on page 734
- ":WMEMory<r>:YOFFset" on page 738
- ":WMEMory<r>:YRANge" on page 739
- ":WMEMory<r>:SKEW" on page 737

32 Obsolete and Discontinued Commands

Obsolete commands are older forms of commands that are provided to reduce customer rework for existing systems and programs (see"Obsolete Commands" on page 828).

Obsolete Command	Current Command Equivalent	Behavior Differences
ANALog<n>:BWLimit	:CHANnel<n>:BWLimit (see page 215)	
ANALog<n>:COUPling	:CHANnel<n>:COUPling (see page 216)	
ANALog<n>:INVert	:CHANnel<n>:INVert (see page 219)	
ANALog<n>:LABel	:CHANnel<n>:LABel (see page 220)	
ANALog<n>:OFFSet	:CHANnel<n>:OFFSet (see page 221)	
ANALog<n>:PROBe	:CHANnel<n>:PROBe (see page 222)	
ANALog<n>:PMODe	none	
ANALog<n>:RANGe	:CHANnel<n>:RANGe (see page 228)	
:CHANnel:LABel (see page 746)	:CHANnel<n>:LABel (see page 220)	use CHANnel<n>:LABel for analog channels
:CHANnel2:SKEW (see page 747)	:CHANnel<n>:PROBe:SKEW (see page 225)	
:CHANnel<n>:INPut (see page 748)	:CHANnel<n>:IMPedance (see page 218)	
:CHANnel<n>:PMODe (see page 749)	none	

Obsolete Command	Current Command Equivalent	Behavior Differences
:DISPlay:CONNect (see page 750)	:DISPlay:VECTors (see page 251)	
:ERASe (see page 751)	:DISplay:CLEar (see page 243)	
:EXTernal:PMODe (see page 752)	none	
:FRANalysis:PPDecade (see page 753)	:FRANalysis:SWEep:POINts (see page 296)	Instead of points-per-decade, the :FRANalysis:SWEep:POINts command lets you specify the total number of points in the frequency response analysis.
FUNCtion1, FUNCtion2	:FUNCtion Commands (see page 301)	ADD not included
:FUNCtion:SOURce (see page 754)	:FUNCtion:SOURce1 (see page 320)	Obsolete command has ADD, SUBTract, and MULTiply parameters; current command has GOFT parameter.
:FUNCtion:VIEW (see page 755)	:FUNCtion:DISPlay (see page 304)	
:HARDcopy:DESTination (see page 756)	:HARDcopy:FILename (see page 757)	
:HARDcopy:FILename (see page 757)	:RECall:FILename (see page 459) :SAVE:FILename (see page 459)	
:HARDcopy:GRAYscale (see page 758)	:HARDcopy:PALette (see page 334)	
:HARDcopy:IGColors (see page 759)	:HARDcopy:INKSaver (see page 329)	
:HARDcopy:PDRiver (see page 760)	:HARDcopy:APRinter (see page 326)	
:MEASure:LOWer (see page 761)	:MEASure:DEFine:THResholds (see page 373)	MEASure:DEFine:THResholds can define absolute values or percentage
:MEASure:SCRatch (see page 762)	:MEASure:CLEar (see page 371)	
:MEASure:TDELta (see page 763)	:MARKer:XDELta (see page 349)	
:MEASure:THResholds (see page 764)	:MEASure:DEFine:THResholds (see page 373)	MEASure:DEFine:THResholds can define absolute values or percentage

Obsolete Command	Current Command Equivalent	Behavior Differences
:MEASure:TMAX (see page 765)	:MEASure:XMAX (see page 421)	
:MEASure:TMIN (see page 766)	:MEASure:XMIN (see page 422)	
:MEASure:TSTArt (see page 767)	:MARKer:X1Position (see page 345)	
:MEASure:TSTOp (see page 768)	:MARKer:X2Position (see page 347)	
:MEASure:TVOLt (see page 769)	:MEASure:TVALue (see page 409)	TVALue measures additional values such as db, Vs, etc.
:MEASure:UPPer (see page 770)	:MEASure:DEFine:THResholds (see page 373)	MEASure:DEFine:THResholds can define absolute values or percentage
:MEASure:VDELta (see page 771)	:MARKer:YDELta (see page 354)	
:MEASure:VSTArt (see page 772)	:MARKer:Y1Position (see page 352)	
:MEASure:VSTOp (see page 773)	:MARKer:Y2Position (see page 353)	
:MTESt:AMASk:{SAVE | STORe} (see page 774)	:SAVE:MASK[:STARt] (see page 475)	
:MTESt:AVERage (see page 775)	:ACQuire:TYPE AVERage (see page 199)	
:MTESt:AVERage:COUNt (see page 776)	:ACQuire:COUNt (see page 190)	
:MTESt:LOAD (see page 777)	:RECall:MASK[:STARt] (see page 460)	
:MTESt:RUMode (see page 778)	:MTESt:RMODe (see page 442)	
:MTESt:RUMode:SOFailure (see page 779)	:MTESt:RMODe:FACTion:STOP (see page 446)	
:MTESt:{STARt | STOP} (see page 780)	:RUN (see page 170) or :STOP (see page 174)	
:MTESt:TRIGger:SOURce (see page 781)	:TRIGger Commands (see page 615)	There are various commands for setting the source with different types of triggers.
:PRINt? (see page 782)	:DISPlay:DATA? (see page 244)	

Obsolete Command	Current Command Equivalent	Behavior Differences
:SAVE:IMAGe:AREA (see page 784)	none	
:TIMebase:DELay (see page 785)	:TIMebase:POSition (see page 606) or :TIMebase:WINDow:POSition (see page 611)	TIMebase:POSition is position value of main time base; TIMebase:WINDow:POSition is position value of zoomed (delayed) time base window.
:TRIGger:TV:TVMode (see page 786)	:TRIGger:TV:MODE (see page 659)	

Discontinued Commands

Discontinued commands are commands that were used by previous oscilloscopes, but are not supported by the InfiniiVision 1200 X-Series and EDUX11052A/G oscilloscopes. Listed below are the Discontinued commands and the nearest equivalent command available (if any).

Discontinued Command	Current Command Equivalent	Comments
ASTore	:DISPlay:PERSistence INFinite (see page 249)	
CHANnel:MATH	:FUNCtion:OPERation (see page 315)	ADD not included
CHANnel<n>:PROTect	:CHANnel<n>:PROTection (see page 227)	Previous form of this command was used to enable/disable 50Ω protection. The new command resets a tripped protect and the query returns the status of TRIPed or NORMal.
DISPlay:INVerse	none	
DISPlay:COLumn	none	
DISPlay:FREeze	none	
DISPlay:GRID	none	
DISPLay:LINE	none	
DISPlay:PIXel	none	
DISPlay:POSition	none	
DISPlay:ROW	none	
DISPlay:TEXT	none	
FUNCtion:MOVE	none	
FUNCtion:PEAKs	none	

Discontinued Command	Current Command Equivalent	Comments
HARDcopy:ADDRess	none	Only parallel printer port is supported. GPIB printing not supported
MASK	none	All commands discontinued, feature not available
SYSTem:KEY	none	
TEST:ALL	*TST (Self Test) (see page 140)	
TRACE subsystem	none	All commands discontinued, feature not available
TRIGger:ADVanced subsystem		Use new GLITch, PATTern, or TV trigger modes
TRIGger:TV:FIELd	:TRIGger:TV:MODE (see page 659)	
TRIGger:TV:TVHFrej		
TRIGger:TV:VIR	none	
VAUToscale	none	

Discontinued Parameters

Some previous oscilloscope queries returned control setting values of OFF and ON. The InfiniiVision 1200 X-Series and EDUX11052A/G oscilloscopes only return the enumerated values 0 (for off) and 1 (for on).

:CHANnel:LABel

(see page 828)

Command Syntax

```
:CHANnel:LABel <source_text><string>

<source_text> ::= {CHANnel1 | CHANnel2}

<string> ::= quoted ASCII string
```

The :CHANnel:LABel command sets the source text to the string that follows. Setting a channel will also result in the name being added to the label list.

NOTE The :CHANnel:LABel command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :CHANnel<n>:LABel command (see page 220).

Query Syntax

```
:CHANnel:LABel?
```

The :CHANnel:LABel? query returns the label associated with a particular analog channel.

Return Format

```
<string><NL>

<string> ::= quoted ASCII string
```

:CHANnel2:SKEW

(see page 828)

Command Syntax

```
:CHANnel2:SKEW <skew value>

<skew value> ::= skew time in NR3 format

<skew value> ::= -100 ns to +100 ns
```

The :CHANnel2:SKEW command sets the skew between channels 1 and 2. The maximum skew is +/-100 ns. You can use the oscilloscope's analog probe skew control to remove cable delay errors between channel 1 and channel 2.

NOTE The :CHANnel2:SKEW command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :CHANnel<n>:PROBe:SKEW command (see page 225) instead.

NOTE This command is only valid for the two channel oscilloscope models.

Query Syntax

```
:CHANnel2:SKEW?
```

The :CHANnel2:SKEW? query returns the current probe skew setting for the selected channel.

Return Format

```
<skew value><NL>

<skew value> ::= skew value in NR3 format
```

See Also

- "Introduction to :CHANnel<n> Commands" on page 213

:CHANnel<n>:INPut

(see page 828)

Command Syntax

```
:CHANnel<n>:INPut <impedance>

<impedance> ::= {ONEMeg | FIFTy}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :CHANnel<n>:INPut command selects the input impedance setting for the specified channel. The legal values for this command are ONEMeg (1 MΩ) and FIFTy (50Ω).

NOTE

The :CHANnel<n>:INPut command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :CHANnel<n>:IMPedance command (see page 218) instead.

Query Syntax

```
:CHANnel<n>:INPut?
```

The :CHANnel<n>:INPut? query returns the current input impedance setting for the specified channel.

Return Format

```
<impedance value><NL>

<impedance value> ::= {ONEM | FIFT}
```

:CHANnel<n>:PMODe

(see page 828)

Command Syntax

```
:CHANnel<n>:PMODe <pmode value>

<pmode value> ::= {AUTo | MANual}

<n> ::= 1 to (# analog channels) in NR1 format
```

The probe sense mode is controlled internally and cannot be set. If a probe with sense is connected to the specified channel, auto sensing is enabled; otherwise, the mode is manual.

If the PMODe sent matches the oscilloscope's setting, the command will be accepted. Otherwise, a setting conflict error is generated.

NOTE **The :CHANnel<n>:PMODe command is an obsolete command provided for compatibility to previous oscilloscopes.**

Query Syntax

```
:CHANnel<n>:PMODe?
```

The :CHANnel<n>:PMODe? query returns AUT if an autosense probe is attached and MAN otherwise.

Return Format

```
<pmode value><NL>

<pmode value> ::= {AUT | MAN}
```

:DISPlay:CONNect

(see page 828)

Command Syntax

```
:DISPlay:CONNect <connect>

<connect> ::= {{ 1 | ON} | {0 | OFF}}
```

The :DISPlay:CONNect command turns vectors on and off. When vectors are turned on, the oscilloscope displays lines connecting sampled data points. When vectors are turned off, only the sampled data is displayed.

NOTE The :DISPlay:CONNEct command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :DISPlay:VECTors command (see page 251) instead.

Query Syntax

```
:DISPlay:CONNect?
```

The :DISPlay:CONNect? query returns the current state of the vectors setting.

Return Format

```
<connect><NL>

<connect> ::= {1 | 0}
```

See Also

- ":DISPlay:VECTors" on page 251

:ERASe

(see page 828)

Command Syntax `:ERASe`

The :ERASe command erases the screen.

NOTE The :ERASe command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :DISplay:CLEar command (see page 243) instead.

:EXTernal:PMODe

(see page 828)

Command Syntax

```
:EXTernal:PMODe <pmode value>

<pmode value> ::= {AUTo | MANual}
```

The probe sense mode is controlled internally and cannot be set. If a probe with sense is connected to the specified channel, auto sensing is enabled; otherwise, the mode is manual.

If the pmode sent matches the oscilloscope's setting, the command will be accepted. Otherwise, a setting conflict error is generated.

NOTE **The :EXTernal:PMODe command is an obsolete command provided for compatibility to previous oscilloscopes.**

Query Syntax

```
:EXTernal:PMODe?
```

The :EXTernal:PMODe? query returns AUT if an autosense probe is attached and MAN otherwise.

Return Format

```
<pmode value><NL>

<pmode value> ::= {AUT | MAN}
```

:FRANalysis:PPDecade

(see page 828)

Command Syntax

```
:FRANalysis:PPDecade <value>

<value> ::= {10 | 20 | 30 | 40 | 50}
```

The :FRANalysis:PPDecade command specifies the number of points per decade in the frequency response analysis.

NOTE

This command is deprecated. You should now use the :FRANalysis:SWEep:POINts command instead, which lets you specify the total number of points in the entire frequency sweep.

If you use this command, it will set the :FRANalysis:SWEep:POINts setting to a roughly equivalent value.

Query Syntax

```
:FRANalysis:PPDecade?
```

The :FRANalysis:PPDecade? query returns the points per decade setting.

Return Format

```
<value><NL>
```

See Also

- ":FRANalysis:SWEep:POINts" on page 296
- ":FRANalysis:FREQuency:STARt" on page 291
- ":FRANalysis:FREQuency:STOP" on page 292

:FUNCtion:SOURce

(see page 828)

Command Syntax

```
:FUNCtion:SOURce <value>

<value> ::= {CHANnel<n> | ADD | SUBTract | MULTiply}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :FUNCtion:SOURce command is only used when an FFT (Fast Fourier Transform) operation is selected (see the:FUNCtion:OPERation command for more information about selecting an operation). The :FUNCtion:SOURce command selects the source for function operations. Choose CHANnel<n>, or ADD, SUBT, or MULT to specify the desired source for FFT operations specified by the :FUNCtion:OPERation command.

NOTE **The :FUNCtion:SOURce command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :FUNCtion:SOURce1 command (see page 320) instead.**

Query Syntax

```
:FUNCtion:SOURce?
```

The :FUNCtion:SOURce? query returns the current source for function operations.

Return Format

```
<value><NL>

<value> ::= {CHAN<n> | ADD | SUBT | MULT}

<n> ::= 1 to (# analog channels) in NR1 format
```

See Also

- "Introduction to :FUNCtion Commands" on page 303
- ":FUNCtion:OPERation" on page 315

:FUNCtion:VIEW

(see page 828)

Command Syntax

```
:FUNCtion:VIEW <view>

<view> ::= {{1 | ON} | (0 | OFF}}
```

The :FUNCtion:VIEW command turns the selected function on or off. When ON is selected, the function performs as specified using the other FUNCtion commands. When OFF is selected, function is neither calculated nor displayed.

NOTE The :FUNCtion:VIEW command is provided for backward compatibility to previous oscilloscopes. Use the :FUNCtion:DISPlay command (see page 304) instead.

Query Syntax

```
:FUNCtion:VIEW?
```

The :FUNCtion:VIEW? query returns the current state of the selected function.

Return Format

```
<view><NL>

<view> ::= {1 | 0}
```

:HARDcopy:DESTination

(see page 828)

Command Syntax

```
:HARDcopy:DESTination <destination>

<destination> ::= {CENTronics | FLOPpy}
```

The :HARDcopy:DESTination command sets the hardcopy destination.

NOTE The :HARDcopy:DESTination command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :HARDcopy:FILename command (see page 757) instead.

Query Syntax

```
:HARDcopy:DESTination?
```

The :HARDcopy:DESTination? query returns the selected hardcopy destination.

Return Format

```
<destination><NL>

<destination> ::= {CENT | FLOP}
```

See Also

- "Introduction to :HARDcopy Commands" on page 324

:HARDcopy:FILename

(see page 828)

Command Syntax

```
:HARDcopy:FILename <string>

<string> ::= quoted ASCII string
```

The HARDcopy:FILename command sets the output filename for those print formats whose output is a file.

NOTE The :HARDcopy:FILename command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :SAVE:FILename command (see page 468) and :RECall:FILename command (see page 459) instead.

Query Syntax

```
:HARDcopy:FILename?
```

The :HARDcopy:FILename? query returns the current hardcopy output filename.

Return Format

```
<string><NL>

<string> ::= quoted ASCII string
```

See Also

- "Introduction to :HARDcopy Commands" on page 324

:HARDcopy:GRAYscale

(see page 828)

Command Syntax

```
:HARDcopy:GRAYscale <gray>

<gray> ::= {{OFF | 0} | {ON | 1}}
```

The :HARDcopy:GRAYscale command controls whether grayscaling is performed in the hardcopy dump.

NOTE

The :HARDcopy:GRAYscale command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :HARDcopy:PALette command (see page 334) instead. (":HARDcopy:GRAYscale ON" is the same as ":HARDcopy:PALette GRAYscale" and ":HARDcopy:GRAYscale OFF" is the same as ":HARDcopy:PALette COLor".)

Query Syntax

```
:HARDcopy:GRAYscale?
```

The :HARDcopy:GRAYscale? query returns a flag indicating whether grayscaling is performed in the hardcopy dump.

Return Format

```
<gray><NL>

<gray> ::= {0 | 1}
```

See Also

- "Introduction to :HARDcopy Commands" on page 324

:HARDcopy:IGColors

(see page 828)

Command Syntax

```
:HARDcopy:IGColors <value>

<value> ::= {{OFF | 0} | {ON | 1}}
```

The HARDcopy:IGColors command controls whether the graticule colors are inverted or not.

NOTE

The :HARDcopy:IGColors command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :HARDcopy:INKSaver (see page 329) command instead.

Query Syntax

```
:HARDcopy:IGColors?
```

The :HARDcopy:IGColors? query returns a flag indicating whether graticule colors are inverted or not.

Return Format

```
<value><NL>

<value> ::= {0 | 1}
```

See Also

- "Introduction to :HARDcopy Commands" on page 324

:HARDcopy:PDRiver

(see page 828)

Command Syntax

```
:HARDcopy:PDRiver <driver>

<driver> ::= {AP2Xxx | AP21xx | {AP2560 | AP25} | {DJ350 | DJ35} |
              DJ6xx | {DJ630 | DJ63} | DJ6Special | DJ6Photo |
              DJ8Special | DJ8xx | DJ9Vip | OJPRokx50 | DJ9xx | GVIP |
              DJ55xx | {PS470 | PS47} {PS100 | PS10} | CLASer |
              MLASer | LJFastraster | POSTscript}
```

The HARDcopy:PDRiver command sets the hardcopy printer driver used for the selected printer.

If the correct driver for the selected printer can be identified, it will be selected and cannot be changed.

NOTE The :HARDcopy:PDRiver command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :HARDcopy:APRinter (see page 326) command instead.

Query Syntax

```
:HARDcopy:PDRiver?
```

The :HARDcopy:PDRiver? query returns the selected hardcopy printer driver.

Return Format

```
<driver><NL>

<driver> ::= {AP2X | AP21 | AP25 | DJ35 | DJ6 | DJ63 | DJ6S | DJ6P |
              DJ8S | DJ8 | DJ9V | OJPR | DJ9 | GVIP | DJ55 | PS10 |
              PS47 | CLAS | MLAS | LJF | POST}
```

See Also

- "Introduction to :HARDcopy Commands" on page 324

:MEASure:LOWer

(see page 828)

Command Syntax `:MEASure:LOWer <voltage>`

The :MEASure:LOWer command sets the lower measurement threshold value. This value and the UPPer value represent absolute values when the thresholds are ABSolute and percentage when the thresholds are PERCent as defined by the :MEASure:DEFine THResholds command.

NOTE **The :MEASure:LOWer command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :MEASure:DEFine THResholds command (see page 373) instead.**

Query Syntax `:MEASure:LOWer?`

The :MEASure:LOWer? query returns the current lower threshold level.

Return Format `<voltage><NL>`

`<voltage> ::= the user-defined lower threshold in volts in NR3 format`

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:THResholds" on page 764
- ":MEASure:UPPer" on page 770

:MEASure:SCRatch

(see page 828)

Command Syntax `:MEASure:SCRatch`

The :MEASure:SCRatch command clears all selected measurements and markers from the screen.

NOTE **The :MEASure:SCRatch command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :MEASure:CLEar command (see page 371) instead.**

:MEASure:TDELta

(see page 828)

Query Syntax `:MEASure:TDELta?`

The :MEASure:TDELta? query returns the time difference between the Tstop marker (X2 cursor) and the Tstart marker (X1 cursor).

Tdelta = Tstop - Tstart

Tstart is the time at the start marker (X1 cursor) and Tstop is the time at the stop marker (X2 cursor). No measurement is made when the :MEASure:TDELta? query is received by the oscilloscope. The delta time value that is output is the current value. This is the same value as the front-panel cursors delta X value.

NOTE **The :MEASure:TDELta command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :MARKer:XDELta command (see page 349) instead.**

Return Format `<value><NL>`

`<value> ::= time difference between start and stop markers in NR3 format`

See Also

- "Introduction to :MARKer Commands" on page 342
- "Introduction to :MEASure Commands" on page 367
- ":MARKer:X1Position" on page 345
- ":MARKer:X2Position" on page 347
- ":MARKer:XDELta" on page 349
- ":MEASure:TSTArt" on page 767
- ":MEASure:TSTOp" on page 768

:MEASure:THResholds

(see page 828)

Command Syntax `:MEASure:THResholds {T1090 | T2080 | VOLTage}`

The :MEASure:THResholds command selects the thresholds used when making time measurements.

NOTE **The :MEASure:THResholds command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :MEASure:DEFine THResholds command (see page 373) instead.**

Query Syntax `:MEASure:THResholds?`

The :MEASure:THResholds? query returns the current thresholds selected when making time measurements.

Return Format `{T1090 | T2080 | VOLTage}<NL>`

`{T1090} uses the 10% and 90% levels of the selected waveform.`

`{T2080} uses the 20% and 80% levels of the selected waveform.`

`{VOLTage} uses the upper and lower voltage thresholds set by the UPPer and LOWer commands on the selected waveform.`

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:LOWer" on page 761
- ":MEASure:UPPer" on page 770

:MEASure:TMAX

(see page 828)

Command Syntax

```
:MEASure:TMAX [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :MEASure:TMAX command installs a screen measurement and starts an X-at-Max-Y measurement on the selected waveform. If the optional source is specified, the current source is modified.

NOTE **The :MEASure:TMAX command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :MEASure:XMAX command (see page 421) instead.**

Query Syntax

```
:MEASure:TMAX? [<source>]
```

The :MEASure:TMAX? query returns the horizontal axis value at which the maximum vertical value occurs on the current source. If the optional source is specified, the current source is modified. If all channels are off, the query returns 9.9E+37.

Return Format

```
<value><NL>

<value> ::= time at maximum in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:TMIN" on page 766
- ":MEASure:XMAX" on page 421
- ":MEASure:XMIN" on page 422

:MEASure:TMIN

(see page 828)

Command Syntax

```
:MEASure:TMIN [<source>]

<source> ::= {CHANnel<n> | FUNCtion | MATH}

<n> ::= 1 to (# analog channels) in NR1 format
```

The :MEASure:TMIN command installs a screen measurement and starts an X-at-Min-Y measurement on the selected waveform. If the optional source is specified, the current source is modified.

NOTE The :MEASure:TMIN command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :MEASure:XMIN command (see page 422) instead.

Query Syntax

```
:MEASure:TMIN? [<source>]
```

The :MEASure:TMIN? query returns the horizontal axis value at which the minimum vertical value occurs on the current source. If the optional source is specified, the current source is modified. If all channels are off, the query returns 9.9E+37.

Return Format

```
<value><NL>

<value> ::= time at minimum in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:TMAX" on page 765
- ":MEASure:XMAX" on page 421
- ":MEASure:XMIN" on page 422

:MEASure:TSTArt

(see page 828)

Command Syntax

```
:MEASure:TSTArt <value> [suffix]

<value> ::= time at the start marker in seconds

[suffix] ::= {s | ms | us | ns | ps}
```

The :MEASure:TSTArt command moves the start marker (X1 cursor) to the specified time with respect to the trigger time.

NOTE The short form of this command, TSTA, does not follow the defined Long Form to Short Form Truncation Rules (see page 830). The normal short form "TST" would be the same for both TSTArt and TSTOp, so sending TST for the TSTArt command produces an error.

NOTE The :MEASure:TSTArt command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :MARKer:X1Position command (see page 345) instead.

Query Syntax

```
:MEASure:TSTArt?
```

The :MEASure:TSTArt? query returns the time at the start marker (X1 cursor).

Return Format

```
<value><NL>

<value> ::= time at the start marker in NR3 format
```

See Also

- "Introduction to :MARKer Commands" on page 342
- "Introduction to :MEASure Commands" on page 367
- ":MARKer:X1Position" on page 345
- ":MARKer:X2Position" on page 347
- ":MARKer:XDELta" on page 349
- ":MEASure:TDELta" on page 763
- ":MEASure:TSTOp" on page 768

:MEASure:TSTOp

(see page 828)

Command Syntax

```
:MEASure:TSTOp <value> [suffix]

<value> ::= time at the stop marker in seconds

[suffix] ::= {s | ms | us | ns | ps}
```

The :MEASure:TSTOp command moves the stop marker (X2 cursor) to the specified time with respect to the trigger time.

NOTE The short form of this command, TSTO, does not follow the defined Long Form to Short Form Truncation Rules (see page 830). The normal short form "TST" would be the same for both TSTArt and TSTOp, so sending TST for the TSTOp command produces an error.

NOTE The :MEASure:TSTOp command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :MARKer:X2Position command (see page 347) instead.

Query Syntax

```
:MEASure:TSTOp?
```

The :MEASure:TSTOp? query returns the time at the stop marker (X2 cursor).

Return Format

```
<value><NL>

<value> ::= time at the stop marker in NR3 format
```

See Also

- "Introduction to :MARKer Commands" on page 342
- "Introduction to :MEASure Commands" on page 367
- ":MARKer:X1Position" on page 345
- ":MARKer:X2Position" on page 347
- ":MARKer:XDELta" on page 349
- ":MEASure:TDELta" on page 763
- ":MEASure:TSTArt" on page 767

:MEASure:TVOLt

(see page 828)

Query Syntax

```
:MEASure:TVOLt? <value>, [<slope>]<occurrence>[,<source>]

<value> ::= the voltage level that the waveform must cross.

<slope> ::= direction of the waveform.  A rising slope is indicated by
            a plus sign (+).  A falling edge is indicated by a minus
            sign (-).

<occurrence> ::= the transition to be reported.  If the occurrence
                 number is one, the first crossing is reported.  If
                 the number is two, the second crossing is reported,
                 etc.

<source> ::= {CHANnel<n> | FUNCtion | MATH}

<n> ::= 1 to (# analog channels) in NR1 format
```

When the :MEASure:TVOLt? query is sent, the displayed signal is searched for the specified voltage level and transition. The time interval between the trigger event and this defined occurrence is returned as the response to the query.

The specified voltage can be negative or positive. To specify a negative voltage, use a minus sign (-). The sign of the slope selects a rising (+) or falling (-) edge. If no sign is specified for the slope, it is assumed to be the rising edge.

The magnitude of the occurrence defines the occurrence to be reported. For example, +3 returns the time for the third time the waveform crosses the specified voltage level in the positive direction. Once this voltage crossing is found, the oscilloscope reports the time at that crossing in seconds, with the trigger point (time zero) as the reference.

If the specified crossing cannot be found, the oscilloscope reports +9.9E+37. This value is returned if the waveform does not cross the specified voltage, or if the waveform does not cross the specified voltage for the specified number of times in the direction specified.

If the optional source parameter is specified, the current source is modified.

NOTE The :MEASure:TVOLt command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :MEASure:TVALue command (see page 409).

Return Format

```
<value><NL>

<value> ::= time in seconds of the specified voltage crossing
            in NR3 format
```

:MEASure:UPPer

(see page 828)

Command Syntax `:MEASure:UPPer <value>`

The :MEASure:UPPer command sets the upper measurement threshold value. This value and the LOWer value represent absolute values when the thresholds are ABSolute and percentage when the thresholds are PERCent as defined by the :MEASure:DEFine THResholds command.

NOTE **The :MEASure:UPPer command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :MEASure:DEFine THResholds command (see page 373) instead.**

Query Syntax `:MEASure:UPPer?`

The :MEASure:UPPer? query returns the current upper threshold level.

Return Format `<value><NL>`

```
<value> ::= the user-defined upper threshold in NR3 format
```

See Also

- "Introduction to :MEASure Commands" on page 367
- ":MEASure:LOWer" on page 761
- ":MEASure:THResholds" on page 764

:MEASure:VDELta

(see page 828)

Query Syntax `:MEASure:VDELta?`

The :MEASure:VDELta? query returns the voltage difference between vertical marker 1 (Y1 cursor) and vertical marker 2 (Y2 cursor). No measurement is made when the :MEASure:VDELta? query is received by the oscilloscope. The delta value that is returned is the current value. This is the same value as the front-panel cursors delta Y value.

VDELta = value at marker 2 - value at marker 1

NOTE **The :MEASure:VDELta command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :MARKer:YDELta command (see page 354) instead.**

Return Format `<value><NL>`

`<value> ::= delta V value in NR1 format`

See Also

- "Introduction to :MARKer Commands" on page 342
- "Introduction to :MEASure Commands" on page 367
- ":MARKer:Y1Position" on page 352
- ":MARKer:Y2Position" on page 353
- ":MARKer:YDELta" on page 354
- ":MEASure:TDELta" on page 763
- ":MEASure:TSTArt" on page 767

:MEASure:VSTArt

(see page 828)

Command Syntax

```
:MEASure:VSTArt <vstart_argument>

<vstart_argument> ::= value for vertical marker 1
```

The :MEASure:VSTArt command moves the vertical marker (Y1 cursor) to the specified value corresponding to the selected source. The source can be selected by the MARKer:X1Y1source command.

NOTE The short form of this command, VSTA, does not follow the defined Long Form to Short Form Truncation Rules (see page 830). The normal short form, VST, would be the same for both VSTArt and VSTOp, so sending VST for the VSTArt command produces an error.

NOTE The :MEASure:VSTArt command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :MARKer:Y1Position command (see page 352) instead.

Query Syntax

```
:MEASure:VSTArt?
```

The :MEASure:VSTArt? query returns the current value of the Y1 cursor.

Return Format

```
<value><NL>

<value> ::= voltage at voltage marker 1 in NR3 format
```

See Also

- "Introduction to :MARKer Commands" on page 342
- "Introduction to :MEASure Commands" on page 367
- ":MARKer:Y1Position" on page 352
- ":MARKer:Y2Position" on page 353
- ":MARKer:YDELta" on page 354
- ":MARKer:X1Y1source" on page 346
- ":MEASure:SOURce" on page 399
- ":MEASure:TDELta" on page 763
- ":MEASure:TSTArt" on page 767

:MEASure:VSTOp

(see page 828)

Command Syntax

```
:MEASure:VSTOp <vstop_argument>

<vstop_argument> ::= value for Y2 cursor
```

The :MEASure:VSTOp command moves the vertical marker 2 (Y2 cursor) to the specified value corresponding to the selected source. The source can be selected by the MARKer:X2Y2source command.

NOTE The short form of this command, VSTO, does not follow the defined Long Form to Short Form Truncation Rules (see page 830). The normal short form, VST, would be the same for both VSTArt and VSTOp, so sending VST for the VSTOp command produces an error.

NOTE The :MEASure:VSTOp command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :MARKer:Y2Position command (see page 353) instead.

Query Syntax

```
:MEASure:VSTOp?
```

The :MEASure:VSTOp? query returns the current value of the Y2 cursor.

Return Format

```
<value><NL>

<value> ::= value of the Y2 cursor in NR3 format
```

See Also

- "Introduction to :MARKer Commands" on page 342
- "Introduction to :MEASure Commands" on page 367
- ":MARKer:Y1Position" on page 352
- ":MARKer:Y2Position" on page 353
- ":MARKer:YDELta" on page 354
- ":MARKer:X2Y2source" on page 348
- ":MEASure:SOURce" on page 399
- ":MEASure:TDELta" on page 763
- ":MEASure:TSTArt" on page 767

:MTESt:AMASk:{SAVE | STORe}

(see page 828)

Command Syntax

```
:MTESt:AMASk:{SAVE | STORe} "<filename>"
```

The :MTESt:AMASk:SAVE command saves the automask generated mask to a file. If an automask has not been generated, an error occurs.

The <filename> parameter is an MS-DOS compatible name of the file, a maximum of 254 characters long (including the path name, if used). The filename assumes the present working directory if a path does not precede the file name.

NOTE

The :MTESt:AMASk:{SAVE | STORe} command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :SAVE:MASK[:STARt] command (see page 475) instead.

See Also

- "Introduction to :MTESt Commands" on page 425

:MTESt:AVERage

(see page 828)

Command Syntax

```
:MTESt:AVERage <on_off>

<on_off> ::= {{1 | ON} | {0 | OFF}}
```

The :MTESt:AVERage command enables or disables averaging. When ON, the oscilloscope acquires multiple data values for each time bucket, and averages them. When OFF, averaging is disabled. To set the number of averages, use the :MTESt:AVERage:COUNt command described next.

NOTE The :MTESt:AVERage command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :ACQuire:TYPE AVERage command (see page 199) instead.

Query Syntax

```
:MTESt:AVERage?
```

The :MTESt:AVERage? query returns the current setting for averaging.

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:AVERage:COUNt" on page 776

:MTESt:AVERage:COUNt

(see page 828)

Command Syntax

```
:MTESt:AVERage:COUNt <count>

<count> ::= an integer from 2 to 65536 in NR1 format
```

The :MTESt:AVERage:COUNt command sets the number of averages for the waveforms. With the AVERage acquisition type, the :MTESt:AVERage:COUNt command specifies the number of data values to be averaged for each time bucket before the acquisition is considered complete for that time bucket.

NOTE **The :MTESt:AVERage:COUNt command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :ACQuire:COUNt command (see page 190) instead.**

Query Syntax

```
:MTESt:AVERage:COUNt?
```

The :MTESt:AVERage:COUNt? query returns the currently selected count value.

Return Format

```
<count><NL>

<count> ::= an integer from 2 to 65536 in NR1 format
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:AVERage" on page 775

:MTESt:LOAD

(see page 828)

Command Syntax `:MTESt:LOAD "<filename>"`

The :MTESt:LOAD command loads the specified mask file.

The <filename> parameter is an MS-DOS compatible name of the file, a maximum of 254 characters long (including the path name, if used).

NOTE **The :MTESt:LOAD command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :RECall:MASK[:STARt] command (see page 460) instead.**

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:AMASk:{SAVE | STORe}" on page 774

:MTESt:RUMode

(see page 828)

Command Syntax

```
:MTESt:RUMode {FORever | TIME,<seconds> | {WAVeforms,<wfm_count>}}

<seconds> ::= from 1 to 86400 in NR3 format

<wfm_count> ::= number of waveforms in NR1 format
                from 1 to 1,000,000,000
```

The :MTESt:RUMode command determines the termination conditions for the mask test. The choices are FORever, TIME, or WAVeforms.

- FORever – runs the Mask Test until the test is turned off.
- TIME – sets the amount of time in seconds that a mask test will run before it terminates. The <seconds> parameter is a real number from 1 to 86400 seconds.
- WAVeforms – sets the maximum number of waveforms that are required before the mask test terminates. The <wfm_count> parameter indicates the number of waveforms that are to be acquired; it is an integer from 1 to 1,000,000,000.

NOTE The :MTESt:RUMode command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :MTESt:RMODe command (see page 442) instead.

Query Syntax

```
:MTESt:RUMode?
```

The :MTESt:RUMode? query returns the currently selected termination condition and value.

Return Format

```
{FOR | TIME,<seconds> | {WAV,<wfm_count>}}<NL>

<seconds> ::= from 1 to 86400 in NR3 format

<wfm_count> ::= number of waveforms in NR1 format
                from 1 to 1,000,000,000
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:RUMode:SOFailure" on page 779

:MTESt:RUMode:SOFailure

(see page 828)

Command Syntax

```
:MTESt:RUMode:SOFailure <on_off>

<on_off> ::= {{1 | ON} | {0 | OFF}}
```

The :MTESt:RUMode:SOFailure command enables or disables the Stop On Failure run until criteria. When a mask test is run and a mask violation is detected, the mask test is stopped and the acquisition system is stopped.

NOTE The :MTESt:RUMode:SOFailure command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :MTESt:RMODe:FACTion:STOP command (see page 446) instead.

Query Syntax

```
:MTESt:RUMode:SOFailure?
```

The :MTESt:RUMode:SOFailure? query returns the current state of the Stop on Failure control.

Return Format

```
<on_off><NL>

<on_off> ::= {1 | 0}
```

See Also

- "Introduction to :MTESt Commands" on page 425
- ":MTESt:RUMode" on page 778

:MTESt:{STARt | STOP}

(see page 828)

Command Syntax

```
:MTESt:{STARt | STOP}
```

The :MTESt:{STARt | STOP} command starts or stops the acquisition system.

NOTE

The :MTESt:STARt and :MTESt:STOP commands are obsolete and are provided for backward compatibility to previous oscilloscopes. Use the :RUN command (see page 170) and :STOP command (see page 174) instead.

See Also

- "Introduction to :MTESt Commands" on page 425

:MTESt:TRIGger:SOURce

(see page 828)

Command Syntax

```
:MTESt:TRIGger:SOURce <source>

<source> ::= CHANnel<n>

<n> ::= 1 to (# analog channels) in NR1 format
```

The :MTESt:TRIGger:SOURce command sets the channel to use as the trigger.

NOTE The :MTESt:TRIGger:SOURce command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the trigger source commands (see page 615) instead.

Query Syntax

```
:MTESt:TRIGger:SOURce?
```

The :MTESt:TRIGger:SOURce? query returns the currently selected trigger source.

Return Format

```
<source> ::= CHAN<n>

<n> ::= 1 to (# analog channels) in NR1 format
```

See Also

- "Introduction to :MTESt Commands" on page 425

:PRINt?

(see page 828)

Query Syntax

```
:PRINt? [<options>]
<options> ::= [<print option>][,..,<print option>]
<print option> ::= {COLor | GRAYscale | BMP8bit | BMP}
```

The :PRINt? query pulls image data back over the bus for storage.

NOTE The :PRINT command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :DISPlay:DATA command (see page 244) instead.

Print Option	:PRINt command	:PRINt? query	Query Default
COLor	Sets palette=COLor		
GRAYscale	Sets palette=GRAYscale		palette=COLor
PRINter0,1	Causes the USB printer #0,1 to be selected as destination (if connected)	Not used	N/A
BMP8bit	Sets print format to 8-bit BMP	Selects 8-bit BMP formatting for query	N/A
BMP	Sets print format to BMP	Selects BMP formatting for query	N/A
FACTors	Selects outputting of additional settings information for :PRINT	Not used	N/A
NOFactors	Deselects outputting of additional settings information for :PRINT	Not used	N/A

Old Print Option:	Is Now:
HIRes	COLor
LORes	GRAYscale
PARallel	PRINter0
DISK	invalid
PCL	invalid

NOTE The PRINt? query is not a core command.

See Also
- "Introduction to Root (:) Commands" on page 145
- "Introduction to :HARDcopy Commands" on page 324
- ":HARDcopy:FACTors" on page 327
- ":HARDcopy:GRAYscale" on page 758
- ":DISPlay:DATA" on page 244

:SAVE:IMAGe:AREA

(see page 828)

Query Syntax `:SAVE:IMAGe:AREA?`

The :SAVE:IMAGe:AREA? query returns the selected image area.

When saving images, this query returns SCR (screen). When saving setups or waveform data, this query returns GRAT (graticule) even though graticule images are not saved.

Return Format `<area><NL>`

`<area> ::= {GRAT | SCR}`

See Also

- "Introduction to :SAVE Commands" on page 467
- ":SAVE:IMAGe[:STARt]" on page 469
- ":SAVE:IMAGe:FACTors" on page 470
- ":SAVE:IMAGe:FORMat" on page 471
- ":SAVE:IMAGe:INKSaver" on page 472
- ":SAVE:IMAGe:PALette" on page 473

:TIMebase:DELay

(see page 828)

Command Syntax

```
:TIMebase:DELay <delay_value>

<delay_value> ::= time in seconds from trigger to the delay reference
                  point on the screen.

The valid range for delay settings depends on the time/division
setting for the main time base.
```

The :TIMebase:DELay command sets the main time base delay. This delay is the time between the trigger event and the delay reference point on the screen. The delay reference point is set with the :TIMebase:REFerence command (see page 608).

NOTE The :TIMebase:DELay command is obsolete and is provided for backward compatibility to previous oscilloscopes. Use the :TIMebase:POSition command (see page 606) instead.

Query Syntax

```
:TIMebase:DELay?
```

The :TIMebase:DELay query returns the current delay value.

Return Format

```
<delay_value><NL>

<delay_value> ::= time from trigger to display reference in seconds
                  in NR3 format.
```

Example Code

```
' TIMEBASE_DELAY - Sets the time base delay.  This delay
' is the internal time between the trigger event and the
' onscreen delay reference point.

' Set time base delay to 0.0.
myScope.WriteString ":TIMEBASE:DELAY 0.0"
```

See complete example programs at: Chapter 37, “Programming Examples,” starting on page 837

:TRIGger:TV:TVMode

(see page 828)

Command Syntax

```
:TRIGger:TV:TVMode <mode>

<mode> ::= {FIEld1 | FIEld2 | AFIelds | ALINes | LINE | VERTical
           | LFIeld1 | LFIeld2 | LALTernate | LVERtical}
```

The :TRIGger:TV:MODE command selects the TV trigger mode and field. The LVERtical parameter is only available when :TRIGger:TV:STANdard is GENeric. The LALTernate parameter is not available when :TRIGger:TV:STANdard is GENeric (see page 662).

Old forms for <mode> are accepted:

<mode>	Old Forms Accepted
FIEld1	F1
FIEld2	F2
AFIeld	ALLFields, ALLFLDS
ALINes	ALLLines
LFIeld1	LINEF1, LINEFIELD1
LFIeld2	LINEF2, LINEFIELD2
LALTernate	LINEAlt
LVERtical	LINEVert

NOTE The :TRIGger:TV:TVMode command is an obsolete command provided for compatibility to previous oscilloscopes. Use the :TRIGger:TV:MODE command (see page 659) instead.

Query Syntax

```
:TRIGger:TV:TVMode?
```

The :TRIGger:TV:TVMode? query returns the TV trigger mode.

Return Format

```
<value><NL>

<value> ::= {FIE1 | FIE2 | AFI | ALIN | LINE | VERT | LFI1 | LFI2
            | LALT | LVER}
```

33 Error Messages

-440, Query UNTERMINATED after indefinite response

-430, Query DEADLOCKED

-420, Query UNTERMINATED

-410, Query INTERRUPTED

-400, Query error

-340, Calibration failed

-330, Self-test failed

-321, Out of memory

-320, Storage fault

-315, Configuration memory lost

-314, Save/recall memory lost

-313, Calibration memory lost

-311, Memory error

-310, System error

-300, Device specific error

-278, Macro header not found

-277, Macro redefinition not allowed

-276, Macro recursion error

-273, Illegal macro label

-272, Macro execution error

-258, Media protected

-257, File name error

-256, File name not found

-255, Directory full

-254, Media full

-253, Corrupt media

-252, Missing media

-251, Missing mass storage

-250, Mass storage error

-241, Hardware missing

This message can occur when a feature is unavailable or unlicensed.

For example, some serial bus decode commands are only available when the serial decode options are licensed.

-240, Hardware error

-231, Data questionable

-230, Data corrupt or stale

-224, Illegal parameter value

-223, Too much data

-222, Data out of range

-221, Settings conflict

-220, Parameter error

-200, Execution error

-183, Invalid inside macro definition

-181, Invalid outside macro definition

-178, Expression data not allowed

-171, Invalid expression

-170, Expression error

-168, Block data not allowed

-161, Invalid block data

-158, String data not allowed

-151, Invalid string data

-150, String data error

-148, Character data not allowed

-138, Suffix not allowed

-134, Suffix too long

-131, Invalid suffix

-128, Numeric data not allowed

-124, Too many digits

-123, Exponent too large

-121, Invalid character in number

-120, Numeric data error

-114, Header suffix out of range

-113, Undefined header

-112, Program mnemonic too long

-109, Missing parameter

-108, Parameter not allowed

-105, GET not allowed

-104, Data type error

-103, Invalid separator

-102, Syntax error

-101, Invalid character

-100, Command error

+10, Software Fault Occurred

+100, File Exists

+101, End-Of-File Found

+102, Read Error

+103, Write Error

+104, Illegal Operation

+105, Print Canceled

+106, Print Initialization Failed

+107, Invalid Trace File

+108, Compression Error

+109, No Data For Operation

A remote operation wants some information, but there is no information available. For example, you may request a stored TIFF image using the :DISPlay:DATA? query, but there may be no image stored.

+112, Unknown File Type

+113, Directory Not Supported

34 Status Reporting

Status Reporting Data Structures / 797
Status Byte Register (STB) / 800
Service Request Enable Register (SRE) / 802
Trigger Event Register (TER) / 803
Output Queue / 804
Message Queue / 805
(Standard) Event Status Register (ESR) / 806
(Standard) Event Status Enable Register (ESE) / 807
Error Queue / 808
Operation Status Event Register (:OPERegister[:EVENt]) / 809
Operation Status Condition Register (:OPERegister:CONDition) / 810
Arm Event Register (AER) / 811
Overload Event Register (:OVLRegister) / 812
Mask Test Event Event Register (:MTERegister[:EVENt]) / 813
Clearing Registers and Queues / 814
Status Reporting Decision Chart / 815

IEEE 488.2 defines data structures, commands, and common bit definitions for status reporting (for example, the Status Byte Register and the Standard Event Status Register). There are also instrument-defined structures and bits (for example, the Operation Status Event Register and the Overload Event Register).

An overview of the oscilloscope's status reporting structure is shown in the following block diagram. The status reporting structure allows monitoring specified events in the oscilloscope. The ability to monitor and report these events allows determination of such things as the status of an operation, the availability and reliability of the measured data, and more.



- To monitor an event, first clear the event; then, enable the event. All of the events are cleared when you initialize the instrument.
- To allow a service request (SRQ) interrupt to an external controller, enable at least one bit in the Status Byte Register (by setting, or unmasking, the bit in the Service Request Enable register).

The Status Byte Register, the Standard Event Status Register group, and the Output Queue are defined as the Standard Status Data Structure Model in IEEE 488.2-1987.

The bits in the status byte act as summary bits for the data structures residing behind them. In the case of queues, the summary bit is set if the queue is not empty. For registers, the summary bit is set if any enabled bit in the event register is set. The events are enabled with the corresponding event enable register. Events captured by an event register remain set until the register is read or cleared. Registers are read with their associated commands. The *CLS command clears all event registers and all queues except the output queue. If you send *CLS immediately after a program message terminator, the output queue is also cleared.

Status Reporting Data Structures

The following figure shows how the status register bits are masked and logically OR'ed to generate service requests (SRQ) on particular events.





The status register bits are described in more detail in the following tables:

- Table 44
- Table 42
- Table 49
- Table 50
- Table 52
- Table 47

The status registers picture above shows how the different status reporting data structures work together. To make it possible for any of the Standard Event Status Register bits to generate a summary bit, the bits must be enabled. These bits are enabled by using the *ESE common command to set the corresponding bit in the Standard Event Status Enable Register.

To generate a service request (SRQ) interrupt to an external controller, at least one bit in the Status Byte Register must be enabled. These bits are enabled by using the *SRE common command to set the corresponding bit in the Service Request Enable Register. These enabled bits can then set RQS and MSS (bit 6) in the Status Byte Register.

Status Byte Register (STB)

The Status Byte Register is the summary-level register in the status reporting structure. It contains summary bits that monitor activity in the other status registers and queues. The Status Byte Register is a live register. That is, its summary bits are set and cleared by the presence and absence of a summary bit from other event registers or queues.

If the Status Byte Register is to be used with the Service Request Enable Register to set bit 6 (RQS/MSS) and to generate an SRQ, at least one of the summary bits must be enabled, then set. Also, event bits in all other status registers must be specifically enabled to generate the summary bit that sets the associated summary bit in the Status Byte Register.

The Status Byte Register can be read using either the *STB? Common Command or the programming interface serial poll command. Both commands return the decimal-weighted sum of all set bits in the register. The difference between the two methods is that the serial poll command reads bit 6 as the Request Service (RQS) bit and clears the bit which clears the SRQ interrupt. The *STB? command reads bit 6 as the Master Summary Status (MSS) and does not clear the bit or have any affect on the SRQ interrupt. The value returned is the total bit weights of all of the bits that are set at the present time.

The use of bit 6 can be confusing. This bit was defined to cover all possible computer interfaces, including a computer that could not do a serial poll. The important point to remember is that, if you are using an SRQ interrupt to an external computer, the serial poll command clears bit 6. Clearing bit 6 allows the oscilloscope to generate another SRQ interrupt when another enabled event occurs.

No other bits in the Status Byte Register are cleared by either the *STB? query or the serial poll, except the Message Available bit (bit 4). If there are no other messages in the Output Queue, bit 4 (MAV) can be cleared as a result of reading the response to the *STB? command.

If bit 4 (weight = 16) and bit 5 (weight = 32) are set, the program prints the sum of the two weights. Since these bits were not enabled to generate an SRQ, bit 6 (weight = 64) is not set.

The following example uses the *STB? query to read the contents of the oscilloscope's Status Byte Register.

```
myScope.WriteString "*STB?"
varQueryResult = myScope.ReadNumber
MsgBox "Status Byte Register, Read: 0x" + Hex(varQueryResult)
```

The next program prints 0xD1 and clears bit 6 (RQS) and bit 4 (MAV) of the Status Byte Register. The difference in the output value between this example and the previous one is the value of bit 6 (weight = 64). Bit 6 is set when the first enabled summary bit is set and is cleared when the Status Byte Register is read by the serial poll command.

Example The following example uses the resource session object's ReadSTB method to read the contents of the oscilloscope's Status Byte Register.

```
varQueryResult = myScope.IO.ReadSTB
MsgBox "Status Byte Register, Serial Poll: 0x" + Hex(varQueryResult)
```

NOTE **Use Serial Polling to Read Status Byte Register**. Serial polling is the preferred method to read the contents of the Status Byte Register because it resets bit 6 and allows the next enabled event that occurs to generate a new SRQ interrupt.

Service Request Enable Register (SRE)

Setting the Service Request Enable Register bits enable corresponding bits in the Status Byte Register. These enabled bits can then set RQS and MSS (bit 6) in the Status Byte Register.

Bits are set in the Service Request Enable Register using the *SRE command and the bits that are set are read with the *SRE? query.

Example The following example sets bit 4 (MAV) and bit 5 (ESB) in the Service Request Enable Register.

```
myScope.WriteString "*SRE " + CStr(CInt("&H30"))
```

This example uses the decimal parameter value of 48, the string returned by CStr(CInt("&H30")), to enable the oscilloscope to generate an SRQ interrupt under the following conditions:

- When one or more bytes in the Output Queue set bit 4 (MAV).
- When an enabled event in the Standard Event Status Register generates a summary bit that sets bit 5 (ESB).

Trigger Event Register (TER)

This register sets the TRG bit in the status byte when a trigger event occurs.

The TER event register stays set until it is cleared by reading the register or using the *CLS command. If your application needs to detect multiple triggers, the TER event register must be cleared after each one.

If you are using the Service Request to interrupt a program or controller operation, you must clear the event register each time the trigger bit is set.

Output Queue

The output queue stores the oscilloscope-to-controller responses that are generated by certain instrument commands and queries. The output queue generates the Message Available summary bit when the output queue contains one or more bytes. This summary bit sets the MAV bit (bit 4) in the Status Byte Register.

When using the Keysight VISA COM library, the output queue may be read with the FormattedIO488 object's ReadString, ReadNumber, ReadList, or ReadIEEEBlock methods.

Message Queue

The message queue contains the text of the last message written to the advisory line on the screen of the oscilloscope. The length of the oscilloscope's message queue is 1. Note that messages sent with the :SYSTem:DSP command do not set the MSG status bit in the Status Byte Register.

(Standard) Event Status Register (ESR)

The (Standard) Event Status Register (ESR) monitors the following oscilloscope status events:

- PON - Power On
- URQ - User Request
- CME - Command Error
- EXE - Execution Error
- DDE - Device Dependent Error
- QYE - Query Error
- RQC - Request Control
- OPC - Operation Complete

When one of these events occur, the event sets the corresponding bit in the register. If the bits are enabled in the Standard Event Status Enable Register, the bits set in this register generate a summary bit to set bit 5 (ESB) in the Status Byte Register.

You can read the contents of the Standard Event Status Register and clear the register by sending the *ESR? query. The value returned is the total bit weights of all of the bits that are set at the present time.

Example The following example uses the *ESR query to read the contents of the Standard Event Status Register.

```
myScope.WriteString "*ESR?"
varQueryResult = myScope.ReadNumber
MsgBox "Standard Event Status Register: 0x" + Hex(varQueryResult)
```

If bit 4 (weight = 16) and bit 5 (weight = 32) are set, the program prints the sum of the two weights.

(Standard) Event Status Enable Register (ESE)

To allow any of the (Standard) Event Status Register (ESR) bits to generate a summary bit, you must first enable that bit. Enable the bit by using the *ESE (Event Status Enable) common command to set the corresponding bit in the (Standard) Event Status Enable Register (ESE).

Set bits are read with the *ESE? query.

Example Suppose your application requires an interrupt whenever any type of error occurs. The error related bits in the (Standard) Event Status Register are bits 2 through 5 (hexadecimal value 0x3C). Therefore, you can enable any of these bits to generate the summary bit by sending:

```
myScope.WriteString "*ESE " + CStr(CInt("&H3C"))
```

Whenever an error occurs, it sets one of these bits in the (Standard) Event Status Register. Because all the error related bits are enabled, a summary bit is generated to set bit 5 (ESB) in the Status Byte Register.

If bit 5 (ESB) in the Status Byte Register is enabled (via the *SRE command), an SRQ service request interrupt is sent to the controller PC.

NOTE **Disabled (Standard) Event Status Register bits respond but do not generate a summary bit.** (Standard) Event Status Register bits that are not enabled still respond to their corresponding conditions (that is, they are set if the corresponding event occurs). However, because they are not enabled, they do not generate a summary bit to the Status Byte Register.

Error Queue

As errors are detected, they are placed in an error queue. This queue is first in, first out. If the error queue overflows, the last error in the queue is replaced with error 350, Queue overflow. Any time the queue overflows, the least recent errors remain in the queue, and the most recent error is discarded. The length of the oscilloscope's error queue is 30 (29 positions for the error messages, and 1 position for the Queue overflow message).

The error queue is read with the :SYSTem:ERRor? query. Executing this query reads and removes the oldest error from the head of the queue, which opens a position at the tail of the queue for a new error. When all the errors have been read from the queue, subsequent error queries return "0, No error".

The error queue is cleared when:

- the instrument is powered up,
- the instrument receives the *CLS common command, or
- the last item is read from the error queue.

Operation Status Event Register (:OPERegister[:EVENt])

The Operation Status Event Register register hosts these bits:

Name	Location	Description
RUN bit	bit 3	Is set whenever the instrument goes from a stop state to a single or running state.
WAIT TRIG bit	bit 5	Is set by the Trigger Armed Event Register and indicates that the trigger is armed.
MTE bit	bit 9	Comes from the Mask Test Event Registers.
OVLR bit	bit 11	Is set whenever a 50Ω input overload occurs.

If any of these bits are set, the OPER bit (bit 7) of the Status Byte Register is set. The Operation Status Event Register is read and cleared with the :OPERegister[:EVENt]? query. The register output is enabled or disabled using the mask value supplied with the OPEE command.

Operation Status Condition Register (:OPERegister:CONDition)

The Operation Status Condition Register register hosts these bits:

Name	Location	Description
RUN bit	bit 3	Is set whenever the instrument is not stopped.
WAIT TRIG bit	bit 5	Is set by the Trigger Armed Event Register and indicates that the trigger is armed.
MTE bit	bit 9	Comes from the Mask Test Event Registers.
OVLR bit	bit 11	Is set whenever a 50Ω input overload occurs.

The :OPERegister:CONDition? query returns the value of the Operation Status Condition Register.

Arm Event Register (AER)

This register sets bit 5 (Wait Trig bit) in the Operation Status Register and the OPER bit (bit 7) in the Status Byte Register when the instrument becomes armed.

The ARM event register stays set until it is cleared by reading the register with the AER? query or using the *CLS command. If your application needs to detect multiple triggers, the ARM event register must be cleared after each one.

If you are using the Service Request to interrupt a program or controller operation when the trigger bit is set, then you must clear the event register after each time it has been set.

Overload Event Register (:OVLRegister)

The Overload Event Register register hosts these bits:

Name	Location	Description
Channel 1 Fault	bit 6	Fault has occurred on Channel 1 input.
Channel 2 Fault	bit 7	Fault has occurred on Channel 2 input.
Channel 3 Fault	bit 8	Fault has occurred on Channel 3 input.
Channel 4 Fault	bit 9	Fault has occurred on Channel 4 input.
External Trigger Fault	bit 10	Fault has occurred on External Trigger input.

Mask Test Event Event Register (:MTERegister[:EVENt])

The Mask Test Event Event Register register hosts these bits:

Name	Location	Description
Complete	bit 0	Is set when the mask test is complete.
Fail	bit 1	Is set when there is a mask test failure.
Started	bit 8	Is set when mask testing is started.
Auto Mask	bit 10	Is set when auto mask creation is completed.

The :MTERegister[:EVENt]? query returns the value of, and clears, the Mask Test Event Event Register.

Clearing Registers and Queues

The *CLS common command clears all event registers and all queues except the output queue. If *CLS is sent immediately after a program message terminator, the output queue is also cleared.

Status Reporting Decision Chart



35 Synchronizing Acquisitions

Synchronization in the Programming Flow / 818
Blocking Synchronization / 819
Polling Synchronization With Timeout / 820
Synchronizing with a Single-Shot Device Under Test (DUT) / 822
Synchronization with an Averaging Acquisition / 824

When remotely controlling an oscilloscope with programming commands, it is often necessary to know when the oscilloscope has finished the previous operation and is ready for the next command. The most common example is when an acquisition is started using the :DIGitize, :RUN, or :SINGle commands. Before a measurement result can be queried, the acquisition must complete. Too often fixed delays are used to accomplish this wait, but fixed delays often use excessive time or the time may not be long enough. A better solution is to use synchronous commands and status to know when the oscilloscope is ready for the next request.

Synchronization in the Programming Flow

Most remote programming follows these three general steps:

1. Set up the oscilloscope and device under test (see page 818).
2. Acquire a waveform (see page 818).
3. Retrieve results (see page 818).

Set Up the Oscilloscope

Before making changes to the oscilloscope setup, it is best to make sure it is stopped using the :STOP command followed by the *OPC? query.

NOTE **It is not necessary to use *OPC?, hard coded waits, or status checking when setting up the oscilloscope. After the oscilloscope is configured, it is ready for an acquisition.**

Acquire a Waveform

When acquiring a waveform there are two possible methods used to wait for the acquisition to complete. These methods are blocking and polling. The table below details when each method should be chosen and why.

	Blocking Wait	Polling Wait
Use When	You know the oscilloscope *will* trigger based on the oscilloscope setup and device under test.	You know the oscilloscope *may or may not* trigger on the oscilloscope setup and device under test.
Advantages	No need for polling. Fastest method.	Remote interface will not timeout No need for device clear if no trigger.
Disadvantages	Remote interface may timeout. Device clear only way to get control of oscilloscope if there is no trigger.	Slower method. Requires polling loop. Requires known maximum wait time.
Implementation Details	See "Blocking Synchronization" on page 819.	See "Polling Synchronization With Timeout" on page 820.

Retrieve Results

Once the acquisition is complete, it is safe to retrieve measurements and statistics.

Blocking Synchronization

Use the :DIGitize command to start the acquisition. This blocks subsequent queries until the acquisition and processing is complete. For example:

```
'
' Synchronizing acquisition using blocking.
' ====================================================================

Option Explicit

Public myMgr As VisaComLib.ResourceManager
Public myScope As VisaComLib.FormattedIO488
Public varQueryResult As Variant
Public strQueryResult As String

Sub Main()

  On Error GoTo VisaComError

  ' Create the VISA COM I/O resource.
  Set myMgr = New VisaComLib.ResourceManager
  Set myScope = New VisaComLib.FormattedIO488
  Set myScope.IO = myMgr.Open("TCPIP0::130.29.69.12::inst0::INSTR")
  myScope.IO.Clear   ' Clear the interface.

  ' Set up.
  ' ---------------------------------------------------------------
  myScope.WriteString ":TRIGger:MODE EDGE"
  myScope.WriteString ":TRIGger:EDGE:LEVel 2"
  myScope.WriteString ":TIMebase:SCALe 5e-8"

  ' Acquire.
  ' ---------------------------------------------------------------
  myScope.WriteString ":DIGitize"

  ' Get results.
  ' ---------------------------------------------------------------
  myScope.WriteString ":MEASure:RISetime"
  myScope.WriteString ":MEASure:RISetime?"
  varQueryResult = myScope.ReadNumber   ' Read risetime.
  Debug.Print "Risetime: " + _
      FormatNumber(varQueryResult * 1000000000, 1) + " ns"

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error:" + vbCrLf + Err.Description

End Sub
```

Polling Synchronization With Timeout

This example requires a timeout value so the operation can abort if an acquisition does not occur within the timeout period:

```
'
' Synchronizing acquisition using polling.
' ====================================================================

Option Explicit

Public myMgr As VisaComLib.ResourceManager
Public myScope As VisaComLib.FormattedIO488
Public varQueryResult As Variant
Public strQueryResult As String

Private Declare Sub Sleep Lib "kernel32" (ByVal dwMilliseconds As Long)

Sub Main()

  On Error GoTo VisaComError

  ' Create the VISA COM I/O resource.
  Set myMgr = New VisaComLib.ResourceManager
  Set myScope = New VisaComLib.FormattedIO488
  Set myScope.IO = myMgr.Open("TCPIP0::130.29.69.12::inst0::INSTR")
  myScope.IO.Clear   ' Clear the interface.

  ' Set up.
  ' --------------------------------------------------------------------
  ' Set up the trigger and horizontal scale.
  myScope.WriteString ":TRIGger:MODE EDGE"
  myScope.WriteString ":TRIGger:EDGE:LEVel 2"
  myScope.WriteString ":TIMebase:SCALe 5e-8"

  ' Stop acquisitions and wait for the operation to complete.
  myScope.WriteString ":STOP"
  myScope.WriteString "*OPC?"
  strQueryResult = myScope.ReadString

  ' Acquire.
  ' --------------------------------------------------------------------
  ' Start a single acquisition.
  myScope.WriteString ":SINGle"

  ' Oscilloscope is armed and ready, enable DUT here.
  Debug.Print "Oscilloscope is armed and ready, enable DUT."

  ' Look for RUN bit = stopped (acquisition complete).
  Dim lngTimeout As Long   ' Max millisecs to wait for single-shot.
  Dim lngElapsed As Long
  lngTimeout = 10000   ' 10 seconds.
  lngElapsed = 0

  Do While lngElapsed <= lngTimeout
```

```
    myScope.WriteString ":OPERegister:CONDition?"
    varQueryResult = myScope.ReadNumber
    ' Mask RUN bit (bit 3, &H8).
    If (varQueryResult And &H8) = 0 Then
      Exit Do
    Else
      Sleep 100   ' Small wait to prevent excessive queries.
      lngElapsed = lngElapsed + 100
    End If
  Loop

  ' Get results.
  ' ------------------------------------------------------------------
  If lngElapsed < lngTimeout Then
    myScope.WriteString ":MEASure:RISetime"
    myScope.WriteString ":MEASure:RISetime?"
    varQueryResult = myScope.ReadNumber   ' Read risetime.
    Debug.Print "Risetime: " + _
        FormatNumber(varQueryResult * 1000000000, 1) + " ns"
  Else
    Debug.Print "Timeout waiting for single-shot trigger."
  End If

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error:" + vbCrLf + Err.Description

End Sub
```

Synchronizing with a Single-Shot Device Under Test (DUT)

The examples in "Blocking Synchronization" on page 819 and "Polling Synchronization With Timeout" on page 820 assume the DUT is continually running and therefore the oscilloscope will have more than one opportunity to trigger. With a single shot DUT, there is only one opportunity for the oscilloscope to trigger, so it is necessary for the oscilloscope to be armed and ready before the DUT is enabled.

NOTE **The blocking :DIGitize command cannot be used for a single shot DUT because once the :DIGitize command is issued, the oscilloscope is blocked from any further commands until the acquisition is complete.**

This example is the same "Polling Synchronization With Timeout" on page 820 with the addition of checking for the armed event status.

```
'
' Synchronizing single-shot acquisition using polling.
' ====================================================================

Option Explicit

Public myMgr As VisaComLib.ResourceManager
Public myScope As VisaComLib.FormattedIO488
Public varQueryResult As Variant
Public strQueryResult As String

Private Declare Sub Sleep Lib "kernel32" (ByVal dwMilliseconds As Long)

Sub Main()

  On Error GoTo VisaComError

  ' Create the VISA COM I/O resource.
  Set myMgr = New VisaComLib.ResourceManager
  Set myScope = New VisaComLib.FormattedIO488
  Set myScope.IO = myMgr.Open("TCPIP0::130.29.69.12::inst0::INSTR")
  myScope.IO.Clear   ' Clear the interface.

  ' Set up.
  ' ---------------------------------------------------------------------
  ' Set up the trigger and horizontal scale.
  myScope.WriteString ":TRIGger:MODE EDGE"
  myScope.WriteString ":TRIGger:EDGE:LEVel 2"
  myScope.WriteString ":TIMebase:SCALe 5e-8"

  ' Stop acquisitions and wait for the operation to complete.
  myScope.WriteString ":STOP"
  myScope.WriteString "*OPC?"
  strQueryResult = myScope.ReadString

  ' Acquire.
```

```
  ' ------------------------------------------------------------------
  ' Start a single acquisition.
  myScope.WriteString ":SINGle"

  ' Wait until the trigger system is armed.
  Do
    Sleep 100   ' Small wait to prevent excessive queries.
    myScope.WriteString ":AER?"
    varQueryResult = myScope.ReadNumber
  Loop Until varQueryResult = 1

  ' Oscilloscope is armed and ready, enable DUT here.
  Debug.Print "Oscilloscope is armed and ready, enable DUT."

  ' Now, look for RUN bit = stopped (acquisition complete).
  Dim lngTimeout As Long   ' Max millisecs to wait for single-shot.
  Dim lngElapsed As Long
  lngTimeout = 10000   ' 10 seconds.
  lngElapsed = 0

  Do While lngElapsed <= lngTimeout
    myScope.WriteString ":OPERegister:CONDition?"
    varQueryResult = myScope.ReadNumber
    ' Mask RUN bit (bit 3, &H8).
    If (varQueryResult And &H8) = 0 Then
      Exit Do
    Else
      Sleep 100   ' Small wait to prevent excessive queries.
      lngElapsed = lngElapsed + 100
    End If
  Loop

  ' Get results.
  ' ------------------------------------------------------------------
  If lngElapsed < lngTimeout Then
    myScope.WriteString ":MEASure:RISetime"
    myScope.WriteString ":MEASure:RISetime?"
    varQueryResult = myScope.ReadNumber   ' Read risetime.
    Debug.Print "Risetime: " + _
        FormatNumber(varQueryResult * 1000000000, 1) + " ns"
  Else
    Debug.Print "Timeout waiting for single-shot trigger."
  End If

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error:" + vbCrLf + Err.Description

End Sub
```

Synchronization with an Averaging Acquisition

When averaging, it is necessary to know when the average count has been reached. The :SINGle command does not average.

If it is known that a trigger will occur, a :DIGitize will acquire the complete number of averages, but if the number of averages is large, a timeout on the connection can occur.

The example below polls during the :DIGitize to prevent a timeout on the connection.

```
'
' Synchronizing in averaging acquisition mode.
' ====================================================================

Option Explicit

Public myMgr As VisaComLib.ResourceManager
Public myScope As VisaComLib.FormattedIO488
Public varQueryResult As Variant
Public strQueryResult As String

Private Declare Sub Sleep Lib "kernel32" (ByVal dwMilliseconds As Long)

Sub Main()

  On Error GoTo VisaComError

  ' Create the VISA COM I/O resource.
  Set myMgr = New VisaComLib.ResourceManager
  Set myScope = New VisaComLib.FormattedIO488
  Set myScope.IO = myMgr.Open("TCPIP0::130.29.69.12::inst0::INSTR")
  myScope.IO.Clear   ' Clear the interface.
  myScope.IO.Timeout = 5000

  ' Set up.
  ' --------------------------------------------------------------------
  ' Set up the trigger and horizontal scale.
  myScope.WriteString ":TRIGger:SWEep NORMal"
  myScope.WriteString ":TRIGger:MODE EDGE"
  myScope.WriteString ":TRIGger:EDGE:LEVel 2"
  myScope.WriteString ":TIMebase:SCALe 5e-8"

  ' Stop acquisitions and wait for the operation to complete.
  myScope.WriteString ":STOP"
  myScope.WriteString "*OPC?"
  strQueryResult = myScope.ReadString

  ' Set up average acquisition mode.
  Dim lngAverages As Long
  lngAverages = 256
  myScope.WriteString ":ACQuire:COUNt " + CStr(lngAverages)
  myScope.WriteString ":ACQuire:TYPE AVERage"
```

```
  ' Save *ESE (Standard Event Status Enable register) mask
  ' (so it can be restored later).
  Dim varInitialESE As Variant
  myScope.WriteString "*ESE?"
  varInitialESE = myScope.ReadNumber

  ' Set *ESE mask to allow only OPC (Operation Complete) bit.
  myScope.WriteString "*ESE " + CStr(CInt("&H01"))

  ' Acquire using :DIGitize.  Set up OPC bit to be set when the
  ' operation is complete.
  ' ------------------------------------------------------------------
  myScope.WriteString ":DIGitize"
  myScope.WriteString "*OPC"

  ' Assume the oscilloscope will trigger, if not put a check here.

  ' Wait until OPC becomes true (bit 5 of Status Byte register, STB,
  ' from Standard Event Status register, ESR, is set).  STB can be
  ' read during :DIGitize without generating a timeout.
  Do
    Sleep 4000   ' Poll more often than the timeout setting.
    varQueryResult = myScope.IO.ReadSTB
  Loop While (varQueryResult And &H20) = 0

  ' Clear ESR and restore previously saved *ESE mask.
  myScope.WriteString "*ESR?"   ' Clear ESR by reading it.
  varQueryResult = myScope.ReadNumber
  myScope.WriteString "*ESE " + CStr(varInitialESE)

  ' Get results.
  ' ------------------------------------------------------------------
  myScope.WriteString ":WAVeform:COUNt?"
  varQueryResult = myScope.ReadNumber
  Debug.Print "Averaged waveforms: " + CStr(varQueryResult)

  myScope.WriteString ":MEASure:RISetime"
  myScope.WriteString ":MEASure:RISetime?"
  varQueryResult = myScope.ReadNumber   ' Read risetime.
  Debug.Print "Risetime: " + _
      FormatNumber(varQueryResult * 1000000000, 1) + " ns"

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error:" + vbCrLf + Err.Description

End Sub
```

36 More About Oscilloscope Commands

Command Classifications / 828
Valid Command/Query Strings / 829
Query Return Values / 835
All Oscilloscope Commands Are Sequential / 836

Command Classifications

To help you use existing programs with your oscilloscope, or use current programs with the next generation of Keysight InfiniiVision oscilloscopes, commands are classified by the following categories:

- "Core Commands" on page 828
- "Non-Core Commands" on page 828
- "Obsolete Commands" on page 828

Core Commands

Core commands are a common set of commands that provide basic oscilloscope functionality on this oscilloscope and future Keysight InfiniiVision oscilloscopes. Core commands are unlikely to be modified in the future. If you restrict your programs to core commands, the programs should work across product offerings in the future, assuming appropriate programming methods are employed.

Non-Core Commands

Non-core commands are commands that provide specific features, but are not universal across all Keysight InfiniiVision oscilloscope models. Non-core commands may be modified or deleted in the future. With a command structure as complex as the one for your oscilloscope, some evolution over time is inevitable. Keysight's intent is to continue to expand command subsystems, such as the rich and evolving trigger feature set.

Obsolete Commands

Obsolete commands are older forms of commands that are provided to reduce customer rework for existing systems and programs. Generally, these commands are mapped onto some of the Core and Non-core commands, but may not strictly have the same behavior as the new command. None of the obsolete commands are guaranteed to remain functional in future products. New systems and programs should use the Core (and Non-core) commands. Obsolete commands are listed in:

- Chapter 32, “Obsolete and Discontinued Commands,” starting on page 741

Valid Command/Query Strings

- "Program Message Syntax" on page 829
- "Duplicate Mnemonics" on page 833
- "Tree Traversal Rules and Multiple Commands" on page 833

Program Message Syntax

To program the instrument remotely, you must understand the command format and structure expected by the instrument. The IEEE 488.2 syntax rules govern how individual elements such as headers, separators, program data, and terminators may be grouped together to form complete instructions. Syntax definitions are also given to show how query responses are formatted. The following figure shows the main syntactical parts of a typical program statement.



Instructions (both commands and queries) normally appear as a string embedded in a statement of your host language, such as Visual Basic or C/C++. The only time a parameter is not meant to be expressed as a string is when the instruction's syntax definition specifies <block data>, such as <learn string>. There are only a few instructions that use block data.

Program messages can have long or short form commands (and data in some cases – see "Long Form to Short Form Truncation Rules" on page 830), and upper and/or lower case ASCII characters may be used. (Query responses, however, are always returned in upper case.)

Instructions are composed of two main parts:

- The header, which specifies the command or query to be sent.
- The program data, which provide additional information needed to clarify the meaning of the instruction.

Instruction Header

The instruction header is one or more mnemonics separated by colons (:) that represent the operation to be performed by the instrument.

":DISPlay:LABel ON" is a command. Queries are indicated by adding a question mark (?) to the end of the header, for example, ":DISPlay:LABel?". Many instructions can be used as either commands or queries, depending on whether or

not you have included the question mark. The command and query forms of an instruction usually have different program data. Many queries do not use any program data.

There are three types of headers:

- "Simple Command Headers" on page 831
- "Compound Command Headers" on page 831
- "Common Command Headers" on page 831

White Space (Separator)

White space is used to separate the instruction header from the program data. If the instruction does not require any program data parameters, you do not need to include any white space. White space is defined as one or more space characters. ASCII defines a space to be character 32 (in decimal).

Program Data

Program data are used to clarify the meaning of the command or query. They provide necessary information, such as whether a function should be on or off, or which waveform is to be displayed. Each instruction's syntax definition shows the program data, as well as the values they accept. "Program Data Syntax Rules" on page 832 describes all of the general rules about acceptable values.

When there is more than one data parameter, they are separated by commas(,). Spaces can be added around the commas to improve readability.

Program Message Terminator

The program instructions within a data message are executed after the program message terminator is received. The terminator may be either an NL (New Line) character, an EOI (End-Or-Identify) asserted in the programming interface, or a combination of the two. Asserting the EOI sets the EOI control line low on the last byte of the data message. The NL character is an ASCII linefeed (decimal 10).

NOTE

New Line Terminator Functions. The NL (New Line) terminator has the same function as an EOS (End Of String) and EOT (End Of Text) terminator.

Long Form to Short Form Truncation Rules

To get the short form of a command/keyword:

- When the command/keyword is longer than four characters, use the first four characters of the command/keyword unless the fourth character is a vowel; when the fourth character is a vowel, use the first three characters of the command/keyword.
- When the command/keyword is four or fewer characters, use all of the characters.

Long Form	Short form
RANGe	RANG
PATTern	PATT

Long Form	Short form
TIMebase	TIM
DELay	DEL
TYPE	TYPE

In the oscilloscope programmer's documentation, the short form of a command is indicated by uppercase characters.

Programs written in long form are easily read and are almost self-documenting. The short form syntax conserves the amount of controller memory needed for program storage and reduces I/O activity.

Simple Command Headers

Simple command headers contain a single mnemonic. :AUToscale and :DIGitize are examples of simple command headers typically used in the oscilloscope. The syntax is:

```
<program mnemonic><terminator>
```

Simple command headers must occur at the beginning of a program message; if not, they must be preceded by a colon.

When program data must be included with the simple command header (for example, :DIGitize CHANnel1), white space is added to separate the data from the header. The syntax is:

```
<program mnemonic><separator><program data><terminator>
```

Compound Command Headers

Compound command headers are a combination of two or more program mnemonics. The first mnemonic selects the subsystem, and the second mnemonic selects the function within that subsystem. The mnemonics within the compound message are separated by colons. For example, to execute a single function within a subsystem:

```
:<subsystem>:<function><separator><program data><terminator>
```

For example, :CHANnel1:BWLimit ON

Common Command Headers

Common command headers control IEEE 488.2 functions within the instrument (such as clear status). Their syntax is:

```
*<command header><terminator>
```

No space or separator is allowed between the asterisk (*) and the command header. *CLS is an example of a common command header.

Program Data Syntax Rules

Program data is used to convey a parameter information related to the command header. At least one space must separate the command header or query header from the program data.

```
<program mnemonic><separator><data><terminator>
```

When a program mnemonic or query has multiple program data, a comma separates sequential program data.

```
<program mnemonic><separator><data>,<data><terminator>
```

For example, :MEASure:DELay CHANnel1,CHANnel2 has two program data: CHANnel1 and CHANnel2.

Two main types of program data are used in commands: character and numeric.

Character Program Data

Character program data is used to convey parameter information as alpha or alphanumeric strings. For example, the :TIMebase:MODE command can be set to normal, zoomed (delayed), XY, or ROLL. The character program data in this case may be MAIN, WINDow, XY, or ROLL. The command :TIMebase:MODE WINDow sets the time base mode to zoomed.

The available mnemonics for character program data are always included with the command's syntax definition.

When sending commands, you may either the long form or short form (if one exists). Uppercase and lowercase letters may be mixed freely.

When receiving query responses, uppercase letters are used exclusively.

Numeric Program Data

Some command headers require program data to be expressed numerically. For example, :TIMebase:RANGe requires the desired full scale range to be expressed numerically.

For numeric program data, you have the option of using exponential notation or using suffix multipliers to indicate the numeric value. The following numbers are all equal:

```
28 = 0.28E2 = 280e-1 = 28000m = 0.028K = 28e-3K.
```

When a syntax definition specifies that a number is an integer, that means that the number should be whole. Any fractional part will be ignored, truncating the number. Numeric data parameters accept fractional values are called real numbers.

All numbers must be strings of ASCII characters. Thus, when sending the number 9, you would send a byte representing the ASCII code for the character 9 (which is 57). A three-digit number like 102 would take up three bytes (ASCII codes 49, 48, and 50). This is handled automatically when you include the entire instruction in a string.

Duplicate Mnemonics

Identical function mnemonics can be used in more than one subsystem. For example, the function mnemonic RANGe may be used to change the vertical range or to change the horizontal range:

```
:CHANnel1:RANGe .4
```

Sets the vertical range of channel 1 to 0.4 volts full scale.

```
:TIMebase:RANGe 1
```

Sets the horizontal time base to 1 second full scale.

:CHANnel1 and :TIMebase are subsystem selectors and determine which range is being modified.

Tree Traversal Rules and Multiple Commands

Command headers are created by traversing down the command tree. A legal command header would be :TIMebase:RANGe. This is referred to as a *compound header*. A compound header is a header made of two or more mnemonics separated by colons. The mnemonic created contains no spaces.

The following rules apply to traversing the tree:

- A leading colon (<NL> or EOI true on the last byte) places the parser at the root of the command tree. A leading colon is a colon that is the first character of a program header. Executing a subsystem command lets you access that subsystem until a leading colon or a program message terminator (<NL>) or EOI true is found.
- In the command tree, use the last mnemonic in the compound header as the reference point (for example, RANGe). Then find the last colon above that mnemonic (TIMebase:). That is the point where the parser resides. Any command below that point can be sent within the current program message without sending the mnemonics which appear above them (for example, POSition).

The output statements in the examples are written using the Keysight VISA COM library in Visual Basic. The quoted string is placed on the bus, followed by a carriage return and linefeed (CRLF).

To execute more than one function within the same subsystem, separate the functions with a semicolon (;):

```
:<subsystem>:<function><separator><data>;<function><separator><data><ter
minator>
```

For example:

```
myScope.WriteString ":TIMebase:RANGe 0.5;POSition 0"
```

NOTE

The colon between TIMebase and RANGe is necessary because TIMebase:RANGe is a compound command. The semicolon between the RANGe command and the POSition command is the required program message unit separator. The POSition command does not need TIMebase preceding it because the TIMebase:RANGe command sets the parser to the TIMebase node in the tree.

Example 2: Program Message Terminator Sets Parser Back to Root

```
myScope.WriteString ":TIMebase:REFerence CENTer;POSition 0.00001"
```

or

```
myScope.WriteString ":TIMebase:REFerence CENTer"
myScope.WriteString ":TIMebase:POSition 0.00001"
```

NOTE

In the first line of example 2, the subsystem selector is implied for the POSition command in the compound command. The POSition command must be in the same program message as the REFerence command because the program message terminator places the parser back at the root of the command tree.

A second way to send these commands is by placing TIMebase: before the POSition command as shown in the second part of example 2. The space after POSition is required.

Example 3: Selecting Multiple Subsystems

You can send multiple program commands and program queries for different subsystems on the same line by separating each command with a semicolon. The colon following the semicolon enables you to enter a new subsystem. For example:

```
<program mnemonic><data>;:<program mnemonic><data><terminator>
```

For example:

```
myScope.WriteString ":TIMebase:REFerence CENTer;:DISPlay:VECTors ON"
```

NOTE

The leading colon before DISPlay:VECTors ON tells the parser to go back to the root of the command tree. The parser can then see the DISPlay:VECTors ON command. The space between REFerence and CENter is required; so is the space between VECTors and ON.

Multiple commands may be any combination of compound and simple commands.

Query Return Values

Command headers immediately followed by a question mark (?) are queries. Queries are used to get results of measurements made by the instrument or to find out how the instrument is currently configured.

After receiving a query, the instrument interrogates the requested function and places the answer in its output queue. The answer remains in the output queue until it is read or another command is issued.

When read, the answer is transmitted across the bus to the designated listener (typically a controller). For example, the query :TIMebase:RANGe? places the current time base setting in the output queue. When using the Keysight VISA COM library in Visual Basic, the controller statements:

```
Dim strQueryResult As String
myScope.WriteString ":TIMebase:RANGe?"
strQueryResult = myScope.ReadString
```

pass the value across the bus to the controller and place it in the variable strQueryResult.

NOTE **Read Query Results Before Sending Another Command.** Sending another command or query before reading the result of a query clears the output buffer (the current response) and places a Query INTERRUPTED error in the error queue.

Infinity Representation

The representation of infinity is +9.9E+37. This is also the value returned when a measurement cannot be made.

All Oscilloscope Commands Are Sequential

IEEE 488.2 makes the distinction between sequential and overlapped commands:

- *Sequential commands* finish their task before the execution of the next command starts.
- *Overlapped commands* run concurrently. Commands following an overlapped command may be started before the overlapped command is completed.

All of the oscilloscope commands are sequential.

37 Programming Examples

VISA COM Examples / 838
VISA Examples / 871
VISA.NET Examples / 918
SICL Examples / 931
SCPI.NET Examples / 951

Example programs are ASCII text files that can be cut from the help file and pasted into your favorite text editor.

See Also

- You can find additional programming examples for the InfiniiVision 1200 X-Series oscilloscopes on the Keysight Technologies website at: www.keysight.com/find/1200X-Series-examples

VISA COM Examples

- "VISA COM Example in Visual Basic" on page 838
- "VISA COM Example in C#" on page 847
- "VISA COM Example in Visual Basic .NET" on page 856
- "VISA COM Example in Python 3" on page 864

VISA COM Example in Visual Basic

To run this example in Visual Basic for Applications (VBA):

1. Start the application that provides Visual Basic for Applications (for example, Microsoft Excel).
2. Press ALT+F11 to launch the Visual Basic editor.
3. Reference the Keysight VISA COM library:
   a. Choose **Tools > References...** from the main menu.
   b. In the References dialog, check the "VISA COM 5.9 Type Library".
   c. Click **OK**.
4. Choose **Insert > Module**.
5. Cut-and-paste the code that follows into the editor.
6. Edit the program to use the VISA address of your oscilloscope, and save the changes.
7. Run the program.

```
'
' Keysight VISA COM Example in Visual Basic
' ----------------------------------------------------------------------
' This program illustrates a few commonly-used programming
' features of your Keysight oscilloscope.
' ----------------------------------------------------------------------

Option Explicit

Public myMgr As VisaComLib.ResourceManager
Public myScope As VisaComLib.FormattedIO488
Public varQueryResult As Variant
Public strQueryResult As String

' For Sleep subroutine.
Private Declare Sub Sleep Lib "kernel32" (ByVal dwMilliseconds As Long)

'
' Main Program
' ----------------------------------------------------------------------

Sub Main()
```

```
  On Error GoTo VisaComError

  ' Create the VISA COM I/O resource.
  Set myMgr = New VisaComLib.ResourceManager
  Set myScope = New VisaComLib.FormattedIO488
  Set myScope.IO = _
      myMgr.Open("USB0::0x0957::0x17A6::US50210029::0::INSTR")
  myScope.IO.Clear   ' Clear the interface.
  myScope.IO.Timeout = 10000   ' Set I/O communication timeout.

  ' Initialize - start from a known state.
  Initialize

  ' Capture data.
  Capture

  ' Analyze the captured waveform.
  Analyze

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error:" + vbCrLf + Err.Description
  End

End Sub

'
' Initialize the oscilloscope to a known state.
' ---------------------------------------------------------------------

Private Sub Initialize()

  On Error GoTo VisaComError

  ' Get and display the device's *IDN? string.
  strQueryResult = DoQueryString("*IDN?")
  Debug.Print "Identification string: " + strQueryResult

  ' Clear status and load the default setup.
  DoCommand "*CLS"
  DoCommand "*RST"

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error:" + vbCrLf + Err.Description
  End

End Sub

'
' Capture the waveform.
' ---------------------------------------------------------------------

Private Sub Capture()
```

```
On Error GoTo VisaComError

' Use auto-scale to automatically configure oscilloscope.
' ------------------------------------------------------------------
DoCommand ":AUToscale"

' Set trigger mode (EDGE, PULSe, PATTern, etc., and input source.
DoCommand ":TRIGger:MODE EDGE"
Debug.Print "Trigger mode: " + _
    DoQueryString(":TRIGger:MODE?")

' Set EDGE trigger parameters.
DoCommand ":TRIGger:EDGE:SOURCe CHANnel1"
Debug.Print "Trigger edge source: " + _
    DoQueryString(":TRIGger:EDGE:SOURce?")

DoCommand ":TRIGger:EDGE:LEVel 1.5"
Debug.Print "Trigger edge level: " + _
    DoQueryString(":TRIGger:EDGE:LEVel?")

DoCommand ":TRIGger:EDGE:SLOPe POSitive"
Debug.Print "Trigger edge slope: " + _
    DoQueryString(":TRIGger:EDGE:SLOPe?")

' Save oscilloscope configuration.
' ------------------------------------------------------------------
varQueryResult = DoQueryIEEEBlock_UI1(":SYSTem:SETup?")

' Output setup string to a file:
Dim strPath As String
strPath = "c:\scope\config\setup.dat"
Dim hFile As Long
hFile = FreeFile
Open strPath For Binary Access Write Lock Write As hFile
Put hFile, , varQueryResult   ' Write data.
Close hFile   ' Close file.
Debug.Print "Setup bytes saved: " + CStr(LenB(varQueryResult))

' Change settings with individual commands:
' ------------------------------------------------------------------

' Set vertical scale and offset.
DoCommand ":CHANnel1:SCALe 0.05"
Debug.Print "Channel 1 vertical scale: " + _
    DoQueryString(":CHANnel1:SCALe?")

DoCommand ":CHANnel1:OFFSet -1.5"
Debug.Print "Channel 1 vertical offset: " + _
    DoQueryString(":CHANnel1:OFFSet?")

' Set horizontal scale and offset.
DoCommand ":TIMebase:SCALe 0.0002"
Debug.Print "Timebase scale: " + _
    DoQueryString(":TIMebase:SCALe?")

DoCommand ":TIMebase:POSition 0.0"
Debug.Print "Timebase position: " + _
```

```
      DoQueryString(":TIMebase:POSition?")

  ' Set the acquisition type (NORMal, PEAK, AVERage, or HRESolution).
  DoCommand ":ACQuire:TYPE NORMal"
  Debug.Print "Acquire type: " + _
      DoQueryString(":ACQuire:TYPE?")

  ' Or, configure by loading a previously saved setup.
  ' --------------------------------------------------------------------
  Dim varSetupString As Variant
  strPath = "c:\scope\config\setup.dat"
  Open strPath For Binary Access Read As hFile   ' Open file for input.
  Get hFile, , varSetupString   ' Read data.
  Close hFile   ' Close file.
  ' Write learn string back to oscilloscope using ":SYSTem:SETup"
  ' command:
  DoCommandIEEEBlock ":SYSTem:SETup", varSetupString
  Debug.Print "Setup bytes restored: " + CStr(LenB(varSetupString))

  ' Capture an acquisition using :DIGitize.
  ' --------------------------------------------------------------------
  DoCommand ":DIGitize CHANnel1"

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error:" + vbCrLf + Err.Description
  End

End Sub

'
' Analyze the captured waveform.
' ----------------------------------------------------------------------

Private Sub Analyze()

  On Error GoTo VisaComError

  ' Make a couple of measurements.
  ' --------------------------------------------------------------------
  DoCommand ":MEASure:SOURce CHANnel1"
  Debug.Print "Measure source: " + _
      DoQueryString(":MEASure:SOURce?")

  DoCommand ":MEASure:FREQuency"
  varQueryResult = DoQueryNumber(":MEASure:FREQuency?")
  MsgBox "Frequency:" + vbCrLf + _
      FormatNumber(varQueryResult / 1000, 4) + " kHz"

  DoCommand ":MEASure:VAMPlitude"
  varQueryResult = DoQueryNumber(":MEASure:VAMPlitude?")
  MsgBox "Vertical amplitude:" + vbCrLf + _
      FormatNumber(varQueryResult, 4) + " V"


  ' Download the screen image.
```

```
' ----------------------------------------------------------------------
' Get screen image.
DoCommand ":HARDcopy:INKSaver OFF"
Dim byteData() As Byte
byteData = DoQueryIEEEBlock_UI1(":DISPlay:DATA? PNG, COLor")

' Save screen image to a file.
Dim strPath As String
strPath = "c:\scope\data\screen.png"
If Len(Dir(strPath)) Then
  Kill strPath   ' Remove file if it exists.
End If

Dim hFile As Long
hFile = FreeFile
Open strPath For Binary Access Write Lock Write As hFile
Put hFile, , byteData   ' Write data.
Close hFile   ' Close file.
MsgBox "Screen image (" + CStr(UBound(byteData) + 1) + _
    " bytes) written to " + strPath


' Download waveform data.
' ----------------------------------------------------------------------

' Set the waveform points mode.
DoCommand ":WAVeform:POINts:MODE RAW"
Debug.Print "Waveform points mode: " + _
    DoQueryString(":WAVeform:POINts:MODE?")

' Get the number of waveform points available.
Debug.Print "Waveform points available: " + _
    DoQueryString(":WAVeform:POINts?")

' Set the waveform source.
DoCommand ":WAVeform:SOURce CHANnel1"
Debug.Print "Waveform source: " + _
    DoQueryString(":WAVeform:SOURce?")

' Choose the format of the data returned (WORD, BYTE, ASCII):
DoCommand ":WAVeform:FORMat BYTE"
Debug.Print "Waveform format: " + _
    DoQueryString(":WAVeform:FORMat?")

' Display the waveform settings:
Dim Preamble()
Dim intFormat As Integer
Dim intType As Integer
Dim lngPoints As Long
Dim lngCount As Long
Dim dblXIncrement As Double
Dim dblXOrigin As Double
Dim lngXReference As Long
Dim sngYIncrement As Single
Dim sngYOrigin As Single
Dim lngYReference As Long
```

```
Preamble() = DoQueryNumbers(":WAVeform:PREamble?")

intFormat = Preamble(0)
intType = Preamble(1)
lngPoints = Preamble(2)
lngCount = Preamble(3)
dblXIncrement = Preamble(4)
dblXOrigin = Preamble(5)
lngXReference = Preamble(6)
sngYIncrement = Preamble(7)
sngYOrigin = Preamble(8)
lngYReference = Preamble(9)

If intFormat = 0 Then
  Debug.Print "Waveform format: BYTE"
ElseIf intFormat = 1 Then
  Debug.Print "Waveform format: WORD"
ElseIf intFormat = 4 Then
  Debug.Print "Waveform format: ASCii"
End If

If intType = 0 Then
  Debug.Print "Acquisition type: NORMal"
ElseIf intType = 1 Then
  Debug.Print "Acquisition type: PEAK"
ElseIf intType = 2 Then
  Debug.Print "Acquisition type: AVERage"
ElseIf intType = 3 Then
  Debug.Print "Acquisition type: HRESolution"
End If

Debug.Print "Waveform points: " + _
    FormatNumber(lngPoints, 0)

Debug.Print "Waveform average count: " + _
    FormatNumber(lngCount, 0)

Debug.Print "Waveform X increment: " + _
    Format(dblXIncrement, "Scientific")

Debug.Print "Waveform X origin: " + _
    Format(dblXOrigin, "Scientific")

Debug.Print "Waveform X reference: " + _
    FormatNumber(lngXReference, 0)

Debug.Print "Waveform Y increment: " + _
    Format(sngYIncrement, "Scientific")

Debug.Print "Waveform Y origin: " + _
    FormatNumber(sngYOrigin, 0)

Debug.Print "Waveform Y reference: " + _
    FormatNumber(lngYReference, 0)

' Get the waveform data
varQueryResult = DoQueryIEEEBlock_UI1(":WAVeform:DATA?")
```

```
  Debug.Print "Number of data values: " + _
      CStr(UBound(varQueryResult) + 1)

  ' Set up output file:
  strPath = "c:\scope\data\waveform_data.csv"

  ' Open file for output.
  Open strPath For Output Access Write Lock Write As hFile

  ' Output waveform data in CSV format.
  Dim lngDataValue As Long
  Dim lngI As Long

  For lngI = 0 To UBound(varQueryResult)
    lngDataValue = varQueryResult(lngI)

    ' Write time value, voltage value.
    Print #hFile, _
        FormatNumber(dblXOrigin + (lngI * dblXIncrement), 9) + _
        ", " + _
        FormatNumber(((lngDataValue - lngYReference) * _
        sngYIncrement) + sngYOrigin)

  Next lngI

  ' Close output file.
  Close hFile   ' Close file.
  MsgBox "Waveform format BYTE data written to " + _
      "c:\scope\data\waveform_data.csv."

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error:" + vbCrLf + Err.Description
  End

End Sub

Private Sub DoCommand(command As String)

  On Error GoTo VisaComError

  myScope.WriteString command
  CheckInstrumentErrors

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error: " + vbCrLf + CStr(Err.Number) + ", " + _
      Err.Source + ", " + _
      Err.Description, vbExclamation, "VISA COM Error"
  End

End Sub

Private Sub DoCommandIEEEBlock(command As String, data As Variant)
```

```
  On Error GoTo VisaComError

  Dim strErrors As String

  myScope.WriteIEEEBlock command, data
  CheckInstrumentErrors

  Exit Sub

VisaComError:
  MsgBox "VISA COM Error: " + vbCrLf + CStr(Err.Number) + ", " + _
      Err.Source + ", " + _
      Err.Description, vbExclamation, "VISA COM Error"
  End

End Sub

Private Function DoQueryString(query As String) As String

  On Error GoTo VisaComError

  myScope.WriteString query
  DoQueryString = myScope.ReadString
  CheckInstrumentErrors

  Exit Function

VisaComError:
  MsgBox "VISA COM Error: " + vbCrLf + CStr(Err.Number) + ", " + _
      Err.Source + ", " + _
      Err.Description, vbExclamation, "VISA COM Error"
  End

End Function

Private Function DoQueryNumber(query As String) As Variant

  On Error GoTo VisaComError

  myScope.WriteString query
  DoQueryNumber = myScope.ReadNumber
  CheckInstrumentErrors

  Exit Function

VisaComError:
  MsgBox "VISA COM Error: " + vbCrLf + CStr(Err.Number) + ", " + _
      Err.Source + ", " + _
      Err.Description, vbExclamation, "VISA COM Error"
  End

End Function

Private Function DoQueryNumbers(query As String) As Variant()

  On Error GoTo VisaComError
```

```
  Dim strErrors As String

  myScope.WriteString query
  DoQueryNumbers = myScope.ReadList
  CheckInstrumentErrors

  Exit Function

VisaComError:
  MsgBox "VISA COM Error: " + vbCrLf + CStr(Err.Number) + ", " + _
      Err.Source + ", " + _
      Err.Description, vbExclamation, "VISA COM Error"
  End

End Function

Private Function DoQueryIEEEBlock_UI1(query As String) As Variant

  On Error GoTo VisaComError

  myScope.WriteString query
  DoQueryIEEEBlock_UI1 = myScope.ReadIEEEBlock(BinaryType_UI1)
  CheckInstrumentErrors

  Exit Function

VisaComError:
  MsgBox "VISA COM Error: " + vbCrLf + CStr(Err.Number) + ", " + _
      Err.Source + ", " + _
      Err.Description, vbExclamation, "VISA COM Error"
  End

End Function

Private Sub CheckInstrumentErrors()

  On Error GoTo VisaComError

  Dim strErrVal As String
  Dim strOut As String

  myScope.WriteString ":SYSTem:ERRor?"    ' Query any errors data.
  strErrVal = myScope.ReadString          ' Read: Errnum,"Error String".
  While Val(strErrVal) <> 0               ' End if find: 0,"No Error".
    strOut = strOut + "INST Error: " + strErrVal
    myScope.WriteString ":SYSTem:ERRor?"   ' Request error message.
    strErrVal = myScope.ReadString         ' Read error message.
  Wend

  If Not strOut = "" Then
    MsgBox strOut, vbExclamation, "INST Error Messages"
    myScope.FlushWrite (False)
    myScope.FlushRead

  End If

  Exit Sub
```

```
VisaComError:
  MsgBox "VISA COM Error: " + vbCrLf + Err.Description

End Sub
```

VISA COM Example in C#

To compile and run this example in Microsoft Visual Studio 2008:

1. Open Visual Studio.
2. Create a new Visual C#, Windows, Console Application project.
3. Cut-and-paste the code that follows into the C# source file.
4. Edit the program to use the VISA address of your oscilloscope.
5. Add a reference to the VISA COM 5.9 Type Library:
   a. Right-click the project you wish to modify (not the solution) in the Solution Explorer window of the Microsoft Visual Studio environment.
   b. Choose **Add Reference...**.
   c. In the Add Reference dialog, select the **COM** tab.
   d. Select **VISA COM 5.9 Type Library**; then click **OK**.
6. Build and run the program.

For more information, see the VISA COM Help that comes with Keysight IO Libraries Suite.

```
/*
 * Keysight VISA COM Example in C#
 * ------------------------------------------------------------------------
 * This program illustrates a few commonly used programming
 * features of your Keysight oscilloscope.
 * ------------------------------------------------------------------------
 */

using System;
using System.IO;
using System.Text;
using Ivi.Visa.Interop;
using System.Runtime.InteropServices;

namespace InfiniiVision
{
  class VisaComInstrumentApp
  {
    private static VisaComInstrument myScope;

    public static void Main(string[] args)
    {
      try
      {
        myScope = new
```

```
            VisaComInstrument("USB0::0x0957::0x17A6::US50210029::0::INSTR"
);
        myScope.SetTimeoutSeconds(10);

        // Initialize - start from a known state.
        Initialize();

        // Capture data.
        Capture();

        // Analyze the captured waveform.
        Analyze();
      }
      catch (System.ApplicationException err)
      {
        Console.WriteLine("*** VISA COM Error : " + err.Message);
      }
      catch (System.SystemException err)
      {
        Console.WriteLine("*** System Error Message : " + err.Message);
      }
      catch (System.Exception err)
      {
        System.Diagnostics.Debug.Fail("Unexpected Error");
        Console.WriteLine("*** Unexpected Error : " + err.Message);
      }
      finally
      {
        myScope.Close();
      }
    }

    /*
     * Initialize the oscilloscope to a known state.
     * -------------------------------------------------------------
     */
    private static void Initialize()
    {
      string strResults;

      // Get and display the device's *IDN? string.
      strResults = myScope.DoQueryString("*IDN?");
      Console.WriteLine("*IDN? result is: {0}", strResults);

      // Clear status and load the default setup.
      myScope.DoCommand("*CLS");
      myScope.DoCommand("*RST");
    }

    /*
     * Capture the waveform.
     * -------------------------------------------------------------
     */
    private static void Capture()
    {
      // Use auto-scale to automatically configure oscilloscope.
      myScope.DoCommand(":AUToscale");
```

```
        // Set trigger mode (EDGE, PULSe, PATTern, etc., and input source.
        myScope.DoCommand(":TRIGger:MODE EDGE");
        Console.WriteLine("Trigger mode: {0}",
            myScope.DoQueryString(":TRIGger:MODE?"));

        // Set EDGE trigger parameters.
        myScope.DoCommand(":TRIGger:EDGE:SOURCe CHANnel1");
        Console.WriteLine("Trigger edge source: {0}",
            myScope.DoQueryString(":TRIGger:EDGE:SOURce?"));

        myScope.DoCommand(":TRIGger:EDGE:LEVel 1.5");
        Console.WriteLine("Trigger edge level: {0}",
            myScope.DoQueryString(":TRIGger:EDGE:LEVel?"));

        myScope.DoCommand(":TRIGger:EDGE:SLOPe POSitive");
        Console.WriteLine("Trigger edge slope: {0}",
            myScope.DoQueryString(":TRIGger:EDGE:SLOPe?"));

        // Save oscilloscope configuration.
        byte[] ResultsArray;   // Results array.
        int nLength;   // Number of bytes returned from instrument.
        string strPath;

        // Query and read setup string.
        ResultsArray = myScope.DoQueryIEEEBlock(":SYSTem:SETup?");
        nLength = ResultsArray.Length;

        // Write setup string to file.
        strPath = "c:\\scope\\config\\setup.stp";
        FileStream fStream = File.Open(strPath, FileMode.Create);
        fStream.Write(ResultsArray, 0, nLength);
        fStream.Close();
        Console.WriteLine("Setup bytes saved: {0}", nLength);

        // Change settings with individual commands:

        // Set vertical scale and offset.
        myScope.DoCommand(":CHANnel1:SCALe 0.05");
        Console.WriteLine("Channel 1 vertical scale: {0}",
            myScope.DoQueryString(":CHANnel1:SCALe?"));

        myScope.DoCommand(":CHANnel1:OFFSet -1.5");
        Console.WriteLine("Channel 1 vertical offset: {0}",
            myScope.DoQueryString(":CHANnel1:OFFSet?"));

        // Set horizontal scale and offset.
        myScope.DoCommand(":TIMebase:SCALe 0.0002");
        Console.WriteLine("Timebase scale: {0}",
            myScope.DoQueryString(":TIMebase:SCALe?"));

        myScope.DoCommand(":TIMebase:POSition 0.0");
        Console.WriteLine("Timebase position: {0}",
            myScope.DoQueryString(":TIMebase:POSition?"));

        // Set the acquisition type (NORMal, PEAK, AVERage, or HRESolution
    ).
```

```
  myScope.DoCommand(":ACQuire:TYPE NORMal");
  Console.WriteLine("Acquire type: {0}",
      myScope.DoQueryString(":ACQuire:TYPE?"));

  // Or, configure by loading a previously saved setup.
  byte[] DataArray;
  int nBytesWritten;

  // Read setup string from file.
  strPath = "c:\\scope\\config\\setup.stp";
  DataArray = File.ReadAllBytes(strPath);
  nBytesWritten = DataArray.Length;

  // Restore setup string.
  myScope.DoCommandIEEEBlock(":SYSTem:SETup", DataArray);
  Console.WriteLine("Setup bytes restored: {0}", nBytesWritten);

  // Capture an acquisition using :DIGitize.
  myScope.DoCommand(":DIGitize CHANnel1");
}

/*
 * Analyze the captured waveform.
 * -------------------------------------------------------------------
 */
private static void Analyze()
{
  byte[] ResultsArray;   // Results array.
  int nLength;   // Number of bytes returned from instrument.
  string strPath;

  // Make a couple of measurements.
  // ----------------------------------------------------------
  myScope.DoCommand(":MEASure:SOURce CHANnel1");
  Console.WriteLine("Measure source: {0}",
      myScope.DoQueryString(":MEASure:SOURce?"));

  double fResult;
  myScope.DoCommand(":MEASure:FREQuency");
  fResult = myScope.DoQueryNumber(":MEASure:FREQuency?");
  Console.WriteLine("Frequency: {0:F4} kHz", fResult / 1000);

  myScope.DoCommand(":MEASure:VAMPlitude");
  fResult = myScope.DoQueryNumber(":MEASure:VAMPlitude?");
  Console.WriteLine("Vertical amplitude: {0:F2} V", fResult);

  // Download the screen image.
  // ----------------------------------------------------------
  myScope.DoCommand(":HARDcopy:INKSaver OFF");

  // Get the screen data.
  ResultsArray =
      myScope.DoQueryIEEEBlock(":DISPlay:DATA? PNG, COLor");
  nLength = ResultsArray.Length;

  // Store the screen data to a file.
  strPath = "c:\\scope\\data\\screen.png";
```

```
FileStream fStream = File.Open(strPath, FileMode.Create);
fStream.Write(ResultsArray, 0, nLength);
fStream.Close();
Console.WriteLine("Screen image ({0} bytes) written to {1}",
    nLength, strPath);

// Download waveform data.
// ------------------------------------------------------------

// Set the waveform points mode.
myScope.DoCommand(":WAVeform:POINts:MODE RAW");
Console.WriteLine("Waveform points mode: {0}",
    myScope.DoQueryString(":WAVeform:POINts:MODE?"));

// Get the number of waveform points available.
Console.WriteLine("Waveform points available: {0}",
    myScope.DoQueryString(":WAVeform:POINts?"));

// Set the waveform source.
myScope.DoCommand(":WAVeform:SOURce CHANnel1");
Console.WriteLine("Waveform source: {0}",
    myScope.DoQueryString(":WAVeform:SOURce?"));

// Choose the format of the data returned (WORD, BYTE, ASCII):
myScope.DoCommand(":WAVeform:FORMat BYTE");
Console.WriteLine("Waveform format: {0}",
    myScope.DoQueryString(":WAVeform:FORMat?"));

// Display the waveform settings:
double[] fResultsArray;
fResultsArray = myScope.DoQueryNumbers(":WAVeform:PREamble?");

double fFormat = fResultsArray[0];
if (fFormat == 0.0)
{
  Console.WriteLine("Waveform format: BYTE");
}
else if (fFormat == 1.0)
{
  Console.WriteLine("Waveform format: WORD");
}
else if (fFormat == 2.0)
{
  Console.WriteLine("Waveform format: ASCii");
}

double fType = fResultsArray[1];
if (fType == 0.0)
{
  Console.WriteLine("Acquire type: NORMal");
}
else if (fType == 1.0)
{
  Console.WriteLine("Acquire type: PEAK");
}
else if (fType == 2.0)
{
```

```
      Console.WriteLine("Acquire type: AVERage");
    }
    else if (fType == 3.0)
    {
      Console.WriteLine("Acquire type: HRESolution");
    }

    double fPoints = fResultsArray[2];
    Console.WriteLine("Waveform points: {0:e}", fPoints);

    double fCount = fResultsArray[3];
    Console.WriteLine("Waveform average count: {0:e}", fCount);

    double fXincrement = fResultsArray[4];
    Console.WriteLine("Waveform X increment: {0:e}", fXincrement);

    double fXorigin = fResultsArray[5];
    Console.WriteLine("Waveform X origin: {0:e}", fXorigin);

    double fXreference = fResultsArray[6];
    Console.WriteLine("Waveform X reference: {0:e}", fXreference);

    double fYincrement = fResultsArray[7];
    Console.WriteLine("Waveform Y increment: {0:e}", fYincrement);

    double fYorigin = fResultsArray[8];
    Console.WriteLine("Waveform Y origin: {0:e}", fYorigin);

    double fYreference = fResultsArray[9];
    Console.WriteLine("Waveform Y reference: {0:e}", fYreference);

    // Read waveform data.
    ResultsArray = myScope.DoQueryIEEEBlock(":WAVeform:DATA?");
    nLength = ResultsArray.Length;
    Console.WriteLine("Number of data values: {0}", nLength);

    // Set up output file:
    strPath = "c:\\scope\\data\\waveform_data.csv";
    if (File.Exists(strPath)) File.Delete(strPath);

    // Open file for output.
    StreamWriter writer = File.CreateText(strPath);

    // Output waveform data in CSV format.
    for (int i = 0; i < nLength - 1; i++)
      writer.WriteLine("{0:f9}, {1:f6}",
          fXorigin + ((float)i * fXincrement),
          (((float)ResultsArray[i] - fYreference)
          * fYincrement) + fYorigin);

    // Close output file.
    writer.Close();
    Console.WriteLine("Waveform format BYTE data written to {0}",
        strPath);
  }
}
```

```
class VisaComInstrument
{
  private ResourceManagerClass m_ResourceManager;
  private FormattedIO488Class m_IoObject;
  private string m_strVisaAddress;

  // Constructor.
  public VisaComInstrument(string strVisaAddress)
  {
    // Save VISA address in member variable.
    m_strVisaAddress = strVisaAddress;

    // Open the default VISA COM IO object.
    OpenIo();

    // Clear the interface.
    m_IoObject.IO.Clear();
  }

  public void DoCommand(string strCommand)
  {
    // Send the command.
    m_IoObject.WriteString(strCommand, true);

    // Check for inst errors.
    CheckInstrumentErrors(strCommand);
  }

  public void DoCommandIEEEBlock(string strCommand,
      byte[] DataArray)
  {
    // Send the command to the device.
    m_IoObject.WriteIEEEBlock(strCommand, DataArray, true);

    // Check for inst errors.
    CheckInstrumentErrors(strCommand);
  }

  public string DoQueryString(string strQuery)
  {
    // Send the query.
    m_IoObject.WriteString(strQuery, true);

    // Get the result string.
    string strResults;
    strResults = m_IoObject.ReadString();

    // Check for inst errors.
    CheckInstrumentErrors(strQuery);

    // Return results string.
    return strResults;
  }

  public double DoQueryNumber(string strQuery)
  {
    // Send the query.
```

```
  m_IoObject.WriteString(strQuery, true);

  // Get the result number.
  double fResult;
  fResult = (double)m_IoObject.ReadNumber(
    IEEEASCIIType.ASCIIType_R8, true);

  // Check for inst errors.
  CheckInstrumentErrors(strQuery);

  // Return result number.
  return fResult;
}

public double[] DoQueryNumbers(string strQuery)
{
  // Send the query.
  m_IoObject.WriteString(strQuery, true);

  // Get the result numbers.
  double[] fResultsArray;
  fResultsArray = (double[])m_IoObject.ReadList(
    IEEEASCIIType.ASCIIType_R8, ",;");

  // Check for inst errors.
  CheckInstrumentErrors(strQuery);

  // Return result numbers.
  return fResultsArray;
}

public byte[] DoQueryIEEEBlock(string strQuery)
{
  // Send the query.
  m_IoObject.WriteString(strQuery, true);

  // Get the results array.
  System.Threading.Thread.Sleep(2000); // Delay before reading.
  byte[] ResultsArray;
  ResultsArray = (byte[])m_IoObject.ReadIEEEBlock(
    IEEEBinaryType.BinaryType_UI1, false, true);

  // Check for inst errors.
  CheckInstrumentErrors(strQuery);

  // Return results array.
  return ResultsArray;
}

private void CheckInstrumentErrors(string strCommand)
{
  // Check for instrument errors.
  string strInstrumentError;
  bool bFirstError = true;

  do   // While not "0,No error".
  {
```

```
    m_IoObject.WriteString(":SYSTem:ERRor?", true);
    strInstrumentError = m_IoObject.ReadString();

    if (!strInstrumentError.ToString().StartsWith("+0,"))
    {
      if (bFirstError)
      {
        Console.WriteLine("ERROR(s) for command '{0}': ",
          strCommand);
        bFirstError = false;
      }
      Console.Write(strInstrumentError);
    }
  } while (!strInstrumentError.ToString().StartsWith("+0,"));
}

private void OpenIo()
{
  m_ResourceManager = new ResourceManagerClass();
  m_IoObject = new FormattedIO488Class();

  // Open the default VISA COM IO object.
  try
  {
    m_IoObject.IO =
      (IMessage)m_ResourceManager.Open(m_strVisaAddress,
      AccessMode.NO_LOCK, 0, "");
  }
  catch (Exception e)
  {
    Console.WriteLine("An error occurred: {0}", e.Message);
  }
}

public void SetTimeoutSeconds(int nSeconds)
{
  m_IoObject.IO.Timeout = nSeconds * 1000;
}

public void Close()
{
  try
  {
    m_IoObject.IO.Close();
  }
  catch { }

  try
  {
    Marshal.ReleaseComObject(m_IoObject);
  }
  catch { }

  try
  {
    Marshal.ReleaseComObject(m_ResourceManager);
  }
```

```
      catch { }
    }
  }
}
```

VISA COM Example in Visual Basic .NET

To compile and run this example in Microsoft Visual Studio 2008:

1. Open Visual Studio.
2. Create a new Visual Basic, Windows, Console Application project.
3. Cut-and-paste the code that follows into the Visual Basic .NET source file.
4. Edit the program to use the VISA address of your oscilloscope.
5. Add a reference to the VISA COM 5.9 Type Library:
   a. Right-click the project you wish to modify (not the solution) in the Solution Explorer window of the Microsoft Visual Studio environment.
   b. Choose **Add Reference...**.
   c. In the Add Reference dialog, select the **COM** tab.
   d. Select **VISA COM 5.9 Type Library**; then click **OK**.
   e. Right-click the project you wish to modify (not the solution) in the Solution Explorer window of the Microsoft Visual Studio environment and choose **Properties**; then, select "InfiniiVision.VisaComInstrumentApp" as the **Startup object**.
6. Build and run the program.

For more information, see the VISA COM Help that comes with Keysight IO Libraries Suite.

```
'
' Keysight VISA COM Example in Visual Basic .NET
' ----------------------------------------------------------------------
' This program illustrates a few commonly used programming
' features of your Keysight oscilloscope.
' ----------------------------------------------------------------------

Imports System
Imports System.IO
Imports System.Text
Imports Ivi.Visa.Interop
Imports System.Runtime.InteropServices

Namespace InfiniiVision
  Class VisaComInstrumentApp
    Private Shared myScope As VisaComInstrument

    Public Shared Sub Main(ByVal args As String())
      Try
        myScope = New  _
          VisaComInstrument("USB0::0x0957::0x17A6::US50210029::0::INSTR"
```

```
)
        myScope.SetTimeoutSeconds(10)

        ' Initialize - start from a known state.
        Initialize()

        ' Capture data.
        Capture()

        ' Analyze the captured waveform.
        Analyze()

      Catch err As System.ApplicationException
        Console.WriteLine("*** VISA Error Message : " + err.Message)
      Catch err As System.SystemException
        Console.WriteLine("*** System Error Message : " + err.Message)
      Catch err As System.Exception
        System.Diagnostics.Debug.Fail("Unexpected Error")
        Console.WriteLine("*** Unexpected Error : " + err.Message)
      Finally
        myScope.Close()
      End Try
    End Sub

    ' Initialize the oscilloscope to a known state.
    ' ------------------------------------------------------------------

    Private Shared Sub Initialize()
      Dim strResults As String

      ' Get and display the device's *IDN? string.
      strResults = myScope.DoQueryString("*IDN?")
      Console.WriteLine("*IDN? result is: {0}", strResults)

      ' Clear status and load the default setup.
      myScope.DoCommand("*CLS")
      myScope.DoCommand("*RST")

    End Sub

    ' Capture the waveform.
    ' ------------------------------------------------------------------

    Private Shared Sub Capture()

      ' Use auto-scale to automatically configure oscilloscope.
      myScope.DoCommand(":AUToscale")

      ' Set trigger mode (EDGE, PULSe, PATTern, etc., and input source.
      myScope.DoCommand(":TRIGger:MODE EDGE")
      Console.WriteLine("Trigger mode: {0}", _
          myScope.DoQueryString(":TRIGger:MODE?"))

      ' Set EDGE trigger parameters.
      myScope.DoCommand(":TRIGger:EDGE:SOURCe CHANnel1")
      Console.WriteLine("Trigger edge source: {0}", _
          myScope.DoQueryString(":TRIGger:EDGE:SOURce?"))
```

```
myScope.DoCommand(":TRIGger:EDGE:LEVel 1.5")
Console.WriteLine("Trigger edge level: {0}", _
    myScope.DoQueryString(":TRIGger:EDGE:LEVel?"))

myScope.DoCommand(":TRIGger:EDGE:SLOPe POSitive")
Console.WriteLine("Trigger edge slope: {0}", _
    myScope.DoQueryString(":TRIGger:EDGE:SLOPe?"))

' Save oscilloscope configuration.
Dim ResultsArray As Byte()   ' Results array.
Dim nLength As Integer   ' Number of bytes returned from inst.
Dim strPath As String
Dim fStream As FileStream

' Query and read setup string.
ResultsArray = myScope.DoQueryIEEEBlock(":SYSTem:SETup?")
nLength = ResultsArray.Length

' Write setup string to file.
strPath = "c:\scope\config\setup.stp"
fStream = File.Open(strPath, FileMode.Create)
fStream.Write(ResultsArray, 0, nLength)
fStream.Close()
Console.WriteLine("Setup bytes saved: {0}", nLength)

' Change settings with individual commands:

' Set vertical scale and offset.
myScope.DoCommand(":CHANnel1:SCALe 0.05")
Console.WriteLine("Channel 1 vertical scale: {0}", _
    myScope.DoQueryString(":CHANnel1:SCALe?"))

myScope.DoCommand(":CHANnel1:OFFSet -1.5")
Console.WriteLine("Channel 1 vertical offset: {0}", _
    myScope.DoQueryString(":CHANnel1:OFFSet?"))

' Set horizontal scale and offset.
myScope.DoCommand(":TIMebase:SCALe 0.0002")
Console.WriteLine("Timebase scale: {0}", _
    myScope.DoQueryString(":TIMebase:SCALe?"))

myScope.DoCommand(":TIMebase:POSition 0.0")
Console.WriteLine("Timebase position: {0}", _
    myScope.DoQueryString(":TIMebase:POSition?"))

' Set the acquisition type (NORMal, PEAK, AVERage, or HRESolution)
.
myScope.DoCommand(":ACQuire:TYPE NORMal")
Console.WriteLine("Acquire type: {0}", _
    myScope.DoQueryString(":ACQuire:TYPE?"))

' Or, configure by loading a previously saved setup.
Dim DataArray As Byte()
Dim nBytesWritten As Integer

' Read setup string from file.
```

```
        strPath = "c:\scope\config\setup.stp"
        DataArray = File.ReadAllBytes(strPath)
        nBytesWritten = DataArray.Length

        ' Restore setup string.
        myScope.DoCommandIEEEBlock(":SYSTem:SETup", DataArray)
        Console.WriteLine("Setup bytes restored: {0}", nBytesWritten)

        ' Capture an acquisition using :DIGitize.
        myScope.DoCommand(":DIGitize CHANnel1")

    End Sub

    ' Analyze the captured waveform.
    ' --------------------------------------------------------------

    Private Shared Sub Analyze()

        Dim fResult As Double
        Dim ResultsArray As Byte()   ' Results array.
        Dim nLength As Integer   ' Number of bytes returned from inst.
        Dim strPath As String

        ' Make a couple of measurements.
        ' --------------------------------------------------------------
        myScope.DoCommand(":MEASure:SOURce CHANnel1")
        Console.WriteLine("Measure source: {0}", _
            myScope.DoQueryString(":MEASure:SOURce?"))

        myScope.DoCommand(":MEASure:FREQuency")
        fResult = myScope.DoQueryNumber(":MEASure:FREQuency?")
        Console.WriteLine("Frequency: {0:F4} kHz", fResult / 1000)

        myScope.DoCommand(":MEASure:VAMPlitude")
        fResult = myScope.DoQueryNumber(":MEASure:VAMPlitude?")
        Console.WriteLine("Vertical amplitude: {0:F2} V", fResult)

        ' Download the screen image.
        ' --------------------------------------------------------------
        myScope.DoCommand(":HARDcopy:INKSaver OFF")

        ' Get the screen data.
        ResultsArray = myScope.DoQueryIEEEBlock(":DISPlay:DATA? PNG, COLor
")
        nLength = ResultsArray.Length

        ' Store the screen data to a file.
        strPath = "c:\scope\data\screen.png"
        Dim fStream As FileStream
        fStream = File.Open(strPath, FileMode.Create)
        fStream.Write(ResultsArray, 0, nLength)
        fStream.Close()
        Console.WriteLine("Screen image ({0} bytes) written to {1}", _
            nLength, strPath)

        ' Download waveform data.
        ' --------------------------------------------------------------
```

```
' Set the waveform points mode.
myScope.DoCommand(":WAVeform:POINts:MODE RAW")
Console.WriteLine("Waveform points mode: {0}", _
    myScope.DoQueryString(":WAVeform:POINts:MODE?"))

' Get the number of waveform points available.
Console.WriteLine("Waveform points available: {0}", _
    myScope.DoQueryString(":WAVeform:POINts?"))

' Set the waveform source.
myScope.DoCommand(":WAVeform:SOURce CHANnel1")
Console.WriteLine("Waveform source: {0}", _
    myScope.DoQueryString(":WAVeform:SOURce?"))

' Choose the format of the data returned (WORD, BYTE, ASCII):
myScope.DoCommand(":WAVeform:FORMat BYTE")
Console.WriteLine("Waveform format: {0}", _
    myScope.DoQueryString(":WAVeform:FORMat?"))

' Display the waveform settings:
Dim fResultsArray As Double()
fResultsArray = myScope.DoQueryNumbers(":WAVeform:PREamble?")

Dim fFormat As Double = fResultsArray(0)
If fFormat = 0 Then
  Console.WriteLine("Waveform format: BYTE")
ElseIf fFormat = 1 Then
  Console.WriteLine("Waveform format: WORD")
ElseIf fFormat = 2 Then
  Console.WriteLine("Waveform format: ASCii")
End If

Dim fType As Double = fResultsArray(1)
If fType = 0 Then
  Console.WriteLine("Acquire type: NORMal")
ElseIf fType = 1 Then
  Console.WriteLine("Acquire type: PEAK")
ElseIf fType = 2 Then
  Console.WriteLine("Acquire type: AVERage")
ElseIf fType = 3 Then
  Console.WriteLine("Acquire type: HRESolution")
End If

Dim fPoints As Double = fResultsArray(2)
Console.WriteLine("Waveform points: {0:e}", fPoints)

Dim fCount As Double = fResultsArray(3)
Console.WriteLine("Waveform average count: {0:e}", fCount)

Dim fXincrement As Double = fResultsArray(4)
Console.WriteLine("Waveform X increment: {0:e}", fXincrement)

Dim fXorigin As Double = fResultsArray(5)
Console.WriteLine("Waveform X origin: {0:e}", fXorigin)

Dim fXreference As Double = fResultsArray(6)
```

```
    Console.WriteLine("Waveform X reference: {0:e}", fXreference)

    Dim fYincrement As Double = fResultsArray(7)
    Console.WriteLine("Waveform Y increment: {0:e}", fYincrement)

    Dim fYorigin As Double = fResultsArray(8)
    Console.WriteLine("Waveform Y origin: {0:e}", fYorigin)

    Dim fYreference As Double = fResultsArray(9)
    Console.WriteLine("Waveform Y reference: {0:e}", fYreference)

    ' Get the waveform data.
    ResultsArray = myScope.DoQueryIEEEBlock(":WAVeform:DATA?")
    nLength = ResultsArray.Length
    Console.WriteLine("Number of data values: {0}", nLength)

    ' Set up output file:
    strPath = "c:\scope\data\waveform_data.csv"
    If File.Exists(strPath) Then
      File.Delete(strPath)
    End If

    ' Open file for output.
    Dim writer As StreamWriter = File.CreateText(strPath)

    ' Output waveform data in CSV format.
    For index As Integer = 0 To nLength - 1
      ' Write time value, voltage value.
      writer.WriteLine("{0:f9}, {1:f6}", _
          fXorigin + (CSng(index) * fXincrement), _
          ((CSng(ResultsArray(index)) - fYreference) _
          * fYincrement) + fYorigin)
    Next

    ' Close output file.
    writer.Close()
    Console.WriteLine("Waveform format BYTE data written to {0}", _
        strPath)

  End Sub

End Class

Class VisaComInstrument
  Private m_ResourceManager As ResourceManagerClass
  Private m_IoObject As FormattedIO488Class
  Private m_strVisaAddress As String

  ' Constructor.
  Public Sub New(ByVal strVisaAddress As String)

    ' Save VISA address in member variable.
    m_strVisaAddress = strVisaAddress

    ' Open the default VISA COM IO object.
    OpenIo()
```

```
  ' Clear the interface.
  m_IoObject.IO.Clear()

End Sub

Public Sub DoCommand(ByVal strCommand As String)

  ' Send the command.
  m_IoObject.WriteString(strCommand, True)

  ' Check for inst errors.
  CheckInstrumentErrors(strCommand)

End Sub

Public Sub DoCommandIEEEBlock(ByVal strCommand As String, _
    ByVal DataArray As Byte())

  ' Send the command to the device.
  m_IoObject.WriteIEEEBlock(strCommand, DataArray, True)

  ' Check for inst errors.
  CheckInstrumentErrors(strCommand)

End Sub

Public Function DoQueryString(ByVal strQuery As String) As String
  ' Send the query.
  m_IoObject.WriteString(strQuery, True)

  ' Get the result string.
  Dim strResults As String
  strResults = m_IoObject.ReadString()

  ' Check for inst errors.
  CheckInstrumentErrors(strQuery)

  ' Return results string.
  Return strResults
End Function

Public Function DoQueryNumber(ByVal strQuery As String) As Double
  ' Send the query.
  m_IoObject.WriteString(strQuery, True)

  ' Get the result number.
  Dim fResult As Double
  fResult = _
      CDbl(m_IoObject.ReadNumber(IEEEASCIIType.ASCIIType_R8, True))

  ' Check for inst errors.
  CheckInstrumentErrors(strQuery)

  ' Return result number.
  Return fResult
End Function
```

```
Public Function DoQueryNumbers(ByVal strQuery As String) As _
    Double()
  ' Send the query.
  m_IoObject.WriteString(strQuery, True)

  ' Get the result numbers.
  Dim fResultsArray As Double()
  fResultsArray = _
      m_IoObject.ReadList(IEEEASCIIType.ASCIIType_R8, ",;")

  ' Check for inst errors.
  CheckInstrumentErrors(strQuery)

  ' Return result numbers.
  Return fResultsArray
End Function

Public _
    Function DoQueryIEEEBlock(ByVal strQuery As String) As Byte()
  ' Send the query.
  m_IoObject.WriteString(strQuery, True)

  ' Get the results array.
  System.Threading.Thread.Sleep(2000) ' Delay before reading data.
  Dim ResultsArray As Byte()
  ResultsArray = _
      m_IoObject.ReadIEEEBlock(IEEEBinaryType.BinaryType_UI1, _
      False, True)

  ' Check for inst errors.
  CheckInstrumentErrors(strQuery)

  ' Return results array.
  Return ResultsArray
End Function

Private Sub CheckInstrumentErrors(ByVal strCommand As String)
  ' Check for instrument errors.
  Dim strInstrumentError As String
  Dim bFirstError As Boolean = True
  Do   ' While not "0,No error".
    m_IoObject.WriteString(":SYSTem:ERRor?", True)
    strInstrumentError = m_IoObject.ReadString()

    If Not strInstrumentError.ToString().StartsWith("+0,") Then
      If bFirstError Then
        Console.WriteLine("ERROR(s) for command '{0}': ", _
            strCommand)
        bFirstError = False
      End If
      Console.Write(strInstrumentError)
    End If
  Loop While Not strInstrumentError.ToString().StartsWith("+0,")
End Sub

Private Sub OpenIo()
  m_ResourceManager = New ResourceManagerClass()
```

```
    m_IoObject = New FormattedIO488Class()

    ' Open the default VISA COM IO object.
    Try
      m_IoObject.IO = _
          DirectCast(m_ResourceManager.Open(m_strVisaAddress, _
              AccessMode.NO_LOCK, 0, ""), IMessage)
    Catch e As Exception
      Console.WriteLine("An error occurred: {0}", e.Message)
    End Try
  End Sub

  Public Sub SetTimeoutSeconds(ByVal nSeconds As Integer)
    m_IoObject.IO.Timeout = nSeconds * 1000
  End Sub

  Public Sub Close()
    Try
      m_IoObject.IO.Close()
    Catch
    End Try

    Try
      Marshal.ReleaseComObject(m_IoObject)
    Catch
    End Try

    Try
      Marshal.ReleaseComObject(m_ResourceManager)
    Catch
    End Try
  End Sub
 End Class
End Namespace
```

VISA COM Example in Python 3

You can use the Python programming language with the "comtypes" package to control Keysight oscilloscopes.

The Python language and "comtypes" package can be downloaded from the web at http://www.python.org/ and https://pypi.org/project/comtypes/, respectively.

To run this example with Python and "comtypes":

1. Cut-and-paste the code that follows into a file named "example.py".
2. Edit the program to use the VISA address of your oscilloscope.
3. If "python.exe" can be found via your PATH environment variable, open a Command Prompt window; then, change to the folder that contains the "example.py" file, and enter:

```
python example.py
```

```
#!python3
#
```

```
# Keysight VISA COM Example in Python using "comtypes"
# ******************************************************
# This program illustrates a few commonly used programming
# features of your Keysight oscilloscope.
# ******************************************************

# Import Python modules.
# ----------------------------------------------------------
import string
import time
import sys
import array

from comtypes.client import GetModule
from comtypes.client import CreateObject

# Run GetModule once to generate comtypes.gen.VisaComLib.
if not hasattr(sys, "frozen"):
 GetModule("C:\Program Files (x86)\IVI Foundation\VISA\VisaCom\
GlobMgr.dll")

import comtypes.gen.VisaComLib as VisaComLib


# Global variables (booleans: 0 = False, 1 = True).
# ----------------------------------------------------------


# ==========================================================
# Initialize:
# ==========================================================
def initialize():
 # Get and display the device's *IDN? string.
 idn_string = do_query_string("*IDN?")
 print("Identification string '%s'" % idn_string)

 # Clear status and load the default setup.
 do_command("*CLS")
 do_command("*RST")


# ==========================================================
# Capture:
# ==========================================================
def capture():

 # Use auto-scale to automatically set up oscilloscope.
 print("Autoscale.")
 do_command(":AUToscale")

 # Set trigger mode.
 do_command(":TRIGger:MODE EDGE")
 qresult = do_query_string(":TRIGger:MODE?")
 print("Trigger mode: %s" % qresult)

 # Set EDGE trigger parameters.
 do_command(":TRIGger:EDGE:SOURce CHANnel1")
```

```
qresult = do_query_string(":TRIGger:EDGE:SOURce?")
print("Trigger edge source: %s" % qresult)

do_command(":TRIGger:EDGE:LEVel 1.5")
qresult = do_query_string(":TRIGger:EDGE:LEVel?")
print("Trigger edge level: %s" % qresult)

do_command(":TRIGger:EDGE:SLOPe POSitive")
qresult = do_query_string(":TRIGger:EDGE:SLOPe?")
print("Trigger edge slope: %s" % qresult)

# Save oscilloscope setup.
setup_bytes = do_query_ieee_block(":SYSTem:SETup?")
nLength = len(setup_bytes)
f = open("setup.stp", "wb")
f.write(bytearray(setup_bytes))
f.close()
print("Setup bytes saved: %d" % nLength)

# Change oscilloscope settings with individual commands:

# Set vertical scale and offset.
do_command(":CHANnel1:SCALe 0.05")
qresult = do_query_number(":CHANnel1:SCALe?")
print("Channel 1 vertical scale: %f" % qresult)

do_command(":CHANnel1:OFFSet -1.5")
qresult = do_query_number(":CHANnel1:OFFSet?")
print("Channel 1 offset: %f" % qresult)

# Set horizontal scale and offset.
do_command(":TIMebase:SCALe 0.0002")
qresult = do_query_string(":TIMebase:SCALe?")
print("Timebase scale: %s" % qresult)

do_command(":TIMebase:POSition 0.0")
qresult = do_query_string(":TIMebase:POSition?")
print("Timebase position: %s" % qresult)

# Set the acquisition type.
do_command(":ACQuire:TYPE NORMal")
qresult = do_query_string(":ACQuire:TYPE?")
print("Acquire type: %s" % qresult)

# Or, configure by loading a previously saved setup.
f = open("setup.stp", "rb")
setup_bytes = f.read()
f.close()
do_command_ieee_block(":SYSTem:SETup", array.array('B', setup_bytes))
print("Setup bytes restored: %d" % len(setup_bytes))

# Capture an acquisition using :DIGitize.
do_command(":DIGitize CHANnel1")


# ============================================================
# Analyze:
```

```
# ========================================================
def analyze():

 # Make measurements.
 # --------------------------------------------------------
 do_command(":MEASure:SOURce CHANnel1")
 qresult = do_query_string(":MEASure:SOURce?")
 print("Measure source: %s" % qresult)

 do_command(":MEASure:FREQuency")
 qresult = do_query_string(":MEASure:FREQuency?")
 print("Measured frequency on channel 1: %s" % qresult)

 do_command(":MEASure:VAMPlitude")
 qresult = do_query_string(":MEASure:VAMPlitude?")
 print("Measured vertical amplitude on channel 1: %s" % qresult)

 # Download the screen image.
 # --------------------------------------------------------
 do_command(":HARDcopy:INKSaver OFF")

 image_bytes = do_query_ieee_block(":DISPlay:DATA? PNG, COLor")
 nLength = len(image_bytes)
 f = open("screen.png", "wb")
 f.write(bytearray(image_bytes))
 f.close()
 print("Screen image written to screen.png.")

 # Download waveform data.
 # --------------------------------------------------------

 # Set the waveform points mode.
 do_command(":WAVeform:POINts:MODE RAW")
 qresult = do_query_string(":WAVeform:POINts:MODE?")
 print("Waveform points mode: %s" % qresult)

 # Get the number of waveform points available.
 do_command(":WAVeform:POINts 10240")
 qresult = do_query_string(":WAVeform:POINts?")
 print("Waveform points available: %s" % qresult)

 # Set the waveform source.
 do_command(":WAVeform:SOURce CHANnel1")
 qresult = do_query_string(":WAVeform:SOURce?")
 print("Waveform source: %s" % qresult)

 # Choose the format of the data returned:
 do_command(":WAVeform:FORMat BYTE")
 print("Waveform format: %s" % do_query_string(":WAVeform:FORMat?"))

 # Display the waveform settings from preamble:
 wav_form_dict = {
  0 : "BYTE",
  1 : "WORD",
  4 : "ASCii",
 }
 acq_type_dict = {
```

```
 0 : "NORMal",
 1 : "PEAK",
 2 : "AVERage",
 3 : "HRESolution",
}

(
 wav_form,
 acq_type,
 wfmpts,
 avgcnt,
 x_increment,
 x_origin,
 x_reference,
 y_increment,
 y_origin,
 y_reference
) = do_query_numbers(":WAVeform:PREamble?")

print("Waveform format: %s" % wav_form_dict[wav_form])
print("Acquire type: %s" % acq_type_dict[acq_type])
print("Waveform points desired: %d" % wfmpts)
print("Waveform average count: %d" % avgcnt)
print("Waveform X increment: %1.12f" % x_increment)
print("Waveform X origin: %1.9f" % x_origin)
print("Waveform X reference: %d" % x_reference)   # Always 0.
print("Waveform Y increment: %f" % y_increment)
print("Waveform Y origin: %f" % y_origin)
print("Waveform Y reference: %d" % y_reference)   # Always 125.

# Get numeric values for later calculations.
x_increment = do_query_number(":WAVeform:XINCrement?")
x_origin = do_query_number(":WAVeform:XORigin?")
y_increment = do_query_number(":WAVeform:YINCrement?")
y_origin = do_query_number(":WAVeform:YORigin?")
y_reference = do_query_number(":WAVeform:YREFerence?")

# Get the waveform data.
data_bytes = do_query_ieee_block(":WAVeform:DATA?")
nLength = len(data_bytes)
print("Number of data values: %d" % nLength)

# Open file for output.
strPath = "waveform_data.csv"
f = open(strPath, "w")

# Output waveform data in CSV format.
for i in range(0, nLength - 1):
 time_val = x_origin + (i * x_increment)
 voltage = (data_bytes[i] - y_reference) * y_increment + y_origin
 f.write("%E, %f\n" % (time_val, voltage))

# Close output file.
f.close()
print("Waveform format BYTE data written to %s." % strPath)
```

```
# ==========================================================
# Send a command and check for errors:
# ==========================================================
def do_command(command):
 myScope.WriteString("%s" % command, True)
 check_instrument_errors(command)


# ==========================================================
# Send a command and check for errors:
# ==========================================================
def do_command_ieee_block(command, data):
 myScope.WriteIEEEBlock(command, data, True)
 check_instrument_errors(command)


# ==========================================================
# Send a query, check for errors, return string:
# ==========================================================
def do_query_string(query):
 myScope.WriteString("%s" % query, True)
 result = myScope.ReadString()
 check_instrument_errors(query)
 return result


# ==========================================================
# Send a query, check for errors, return string:
# ==========================================================
def do_query_ieee_block(query):
 myScope.WriteString("%s" % query, True)
 result = myScope.ReadIEEEBlock(VisaComLib.BinaryType_UI1, \
   False, True)
 check_instrument_errors(query)
 return result


# ==========================================================
# Send a query, check for errors, return values:
# ==========================================================
def do_query_number(query):
 myScope.WriteString("%s" % query, True)
 result = myScope.ReadNumber(VisaComLib.ASCIIType_R8, True)
 check_instrument_errors(query)
 return result


# ==========================================================
# Send a query, check for errors, return values:
# ==========================================================
def do_query_numbers(query):
 myScope.WriteString("%s" % query, True)
 result = myScope.ReadList(VisaComLib.ASCIIType_R8, ",;")
 check_instrument_errors(query)
 return result
```

```
# ========================================================
# Check for instrument errors:
# ========================================================
def check_instrument_errors(command):

 while True:
  myScope.WriteString(":SYSTem:ERRor?", True)
  error_string = myScope.ReadString()
  if error_string:   # If there is an error string value.

   if error_string.find("+0,", 0, 3) == -1:   # Not "No error".
    print("ERROR: %s, command: '%s'" % (error_string, command))
    print("Exited because of error.")
    sys.exit(1)

   else:   # "No error"
    break

  else:   # :SYSTem:ERRor? should always return string.
   print("ERROR: :SYSTem:ERRor? returned nothing, command: '%s'" \
     % command)
   print("Exited because of error.")
   sys.exit(1)


# ========================================================
# Main program:
# ========================================================
rm = CreateObject("VISA.GlobalRM", \
 interface=VisaComLib.IResourceManager)
myScope = CreateObject("VISA.BasicFormattedIO", \
 interface=VisaComLib.IFormattedIO488)
myScope.IO = \
 rm.Open("TCPIP0::141.121.237.208::hislip0::INSTR")

# Clear the interface.
myScope.IO.Clear()
print("Interface cleared.")

# Set the Timeout to 15 seconds.
myScope.IO.Timeout = 15000   # 15 seconds.
print("Timeout set to 15000 milliseconds.")

# Initialize the oscilloscope, capture data, and analyze.
initialize()
capture()
analyze()

myScope.IO.Close()
print("End of program")
sys.exit()
```

VISA Examples

- "VISA Example in C" on page 871
- "VISA Example in Visual Basic" on page 880
- "VISA Example in C#" on page 890
- "VISA Example in Visual Basic .NET" on page 901
- "VISA Example in Python 3" on page 911

VISA Example in C

To compile and run this example in Microsoft Visual Studio 2008:

1. Open Visual Studio.
2. Create a new Visual C++, Win32, Win32 Console Application project.
3. In the Win32 Application Wizard, click **Next >**. Then, check **Empty project**, and click **Finish**.
4. Cut-and-paste the code that follows into a file named "example.c" in the project directory.
5. In Visual Studio 2008, right-click the Source Files folder, choose **Add > Add Existing Item...**, select the example.c file, and click **Add**.
6. Edit the program to use the VISA address of your oscilloscope.
7. Choose **Project > Properties...**. In the Property Pages dialog, update these project settings:
   a. Under Configuration Properties, Linker, Input, add "visa32.lib" to the Additional Dependencies field.
   b. Under Configuration Properties, C/C++, Code Generation, select Multi-threaded DLL for the Runtime Library field.
   c. Click **OK** to close the Property Pages dialog.
8. Add the include files and library files search paths:
   a. Choose **Tools > Options...**.
   b. In the Options dialog, under Projects and Solutions, select **VC++ Directories**.
   c. Show directories for **Include files**, and add the include directory (for example, Program Files (x86)\IVI Foundation\VISA\WinNT\Include).
   d. Show directories for **Library files**, and add the library files directory (for example, Program Files (x86)\IVI Foundation\VISA\WinNT\lib\msc).
   e. Click **OK** to close the Options dialog.
9. Build and run the program.

```
/*
 * Keysight VISA Example in C
 * ----------------------------------------------------------------------
```

```
 * This program illustrates a few commonly-used programming
 * features of your Keysight oscilloscope.
 */

#include <stdio.h>            /* For printf(). */
#include <string.h>           /* For strcpy(), strcat(). */
#include <time.h>             /* For clock(). */
#include <visa.h>             /* Keysight VISA routines. */

#define VISA_ADDRESS "USB0::0x0957::0x17A6::US50210029::0::INSTR"
#define IEEEBLOCK_SPACE 5000000

/* Function prototypes */
void initialize(void);          /* Initialize to known state. */
void capture(void);             /* Capture the waveform. */
void analyze(void);             /* Analyze the captured waveform. */

void do_command(char *command);        /* Send command. */
int do_command_ieeeblock(char *command); /* Command w/IEEE block. */
void do_query_string(char *query);     /* Query for string. */
void do_query_number(char *query);     /* Query for number. */
void do_query_numbers(char *query);     /* Query for numbers. */
int do_query_ieeeblock(char *query);   /* Query for IEEE block. */
void check_instrument_errors();        /* Check for inst errors. */
void error_handler();                  /* VISA error handler. */

/* Global variables */
ViSession defaultRM, vi;        /* Device session ID. */
ViStatus err;                   /* VISA function return value. */
char str_result[256] = {0};     /* Result from do_query_string(). */
double num_result;              /* Result from do_query_number(). */
unsigned char ieeeblock_data[IEEEBLOCK_SPACE];   /* Result from
                                   do_query_ieeeblock(). */
double dbl_results[10];         /* Result from do_query_numbers(). */

/* Main Program
 * ---------------------------------------------------------------- */
void main(void)
{
  /* Open the default resource manager session. */
  err = viOpenDefaultRM(&defaultRM);
  if (err != VI_SUCCESS) error_handler();

  /* Open the session using the oscilloscope's VISA address. */
  err = viOpen(defaultRM, VISA_ADDRESS, VI_NULL, VI_NULL, &vi);
  if (err != VI_SUCCESS) error_handler();

/* Set the I/O timeout to fifteen seconds. */
err = viSetAttribute(vi, VI_ATTR_TMO_VALUE, 15000);
  if (err != VI_SUCCESS) error_handler();

  /* Initialize - start from a known state. */
  initialize();

  /* Capture data. */
  capture();
```

```
  /* Analyze the captured waveform. */
  analyze();

  /* Close the vi session and the resource manager session. */
  viClose(vi);
  viClose(defaultRM);
}

/* Initialize the oscilloscope to a known state.
 * ------------------------------------------------------------------- */
void initialize (void)
{
  /* Clear the interface. */
  err = viClear(vi);
  if (err != VI_SUCCESS) error_handler();

  /* Get and display the device's *IDN? string. */
  do_query_string("*IDN?");
  printf("Oscilloscope *IDN? string: %s\n", str_result);

  /* Clear status and load the default setup. */
  do_command("*CLS");
  do_command("*RST");
}

/* Capture the waveform.
 * ------------------------------------------------------------------- */
void capture (void)
{
  int num_bytes;
  FILE *fp;

  /* Use auto-scale to automatically configure oscilloscope. */
  do_command(":AUToscale");

  /* Set trigger mode (EDGE, PULSe, PATTern, etc., and input source. */
  do_command(":TRIGger:MODE EDGE");
  do_query_string(":TRIGger:MODE?");
  printf("Trigger mode: %s\n", str_result);

  /* Set EDGE trigger parameters. */
  do_command(":TRIGger:EDGE:SOURCe CHANnel1");
  do_query_string(":TRIGger:EDGE:SOURce?");
  printf("Trigger edge source: %s\n", str_result);

  do_command(":TRIGger:EDGE:LEVel 1.5");
  do_query_string(":TRIGger:EDGE:LEVel?");
  printf("Trigger edge level: %s\n", str_result);

  do_command(":TRIGger:EDGE:SLOPe POSitive");
  do_query_string(":TRIGger:EDGE:SLOPe?");
  printf("Trigger edge slope: %s\n", str_result);

  /* Save oscilloscope configuration. */

  /* Read system setup. */
  num_bytes = do_query_ieeeblock(":SYSTem:SETup?");
```

```
  printf("Read setup string query (%d bytes).\n", num_bytes);

  /* Write setup string to file. */
  fp = fopen ("c:\\scope\\config\\setup.stp", "wb");
  num_bytes = fwrite(ieeeblock_data, sizeof(unsigned char), num_bytes,
    fp);
  fclose (fp);
  printf("Wrote setup string (%d bytes) to ", num_bytes);
  printf("c:\\scope\\config\\setup.stp.\n");

  /* Change settings with individual commands:

  /* Set vertical scale and offset. */
  do_command(":CHANnel1:SCALe 0.05");
  do_query_string(":CHANnel1:SCALe?");
  printf("Channel 1 vertical scale: %s\n", str_result);

  do_command(":CHANnel1:OFFSet -1.5");
  do_query_string(":CHANnel1:OFFSet?");
  printf("Channel 1 offset: %s\n", str_result);

  /* Set horizontal scale and offset. */
  do_command(":TIMebase:SCALe 0.0002");
  do_query_string(":TIMebase:SCALe?");
  printf("Timebase scale: %s\n", str_result);

  do_command(":TIMebase:POSition 0.0");
  do_query_string(":TIMebase:POSition?");
  printf("Timebase position: %s\n", str_result);

  /* Set the acquisition type (NORMal, PEAK, AVERage, or HRESolution). *
/
  do_command(":ACQuire:TYPE NORMal");
  do_query_string(":ACQuire:TYPE?");
  printf("Acquire type: %s\n", str_result);

  /* Or, configure by loading a previously saved setup. */

  /* Read setup string from file. */
  fp = fopen ("c:\\scope\\config\\setup.stp", "rb");
  num_bytes = fread (ieeeblock_data, sizeof(unsigned char),
    IEEEBLOCK_SPACE, fp);
  fclose (fp);
  printf("Read setup string (%d bytes) from file ", num_bytes);
  printf("c:\\scope\\config\\setup.stp.\n");

  /* Restore setup string. */
  num_bytes = do_command_ieeeblock(":SYSTem:SETup", num_bytes);
  printf("Restored setup string (%d bytes).\n", num_bytes);

  /* Capture an acquisition using :DIGitize. */
  do_command(":DIGitize CHANnel1");
}

/* Analyze the captured waveform.
 * ------------------------------------------------------------------- */
void analyze (void)
```

```
{
  double wav_format;
  double acq_type;
  double wav_points;
  double avg_count;
  double x_increment;
  double x_origin;
  double x_reference;
  double y_increment;
  double y_origin;
  double y_reference;

  FILE *fp;
  int num_bytes;   /* Number of bytes returned from instrument. */
  int i;

  /* Make a couple of measurements.
   * ---------------------------------------------------------- */
  do_command(":MEASure:SOURce CHANnel1");
  do_query_string(":MEASure:SOURce?");
  printf("Measure source: %s\n", str_result);

  do_command(":MEASure:FREQuency");
  do_query_number(":MEASure:FREQuency?");
  printf("Frequency: %.4f kHz\n", num_result / 1000);

  do_command(":MEASure:VAMPlitude");
  do_query_number(":MEASure:VAMPlitude?");
  printf("Vertical amplitude: %.2f V\n", num_result);

  /* Download the screen image.
   * ---------------------------------------------------------- */
  do_command(":HARDcopy:INKSaver OFF");

  /* Read screen image. */
  num_bytes = do_query_ieeeblock(":DISPlay:DATA? PNG, COLor");
  printf("Screen image bytes: %d\n", num_bytes);

  /* Write screen image bytes to file. */
  fp = fopen ("c:\\scope\\data\\screen.png", "wb");
  num_bytes = fwrite(ieeeblock_data, sizeof(unsigned char), num_bytes,
    fp);
  fclose (fp);
  printf("Wrote screen image (%d bytes) to ", num_bytes);
  printf("c:\\scope\\data\\screen.png.\n");

  /* Download waveform data.
   * ---------------------------------------------------------- */

  /* Set the waveform points mode. */
  do_command(":WAVeform:POINts:MODE RAW");
  do_query_string(":WAVeform:POINts:MODE?");
  printf("Waveform points mode: %s\n", str_result);

  /* Get the number of waveform points available. */
  do_query_string(":WAVeform:POINts?");
  printf("Waveform points available: %s\n", str_result);
```

```
/* Set the waveform source. */
do_command(":WAVeform:SOURce CHANnel1");
do_query_string(":WAVeform:SOURce?");
printf("Waveform source: %s\n", str_result);

/* Choose the format of the data returned (WORD, BYTE, ASCII): */
do_command(":WAVeform:FORMat BYTE");
do_query_string(":WAVeform:FORMat?");
printf("Waveform format: %s\n", str_result);

/* Display the waveform settings: */
do_query_numbers(":WAVeform:PREamble?");

wav_format = dbl_results[0];
if (wav_format == 0.0)
{
  printf("Waveform format: BYTE\n");
}
else if (wav_format == 1.0)
{
  printf("Waveform format: WORD\n");
}
else if (wav_format == 2.0)
{
  printf("Waveform format: ASCii\n");
}

acq_type = dbl_results[1];
if (acq_type == 0.0)
{
  printf("Acquire type: NORMal\n");
}
else if (acq_type == 1.0)
{
  printf("Acquire type: PEAK\n");
}
else if (acq_type == 2.0)
{
  printf("Acquire type: AVERage\n");
}
else if (acq_type == 3.0)
{
  printf("Acquire type: HRESolution\n");
}

wav_points = dbl_results[2];
printf("Waveform points: %e\n", wav_points);

avg_count = dbl_results[3];
printf("Waveform average count: %e\n", avg_count);

x_increment = dbl_results[4];
printf("Waveform X increment: %e\n", x_increment);

x_origin = dbl_results[5];
printf("Waveform X origin: %e\n", x_origin);
```

```
  x_reference = dbl_results[6];
  printf("Waveform X reference: %e\n", x_reference);

  y_increment = dbl_results[7];
  printf("Waveform Y increment: %e\n", y_increment);

  y_origin = dbl_results[8];
  printf("Waveform Y origin: %e\n", y_origin);

  y_reference = dbl_results[9];
  printf("Waveform Y reference: %e\n", y_reference);

  /* Read waveform data. */
  num_bytes = do_query_ieeeblock(":WAVeform:DATA?");
  printf("Number of data values: %d\n", num_bytes);

  /* Open file for output. */
  fp = fopen("c:\\scope\\data\\waveform_data.csv", "wb");

  /* Output waveform data in CSV format. */
  for (i = 0; i < num_bytes - 1; i++)
  {
    /* Write time value, voltage value. */
    fprintf(fp, "%9f, %6f\n",
      x_origin + ((float)i * x_increment),
      (((float)ieeeblock_data[i] - y_reference) * y_increment)
      + y_origin);
  }

  /* Close output file. */
   fclose(fp);
   printf("Waveform format BYTE data written to ");
   printf("c:\\scope\\data\\waveform_data.csv.\n");
}

/* Send a command to the instrument.
 * ------------------------------------------------------------- */
void do_command(command)
char *command;
{
  char message[80];

  strcpy(message, command);
  strcat(message, "\n");
  err = viPrintf(vi, message);
  if (err != VI_SUCCESS) error_handler();

  check_instrument_errors();
}

/* Command with IEEE definite-length block.
 * ------------------------------------------------------------- */
int do_command_ieeeblock(command, num_bytes)
char *command;
int num_bytes;
{
```

```
  char message[80];
  int data_length;

  strcpy(message, command);
  strcat(message, " #8%08d");
  err = viPrintf(vi, message, num_bytes);
  if (err != VI_SUCCESS) error_handler();

  err = viBufWrite(vi, ieeeblock_data, num_bytes, &data_length);
  if (err != VI_SUCCESS) error_handler();

  check_instrument_errors();

  return(data_length);
}

/* Query for a string result.
 * ------------------------------------------------------------- */
void do_query_string(query)
char *query;
{
  char message[80];

  strcpy(message, query);
  strcat(message, "\n");

  err = viPrintf(vi, message);
  if (err != VI_SUCCESS) error_handler();

  err = viScanf(vi, "%t", str_result);
  if (err != VI_SUCCESS) error_handler();

  check_instrument_errors();
}

/* Query for a number result.
 * ------------------------------------------------------------- */
void do_query_number(query)
char *query;
{
  char message[80];

  strcpy(message, query);
  strcat(message, "\n");

  err = viPrintf(vi, message);
  if (err != VI_SUCCESS) error_handler();

  err = viScanf(vi, "%lf", &num_result);
  if (err != VI_SUCCESS) error_handler();

  check_instrument_errors();
}

/* Query for numbers result.
 * ------------------------------------------------------------- */
void do_query_numbers(query)
```

```
char *query;
{
  char message[80];

  strcpy(message, query);
  strcat(message, "\n");

  err = viPrintf(vi, message);
  if (err != VI_SUCCESS) error_handler();

  err = viScanf(vi, "%,10lf\n", dbl_results);
  if (err != VI_SUCCESS) error_handler();

  check_instrument_errors();
}

/* Query for an IEEE definite-length block result.
 * ------------------------------------------------------------- */
int do_query_ieeeblock(query)
char *query;
{
  char message[80];
  int data_length;

  strcpy(message, query);
  strcat(message, "\n");
  err = viPrintf(vi, message);
  if (err != VI_SUCCESS) error_handler();

  data_length = IEEEBLOCK_SPACE;
  err = viScanf(vi, "%#b\n", &data_length, ieeeblock_data);
  if (err != VI_SUCCESS) error_handler();

  if (data_length == IEEEBLOCK_SPACE )
  {
    printf("IEEE block buffer full: ");
    printf("May not have received all data.\n");
  }

  check_instrument_errors();

  return(data_length);
}

/* Check for instrument errors.
 * ------------------------------------------------------------- */
void check_instrument_errors()
{
  char str_err_val[256] = {0};
  char str_out[800] = "";

  err = viQueryf(vi, ":SYSTem:ERRor?\n", "%t", str_err_val);
  if (err != VI_SUCCESS) error_handler();
  while(strncmp(str_err_val, "+0,No error", 3) != 0 )
  {
    strcat(str_out, ", ");
    strcat(str_out, str_err_val);
```

```
    err = viQueryf(vi, ":SYSTem:ERRor?\n", "%t", str_err_val);
    if (err != VI_SUCCESS) error_handler();
  }

  if (strcmp(str_out, "") != 0)
  {
    printf("INST Error%s\n", str_out);
    err = viFlush(vi, VI_READ_BUF);
    if (err != VI_SUCCESS) error_handler();
    err = viFlush(vi, VI_WRITE_BUF);
    if (err != VI_SUCCESS) error_handler();
  }
}

/* Handle VISA errors.
 * ------------------------------------------------------------------- */
void error_handler()
{
  char err_msg[1024] = {0};

  viStatusDesc(vi, err, err_msg);
  printf("VISA Error: %s\n", err_msg);
  if (err < VI_SUCCESS)
  {
    exit(1);
  }
}
```

VISA Example in Visual Basic

To run this example in Visual Basic for Applications:

1. Start the application that provides Visual Basic for Applications (for example, Microsoft Excel).
2. Press ALT+F11 to launch the Visual Basic editor.
3. Add the visa32.bas file to your project:
   a. Choose **File > Import File...**.
   b. Navigate to the header file, visa32.bas (installed with Keysight IO Libraries Suite and found in the Program Files (x86)\IVI Foundation\VISA\WinNT\Include), select it, and click **Open**.
4. Choose **Insert > Module**.
5. Cut-and-paste the code that follows into the editor.
6. Edit the program to use the VISA address of your oscilloscope, and save the changes.
7. Run the program.

```
'
' Keysight VISA Example in Visual Basic
' ----------------------------------------------------------------------
' This program illustrates a few commonly-used programming
```

```
' features of your Keysight oscilloscope.
' ----------------------------------------------------------------------

Option Explicit

Public err As Long   ' Error returned by VISA function calls.
Public drm As Long   ' Session to Default Resource Manager.
Public vi As Long    ' Session to instrument.

' Declare variables to hold numeric values returned by
' viVScanf/viVQueryf.
Public dblQueryResult As Double
Public Const ByteArraySize = 5000000
Public retCount As Long
Public byteArray(ByteArraySize) As Byte
Public paramsArray(2) As Long
Public Const DblArraySize = 20
Public dblArray(DblArraySize) As Double

' Declare fixed length string variable to hold string value returned
' by viVScanf/viVQueryf.
Public strQueryResult As String * 200

' For Sleep subroutine.
Private Declare Sub Sleep Lib "kernel32" (ByVal dwMilliseconds As Long)

'
' Main Program
' ----------------------------------------------------------------------

Sub Main()

  ' Open the default resource manager session.
  err = viOpenDefaultRM(drm)
  If (err <> VI_SUCCESS) Then HandleVISAError drm

  ' Open the session using the oscilloscope's VISA address.
  err = viOpen(drm, _
      "USB0::0x0957::0x17A6::US50210029::0::INSTR", 0, 15000, vi)
  If (err <> VI_SUCCESS) Then HandleVISAError drm

  ' Set the I/O timeout to ten seconds.
  err = viSetAttribute(vi, VI_ATTR_TMO_VALUE, 10000)
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  ' Initialize - start from a known state.
  Initialize

  ' Capture data.
  Capture

  ' Analyze the captured waveform.
  Analyze

  ' Close the vi session and the resource manager session.
  err = viClose(vi)
  err = viClose(drm)
```

```
End Sub

'
' Initialize the oscilloscope to a known state.
' --------------------------------------------------------------------

Private Sub Initialize()

  ' Clear the interface.
  err = viClear(vi)
  If Not (err = VI_SUCCESS) Then HandleVISAError vi

  ' Get and display the device's *IDN? string.
  strQueryResult = DoQueryString("*IDN?")
  MsgBox "*IDN? string: " + strQueryResult, vbOKOnly, "*IDN? Result"

  ' Clear status and load the default setup.
  DoCommand "*CLS"
  DoCommand "*RST"

End Sub

'
' Capture the waveform.
' --------------------------------------------------------------------

Private Sub Capture()

  ' Use auto-scale to automatically configure oscilloscope.
  ' ------------------------------------------------------------------
  DoCommand ":AUToscale"

  ' Set trigger mode (EDGE, PULSe, PATTern, etc., and input source.
  DoCommand ":TRIGger:MODE EDGE"
  Debug.Print "Trigger mode: " + _
      DoQueryString(":TRIGger:MODE?")

  ' Set EDGE trigger parameters.
  DoCommand ":TRIGger:EDGE:SOURCe CHANnel1"
  Debug.Print "Trigger edge source: " + _
      DoQueryString(":TRIGger:EDGE:SOURce?")

  DoCommand ":TRIGger:EDGE:LEVel 1.5"
  Debug.Print "Trigger edge level: " + _
      DoQueryString(":TRIGger:EDGE:LEVel?")

  DoCommand ":TRIGger:EDGE:SLOPe POSitive"
  Debug.Print "Trigger edge slope: " + _
      DoQueryString(":TRIGger:EDGE:SLOPe?")

  ' Save oscilloscope configuration.
  ' ------------------------------------------------------------------
  Dim lngSetupStringSize As Long
  lngSetupStringSize = DoQueryIEEEBlock_Bytes(":SYSTem:SETup?")
  Debug.Print "Setup bytes saved: " + CStr(lngSetupStringSize)
```

```
' Output setup string to a file:
Dim strPath As String
strPath = "c:\scope\config\setup.dat"
If Len(Dir(strPath)) Then
  Kill strPath   ' Remove file if it exists.
End If

' Open file for output.
Dim hFile As Long
hFile = FreeFile
Open strPath For Binary Access Write Lock Write As hFile
Dim lngI As Long
For lngI = 0 To lngSetupStringSize - 1
  Put hFile, , byteArray(lngI)   ' Write data.
Next lngI
Close hFile   ' Close file.

' Change settings with individual commands:
' -----------------------------------------------------------------

' Set vertical scale and offset.
DoCommand ":CHANnel1:SCALe 0.05"
Debug.Print "Channel 1 vertical scale: " + _
    DoQueryString(":CHANnel1:SCALe?")

DoCommand ":CHANnel1:OFFSet -1.5"
Debug.Print "Channel 1 vertical offset: " + _
    DoQueryString(":CHANnel1:OFFSet?")

' Set horizontal scale and position.
DoCommand ":TIMebase:SCALe 0.0002"
Debug.Print "Timebase scale: " + _
    DoQueryString(":TIMebase:SCALe?")

DoCommand ":TIMebase:POSition 0.0"
Debug.Print "Timebase position: " + _
    DoQueryString(":TIMebase:POSition?")

' Set the acquisition type (NORMal, PEAK, AVERage, or HRESolution).
DoCommand ":ACQuire:TYPE NORMal"
Debug.Print "Acquire type: " + _
    DoQueryString(":ACQuire:TYPE?")

' Or, configure by loading a previously saved setup.
' -----------------------------------------------------------------
strPath = "c:\scope\config\setup.dat"
Open strPath For Binary Access Read As hFile   ' Open file for input.
Dim lngSetupFileSize As Long
lngSetupFileSize = LOF(hFile)  ' Length of file.
Get hFile, , byteArray   ' Read data.
Close hFile   ' Close file.
' Write learn string back to oscilloscope using ":SYSTem:SETup"
' command:
Dim lngRestored As Long
lngRestored = DoCommandIEEEBlock(":SYSTem:SETup", lngSetupFileSize)
Debug.Print "Setup bytes restored: " + CStr(lngRestored)
```

```
  ' Capture an acquisition using :DIGitize.
  ' ------------------------------------------------------------------
  DoCommand ":DIGitize CHANnel1"

End Sub

'
' Analyze the captured waveform.
' ------------------------------------------------------------------

Private Sub Analyze()

  ' Make a couple of measurements.
  ' ------------------------------------------------------------------
  DoCommand ":MEASure:SOURce CHANnel1"
  Debug.Print "Measure source: " + _
      DoQueryString(":MEASure:SOURce?")

  DoCommand ":MEASure:FREQuency"
  dblQueryResult = DoQueryNumber(":MEASure:FREQuency?")
  MsgBox "Frequency:" + vbCrLf + _
      FormatNumber(dblQueryResult / 1000, 4) + " kHz"

  DoCommand ":MEASure:VAMPlitude"
  dblQueryResult = DoQueryNumber(":MEASure:VAMPlitude?")
  MsgBox "Vertical amplitude:" + vbCrLf + _
      FormatNumber(dblQueryResult, 4) + " V"


  ' Download the screen image.
  ' ------------------------------------------------------------------
  DoCommand ":HARDcopy:INKSaver OFF"

  ' Get screen image.
  Dim lngBlockSize As Long
  lngBlockSize = DoQueryIEEEBlock_Bytes(":DISPlay:DATA? PNG, COLor")
  Debug.Print "Screen image bytes: " + CStr(lngBlockSize)

  ' Save screen image to a file:
  Dim strPath As String
  strPath = "c:\scope\data\screen.png"
  If Len(Dir(strPath)) Then
    Kill strPath   ' Remove file if it exists.
  End If
  Dim hFile As Long
  hFile = FreeFile
  Open strPath For Binary Access Write Lock Write As hFile
  Dim lngI As Long
  For lngI = 0 To lngBlockSize - 1
    Put hFile, , byteArray(lngI)   ' Write data.
  Next lngI
  Close hFile   ' Close file.
  MsgBox "Screen image written to " + strPath


  ' Download waveform data.
  ' ------------------------------------------------------------------
```

```
' Set the waveform points mode.
DoCommand ":WAVeform:POINts:MODE RAW"
Debug.Print "Waveform points mode: " + _
    DoQueryString(":WAVeform:POINts:MODE?")

' Get the number of waveform points available.
Debug.Print "Waveform points available: " + _
    DoQueryString(":WAVeform:POINts?")

' Set the waveform source.
DoCommand ":WAVeform:SOURce CHANnel1"
Debug.Print "Waveform source: " + _
    DoQueryString(":WAVeform:SOURce?")

' Choose the format of the data returned (WORD, BYTE, ASCII):
DoCommand ":WAVeform:FORMat BYTE"
Debug.Print "Waveform format: " + _
    DoQueryString(":WAVeform:FORMat?")

' Display the waveform settings:
Dim intFormat As Integer
Dim intType As Integer
Dim lngPoints As Long
Dim lngCount As Long
Dim dblXIncrement As Double
Dim dblXOrigin As Double
Dim lngXReference As Long
Dim sngYIncrement As Single
Dim lngYOrigin As Long
Dim lngYReference As Long
Dim strOutput As String

Dim lngNumNumbers As Long
lngNumNumbers = DoQueryNumbers(":WAVeform:PREamble?")

intFormat = dblArray(0)
intType = dblArray(1)
lngPoints = dblArray(2)
lngCount = dblArray(3)
dblXIncrement = dblArray(4)
dblXOrigin = dblArray(5)
lngXReference = dblArray(6)
sngYIncrement = dblArray(7)
lngYOrigin = dblArray(8)
lngYReference = dblArray(9)

If intFormat = 0 Then
  Debug.Print "Waveform format: BYTE"
ElseIf intFormat = 1 Then
  Debug.Print "Waveform format: WORD"
ElseIf intFormat = 2 Then
  Debug.Print "Waveform format: ASCii"
End If

If intType = 0 Then
  Debug.Print "Acquisition type: NORMal"
```

```
ElseIf intType = 1 Then
  Debug.Print "Acquisition type: PEAK"
ElseIf intType = 2 Then
  Debug.Print "Acquisition type: AVERage"
ElseIf intType = 3 Then
  Debug.Print "Acquisition type: HRESolution"
End If

Debug.Print "Waveform points: " + _
    FormatNumber(lngPoints, 0)

Debug.Print "Waveform average count: " + _
    FormatNumber(lngCount, 0)

Debug.Print "Waveform X increment: " + _
    Format(dblXIncrement, "Scientific")

Debug.Print "Waveform X origin: " + _
    Format(dblXOrigin, "Scientific")

Debug.Print "Waveform X reference: " + _
    FormatNumber(lngXReference, 0)

Debug.Print "Waveform Y increment: " + _
    Format(sngYIncrement, "Scientific")

Debug.Print "Waveform Y origin: " + _
    FormatNumber(lngYOrigin, 0)

Debug.Print "Waveform Y reference: " + _
    FormatNumber(lngYReference, 0)

' Get the waveform data
Dim lngNumBytes As Long
lngNumBytes = DoQueryIEEEBlock_Bytes(":WAVeform:DATA?")
Debug.Print "Number of data values: " + CStr(lngNumBytes)

' Set up output file:
strPath = "c:\scope\data\waveform_data.csv"

' Open file for output.
Open strPath For Output Access Write Lock Write As hFile

' Output waveform data in CSV format.
Dim lngDataValue As Long

For lngI = 0 To lngNumBytes - 1
  lngDataValue = CLng(byteArray(lngI))

  ' Write time value, voltage value.
  Print #hFile, _
      FormatNumber(dblXOrigin + (lngI * dblXIncrement), 9) + _
      ", " + _
      FormatNumber(((lngDataValue - lngYReference) _
      * sngYIncrement) + lngYOrigin)

Next lngI
```

```
  ' Close output file.
  Close hFile   ' Close file.
  MsgBox "Waveform format BYTE data written to " + _
      "c:\scope\data\waveform_data.csv."

End Sub

Private Sub DoCommand(command As String)

  err = viVPrintf(vi, command + vbLf, 0)
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  CheckInstrumentErrors

End Sub

Private Function DoCommandIEEEBlock(command As String, _
    lngBlockSize As Long)

  retCount = lngBlockSize

  Dim strCommandAndLength As String
  strCommandAndLength = command + " %#" + _
      Format(lngBlockSize) + "b"

  err = viVPrintf(vi, strCommandAndLength + vbLf, paramsArray(1))
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  DoCommandIEEEBlock = retCount

  CheckInstrumentErrors

End Function

Private Function DoQueryString(query As String) As String

  Dim strResult As String * 200

  err = viVPrintf(vi, query + vbLf, 0)
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  err = viVScanf(vi, "%t", strResult)
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  DoQueryString = strResult

  CheckInstrumentErrors

End Function

Private Function DoQueryNumber(query As String) As Variant

  Dim dblResult As Double

  err = viVPrintf(vi, query + vbLf, 0)
  If (err <> VI_SUCCESS) Then HandleVISAError vi
```

```
  err = viVScanf(vi, "%lf" + vbLf, VarPtr(dblResult))
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  DoQueryNumber = dblResult

  CheckInstrumentErrors

End Function

Private Function DoQueryNumbers(query As String) As Long

  Dim dblResult As Double

  ' Send query.
  err = viVPrintf(vi, query + vbLf, 0)
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  ' Set up paramsArray for multiple parameter query returning array.
  paramsArray(0) = VarPtr(retCount)
  paramsArray(1) = VarPtr(dblArray(0))

  ' Set retCount to max number of elements array can hold.
  retCount = DblArraySize

  ' Read numbers.
  err = viVScanf(vi, "%,#lf" + vbLf, paramsArray(0))
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  ' retCount is now actual number of values returned by query.
  DoQueryNumbers = retCount

  CheckInstrumentErrors

End Function

Private Function DoQueryIEEEBlock_Bytes(query As String) As Long

  ' Send query.
  err = viVPrintf(vi, query + vbLf, 0)
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  ' Set up paramsArray for multiple parameter query returning array.
  paramsArray(0) = VarPtr(retCount)
  paramsArray(1) = VarPtr(byteArray(0))

  ' Set retCount to max number of elements array can hold.
  retCount = ByteArraySize

  ' Get unsigned integer bytes.
  err = viVScanf(vi, "%#b" + vbLf, paramsArray(0))
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  err = viFlush(vi, VI_READ_BUF)
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  err = viFlush(vi, VI_WRITE_BUF)
```

```
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  ' retCount is now actual number of bytes returned by query.
  DoQueryIEEEBlock_Bytes = retCount

  CheckInstrumentErrors

End Function

Private Sub CheckInstrumentErrors()

  On Error GoTo ErrorHandler

  Dim strErrVal As String * 200
  Dim strOut As String

  err = viVPrintf(vi, ":SYSTem:ERRor?" + vbLf, 0)   ' Query any errors.
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  err = viVScanf(vi, "%t", strErrVal)   ' Read: Errnum,"Error String".
  If (err <> VI_SUCCESS) Then HandleVISAError vi

  While Val(strErrVal) <> 0             ' End if find: 0,"No Error".
    strOut = strOut + "INST Error: " + strErrVal

    err = viVPrintf(vi, ":SYSTem:ERRor?" + vbLf, 0)   ' Request error.
    If (err <> VI_SUCCESS) Then HandleVISAError vi

    err = viVScanf(vi, "%t", strErrVal)   ' Read error message.
    If (err <> VI_SUCCESS) Then HandleVISAError vi

  Wend

  If Not strOut = "" Then
    MsgBox strOut, vbExclamation, "INST Error Messages"

    err = viFlush(vi, VI_READ_BUF)
    If (err <> VI_SUCCESS) Then HandleVISAError vi

    err = viFlush(vi, VI_WRITE_BUF)
    If (err <> VI_SUCCESS) Then HandleVISAError vi

  End If

  Exit Sub

ErrorHandler:

  MsgBox "*** Error : " + Error, vbExclamation
  End

End Sub

Private Sub HandleVISAError(session As Long)

  Dim strVisaErr As String * 200
  Call viStatusDesc(session, err, strVisaErr)
```

```
  MsgBox "*** VISA Error : " + strVisaErr, vbExclamation

  ' If the error is not a warning, close the session.
  If err < VI_SUCCESS Then
    If session <> 0 Then Call viClose(session)
    End
  End If

End Sub
```

VISA Example in C#

To compile and run this example in Microsoft Visual Studio 2008:

1. Open Visual Studio.
2. Create a new Visual C#, Windows, Console Application project.
3. Cut-and-paste the code that follows into the C# source file.
4. Edit the program to use the VISA address of your oscilloscope.
5. Add Keysight's VISA header file to your project:
   a. Right-click the project you wish to modify (not the solution) in the Solution Explorer window of the Microsoft Visual Studio environment.
   b. Click **Add** and then click **Add Existing Item...**
   c. Navigate to the header file, visa32.cs (installed with Keysight IO Libraries Suite and found in the Program Files (x86)\IVI Foundation\VISA\WinNT\ Include directory), select it, but *do not click the Open button*.
   d. Click the down arrow to the right of the **Add** button, and choose **Add as Link**.

      You should now see the file underneath your project in the Solution Explorer. It will have a little arrow icon in its lower left corner, indicating that it is a link.
6. Build and run the program.

For more information, see the tutorial on using VISA in Microsoft .NET in the VISA Help that comes with Keysight IO Libraries Suite.

```
/*
 * Keysight VISA Example in C#
 * ----------------------------------------------------------------------
 * This program illustrates a few commonly used programming
 * features of your Keysight oscilloscope.
 * ----------------------------------------------------------------------
 */

using System;
using System.IO;
using System.Text;

namespace InfiniiVision
{
  class VisaInstrumentApp
```

```
{
  private static VisaInstrument myScope;

  public static void Main(string[] args)
  {
    try
    {
      myScope = new
        VisaInstrument("USB0::0x0957::0x17A6::US50210029::0::INSTR");
      myScope.SetTimeoutSeconds(10);

      // Initialize - start from a known state.
      Initialize();

      // Capture data.
      Capture();

      // Analyze the captured waveform.
      Analyze();

    }
    catch (System.ApplicationException err)
    {
      Console.WriteLine("*** VISA Error Message : " + err.Message);
    }
    catch (System.SystemException err)
    {
      Console.WriteLine("*** System Error Message : " + err.Message);
    }
    catch (System.Exception err)
    {
      System.Diagnostics.Debug.Fail("Unexpected Error");
      Console.WriteLine("*** Unexpected Error : " + err.Message);
    }
    finally
    {
      myScope.Close();
    }
  }

  /*
   * Initialize the oscilloscope to a known state.
   * ---------------------------------------------------------------
   */
  private static void Initialize()
  {
    StringBuilder strResults;

    // Get and display the device's *IDN? string.
    strResults = myScope.DoQueryString("*IDN?");
    Console.WriteLine("*IDN? result is: {0}", strResults);

    // Clear status and load the default setup.
    myScope.DoCommand("*CLS");
    myScope.DoCommand("*RST");
  }
```

```
/*
 * Capture the waveform.
 * -----------------------------------------------------------------
 */
private static void Capture()
{
  // Use auto-scale to automatically configure oscilloscope.
  myScope.DoCommand(":AUToscale");

  // Set trigger mode (EDGE, PULSe, PATTern, etc., and input source.
  myScope.DoCommand(":TRIGger:MODE EDGE");
  Console.WriteLine("Trigger mode: {0}",
      myScope.DoQueryString(":TRIGger:MODE?"));

  // Set EDGE trigger parameters.
  myScope.DoCommand(":TRIGger:EDGE:SOURCe CHANnel1");
  Console.WriteLine("Trigger edge source: {0}",
      myScope.DoQueryString(":TRIGger:EDGE:SOURce?"));

  myScope.DoCommand(":TRIGger:EDGE:LEVel 1.5");
  Console.WriteLine("Trigger edge level: {0}",
      myScope.DoQueryString(":TRIGger:EDGE:LEVel?"));

  myScope.DoCommand(":TRIGger:EDGE:SLOPe POSitive");
  Console.WriteLine("Trigger edge slope: {0}",
      myScope.DoQueryString(":TRIGger:EDGE:SLOPe?"));

  // Save oscilloscope configuration.
  byte[] ResultsArray;   // Results array.
  int nLength;   // Number of bytes returned from instrument.
  string strPath;

  // Query and read setup string.
  nLength = myScope.DoQueryIEEEBlock(":SYSTem:SETup?",
    out ResultsArray);

  // Write setup string to file.
  strPath = "c:\\scope\\config\\setup.stp";
  FileStream fStream = File.Open(strPath, FileMode.Create);
  fStream.Write(ResultsArray, 0, nLength);
  fStream.Close();
  Console.WriteLine("Setup bytes saved: {0}", nLength);

  // Change settings with individual commands:

  // Set vertical scale and offset.
  myScope.DoCommand(":CHANnel1:SCALe 0.05");
  Console.WriteLine("Channel 1 vertical scale: {0}",
      myScope.DoQueryString(":CHANnel1:SCALe?"));

  myScope.DoCommand(":CHANnel1:OFFSet -1.5");
  Console.WriteLine("Channel 1 vertical offset: {0}",
      myScope.DoQueryString(":CHANnel1:OFFSet?"));

  // Set horizontal scale and position.
  myScope.DoCommand(":TIMebase:SCALe 0.0002");
  Console.WriteLine("Timebase scale: {0}",
```

```
            myScope.DoQueryString(":TIMebase:SCALe?"));

        myScope.DoCommand(":TIMebase:POSition 0.0");
        Console.WriteLine("Timebase position: {0}",
            myScope.DoQueryString(":TIMebase:POSition?"));

        // Set the acquisition type (NORMal, PEAK, AVERage, or HRESolution
).
        myScope.DoCommand(":ACQuire:TYPE NORMal");
        Console.WriteLine("Acquire type: {0}",
            myScope.DoQueryString(":ACQuire:TYPE?"));

        // Or, configure by loading a previously saved setup.
        byte[] DataArray;
        int nBytesWritten;

        // Read setup string from file.
        strPath = "c:\\scope\\config\\setup.stp";
        DataArray = File.ReadAllBytes(strPath);

        // Restore setup string.
        nBytesWritten = myScope.DoCommandIEEEBlock(":SYSTem:SETup",
          DataArray);
        Console.WriteLine("Setup bytes restored: {0}", nBytesWritten);

        // Capture an acquisition using :DIGitize.
        myScope.DoCommand(":DIGitize CHANnel1");
      }

      /*
       * Analyze the captured waveform.
       * -------------------------------------------------------------
       */
      private static void Analyze()
      {
        byte[] ResultsArray;   // Results array.
        int nLength;   // Number of bytes returned from instrument.
        string strPath;

        // Make a couple of measurements.
        // -------------------------------------------------------------
        myScope.DoCommand(":MEASure:SOURce CHANnel1");
        Console.WriteLine("Measure source: {0}",
            myScope.DoQueryString(":MEASure:SOURce?"));

        double fResult;
        myScope.DoCommand(":MEASure:FREQuency");
        fResult = myScope.DoQueryNumber(":MEASure:FREQuency?");
        Console.WriteLine("Frequency: {0:F4} kHz", fResult / 1000);

        myScope.DoCommand(":MEASure:VAMPlitude");
        fResult = myScope.DoQueryNumber(":MEASure:VAMPlitude?");
        Console.WriteLine("Vertical amplitude: {0:F2} V", fResult);

        // Download the screen image.
        // -------------------------------------------------------------
        myScope.DoCommand(":HARDcopy:INKSaver OFF");
```

```
// Get the screen data.
nLength = myScope.DoQueryIEEEBlock(":DISPlay:DATA? PNG, COLor",
    out ResultsArray);

// Store the screen data to a file.
strPath = "c:\\scope\\data\\screen.png";
FileStream fStream = File.Open(strPath, FileMode.Create);
fStream.Write(ResultsArray, 0, nLength);
fStream.Close();
Console.WriteLine("Screen image ({0} bytes) written to {1}",
    nLength, strPath);

// Download waveform data.
// ------------------------------------------------------------

// Set the waveform points mode.
myScope.DoCommand(":WAVeform:POINts:MODE RAW");
Console.WriteLine("Waveform points mode: {0}",
    myScope.DoQueryString(":WAVeform:POINts:MODE?"));

// Get the number of waveform points available.
myScope.DoCommand(":WAVeform:POINts 10240");
Console.WriteLine("Waveform points available: {0}",
    myScope.DoQueryString(":WAVeform:POINts?"));

// Set the waveform source.
myScope.DoCommand(":WAVeform:SOURce CHANnel1");
Console.WriteLine("Waveform source: {0}",
    myScope.DoQueryString(":WAVeform:SOURce?"));

// Choose the format of the data returned (WORD, BYTE, ASCII):
myScope.DoCommand(":WAVeform:FORMat BYTE");
Console.WriteLine("Waveform format: {0}",
    myScope.DoQueryString(":WAVeform:FORMat?"));

// Display the waveform settings:
double[] fResultsArray;
fResultsArray = myScope.DoQueryNumbers(":WAVeform:PREamble?");

double fFormat = fResultsArray[0];
if (fFormat == 0.0)
{
  Console.WriteLine("Waveform format: BYTE");
}
else if (fFormat == 1.0)
{
  Console.WriteLine("Waveform format: WORD");
}
else if (fFormat == 2.0)
{
  Console.WriteLine("Waveform format: ASCii");
}

double fType = fResultsArray[1];
if (fType == 0.0)
{
```

```
  Console.WriteLine("Acquire type: NORMal");
}
else if (fType == 1.0)
{
  Console.WriteLine("Acquire type: PEAK");
}
else if (fType == 2.0)
{
  Console.WriteLine("Acquire type: AVERage");
}
else if (fType == 3.0)
{
  Console.WriteLine("Acquire type: HRESolution");
}

double fPoints = fResultsArray[2];
Console.WriteLine("Waveform points: {0:e}", fPoints);

double fCount = fResultsArray[3];
Console.WriteLine("Waveform average count: {0:e}", fCount);

double fXincrement = fResultsArray[4];
Console.WriteLine("Waveform X increment: {0:e}", fXincrement);

double fXorigin = fResultsArray[5];
Console.WriteLine("Waveform X origin: {0:e}", fXorigin);

double fXreference = fResultsArray[6];
Console.WriteLine("Waveform X reference: {0:e}", fXreference);

double fYincrement = fResultsArray[7];
Console.WriteLine("Waveform Y increment: {0:e}", fYincrement);

double fYorigin = fResultsArray[8];
Console.WriteLine("Waveform Y origin: {0:e}", fYorigin);

double fYreference = fResultsArray[9];
Console.WriteLine("Waveform Y reference: {0:e}", fYreference);

// Read waveform data.
nLength = myScope.DoQueryIEEEBlock(":WAVeform:DATA?",
    out ResultsArray);
Console.WriteLine("Number of data values: {0}", nLength);

// Set up output file:
strPath = "c:\\scope\\data\\waveform_data.csv";
if (File.Exists(strPath)) File.Delete(strPath);

// Open file for output.
StreamWriter writer = File.CreateText(strPath);

// Output waveform data in CSV format.
for (int i = 0; i < nLength - 1; i++)
  writer.WriteLine("{0:f9}, {1:f6}",
      fXorigin + ((float)i * fXincrement),
      (((float)ResultsArray[i] - fYreference) *
      fYincrement) + fYorigin);
```

```
    // Close output file.
    writer.Close();
    Console.WriteLine("Waveform format BYTE data written to {0}",
        strPath);
  }
}

class VisaInstrument
{
  private int m_nResourceManager;
  private int m_nSession;
  private string m_strVisaAddress;

  // Constructor.
  public VisaInstrument(string strVisaAddress)
  {
    // Save VISA address in member variable.
    m_strVisaAddress = strVisaAddress;

    // Open the default VISA resource manager.
    OpenResourceManager();

    // Open a VISA resource session.
    OpenSession();

    // Clear the interface.
    int nViStatus;
    nViStatus = visa32.viClear(m_nSession);
  }

  public void DoCommand(string strCommand)
  {
    // Send the command.
    VisaSendCommandOrQuery(strCommand);

    // Check for inst errors.
    CheckInstrumentErrors(strCommand);
  }

  public int DoCommandIEEEBlock(string strCommand,
    byte[] DataArray)
  {
    // Send the command to the device.
    string strCommandAndLength;
    int nViStatus, nLength, nBytesWritten;

    nLength = DataArray.Length;
    strCommandAndLength = String.Format("{0} #8%08d",
      strCommand);

    // Write first part of command to formatted I/O write buffer.
    nViStatus = visa32.viPrintf(m_nSession, strCommandAndLength,
      nLength);
    CheckVisaStatus(nViStatus);

    // Write the data to the formatted I/O write buffer.
```

```
    nViStatus = visa32.viBufWrite(m_nSession, DataArray, nLength,
      out nBytesWritten);
    CheckVisaStatus(nViStatus);

    // Check for inst errors.
    CheckInstrumentErrors(strCommand);

    return nBytesWritten;
  }

  public StringBuilder DoQueryString(string strQuery)
  {
    // Send the query.
    VisaSendCommandOrQuery(strQuery);

    // Get the result string.
    StringBuilder strResults = new StringBuilder(1000);
    strResults = VisaGetResultString();

    // Check for inst errors.
    CheckInstrumentErrors(strQuery);

    // Return string results.
    return strResults;
  }

  public double DoQueryNumber(string strQuery)
  {
    // Send the query.
    VisaSendCommandOrQuery(strQuery);

    // Get the result string.
    double fResults;
    fResults = VisaGetResultNumber();

    // Check for inst errors.
    CheckInstrumentErrors(strQuery);

    // Return string results.
    return fResults;
  }

  public double[] DoQueryNumbers(string strQuery)
  {
    // Send the query.
    VisaSendCommandOrQuery(strQuery);

    // Get the result string.
    double[] fResultsArray;
    fResultsArray = VisaGetResultNumbers();

    // Check for inst errors.
    CheckInstrumentErrors(strQuery);

    // Return string results.
    return fResultsArray;
  }
```

```
public int DoQueryIEEEBlock(string strQuery,
  out byte[] ResultsArray)
{
  // Send the query.
  VisaSendCommandOrQuery(strQuery);

  // Get the result string.
  int length;   // Number of bytes returned from instrument.
  length = VisaGetResultIEEEBlock(out ResultsArray);

  // Check for inst errors.
  CheckInstrumentErrors(strQuery);

  // Return string results.
  return length;
}

private void VisaSendCommandOrQuery(string strCommandOrQuery)
{
  // Send command or query to the device.
  string strWithNewline;
  strWithNewline = String.Format("{0}\n", strCommandOrQuery);
  int nViStatus;
  nViStatus = visa32.viPrintf(m_nSession, strWithNewline);
  CheckVisaStatus(nViStatus);
}

private StringBuilder VisaGetResultString()
{
  StringBuilder strResults = new StringBuilder(1000);

  // Read return value string from the device.
  int nViStatus;
  nViStatus = visa32.viScanf(m_nSession, "%1000t", strResults);
  CheckVisaStatus(nViStatus);

  return strResults;
}

private double VisaGetResultNumber()
{
  double fResults = 0;

  // Read return value string from the device.
  int nViStatus;
  nViStatus = visa32.viScanf(m_nSession, "%lf", out fResults);
  CheckVisaStatus(nViStatus);

  return fResults;
}

private double[] VisaGetResultNumbers()
{
  double[] fResultsArray;
  fResultsArray = new double[10];
```

```
  // Read return value string from the device.
  int nViStatus;
  nViStatus = visa32.viScanf(m_nSession, "%,10lf\n",
      fResultsArray);
  CheckVisaStatus(nViStatus);

  return fResultsArray;
}

private int VisaGetResultIEEEBlock(out byte[] ResultsArray)
{
  // Results array, big enough to hold a PNG.
  ResultsArray = new byte[300000];
  int length;   // Number of bytes returned from instrument.

  // Set the default number of bytes that will be contained in
  // the ResultsArray to 300,000 (300kB).
  length = 300000;

  // Read return value string from the device.
  int nViStatus;
  nViStatus = visa32.viScanf(m_nSession, "%#b", ref length,
    ResultsArray);
  CheckVisaStatus(nViStatus);

  // Write and read buffers need to be flushed after IEEE block?
  nViStatus = visa32.viFlush(m_nSession, visa32.VI_WRITE_BUF);
  CheckVisaStatus(nViStatus);

  nViStatus = visa32.viFlush(m_nSession, visa32.VI_READ_BUF);
  CheckVisaStatus(nViStatus);

  return length;
}

private void CheckInstrumentErrors(string strCommand)
{
  // Check for instrument errors.
  StringBuilder strInstrumentError = new StringBuilder(1000);
  bool bFirstError = true;

  do   // While not "0,No error"
  {
    VisaSendCommandOrQuery(":SYSTem:ERRor?");
    strInstrumentError = VisaGetResultString();

    if (!strInstrumentError.ToString().StartsWith("+0,"))
    {
      if (bFirstError)
      {
        Console.WriteLine("ERROR(s) for command '{0}': ",
          strCommand);
        bFirstError = false;
      }
      Console.Write(strInstrumentError);
    }
  } while (!strInstrumentError.ToString().StartsWith("+0,"));
```

```
    }

    private void OpenResourceManager()
    {
      int nViStatus;
      nViStatus =
        visa32.viOpenDefaultRM(out this.m_nResourceManager);
      if (nViStatus < visa32.VI_SUCCESS)
        throw new
          ApplicationException("Failed to open Resource Manager");
    }

    private void OpenSession()
    {
      int nViStatus;
      nViStatus = visa32.viOpen(this.m_nResourceManager,
        this.m_strVisaAddress, visa32.VI_NO_LOCK,
        visa32.VI_TMO_IMMEDIATE, out this.m_nSession);
      CheckVisaStatus(nViStatus);
    }

    public void SetTimeoutSeconds(int nSeconds)
    {
      int nViStatus;
      nViStatus = visa32.viSetAttribute(this.m_nSession,
        visa32.VI_ATTR_TMO_VALUE, nSeconds * 1000);
      CheckVisaStatus(nViStatus);
    }

    public void CheckVisaStatus(int nViStatus)
    {
      // If VISA error, throw exception.
      if (nViStatus < visa32.VI_SUCCESS)
      {
        StringBuilder strError = new StringBuilder(256);
        visa32.viStatusDesc(this.m_nResourceManager, nViStatus,
          strError);
        throw new ApplicationException(strError.ToString());
      }
    }

    public void Close()
    {
      if (m_nSession != 0)
        visa32.viClose(m_nSession);
      if (m_nResourceManager != 0)
        visa32.viClose(m_nResourceManager);
    }
  }
}
```

VISA Example in Visual Basic .NET

To compile and run this example in Microsoft Visual Studio 2008:

1. Open Visual Studio.
2. Create a new Visual Basic, Windows, Console Application project.
3. Cut-and-paste the code that follows into the Visual Basic .NET source file.
4. Edit the program to use the VISA address of your oscilloscope.
5. Add Keysight's VISA header file to your project:
   a. Right-click the project you wish to modify (not the solution) in the Solution Explorer window of the Microsoft Visual Studio environment.
   b. Choose **Add** and then choose **Add Existing Item...**
   c. Navigate to the header file, visa32.vb (installed with Keysight IO Libraries Suite and found in the Program Files (x86)\IVI Foundation\VISA\WinNT\ Include directory), select it, but *do not click the Open button*.
   d. Click the down arrow to the right of the **Add** button, and choose **Add as Link**.

      You should now see the file underneath your project in the Solution Explorer. It will have a little arrow icon in its lower left corner, indicating that it is a link.
   e. Right-click the project again and choose **Properties**; then, select "InfiniiVision.VisaInstrumentApp" as the **Startup object**.
6. Build and run the program.

For more information, see the tutorial on using VISA in Microsoft .NET in the VISA Help that comes with Keysight IO Libraries Suite.

```
'
' Keysight VISA Example in Visual Basic .NET
' ----------------------------------------------------------------------
' This program illustrates a few commonly-used programming
' features of your Keysight oscilloscope.
' ----------------------------------------------------------------------

Imports System
Imports System.IO
Imports System.Text

Namespace InfiniiVision
  Class VisaInstrumentApp
    Private Shared myScope As VisaInstrument

    Public Shared Sub Main(ByVal args As String())
      Try
        myScope = _
          New VisaInstrument("USB0::0x0957::0x17A6::US50210029::0::INSTR
")
        myScope.SetTimeoutSeconds(10)
```

```
    ' Initialize - start from a known state.
    Initialize()

    ' Capture data.
    Capture()

    ' Analyze the captured waveform.
    Analyze()

  Catch err As System.ApplicationException
    Console.WriteLine("*** VISA Error Message : " + err.Message)
  Catch err As System.SystemException
    Console.WriteLine("*** System Error Message : " + err.Message)
  Catch err As System.Exception
    Debug.Fail("Unexpected Error")
    Console.WriteLine("*** Unexpected Error : " + err.Message)
  End Try
End Sub

'
' Initialize the oscilloscope to a known state.
' ---------------------------------------------------------------

Private Shared Sub Initialize()
  Dim strResults As StringBuilder

  ' Get and display the device's *IDN? string.
  strResults = myScope.DoQueryString("*IDN?")
  Console.WriteLine("*IDN? result is: {0}", strResults)

  ' Clear status and load the default setup.
  myScope.DoCommand("*CLS")
  myScope.DoCommand("*RST")

End Sub

'
' Capture the waveform.
' ---------------------------------------------------------------

Private Shared Sub Capture()

  ' Use auto-scale to automatically configure oscilloscope.
  myScope.DoCommand(":AUToscale")

  ' Set trigger mode (EDGE, PULSe, PATTern, etc., and input source.
  myScope.DoCommand(":TRIGger:MODE EDGE")
  Console.WriteLine("Trigger mode: {0}", _
      myScope.DoQueryString(":TRIGger:MODE?"))

  ' Set EDGE trigger parameters.
  myScope.DoCommand(":TRIGger:EDGE:SOURCe CHANnel1")
  Console.WriteLine("Trigger edge source: {0}", _
      myScope.DoQueryString(":TRIGger:EDGE:SOURce?"))

  myScope.DoCommand(":TRIGger:EDGE:LEVel 1.5")
  Console.WriteLine("Trigger edge level: {0}", _
```

```
    myScope.DoQueryString(":TRIGger:EDGE:LEVel?"))

myScope.DoCommand(":TRIGger:EDGE:SLOPe POSitive")
Console.WriteLine("Trigger edge slope: {0}", _
    myScope.DoQueryString(":TRIGger:EDGE:SLOPe?"))

' Save oscilloscope configuration.
Dim ResultsArray As Byte()   ' Results array.
Dim nLength As Integer   ' Number of bytes returned from inst.
Dim strPath As String
Dim fStream As FileStream

' Query and read setup string.
nLength = myScope.DoQueryIEEEBlock(":SYSTem:SETup?", _
    ResultsArray)

' Write setup string to file.
strPath = "c:\scope\config\setup.stp"
fStream = File.Open(strPath, FileMode.Create)
fStream.Write(ResultsArray, 0, nLength)
fStream.Close()
Console.WriteLine("Setup bytes saved: {0}", nLength)

' Change settings with individual commands:

' Set vertical scale and offset.
myScope.DoCommand(":CHANnel1:SCALe 0.05")
Console.WriteLine("Channel 1 vertical scale: {0}", _
    myScope.DoQueryString(":CHANnel1:SCALe?"))

myScope.DoCommand(":CHANnel1:OFFSet -1.5")
Console.WriteLine("Channel 1 vertical offset: {0}", _
    myScope.DoQueryString(":CHANnel1:OFFSet?"))

' Set horizontal scale and position.
myScope.DoCommand(":TIMebase:SCALe 0.0002")
Console.WriteLine("Timebase scale: {0}", _
    myScope.DoQueryString(":TIMebase:SCALe?"))

myScope.DoCommand(":TIMebase:POSition 0.0")
Console.WriteLine("Timebase position: {0}", _
    myScope.DoQueryString(":TIMebase:POSition?"))

' Set the acquisition type (NORMal, PEAK, AVERage, or HRESolution)
.
myScope.DoCommand(":ACQuire:TYPE NORMal")
Console.WriteLine("Acquire type: {0}", _
    myScope.DoQueryString(":ACQuire:TYPE?"))

' Or, configure by loading a previously saved setup.
Dim DataArray As Byte()
Dim nBytesWritten As Integer

' Read setup string from file.
strPath = "c:\scope\config\setup.stp"
DataArray = File.ReadAllBytes(strPath)
```

```
  ' Restore setup string.
  nBytesWritten = myScope.DoCommandIEEEBlock(":SYSTem:SETup", _
      DataArray)
  Console.WriteLine("Setup bytes restored: {0}", nBytesWritten)

  ' Capture an acquisition using :DIGitize.
  myScope.DoCommand(":DIGitize CHANnel1")

End Sub

'
' Analyze the captured waveform.
' ---------------------------------------------------------------

Private Shared Sub Analyze()

  Dim fResult As Double
  Dim ResultsArray As Byte()   ' Results array.
  Dim nLength As Integer   ' Number of bytes returned from inst.
  Dim strPath As String

  ' Make a couple of measurements.
  ' ---------------------------------------------------------------
  myScope.DoCommand(":MEASure:SOURce CHANnel1")
  Console.WriteLine("Measure source: {0}", _
      myScope.DoQueryString(":MEASure:SOURce?"))

  myScope.DoCommand(":MEASure:FREQuency")
  fResult = myScope.DoQueryNumber(":MEASure:FREQuency?")
  Console.WriteLine("Frequency: {0:F4} kHz", fResult / 1000)

  myScope.DoCommand(":MEASure:VAMPlitude")
  fResult = myScope.DoQueryNumber(":MEASure:VAMPlitude?")
  Console.WriteLine("Vertical amplitude: {0:F2} V", fResult)

  ' Download the screen image.
  ' ---------------------------------------------------------------
  myScope.DoCommand(":HARDcopy:INKSaver OFF")

  ' Get the screen data.
  nLength = myScope.DoQueryIEEEBlock(":DISPlay:DATA? PNG, COLor", _
      ResultsArray)

  ' Store the screen data to a file.
  strPath = "c:\scope\data\screen.png"
  Dim fStream As FileStream
  fStream = File.Open(strPath, FileMode.Create)
  fStream.Write(ResultsArray, 0, nLength)
  fStream.Close()
  Console.WriteLine("Screen image ({0} bytes) written to {1}", _
      nLength, strPath)

  ' Download waveform data.
  ' ---------------------------------------------------------------

  ' Set the waveform points mode.
  myScope.DoCommand(":WAVeform:POINts:MODE RAW")
```

```
Console.WriteLine("Waveform points mode: {0}", _
    myScope.DoQueryString(":WAVeform:POINts:MODE?"))

' Get the number of waveform points available.
myScope.DoCommand(":WAVeform:POINts 10240")
Console.WriteLine("Waveform points available: {0}", _
    myScope.DoQueryString(":WAVeform:POINts?"))

' Set the waveform source.
myScope.DoCommand(":WAVeform:SOURce CHANnel1")
Console.WriteLine("Waveform source: {0}", _
    myScope.DoQueryString(":WAVeform:SOURce?"))

' Choose the format of the data returned (WORD, BYTE, ASCII):
myScope.DoCommand(":WAVeform:FORMat BYTE")
Console.WriteLine("Waveform format: {0}", _
    myScope.DoQueryString(":WAVeform:FORMat?"))

' Display the waveform settings:
Dim fResultsArray As Double()
fResultsArray = myScope.DoQueryNumbers(":WAVeform:PREamble?")

Dim fFormat As Double = fResultsArray(0)
If fFormat = 0 Then
  Console.WriteLine("Waveform format: BYTE")
ElseIf fFormat = 1 Then
  Console.WriteLine("Waveform format: WORD")
ElseIf fFormat = 2 Then
  Console.WriteLine("Waveform format: ASCii")
End If

Dim fType As Double = fResultsArray(1)
If fType = 0 Then
  Console.WriteLine("Acquire type: NORMal")
ElseIf fType = 1 Then
  Console.WriteLine("Acquire type: PEAK")
ElseIf fType = 2 Then
  Console.WriteLine("Acquire type: AVERage")
ElseIf fType = 3 Then
  Console.WriteLine("Acquire type: HRESolution")
End If

Dim fPoints As Double = fResultsArray(2)
Console.WriteLine("Waveform points: {0:e}", fPoints)

Dim fCount As Double = fResultsArray(3)
Console.WriteLine("Waveform average count: {0:e}", fCount)

Dim fXincrement As Double = fResultsArray(4)
Console.WriteLine("Waveform X increment: {0:e}", fXincrement)

Dim fXorigin As Double = fResultsArray(5)
Console.WriteLine("Waveform X origin: {0:e}", fXorigin)

Dim fXreference As Double = fResultsArray(6)
Console.WriteLine("Waveform X reference: {0:e}", fXreference)
```

```
    Dim fYincrement As Double = fResultsArray(7)
    Console.WriteLine("Waveform Y increment: {0:e}", fYincrement)

    Dim fYorigin As Double = fResultsArray(8)
    Console.WriteLine("Waveform Y origin: {0:e}", fYorigin)

    Dim fYreference As Double = fResultsArray(9)
    Console.WriteLine("Waveform Y reference: {0:e}", fYreference)

    ' Get the waveform data.
    nLength = myScope.DoQueryIEEEBlock(":WAVeform:DATA?", _
        ResultsArray)
    Console.WriteLine("Number of data values: {0}", nLength)

    ' Set up output file:
    strPath = "c:\scope\data\waveform_data.csv"
    If File.Exists(strPath) Then
      File.Delete(strPath)
    End If

    ' Open file for output.
    Dim writer As StreamWriter = File.CreateText(strPath)

    ' Output waveform data in CSV format.
    For index As Integer = 0 To nLength - 1
      ' Write time value, voltage value.
      writer.WriteLine("{0:f9}, {1:f6}", _
          fXorigin + (CSng(index) * fXincrement), _
          ((CSng(ResultsArray(index)) - fYreference) _
          * fYincrement) + fYorigin)
    Next

    ' Close output file.
    writer.Close()
    Console.WriteLine("Waveform format BYTE data written to {0}", _
        strPath)

  End Sub

End Class

Class VisaInstrument
  Private m_nResourceManager As Integer
  Private m_nSession As Integer
  Private m_strVisaAddress As String

  ' Constructor.
  Public Sub New(ByVal strVisaAddress As String)
    ' Save VISA address in member variable.
    m_strVisaAddress = strVisaAddress

    ' Open the default VISA resource manager.
    OpenResourceManager()

    ' Open a VISA resource session.
    OpenSession()
```

```
  ' Clear the interface.
  Dim nViStatus As Integer
  nViStatus = visa32.viClear(m_nSession)
End Sub

Public Sub DoCommand(ByVal strCommand As String)
  ' Send the command.
  VisaSendCommandOrQuery(strCommand)

  ' Check for inst errors.
  CheckInstrumentErrors(strCommand)

End Sub

Public Function DoCommandIEEEBlock(ByVal strCommand As String, _
    ByVal DataArray As Byte()) As Integer

  ' Send the command to the device.
  Dim strCommandAndLength As String
  Dim nViStatus As Integer
  Dim nLength As Integer
  Dim nBytesWritten As Integer

  nLength = DataArray.Length
  strCommandAndLength = [String].Format("{0} #8{1:D8}", _
      strCommand, nLength)

  ' Write first part of command to formatted I/O write buffer.
  nViStatus = visa32.viPrintf(m_nSession, strCommandAndLength)
  CheckVisaStatus(nViStatus)

  ' Write the data to the formatted I/O write buffer.
  nViStatus = visa32.viBufWrite(m_nSession, DataArray, nLength, _
      nBytesWritten)
  CheckVisaStatus(nViStatus)

  ' Check for inst errors.
  CheckInstrumentErrors(strCommand)

  Return nBytesWritten
End Function

Public Function DoQueryString(ByVal strQuery As String) _
  As StringBuilder
  ' Send the query.
  VisaSendCommandOrQuery(strQuery)

  ' Get the result string.
  Dim strResults As New StringBuilder(1000)
  strResults = VisaGetResultString()

  ' Check for inst errors.
  CheckInstrumentErrors(strQuery)

  ' Return string results.
  Return strResults
End Function
```

```
Public Function DoQueryNumber(ByVal strQuery As String) As Double
  ' Send the query.
  VisaSendCommandOrQuery(strQuery)

  ' Get the result string.
  Dim fResults As Double
  fResults = VisaGetResultNumber()

  ' Check for inst errors.
  CheckInstrumentErrors(strQuery)

  ' Return string results.
  Return fResults
End Function

Public Function DoQueryNumbers(ByVal strQuery As String) _
    As Double()
  ' Send the query.
  VisaSendCommandOrQuery(strQuery)

  ' Get the result string.
  Dim fResultsArray As Double()
  fResultsArray = VisaGetResultNumbers()

  ' Check for instrument errors (another command and result).
  CheckInstrumentErrors(strQuery)

  ' Return string results.
  Return fResultsArray
End Function

Public Function DoQueryIEEEBlock(ByVal strQuery As String, _
    ByRef ResultsArray As Byte()) As Integer
  ' Send the query.
  VisaSendCommandOrQuery(strQuery)

  ' Get the result string.
  System.Threading.Thread.Sleep(2000) ' Delay before reading data.
  Dim length As Integer
  ' Number of bytes returned from instrument.
  length = VisaGetResultIEEEBlock(ResultsArray)

  ' Check for inst errors.
  CheckInstrumentErrors(strQuery)

  ' Return string results.
  Return length
End Function

Private Sub VisaSendCommandOrQuery(ByVal strCommandOrQuery _
     As String)
  ' Send command or query to the device.
  Dim strWithNewline As String
  strWithNewline = [String].Format("{0}" & Chr(10) & "", _
      strCommandOrQuery)
  Dim nViStatus As Integer
```

```
  nViStatus = visa32.viPrintf(m_nSession, strWithNewline)
  CheckVisaStatus(nViStatus)
End Sub

Private Function VisaGetResultString() As StringBuilder
  Dim strResults As New StringBuilder(1000)

  ' Read return value string from the device.
  Dim nViStatus As Integer
  nViStatus = visa32.viScanf(m_nSession, "%1000t", strResults)
  CheckVisaStatus(nViStatus)

  Return strResults
End Function

Private Function VisaGetResultNumber() As Double
  Dim fResults As Double = 0

  ' Read return value string from the device.
  Dim nViStatus As Integer
  nViStatus = visa32.viScanf(m_nSession, "%lf", fResults)
  CheckVisaStatus(nViStatus)

  Return fResults
End Function

Private Function VisaGetResultNumbers() As Double()
  Dim fResultsArray As Double()
  fResultsArray = New Double(9) {}

  ' Read return value string from the device.
  Dim nViStatus As Integer
  nViStatus = visa32.viScanf(m_nSession, _
      "%,10lf" & Chr(10) & "", fResultsArray)
  CheckVisaStatus(nViStatus)

  Return fResultsArray
End Function

Private Function VisaGetResultIEEEBlock(ByRef ResultsArray _
    As Byte()) As Integer
  ' Results array, big enough to hold a PNG.
  ResultsArray = New Byte(299999) {}
  Dim length As Integer
  ' Number of bytes returned from instrument.
  ' Set the default number of bytes that will be contained in
  ' the ResultsArray to 300,000 (300kB).
  length = 300000

  ' Read return value string from the device.
  Dim nViStatus As Integer
  nViStatus = visa32.viScanf(m_nSession, "%#b", length, _
      ResultsArray)
  CheckVisaStatus(nViStatus)

  ' Write and read buffers need to be flushed after IEEE block?
  nViStatus = visa32.viFlush(m_nSession, visa32.VI_WRITE_BUF)
```

```
  CheckVisaStatus(nViStatus)

  nViStatus = visa32.viFlush(m_nSession, visa32.VI_READ_BUF)
  CheckVisaStatus(nViStatus)

  Return length
End Function

Private Sub CheckInstrumentErrors(ByVal strCommand As String)
  ' Check for instrument errors.
  Dim strInstrumentError As New StringBuilder(1000)
  Dim bFirstError As Boolean = True
  Do   ' While not "0,No error"
    VisaSendCommandOrQuery(":SYSTem:ERRor?")
    strInstrumentError = VisaGetResultString()

    If Not strInstrumentError.ToString().StartsWith("+0,") Then
      If bFirstError Then
        Console.WriteLine("ERROR(s) for command '{0}': ", _
            strCommand)
        bFirstError = False
      End If
      Console.Write(strInstrumentError)
    End If
  Loop While Not strInstrumentError.ToString().StartsWith("+0,")
End Sub

Private Sub OpenResourceManager()
  Dim nViStatus As Integer
  nViStatus = visa32.viOpenDefaultRM(Me.m_nResourceManager)
  If nViStatus < visa32.VI_SUCCESS Then
    Throw New  _
        ApplicationException("Failed to open Resource Manager")
  End If
End Sub

Private Sub OpenSession()
  Dim nViStatus As Integer
  nViStatus = visa32.viOpen(Me.m_nResourceManager, _
      Me.m_strVisaAddress, visa32.VI_NO_LOCK, _
      visa32.VI_TMO_IMMEDIATE, Me.m_nSession)
  CheckVisaStatus(nViStatus)
End Sub

Public Sub SetTimeoutSeconds(ByVal nSeconds As Integer)
  Dim nViStatus As Integer
  nViStatus = visa32.viSetAttribute(Me.m_nSession, _
      visa32.VI_ATTR_TMO_VALUE, nSeconds * 1000)
  CheckVisaStatus(nViStatus)
End Sub

Public Sub CheckVisaStatus(ByVal nViStatus As Integer)
  ' If VISA error, throw exception.
  If nViStatus < visa32.VI_SUCCESS Then
    Dim strError As New StringBuilder(256)
    visa32.viStatusDesc(Me.m_nResourceManager, nViStatus, strError)
    Throw New ApplicationException(strError.ToString())
```

```
      End If
    End Sub

    Public Sub Close()
      If m_nSession <> 0 Then
        visa32.viClose(m_nSession)
      End If
      If m_nResourceManager <> 0 Then
        visa32.viClose(m_nResourceManager)
      End If
    End Sub
  End Class
End Namespace
```

VISA Example in Python 3

You can use the Python programming language with the PyVISA package to control Keysight InfiniiVision Series oscilloscopes.

The Python language and PyVISA package can be downloaded from the web at http://www.python.org/ and http://pyvisa.readthedocs.io/, respectively.

To run this example with Python and PyVISA:

1. Cut-and-paste the code that follows into a file named "example.py".
2. Edit the program to use the VISA address of your oscilloscope.
3. If "python.exe" can be found via your PATH environment variable, open a Command Prompt window; then, change to the folder that contains the "example.py" file, and enter:

```
python example.py
```

```
#!python3

# ********************************************************
# This program illustrates a few commonly-used programming
# features of your Keysight oscilloscope.
# ********************************************************

# Import modules.
# --------------------------------------------------------
import visa
import string
import struct
import sys

# Global variables (booleans: 0 = False, 1 = True).
# --------------------------------------------------------
debug = 0


# ========================================================
# Initialize:
# ========================================================
def initialize():
```

```
 # Get and display the device's *IDN? string.
 idn_string = do_query_string("*IDN?")
 print("Identification string: '%s'" % idn_string)

 # Clear status and load the default setup.
 do_command("*CLS")
 do_command("*RST")


# ============================================================
# Capture:
# ============================================================
def capture():

 # Use auto-scale to automatically set up oscilloscope.
 print("Autoscale.")
 do_command(":AUToscale")

 # Set trigger mode.
 do_command(":TRIGger:MODE EDGE")
 qresult = do_query_string(":TRIGger:MODE?")
 print("Trigger mode: %s" % qresult)

 # Set EDGE trigger parameters.
 do_command(":TRIGger:EDGE:SOURce CHANnel1")
 qresult = do_query_string(":TRIGger:EDGE:SOURce?")
 print("Trigger edge source: %s" % qresult)

 do_command(":TRIGger:EDGE:LEVel 1.5")
 qresult = do_query_string(":TRIGger:EDGE:LEVel?")
 print("Trigger edge level: %s" % qresult)

 do_command(":TRIGger:EDGE:SLOPe POSitive")
 qresult = do_query_string(":TRIGger:EDGE:SLOPe?")
 print("Trigger edge slope: %s" % qresult)

 # Save oscilloscope setup.
 sSetup = do_query_ieee_block(":SYSTem:SETup?")

 f = open("setup.stp", "wb")
 f.write(sSetup)
 f.close()
 print("Setup bytes saved: %d" % len(sSetup))

 # Change oscilloscope settings with individual commands:

 # Set vertical scale and offset.
 do_command(":CHANnel1:SCALe 0.05")
 qresult = do_query_string(":CHANnel1:SCALe?")
 print("Channel 1 vertical scale: %s" % qresult)

 do_command(":CHANnel1:OFFSet -1.5")
 qresult = do_query_string(":CHANnel1:OFFSet?")
 print("Channel 1 offset: %s" % qresult)

 # Set horizontal scale and offset.
```

```
 do_command(":TIMebase:SCALe 0.0002")
 qresult = do_query_string(":TIMebase:SCALe?")
 print("Timebase scale: %s" % qresult)

 do_command(":TIMebase:POSition 0.0")
 qresult = do_query_string(":TIMebase:POSition?")
 print("Timebase position: %s" % qresult)

 # Set the acquisition type.
 do_command(":ACQuire:TYPE NORMal")
 qresult = do_query_string(":ACQuire:TYPE?")
 print("Acquire type: %s" % qresult)

 # Or, set up oscilloscope by loading a previously saved setup.
 sSetup = ""
 f = open("setup.stp", "rb")
 sSetup = f.read()
 f.close()
 do_command_ieee_block(":SYSTem:SETup", sSetup)
 print("Setup bytes restored: %d" % len(sSetup))

 # Capture an acquisition using :DIGitize.
 do_command(":DIGitize CHANnel1")


# ============================================================
# Analyze:
# ============================================================
def analyze():

 # Make measurements.
 # ------------------------------------------------------------
 do_command(":MEASure:SOURce CHANnel1")
 qresult = do_query_string(":MEASure:SOURce?")
 print("Measure source: %s" % qresult)

 do_command(":MEASure:FREQuency")
 qresult = do_query_string(":MEASure:FREQuency?")
 print("Measured frequency on channel 1: %s" % qresult)

 do_command(":MEASure:VAMPlitude")
 qresult = do_query_string(":MEASure:VAMPlitude?")
 print("Measured vertical amplitude on channel 1: %s" % qresult)

 # Download the screen image.
 # ------------------------------------------------------------
 do_command(":HARDcopy:INKSaver OFF")

 sDisplay = do_query_ieee_block(":DISPlay:DATA? PNG, COLor")

 # Save display data values to file.
 f = open("screen_image.png", "wb")
 f.write(sDisplay)
 f.close()
 print("Screen image written to screen_image.png.")

 # Download waveform data.
```

```
# ----------------------------------------------------------

# Set the waveform points mode.
do_command(":WAVeform:POINts:MODE RAW")
qresult = do_query_string(":WAVeform:POINts:MODE?")
print("Waveform points mode: %s" % qresult)

# Get the number of waveform points available.
do_command(":WAVeform:POINts 10240")
qresult = do_query_string(":WAVeform:POINts?")
print("Waveform points available: %s" % qresult)

# Set the waveform source.
do_command(":WAVeform:SOURce CHANnel1")
qresult = do_query_string(":WAVeform:SOURce?")
print("Waveform source: %s" % qresult)

# Choose the format of the data returned:
do_command(":WAVeform:FORMat BYTE")
print("Waveform format: %s" % do_query_string(":WAVeform:FORMat?"))

# Display the waveform settings from preamble:
wav_form_dict = {
 0 : "BYTE",
 1 : "WORD",
 4 : "ASCii",
}
acq_type_dict = {
 0 : "NORMal",
 1 : "PEAK",
 2 : "AVERage",
 3 : "HRESolution",
}

preamble_string = do_query_string(":WAVeform:PREamble?")
(
 wav_form, acq_type, wfmpts, avgcnt, x_increment, x_origin,
 x_reference, y_increment, y_origin, y_reference
) = preamble_string.split(",")

print("Waveform format: %s" % wav_form_dict[int(wav_form)])
print("Acquire type: %s" % acq_type_dict[int(acq_type)])
print("Waveform points desired: %s" % wfmpts)
print("Waveform average count: %s" % avgcnt)
print("Waveform X increment: %s" % x_increment)
print("Waveform X origin: %s" % x_origin)
print("Waveform X reference: %s" % x_reference)   # Always 0.
print("Waveform Y increment: %s" % y_increment)
print("Waveform Y origin: %s" % y_origin)
print("Waveform Y reference: %s" % y_reference)

# Get numeric values for later calculations.
x_increment = do_query_number(":WAVeform:XINCrement?")
x_origin = do_query_number(":WAVeform:XORigin?")
y_increment = do_query_number(":WAVeform:YINCrement?")
y_origin = do_query_number(":WAVeform:YORigin?")
y_reference = do_query_number(":WAVeform:YREFerence?")
```

```
 # Get the waveform data.
 sData = do_query_ieee_block(":WAVeform:DATA?")

 # Unpack unsigned byte data.
 values = struct.unpack("%dB" % len(sData), sData)
 print("Number of data values: %d" % len(values))

 # Save waveform data values to CSV file.
 f = open("waveform_data.csv", "w")

 for i in range(0, len(values) - 1):
  time_val = x_origin + (i * x_increment)
  voltage = ((values[i] - y_reference) * y_increment) + y_origin
  f.write("%E, %f\n" % (time_val, voltage))

 f.close()
 print("Waveform format BYTE data written to waveform_data.csv.")


# ============================================================
# Send a command and check for errors:
# ============================================================
def do_command(command, hide_params=False):

 if hide_params:
  (header, data) = command.split(" ", 1)
  if debug:
   print("\nCmd = '%s'" % header)
 else:
  if debug:
   print("\nCmd = '%s'" % command)

 InfiniiVision.write("%s" % command)

 if hide_params:
  check_instrument_errors(header)
 else:
  check_instrument_errors(command)


# ============================================================
# Send a command and binary values and check for errors:
# ============================================================
def do_command_ieee_block(command, values):
 if debug:
  print("Cmb = '%s'" % command)
 InfiniiVision.write_binary_values("%s " % command, values, datatype='B'
)
 check_instrument_errors(command)


# ============================================================
# Send a query, check for errors, return string:
# ============================================================
def do_query_string(query):
 if debug:
```

```
  print("Qys = '%s'" % query)
 result = InfiniiVision.query("%s" % query)
 check_instrument_errors(query)
 return result


# ============================================================
# Send a query, check for errors, return floating-point value:
# ============================================================
def do_query_number(query):
 if debug:
  print("Qyn = '%s'" % query)
 results = InfiniiVision.query("%s" % query)
 check_instrument_errors(query)
 return float(results)


# ============================================================
# Send a query, check for errors, return binary values:
# ============================================================
def do_query_ieee_block(query):
 if debug:
  print("Qys = '%s'" % query)
 result = InfiniiVision.query_binary_values("%s" % query, datatype='s')
 check_instrument_errors(query)
 return result[0]


# ============================================================
# Check for instrument errors:
# ============================================================
def check_instrument_errors(command):

 while True:
  error_string = InfiniiVision.query(":SYSTem:ERRor?")
  if error_string:   # If there is an error string value.

   if error_string.find("+0,", 0, 3) == -1:   # Not "No error".

    print("ERROR: %s, command: '%s'" % (error_string, command))
    print("Exited because of error.")
    sys.exit(1)

   else:   # "No error"
    break

  else:   # :SYSTem:ERRor? should always return string.
   print("ERROR: :SYSTem:ERRor? returned nothing, command: '%s'" % comma
nd)
   print("Exited because of error.")
   sys.exit(1)


# ============================================================
# Main program:
# ============================================================
```

```
rm = visa.ResourceManager("C:\\Windows\\System32\\agvisa32.dll")
InfiniiVision= rm.open_resource("TCPIP0::141.121.237.208::hislip0::INSTR
")

InfiniiVision.timeout = 15000
InfiniiVision.clear()

# Initialize the oscilloscope, capture data, and analyze.
initialize()
capture()
analyze()

InfiniiVision.close()
print("End of program.")
sys.exit()
```

VISA.NET Examples

These programming examples show how to use the VISA.NET drivers that come with Keysight IO Libraries Suite.

- "VISA.NET Example in C#" on page 918
- "VISA.NET Example in Visual Basic .NET" on page 924

VISA.NET Example in C#

To compile and run this example in Microsoft Visual Studio 2013:

1. Open Visual Studio.
2. Choose **FILE > New > Project...**.
3. In the New Project dialog box, select **.NET Framework 4.5.2**.
4. Create a new Visual C#, Console Application project.
5. Cut-and-paste the code that follows into the C# source file.
6. Edit the program to use the VISA address of your oscilloscope.
7. Add a reference to the VISA.NET driver:
   a. Right-click the project you wish to modify (not the solution) in the Solution Explorer window of the Microsoft Visual Studio environment.
   b. Choose **Add Reference...**.
   c. In the Reference Manager dialog box, under **Assemblies**, select **Extensions**.
   d. In the "Targeting: .NET Framework 4.5.2" list, select the **Ivi.Visa Assembly** check box; then, click **OK**.
8. Build and run the program.

For more information, see the VISA.NET Help that comes with Keysight IO Libraries Suite.

```
/*
 * Keysight VISA.NET Example in C#
 * ----------------------------------------------------------------------
 * This program illustrates a few commonly used programming
 * features of your Keysight InfiniiVision oscilloscope.
 * ----------------------------------------------------------------------
 */

using System;
using System.IO;
using System.Collections.Generic;
using System.Text;

using Ivi.Visa;
using Ivi.Visa.FormattedIO;
```

```
namespace Example
{
  class Program
  {

    static void Main(string[] args)
    {
      // Change this variable to the address of your instrument
      string VISA_ADDRESS = "USB0::0x2A8D::0x1797::CN56240004::0::INSTR"
;

      // Create a connection (session) to the instrument
      IMessageBasedSession session;
      try
      {
        session = GlobalResourceManager.Open(VISA_ADDRESS) as
          IMessageBasedSession;
      }
      catch (NativeVisaException visaException)
      {
        Console.WriteLine("Couldn't connect.");
        Console.WriteLine("Error is:\r\n{0}\r\n", visaException);
        Console.WriteLine("Press any key to exit...");
        Console.ReadKey();
        return;
      }

      // Create a formatted I/O object which will help us format the
      // data we want to send/receive to/from the instrument
      MessageBasedFormattedIO myScope =
        new MessageBasedFormattedIO(session);

      // For Serial and TCP/IP socket connections enable the read
      // Termination Character, or read's will timeout
      if (session.ResourceName.Contains("ASRL") ||
          session.ResourceName.Contains("SOCKET"))
        session.TerminationCharacterEnabled = true;

      session.TimeoutMilliseconds = 20000;

      // Initialize - start from a known state.
      // ================================================================
      string strResults;
      FileStream fStream;

      // Get and display the device's *IDN? string.
      myScope.WriteLine("*IDN?");
      strResults = myScope.ReadLine();
      Console.WriteLine("*IDN? result is: {0}", strResults);

      // Clear status and load the default setup.
      myScope.WriteLine("*CLS");
      myScope.WriteLine("*RST");

      // Capture data.
      // ================================================================
      // Use auto-scale to automatically configure oscilloscope.
```

```
myScope.WriteLine(":AUToscale");

// Set trigger mode (EDGE, PULSe, PATTern, etc., and input source.
myScope.WriteLine(":TRIGger:MODE EDGE");
myScope.WriteLine(":TRIGger:MODE?");
strResults = myScope.ReadLine();
Console.WriteLine("Trigger mode: {0}", strResults);

// Set EDGE trigger parameters.
myScope.WriteLine(":TRIGger:EDGE:SOURce CHANnel1");
myScope.WriteLine(":TRIGger:EDGE:SOURce?");
strResults = myScope.ReadLine();
Console.WriteLine("Trigger edge source: {0}", strResults);

myScope.WriteLine(":TRIGger:EDGE:LEVel 1.5");
myScope.WriteLine(":TRIGger:EDGE:LEVel?");
strResults = myScope.ReadLine();
Console.WriteLine("Trigger edge level: {0}", strResults);

myScope.WriteLine(":TRIGger:EDGE:SLOPe POSitive");
myScope.WriteLine(":TRIGger:EDGE:SLOPe?");
strResults = myScope.ReadLine();
Console.WriteLine("Trigger edge slope: {0}", strResults);

// Save oscilloscope configuration.
byte[] ResultsArray;   // Results array.
int nLength;   // Number of bytes returned from instrument.
string strPath;

// Query and read setup string.
myScope.WriteLine(":SYSTem:SETup?");
ResultsArray = myScope.ReadLineBinaryBlockOfByte();
nLength = ResultsArray.Length;

// Write setup string to file.
strPath = "c:\\scope\\config\\setup.stp";
fStream = File.Open(strPath, FileMode.Create);
fStream.Write(ResultsArray, 0, nLength);
fStream.Close();
Console.WriteLine("Setup bytes saved: {0}", nLength);

// Change settings with individual commands:

// Set vertical scale and offset.
myScope.WriteLine(":CHANnel1:SCALe 0.05");
myScope.WriteLine(":CHANnel1:SCALe?");
strResults = myScope.ReadLine();
Console.WriteLine("Channel 1 vertical scale: {0}", strResults);

myScope.WriteLine(":CHANnel1:OFFSet -1.5");
myScope.WriteLine(":CHANnel1:OFFSet?");
strResults = myScope.ReadLine();
Console.WriteLine("Channel 1 vertical offset: {0}", strResults);

// Set horizontal scale and offset.
myScope.WriteLine(":TIMebase:SCALe 0.0002");
myScope.WriteLine(":TIMebase:SCALe?");
```

```
        strResults = myScope.ReadLine();
        Console.WriteLine("Timebase scale: {0}", strResults);

        myScope.WriteLine(":TIMebase:POSition 0.0");
        myScope.WriteLine(":TIMebase:POSition?");
        strResults = myScope.ReadLine();
        Console.WriteLine("Timebase position: {0}", strResults);

        // Set the acquisition type (NORMal, PEAK, AVERage, or HRESolution
).
        myScope.WriteLine(":ACQuire:TYPE NORMal");
        myScope.WriteLine(":ACQuire:TYPE?");
        strResults = myScope.ReadLine();
        Console.WriteLine("Acquire type: {0}", strResults);

        // Or, configure by loading a previously saved setup.
        byte[] DataArray;
        int nBytesWritten;

        // Read setup string from file.
        strPath = "c:\\scope\\config\\setup.stp";
        DataArray = File.ReadAllBytes(strPath);
        nBytesWritten = DataArray.Length;

        // Restore setup string.
        myScope.Write(":SYSTem:SETup ");
        myScope.WriteBinary(DataArray);
        myScope.WriteLine("");
        Console.WriteLine("Setup bytes restored: {0}", nBytesWritten);

        // Capture an acquisition using :DIGitize.
        myScope.WriteLine(":DIGitize CHANnel1");

        // Analyze the captured waveform.
        // ============================================================

        // Make a couple of measurements.
        // ------------------------------------------------------------
        myScope.WriteLine(":MEASure:SOURce CHANnel1");
        myScope.WriteLine(":MEASure:SOURce?");
        strResults = myScope.ReadLine();
        Console.WriteLine("Measure source: {0}", strResults);

        double fResult;
        myScope.WriteLine(":MEASure:FREQuency");
        myScope.WriteLine(":MEASure:FREQuency?");
        fResult = myScope.ReadLineDouble();
        Console.WriteLine("Frequency: {0:F4} kHz", fResult / 1000);

        myScope.WriteLine(":MEASure:VAMPlitude");
        myScope.WriteLine(":MEASure:VAMPlitude?");
        fResult = myScope.ReadLineDouble();
        Console.WriteLine("Vertical amplitude: {0:F2} V", fResult);

        // Download the screen image.
        // ------------------------------------------------------------
        myScope.WriteLine(":HARDcopy:INKSaver OFF");
```

```
// Get the screen data.
myScope.WriteLine(":DISPlay:DATA? PNG, COLor");
ResultsArray = myScope.ReadLineBinaryBlockOfByte();
nLength = ResultsArray.Length;

// Store the screen data to a file.
strPath = "c:\\scope\\data\\screen.png";
fStream = File.Open(strPath, FileMode.Create);
fStream.Write(ResultsArray, 0, nLength);
fStream.Close();
Console.WriteLine("Screen image ({0} bytes) written to {1}",
    nLength, strPath);

// Download waveform data.
// ------------------------------------------------------------

// Set the waveform points mode.
myScope.WriteLine(":WAVeform:POINts:MODE RAW");
myScope.WriteLine(":WAVeform:POINts:MODE?");
strResults = myScope.ReadLine();
Console.WriteLine("Waveform points mode: {0}", strResults);

// Get the number of waveform points available.
myScope.WriteLine(":WAVeform:POINts?");
strResults = myScope.ReadLine();
Console.WriteLine("Waveform points available: {0}", strResults);

// Set the waveform source.
myScope.WriteLine(":WAVeform:SOURce CHANnel1");
myScope.WriteLine(":WAVeform:SOURce?");
strResults = myScope.ReadLine();
Console.WriteLine("Waveform source: {0}", strResults);

// Choose the format of the data returned (WORD, BYTE, ASCII):
myScope.WriteLine(":WAVeform:FORMat BYTE");
myScope.WriteLine(":WAVeform:FORMat?");
strResults = myScope.ReadLine();
Console.WriteLine("Waveform format: {0}", strResults);

// Display the waveform settings:
double[] fResultsArray;
myScope.WriteLine(":WAVeform:PREamble?");
fResultsArray = myScope.ReadLineListOfDouble();

double fFormat = fResultsArray[0];
if (fFormat == 0.0)
{
  Console.WriteLine("Waveform format: BYTE");
}
else if (fFormat == 1.0)
{
  Console.WriteLine("Waveform format: WORD");
}
else if (fFormat == 2.0)
{
  Console.WriteLine("Waveform format: ASCii");
```

```
}

double fType = fResultsArray[1];
if (fType == 0.0)
{
  Console.WriteLine("Acquire type: NORMal");
}
else if (fType == 1.0)
{
  Console.WriteLine("Acquire type: PEAK");
}
else if (fType == 2.0)
{
  Console.WriteLine("Acquire type: AVERage");
}
else if (fType == 3.0)
{
  Console.WriteLine("Acquire type: HRESolution");
}

double fPoints = fResultsArray[2];
Console.WriteLine("Waveform points: {0:e}", fPoints);

double fCount = fResultsArray[3];
Console.WriteLine("Waveform average count: {0:e}", fCount);

double fXincrement = fResultsArray[4];
Console.WriteLine("Waveform X increment: {0:e}", fXincrement);

double fXorigin = fResultsArray[5];
Console.WriteLine("Waveform X origin: {0:e}", fXorigin);

double fXreference = fResultsArray[6];
Console.WriteLine("Waveform X reference: {0:e}", fXreference);

double fYincrement = fResultsArray[7];
Console.WriteLine("Waveform Y increment: {0:e}", fYincrement);

double fYorigin = fResultsArray[8];
Console.WriteLine("Waveform Y origin: {0:e}", fYorigin);

double fYreference = fResultsArray[9];
Console.WriteLine("Waveform Y reference: {0:e}", fYreference);

// Read waveform data.
myScope.WriteLine(":WAVeform:DATA?");
ResultsArray = myScope.ReadLineBinaryBlockOfByte();
nLength = ResultsArray.Length;
Console.WriteLine("Number of data values: {0}", nLength);

// Set up output file:
strPath = "c:\\scope\\data\\waveform_data.csv";
if (File.Exists(strPath)) File.Delete(strPath);

// Open file for output.
StreamWriter writer = File.CreateText(strPath);
```

```
            // Output waveform data in CSV format.
            for (int i = 0; i < nLength - 1; i++)
              writer.WriteLine("{0:f9}, {1:f6}",
                  fXorigin + ((float)i * fXincrement),
                  (((float)ResultsArray[i] - fYreference)
                  * fYincrement) + fYorigin);

            // Close output file.
            writer.Close();
            Console.WriteLine("Waveform format BYTE data written to {0}",
                strPath);

            // Close the connection to the instrument
            // ------------------------------------------------------------
            session.Dispose();

            Console.WriteLine("Press any key to exit...");
            Console.ReadKey();

        }
      }
    }
```

VISA.NET Example in Visual Basic .NET

To compile and run this example in Microsoft Visual Studio 2013:

1. Open Visual Studio.
2. Choose **FILE > New > Project...**.
3. In the New Project dialog box, select **.NET Framework 4.5.2**.
4. Create a new Visual Basic, Console Application project.
5. Cut-and-paste the code that follows into the Visual Basic .NET source file.
6. Edit the program to use the VISA address of your oscilloscope.
7. Add a reference to the VISA.NET driver:
   a. Right-click the project you wish to modify (not the solution) in the Solution Explorer window of the Microsoft Visual Studio environment.
   b. Choose **Add Reference...**.
   c. In the Reference Manager dialog box, under **Assemblies**, select **Extensions**.
   d. In the "Targeting: .NET Framework 4.5.2" list, select the **Ivi.Visa Assembly** check box; then, click **OK**.

8 Specify the Startup object:

   a Right-click the project you wish to modify (not the solution) in the Solution Explorer window of the Microsoft Visual Studio environment.

   b Choose **Properties**.

   c In the Properties dialog box, under **Application**, select the **Startup object:** field and choose **Sub Main**.

   d Save your change and close the Properties dialog box.

9 Build and run the program.

For more information, see the VISA.NET driver help that comes with Keysight Command Expert.

```
'
' Keysight VISA.NET Example in VB.NET
' ----------------------------------------------------------------------
' This program illustrates a few commonly used programming
' features of your Keysight InfiniiVision oscilloscope.
' ----------------------------------------------------------------------

Imports System
Imports System.IO
Imports System.Collections.Generic
Imports System.Text

Imports Ivi.Visa
Imports Ivi.Visa.FormattedIO


Namespace Example
  Class Program

    Public Shared Sub Main(args As String())
      ' Change this variable to the address of your instrument
      Dim VISA_ADDRESS As String = "USB0::0x2A8D::0x1797::CN56240004::0:
:INSTR"

      ' Create a connection (session) to the instrument
      Dim session As IMessageBasedSession
      Try
        session = TryCast(GlobalResourceManager.Open(VISA_ADDRESS),  _
            IMessageBasedSession)
      Catch visaException As NativeVisaException
        Console.WriteLine("Couldn't connect.")
        Console.WriteLine("Error is:" & vbCr & vbLf & "{0}" _
            & vbCr & vbLf, visaException)
        Console.WriteLine("Press any key to exit...")
        Console.ReadKey()
        Return
      End Try

      ' Create a formatted I/O object which will help us format the
      ' data we want to send/receive to/from the instrument
      Dim myScope As New MessageBasedFormattedIO(session)
```

```
' For Serial and TCP/IP socket connections enable the read
' Termination Character, or read's will timeout
If session.ResourceName.Contains("ASRL") OrElse _
  session.ResourceName.Contains("SOCKET") Then
  session.TerminationCharacterEnabled = True
End If

session.TimeoutMilliseconds = 20000

' Initialize - start from a known state.
' ================================================================
Dim strResults As String
Dim fStream As FileStream

' Get and display the device's *IDN? string.
myScope.WriteLine("*IDN?")
strResults = myScope.ReadLine()
Console.WriteLine("*IDN? result is: {0}", strResults)

' Clear status and load the default setup.
myScope.WriteLine("*CLS")
myScope.WriteLine("*RST")

' Capture data.
' ================================================================
' Use auto-scale to automatically configure oscilloscope.
myScope.WriteLine(":AUToscale")

' Set trigger mode (EDGE, PULSe, PATTern, etc., and input source.
myScope.WriteLine(":TRIGger:MODE EDGE")
myScope.WriteLine(":TRIGger:MODE?")
strResults = myScope.ReadLine()
Console.WriteLine("Trigger mode: {0}", strResults)

' Set EDGE trigger parameters.
myScope.WriteLine(":TRIGger:EDGE:SOURce CHANnel1")
myScope.WriteLine(":TRIGger:EDGE:SOURce?")
strResults = myScope.ReadLine()
Console.WriteLine("Trigger edge source: {0}", strResults)

myScope.WriteLine(":TRIGger:EDGE:LEVel 1.5")
myScope.WriteLine(":TRIGger:EDGE:LEVel?")
strResults = myScope.ReadLine()
Console.WriteLine("Trigger edge level: {0}", strResults)

myScope.WriteLine(":TRIGger:EDGE:SLOPe POSitive")
myScope.WriteLine(":TRIGger:EDGE:SLOPe?")
strResults = myScope.ReadLine()
Console.WriteLine("Trigger edge slope: {0}", strResults)

' Save oscilloscope configuration.
Dim ResultsArray As Byte()
' Results array.
Dim nLength As Integer
' Number of bytes returned from instrument.
Dim strPath As String
```

```
' Query and read setup string.
myScope.WriteLine(":SYSTem:SETup?")
ResultsArray = myScope.ReadLineBinaryBlockOfByte()
nLength = ResultsArray.Length

' Write setup string to file.
strPath = "c:\scope\config\setup.stp"
fStream = File.Open(strPath, FileMode.Create)
fStream.Write(ResultsArray, 0, nLength)
fStream.Close()
Console.WriteLine("Setup bytes saved: {0}", nLength)

' Change settings with individual commands:

' Set vertical scale and offset.
myScope.WriteLine(":CHANnel1:SCALe 0.05")
myScope.WriteLine(":CHANnel1:SCALe?")
strResults = myScope.ReadLine()
Console.WriteLine("Channel 1 vertical scale: {0}", strResults)

myScope.WriteLine(":CHANnel1:OFFSet -1.5")
myScope.WriteLine(":CHANnel1:OFFSet?")
strResults = myScope.ReadLine()
Console.WriteLine("Channel 1 vertical offset: {0}", strResults)

' Set horizontal scale and offset.
myScope.WriteLine(":TIMebase:SCALe 0.0002")
myScope.WriteLine(":TIMebase:SCALe?")
strResults = myScope.ReadLine()
Console.WriteLine("Timebase scale: {0}", strResults)

myScope.WriteLine(":TIMebase:POSition 0.0")
myScope.WriteLine(":TIMebase:POSition?")
strResults = myScope.ReadLine()
Console.WriteLine("Timebase position: {0}", strResults)

' Set the acquisition type (NORMal, PEAK, AVERage, or HRESolution)
.
myScope.WriteLine(":ACQuire:TYPE NORMal")
myScope.WriteLine(":ACQuire:TYPE?")
strResults = myScope.ReadLine()
Console.WriteLine("Acquire type: {0}", strResults)

' Or, configure by loading a previously saved setup.
Dim DataArray As Byte()
Dim nBytesWritten As Integer

' Read setup string from file.
strPath = "c:\scope\config\setup.stp"
DataArray = File.ReadAllBytes(strPath)
nBytesWritten = DataArray.Length

' Restore setup string.
myScope.Write(":SYSTem:SETup ")
myScope.WriteBinary(DataArray)
myScope.WriteLine("")
```

```
Console.WriteLine("Setup bytes restored: {0}", nBytesWritten)

' Capture an acquisition using :DIGitize.
myScope.WriteLine(":DIGitize CHANnel1")

' Analyze the captured waveform.
' ==========================================================

' Make a couple of measurements.
' ----------------------------------------------------------
myScope.WriteLine(":MEASure:SOURce CHANnel1")
myScope.WriteLine(":MEASure:SOURce?")
strResults = myScope.ReadLine()
Console.WriteLine("Measure source: {0}", strResults)

Dim fResult As Double
myScope.WriteLine(":MEASure:FREQuency")
myScope.WriteLine(":MEASure:FREQuency?")
fResult = myScope.ReadLineDouble()
Console.WriteLine("Frequency: {0:F4} kHz", fResult / 1000)

myScope.WriteLine(":MEASure:VAMPlitude")
myScope.WriteLine(":MEASure:VAMPlitude?")
fResult = myScope.ReadLineDouble()
Console.WriteLine("Vertical amplitude: {0:F2} V", fResult)

' Download the screen image.
' ----------------------------------------------------------
myScope.WriteLine(":HARDcopy:INKSaver OFF")

' Get the screen data.
myScope.WriteLine(":DISPlay:DATA? PNG, COLor")
ResultsArray = myScope.ReadLineBinaryBlockOfByte()
nLength = ResultsArray.Length

' Store the screen data to a file.
strPath = "c:\scope\data\screen.png"
fStream = File.Open(strPath, FileMode.Create)
fStream.Write(ResultsArray, 0, nLength)
fStream.Close()
Console.WriteLine("Screen image ({0} bytes) written to {1}", _
    nLength, strPath)

' Download waveform data.
' ----------------------------------------------------------

' Set the waveform points mode.
myScope.WriteLine(":WAVeform:POINts:MODE RAW")
myScope.WriteLine(":WAVeform:POINts:MODE?")
strResults = myScope.ReadLine()
Console.WriteLine("Waveform points mode: {0}", strResults)

' Get the number of waveform points available.
myScope.WriteLine(":WAVeform:POINts?")
strResults = myScope.ReadLine()
Console.WriteLine("Waveform points available: {0}", strResults)
```

```
' Set the waveform source.
myScope.WriteLine(":WAVeform:SOURce CHANnel1")
myScope.WriteLine(":WAVeform:SOURce?")
strResults = myScope.ReadLine()
Console.WriteLine("Waveform source: {0}", strResults)

' Choose the format of the data returned (WORD, BYTE, ASCII):
myScope.WriteLine(":WAVeform:FORMat BYTE")
myScope.WriteLine(":WAVeform:FORMat?")
strResults = myScope.ReadLine()
Console.WriteLine("Waveform format: {0}", strResults)

' Display the waveform settings:
Dim fResultsArray As Double()
myScope.WriteLine(":WAVeform:PREamble?")
fResultsArray = myScope.ReadLineListOfDouble()

Dim fFormat As Double = fResultsArray(0)
If fFormat = 0.0 Then
  Console.WriteLine("Waveform format: BYTE")
ElseIf fFormat = 1.0 Then
  Console.WriteLine("Waveform format: WORD")
ElseIf fFormat = 2.0 Then
  Console.WriteLine("Waveform format: ASCii")
End If

Dim fType As Double = fResultsArray(1)
If fType = 0.0 Then
  Console.WriteLine("Acquire type: NORMal")
ElseIf fType = 1.0 Then
  Console.WriteLine("Acquire type: PEAK")
ElseIf fType = 2.0 Then
  Console.WriteLine("Acquire type: AVERage")
ElseIf fType = 3.0 Then
  Console.WriteLine("Acquire type: HRESolution")
End If

Dim fPoints As Double = fResultsArray(2)
Console.WriteLine("Waveform points: {0:e}", fPoints)

Dim fCount As Double = fResultsArray(3)
Console.WriteLine("Waveform average count: {0:e}", fCount)

Dim fXincrement As Double = fResultsArray(4)
Console.WriteLine("Waveform X increment: {0:e}", fXincrement)

Dim fXorigin As Double = fResultsArray(5)
Console.WriteLine("Waveform X origin: {0:e}", fXorigin)

Dim fXreference As Double = fResultsArray(6)
Console.WriteLine("Waveform X reference: {0:e}", fXreference)

Dim fYincrement As Double = fResultsArray(7)
Console.WriteLine("Waveform Y increment: {0:e}", fYincrement)

Dim fYorigin As Double = fResultsArray(8)
Console.WriteLine("Waveform Y origin: {0:e}", fYorigin)
```

```
        Dim fYreference As Double = fResultsArray(9)
        Console.WriteLine("Waveform Y reference: {0:e}", fYreference)

        ' Read waveform data.
        myScope.WriteLine(":WAVeform:DATA?")
        ResultsArray = myScope.ReadLineBinaryBlockOfByte()
        nLength = ResultsArray.Length
        Console.WriteLine("Number of data values: {0}", nLength)

        ' Set up output file:
        strPath = "c:\scope\data\waveform_data.csv"
        If File.Exists(strPath) Then
          File.Delete(strPath)
        End If

        ' Open file for output.
        Dim writer As StreamWriter = File.CreateText(strPath)

        ' Output waveform data in CSV format.
        For i As Integer = 0 To nLength - 2
          writer.WriteLine("{0:f9}, {1:f6}", _
              fXorigin + (CSng(i) * fXincrement), _
              ((CSng(ResultsArray(i)) - fYreference) _
              * fYincrement) + fYorigin)
        Next

        ' Close output file.
        writer.Close()
        Console.WriteLine("Waveform format BYTE data written to {0}", _
            strPath)

        ' Close the connection to the instrument
        ' ------------------------------------------------------------
        session.Dispose()

        Console.WriteLine("Press any key to exit...")
        Console.ReadKey()

    End Sub
  End Class
End Namespace
```

SICL Examples

- "SICL Example in C" on page 931
- "SICL Example in Visual Basic" on page 940

SICL Example in C

To compile and run this example in Microsoft Visual Studio 2008:

1. Open Visual Studio.
2. Create a new Visual C++, Win32, Win32 Console Application project.
3. In the Win32 Application Wizard, click **Next >**. Then, check **Empty project**, and click **Finish**.
4. Cut-and-paste the code that follows into a file named "example.c" in the project directory.
5. In Visual Studio 2008, right-click the Source Files folder, choose **Add > Add Existing Item...**, select the example.c file, and click **Add**.
6. Edit the program to use the SICL address of your oscilloscope.
7. Choose **Project > Properties...**. In the Property Pages dialog, update these project settings:
   a. Under Configuration Properties, Linker, Input, add "sicl32.lib" to the Additional Dependencies field.
   b. Under Configuration Properties, C/C++, Code Generation, select Multi-threaded DLL for the Runtime Library field.
   c. Click **OK** to close the Property Pages dialog.
8. Add the include files and library files search paths:
   a. Choose **Tools > Options...**.
   b. In the Options dialog, select **VC++ Directories** under Projects and Solutions.
   c. Show directories for **Include files**, and add the include directory (for example, Program Files\Agilent\IO Libraries Suite\include).
   d. Show directories for **Library files**, and add the library files directory (for example, Program Files\Agilent\IO Libraries Suite\lib).
   e. Click **OK** to close the Options dialog.
9. Build and run the program.

```
/*
 * Keysight SICL Example in C
 * ------------------------------------------------------------------------
 * This program illustrates a few commonly-used programming
 * features of your Keysight oscilloscope.
 */

#include <stdio.h>            /* For printf(). */
```

```
#include <string.h>           /* For strcpy(), strcat(). */
#include <time.h>             /* For clock(). */
#include <sicl.h>             /* Keysight SICL routines. */

#define SICL_ADDRESS      "usb0[2391::6054::US50210029::0]"
#define TIMEOUT           5000
#define IEEEBLOCK_SPACE   100000

/* Function prototypes */
void initialize(void);          /* Initialize to known state. */
void capture(void);             /* Capture the waveform. */
void analyze(void);             /* Analyze the captured waveform. */

void do_command(char *command);        /* Send command. */
int do_command_ieeeblock(char *command); /* Command w/IEEE block. */
void do_query_string(char *query);     /* Query for string. */
void do_query_number(char *query);     /* Query for number. */
void do_query_numbers(char *query);    /* Query for numbers. */
int do_query_ieeeblock(char *query);   /* Query for IEEE block. */
void check_instrument_errors();        /* Check for inst errors. */

/* Global variables */
INST id;                        /* Device session ID. */
char str_result[256] = {0};     /* Result from do_query_string(). */
double num_result;              /* Result from do_query_number(). */
unsigned char ieeeblock_data[IEEEBLOCK_SPACE];   /* Result from
                                   do_query_ieeeblock(). */
double dbl_results[10];         /* Result from do_query_numbers(). */

/* Main Program
 * ------------------------------------------------------------- */
void main(void)
{
  /* Install a default SICL error handler that logs an error message
   * and exits.  On Windows 98SE or Windows Me, view messages with
   * the SICL Message Viewer.  For Windows 2000 or XP, use the Event
   * Viewer.
   */
  ionerror(I_ERROR_EXIT);

  /* Open a device session using the SICL_ADDRESS */
  id = iopen(SICL_ADDRESS);

  if (id == 0)
  {
    printf ("Oscilloscope iopen failed!\n");
  }
  else
  {
    printf ("Oscilloscope session opened!\n");
  }

  /* Initialize - start from a known state. */
  initialize();

  /* Capture data. */
  capture();
```

```
  /* Analyze the captured waveform. */
  analyze();

  /* Close the device session to the instrument. */
  iclose(id);
  printf ("Program execution is complete...\n");

  /* For WIN16 programs, call _siclcleanup before exiting to release
   * resources allocated by SICL for this application.  This call is
   * a no-op for WIN32 programs.
   */
  _siclcleanup();
}

/* Initialize the oscilloscope to a known state.
 * ------------------------------------------------------------------- */
void initialize (void)
{
  /* Set the I/O timeout value for this session to 5 seconds. */
  itimeout(id, TIMEOUT);

  /* Clear the interface. */
  iclear(id);

  /* Get and display the device's *IDN? string. */
  do_query_string("*IDN?");
  printf("Oscilloscope *IDN? string: %s\n", str_result);

  /* Clear status and load the default setup. */
  do_command("*CLS");
  do_command("*RST");
}

/* Capture the waveform.
 * ------------------------------------------------------------------- */
void capture (void)
{
  int num_bytes;
  FILE *fp;

  /* Use auto-scale to automatically configure oscilloscope.
   * ------------------------------------------------------------ */
  do_command(":AUToscale");

  /* Set trigger mode (EDGE, PULSe, PATTern, etc., and input source. */
  do_command(":TRIGger:MODE EDGE");
  do_query_string(":TRIGger:MODE?");
  printf("Trigger mode: %s\n", str_result);

  /* Set EDGE trigger parameters. */
  do_command(":TRIGger:EDGE:SOURCe CHANnel1");
  do_query_string(":TRIGger:EDGE:SOURce?");
  printf("Trigger edge source: %s\n", str_result);

  do_command(":TRIGger:EDGE:LEVel 1.5");
  do_query_string(":TRIGger:EDGE:LEVel?");
```

```
  printf("Trigger edge level: %s\n", str_result);

  do_command(":TRIGger:EDGE:SLOPe POSitive");
  do_query_string(":TRIGger:EDGE:SLOPe?");
  printf("Trigger edge slope: %s\n", str_result);

  /* Save oscilloscope configuration.
   * ------------------------------------------------------------ */

  /* Read system setup. */
  num_bytes = do_query_ieeeblock(":SYSTem:SETup?");
  printf("Read setup string query (%d bytes).\n", num_bytes);

  /* Write setup string to file. */
  fp = fopen ("c:\\scope\\config\\setup.stp", "wb");
  num_bytes = fwrite(ieeeblock_data, sizeof(unsigned char), num_bytes,
    fp);
  fclose (fp);
  printf("Wrote setup string (%d bytes) to ", num_bytes);
  printf("c:\\scope\\config\\setup.stp.\n");

  /* Change settings with individual commands:
   * ------------------------------------------------------------ */

  /* Set vertical scale and offset. */
  do_command(":CHANnel1:SCALe 0.05");
  do_query_string(":CHANnel1:SCALe?");
  printf("Channel 1 vertical scale: %s\n", str_result);

  do_command(":CHANnel1:OFFSet -1.5");
  do_query_string(":CHANnel1:OFFSet?");
  printf("Channel 1 offset: %s\n", str_result);

  /* Set horizontal scale and position. */
  do_command(":TIMebase:SCALe 0.0002");
  do_query_string(":TIMebase:SCALe?");
  printf("Timebase scale: %s\n", str_result);

  do_command(":TIMebase:POSition 0.0");
  do_query_string(":TIMebase:POSition?");
  printf("Timebase position: %s\n", str_result);

  /* Set the acquisition type (NORMal, PEAK, AVERage, or HRESolution). *
/
  do_command(":ACQuire:TYPE NORMal");
  do_query_string(":ACQuire:TYPE?");
  printf("Acquire type: %s\n", str_result);

  /* Or, configure by loading a previously saved setup.
  * ------------------------------------------------------------ */

  /* Read setup string from file. */
  fp = fopen ("c:\\scope\\config\\setup.stp", "rb");
  num_bytes = fread (ieeeblock_data, sizeof(unsigned char),
    IEEEBLOCK_SPACE, fp);
  fclose (fp);
  printf("Read setup string (%d bytes) from file ", num_bytes);
```

```
  printf("c:\\scope\\config\\setup.stp.\n");

  /* Restore setup string. */
  num_bytes = do_command_ieeeblock(":SYSTem:SETup", num_bytes);
  printf("Restored setup string (%d bytes).\n", num_bytes);

  /* Capture an acquisition using :DIGitize.
   * ------------------------------------------------------------- */
  do_command(":DIGitize CHANnel1");
}

/* Analyze the captured waveform.
 * ------------------------------------------------------------- */
void analyze (void)
{
  double wav_format;
  double acq_type;
  double wav_points;
  double avg_count;
  double x_increment;
  double x_origin;
  double x_reference;
  double y_increment;
  double y_origin;
  double y_reference;

  FILE *fp;
  int num_bytes;   /* Number of bytes returned from instrument. */
  int i;

  /* Make a couple of measurements.
   * ------------------------------------------------------------- */
  do_command(":MEASure:SOURce CHANnel1");
  do_query_string(":MEASure:SOURce?");
  printf("Measure source: %s\n", str_result);

  do_command(":MEASure:FREQuency");
  do_query_number(":MEASure:FREQuency?");
  printf("Frequency: %.4f kHz\n", num_result / 1000);

  do_command(":MEASure:VAMPlitude");
  do_query_number(":MEASure:VAMPlitude?");
  printf("Vertical amplitude: %.2f V\n", num_result);

  /* Download the screen image.
   * ------------------------------------------------------------- */
  do_command(":HARDcopy:INKSaver OFF");

  /* Read screen image. */
  num_bytes = do_query_ieeeblock(":DISPlay:DATA? PNG, COLor");
  printf("Screen image bytes: %d\n", num_bytes);

  /* Write screen image bytes to file. */
  fp = fopen ("c:\\scope\\data\\screen.png", "wb");
  num_bytes = fwrite(ieeeblock_data, sizeof(unsigned char), num_bytes,
    fp);
  fclose (fp);
```

```
printf("Wrote screen image (%d bytes) to ", num_bytes);
printf("c:\\scope\\data\\screen.png.\n");

/* Download waveform data.
 * -------------------------------------------------------------- */

/* Set the waveform points mode. */
do_command(":WAVeform:POINts:MODE RAW");
do_query_string(":WAVeform:POINts:MODE?");
printf("Waveform points mode: %s\n", str_result);

/* Get the number of waveform points available. */
do_command(":WAVeform:POINts 10240");
do_query_string(":WAVeform:POINts?");
printf("Waveform points available: %s\n", str_result);

/* Set the waveform source. */
do_command(":WAVeform:SOURce CHANnel1");
do_query_string(":WAVeform:SOURce?");
printf("Waveform source: %s\n", str_result);

/* Choose the format of the data returned (WORD, BYTE, ASCII): */
do_command(":WAVeform:FORMat BYTE");
do_query_string(":WAVeform:FORMat?");
printf("Waveform format: %s\n", str_result);

/* Display the waveform settings: */
do_query_numbers(":WAVeform:PREamble?");

wav_format = dbl_results[0];
if (wav_format == 0.0)
{
  printf("Waveform format: BYTE\n");
}
else if (wav_format == 1.0)
{
  printf("Waveform format: WORD\n");
}
else if (wav_format == 2.0)
{
  printf("Waveform format: ASCii\n");
}

acq_type = dbl_results[1];
if (acq_type == 0.0)
{
  printf("Acquire type: NORMal\n");
}
else if (acq_type == 1.0)
{
  printf("Acquire type: PEAK\n");
}
else if (acq_type == 2.0)
{
  printf("Acquire type: AVERage\n");
}
else if (acq_type == 3.0)
```

```
  {
    printf("Acquire type: HRESolution\n");
  }

  wav_points = dbl_results[2];
  printf("Waveform points: %e\n", wav_points);

  avg_count = dbl_results[3];
  printf("Waveform average count: %e\n", avg_count);

  x_increment = dbl_results[4];
  printf("Waveform X increment: %e\n", x_increment);

  x_origin = dbl_results[5];
  printf("Waveform X origin: %e\n", x_origin);

  x_reference = dbl_results[6];
  printf("Waveform X reference: %e\n", x_reference);

  y_increment = dbl_results[7];
  printf("Waveform Y increment: %e\n", y_increment);

  y_origin = dbl_results[8];
  printf("Waveform Y origin: %e\n", y_origin);

  y_reference = dbl_results[9];
  printf("Waveform Y reference: %e\n", y_reference);

  /* Read waveform data. */
  num_bytes = do_query_ieeeblock(":WAVeform:DATA?");
  printf("Number of data values: %d\n", num_bytes);

  /* Open file for output. */
  fp = fopen("c:\\scope\\data\\waveform_data.csv", "wb");

  /* Output waveform data in CSV format. */
  for (i = 0; i < num_bytes - 1; i++)
  {
    /* Write time value, voltage value. */
    fprintf(fp, "%9f, %6f\n",
      x_origin + ((float)i * x_increment),
      (((float)ieeeblock_data[i] - y_reference) * y_increment)
      + y_origin);
  }

  /* Close output file. */
   fclose(fp);
   printf("Waveform format BYTE data written to ");
   printf("c:\\scope\\data\\waveform_data.csv.\n");
}

/* Send a command to the instrument.
 * ---------------------------------------------------------------- */
void do_command(command)
char *command;
{
  char message[80];
```

```
  strcpy(message, command);
  strcat(message, "\n");
  iprintf(id, message);

  check_instrument_errors();
}

/* Command with IEEE definite-length block.
 * ------------------------------------------------------------------- */
int do_command_ieeeblock(command, num_bytes)
char *command;
int num_bytes;
{
  char message[80];
  int data_length;

  strcpy(message, command);
  strcat(message, " #8%08d");
  iprintf(id, message, num_bytes);
  ifwrite(id, ieeeblock_data, num_bytes, 1, &data_length);

  check_instrument_errors();

  return(data_length);
}

/* Query for a string result.
 * ------------------------------------------------------------------- */
void do_query_string(query)
char *query;
{
  char message[80];

  strcpy(message, query);
  strcat(message, "\n");
  iprintf(id, message);

  iscanf(id, "%t\n", str_result);

  check_instrument_errors();
}

/* Query for a number result.
 * ------------------------------------------------------------------- */
void do_query_number(query)
char *query;
{
  char message[80];

  strcpy(message, query);
  strcat(message, "\n");
  iprintf(id, message);

  iscanf(id, "%lf", &num_result);

  check_instrument_errors();
```

```
}

/* Query for numbers result.
 * ------------------------------------------------------------------- */
void do_query_numbers(query)
char *query;
{
  char message[80];

  strcpy(message, query);
  strcat(message, "\n");
  iprintf(id, message);

  iscanf(id, "%,10lf\n", dbl_results);

  check_instrument_errors();
}

/* Query for an IEEE definite-length block result.
 * ------------------------------------------------------------------- */
int do_query_ieeeblock(query)
char *query;
{
  char message[80];
  int data_length;

  strcpy(message, query);
  strcat(message, "\n");
  iprintf(id, message);

  data_length = IEEEBLOCK_SPACE;
  iscanf(id, "%#b", &data_length, ieeeblock_data);

  if (data_length == IEEEBLOCK_SPACE )
  {
    printf("IEEE block buffer full: ");
    printf("May not have received all data.\n");
  }

  check_instrument_errors();

  return(data_length);
}

/* Check for instrument errors.
 * ------------------------------------------------------------------- */
void check_instrument_errors()
{
  char str_err_val[256] = {0};
  char str_out[800] = "";

  ipromptf(id, ":SYSTem:ERRor?\n", "%t", str_err_val);
  while(strncmp(str_err_val, "+0,No error", 3) != 0 )
  {
    strcat(str_out, ", ");
    strcat(str_out, str_err_val);
    ipromptf(id, ":SYSTem:ERRor?\n", "%t", str_err_val);
```

```
  }

  if (strcmp(str_out, "") != 0)
  {
    printf("INST Error%s\n", str_out);
    iflush(id, I_BUF_READ | I_BUF_WRITE);
  }
}
```

SICL Example in Visual Basic

To run this example in Visual Basic for Applications:

1. Start the application that provides Visual Basic for Applications (for example, Microsoft Excel).
2. Press ALT+F11 to launch the Visual Basic editor.
3. Add the sicl32.bas file to your project:
   a. Choose **File > Import File...**.
   b. Navigate to the header file, sicl32.bas (installed with Keysight IO Libraries Suite and found in the Program Files\Agilent\IO Libraries Suite\include directory), select it, and click **Open**.
4. Choose **Insert > Module**.
5. Cut-and-paste the code that follows into the editor.
6. Edit the program to use the SICL address of your oscilloscope, and save the changes.
7. Run the program.

```
'
' Keysight SICL Example in Visual Basic
' ----------------------------------------------------------------------
' This program illustrates a few commonly-used programming
' features of your Keysight oscilloscope.
' ----------------------------------------------------------------------

Option Explicit

Public id As Integer   ' Session to instrument.

' Declare variables to hold numeric values returned by
' ivscanf/ifread.
Public dblQueryResult As Double
Public Const ByteArraySize = 5000000
Public retCount As Long
Public byteArray(ByteArraySize) As Byte

' Declare fixed length string variable to hold string value returned
' by ivscanf.
Public strQueryResult As String * 200

' For Sleep subroutine.
```

```
Private Declare Sub Sleep Lib "kernel32" (ByVal dwMilliseconds As Long)

'
' Main Program
' ---------------------------------------------------------------------

Sub Main()

  On Error GoTo ErrorHandler

  ' Open a device session using the SICL_ADDRESS.
  id = iopen("usb0[2391::6054::US50210029::0]")
  Call itimeout(id, 5000)

  ' Initialize - start from a known state.
  Initialize

  ' Capture data.
  Capture

  ' Analyze the captured waveform.
  Analyze

  ' Close the vi session and the resource manager session.
  Call iclose(id)

  Exit Sub

ErrorHandler:

  MsgBox "*** Error : " + Error, vbExclamation
  End

End Sub

'
' Initialize the oscilloscope to a known state.
' ---------------------------------------------------------------------

Private Sub Initialize()

  On Error GoTo ErrorHandler

  ' Clear the interface.
  Call iclear(id)

  ' Get and display the device's *IDN? string.
  strQueryResult = DoQueryString("*IDN?")
  MsgBox "Result is: " + RTrim(strQueryResult), vbOKOnly, "*IDN? Result"

  ' Clear status and load the default setup.
  DoCommand "*CLS"
  DoCommand "*RST"

  Exit Sub

ErrorHandler:
```

```
  MsgBox "*** Error : " + Error, vbExclamation
  End

End Sub

'
' Capture the waveform.
' ----------------------------------------------------------------------

Private Sub Capture()

  On Error GoTo ErrorHandler

  ' Use auto-scale to automatically configure oscilloscope.
  ' ----------------------------------------------------------------------
  DoCommand ":AUToscale"

  ' Set trigger mode (EDGE, PULSe, PATTern, etc., and input source.
  DoCommand ":TRIGger:MODE EDGE"
  Debug.Print "Trigger mode: " + _
      DoQueryString(":TRIGger:MODE?")

  ' Set EDGE trigger parameters.
  DoCommand ":TRIGger:EDGE:SOURCe CHANnel1"
  Debug.Print "Trigger edge source: " + _
      DoQueryString(":TRIGger:EDGE:SOURce?")

  DoCommand ":TRIGger:EDGE:LEVel 1.5"
  Debug.Print "Trigger edge level: " + _
      DoQueryString(":TRIGger:EDGE:LEVel?")

  DoCommand ":TRIGger:EDGE:SLOPe POSitive"
  Debug.Print "Trigger edge slope: " + _
      DoQueryString(":TRIGger:EDGE:SLOPe?")

  ' Save oscilloscope configuration.
  ' ----------------------------------------------------------------------
  Dim lngSetupStringSize As Long
  lngSetupStringSize = DoQueryIEEEBlock_Bytes(":SYSTem:SETup?")
  Debug.Print "Setup bytes saved: " + CStr(lngSetupStringSize)

  ' Output setup string to a file:
  Dim strPath As String
  strPath = "c:\scope\config\setup.dat"
  If Len(Dir(strPath)) Then
    Kill strPath   ' Remove file if it exists.
  End If

  ' Open file for output.
  Dim hFile As Long
  hFile = FreeFile
  Open strPath For Binary Access Write Lock Write As hFile
  Dim lngI As Long
  For lngI = 0 To lngSetupStringSize - 1
    Put hFile, , byteArray(lngI)   ' Write data.
  Next lngI
```

```
  Close hFile   ' Close file.

  ' Change settings with individual commands:
  ' ------------------------------------------------------------------

  ' Set vertical scale and offset.
  DoCommand ":CHANnel1:SCALe 0.05"
  Debug.Print "Channel 1 vertical scale: " + _
      DoQueryString(":CHANnel1:SCALe?")

  DoCommand ":CHANnel1:OFFSet -1.5"
  Debug.Print "Channel 1 vertical offset: " + _
      DoQueryString(":CHANnel1:OFFSet?")

  ' Set horizontal scale and position.
  DoCommand ":TIMebase:SCALe 0.0002"
  Debug.Print "Timebase scale: " + _
      DoQueryString(":TIMebase:SCALe?")

  DoCommand ":TIMebase:POSition 0.0"
  Debug.Print "Timebase position: " + _
      DoQueryString(":TIMebase:POSition?")

  ' Set the acquisition type (NORMal, PEAK, AVERage, or HRESolution).
  DoCommand ":ACQuire:TYPE NORMal"
  Debug.Print "Acquire type: " + _
      DoQueryString(":ACQuire:TYPE?")

  ' Or, configure by loading a previously saved setup.
  ' ------------------------------------------------------------------
  strPath = "c:\scope\config\setup.dat"
  Open strPath For Binary Access Read As hFile   ' Open file for input.
  Dim lngSetupFileSize As Long
  lngSetupFileSize = LOF(hFile)  ' Length of file.
  Get hFile, , byteArray   ' Read data.
  Close hFile   ' Close file.
  ' Write setup string back to oscilloscope using ":SYSTem:SETup"
  ' command:
  Dim lngRestored As Long
  lngRestored = DoCommandIEEEBlock(":SYSTem:SETup", lngSetupFileSize)
  Debug.Print "Setup bytes restored: " + CStr(lngRestored)

  ' Capture an acquisition using :DIGitize.
  ' ------------------------------------------------------------------
  DoCommand ":DIGitize CHANnel1"

  Exit Sub

ErrorHandler:

  MsgBox "*** Error : " + Error, vbExclamation
  End

End Sub

'
' Analyze the captured waveform.
```

```
' ----------------------------------------------------------------------

Private Sub Analyze()

  On Error GoTo ErrorHandler

  ' Make a couple of measurements.
  ' --------------------------------------------------------------------
  DoCommand ":MEASure:SOURce CHANnel1"
  Debug.Print "Measure source: " + _
      DoQueryString(":MEASure:SOURce?")

  DoCommand ":MEASure:FREQuency"
  dblQueryResult = DoQueryNumber(":MEASure:FREQuency?")
  MsgBox "Frequency:" + vbCrLf + _
      FormatNumber(dblQueryResult / 1000, 4) + " kHz"

  DoCommand ":MEASure:VAMPlitude"
  dblQueryResult = DoQueryNumber(":MEASure:VAMPlitude?")
  MsgBox "Vertical amplitude:" + vbCrLf + _
      FormatNumber(dblQueryResult, 4) + " V"

  ' Download the screen image.
  ' --------------------------------------------------------------------
  DoCommand ":HARDcopy:INKSaver OFF"

  ' Get screen image.
  Dim lngBlockSize As Long
  lngBlockSize = DoQueryIEEEBlock_Bytes(":DISPlay:DATA? PNG, COLor")
  Debug.Print "Screen image bytes: " + CStr(lngBlockSize)

  ' Save screen image to a file:
  Dim strPath As String
  strPath = "c:\scope\data\screen.png"
  If Len(Dir(strPath)) Then
    Kill strPath   ' Remove file if it exists.
  End If
  Dim hFile As Long
  hFile = FreeFile
  Open strPath For Binary Access Write Lock Write As hFile
  Dim lngI As Long
  ' Skip past header.
  For lngI = CInt(Chr(byteArray(1))) + 2 To lngBlockSize - 1
    Put hFile, , byteArray(lngI)   ' Write data.
  Next lngI
  Close hFile   ' Close file.
  MsgBox "Screen image written to " + strPath

  ' Download waveform data.
  ' --------------------------------------------------------------------

  ' Set the waveform points mode.
  DoCommand ":WAVeform:POINts:MODE RAW"
  Debug.Print "Waveform points mode: " + _
      DoQueryString(":WAVeform:POINts:MODE?")

  ' Get the number of waveform points available.
```

```
DoCommand ":WAVeform:POINts 10240"
Debug.Print "Waveform points available: " + _
    DoQueryString(":WAVeform:POINts?")

' Set the waveform source.
DoCommand ":WAVeform:SOURce CHANnel1"
Debug.Print "Waveform source: " + _
    DoQueryString(":WAVeform:SOURce?")

' Choose the format of the data returned (WORD, BYTE, ASCII):
DoCommand ":WAVeform:FORMat BYTE"
Debug.Print "Waveform format: " + _
    DoQueryString(":WAVeform:FORMat?")

' Display the waveform settings:
Dim Preamble() As Double
Dim intFormat As Integer
Dim intType As Integer
Dim lngPoints As Long
Dim lngCount As Long
Dim dblXIncrement As Double
Dim dblXOrigin As Double
Dim lngXReference As Long
Dim sngYIncrement As Single
Dim sngYOrigin As Single
Dim lngYReference As Long

Preamble() = DoQueryNumbers(":WAVeform:PREamble?")

intFormat = Preamble(0)
intType = Preamble(1)
lngPoints = Preamble(2)
lngCount = Preamble(3)
dblXIncrement = Preamble(4)
dblXOrigin = Preamble(5)
lngXReference = Preamble(6)
sngYIncrement = Preamble(7)
sngYOrigin = Preamble(8)
lngYReference = Preamble(9)

If intFormat = 0 Then
  Debug.Print "Waveform format: BYTE"
ElseIf intFormat = 1 Then
  Debug.Print "Waveform format: WORD"
ElseIf intFormat = 2 Then
  Debug.Print "Waveform format: ASCii"
End If

If intType = 0 Then
  Debug.Print "Acquisition type: NORMal"
ElseIf intType = 1 Then
  Debug.Print "Acquisition type: PEAK"
ElseIf intType = 2 Then
  Debug.Print "Acquisition type: AVERage"
ElseIf intType = 3 Then
  Debug.Print "Acquisition type: HRESolution"
End If
```

```
Debug.Print "Waveform points: " + _
    FormatNumber(lngPoints, 0)

Debug.Print "Waveform average count: " + _
    FormatNumber(lngCount, 0)

Debug.Print "Waveform X increment: " + _
    Format(dblXIncrement, "Scientific")

Debug.Print "Waveform X origin: " + _
    Format(dblXOrigin, "Scientific")

Debug.Print "Waveform X reference: " + _
    FormatNumber(lngXReference, 0)

Debug.Print "Waveform Y increment: " + _
    Format(sngYIncrement, "Scientific")

Debug.Print "Waveform Y origin: " + _
    FormatNumber(sngYOrigin, 0)

Debug.Print "Waveform Y reference: " + _
    FormatNumber(lngYReference, 0)

' Get the waveform data
Dim lngNumBytes As Long
lngNumBytes = DoQueryIEEEBlock_Bytes(":WAVeform:DATA?")
Debug.Print "Number of data values: " + _
    CStr(lngNumBytes - CInt(Chr(byteArray(1))) - 2)

' Set up output file:
strPath = "c:\scope\data\waveform_data.csv"

' Open file for output.
Open strPath For Output Access Write Lock Write As hFile

' Output waveform data in CSV format.
Dim lngDataValue As Long

' Skip past header.
For lngI = CInt(Chr(byteArray(1))) + 2 To lngNumBytes - 2
  lngDataValue = CLng(byteArray(lngI))

  ' Write time value, voltage value.
  Print #hFile, _
      FormatNumber(dblXOrigin + (lngI * dblXIncrement), 9) + _
      ", " + _
      FormatNumber(((lngDataValue - lngYReference) * _
      sngYIncrement) + sngYOrigin)

Next lngI

' Close output file.
Close hFile   ' Close file.
MsgBox "Waveform format BYTE data written to " + _
    "c:\scope\data\waveform_data.csv."
```

```
  Exit Sub

ErrorHandler:

  MsgBox "*** Error : " + Error, vbExclamation
  End

End Sub

Private Sub DoCommand(command As String)

  On Error GoTo ErrorHandler

  Call ivprintf(id, command + vbLf)

  CheckInstrumentErrors

  Exit Sub

ErrorHandler:

  MsgBox "*** Error : " + Error, vbExclamation
  End

End Sub

Private Function DoCommandIEEEBlock(command As String, _
    lngBlockSize As Long)

  On Error GoTo ErrorHandler

  ' Send command part.
  Call ivprintf(id, command + " ")

  ' Write definite-length block bytes.
  Call ifwrite(id, byteArray(), lngBlockSize, vbNull, retCount)

  ' retCount is now actual number of bytes written.
  DoCommandIEEEBlock = retCount

  CheckInstrumentErrors

  Exit Function

ErrorHandler:

  MsgBox "*** Error : " + Error, vbExclamation
  End

End Function

Private Function DoQueryString(query As String) As String

  Dim actual As Long

  On Error GoTo ErrorHandler
```

```
  Dim strResult As String * 200

  Call ivprintf(id, query + vbLf)
  Call ivscanf(id, "%200t", strResult)
  DoQueryString = strResult

  CheckInstrumentErrors

  Exit Function

ErrorHandler:

  MsgBox "*** Error : " + Error, vbExclamation
  End

End Function

Private Function DoQueryNumber(query As String) As Double

  On Error GoTo ErrorHandler

  Dim dblResult As Double

  Call ivprintf(id, query + vbLf)
  Call ivscanf(id, "%lf" + vbLf, dblResult)
  DoQueryNumber = dblResult

  CheckInstrumentErrors

  Exit Function

ErrorHandler:

  MsgBox "*** Error : " + Error, vbExclamation
  End

End Function

Private Function DoQueryNumbers(query As String) As Double()

  On Error GoTo ErrorHandler

  Dim dblResults(10) As Double

  Call ivprintf(id, query + vbLf)
  Call ivscanf(id, "%,10lf" + vbLf, dblResults)
  DoQueryNumbers = dblResults

  CheckInstrumentErrors

  Exit Function

ErrorHandler:

  MsgBox "*** Error : " + Error, vbExclamation
  End
```

```
End Function

Private Function DoQueryIEEEBlock_Bytes(query As String) As Long

  On Error GoTo ErrorHandler

  ' Send query.
  Call ivprintf(id, query + vbLf)

  ' Read definite-length block bytes.
  Sleep 2000   ' Delay before reading data.
  Call ifread(id, byteArray(), ByteArraySize, vbNull, retCount)

  ' Get number of block length digits.
  Dim intLengthDigits As Integer
  intLengthDigits = CInt(Chr(byteArray(1)))

  ' Get block length from those digits.
  Dim strBlockLength As String
  strBlockLength = ""
  Dim i As Integer
  For i = 2 To intLengthDigits + 1
    strBlockLength = strBlockLength + Chr(byteArray(i))
  Next

  ' Return number of bytes in block plus header.
  DoQueryIEEEBlock_Bytes = CLng(strBlockLength) + intLengthDigits + 2

  CheckInstrumentErrors

  Exit Function

ErrorHandler:

  MsgBox "*** Error : " + Error, vbExclamation
  End

End Function

Private Sub CheckInstrumentErrors()

  On Error GoTo ErrorHandler

  Dim strErrVal As String * 200
  Dim strOut As String

  Call ivprintf(id, ":SYSTem:ERRor?" + vbLf)   ' Query any errors data.
  Call ivscanf(id, "%200t", strErrVal)   ' Read: Errnum,"Error String".
  While Val(strErrVal) <> 0             ' End if find: +0,"No Error".
    strOut = strOut + "INST Error: " + strErrVal
    Call ivprintf(id, ":SYSTem:ERRor?" + vbLf)   ' Request error message
.
    Call ivscanf(id, "%200t", strErrVal)   ' Read error message.
  Wend

  If Not strOut = "" Then
```

```
    MsgBox strOut, vbExclamation, "INST Error Messages"
    Call iflush(id, I_BUF_READ Or I_BUF_WRITE)

  End If

  Exit Sub

ErrorHandler:

  MsgBox "*** Error : " + Error, vbExclamation
  End

End Sub
```

SCPI.NET Examples

You can also program the oscilloscope using the SCPI.NET drivers that come with Keysight's free Command Expert software.

While you can write code manually using the SCPI.NET drivers, you can also use the Command Expert software to:

- Connect to instruments and control them interactively using SCPI command sets.
- Quickly prototype and test command sequences.
- Generate C#, VB.NET, or C/C++ code for command sequences.
- Find, download, and install SCPI command sets.
- Browse command trees, search for commands, and view command descriptions.

The Command Expert suite also comes with Add-ons for easy instrument control and measurement data retrieval in NI LabVIEW, Microsoft Excel, Keysight VEE, and Keysight SystemVue.

To download the Keysight Command Expert software, see:
http://www.keysight.com/find/commandexpert

For more on programming with the SCPI.NET drivers, see "Using SCPI.NET Drivers" in the help that comes with Keysight Command Expert.

Index

Symbols

+9.9E+37, infinity representation, 835
+9.9E+37, measurement error, 367

Numerics

0 (zero) values in waveform data, 672
1 (one) values in waveform data, 672
1000 X-Series oscilloscopes, command differences from, 32
82350A GPIB interface, 6

A

abus bit selection command, 179
abus bits selection commands, 180
abus clear command, 182
ABUS commands, 177, 178
abus display, 183
abus label command, 184
abus mask command, 185
AC coupling, trigger edge, 628
AC input coupling for specified channel, 216
AC RMS measured on waveform, 417
ACQuire commands, 187
acquire data, 153, 199
acquire mode on autoscale, 149
acquire reset conditions, 131, 586
acquire sample rate, 198
ACQuire subsystem, 47
acquired data points, 192
acquisition count, 190
acquisition mode, 187, 191, 689
acquisition type, 187, 199
acquisition types, 665
active printer, 326
add function, 684
add math function, 315
add math function as g(t) source, 311
address field size, IIC serial decode, 510
address of network printer, 331
address, IIC trigger pattern, 513
Addresses softkey, 38
AER (Arm Event Register), 146, 161, 163, 811
all (snapshot) measurement, 369
ALL segments waveform save option, 483
AM demo signal, 234
AM depth, waveform generator modulation, 709
AM modulation type, waveform generator, 719
amplitude, vertical, 411
amplitude, waveform generator, 299, 726
analog channel coupling, 216
analog channel display, 217
analog channel impedance, 218
analog channel input, 748
analog channel inversion, 219
analog channel labels, 220, 247
analog channel offset, 221
analog channel protection lock, 589
analog channel range, 228
analog channel scale, 229
analog channel source for glitch, 640
analog channel units, 230
analog probe attenuation, 222
analog probe head type, 223
analog probe sensing, 749
analog probe skew, 225, 747
analyzing captured data, 43
angle brackets, 114
annotate channels, 220
annotation background, display, 240
annotation color, display, 241
annotation text, display, 242
annotation, display, 239
apply network printer connection settings, 332
area for hardcopy print, 325
area for saved image, 784
Arm Event Register (AER), 146, 161, 163, 811
ASCII format, 674
ASCII format for data transfer, 668
ASCII string, quoted, 114
ASCiixy waveform data format, 480
assign channel names, 220
attenuation factor (external trigger) probe, 268
attenuation for oscilloscope probe, 222
AUT option for probe sense, 749, 752
Auto Range capability for DVM, 254
auto set up, trigger level, 621
auto trigger sweep mode, 615
automask create, 429
automask source, 430
automask units, 431
automatic measurements constants, 222
automatic probe type detection, 749, 752
autoscale, 147
autoscale acquire mode, 149
autoscale channels, 150
AUToscale command, 46
average value measurement, 412
averaging acquisition type, 188, 667
averaging, synchronizing with, 824

B

bandwidth filter limits, 214, 263
bandwidth filter limits to 20 MHz, 215
base value measurement, 413
base, UART trigger, 567
basic instrument functions, 119
baud rate, 500, 523, 556
begin acquisition, 153, 170, 172
BHARris window for minimal spectral leakage, 282, 309
binary block data, 114, 244, 597, 672
BINary waveform data format, 480
bind levels for masks, 450
bit order, 557
bit order, SPI decode, 535
bit rate measurement, 370
bit selection command, abus, 179
bit weights, 124
bitmap display, 244
bits in Service Request Enable Register, 136
bits in Standard Event Status Enable Register, 123
bits in Status Byte Register, 138
bits selection command, abus, 180
blank, 152
block data, 114, 127, 597
block response data, 50
blocking synchronization, 819
blocking wait, 818
BMP format screen image data, 244
braces, 113
built-in measurements, 43
burst data demo signal, 234
button disable, 582
button, calibration protect, 206
byte format for data transfer, 669, 674
BYTeorder, 670

C

C, SICL library example, 931
C, VISA library example, 871

C#, VISA COM example, 847
C#, VISA example, 890
C#, VISA.NET example, 918
CAL PROTECT button, 206
CAL PROTECT switch, 202
calculating preshoot of waveform, 391
calculating the waveform overshoot, 385
calibrate, 203, 204, 206, 210
CALibrate commands, 201
calibrate date, 203
calibrate introduction, 202
calibrate label, 204
calibrate output, 205
calibrate start, 207
calibrate status, 208
calibrate switch, 206
calibrate temperature, 209
calibrate time, 210
CAN acknowledge, 499
CAN baud rate, 500
CAN demo signal, 235
CAN frame counters, reset, 496
CAN serial bus commands, 492
CAN signal definition, 501
CAN source, 502
CAN trigger, 503, 506
CAN trigger data pattern, 505
CAN trigger ID pattern, 507
CAN trigger pattern id mode, 508
CAN triggering, 487
capture data, 153
capturing data, 42
center frequency set, 273, 303, 305, 315
center of screen, 697
center reference, 608
center screen, FFT vertical value at, 275, 277
center screen, vertical value at, 314, 318
channel, 176, 220
channel coupling, 216
channel display, 217
channel input impedance, 218
channel inversion, 219
channel label, 220, 746
channel labels, 246, 247
channel overload, 227
channel protection, 227
channel reset conditions, 131, 586
channel selected to produce trigger, 640, 661
channel signal type, 226
channel skew for oscilloscope probe, 225, 747
channel status, 173
channel vernier, 231
channel, stop displaying, 152
CHANnel<n> commands, 211, 213
channels to autoscale, 150
channels, how autoscale affects, 147
characters to display, 580
classes of input signals, 282, 309
classifications, command, 828
clear, 243
clear abus command, 182
clear markers, 371, 762
clear measurement, 371, 762
clear message queue, 121
Clear method, 45
clear reference waveforms, 733
clear screen, 751
clear status, 121
clear waveform area, 238
clipped high waveform data value, 672
clipped low waveform data value, 672
clock, 511, 536, 539
clock source, setup and hold trigger, 648
clock timeout, SPI, 537
clock with infrequent glitch demo signal, 234
CLS (Clear Status), 121
CME (Command Error) status bit, 123, 125
code, :ACQuire:COMPlete, 189
code, :ACQuire:SEGMented, 195
code, :ACQuire:TYPE, 200
code, :AUToscale, 148
code, :CHANnel<n>:LABel, 220
code, :CHANnel<n>:PROBe, 222
code, :CHANnel<n>:RANGe, 228
code, :DIGitize, 154
code, :DISPlay:DATA, 244
code, :DISPlay:LABel, 246
code, :MEASure:PERiod, 399
code, :MEASure:RESults, 393
code, :MEASure:TEDGe, 408
code, :MTESt, 425
code, :RUN/:STOP, 170
code, :SYSTem:SETup, 597
code, :TIMebase:DELay, 785
code, :TIMebase:MODE, 605
code, :TIMebase:RANGe, 607
code, :TIMebase:REFerence, 608
code, :TRIGger:MODE, 624
code, :TRIGger:SLOPe, 631
code, :TRIGger:SOURce, 632
code, :VIEW and :BLANk, 176
code, :WAVeform, 684
code, :WAVeform:DATA, 672
code, :WAVeform:POINts, 676
code, :WAVeform:PREamble, 680
code, :WAVeform:SEGMented, 195
code, *RST, 133
code, SICL library example in C, 931
code, SICL library example in Visual Basic, 940
code, VISA COM library example in C#, 847
code, VISA COM library example in Python, 864
code, VISA COM library example in Visual Basic, 838
code, VISA COM library example in Visual Basic .NET, 856
code, VISA library example in C, 871
code, VISA library example in C#, 890
code, VISA library example in Python, 911
code, VISA library example in Visual Basic, 880
code, VISA library example in Visual Basic .NET, 901
code, VISA.NET library example in C#, 918
code, VISA.NET library example in Visual Basic .NET, 924
colon, root commands prefixed by, 145
color palette for hardcopy, 334
color palette for image, 473
Comma Separated Values (CSV) waveform data format, 480
command classifications, 828
command differences from 1000 X-Series oscilloscopes, 32
command errors detected in Standard Event Status, 125
Command Expert, 918, 951
command header, 829
command headers, common, 831
command headers, compound, 831
command headers, simple, 831
command strings, valid, 829
commands quick reference, 55
commands sent over interface, 120
commands, more about, 827
commands, obsolete and discontinued, 741
common (*) commands, 3, 117, 119
common command headers, 831
completion criteria for an acquisition, 189, 190
compound command headers, 831
compound header, 833
computer control examples, 837
conditions for external trigger, 262
conditions, reset, 131, 586
Config softkey, 38
configurations, oscilloscope, 127, 130, 134, 597
Configure softkey, 38
connect oscilloscope, 37
connect sampled data points, 750
Connection Expert, 39
constants for making automatic measurements, 222
constants for scaling display factors, 222
constants for setting trigger levels, 222
controller initialization, 42
copy display, 169
copyright, 2
core commands, 828
count, 671
count values, 190
counter, 372
coupling, 628
COUPling demo signal, 234
coupling for channels, 216
create automask, 429
CSV (Comma Separated Values) waveform data format, 480

current oscilloscope configuration, 127, 130, 134, 597
current probe, 230, 270
CURRent segment waveform save option, 483
cursor mode, 344
cursor position, 345, 347, 349, 352, 354
cursor readout, 763, 767, 768
cursor reset conditions, 131, 586
cursor source, 346, 348
cursor time, 763, 767, 768
cursor units, X, 350, 351
cursor units, Y, 355, 356
cursors track measurements, 398
cursors, how autoscale affects, 147
cursors, X1, X2, Y1, Y2, 342
cycle measured, 378, 381
cycle time, 388

D

data, 512, 514, 672
data (waveform) maximum length, 482
data 2, 515
data acquisition types, 665
data conversion, 667
data format for transfer, 668
data output order, 670
data pattern length, 506, 531
data pattern width, 549
data pattern, CAN trigger, 505
data pattern, SPI trigger, 544
data point index, 694
data points, 192
data record, measurement, 677
data record, raw acquisition, 677
data required to fill time buckets, 189
data source, setup and hold trigger, 649
data source, SPI trigger, 540
data structures, status reporting, 797
data, saving and recalling, 238
date, calibration, 203
date, system, 578
dB versus frequency, 303
DC coupling for edge trigger, 628
DC input coupling for specified channel, 216
DC RMS measured on waveform, 417
DC waveform generator output, 704
DDE (Device Dependent Error) status bit, 123, 125
decision chart, status reporting, 815
default conditions, 131, 586
define channel labels, 220
define glitch trigger, 638
define measurement, 374
define measurement source, 399
define trigger, 639
defined as, 113
definite-length block query response, 50
definite-length block response data, 114
delay measured to calculate phase, 389
delay measurement, 374
delay measurements, 407
delay parameters for measurement, 376
delay, how autoscale affects, 147
delayed time base, 605
delayed window horizontal scale, 613
delete mask, 439
delta time, 763
delta voltage measurement, 771
delta X cursor, 342
delta Y cursor, 342
demo, 233
DEMO commands, 233
demo signal, 234
demo signal function, 234
demo signals output control, 236
destination, remote command logging, 591
detecting probe types, 749, 752
device-defined error queue clear, 121
differences from 1000 X-Series oscilloscope commands, 32
differential probe heads, 223
differential signal type, 226
digital channel source for glitch trigger, 640
digitize channels, 153
DIGitize command, 42, 47, 666
digits, 114
disable front panel, 582
disable function, 755
disabling calibration, 206
disabling channel display, 217
disabling status register bits, 122, 135
discontinued and obsolete commands, 741
display annotation, 239
display annotation background, 240
display annotation color, 241
display annotation text, 242
display channel labels, 246
display clear, 243
DISPlay commands, 237
display commands introduction, 238
display connect, 750
display date, 578
display factors scaling, 222
display for channels, 217
display frequency span, 280, 307
display measurements, 367, 398
display persistence, 249
display reference, 606, 608
display reference waveforms, 734
display reset conditions, 132, 587
display serial number, 171
display transparent, 250
display vectors, 251
display, FFT function, 274
display, lister, 339
display, measurement statistics on/off, 402
display, oscilloscope, 249, 304, 580
display, serial decode bus, 490
displaying a baseline, 626
displaying unsynchronized signal, 626
divide math function, 315
DNS IP, 38
domain, 38
driver, printer, 760
duplicate mnemonics, 833
duration for glitch trigger, 634, 635, 639
duration triggering, 616
duty cycle measurement, 43, 367, 378, 381
DVM commands, 253
DVM displayed value, 255
DVM enable/disable, 256
DVM frequency value, 257
DVM input source, 259
DVM mode, 258

E

edge coupling, 628
edge fall time, 379
edge parameter for delay measurement, 376
edge preshoot measured, 391
edge rise time, 396
edge slope, 631
edge source, 632
EDGE trigger commands, 627
edge triggering, 615
edges in measurement, 374
eject USB storage devices, 601
elapsed time in mask test, 436
ellipsis, 114
enable channel labels, 246
enabling calibration, 206
enabling channel display, 217
enabling status register bits, 122, 135
end of string (EOS) terminator, 830
end of text (EOT) terminator, 830
end or identify (EOI), 830
EOI (end or identify), 830
EOS (end of string) terminator, 830
EOT (end of text) terminator, 830
erase data, 243
erase measurements, 762
erase screen, 751
error frame count (CAN), 494
error frame count (UART), 558
error messages, 581, 787
error number, 581
error queue, 581, 808
error, measurement, 367
ESB (Event Status Bit), 136, 138
ESE (Standard Event Status Enable Register), 122, 807
ESR (Standard Event Status Register), 124, 806
event status conditions occurred, 138
Event Status Enable Register (ESE), 122, 807
Event Status Register (ESR), 124, 175, 806

example code, :ACQuire:COMPlete, 189
example code, :ACQuire:SEGMented, 195
example code, :ACQuire:TYPE, 200
example code, :AUToscale, 148
example code, :CHANnel<n>:LABel, 220
example code, :CHANnel<n>:PROBe, 222
example code, :CHANnel<n>:RANGe, 228
example code, :DIGitize, 154
example code, :DISPlay:DATA, 244
example code, :DISPlay:LABel, 246
example code, :MEASure:PERiod, 399
example code, :MEASure:RESults, 393
example code, :MEASure:TEDGe, 408
example code, :MTESt, 425
example code, :RUN/:STOP, 170
example code, :SYSTem:SETup, 597
example code, :TIMebase:DELay, 785
example code, :TIMebase:MODE, 605
example code, :TIMebase:RANGe, 607
example code, :TIMebase:REFerence, 608
example code, :TRIGger:MODE, 624
example code, :TRIGger:SLOPe, 631
example code, :TRIGger:SOURce, 632
example code, :VIEW and :BLANk, 176
example code, :WAVeform, 684
example code, :WAVeform:DATA, 672
example code, :WAVeform:POINts, 676
example code, :WAVeform:PREamble, 680
example code, :WAVeform:SEGMented, 195
example code, *RST, 133
example programs, 5, 837
examples on the website, 837
EXE (Execution Error) status bit, 123, 125
execution error detected in Standard Event Status, 125
exponential notation, 113
external glitch trigger source, 640
external range, 269
external trigger, 262, 268, 632
EXTernal trigger commands, 261
external trigger input waveform, vertical position, 267
external trigger input, display setting, 264
external trigger input, trigger level, 266
EXTernal trigger level, 629
external trigger probe attenuation factor, 268
external trigger probe sensing, 752
EXTernal trigger source, 632
external trigger units, 270
external waveform label, 265

F

failed waveforms in mask test, 434
failure, self test, 140
fall time measurement, 367, 379
falling edge count measurement, 382
falling pulse count measurement, 383
Fast Fourier Transform (FFT) functions, 273, 280, 282, 303, 305, 307, 309, 315, 321, 754
FF values in waveform data, 672
FFT (Fast Fourier Transform) functions, 273, 280, 282, 303, 305, 307, 309, 315, 321, 754
FFT (Fast Fourier Transform) operation, 684
FFT commands, 271
FFT function display, 274
FFT function, source input, 279
FFT vertical units, 281, 308
FFTPhase (Fast Fourier Transform) functions, 315
fifty ohm impedance, disable setting, 589
filename for hardcopy, 757
filename for recall, 459, 702
filename for save, 468
filter for frequency reject, 630
filter for high frequency reject, 619
filter for noise reject, 625
filter used to limit bandwidth, 215, 263
filters to Fast Fourier Transforms, 282, 309
fine horizontal adjustment (vernier), 610
fine vertical adjustment (vernier), 231
finish pending device operations, 128
first point displayed, 694
FLATtop window for amplitude measurements, 282, 309
FM burst demo signal, 234
FM modulation type, waveform generator, 719
force trigger, 618
format, 674, 679
format for block data, 127
format for hardcopy, 756
format for image, 471
format for waveform data, 480
FormattedIO488 object, 45
formfeed for hardcopy, 324, 328
formulas for data conversion, 667
frame, 541
frame counters (CAN), error, 494
frame counters (CAN), overload, 495
frame counters (CAN), reset, 496
frame counters (CAN), total, 497
frame counters (UART), error, 558
frame counters (UART), reset, 559
frame counters (UART), Rx frames, 560
frame counters (UART), Tx frames, 561
framing, 538
FRANalysis commands, 285
frequency deviation, waveform generator FM modulation, 711
frequency measurement, 43, 367, 380
frequency measurements with X cursors, 350
frequency resolution, 282, 309
frequency response analysis, data, 287
frequency response analysis, enable, 288
frequency response analysis, run, 293
frequency response analysis, single frequency, 290
frequency response analysis, sweep start frequency, 291
frequency response analysis, sweep stop frequency, 292
frequency span of display, 280, 307
frequency versus dB, 303
front panel mode, 626
front panel Single key, 172
front panel Stop key, 174
front-panel lock, 582
FSK modulation type, waveform generator, 719
FSK rate, waveform generator modulation, 714
full-scale horizontal time, 607, 612
full-scale vertical axis defined, 276, 317
function, 176, 273, 280, 282, 304, 305, 307, 309, 314, 315, 317, 318, 319, 754, 755
FUNCtion commands, 301
function memory, 173
function turned on or off, 755
function, demo signal, 234
function, waveform generator, 703
functions, 684

G

g(t) source, first input channel, 312
g(t) source, math operation, 311
g(t) source, second input channel, 313
gain data, including in FRA results, 297
gateway IP, 38
Gen Out BNC, 205
general SBUS<n> commands, 489
general trigger commands, 617
glitch demo signal, 234
glitch duration, 639
glitch qualifier, 638
glitch source, 640
GLITch trigger commands, 633
glitch trigger duration, 634
glitch trigger polarity, 637
glitch trigger source, 634
graticule area for hardcopy print, 325
graticule colors, invert for hardcopy, 329, 759
graticule colors, invert for image, 472
grayscale palette for hardcopy, 334
grayscale palette for image, 473
grayscaling on hardcopy, 758
greater than qualifier, 638
greater than time, 634, 639

H

HANNing window for frequency resolution, 282, 309

hardcopy, 169, 324
HARDcopy commands, 323
hardcopy factors, 327, 470
hardcopy filename, 757
hardcopy format, 756
hardcopy formfeed, 328
hardcopy grayscale, 758
hardcopy invert graticule colors, 329, 759
hardcopy layout, 330
hardcopy palette, 334
hardcopy print, area, 325
hardcopy printer driver, 760
HARMonics demo signal, 234
head type, probe, 223
header, 829
high resolution acquisition type, 667
high trigger level, 622
high-frequency reject filter, 619, 630
high-level voltage, waveform generator, 727
high-resolution acquisition type, 188
hold time, setup and hold trigger, 650
hold until operation complete, 128
holdoff time, 620
holes in waveform data, 672
hop frequency, waveform generator FSK modulation, 713
horizontal adjustment, fine (vernier), 610
horizontal position, 611
horizontal scale, 609, 613
horizontal scaling, 679
horizontal time, 607, 612, 763
Host ID of oscilloscope, 579
Host name softkey, 38
hostname, 38

I

id mode, 508
ID pattern, CAN trigger, 507
identification number, 126
identification of options, 129
identifier, LIN, 528
idle until operation complete, 128
IDN (Identification Number), 126
IEEE 488.2 standard, 119
IIC address, 513
IIC clock, 511
IIC data, 512, 514
IIC data 2, 515
IIC serial decode address field size, 510
IIC trigger commands, 509
IIC trigger qualifier, 516
IIC trigger type, 517
IIC triggering, 487
image format, 471
image invert graticule colors, 472
image memory, 173
image palette, 473
image, save, 469
image, save with inksaver, 472
impedance, 218
infinity representation, 835
initialization, 42, 45
initialize, 131, 586
initialize label list, 247
initiate acquisition, 153
inksaver, save image with, 472
input coupling for channels, 216
input impedance for channels, 218, 748
input inversion for specified channel, 219
insert label, 220
installed options identified, 129
instruction header, 829
instrument number, 126
instrument options identified, 129
instrument requests service, 138
instrument serial number, 171
instrument settings, 324
instrument status, 52
instrument type, 126
intensity, waveform, 245
internal low-pass filter, 214, 215, 263
introduction to :ABUS commands, 178
introduction to :ACQuire commands, 187
introduction to :CALibrate commands, 202
introduction to :CHANnel<n> commands, 213
introduction to :DEMO commands, 233
introduction to :DISPlay commands, 238
introduction to :EXTernal commands, 262
introduction to :FFT commands, 272
introduction to :FRANalysis commands, 286
introduction to :FUNCtion commands, 303
introduction to :HARDcopy commands, 324
introduction to :LISTer commands, 337
introduction to :MARKer commands, 342
introduction to :MEASure commands, 367
introduction to :RECall commands, 457
introduction to :SAVE commands, 467
introduction to :SBUS commands, 487
introduction to :SYSTem commands, 577
introduction to :TIMebase commands, 604
introduction to :TRIGger commands, 615
introduction to :WAVeform commands, 665
introduction to :WGEN commands, 701
introduction to :WMEMory<r> commands, 731
introduction to common (*) commands, 119
introduction to root (:) commands, 145
invert graticule colors for hardcopy, 329, 759
invert graticule colors for image, 472
inverted masks, bind levels, 450
inverting input for channels, 219
IO library, referencing, 44
IP address, 38

K

key disable, 582
key press detected in Standard Event Status Register, 125
Keysight Interactive IO application, 40
Keysight IO Control icon, 39
Keysight IO Libraries Suite, 6, 35, 44, 46
Keysight IO Libraries Suite, installing, 36
knob disable, 582
known state, 131, 586

L

label, 746
label command, abus, 184
label list, 220, 247
label reference waveforms, 735
labels, 220, 246, 247
labels to store calibration information, 204
labels, specifying, 238
LAN interface, 37
LAN Settings softkey, 38
landscape layout for hardcopy, 330
language for program examples, 41
layout for hardcopy, 330
leakage into peak spectrum, 282, 309
learn string, 127, 597
least significant byte first, 670
left reference, 608
legal values for channel offset, 221
legal values for frequency span, 280, 307
legal values for offset, 314, 318
length for waveform data, 481
less than qualifier, 638
less than time, 635, 639
level for trigger voltage, 629, 636
LF coupling, 628
license information, 129
limit bandwidth, 214
limits for line number, 658
LIN acknowledge, 522
LIN baud rate, 523
LIN demo signal, 235
LIN identifier, 528
LIN pattern data, 529
LIN pattern format, 532
LIN serial decode bus parity bits, 521
LIN source, 524
LIN standard, 525
LIN sync break, 526
LIN trigger, 527, 531
LIN trigger commands, 519
LIN triggering, 487
line glitch trigger source, 640
line number for TV trigger, 658
line terminator, 113
LINE trigger level, 629
LINE trigger source, 632
list of channel labels, 247

LISTer commands, 337
lister display, 339
lister time reference, 340
load utilization (CAN), 498
local lockout, 582
lock, 582
lock mask to signal, 441
lock, analog channel protection, 589
lockout message, 582
log file name, remote command logging, 590, 593
long form, 830
low frequency sine with glitch demo signal, 234
low pass filter math function, 315
low trigger level, 623
lower threshold, 388
lower threshold voltage for measurement, 761
lowercase characters in commands, 829
low-frequency reject filter, 630
low-level voltage, waveform generator, 728
low-pass filter cutoff frequency, 310
low-pass filter used to limit bandwidth, 214, 215, 263
LRN (Learn Device Setup), 127
lsbfirst, 670

M

magnitude of occurrence, 409
main sweep range, 611
main time base, 785
main time base mode, 605
making measurements, 367
MAN option for probe sense, 749, 752
manual cursor mode, 344
manufacturer string, 584, 585
MARKer commands, 341
marker mode, 352
marker position, 353
marker readout, 767, 768
marker set for voltage measurement, 772, 773
marker sets start time, 764
marker time, 763
markers for delta voltage measurement, 771
markers track measurements, 398
markers, command overview, 342
markers, mode, 344
markers, time at start, 768
markers, time at stop, 767
markers, X delta, 349
markers, X1 position, 345
markers, X1Y1 source, 346
markers, X2 position, 347
markers, X2Y2 source, 348
markers, Y delta, 354
markers, Y1 position, 352
markers, Y2 position, 353
mask, 122, 135
mask command, abus, 185
mask statistics, reset, 435
mask test commands, 423
Mask Test Event Enable Register (MTEenable), 155
mask test event event register, 157
Mask Test Event Event Register (:MTERegister[:EVENt]), 157, 813
mask test run mode, 442
mask test termination conditions, 442
mask test, all channels, 428
mask test, enable/disable, 440
mask, delete, 439
mask, get as binary block data, 438
mask, load from binary block data, 438
mask, lock to signal, 441
mask, recall, 460
mask, save, 474, 475
masks, bind levels, 450
master summary status bit, 138
math function, stop displaying, 152
math operations, 303
MAV (Message Available), 121, 136, 138
maximum duration, 635
maximum position, 606
maximum range for zoomed window, 612
maximum scale for zoomed window, 613
maximum vertical value measurement, 414
maximum vertical value, time of, 421, 765
maximum waveform data length, 482
MEASure commands, 357
measure mask test failures, 443
measure overshoot, 385
measure period, 388
measure phase between channels, 389
measure preshoot, 391
measure start voltage, 772
measure stop voltage, 773
measure value at a specified time, 418
measure value at top of waveform, 419
measurement error, 367
measurement record, 677
measurement setup, 367, 399
measurement source, 399
measurement statistics results, 393
measurement statistics, display on/off, 402
measurement window, 420
measurements, AC RMS, 417
measurements, average value, 412
measurements, base value, 413
measurements, built-in, 43
measurements, clear, 371, 762
measurements, command overview, 367
measurements, counter, 372
measurements, DC RMS, 417
measurements, definition setup, 374
measurements, delay, 376
measurements, duty cycle, 378
measurements, fall time, 379
measurements, falling edge count, 382
measurements, falling pulse count, 383
measurements, frequency, 380
measurements, how autoscale affects, 147
measurements, lower threshold level, 761
measurements, maximum vertical value, 414
measurements, maximum vertical value, time of, 421, 765
measurements, minimum vertical value, 415
measurements, minimum vertical value, time of, 422, 766
measurements, negative duty cycle, 381
measurements, overshoot, 385
measurements, period, 388
measurements, phase, 389
measurements, preshoot, 391
measurements, pulse width, negative, 384
measurements, pulse width, positive, 392
measurements, rise time, 396
measurements, rising edge count, 387
measurements, rising pulse count, 390
measurements, show, 398
measurements, snapshot all, 369
measurements, source channel, 399
measurements, standard deviation, 397
measurements, start marker time, 767
measurements, stop marker time, 768
measurements, thresholds, 764
measurements, time between start and stop markers, 763
measurements, time between trigger and edge, 407
measurements, time between trigger and vertical value, 409
measurements, time between trigger and voltage level, 769
measurements, upper threshold value, 770
measurements, vertical amplitude, 411
measurements, vertical peak-to-peak, 416
measurements, voltage difference, 771
memory setup, 134, 597
menu timeout, 248
menu, system, 583
message available bit, 138
message available bit clear, 121
message displayed, 138
message error, 787
message queue, 805
messages ready, 138
midpoint of thresholds, 388
minimum duration, 634
minimum vertical value measurement, 415
minimum vertical value, time of, 422, 766
MISO data pattern width, 546
MISO data pattern, SPI trigger, 545
MISO data source, SPI trigger, 542
MISO data, SPI, 688
mnemonics, duplicate, 833
mode, 344, 605
mode, serial decode, 491
model number, 126

models, oscilloscope, 3
modes for triggering, 624
Modify softkey, 38
modulating signal frequency, waveform generator, 710, 712
modulation (waveform generator), enabling/disabling, 718
modulation type, waveform generator, 719
MOSI data pattern width, 548
MOSI data pattern, SPI trigger, 547
MOSI data source, SPI trigger, 543
most significant byte first, 670
move cursors, 767, 768
msbfirst, 670
MSG (Message), 136, 138
MSS (Master Summary Status), 138
MTEenable (Mask Test Event Enable Register), 155
MTERegister[:EVENt] (Mask Test Event Event Register), 157, 813
MTESt commands, 423
multi-channel waveform data, save, 476
multiple commands, 833
multiple queries, 51
multiply math function, 303, 315, 684
multiply math function as g(t) source, 311

N

N8900A InfiniiView oscilloscope analysis software, 476
name channels, 220
name list, 247
negative glitch trigger polarity, 637
negative pulse width, 384
negative pulse width measurement, 43
negative slope, 536, 631
negative TV trigger polarity, 660
network printer address, 331
network printer slot, 333
network printer, apply connection settings, 332
new line (NL) terminator, 113, 830
NL (new line) terminator, 113, 830
noise reject filter, 625
noise waveform generator output, 704
noise, adding to waveform generator output, 717
noisy sine waveform demo signal, 234
non-core commands, 828
non-volatile memory, label list, 247
normal acquisition type, 187, 666
normal trigger sweep mode, 615
notices, 2
NR1 number format, 113
NR3 number format, 113
NTSC, 658, 662
NULL string, 580
number format, 113
number of points, 192, 675, 677
number of time buckets, 675, 677
numeric variables, 50
numeric variables, reading query results into multiple, 52
nwidth, 384

O

obsolete and discontinued commands, 741
obsolete commands, 828
occurrence reported by magnitude, 769
offset value for channel voltage, 221
offset value for FFT function, 275, 277
offset value for selected function, 314, 318
offset, waveform generator, 729
one values in waveform data, 672
OPC (Operation Complete) command, 128
OPC (Operation Complete) status bit, 123, 125
OPEE (Operation Status Enable Register), 159
Open method, 45
operating configuration, 127, 597
operating state, 134
operation complete, 128
operation status condition register, 161
Operation Status Condition Register (:OPERegister:CONDition), 161, 810
operation status conditions occurred, 138
Operation Status Enable Register (OPEE), 159
operation status event register, 163
Operation Status Event Register (:OPERegister[:EVENt]), 163, 809
operation, math, 303
operations for function, 315
OPERegister:CONDition (Operation Status Condition Register), 161, 810
OPERegister[:EVENt] (Operation Status Event Register), 163, 809
OPT (Option Identification), 129
optional syntax terms, 113
options, 129
order of output, 670
oscilloscope connection, opening, 45
oscilloscope connection, verifying, 39
oscilloscope external trigger, 262
oscilloscope models, 3
oscilloscope rate, 198
oscilloscope, connecting, 37
oscilloscope, initialization, 42
oscilloscope, operation, 6
oscilloscope, program structure, 42
oscilloscope, setting up, 37
oscilloscope, setup, 46
output control, demo signals, 236
output control, waveform generator, 721
output load impedance, waveform generator, 298, 722
output messages ready, 138
output polarity, waveform generator, 723
output queue, 128, 804
output queue clear, 121
output sequence, 670
overlapped commands, 836
overload, 227
Overload Event Enable Register (OVL), 165
Overload Event Register (:OVLRegister), 812
Overload Event Register (OVLR), 167
overload frame count (CAN), 495
overload protection, 165, 167
overshoot of waveform, 385
overvoltage, 227
OVL (Overload Event Enable Register), 165
OVLR (Overload Event Register), 167
OVLR bit, 161, 163
OVLRegister (Overload Event Register), 812

P

PAL, 658, 662
palette for hardcopy, 334
palette for image, 473
PAL-M, 658, 662
parameters for delay measurement, 376
parametric measurements, 367
parity, 563
parity bits, LIN serial decode bus, 521
parser, 145, 833
pass, self test, 140
path information, recall, 461
path information, save, 477
pattern, 513, 514, 515
pattern data, LIN, 529
pattern duration, 634, 635
pattern for pattern trigger, 642
pattern format, LIN, 532
pattern length, 506, 531
PATTern trigger commands, 641
pattern trigger format, 644
pattern trigger qualifier, 645
pattern triggering, 616
pattern width, 546, 548, 549
peak data, 667
peak detect, 199
peak detect acquisition type, 188, 667
peak-to-peak vertical value measurement, 416
pending operations, 128
percent of waveform overshoot, 385
percent thresholds, 374
period measured to calculate phase, 389
period measurement, 43, 367, 388
period, waveform generator, 724
persistence, waveform, 238, 249
phase data, including in FRA results, 297
phase measured between channels, 389
phase measurements, 407
phase measurements with X cursors, 350
PNG format screen image data, 244
pod, stop displaying, 152
points, 192, 675, 677

points in waveform data, 666
points per decade, frequency response analysis, 753
points, frequency response analysis, 296
polarity, 564, 660
polarity for glitch trigger, 637
polling synchronization with timeout, 820
polling wait, 818
PON (Power On) status bit, 123, 125
portrait layout for hardcopy, 330
position, 347, 606, 611
position cursors, 767, 768
position in zoomed view, 611
positive glitch trigger polarity, 637
positive pulse width, 392
positive pulse width measurement, 43
positive slope, 536, 631
positive TV trigger polarity, 660
positive width, 392
preamble data, 679
preamble metadata, 665
present working directory, recall operations, 461
present working directory, save operations, 477
preset conditions, 586
preshoot measured on waveform, 391
previously stored configuration, 130
print command, 169
print job, start, 336
print mask test failures, 444
print query, 782
printer driver for hardcopy, 760
printer, active, 326
printing, 324
printing in grayscale, 758
probe, 629
probe attenuation affects channel voltage range, 228
probe attenuation factor (external trigger), 268
probe attenuation factor for selected channel, 222
probe head type, 223
probe ID, 224
probe sense for oscilloscope, 749, 752
probe skew value, 225, 747
process sigma, mask test run, 447
program data, 830
program data syntax rules, 832
program initialization, 42
program message, 45, 120
program message syntax, 829
program message terminator, 830
program structure, 42
programming examples, 5, 837
protecting against calibration, 206
protection, 165, 167, 227
protection lock, 589
pulse waveform generator output, 704
pulse width, 384, 392
pulse width duration trigger, 634, 635, 639
pulse width measurement, 43, 367
pulse width trigger, 625
pulse width trigger level, 636
pulse width triggering, 616
pulse width, waveform generator, 706
pwidth, 392
Python, VISA COM example, 864
Python, VISA example, 911
PyVISA package, 911

Q

qualifier, 639
qualifier, transition trigger, 653
qualifier, trigger pattern, 645
queries, multiple, 51
query error detected in Standard Event Status, 125
query responses, block data, 50
query responses, reading, 49
query results, reading into numeric variables, 50
query results, reading into string variables, 50
query return values, 835
query setup, 324, 342, 367, 597
querying setup, 213
querying the subsystem, 616
queues, clearing, 814
quick reference, commands, 55
quoted ASCII string, 114
QYE (Query Error) status bit, 123, 125

R

ramp symmetry, waveform generator, 707
ramp symmetry, waveform generator modulating signal, 716
ramp waveform generator output, 704
range, 612
range for channels, 228
range for external trigger, 269
range for full-scale vertical axis, 276, 317
range for glitch trigger, 639
range for time base, 607
range of offset values, 221
range qualifier, 638
ranges, value, 114
rate, 198
ratio measurements with X cursors, 350
ratio measurements with Y cursors, 355
raw acquisition record, 677
RCL (Recall), 130
read configuration, 127
ReadIEEEBlock method, 45, 49, 51
ReadList method, 45, 49
ReadNumber method, 45, 49
readout, 763
ReadString method, 45, 49
real-time acquisition mode, 191
recall, 130, 457, 597
RECall commands, 457
recall filename, 459, 702
recall mask, 460
recall path information, 461
recall reference waveform, 463
recall setup, 462
recalling and saving data, 238
RECTangular window for transient signals, 282, 309
reference, 608
reference for time base, 785
reference point, FFT Phase, 306
reference waveform save source, 484
reference waveform, recall, 463
reference waveform, save, 485
reference waveforms, clear, 733
reference waveforms, display, 734
reference waveforms, label, 735
reference waveforms, save to, 736
reference waveforms, skew, 737
reference waveforms, Y offset, 738
reference waveforms, Y range, 739
reference waveforms, Y scale, 740
reference, lister, 340
registers, 124, 130, 134, 146, 155, 157, 159, 161, 163, 165, 167
registers, clearing, 814
reject filter, 630
reject high frequency, 619
reject noise, 625
relative standard deviation, 406
remote command logging, enable/disable, 590, 594
remote control examples, 837
remove cursor information, 344
remove labels, 246
remove message from display, 580
reorder channels, 147
repetitive acquisitions, 170
report errors, 581
report transition, 407, 409
reporting status, 795
reporting the setup, 616
request service, 138
Request-for-OPC flag clear, 121
reset, 131
reset conditions, 131
reset defauts, waveform generator, 725
reset mask statistics, 435
reset measurements, 243
resolution of printed copy, 758
resource session object, 45
ResourceManager object, 45
restore configurations, 127, 130, 134, 597
restore labels, 246
restore setup, 130
return values, query, 835
returning acquisition type, 199
returning number of data points, 192

RF burst demo signal, 234
right reference, 608
ringing pulse demo signal, 234
rise time measurement, 367
rise time of positive edge, 396
rising edge count measurement, 387
rising pulse count measurement, 390
RMS value measurement, 417
roll time base mode, 605
root (:) commands, 143, 145
root level commands, 3
root path for USB storage devices, 602
RQL (Request Control) status bit, 123, 125
RQS (Request Service), 138
RS-232/UART triggering, 488
RST (Reset), 131
rules, tree traversal, 833
rules, truncation, 830
run, 139, 170
Run bit, 161, 163
run mode, mask test, 442
running configuration, 134, 597
Rx frame count (UART), 560
Rx source, 565

S

sample rate, 3, 198
sampled data, 750
sampled data points, 672
SAV (Save), 134
save, 134, 467
SAVE commands, 465
save filename, 468
save image, 469
save image with inksaver, 472
save mask, 474, 475
save mask test failures, 445
save path information, 477
save reference waveform, 485
save setup, 478
save to reference waveform location, 736
save waveform data, 479
saved image, area, 784
saving and recalling data, 238
SBUS CAN commands, 492
SBUS commands, 487
SBUS<n> commands, general, 489
scale, 278, 319, 609, 613
scale factors output on hardcopy, 327, 470
scale for channels, 229
scale units for channels, 230
scale units for external trigger, 270
scaling display factors, 222
SCPI commands, 53
SCPI.NET examples, 951
scratch measurements, 762
screen area for hardcopy print, 325
screen area for saved image, 784
screen display of logged remote commands, enable/disable, 592
screen image data, 244
SECAM, 658, 662
seconds per division, 609
segmented waveform save option, 483
segments, analyze, 193
segments, count of waveform, 682
segments, setting number of memory, 194
segments, setting the index, 195
segments, time tag, 683
select measurement channel, 399
self-test, 140
sensing a channel probe, 749
sensing a external trigger probe, 752
sensitivity of oscilloscope input, 222
sequential commands, 836
serial clock, 511, 539
serial data, 512
serial decode bus, 487
serial decode bus display, 490
serial decode mode, 491
serial frame, 541
serial number, 171
service request, 138
Service Request Enable Register (SRE), 136, 802
set center frequency, 273, 305
set cursors, 767, 768
set date, 578
set time, 599
set up oscilloscope, 37
setting display, 304
setting external trigger level, 262
setting impedance for channels, 218
setting inversion for channels, 219
settings, 130, 134
settings, instrument, 324
setup, 188, 213, 238, 324, 597
setup and hold trigger clock source, 648
setup and hold trigger data source, 649
setup and hold trigger hold time, 650
setup and hold trigger setup time, 651
setup and hold trigger slope, 647
setup configuration, 130, 134, 597
setup defaults, 131, 586
setup memory, 130
setup reported, 616
setup time, setup and hold trigger, 651
setup, recall, 462
setup, save, 478
shape of modulation signal, waveform generator, 715
SHOLd trigger commands, 646
short form, 5, 830
show channel labels, 246
show measurements, 367, 398
SICL example in C, 931
SICL example in Visual Basic, 940
SICL examples, 931
sigma, mask test run, 447
signal type, 226
signed data, 668
simple command headers, 831
sine waveform demo signal, 234
sine waveform generator output, 703
single acquisition, 172
single frequency, frequency response analysis, 289
single-ended probe heads, 223
single-ended signal type, 226
single-shot demo signal, 234
single-shot DUT, synchronizing with, 822
skew, 225, 747
skew reference waveform, 737
slope, 536, 631
slope (direction) of waveform, 769
slope not valid in TV trigger mode, 631
slope parameter for delay measurement, 376
slope, setup and hold trigger, 647
slope, transition trigger, 654
slot, network printer, 333
smoothing acquisition type, 667
snapshot all measurement, 369
softkey menu timeout, 248
software version, 126
source, 399, 502, 524
source for function, 320, 321, 754
source for trigger, 632
source for TV trigger, 661
source input for FFT function, 279
source, automask, 430
source, mask test, 455
source, save reference waveform, 484
source, transition trigger, 655
source, waveform, 684
span, 303, 315
span of frequency on display, 280, 307
specify measurement, 399
SPI, 536
SPI clock timeout, 537
SPI decode bit order, 535
SPI decode word width, 551
SPI MISO data, 688
SPI trigger, 538, 546, 548, 549
SPI trigger clock, 539
SPI trigger commands, 533
SPI trigger data pattern, 544
SPI trigger frame, 541
SPI trigger MISO data pattern, 545
SPI trigger MOSI data pattern, 547
SPI trigger type, 550
SPI trigger, data source, 540
SPI trigger, MISO data source, 542
SPI trigger, MOSI data source, 543
SPI triggering, 488
square wave duty cycle, waveform generator, 708
square waveform generator output, 703
SRE (Service Request Enable Register), 136, 802
SRQ (Service Request interrupt), 155, 159
standard deviation measured on waveform, 397

Standard Event Status Enable Register (ESE), 122, 807
Standard Event Status Register (ESR), 124, 806
standard for video, 662
standard, LIN, 525
start acquisition, 139, 153, 170, 172
start and stop edges, 374
start cursor, 767
start measurement, 367
start print job, 336
start time, 639, 767
start time marker, 764
state memory, 134
state of instrument, 127, 597
statistics increment, 403
statistics reset, 405
statistics results, 393
statistics, max count, 404
statistics, relative standard deviation, 406
statistics, type of, 401
status, 137, 173, 175
Status Byte Register (STB), 135, 137, 138, 800
status data structure clear, 121
status registers, 52
status reporting, 795
STB (Status Byte Register), 135, 137, 138, 800
step size for frequency span, 280, 307
stop, 153, 174
stop acquisition, 174
stop cursor, 768
stop displaying channel, 152
stop displaying math function, 152
stop displaying pod, 152
stop on mask test failure, 446
stop time, 639, 768
storage, 134
store instrument setup, 127, 134
store setup, 134
storing calibration information, 204
string variables, 50
string variables, reading multiple query results into, 51
string variables, reading query results into multiple, 51
string, quoted ASCII, 114
subnet mask, 38
subsource, waveform source, 688
subsystem commands, 3, 833
subtract math function, 303, 315, 684
subtract math function as g(t) source, 311
sweep mode, trigger, 615, 626
sweep speed set to fast to measure fall time, 379
sweep speed set to fast to measure rise time, 396
switch disable, 582
sync break, LIN, 526
syntax elements, 113
syntax rules, program data, 832
syntax, optional terms, 113
syntax, program message, 829
SYSTem commands, 575
system commands, 578, 580, 581, 582, 597, 599
system commands introduction, 577

T

tdelta, 763
tedge, 407
telnet ports 5024 and 5025, 672
Telnet sockets, 53
temporary message, 580
TER (Trigger Event Register), 175, 803
termination conditions, mask test, 442
test sigma, mask test run, 447
test, self, 140
text, writing to display, 580
threshold voltage (lower) for measurement, 761
threshold voltage (upper) for measurement, 770
thresholds, 374, 764
thresholds used to measure period, 388
thresholds, how autoscale affects, 147
time base, 605, 606, 607, 608, 609, 785
time base commands introduction, 604
time base reset conditions, 132, 587
time base window, 611, 612, 613
time between points, 763
time buckets, 189, 190
time delay, 785
time delta, 763
time difference between data points, 692
time duration, 639
time holdoff for trigger, 620
time interval, 407, 409, 763
time interval between trigger and occurrence, 769
time marker sets start time, 764
time measurements with X cursors, 350
time per division, 607
time record, 282, 309
time reference, lister, 340
time specified, 418
time, calibration, 210
time, mask test run, 448
time, start marker, 767
time, stop marker, 768
time, system, 599
time, transition trigger, 656
time/div, how autoscale affects, 147
time-at-max measurement, 765
time-at-min measurement, 766
TIMebase commands, 603
timebase vernier, 610
TIMebase:MODE, 48
time-ordered label list, 247
timeout, SPI clock, 537
timezone, 600
timing measurement, 367
title channels, 220
title, mask test, 456
tolerance, automask, 432, 433
top of waveform value measured, 419
total frame count (CAN), 497
total waveforms in mask test, 437
trace memory, 173
track measurements, 398
transfer instrument state, 127, 597
transition trigger qualifier, 653
transition trigger slope, 654
transition trigger source, 655
transition trigger time, 656
transparent screen background, remote command logging, 595
transparent, display, 250
tree traversal rules, 833
TRG (Trigger), 136, 138, 139
trigger armed event register, 161, 163
trigger burst, UART, 568
trigger channel source, 640, 661
TRIGger commands, 615
TRIGger commands, general, 617
trigger data, UART, 569
TRIGger EDGE commands, 627
trigger edge coupling, 628
trigger edge slope, 631
trigger event bit, 175
Trigger Event Register (TER), 803
TRIGger GLITch commands, 633
trigger holdoff, 620
trigger idle, UART, 570
TRIGger IIC commands, 509
trigger level auto set up, 621
trigger level constants, 222
trigger level voltage, 629
trigger level, high, 622
trigger level, low, 623
TRIGger LIN commands, 519
trigger occurred, 138
TRIGger PATTern commands, 641
trigger pattern qualifier, 645
trigger qualifier, UART, 571
trigger reset conditions, 132, 587
TRIGger SHOLd commands, 646
trigger SPI clock slope, 536
TRIGger SPI commands, 533
trigger status bit, 175
trigger sweep mode, 615
TRIGger TV commands, 652, 657
trigger type, SPI, 550
trigger type, UART, 572
TRIGger UART commands, 552
trigger, CAN, 503
trigger, CAN pattern data length, 506
trigger, CAN pattern ID mode, 508
trigger, CAN sample point, 499
trigger, CAN signal baudrate, 500
trigger, CAN signal definition, 501
trigger, CAN source, 502
trigger, edge coupling, 628

trigger, edge level, 629
trigger, edge reject, 630
trigger, edge slope, 631
trigger, edge source, 632
trigger, force a, 618
trigger, glitch greater than, 634
trigger, glitch less than, 635
trigger, glitch level, 636
trigger, glitch polarity, 637
trigger, glitch qualifier, 638
trigger, glitch range, 639
trigger, glitch source, 640
trigger, high frequency reject filter, 619
trigger, holdoff, 620
trigger, IIC clock source, 511
trigger, IIC data source, 512
trigger, IIC pattern address, 513
trigger, IIC pattern data, 514
trigger, IIC pattern data 2, 515
trigger, IIC qualifier, 516
trigger, IIC signal baudrate, 523
trigger, IIC type, 517
trigger, LIN, 527
trigger, LIN pattern data, 529
trigger, LIN pattern data length, 531
trigger, LIN pattern format, 532
trigger, LIN sample point, 522
trigger, LIN source, 524
trigger, mode, 624
trigger, noise reject filter, 625
trigger, SPI clock slope, 536
trigger, SPI clock source, 539
trigger, SPI clock timeout, 537
trigger, SPI frame source, 541
trigger, SPI framing, 538
trigger, SPI pattern MISO width, 546
trigger, SPI pattern MOSI width, 548
trigger, SPI pattern width, 549
trigger, sweep, 626
trigger, TV line, 658
trigger, TV mode, 659, 786
trigger, TV polarity, 660
trigger, TV source, 661
trigger, TV standard, 662
trigger, UART base, 567
trigger, UART baudrate, 556
trigger, UART bit order, 557
trigger, UART parity, 563
trigger, UART polarity, 564
trigger, UART Rx source, 565
trigger, UART Tx source, 566
trigger, UART width, 573
truncation rules, 830
TST (Self Test), 140
tstart, 767
tstop, 768
turn function on or off, 755
turn off channel, 152
turn off channel labels, 246
turn off math function, 152
turn on channel labels, 246
turning channel display on and off, 217
turning off/on function calculation, 304
turning vectors on or off, 750
TV mode, 659, 786
TV trigger commands, 652, 657
TV trigger line number setting, 658
TV trigger mode, 661
TV trigger polarity, 660
TV trigger standard setting, 662
TV triggering, 616
tvmode, 786
Tx data, UART, 688
Tx frame count (UART), 561
Tx source, 566
type, 689

U

UART base, 567
UART baud rate, 556
UART bit order, 557
UART frame counters, reset, 559
UART parity, 563
UART polarity, 564
UART Rx source, 565
UART trigger burst, 568
UART trigger commands, 552
UART trigger data, 569
UART trigger idle, 570
UART trigger qualifier, 571
UART trigger type, 572
UART Tx data, 688
UART Tx source, 566
UART width, 573
UART/RS-232 triggering, 488
units (vertical) for FFT, 281, 308
units per division, 229, 230, 270, 609
units per division (vertical) for FFT function, 278
units per division (vertical) for function, 229, 319
units, automask, 431
units, X cursor, 350, 351
units, Y cursor, 355, 356
unsigned data, 668
unsigned mode, 690
upper threshold, 388
upper threshold voltage for measurement, 770
uppercase characters in commands, 829
URQ (User Request) status bit, 123, 125
USB (Device) interface, 37
user defined channel labels, 220
user event conditions occurred, 138
User's Guide, 6
USR (User Event bit), 136, 138
utilization, CAN bus, 498

V

valid command strings, 829
value, 409
value measured at base of waveform, 413
value measured at specified time, 418
value measured at top of waveform, 419
value ranges, 114
values required to fill time buckets, 190
VBA, 44, 838
vectors turned on or off, 750
vectors, display, 251
vectors, turning on or off, 238
vernier, channel, 231
vernier, horizontal, 610
vertical adjustment, fine (vernier), 231
vertical amplitude measurement, 411
vertical axis defined by RANGe, 276, 317
vertical axis range for channels, 228
vertical offset for channels, 221
vertical peak-to-peak measured on waveform, 416
vertical scale, 229, 278, 319
vertical scaling, 679
vertical units for FFT, 281, 308
vertical value at center screen, 275, 277, 314, 318
vertical value maximum measured on waveform, 414
vertical value measurements to calculate overshoot, 385
vertical value minimum measured on waveform, 415
video line to trigger on, 658
video standard selection, 662
view, 176, 303, 691
view turns function on or off, 755
VISA COM example in C#, 847
VISA COM example in Python, 864
VISA COM example in Visual Basic, 838
VISA COM example in Visual Basic .NET, 856
VISA example in C, 871
VISA example in C#, 890
VISA example in Python, 911
VISA example in Visual Basic, 880
VISA example in Visual Basic .NET, 901
VISA examples, 838, 871
VISA.NET example in C#, 918
VISA.NET example in Visual Basic .NET, 924
VISA.NET examples, 918
Visual Basic .NET, VISA COM example, 856
Visual Basic .NET, VISA example, 901
Visual Basic .NET, VISA.NET example, 924
Visual Basic 6.0, 45
Visual Basic for Applications, 44, 838
Visual Basic, SICL library example, 940
Visual Basic, VISA COM example, 838
Visual Basic, VISA example, 880
voltage crossing reported or not found, 769
voltage difference between data points, 695
voltage difference measured, 771

voltage in, frequency response analysis, 294, 295
voltage level for active trigger, 629
voltage marker used to measure waveform, 772, 773
voltage offset value for channels, 221
voltage probe, 230, 270
voltage ranges for channels, 228
voltage ranges for external trigger, 269
voltage threshold, 374

W

WAI (Wait To Continue), 141
wait, 141
wait for operation complete, 128
Wait Trig bit, 161, 163
warranty, 2
waveform base value measured, 413
WAVeform command, 43
WAVeform commands, 663
waveform data, 665
waveform data format, 480
waveform data length, 481
waveform data length, maximum, 482
waveform data, save, 479
waveform generator, 701
waveform generator amplitude, 299, 726
waveform generator function, 703
waveform generator high-level voltage, 727
waveform generator low-level voltage, 728
waveform generator offset, 729
waveform generator output control, 721
waveform generator output load impedance, 298, 722
waveform generator output polarity, 723
waveform generator period, 724
waveform generator pulse width, 706
waveform generator ramp symmetry, 707
waveform generator reset defaults, 725
waveform generator square wave duty cycle, 708
waveform introduction, 665
waveform maximum vertical value measured, 414
waveform minimum vertical value measured, 415
waveform must cross voltage level to be an occurrence, 769
WAVeform parameters, 48
waveform peak-to-peak vertical value measured, 416
waveform period, 388
waveform persistence, 238
waveform RMS value measured, 417
waveform save option for segments, 483
waveform source, 684
waveform source subsource, 688
waveform standard deviation value measured, 397
waveform vertical amplitude, 411
waveform voltage measured at marker, 772, 773
waveform, byte order, 670
waveform, count, 671
waveform, data, 672
waveform, format, 674
waveform, points, 675, 677
waveform, preamble, 679
waveform, type, 689
waveform, unsigned, 690
waveform, view, 691
waveform, X increment, 692
waveform, X origin, 693
waveform, X reference, 694
waveform, Y increment, 695
waveform, Y origin, 696
waveform, Y reference, 697
WAVeform:FORMat, 48
waveforms, mask test run, 449
Web control, 53
website, examples on, 837
WGEN commands, 699
WGEN trigger source, 632
what's new, 25
width, 573, 639
window, 611, 612, 613
window time, 607
window time base mode, 605
window, measurement, 420
windows, 282, 309
windows as filters to Fast Fourier Transforms, 282, 309
windows for Fast Fourier Transform functions, 282, 309
WMEMory commands, 731
word format, 674
word format for data transfer, 668
word width, SPI decode, 551
write mode, remote command logging, 590, 596
write text to display, 580
WriteIEEEBlock method, 45, 51
WriteList method, 45
WriteNumber method, 45
WriteString method, 45

X

X axis markers, 342
X cursor units, 350, 351
X delta, 349
X delta, mask scaling, 452
X1 and X2 cursor value difference, 349
X1 cursor, 342, 345, 346
X1, mask scaling, 451
X2 cursor, 342, 347, 348
X-axis functions, 604
X-increment, 692
X-of-max measurement, 421
X-of-min measurement, 422
X-origin, 693
X-reference, 694
X-Y mode, 604, 605

Y

Y axis markers, 342
Y cursor units, 355, 356
Y offset, reference waveform, 738
Y range, reference waveform, 739
Y scale, reference waveform, 740
Y1 and Y2 cursor value difference, 354
Y1 cursor, 342, 346, 352, 354
Y1, mask scaling, 453
Y2 cursor, 342, 348, 353, 354
Y2, mask scaling, 454
Y-axis value, 696
Y-increment, 695
Y-origin, 696, 697
Y-reference, 697

Z

zero values in waveform data, 672
zoomed time base, 605
zoomed time base measurement window, 420
zoomed time base mode, how autoscale affects, 147
zoomed window horizontal scale, 613