


In-Circuit Test Fixture Accessories

Introduction

Enhance the functionality and productivity of your i3070 in-circuit test system with the right accessories, such as fixture kits, personality pins, and vectorless test items. Obtain a quick quote by visiting www.keysight.com/us/en/product/3070AF/ICT-i3070-accessories-fixture.html today.



Accessories

Part Number	Description	Quantity per Pack	Image
44200P-FG	Tapered tooling pins for use in 442xx test fixtures	20	
44275P-FG	Personality Pins	5000	
44275R-FG	Personality Pins, Offset, used with 44275P	25	
E3701A-FG	Left bumpout for SimPlate Express Fixture (short wire)	1	
N4333B-001	nanoVTEP Signal Conditioner Card The product color may be blue/red. This does not impact the functionality	1	
N4333B-002	nanoVTEP Signal Conditioner Card The product color may be blue/red. This does not impact the functionality	10	
N4333B-102	nanoVTEP/ConnectCheck Signal Conditioner Card	10	
E3980A-FG	SimPlate Fixture Alignment Plates, Standard	10	
E3981A-FG	SimPlate Fixture Alignment Plates, Large	10	

Vectorless Test

Only the same generation of components can be used together for the following components of nanoVTEP (receptacle, barrel, and spring clip).

Gen 1

N4333A-201/N4333A-202, nanoVTEP, full assembly with a receptacle, pack of 100/250 [Obsoleted]



N4333A-211, nanoVTEP, pre-assembled barrel, amplifier and spring clip, pack of 50 [Obsoleted]



N4333A-601, nanoVTEP barrel with spring clip, pack of 50 [Obsoleted]



N4333A-701, nanoVTEP spring clip, pack of 50 [Obsoleted]



Gen 2

N4333C-201/N4333C-202, nanoVTEP, Gen 2 full assembly with a receptacle, pack of 100/250



N4333C-A01, nanoVTEP, Gen 2 receptacle, pack of 50



N4333C-211, nanoVTEP Gen 2, pre-assembled barrel, amplifier, and spring clip, pack of 50




N4333C-601, nanoVTEP Gen 2 barrel with spring clip, pack of 50



N4333C-701, nanoVTEP Gen 2 spring clip, pack of 50



For the following components of nanoVTEP (amplifier and sensor plate), the parts are the same between generations

Part Number	Description	Quantity per Pack	Image
N4333A-801	Spring probes	100	
N4333A-301	nanoVTEP amplifier	50	
N4333A-401	nanoVTEP Sensor Plate, Single Probe, 0.16 inches/4mm	50	
N4333A-402	nanoVTEP Sensor Plate, Single Probe, 0.16 inches/4mm	200	
N4333A-403	nanoVTEP sensor plate, single probe, 4mmx6.65mm, Tant. C/D	20	
N4333A-404	nanoVTEP sensor plate, single probe, 4mmx6.65mm, Tant. C/D	100	
N4333A-405	nanoVTEP Sensor Plate, Single Probe, 0.4 inches/10mm	50	
N4333A-406	nanoVTEP Sensor Plate, Single Probe, 0.4 inches/10mm	200	
N4333A-501	nanoVTEP Sensor Plate, 1.2 inches/30.5mm	20	
N4333A-502	nanoVTEP Sensor Plate, 1.2 inches/30.5mm	100	

Part Number	Description	Quantity per Pack	Image
N4333A-503	nanoVTEP Sensor Plate, 2.5 inches/63.3mm	10	
N4333A-504	nanoVTEP Sensor Plate, 2.5 inches/63.3mm	50	
N4333A-505	nanoVTEP sensor plate, 12.5mm X 152mm	10	

For More Information

To learn more about i3070 fixture accessories, go to

www.keysight.com/us/en/product/3070AF/ICT-i3070-accessories-fixture.html

For more information on Keysight Technologies' products, applications, or services, please visit: www.keysight.com



This information is subject to change without notice. © Keysight Technologies, 2011 - 2026, Published in USA, June 19, 2026, 5991-3177EN