

Keysight RF and Microwave Test Accessories, 40/50/54/67 GHz

Choose high quality for every connection

Keysight's RF and microwave test accessories eliminate the weak links in your measurement systems



Beyond your expectation

These test accessories will accommodate the required level of accuracy and performance in high frequency testing up to 67 GHz. They are ideal for radar and satellite testing, wireless communications, microwave backhaul and other high frequency applications where performance and reliability are the priority.

Key features

- Superior performance and repeatable results up to 67 GHz
- Unmatched quality and reliability minimizing measurement uncertainty
- Superior performance optimizing your test equipment capability

| Product family | Model number | Description |
|----------------------|----------------------|---|
| Switches | U1816E/F (NEW) | Dual-SP6T USB switch matrices, DC to 50/67 GHz |
| | U7104/6E/N/F (NEW) | SP4/6T switches, DC to 50/54/67 GHz |
| | N1810/1/2 Option 040 | SPDT and bypass switches, DC to 40 GHz |
| | N1810/1/2 Option 050 | SPDT and bypass switches, DC to 50 GHz |
| | N1810/1/2 Option 067 | SPDT and bypass switches, DC to 67 GHz |
| | 87104D/6D | Multiport Electromechanical Coaxial Switch, DC to 40 GHz, SP4T/SP6T |
| | 87222D | Coaxial Transfer Switch, DC to 40 GHz |
| | 8765D | Coaxial SPDT Switch, DC to 40 GHz |
| | 87222E | Coaxial Transfer Switch, DC to 50 GHz |
| | 8767/8/9M | Multiport Coaxial Switch, DC to 50 GHz, SP4T/SP5T/SP6T |
| | 85331B | Solid State Switch, 45 to 50 GHz, SPDT |
| | 85332B | Solid State Switch, 45 to 50 GHz, SP4T |
| Attenuators | 84904L | Programmable Step Attenuator, DC to 40 GHz, 0 to 11 dB, 1 dB Steps |
| | 84906L | Programmable Step Attenuator, DC to 40 GHz, 0 to 90 dB, 10 dB Steps |
| | 84907L | Programmable Step Attenuator, DC to 40 GHz, 0 to 70 dB, 10 dB Steps |
| | 84904M | Programmable Step Attenuator, DC to 50 GHz, 0 to 11 dB, 1 dB Steps |
| | 84905M | Programmable Step Attenuator, DC to 50 GHz, 0 to 60 dB, 10 dB Steps |
| | 84908M | Programmable Step Attenuator, DC to 50 GHz, 0 to 65 dB, 5 dB Steps |
| | 8490D | Coaxial Fixed Attenuator, DC to 50 GHz |
| | 8490G | Coaxial Fixed Attenuator, DC to 67 GHz |
| Amplifiers | 83050A | Microwave System Amplifier, 2 to 50 GHz |
| | 83051A | Microwave System Amplifier, 45 MHz to 50 GHz |
| DC blocks | N9398F | DC Block, 50 kHz to 50 GHz |
| | N9399F | DC Block, 700 kHz to 50 GHz |
| | N9398G | DC Block, 700 kHz to 67 GHz |
| Directional couplers | 87301D | Coaxial Directional Coupler, 1 to 40 GHz |
| | 87301B | Coaxial Directional Coupler, 10 to 46 GHz |
| | 87301C | Coaxial Directional Coupler, 10 to 50 GHz |
| | 87301E | Coaxial Directional Coupler, 2 to 50 GHz |
| Detectors | 8474E | Planar-Doped Barrier Diode Detector, 0.01 to 50 GHz |
| Power Dividers | 11636C/D (NEW) | Power Divider, DC to 50/67 GHz |
| Power Limiters | N9355F/G (NEW) | Power Limiter, 0.01 to 50/67 GHz |
| Power Splitters | 11667C/D (NEW) | Power Splitter, DC to 50/67 GHz |
| Adapters | N5520A/B/C | 1.85 mm Adapters, DC to 67 GHz |
| | 11900A/B/C | 2.4 mm to 2.4 mm Adapter, DC to 50 GHz |
| | 11904A/B/C/D | 2.4 mm to 2.92 mm Adapter, DC to 40 GHz |
| Terminations | 85138A/B | Coaxial Terminations, DC to 50 GHz |

More RF & Microwave Test Accessories

For selection of more than 300 models of various type of RF and microwave test accessories with operating frequency up to 110 GHz. Go to: www.keysight.com/find/mta

Learn more at: www.keysight.com

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

