
U8903B

Performance Audio Analyzer

Notices

Copyright Notice

© Keysight Technologies 2014–2021, 2024

No part of this manual may be reproduced in any form or by any means (including electronic storage and retrieval or translation into a foreign language) without prior agreement and written consent from Keysight Technologies as governed by United States and international copyright laws.

Trademark

Bluetooth and the *Bluetooth* logos are trademarks owned by *Bluetooth SIG, Inc.*, U.S.A. and licensed to Keysight Technologies.

Manual Part Number

U8903-90055

Edition

Edition 5, January 2024

Printed in:

Printed in Malaysia

Published by:

Keysight Technologies
Bayan Lepas Free Industrial Zone,
11900 Penang, Malaysia

Technology Licenses

The hardware and/or software described in this document are furnished under a license and may be used or copied only in accordance with the terms of such license.

Declaration of Conformity

Declarations of Conformity for this product and for other Keysight products may be downloaded from the Web. Go to <http://www.keysight.com/go/conformity>. You can then search by product number to find the latest Declaration of Conformity.

U.S. Government Rights

The Software is “commercial computer software,” as defined by Federal Acquisition Regulation (“FAR”) 2.101. Pursuant to FAR 12.212 and 27.405-3 and Department of Defense FAR Supplement (“DFARS”) 227.7202, the U.S. government acquires commercial computer software under the same terms by which the software is customarily provided to the public. Accordingly, Keysight provides the Software to U.S. government customers under its standard commercial license, which is embodied in its End User License Agreement (EULA), a copy of which can be found at <http://www.keysight.com/find/sweula>. The license set forth in the EULA represents the exclusive authority by which the U.S. government may use, modify, distribute, or disclose the Software. The EULA and the license set forth therein, does not require or permit, among other things, that Keysight: (1) Furnish technical information related to commercial computer software or commercial computer software documentation that is not customarily provided to the public; or (2) Relinquish to, or otherwise provide, the government rights in excess of these rights customarily provided to the public to use, modify, reproduce, release, perform, display, or disclose commercial computer software or commercial computer software documentation. No additional government requirements beyond those set forth in the EULA shall apply, except to the extent that those terms, rights, or licenses are explicitly required from all providers of commercial computer software pursuant to the FAR and the DFARS and are set forth specifically in writing elsewhere in the EULA. Keysight shall be under no obligation to update, revise or otherwise modify the Software. With respect to any technical data as defined by FAR 2.101, pursuant to FAR 12.211 and 27.404.2 and DFARS 227.7102, the U.S. government acquires no greater than Limited Rights as defined in FAR 27.401 or DFAR 227.7103-5 (c), as applicable in any technical data.

Warranty

THE MATERIAL CONTAINED IN THIS DOCUMENT IS PROVIDED “AS IS,” AND IS SUBJECT TO BEING CHANGED, WITHOUT NOTICE, IN FUTURE EDITIONS. FURTHER, TO THE MAXIMUM EXTENT PERMITTED BY APPLICABLE LAW, KEYSIGHT DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED, WITH REGARD TO THIS MANUAL AND ANY INFORMATION CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. KEYSIGHT SHALL NOT BE LIABLE FOR ERRORS OR FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES IN CONNECTION WITH THE FURNISHING, USE, OR PERFORMANCE OF THIS DOCUMENT OR OF ANY INFORMATION CONTAINED HEREIN. SHOULD KEYSIGHT AND THE USER HAVE A SEPARATE WRITTEN AGREEMENT WITH WARRANTY TERMS COVERING THE MATERIAL IN THIS DOCUMENT THAT CONFLICT WITH THESE TERMS, THE WARRANTY TERMS IN THE SEPARATE AGREEMENT SHALL CONTROL.

Safety Information

CAUTION

A CAUTION notice denotes a hazard. It calls attention to an operating procedure, practice, or the like that, if not correctly performed or adhered to, could result in damage to the product or loss of important data. Do not proceed beyond a CAUTION notice until the indicated conditions are fully understood and met.

WARNING

A WARNING notice denotes a hazard. It calls attention to an operating procedure, practice, or the like that, if not correctly performed or adhered to, could result in personal injury or death. Do not proceed beyond a WARNING notice until the indicated conditions are fully understood and met.

Configuring the U8903B Performance Audio Analyzer

This step-by-step process will help you configure your performance audio analyzer. Tailor the performance to meet your requirements.

For detailed specifications, refer to the U8903B Performance Audio Analyzer data sheet (<http://literature.cdn.keysight.com/litweb/pdf/5991-4551EN.pdf>).

The standard U8903B Performance Audio Analyzer includes:

- U8903B-STD performance audio analyzer with 2 analog generator channel and 2 analog analyzer channel.
- Certificate of Calibration
- Safety Notices
- Supplied accessories:
 - USB cables
 - Power cord (plug matches destination requirements)

Step 1: Select measurement channel options

Keysight provides you the flexibility to select the measurement option combinations to meet your needs.

Table 1-1 Measurement channel options

Option number	Description	Additional information
U8903B-STD	Performance audio analyzer, 2 channels	2 channels analog generator and 2 channels analog analyzer (at product front panel).
U8903B-AN4	Analog analyzer, 4 channels	2 channels analog generator and 4 channels analog analyzer (with 2 channels at the product rear panel).
U8903B-AN8	Analog analyzer, 8 channels	2 channels analog generator and 8 channels analog analyzer (with 6 channels at the product rear panel).
U8903B-DGT	Digital audio card	This option provides the industry standard AES3/ SPDIF, DSI, and TOSLINK (optical) connections. Once this hardware option is selected, the N3434A digital audio software option will be selected. Refer to "Step 2: Select software options" on page 7 for more information.
U8903B-BLU	<i>Bluetooth</i> [®] card	2 RF connectors.
U8903B-BL2	<i>Bluetooth</i> card, secondary option slot	2 RF connectors at a secondary option slot. This is only applicable when U8903B-AN8 is selected. Refer to "" on page 5 for more information.

NOTE

- By default, U8903B-STD will be selected when extra channels, digital audio card, or *Bluetooth* card option is added.
- U8903B provides flexibility in configuring the measurement option in order to tailor to customer application needs. U8903B only allow upgrade for U8903B-BLU and U8903-DGT post ordering. All other order combination has to be configured upon ordering.

Table 1-2 Order combinations

Order combinations	Description
U8903B-STD	<ul style="list-style-type: none"> - 2 analog analyzer channels (front panel) - 2 analog generator channels (front panel)
U8903B-AN4	<ul style="list-style-type: none"> - 2 analog analyzer channels (rear panel)
U8903B-AN8	<ul style="list-style-type: none"> - 6 analog analyzer channels (rear panel)
U8903B-AN4 + U8903B-DGT	<ul style="list-style-type: none"> - 2 analog analyzer channels (rear panel) - Digital audio card
U8903B-AN8 + U8903B-DGT	<ul style="list-style-type: none"> - 6 analog analyzer channels (rear panel) - Digital audio card
U8903B-DGT	<ul style="list-style-type: none"> - Digital audio card
U8903B-BLU	<ul style="list-style-type: none"> - <i>Bluetooth</i> card
U8903B-DGT + U8903B-BLU	<ul style="list-style-type: none"> - Digital audio card - <i>Bluetooth</i> card
U8903B-AN4 + U8903B-BLU	<ul style="list-style-type: none"> - 2 analog analyzer channels (rear panel) - <i>Bluetooth</i> card
U8903B-AN4 + U8903B-DGT + U8903B-BLU	<ul style="list-style-type: none"> - 2 analog analyzer channels (rear panel) - Digital audio card - <i>Bluetooth</i> card
U8903B-AN8 + U8903B-BL2	<ul style="list-style-type: none"> - 6 analog analyzer channels (rear panel) - <i>Bluetooth</i> card

Table 1-3 Bundling options

Option number	Description	Additional information
U8903B-201	Performance audio analyzer with 4 analog analyzer channels and digital audio card (AES3/SPDIF and DSI digital audio).	This bundling option consists of 4 analog analyzer channels (with 2 channels at the product rear panel) and digital audio card (with digital audio software included as standard).

Table 1-3 Bundling options

Option number	Description	Additional information
U8903B-210	Performance audio analyzer with 4 analog analyzer channels, digital audio card (AES3/SPDIF and DSI digital audio), and <i>Bluetooth</i> .	This bundling option consists of 4 analog analyzer channels (with 2 channels at the product rear panel), digital audio card (with digital audio software included as standard), and <i>Bluetooth</i> card.
U8903B-212	Performance audio analyzer; 96 khz bandwidth, 2 channels with 50 ohm impedance.	-

Step 2: Select software options

Table 1-4 Software options

Option number		Description	Additional information
Fixed license	Upgrade license		
N3431A	N3431A	Wide bandwidth option – 1.5 MHz (fixed perpetual license)	This software option offers 2 analog analyzer channels (at the product front panel); channel 1 and channel 2, each with 1.5 MHz bandwidth. Additional analog analyzer channels (at the product rear panel) are limited to 96 kHz bandwidth. This software option does not upgrade the analog generator bandwidth.
N3432A	N3432A	POLQA measurement software (fixed perpetual license)	This software option enables all the analog generator/analyzer to perform POLQA measurements.

NOTE

- All software options are fixed perpetual licenses and are tied to the individual performance audio analyzer.

Step 3: Select accessories options

Table 1-5 Accessories options

Option number	Description	Additional information
U8903A-101	Male BNC to male BNC cable, 1.2 m	-
U8903A-102	Male BNC to male RCA cable, 2 m	-
U8903A-103	Male XLR to female XLR cable 2 m	-
U8903B-105	Digital serial interface cable	-
U8903A-107	Cable, accessory – Male XLR – 2 male BNC analyzer, 0.26 m	This is for the analyzer input to convert the balanced measurement from HP 8903B. For more information, refer to the Migrating Balanced Measurements from HP 8903B to Keysight U8903A Audio Analyzer application note (http://literature.cdn.keysight.com/litweb/pdf/5991-0435EN.pdf)
U8903A-108	Cable, accessory – Female XLR – 2 male BNC generator, 0.26 m	This is for the generator output to convert the balanced measurement from HP 8903B. For more information, refer to the Migrating Balanced Measurements from HP 8903B to Keysight U8903A Audio Analyzer application note (http://literature.cdn.keysight.com/litweb/pdf/5991-0435EN.pdf)
U8903A-109	BNC accessory kit	The kit consists of a BNC socket, a custom threaded metal sleeve, and a BNC plug with a custom center pin. The kit can be used to make an in-line BNC component containing any combination of passive components the user wishes to connect between the input and the output.
U8903A-908	Rackmount kit	132.6H without handle
11500A	Cable assembly, Type-N (male) to Type-N (male), DC to 6.0 GHz	-

Step 4: Select warranty options

Table 1-6 Warranty options

Option number	Description	Additional information
R-51B-001-Z	Warranty 1 year; Return to Keysight	1 year warranty is included at no additional charge.
R-51B-001-5Z	Warranty Assurance Plan 5 years; Return to Keysight	-

This information is subject to change without notice. Always refer to the Keysight website for the latest revision.

© Keysight Technologies 2014–2021, 2024

Edition 5, January 2024

Printed in Malaysia



U8903-90055

www.keysight.com

