

Keysight Technologies

N9310A RF Signal Generator

Configuration Guide



Configure Your Keysight N9310A RF Signal Generator

The Keysight Technologies, Inc. N9310A is a general purpose signal generator from 9 kHz to 3 GHz. Its standard features include:

- Continuous wave output: 9 kHz to 3.0 GHz
- Analog modulation output: AM, FM, Φ M, and pulse modulation
- Low frequency output: 20 Hz to 80 kHz

This step-by-step process will help you to configure your N9310A RF signal generator by tailoring its options to meet your requirements.

For detailed specifications, refer to the N9310A RF signal generator data sheet (5990-8116EN). For a product overview, refer to the N9310A RF signal generator brochure (5990-8115EN).

Ordering Information

Description	Model number	Additional information
RF signal generator, 9 kHz to 3.0 GHz	N9310A	Accessories supplied as standard with each signal generator: Quick Start Guide, USB cable, power cord, and documentation CD-ROM
Description	Option number	Additional information
Step 1. Add additional capabilities		
Precision frequency reference	N9310A-PFR	For enhanced frequency stability (aging rate $< \pm 1 \times 10^{-7}$), available for ordering only with base model at initial purchase
Analog I/Q input, 20 MHz bandwidth per channel	N9310A-001	Requires external baseband signal input Learn more from www.keysight.com/find/IQbundle
Step 2. Choose localized User's Guide		
English User's Guide	N9310A-ABA	
Simplified Chinese User's Guide	N9310A-AB2	
Japanese User's Guide	N9310A-ABJ	
Step 3. Add optional accessories		
Power attenuator, 40 dB, DC to 8.5 GHz	N9311X-561	Provides external power attenuator for reversal power protection
Hard transit case (D x W x H)	N9310A-1TC	– 645 x 444 x 268 mm, 13 kg nominal – 25.4 x 17.5 x 10.6 in, 29 lb nominal
Rack mount kit	N9310A-1CM	Includes a rackmount flange and front handle kit. Fits standard 19-inch rack and occupies three units of rack space

Need more RF and microwave accessories? Visit www.keysight.com/find/N9311X

Step 5. Add calibration, technical training, support, and upgrade services		
Select Keysight Calibration Plan		
Commercial calibration certificate with test data	N9310A-UK6	Calibration certificate only available at time of instrument purchase; only provides measurement results
3-year calibration assurance plan (return to Keysight)	R-50C-011-3	Priority calibration service covering all calibration costs for 3 years; 15% cheaper than buying stand-alone calibrations
5-year calibration assurance plan (return to Keysight)	R-50C-011-5	Priority calibration service covering all calibration costs for 5 years; 20% cheaper than buying stand-alone calibrations

Other calibration options may be available, for more information on calibration, go to: www.keysight.com/find/calibration.

For more information on training and application support services, go to: www.keysight.com/find/training.

Instrument Upgrades

Most of the Keysight N9310A RF signal generator options are available for post-sales retrofit.

For license-key upgrades that do not require additional hardware:

1. Place an order for the upgrade with Keysight and request to receive the software entitlement certificate through email
2. Install the license key in the N9310A. Upgrade firmware to the latest revision if required
3. Restart the N9310A
4. Begin using the new capability

Description	Upgrade number
Add analog I/Q input capability	N9310AK-001
Rack mount kit	N9310AK-1CM
Power attenuator	N9311X-561
Hard transit case	N9310AK-1TC

A comprehensive summary about the N9310A upgrades is also available at: www.keysight.com/find/n9310a_upgrade.


Related Literature

Publication number	Publication title
5990-8115EN	Keysight N9310A RF Signal Generator, Brochure
5990-8116EN	Keysight N9310A RF Signal Generator, Data Sheet

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

http://www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.

Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at:

www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:

www.keysight.com/find/contactus
(BP-9-7-17)

DEKRA Certified
ISO 9001 Quality Management System

www.keysight.com/go/quality

Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System

This information is subject to change without notice.

© Keysight Technologies, 2013 – 2018

Published in USA, April 24, 2018

5990-8117EN

www.keysight.com