

# Keysight Technologies E6618A Multiport Adapter

Data Sheet



Used with the Keysight Technologies, Inc. E6630A wireless connectivity test set, the Keysight Technologies E6618A multiport adapter helps you significantly accelerate throughput during non-signaling wireless connectivity device manufacturing test.

The E6618A is controlled by a plug-and-play USB connection with the E6630A. The solution enables the connection of multiple devices under test (DUTs) to a single instrument for parallel testing.

## Definitions and Conditions

All data listed in this datasheet are nominal values when the E6618A is used in conjunction with the E6630A. Nominal values indicate expected performance, or describe product performance that is useful in the application of the product, such as a 50  $\Omega$  connector. This data is not warranted and is measured at room temperature (approximately 25 °C).

### RF performance

Frequency specifications	
RFIO frequency range	RFIO ports 0 to 7 2.4 to 2.5 GHz 4.85 to 6 GHz
GNSS frequency range	GNSS ports 0 to 3 1.1 to 1.7 GHz
Power range	
Output level ranges	
RFIO ports 0 to 7 <sup>1</sup>	-110 to +5 dBm
GNSS ports 0 to 3 <sup>2</sup>	-110 to -40 dBm
Input level range (average power)	
RFIO ports 0 to 7	-50 to +30 dBm (input level range settable from 50 to +45 dBm)
RFIO maximum input power	+33 dBm
RF IN, RF OUT, and GNSS maximum safe input power	+24 dBm
Amplitude accuracy	
GNSS ports 0 to 3	±0.5 dB, -110 to -40 dBm
RFIO ports 0 to 7	
Output	±0.5 dB, 2.4 to 2.5 GHz, -110 to +5 dBm ±0.7 dB, 4.85 to 6 GHz, -110 to -50 dBm ±0.6 dB, 4.85 to 6 GHz, -50 to +5 dBm
Output (multiple ports enabled)	Add ±0.1 dB to account for RSS of port balancing with output amplitude accuracy <sup>3</sup>
Input	±0.5 dB, 2.4 to 2.5 GHz, -50 to +28 dBm ±0.6 dB, 4.85 to 6 GHz, -50 to +28 dBm
RF return loss	
GNSS ports 0 to 3	> 20 dB, 1.1 to 1.7 GHz
RFIO ports 0 to 7	15 dB, 2.4 to 2.5 GHz, 4.85 to 5.85 GHz (input range > +6 dBm or output power < 0 dBm) 13 dB, 2.4 to 2.5 GHz, 4.85 to 5.85 GHz (input range < +6 dBm or output power > 0 dBm)

<sup>1</sup>Power level is user settable from -150 to +18 dBm.

<sup>2</sup>Power level is user settable from -150 to 0 dBm.

<sup>3</sup>With multiple ports enabled you must RSS the worst-case port balance (0.4 dB) with the worst-case amplitude accuracy to calculate the maximum additional amplitude error (listed above). For non-worst-case conditions the error will be less than that listed.

## RF performance (continued)

<b>WLAN analyzer error vector magnitude (EVM)</b>	
<b>Residual EVM (phase tracking on, pre-amble)</b>	
802.11b, 2.4 to 2.5 GHz, 20 MHz	≤ 4% at +8 dBm input power
802.11g, 2.4 to 2.5 GHz, 20 MHz	≤ -52 dB at +8 dBm input power
802.11a, 4.85 to 6 GHz, 20 MHz	≤ -40 dB at +2 dBm input power
802.11n, 4.85 to 6 GHz, 20 MHz	≤ -42 dB at +2 dBm input power
802.11ac, 4.85 to 6GHz, 80 MHz	≤ -41 dB at +2 dBm input power
802.11ac, 4.85 to 6 GHz, 160 MHz	≤ -40 dB at +2 dBm input power
<b>WLAN source error vector magnitude (EVM)</b>	
<b>Residual EVM</b>	
802.11ac, 4.85 to 6 GHz, 80 MHz	≤ -42 dB at -7 dBm source power
802.11ac, 4.85 to 6 GHz, 160 MHz	≤ -42 dB at -7 dBm source power

## Front panel

<b>RF connectors</b>	
RF In	SMA female, 50 Ω
RF Out	SMA female, 50 Ω
GNSS ports 0 to 3 Out	SMA female, 50 Ω
RFIO ports 0 to 7	SMA female, 50 Ω
<b>USB connector</b>	
Standard	Compatible with USB 2.0
Connector	USB Type-B female
<b>Triggers</b>	
Trig 1	BNC female
Trig 2	BNC female
Trig 3	BNC female
Trig Out	BNC female
Trigger level range	LVTTTL (5 volt compliant)

## General specifications

<b>Size and weight</b>	
Dimensions (H x W x D)	65 mm x 430 mm x 392 mm (2.6 in x 17 in x 15.4 in)
Weight (without shipping package)	6.8 kg (15 lbs)
Weight (with shipping package)	11.8 kg (26 lbs)

[www.keysight.com/find/E6618A](http://www.keysight.com/find/E6618A)

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

### Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

### Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

### Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:  
[www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)  
 (BP-07-10-14)