

Keysight N9343C

Handheld Spectrum Analyzer (HSA)

13.6 GHz

Data Sheet



Field testing just got easier

If you are making measurements in the field, the Keysight Technologies, Inc. N9343C handheld spectrum analyzer (HSA) makes your job easier. It's got the features you need for operating in tough field environments, and its measurement performance gives you confidence the job's been done right. The N9343C HSA lets you automate routine tasks to save time and ensure consistent results. Field testing just got easier with the Keysight N9343C HSA.

Definitions and requirements

This data sheet contains specifications and supplemental information for Keysight N9343C handheld spectrum analyzer. The differences between specifications, typical performance, and nominal values are described as follows.

Definitions

"Specifications" describe the performance of parameters that apply to temperatures ranging from -10 to 50 °C, unless otherwise noted.

95th percentile values indicate the breadth of the population (> 2) of performance tolerances expected to be met in 95% of the cases with a 95% confidence, for any ambient temperature in the range of 20 to 30 °C. In addition to the statistical observations of a sample of instruments, these values include the effects of the uncertainties of external calibration references. These values are not warranted. These values are updated occasionally if a significant change in the statistically observed behavior of production instruments occurs.

"Typical" describes additional product performance information. It is performance beyond specification that 80% of the units exhibit with a 95% confidence level over the temperature range of 20 to 30 °C. Typical performance does not include measurement uncertainty.

"Nominal values" indicate expected performance, or describe product performance that is useful in the application of the product.

Conditions required to meet specifications

The following conditions must be met for the analyzer to meet its specifications.


- The analyzer is within its calibration cycle.
- Under auto couple control, except when Swp Time Rule is set to Accuracy.
- Any analyzer that has been stored at a temperature range inside the allowed storage range but outside the allowed operating range must be stored at an ambient temperature within the allowed operating range for at least two hours before being turned on.
- The analyzer has been turned on at least 30 minutes.

Certification

Keysight Technologies certifies that this product met its published specifications at the time of shipment from the factory. Keysight Technologies further certifies that its calibration measurements are traceable to the United States National Institute of Standards and Technology (NIST), to the extent allowed by the Institute's calibration facility, and to the calibration facilities of other International Standards Organization (ISO) members.

Your job just got easier:

- Get the features you need in a field-ready instrument.
- Gain confidence in your measurements with benchtop performance in a handheld instrument.
- Innovative task planner (www.keysight.com/find/taskplanner) reduces test setup time by 95%, delivers test automation and consistency, and makes it easy to capture test results, generate reports, and share task plans with others.



Specifications

Specification		Supplemental information
Frequency		
Frequency range	1 MHz to 13.6 GHz (usable to 9 kHz)	AC coupled
Internal 10 MHz frequency reference accuracy		
Aging rate	± 1 ppm/year	
Temperature stability	± 1 ppm	Referenced to frequency reading at 25 °C. Temperature varied at max. of 2 °C per minute. Control voltage held at voltage control range midpoint
Frequency readout accuracy with marker (start, stop, center, marker)		
Marker resolution	(frequency span)/(sweep points - 1)	
Uncertainty	\pm (frequency indication \times frequency reference uncertainty + 1% \times span + 20% \times resolution bandwidth + marker resolution + 1 Hz)	Frequency reference uncertainty = (aging rate \times period of time since adjustment + temperature stability)
Marker frequency counter		
Resolution	1 Hz	
Accuracy	\pm (marker frequency \times frequency reference uncertainty + counter resolution)	RBW/span ≥ 0.02 ; marker level to displayed noise level > 25 dB; frequency offset 0 Hz
Frequency span		
Range	0 Hz (zero span), 100 Hz to 13.6 GHz	
Resolution	1 Hz	
Accuracy	\pm (0.22% \times span + span/(sweep points - 1))	Nominal
SSB phase noise		
Carrier offset	30 kHz	< -86 dBc/Hz, typical -89 dBc/Hz
	100 kHz	< -97 dBc/Hz, typical -99 dBc/Hz
	1 MHz	< -115 dBc/Hz, typical -119 dBc/Hz
Resolution bandwidth (RBW)		
-3 dB bandwidth	10 Hz to 3 MHz	1-3-10 sequence
Accuracy	$\pm 5\%$, RBW = 10 Hz to 1 MHz	Nominal
	$\pm 10\%$, RBW = 3 MHz	
Resolution filter shape factor	$< 5:1$	Nominal; 60 dB/3 dB bandwidth ratio; digital, Gaussian-like
EMI bandwidth (CISPR compliant)	200 Hz, 9 kHz, 120 kHz, 1 MHz	Option EMC required
Accuracy	$\pm 10\%$ nominal	
Resolution filter shape factor	$< 5:1$ nominal	-60 dB/-6 dB bandwidth ratio
Video bandwidth (VBW)		
-3 dB bandwidth	1 Hz to 3 MHz	1-3-10 sequence
Accuracy	$\pm 10\%$, VBW = 1 Hz to 1 MHz	Nominal

Specifications (continued)

Amplitude specifications		Supplemental information
Measurement range		
1 to 500 MHz	Displayed average noise level (DANL) to +10 dBm	Preamp off
500 MHz to 13.6 GHz	Displayed average noise level (DANL) to +20 dBm	
Input attenuator range	0 to 50 dB, in 5 dB steps	
Maximum safe input level		
Average continuous power	+30 dBm, 3 minutes maximum	Input attenuator setting ≥ 20 dB, 1 MHz to 13.6 GHz
DC voltage	± 50 VDC maximum	
Displayed average noise level ¹		
Preamp off	Normalized to 1 Hz	Minimum RBW
1 to 10 MHz	-125 dBm, typical -140 dBm	-115 dBm, typical -130 dBm
10 MHz to 3 GHz	-137 dBm, typical -142 dBm	-127 dBm, typical -132 dBm
3 to 7 GHz	-135 dBm, typical -140 dBm	-125 dBm, typical -130 dBm
7 to 10 GHz	-139 dBm, typical -142 dBm	-129 dBm, typical -132 dBm
10 to 13.6 GHz	-137 dBm, typical -140 dBm	-127 dBm, typical -130 dBm
Preamp on		
1 to 10 MHz	-140 dBm, typical -156 dBm	-130 dBm, typical -146 dBm
10 MHz to 3 GHz	-150 dBm, typical -154 dBm	-140 dBm, typical -144 dBm
3 to 6 GHz	-145 dBm, typical -150 dBm	-135 dBm, typical -140 dBm
6 to 13.6 GHz	-151 dBm, typical -155 dBm	-141 dBm, typical -145 dBm
Level display range		
Log scale	10 to 100 dB, 10 divisions displayed, 1, 2, 5, 10 dB/division	
Linear scale	0 to 100%, 10 divisions displayed	
Scale units	dBm, dBmV, dB μ V, W, V, dBmV EMF, dB μ V EMF, V EMF	
Sweep (trace) points	461	
Number of markers	6	
Marker functions	Normal, frequency counter, noise marker, band power and AM/FM demod (tune and listen)	
and listen)	Log scale	0.01 dB
	Linear scale	$\leq 1\%$ of signal level
Detectors	Normal, positive peak, sample, negative peak, average (video, RMS, voltage), quasi-peak (option EMC required)	
Number of traces	4	

1. RMS detector, trace averaging > 40 , 0 dB input attenuation, input terminated 50 Ω , 1 kHz resolution bandwidth, 20 to 30 °C.

Specifications (continued)

Amplitude specifications (continued)				Supplemental information
Level display range (continued)				
Trace functions		Clear/write, maximum hold, minimum hold, average		
Level measurement error	1 MHz to 7 GHz	Excluding input VSWR mismatch ± 1.3 dB		<ul style="list-style-type: none">– 20 to 30 °C, 30 to 70% RH, peak detector, preamp off, input signal –50 to 0 dBm, 95% percentile– Swp Time Rule is set to Accuracy– Adds ± 0.3 dB when Swp Time Rule is set to Speed– Adds ±0.3 dB with 5-minute warm-up
	7 to 13.6 GHz	± 1.6 dB		
Reference level ²				
Setting range		–100 to +30 dBm		Steps of 1 dB
Setting resolution	Log scale	0.01 dB		
	Linear scale	Same as log (2.236 μV to 7.07 V)		
Accuracy		0		
RF input VSWR (at tuned frequency)				
10 MHz to 3 GHz	1 MHz to 7 GHz	< 1.5:1		Nominal, ≥ 10 dB attenuation
	7 to 13.6 GHz	< 2:1		
Spurious response				
Second harmonic distortion		<div>< –65 dBc, typical < –70 dBc, 50 MHz to 7 GHz</div> <div>< –80 dBc, typical < –90 dBc, 7 to 13.6 GHz</div>		Mixer signal level at –30 dBm, input attenuation dB, preamp off, 20 to 30 °C
Third order intermodulation distortion (third order intercept)		5-min warm-up	30-min warm-up	Two –20 dBm tones at input mixer, spaced by 100 kHz, input attenuation 0 dB, preamp off, reference level ≥ –30 dBm, 20 to 30 °C
	50 to 300 MHz	+6.5 dBm, typical +7.5 dBm	+8 dBm, typical +9 dBm	
	300 MHz to 8 GHz	+7.5 dBm, typical +9.5 dBm	+9 dBm, typical +11 dBm	
	8 to 13.6 GHz	+8.5 dBm, typical +10.5 dBm	+10 dBm, typical +12 dBm	
Input related spurious		< –59 dBc, typical < –69 dBc	< –60 dBc, typical < –70 dBc	<ul style="list-style-type: none">– –30 dBm signal at input mixer, span < 2.9 GHz– Exception: –55 dBc (2 x F1 = center frequency –5,890 MHz, 7 GHz < center frequency < 10 GHz, with F1 input frequency)
Inherent residual response	1 MHz to 7 GHz	< –93.5 dBm, typical –108.5 dBm	< –95 dBm, typical –110 dBm	Input terminated and 0 dB RF attenuation, preamplifier off
	7 GHz to 13.6 GHz	< –83.5 dBm, typical –91.5 dBm	< –85 dBm, typical –93 dBm	

2. Reference level only affects the display not the measurement, so trace data markers do not cause additional errors in measurement results.

Specifications (continued)

Sweep specifications		Supplemental information
Sweep time		
Range	2 ms to 1000 s	Span ≥ 100 Hz
	600 ns to 200 s	Span = 0 Hz (zero span)
Sweep mode	Continuous, single	
Sweep time rule	Accuracy, speed	
Trigger source	Free run, video, external, RF burst	
Trigger slope	Selectable positive or negative edge	
Trigger delay	± 12 ms to ± 12 s	Nominal, span = 0 Hz (zero span)
Front panel input/output		Supplemental information
RF input		
Connector and impedance	Type-N female, 50 Ω	Nominal
10 MHz reference/external trigger input		
Reference input frequency	10 MHz	
Reference input amplitude	0 to +10 dBm	
Trigger voltage	5 V TTL level	Nominal
Connector	BNC female, 50 Ω	Nominal
Probe power		
Voltage/current	+15 Vdc, ± 7% at 0 to 150 mA (nominal)	
	−12.6 Vdc, ± 10% at 0 to 150 mA (nominal)	
	GND	
Connectivity		
USB host	USB Type-A female, compatible with USB 2.0 full speed	
USB device	USB Type-mini AB female, compatible with USB 2.0 full speed	
LAN	RJ-45, 10 Base-T	
General specifications		Supplemental information
Display		
Resolution	640 pixels x 480 pixels	
Size and type	170 mm (6.5 in) TFT color display	
Internal memory		
System memory	64 MB	For system use. Not user accessible
User memory	64 MB	User accessible. Able to store about 14,000 traces
Languages		
On-screen GUI	English, Simplified Chinese, Traditional Chinese, French, German, Italian, Japanese, Korean, Russian, Spanish, Portuguese	

Specifications (continued)

General specifications (continued)		Supplemental information
Power requirements and calibration		
Adaptor voltage	100 to 240 V AC, 50 to 60 Hz	Auto-ranging
	15 V DC, 5.3 A, 80 W max	
Power consumption	16 W	Typical
Battery operating time (fully charged battery)	3.5 hours	Tracking generator off, preamplifier on
	3 hours	Tracking generator on, preamplifier on
Charging time	3 hours	
Life time	300 to 500 charge cycles	
Warm-up time	5 minutes	
Calibration cycle	One year	
Environmental and size		
Temperature range	–10 to +50 °C	Operating (battery: 0 to 50 °C)
	–40 to +70 °C	Storage (battery: –20 to 50 °C)
Altitude	9,144 meters (30,000 feet)	Operating with battery
	3,000 meters (9,840 feet)	Operating with AC to DC adapter
	15,240 meters (50,000 feet)	Non-operating
	< 95%	
Weight	3.2 kg (7 lbs)	Net (shipping) approximately, 3.6 kg (7.9 lbs) with battery
Dimensions	318 mm × 207 mm × 69 mm (12.5 in × 8.15 in × 2.7 in)	Approximately (W × H × D)
Option specifications		Supplemental information
Channel scanner (Option SCN)		
Scan modes	Top N, bottom N, and list	
Channels displayed	1 to 20	
Display orientation	Vertical	Number of channels ≤ 5
	Horizontal	Number of channels > 5
Chart	Bar chart, and time chart	
Log file	.CSV and .KML	
Radio standards	Pre-defined and user-defined. Pre-defined standards include the major wireless communication standards such as GSM, CDMA, W-CDMA, LTE, WiMAX, etc.	
Spectrum monitor (Option SIM)		
Display modes	Spectrogram	
	Spectrum trace	
	Combination of spectrogram and spectrum trace in one screen	
RF preamplifier (Option P13)		
Frequency range	1 MHz to 13.6 GHz	
Gain	15 dB	Nominal
Tracking generator (Option TG7)		
Frequency range	5 MHz to 7 GHz	
Output level	0 to –20 dBm	1 dB steps
VSWR	< 2.0:1	Nominal
Connector and impedance	Type-N female, 50 Ω	

Specifications (continued)

Option specifications (continued)		Supplemental information
AM/FM modulation analysis (Option AMA)		
Frequency range	10 MHz to 13.6 GHz	
Carrier power accuracy	< 7 GHz, ± 1.5 dB	Nominal
	7 to 13.6 GHz, ± 1.8 dB	Nominal
Carrier power range	–30 to +10 dBm	1 to 500 MHz
	–30 to +20 dBm	500 MHz to 13.6 GHz
Carrier power displayed resolution	0.01 dBm	
AM measurement		
Modulation rate	20 Hz to 100 kHz	
Accuracy	1 Hz	Nominal (modulation rate < 1 kHz)
	< 0.1% modulation rate	Nominal (modulation rate > 1 kHz)
Depth	5 to 95%	
Accuracy	± 4%	Nominal
FM measurement		
Modulation rate	20 Hz to 200 kHz	
Accuracy	1 Hz	Nominal (modulation rate < 1 kHz)
	< 0.1% modulation rate	Nominal (modulation rate > 1 kHz)
Depth	20 Hz to 400 kHz	
Accuracy	± 4%	Nominal
ASK/FSK modulation analysis (Option DMA)		
Frequency range	2.5 MHz to 6 GHz	
Carrier power accuracy	± 2 dB	Nominal
Carrier power range	–30 to +20 dBm	
Carrier power displayed resolution	0.01 dBm	
ASK measurement		
Symbol rate range	100 Hz to 100 kHz	
Modulation depth/index	5 to 95%	
Accuracy	± 4%	Nominal
Displayed resolution	0.1%	
FSK measurement		
FSK deviation	100 Hz to 400 kHz	
Symbol rate range	100 Hz to 20 kHz	1 ≤ B* ≤ 20
	20 to 50 kHz	1 ≤ B ≤ 8
	50 to 100 kHz	1 ≤ B ≤ 4
Accuracy	± 4%	Nominal
Displayed resolution	0.01 Hz	
Time-gated spectrum analysis (Option TMG)		
Gated sweep		
Span range	Any span	
RBW range	> = 1 kHz	VBW is fixed and equal to RBW ³
Gate delay range	12 μs to 10 s	200 ns resolution
Gate length range	84 μs to 10 s	200 ns resolution

* B is the ratio of frequency deviation to symbol rate (deviation/rate).

Specifications (continued)

Option specifications (continued)		Supplemental information
Time-gated spectrum analysis (Option TMG) (continued)		
Gated sweep (continued)		
Gate sources	External	
	RF burst	
	Periodic timer	<ul style="list-style-type: none">– Sync sources include free, external, and RF burst– Period: 0 to 20.0 s (It should be greater than gate delay plus gate length)– Offset: –5 to +5 s
RF Burst		
Level range		–60 to –20 dBm plus attenuation (nominal)
Bandwidth (–10 dB)		8 MHz (nominal)
Frequency limitations		If the start or center frequency is too close to zero, LO feedthrough can degrade or prevent triggering. How close is too close depends on the bandwidth.
Built-in GPS receiver and GPS antenna (Option GPS)		
GPS information tagging	Longitude, latitude, and altitude	
GPS antenna	Built-in	
Frequency accuracy with GPS on	± 50 ppb	
External GPS antenna connector	SMA-F	External GPS antenna, N934xC-GPA, is offered as an optional accessory
USB peak and average power sensor support (Option PWP)		
Power sensor supported	Keysight U2020 X-series USB peak and average power sensor	
Frequency range	50 MHz to 40 GHz	Sensor dependent
Peak power dynamic range	–30 to +20 dBm	
USB average power sensor support (Option PWM)		
Power sensor supported	Keysight U2000 Series USB power sensor	
Frequency range	9 kHz to 24 GHz	Sensor dependent
Dynamic range	–60 to +44 dBm	Sensor dependent
Security features (Option SEC)		
Security erase method	Erase the entire user flash memory by writing single character “1” over all memory locations	Non-recoverable
Port control	Disable/enable LAN port or USB port	
Task planner for test automation (Option TPN)		
Task plan execution mode	Auto, manual, and manual if fail	
Task plan file	.TPN	Complementary task plan editor is available with HSA PC software
Number of tasks	Maximum 20 in a single .TPN file	
Measurements supported	Regular spectrum analysis and power suite (channel power, ACPR, and OBW)	


Visit www.keysight.com/find/taskplanner for more information.

3. For efficiency and convenience, RBW is restricted to be equal to or greater than 1 kHz and VBW is restricted to be equal to RBW.

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/n9343c

www.keysight.com/find/hsa-videos

www.keysight.com/find/hsa

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at:

www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:

www.keysight.com/find/contactus
(BP-9-7-17)

DEKRA Certified
ISO 9001 Quality Management System

www.keysight.com/go/quality

Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System



Unlocking Measurement Insights

This information is subject to change without notice.

© Keysight Technologies, 2017
Published in USA, December 1, 2017
5990-7499EN

www.keysight.com