

World Leading High-Accurate Dk/Df Measurement System, PCB Measurement, 900MHz - 15GHz


System No. DPS50

Keysight Technologies and KEYCOM Corp.

Highly accurate in dielectric loss tangent ($\tan \delta$) measurement and requires no conductor pattern; Optimum solution for thin film measurement

《ASTM, IPC Standard compliant》

DPS50 is a resonance method, strip line type dielectric constant and dielectric loss tangent measurement system optimized for sheet materials with dielectric constant of approximately 1 to 20 and relatively small dielectric loss in the frequency range of 900MHz to 15GHz. This system is compliant with the IPC-TM-650 2. 5. 5. 5. 1 Stripline Test for Complex Relative Permittivity of Circuit Board Materials to 14GHz, and ASTM D3380 Standard Method of Test for Permittivity (Dielectric Constant) and Dissipation Factor of Plastic-Based Microwave Circuit Substrates. This measurement technique was announced at 2008 IEEE I2MTC.



Compliance standards

IPC-TM-650, ASTM 3380

Publications

Suzuki, H. ; Hotchi, T. ; Nojima, T.

"A New Measurement System for the Perpendicular Complex Permittivity to DUT Sheet by Stripline Simulation"

Instrumentation and Measurement, IEEE Transactions on (Volume:61, Issue: 9) pp2476 - 2482 Date of Publication: Sept. 2012

Specimen examples

— PCB (Prepreg) — Planar antenna — Film

Specifications

Frequency : 900MHz ~ 15GHz

Permittivity : 1.05 ~ 20
(Accuracy : $\pm 5\%$,
depending on VNA)

$\tan \delta$: 0.001 ~ 0.05
(Accuracy : $\pm 10\%$ or
 ± 0.0005 , depending on
VNA)

Sample size :

R-09.B	900MHz	30mm × 150mm
R-1B	1GHz	30mm × 150mm
R-2B	2GHz	30mm × 80mm
R-5B	5GHz	30mm × 80mm
R-10B	10GHz	30mm × 30mm
R-15B	15GHz	30mm × 30mm


Sample thickness :
50 μ m ~ 2mm (≤ 2 mm @ 1GHz,
 ≤ 0.5 mm @ 10GHz)

Features

- Eliminates fringing effect
- No conductor pattern is required
- Capable of measuring in a perpendicular electric field to the sample sheet

World Leading High-Accurate Dk/Df Measurement System, PCB Measurement, 900MHz - 15GHz

Configurations



Ordering Information

Keysight Technologies



KEYCOM Corp.

System No. DPS50

1. Pressure type fixture	FS-03
2. Resonator (measurement + calibration + fixture)	900MHz..... R-0.9B 1GHz..... R-1B 2GHz..... R-2B 5GHz..... R-5B 10GHz..... R-10B 15GHz..... R-15B
3. Software	DMP-61M
4. Coaxial cable	CM06D-APC2.9(m)APC2.9(m)-500 2pc.
5. Windows PC, Printer	Available upon request
6. GPIB interface	GP-01

Product specifications and descriptions in this document subject to change without notice.

Learn more at: www.keysight.com

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

KEYCOM
Characteristic Technologies

KEYCOM Corp.
3-40-2 Minamitsuka Toshima-ku,
Tokyo
170-0005 Japan
Phone:+81-3-5950-3101
FAX:+81-3-5950-3380

KEYCOM USA Corp.
533 Airport Blvd. Suite 400
Burlingame, CA 94010 USA
Phone: +1-650-685-2477
FAX: +1-650-373-2002

www.keysight.co.jp
For more information on KEYCOM Corp. products,
applications or services, please visit our website at
www.keysight.co.jp or
e-mail us at E-mail: Info@keysight.co.jp

Keysight & Solutions Partners
Extending our solutions to meet your needs