

Keysight Technologies

Semiconductor Manufacturer Likes Familiarity, Enhanced Features of New 34461A DMM

Case Study

Introduction

As semiconductor manufacturers develop new chips for battery-powered devices, their goal is to deliver better performance at lower power levels. So their R&D teams spend a lot of time characterizing their devices, studying parameters like power, voltage levels and timing. When they turn on a silicon chip prototype, they need to know how much power it is consuming in all of its states: when it is first turned on, when it is stable, when it is in use, and when it is powered off. And of course, they need to investigate any glitches they discover in the process.

As a chip maker for consumer electronics and high-accuracy, ultraprecision applications, a U.S. semiconductor manufacturer uses many general-purpose test instruments as it characterizes and debugs its prototype products and qualifies first-production silicon. And its digital multimeters are the workhorses of its measurement tool stable.

For years, the semiconductor R&D team has used the Keysight Technologies, Inc. 34401A, the industry-standard 6.5-digit multimeter, to measure DC volts and DC current. Occasionally the team measures resistance, AC voltage and AC current, especially around ripple on regulators. The 34401A DMM gives them all the capabilities they need except high-current measurement capabilities. The 34401A is limited to measuring up to 3 amps.

When a Keysight product development team asked the semiconductor R&D team manager if he would consider replacing his 34401As with a newer DMM, the R&D manager didn't have to think twice about his requirements: The new DMM would have to measure up to 10 A. The new instrument had to be in the same price range as the 34401A with equivalent performance in terms of digits of accuracy, resolution, and stability. And the new DMM had to have a familiar feel. He wanted his engineers to focus on getting their jobs done instead of investing hours in relearning a new voltmeter from scratch.

When the Keysight product development team unveiled the new Truevolt 34461A DMM, the R&D manager and his team declared it a winner. Not only did it meet their criteria, but it offered other enhancements that gave them unexpected benefits.

The large, colorful, liquid-crystal display drew “oohs” and “aahs” when the R&D engineers realized they could get a lot more information and get it faster than they could with just the numbers on the 34401A’s low-resolution numeric display readout. The 34461A’s trend chart display lets them immediately spot trends when they are doing experiments over time. They were pleased to be able to pull up histograms and turn on statistics such as mean, standard deviation, average, min, max – all without having to transfer data to a PC for post processing.

Another 34461A feature that delighted the R&D team was the ability to add labels to measurements on the screen. The R&D manager described his team’s current practice of sticking adhesive-backed notes to each DMM with a description of the measurement it is making. He welcomed the ability to replace the informal notes with on-screen labels.

One of the 34461A DMM’s new features also resolved an issue that had irritated the manager’s R&D engineers. The 34401A DMM’s default mode is low impedance, but the team frequently uses the high-impedance mode. When engineers turn off the 34401A, it defaults back to low-impedance mode, so they have to reconfigure the DMM for high impedance each time they turn it on. With the 34461A, engineers have the ability to save alternative power-up states, eliminating the aggravation of having to reconfigure their previous setups each time.

“You guys have done a good job of making an improved version of what we are already familiar with, and apparently you’ve been able to keep it in the same price range,” said the R&D manager. “This is very important to us.”

The R&D managers also made it clear that he finds it important to work with a company that he knows is going to be there to support him. He appreciates the fact that Keysight stands behind its products and he trusts Keysight test instruments to be in spec.

“Clearly, when we are making measurements and drawing conclusions from the readings we are taking, we need to know we are drawing the proper conclusions,” he said. “We have to be able to trust the meter.”

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.



www.axiestandard.org

AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Keysight is a founding member of the AXIe consortium. ATCA®, AdvancedTCA®, and the ATCA logo are registered US trademarks of the PCI Industrial Computer Manufacturers Group.



www.lxistandard.org

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Keysight is a founding member of the LXI consortium.



www.pxisa.org

PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.



Three-Year Warranty

www.keysight.com/find/ThreeYearWarranty

Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.



www.keysight.com/quality

Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2008
Quality Management System

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/us/en/products/digital-multimeters-dmm.html

For more information on Keysight

Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	0800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:

www.keysight.com/find/contactus

(BP-07-10-14)