


Keysight Competitive Comparison

Keysight S-Series versus Rohde & Schwarz RT01000

Keysight S-Series



The Keysight Technologies, Inc. S-Series oscilloscope provides bandwidths up to 8 GHz with class-leading signal integrity and analysis. Custom ASICs, including a 40 GSa/s, 10-bit ADC, allow you to see your real signal. Class-leading deep memory and a large suite of analysis tools complement a designed-for-touch user interface and a 15" multi-touch capacitive touch-screen display.

Rohde & Schwarz RT01000 Series



A 15" multi-touch capacitive touch-screen display offers 2x more viewing area and much greater sensitivity to user inputs.

	Keysight S-Series		R&S RTO1000	
Bandwidth	Up to 8 GHz	✓	Up to 4 GHz	✗
Max sampling rate	20 GSa/s on all models	✓	10 GSa/s on up to 2 GHz	✗
Standard memory depth (4 ch)	50 Mpts	✓	20 Mpts	✗
	800 Mpts	✓	200 Mpts	✗
ADC bits	10 bits	✓	8 bits	✗
ENOB at 1 GHz	8.0 bits	✓	7.1 bits	✗
RMS noise at 1 mV/div	153 μ V at 4 GHz	✓	240 μ V at 4 GHz	✗
Waveform update rate (vectors on)	Up to 2,000 wfms/s	✗	Up to 600,000 wfms/s	✓
Internal drive	SSD	✓	HDD	✗
Display	15" capacitive multi-touch	✓	10.4" resistive touch	✗
Math functions	16	✓	4	✗
Compliance, protocol, analysis applications	Extensive	✓	Limited	✗
Supported probes	Extensive	✓	Limited	✗
Time scale accuracy	\pm 75 ppb	✓	\pm 5,000 ppb	✗
BenchVue support	Yes	✓	Not available	✗

KEYSIGHT SERVICES

Accelerate Technology Adoption. *Lower costs.*

www.keysight.com/find/services

Keysight Services helps you improve productivity and product quality with our comprehensive service offerings of one-stop calibration, repair, asset management, technology refresh, consulting, training, and more.