

Keysight Technologies

FieldFox Handheld Analyzers

Selection Guide

Choose the FieldFox that meets your needs

RF and microwave (combination) analyzers

Standard: Cable and antenna tester (CAT) ¹

Key options (prices vary):

- Vector network analyzer
- Spectrum analyzer
- Built-in power meter
- Pulse measurements
- Channel scanner
- Real-time spectrum analyzer

RF and microwave vector network analyzers (VNAs)

Standard: Transmission/reflection VNA

Key options (prices vary):

- Built-in power meter
- Pulse measurements

Microwave spectrum analyzers (SAs)

Standard: Spectrum analyzer

Key options (prices vary):

- Built-in power meter
- Pulse measurements
- Channel scanner
- Real-time spectrum analyzer

Select your model and frequency



Combination models (CAT + VNA + SA)						VNA models		SA models	
Maximum frequency									
4 GHz		N9912A-104		N9913A		N9923A-104		-	
6/6.5 GHz		N9912A-106 ²		N9914A ³		N9923A-106 ²		-	
9 GHz		-		N9915A		-		N9925A	
14 GHz		-		N9916A		-		N9926A	
18 GHz		-		N9917A		-		N9927A	
26.5 GHz		-		N9918A		-		N9928A	
32 GHz		-		N9950A		-		-	
44 GHz		-		N9951A		-		-	
50 GHz		-		N9952A		-		-	
Start frequencies									
N991x/2x/3x									
CAT/VNA mode		2 MHz		30 kHz		2 MHz		30 kHz	
SA mode		100 kHz		100 kHz		-		-	
N995x/6x									
CAT/VNA mode		-		300 kHz		-		-	
SA mode		-		9 kHz		-		-	

1. Also referred to as cable and antenna analyzer

2. Maximum frequency is 6 GHz.

3. Maximum frequency is 6.5 GHz



Unlocking Measurement Insights

Customize your FieldFox and choose the options you want

Options must be ordered separately.
Prices vary based on option and analyzer.

	RF combination	Microwave combination	RF VNA	Microwave VNA	Microwave SA
	N9912A	N9913A, N9914A N9915A, N9916A N9917A, N9918A N9950A, N9951A N9952A ¹	N9923A	N9925A, N9926A N9927A, N9928A	N9935A, N9936A N9937A, N9938A N9960A, N9961A N9962A ¹
CAT/VNA features					
Cable and antenna tester	√	√	√	√	Subset ²
TDR cable measurements	-	√	-	√	-
VNA transmission/reflection	Subset ³	√	√	√	-
VNA full 2-port S-parameters	-	√	√	√	-
QuickCal	√ ⁴	√ ⁵	√	√	-
1-port mixed-mode S-parameters	-	√	√	√	-
VNA time domain	√	√	√	√	-
Vector voltmeter	Subset ⁶	√	√	√	-
SA features					
Spectrum analyzer	√	√	-	-	√
Tracking generator	√	√	-	-	√
Preamplifier	√	√	-	-	√
Interference analyzer ⁷	√	√	-	-	√
SA time gating	-	√	-	-	√
Channel scanner	√	√	-	-	√
Analog demodulation	-	√	-	-	√
ERTA ⁸	-	√	-	-	√
Real-time spectrum analyzer (RTSA) ⁹	-	√	-	-	√
Power measurements					
USB power sensor support	√	√	√	√	√
USB sensor meas. vs. freq.	√	√	√	√	√
Pulse meas. with peak sensor	√	√	√	√	√
Built-in power meter	√	√	-	√	√
System features					
Remote control capability	√	√	√	√	√
GPS receiver	External only ¹⁰	√	External only ¹⁰	√	√
DC bias voltage source	-	√	-	√	√
SCPI over LAN and USB ¹¹	√	√	√	√	√

1. In most frequency ranges, the N995xA/6xA models have the highest dynamic range, most stability and best DANL. Measurement accuracy is comparable between the models. The Data Sheet can be used for a more detailed comparison (5990-9783EN).
2. N993xA/6xA (SA only models) offer the ability to measure VSWR/reflection (as an option), but not the full CAT features.
3. N9912A offers S11 mag and phase and S21 mag. There is no S21 phase. Calibration choices: OSL, response and QuickCal.
4. N9912A's QuickCal is a subset of the QuickCal available on other FieldFox models.
5. QuickCal is not available on N995xA models.
6. N9912A's VVM includes a subset of the features: 1-port cable trimming mag and phase, and 2-port transmission mag. The full VVM (available on other models) includes 1-port cable trimming mag and phase, 2-port transmission mag and phase, A/B and B/A.
7. FieldFox's interference analyzer capability includes spectrogram, waterfall, and trace playback and recording.
8. ERTA: Extended range transmission analysis. ERTA enables scalar transmission measurement of long cables using two FieldFoxes.
9. RTSA capability for N991xA/3xA is only available for serial number prefix starting with MY5607/SG5607/US5607 or upgraded with Option N9910HU-100/200/300.
10. N9912A and N9923A can display GPS information using an external USB GPS receiver which the user needs to purchase separately. All other FieldFox models have a built-in GPS receiver, available as Option 307. The user will need to purchase a GPS antenna N9910X-825
11. SCPI over USB is only available for FieldFox with serial number prefix starting with MY5607/SG5607/US5607 or upgraded with Option N9910HU-xxx



Unlocking Measurement Insights

www.keysight.com/find/fieldfox

This information is subject to change without notice.

© Keysight Technologies 2015-2017

Published in USA, February 10, 2017

5992-1016EN

www.keysight.com