

DAQ970A and DAQ973A Data Acquisition Systems

Sample More Signals, Faster and Dynamically



- 1. USB drive
- 2. On/Standby switch with LED indicator
- 3. Color LCD Display / GUI
- 4. Softkeys
- 5. Measurement operation keys
- 6. Measurement configuration keys (to set measurement parameters)
- 7. Knob
- 8. Cursor navigation keypad

The DAQ970A / DAQ973A data acquisition systems have high-quality switching and an advanced 6 ½ digit DMM built in, which allows you to measure accurately.

- The autocalibration compensates for drifts in the internal DMM or on the DAQM907A multifunction module or on the DAQM909A digitizer module caused by time and temperature changes.
- Built-in internal module calibration reduces thermal voltage offset errors.
- Ability to measure very low current ranges (1 µA DC and 100 µA AC) and higher resistance range (1000 MΩ).

Key features

- 3-slot mainframes with built-in 6 ½ digit DMM
- Basic 0.003% DCV accuracy
- 10 switches, RF, and control plug-in modules, including a 4-channel simultaneous sampling digitizer
- Up to 450 channel/s scan rate
- Up to 120 channels per system
- Up to one million points scanning memory
- Measures and converts 14 different input signals: Temperature with a thermocouple, RTDs, and thermistor; DC/AC volts; 2- and 4-wire resistance; frequency and period; DC/AC current, diode, and capacitance; direct strain and bridge strain
- Large 4.3" color display for ease of setup and viewing data
- LAN and USB for easy connectivity to your PC (DAQ973A comes with additional GPIB)
- Code compatible with the 34970A/34972A
- USB flash drive support to copy/log data in standalone applications
- BenchVue DAQ with enhanced time/frequency domain measurement

More Information: www.keysight.com/find/DAQ970A

DAQ970A and DAQ973A Key Capabilities

Features	Description
Types of measurements	Temperature, voltage, current, resistance, frequency, diode and capacitance, direct strain, and bridge strain
Digital input/output	Up to 48 bits
Analog output	-10 V to +10 V, 20 mA
Multiplexing	Maximum 120 (1-wire), 60 (2-wire) channels
Matrix switching	Maximum 96 cross points
General purpose	Maximum 60 switches
RF multiplexing	Maximum 24 channels, 2 GHz
Simultaneous sampling	Maximum 12 channels, up to 800 kSa/s, 24-bit resolution
Interface	Graphic web, USB front/rear, LAN/LXI, GPIB (only for DAQ973A)



Rear image of the DAQ973A mainframe with USB, LAN, and GPIB interfaces



DAQ970A and DAQ973A plug-in modules

Part	Description
DAQ970A	DAQ mainframe with USB and LAN interfaces
DAQ973A	DAQ mainframe with USB, LAN, and GPIB interfaces
DAQM900A	20-channel solid-state multiplexer
DAQM901A	20-channel armature multiplexer + 2 current channels
DAQM902A	16-channel reed multiplexer
DAQM903A	20-channel actuator/GP switch
DAQM904A	4 x 8 matrix
DAQM905A	Dual 4-channel 50 Ω RF mux
DAQM907A	Multifunction module
DAQM908A	40-channel armature multiplexer
DAQM909A	4-channel 24-bit simultaneous sampling digitizer
DAQM910A	20-Channel General Purpose, Low Voltage Multiplexer

DAQ970A / DAQ973A accessories

Part	Description
DAQA190A	Rack mount kit
DAQA191A	2U dual flange kit
DAQA194A	Dual lock link kit
34307A	10-pack J-type thermocouples
34308A	5-pack 10 kΩ thermistors

Keysight enables innovators to push the boundaries of engineering by quickly solving design, emulation, and test challenges to create the best product experiences. Start your innovation journey at www.keysight.com.

This information is subject to change without notice. © Keysight Technologies, 2018 – 2025,
Published in USA, February 6, 2025, 5992-3177.EN