

RF and Microwave Amplifiers



Microwave broadband signal amplification

- Broadband performance up to 50 GHz, replacing several narrow band amplifiers, simplifies test setup and optimizes the operating range of your test systems
- Excellent noise figure and high gain, significantly reduces overall test system noise figure
- High output power, boosts available power for measurements

Introduction

The Keysight Technologies, Inc. 83006/017/018/020 /050 /051A and N4985A test system amplifiers offer ultra broadband performance up to 50 GHz. With excellent noise figure relative to their broad bandwidth and high gain, these products can be used to significantly reduce test system noise figure. By replacing several amplifiers with a single broadband product, test setups can be greatly simplified. You can place this amplification power where you need it by using remotely-locatable Keysight power supplies. In addition, the Keysight 87415A provides octave band performance from 2 to 8 GHz.

The Keysight 87405B/C and N4985A-S30/S50 low noise preamplifiers provide exceptional gain and flatness. The 87405B/C preamplifiers are very portable and come with a convenient probe-power bias connection which eliminates the need for an additional DC power supply, making them an ideal front-end preamplifier for a variety of Keysight instruments.

The N4985A-S30/50 system amplifiers are a high-performance broadband amplifier featuring baseband RF (> 100 kHz) through millimeter wave (> 30 GHz) frequency coverage. These amplifiers are designed to be a multi-use laboratory RF amplifier as a gain block for frequency domain applications, or as a time domain pulse amplifier. Its small size and versatile performance make it an excellent choice for general purpose gain block with moderate power output in a single package, potentially replacing two or three narrower-band amplifiers.



N4985A system amplifier



87405B/C preamplifier



System amplifiers

What Selection Criteria Do I Consider?

Today's engineers are constantly seeking for amplifiers of exceptional gain and power performance over a broad bandwidth.

There exists a very large number of potential electrical specifications that can be applied to a microwave power amplifier selection. These elements are defined by the following characteristics:

Frequency range

RF and microwave applications range in frequency from 100 MHz for semiconductor to 60 GHz for satellite communications. Broadband accessories increase test system flexibility by extending frequency coverage. However, frequency is always application dependent and a broad operating frequency may need to be sacrificed to meet other critical parameters.

Noise figure

Noise figure is the primary specification for a typical microwave power amplifier selection. The noise figure is defined as the ratio of the signal-to-noise power ratio at the input to the signal-to-noise power ratio at the output. The noise factor is thus the ratio of actual output noise to that which would remain if the device itself did not introduce noise, or the ratio of input SNR to output SNR.

Low noise amplifiers are always preferred as the noise figure of the system is dominated by the noise figure of the preamplifier. By adding a preamplifier to noise figure measurement systems, the total system noise figure can also be reduced.

$$F_{new} = F_{pa} + \frac{F_{sys} - 1}{F_{pa}}$$

Where F and G are noise figure and preamplifier gain, both in linear terms.

$$NF_{sys} = 10 \log (F_{sys}) \text{ in dB}$$

For systems with a single preamplifier, where the gain of the preamplifier is greater than or equal to the spectrum analyzer noise figure, the system noise figure is approximately equal to the noise figure of the preamplifier.

Output power (P_{sat} & P_{1dB})

Among the key specifications for microwave amplifiers are their power output specifications. Output power at P_{sat} refers to the saturated output power, or maximum output power from the amplifier. This is the output power where the P_{in}/P_{out} curve slope goes to zero. Output power at P_{1dB} refers to the output power during 1 dB compression point. Unlike the gain specification, implicitly it is assumed that the specification is at an operating point where the amplifier is exhibiting some degree of non-linear behavior. With an inherently broadband amplifier, power output as a function of power input does not vary discontinuously as a function of frequency. Typically, a wideband microwave power amplifier that could deliver in excess of several watts required a solution where numerous narrowband amplifiers were either multiplexed or switched; often introducing undesired issues, such as power curve discontinuities, at frequency cross-over points.

Gain

Gain usually is specified within the context of power output. Often, if no context for power output is given, then this is assumed to be small signal gain. Conditions for small signals at the input and output are usually easy to reproduce and verify, whereas gain and gain flatness can vary significantly when an amplifier approaches compression. Gain flatness for an amplifier with a significant frequency range is often specified over subsets of the entire frequency range. Gain and gain flatness typically include an implicit assumption that the reverse gain from the output to the input is negligible; i.e. the amplifier is unilateral.

Typically, gain flatness could only be achieved over narrow bandwidths with classic reactive matching techniques, such as those used for internally matched devices. Attempts to broaden the gain bandwidth of a high-power microwave amplifier requires trade-offs with resistive matching, or feedback techniques that take power output. The spatially combined topology overcomes these limitations.

Input and output return loss (VSWR)


The standing wave ratio, often referred to interchangeably as VSWR, is the result of wave interference. Peaks and troughs in a given field pattern remain in a static position as long as the sources of interference do not change with respect to each other. Return loss, expressed in dB, is a measure of voltage standing wave ratio (VSWR). Return loss is caused by impedance mismatch between circuits. At microwave frequencies, the material properties as well as the dimensions of a network element play a significant role in determining the impedance match or mismatch caused by the distributed effect. Keysight amplifiers guarantee excellent return loss performance by incorporating appropriate matching circuits to ensure optimum power transfer through the amplifier and the entire network.

Isolation

Isolation is the degree of attenuation from an unwanted signal detected at the port of interest. Isolation becomes more important at higher frequencies. High isolation reduces the influence of signals from other channels, sustains the integrity of the measured signal, and reduces system measurement uncertainties.

Visit: www.keysight.com/find/amplifiers

RF & Microwave Amplifiers Selection Guide



RF & Microwave Amplifiers Specification Table

| Model | Frequency range (GHz) | Noise figure (dB) (typical) | Output power at P _{sat} (dBm) | Output power at P _{1dB} (dBm) | Gain (dB) (min) | VSWR | Isolation (dB) | Bias (nom) | RF connectors (input/output) | Recommended power supply |
|--------------------------|-----------------------|--|--|--|--|------|-----------------|-----------------------------------|------------------------------|--|
| Preamplifiers | | | | | | | | | | |
| 87405B | 0.01 to 4 GHz | 3.5 at 4 GHz | 8 at 4 GHz | 8 at 4 GHz | 22 | 1.9 | 40 | +15 V at 105 mA | Type N (m.f) | 87422A |
| U7227A ⁴ | 0.01 to 4 GHz | 5.5 @ 100 MHz 5 @ 4 GHz | Refer data sheet | Refer data sheet | 10 to 100 MHz: 16 100 MHz to 4 GHz: > 0.5F + 17 | 1.81 | Refer datasheet | 'USB + 5 Vdc at 360 mA | 3.5 mm (m) | Do not require power supply. USB powered |
| 87405C | 0.1 to 18 GHz | 3.5 at 4 GHz 3.8 at 18 GHz | 17 at 18 GHz | 15 at 4 GHz 14 at 18 GHz | 25 | 1.92 | 50 | +15 V at 140 mA -15 V at 3 mA | Type N (m.f) | 87422A |
| U7227C ⁴ | 0.1 to 26.5 GHz | 6 @ 4 GHz 5 @ 6 GHz 4 @ 18 GHz 5 @ 26.5 GHz | Refer data sheet | Refer data sheet | 100 MHz to 26.5 GHz: 16.1 + 0.26F | 2.07 | Refer datasheet | 'USB + 5 Vdc at 400 mA | 3.5 mm (m) | Do not require power supply. USB powered |
| N4985A -S30 ¹ | 0.00001 to 30 GHz | 5 at 2 to 30 GHz | 22 at 26 GHz | N/A | 30 at 26 GHz | 1.92 | N/A | AC power supply included | 2.92 mm (f) | Included |
| U7227F ⁴ | 2 to 50 GHz | 510 @ 4 GHz 8 @ 40 GHz 9 @ 44 GHz 10 @ 50 GHz | Refer data sheet | Refer data sheet | 2 to 50 GHz: 16.5 + 0.23F | 2.27 | Refer datasheet | 'USB + 5 Vdc at 460 mA | 2.4 mm (m) | Do not require power supply. USB powered |
| N4985A -S50 ² | 0.00001 to 50 GHz | 5 at 2 to 30 GHz 6 at 20 to 40 GHz | 17 at 50 GHz | N/A | 27 at 45 GHz | 2.32 | N/A | AC power supply included | 2.4 mm (f) | Included |
| System amplifiers | | | | | | | | | | |
| 87415A | 2 to 8 GHz | 13 at 8 GHz | 26 at 8 GHz | 23 at 8 GHz | 25 | 3 | 60 | +12 V at 900 mA | SMA (f) | 87421A |
| 83006A | 0.01 to 26.5 GHz | 13 at 0.1 GHz 8 at 18 GHz 13 at 26.5 GHz | 18 at 10 GHz 16 at 20 GHz 14 at 26.5 GHz | 13 at 20 GHz 10 at 26.5 GHz | 20 | 3.2 | 65 | +12 V at 450 mA -12 V at 50 mA | 3.5 mm (f) | 87421A or 87422A |
| 83017A ³ | 0.5 to 26.5 GHz | 8 at 20 GHz 13 at 26.5 GHz | 20 at 20 GHz 15 at 26.5 GHz | 18 at 20 GHz 13 at 26.5 GHz | 25 | 2.6 | 65 | +12 V at 700 mA -12 V at 50 mA | 3.5 mm (f) | 87421A or 87422A |
| 83018A ³ | 2 to 26.5 GHz | 10 at 20 GHz 13 at 26.5 GHz | 24 at 20 GHz 21 at 26.5 GHz | 22 at 20 GHz 17 at 26.5 GHz | 27 dB at 20 GHz 23 dB at 26.5 GHz | 2.2 | 55 | +12 V at 2 A -12 V at 50 mA | 3.5 mm (f) | 87421A or 87422A |
| 83020A ³ | 2 to 26.5 GHz | 10 at 20 GHz 13 at 26.5 GHz | 30 at 20 GHz 25 at 26.5 GHz | 27 at 20 GHz 23 at 26.5 GHz | 30 dB at 20 GHz 27 dB at 26.5 GHz | 2.2 | 55 | +15 V at 3.2 A -15 V at 50 mA | 3.5 mm (f) | 87422A |
| N4985A -P15 | 0.01 to 50 GHz | 12 at 50 GHz | 25 at 26.5 GHz 20 at 50 GHz | 23 at 26.5 GHz 17 at 50 GHz | 22 at 50 GHz | 3.01 | 50 | AC power supply included | 2.4 mm (f) | Included |
| 83050A | 2 to 50 GHz | 6 at 26.5 GHz 10 at 50 GHz | 20 at 40 GHz 17 at 50 GHz | 15 at 40 GHz 13 at 50 GHz | 21 | 2.1 | 50 | +12 V at 830 mA -12 V at 50 mA | 2.4 mm (f) | 87421A or 87422A |
| N4985A -P25 | 2 to 50 GHz | 12 at 50 GHz | 25 at 26.5 GHz 20 at 50 GHz | 23 at 26.5 GHz 17 at 50 GHz | 22 at 50 GHz | 3.01 | 50 | AC power supply included | 2.4 mm (f) | Included |
| 83051A | 0.045 to 50 GHz | 12 at 2 GHz 6 at 26.5 GHz 10 at 50 GHz | 12 at 45 GHz 10 at 50 GHz | 8 at 45 GHz 6 at 50 GHz | 23 | 2.2 | 50 | +12 V at 425 mA -12 V at 50 mA | 2.4 mm (f) | 87421A or 87422A |

1. Option OA3 is available for optical application tuning.
2. Option OA5 is available for optical application tuning.
3. 83017A, 83018A and 83020A include internal directional detectors with BNC (f), DC connectors for external leveling applications.
4. U7227A/C/F designed to provide positive gain slope for gain compensation when used with CXA/EXA/MXA/PXA X-series Signal Analyzers. It provide automatic gain correction value with temperature compensation and transfer of calibration data (noise figure and S-parameters) through USB plug and play features for improved noise figure measurement.

Visit: www.keysight.com/find/amplifiers

Application Examples

Adding preamplifiers to measurement systems as shown in Figure 2 can improve sensitivity and reduce the noise floor when measuring low-level signals. By adding a preamplifier to noise figure measurement systems, the total system noise figure can also be reduced. The noise figure of the system is dominated by the noise figure of the preamplifier. For systems with a single preamplifier, where the gain of the preamplifier is greater than or equal to the spectrum analyzer noise figure, the system noise figure is approximately equal to the noise figure of the preamplifier.




Figure 1. Low level signal measurement test setup




Figure 2. Preamplifier with spectrum analyzer setup

System amplifiers

The small envelope size of the Keysight family of microwave system amplifiers make them ideal for automated test and benchtop applications, offering the flexibility to place power where you need it.

Boost source output power

Increase output power from microwave sources to increase test system dynamic range. Drive high input power devices such as TWTs, mixers, power amps, or optical modulators. Drive test devices into compression for device characterization.



Recover systematic losses

The microwave system amplifiers help solve the power loss from connectors, cables, switches, and signal routing components which consume valuable source power. Long transmission paths, common in antenna applications, are particularly susceptible to such losses.


Level source power

By using feedback to an external source ALC input, system designers can level output power at the test port, negating the effects of postsweeper reflections and losses. Simply route the directional detector output to the source external ALC input connector. The figures at right show typical results.

The 83017A, 83018A, and 83020A feature an integral directional detector to supply feedback. To level an 83006A amplifier, use the 0.01 to 26.5 GHz 83036C directional detector or the 1 to 26.5 GHz 87300C coupler with an 8474C detector.



Max Output Power of 83020A amplifier



Gain of 83051A amplifier

Improve system sensitivity


Keysight preamplifiers increase the system sensitivity of spectrum analyzers which have high noise figure. Add a preamplifier to noise figure measurement systems to significantly lower system noise figure. The table below shows typical system noise figure reduction achievable with these amplifiers. Note that the reduced system noise figure is dominated by the preamplifier noise figure. See *Noise Figure Measurement Accuracy – The Y-Factor Method Application Note 57-2*, literature number 5952-3706E.

Benchtop gain block

Benchtop microwave design tasks often require amplification to measure low level output characteristics, improve system dynamic range, perform saturation tests, or boost power levels. The Keysight family of system amplifiers offers small size and immediate, off-the-shelf solutions to microwave design, production, or test engineers.

Pulse parameter measurements

Fast rise time and multi-octave bandwidth make these amplifiers attractive for fast pulse parameter measurements. The 0.01, 0.5, and 2 GHz cutoff frequencies make them more useful for RF or impulse measurements with low duration times.



Typical noise figure improvement

| Amp model | Freq (GHz) | Max NF (dB) | Min gain (dB) | System noise figure (F_{sys}) without preamp (dB) | | | | | | |
|-----------|------------|-------------|---------------|---|------|------|------|------|------|------|
| | | | | 13 | 15 | 18 | 20 | 23 | 25 | 30 |
| 83006A | 0.01–0.2 | 13 | 20 | — | 13.1 | 13.1 | 13.2 | 13.4 | 13.6 | 14.8 |
| | 0.2–18 | 8 | | 8.1 | 8.2 | 8.4 | 8.6 | 9.2 | 9.8 | 12.1 |
| | 18–26.5 | 13 | | — | 13.1 | 13.1 | 13.2 | 13.4 | 13.6 | 14.8 |
| 83017A | 0.5–18 | 8 | 25 | 8.0 | 8.1 | 8.1 | 8.2 | 8.4 | 8.6 | 9.8 |
| | 18–26.5 | 13 | | — | 13.0 | 13.0 | 13.1 | 13.1 | 13.2 | 13.6 |
| 83018A | 1–2 | 10 | 23 | 10.0 | 10.1 | 10.1 | 10.2 | 10.4 | 10.6 | 11.8 |
| | 2–20 | 10 | 27 | 10.0 | 10.0 | 10.1 | 10.1 | 10.2 | 10.3 | 10.8 |
| | 20–26.5 | 13 | 23 | — | 13.0 | 13.1 | 13.1 | 13.2 | 13.3 | 14.0 |
| 83020A | 1–20 | 10 | 30 | 10.0 | 10.0 | 10.0 | 10.0 | 10.1 | 10.1 | 10.4 |
| | 20–26.5 | 13 | 27 | — | 13.0 | 13.1 | 13.1 | 13.1 | 13.1 | 13.4 |
| 83050A | 2–26.5 | 6 | 21 | 6.1 | 6.2 | 6.3 | 6.5 | 7.0 | 7.5 | 9.5 |
| | 26.5–50 | 10 | | 10.0 | 10.1 | 10.1 | 10.2 | 10.4 | 10.6 | 11.8 |
| 83051A | 0.045–2 | 12 | 23 | 12.0 | 12.0 | 12.1 | 12.1 | 12.3 | 12.4 | 13.2 |
| | 2–26.5 | 6 | | 6.1 | 6.2 | 6.3 | 6.5 | 7.0 | 7.5 | 9.5 |
| | 26.5–50 | 10 | | 10.0 | 10.1 | 10.1 | 10.2 | 10.4 | 10.6 | 11.8 |

Power Supply

With excellent noise figure relative to their broad bandwidth and high gain, Keysight system amplifiers significantly improve system noise figure and dynamic range. These products come equipped with a low profile heat sink, an integral mounting bracket, and a two-meter DC power supply cable. Thermal and power supply design allows fast, easy integration into most measurement systems.

The Keysight 83006/017/018/020/050/051A amplifiers are supplied with a 2-meter bias cable that has a connector on one end and bare wires on the other. This bias cable can be used to interface with a power supply provided by the user. Or, for a complete solution, Keysight offers the 87421

/422A remotely locatable power supplies. The 87421A power supply is furnished with one 2-meter cable (87422A, two 2-meter cables) for direct connection to a Keysight amplifier as shown in the amplifier power cable cross reference table below.

The N4985A system amplifier is a series of high-performance broadband amplifiers with excellent power and gain from 0.00001 to 50 GHz. The amplifier is designed to be easily used in lab and test applications. It features an integrated cooling and temperature-referenced power detector outputs, and is completely self-contained with a standard AC power supply.

Power cable cross reference ¹

| Model | Cable part number ² (supplied with amplifier) | Power supply recommended | Cable part number ³ (supplied with power supply) |
|---------------------|---|--------------------------|--|
| 83006A | 83006-60004 | 87421A | 83006-60005 |
| 83017A | 83006-60004 | 87421A | 83006-60005 |
| 83018A | 83006-60004 | 87421A | 83006-60005 |
| 83050A | 83006-60004 | 87421A | 83006-60005 |
| 83051A | 83006-60004 | 87421A | 83006-60005 |
| 87415A | 83006-60004 | 87421A | 83006-60005 |
| 83020A | 83020-60004 | 87422A ² | 87422-60001 83006-60005 |
| 87405B | Integral cable | Spectrum analyzer | |
| 87405C ⁴ | | | |
| 87405C-101 | 87405-20006 | E3631A | No cable supplied |
| 87405C-102 | 87405-20007 | Spectrum analyzer | No cable supplied |
| 87405C-103 | 87405-20010 | 87422A | 87422-60001 83006-60005 |

1. See outline drawings for connector types
2. For use with available power supply
3. For use with power supply for direct connection
4. Must order one of cable options

Power supply specifications

| Model | AC input voltage | DC output (nom) | Output power | Size (H, W, D) |
|---------------------|----------------------------|---|--------------|--------------------------------------|
| 87421A | 100 to 240 VAC 50/60 Hz | +12 V at 2.0 A, -12 V at 200 mA | 25 W max | 57, 114, 176 mm 2.3, 4.5, 6.9 in |
| 87422A ¹ | 100 to 240 VAC 50/60 Hz | +15 V at 3.3 A, -15 V at 50 mA +12 V at 2.0 A, -12 V at 200 mA | 70 W max | 86, 202, 276 mm 3.4, 8.0, 10.9 in |

1. The ± 15 V output is designed to power the Keysight 83020A; the ± 12 V output can be used to power an additional amplifier.

Mechanical Dimensions

| Net Weights | |
|-------------|---------------------|
| Model | Net weight |
| 83006A | 0.64 kg (1.4 lbs) |
| 83017A | 0.64 kg (1.4 lbs) |
| 83050A | 0.64 kg (1.4 lbs) |
| 83051A | 0.64 kg (1.4 lbs) |
| 83018A | 1.8 kg (4 lbs) |
| 83020A | 3.9 kg (8.5 lbs) |
| 87415A | 0.64 kg (1.4 lbs) |
| 87405B | 0.23 kg (0.5 lbs) |
| 87405C | 0.22 kg (0.485 lbs) |
| N4985A-S30 | 0.26 kg (0.57 lbs) |
| N4985A-S50 | 0.26 kg (0.57 lbs) |
| N4985A-P15 | 1.03 kg (2.27 lbs) |
| N4985A-P25 | 1.03 kg (2.27 lbs) |
| U7227A | 0.38 kg (0.84 lbs) |
| U7227C | 0.38 kg (0.84 lbs) |
| U7227F | 0.38 kg (0.84 lbs) |

Ordering Information

| Model | Notes |
|------------|--|
| 87405B | Preamplifier, 0.01 to 4 GHz, 22 dB gain, type-N (m) output to type-N (f) |
| 87405B-001 | Power probe connector to banana plug |
| 87405C | Preamplifier, 0.1 to 18 GHz, type N(M) output to type N(F) |
| 87405C-101 | Cable assembly – banana plug |
| 87405C-102 | Cable assembly – power probe cable |
| 87405C-103 | Cable assembly – 15 pin bias cable |
| 87415A | 2 to 8 GHz remote system amplifier |
| 83006A | Amplifier, 0.01 to 26.5 GHz, 20 dB gain |
| 83017A | Amplifier, 0.5 to 26.5 GHz; 25 dB gain |
| 83018A | Microwave system amplifier, 2 to 26 GHz, 22 dBm |
| 83020A | Power amplifier; 2 to 26.5 GHz, 27 dB gain |
| 83050A | Amplifier; 2 to 50 GHz, 20 dBm at 40 GHz |
| 83051A | Preamplifier; 0.045 to 50 GHz, 23 dB gain |
| N4985A | System amplifiers |
| N4985A-P15 | 10 MHz to 50 GHz |
| N4985A-P25 | 2 to 50 GHz |
| N4985A-S30 | 100 kHz to 30 GHz |
| N4985A-S50 | 100 kHz to 50 GHz |
| N4985A-OA3 | Optical application tuning for Option S30 |
| N4985A-OA5 | Optical application tuning for Option S50 |
| U7227A | 10 MHz to 4 GHz USB Preamplifier |
| U7227C | 100 MHz to 26.5 GHz USB Preamplifier |
| U7227F | 2 to 50 GHz USB Preamplifier |

Related Literature

Preamplifiers

87405B (<http://literature.cdn.keysight.com/litweb/pdf/5988-8452EN.pdf>)

87405C (<http://literature.cdn.keysight.com/litweb/pdf/5989-5743EN.pdf>)

N4985A-S30 (<http://literature.cdn.keysight.com/litweb/pdf/5991-0713EN.pdf>)

N4985A-S50 (<http://literature.cdn.keysight.com/litweb/pdf/5991-0713EN.pdf>)

U7227A/C/F (<http://literature.cdn.keysight.com/litweb/pdf/5991-4246EN.pdf>)

System amplifiers

87415A (<http://literature.cdn.keysight.com/litweb/pdf/5091-1358E.pdf>)

83006A (<http://literature.cdn.keysight.com/litweb/pdf/5963-5110E.pdf>)

83017A (<http://literature.cdn.keysight.com/litweb/pdf/5963-5110E.pdf>)

83018A (<http://literature.cdn.keysight.com/litweb/pdf/5963-5110E.pdf>)

83020A (<http://literature.cdn.keysight.com/litweb/pdf/5963-5110E.pdf>)

N4985A-P15 (<http://literature.cdn.keysight.com/litweb/pdf/5991-0713EN.pdf>)

83050A (<http://literature.cdn.keysight.com/litweb/pdf/5963-5110E.pdf>)

N4985A-P25 (<http://literature.cdn.keysight.com/litweb/pdf/5991-0713EN.pdf>)

83051A (<http://literature.cdn.keysight.com/litweb/pdf/5963-5110E.pdf>)

For more on Keysight amplifiers and ordering information see the *Keysight RF and Microwave Amplifiers*, Brochure, literature number 5989-6949EN

To order our complimentary Keysight RF & Microwave Test Accessories Catalog 2014
www.keysight.com/find/mtacatalog

Learn more at: www.keysight.com

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at:
www.keysight.com/find/contactus

