

Keysight N9310A

An Effective, Professional Field Installation and Maintenance Tool

Minimize Your Operating Cost

In the field installation and maintenance market, the advantage goes to the equipment with a basic test suite at the lowest price. The Keysight Technologies, Inc. N9310A provides such a solution for regular base-station, RX-level calibration.

Built to Perform

General purpose base-station RX-level calibration does not require an elaborate and extensive suite of tests. All that's needed from a signal generator are stable and accurate CW signals. The N9310A is the perfect solution, providing, at a competitive price, the essential tests:

- Frequency: 9 kHz ~ 3 GHz
- Stability: < ± 1 ppm/year aging rate
- Amplitude: -127 dBm ~ +13 dBm,
- Accuracy: < ± 1 dB
- Switching speed: < 10 ms

Easy to Use

- 6.5" high-resolution color LCD provides easy-to read display
- Easily-understood hard and soft keys for essential functions make measurements easy and fast
- Multi-language user interface for worldwide usability
- Customizable frequency step and editable list sweep function improves efficiency

Additional Features

- Programmable
- SCPI compatible
- USB connectivity for remote control
- Compact and lightweight




Figure 1. System connection

RX Level Calibration Example

1. Connect the calibration system as shown in Figure 1.
2. Run calibration software, toggling base station to RX level calibration status. See Figure 2.
3. Configure the N9310A and output the first signal to the first calibration channel.
4. To calibrate the second channel, set frequency increment to 1.6 MHz. Rotate the knob to output the second CW signal, offset 1.6 MHz from the first one. Keep rotating the knob to output CW signals with a 1.6 MHz offset.
5. Save the calibrated data and exit RX-level calibration mode.




Figure 2. Base Station RX Level Calibration Software



Recommended Equipment

- N9310A 9 kHz~3 GHz RF Signal Generator
- Option N9310A-1HB Handle and Bumper
- Option N9310A-1TC Hard Transit Case
- Attenuator 50 W/30 dB

Tip: Please consider the RF cable loss and the effect of the attenuator when using the N9310A.

Reference

Base station RX level calibration requirements (based on Motorola's Mcell and Horizon series base station)

- Frequency
- CW level: -65.2 dBm

For more information, please visit www.keysight.com/find/n9310a

Frequency	Point
881.001 MHz ~ 914.601 MHz	22
880.8052 MHz ~ 914.4052 MHz	22
1710.8052 MHz ~ 1784.4052 MHz	47
1711.001 MHz ~ 1784.401 MHz	47



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
(BP-09-23-14)