

Keysight Technologies

Control Existing Parameter Analyzers
from a PC Using Desktop EasyEXPERT



Introduction

Keysight Technologies, Inc.'s Desktop EasyEXPERT software for the B1500A now supports the 4155B/C and 4156B/C Semiconductor Parameter Analyzers too. The software can be downloaded from the Keysight web site at no charge. This makes it easy to enjoy all of the benefits of PC based instrument control on your existing parameter analyzer.

What is Desktop EasyEXPERT software?



Desktop EasyEXPERT is the same software that is built-in to the PC-based Keysight B1500A Semiconductor Device Analyzer, except that it runs on a stand-alone PC. Just like standard EasyEXPERT, Desktop EasyEXPERT supports all aspects of parametric test, from basic manual measurements to test automation across a wafer in conjunction with a semiautomatic wafer prober.

Features and benefits

- **Large application test library**
Desktop EasyEXPERT comes with more than 150 application tests conveniently organized by device type, application, and technology. Many of these application tests will run on the 4155/4156 without modification, and you can easily edit and customize the furnished application tests to fit your specific needs.
- **Offline capability**
Desktop EasyEXPERT can be run in either online or offline mode. In the offline mode you can perform tasks such as analyzing data and creating new application tests. This frees up your existing analyzer from being needed for development work and enables you to use it for its primary purpose: making measurements.

- **GUI-based classic test mode**
Desktop EasyEXPERT offers a classic test mode that maintains the look, feel, and terminology of the 4155/4156 user interface. In addition, it improves the 4155/4156 user interface by taking full advantage of Microsoft Windows GUI features.

- **Easy test sequencing**
A GUI-based Quick Test mode enables you to perform test sequencing without programming. You can select, copy, rearrange and cut-and-paste any application tests with a few simple mouse clicks. Once you have selected and arranged your tests, simply click on the measurement button to begin running an automated test sequence.




– Prober control

All popular semiautomatic wafer probers are supported by Desktop EasyEXPERT. You can define wafer, die, and module information for probing across an entire wafer. You can also combine wafer prober control with either Quick Test mode or an application test based test sequence to perform multiple testing on various devices across the wafer.

– Automatic data export

The Desktop EasyEXPERT has the ability to automatically export measurement data in real time, in a variety of formats. You can save data to any drive connected to the PC. If you wish, you can export data to a network drive and view test results on your desktop PC as your instruments are performing the testing in your lab.



System Requirements for 415x

The following are the minimum requirement for executing Desktop EasyEXPERT.

Processor: Intel Celeron 2 GHz

Memory: 512 Megabytes DDR266

Display: XGA 1024x768
(SXGA 1280x1024 recommended)

HDD: 1 GB free space on the C drive,
10 GB (30 GB recommended) free
space on a drive for test setup/result
data storage.

GPIO I/F (for online mode):

Keysight 82350B or 82357A/B

GPIO interface

OS: Windows XP Professional SP2
Software:

- Microsoft .NET Framework Ver 1.1 Redistributable Package
- Microsoft .NET Framework 1.1 SP1
- Keysight IO Libraries Suite 14.0 (for online mode)
- Keysight T&M Programmers Toolkit Redistributable Package 1.1 (Programmers Toolkit revision 2.0 is not supported.)

Supported Instruments:

4155B, 4156B, 4155C, and 4156C
(4155A and 4156A are not supported)

Supported 415x Functionality:

Sweep mode (Sampling, Stress, and
QSCV modes are not supported)

Setup Converter Tool

In addition to Desktop EasyEXPERT, Keysight supplies a free setup converter tool that runs on any Windows-based PC. This tool can convert 4155 and 4156 measurement setup files (files of type ".MES") into equivalent Desktop EasyEXPERT classic test mode setup files.

How to Get

The latest versions of Desktop EasyEXPERT and the setup converter tool can be downloaded from:

www.keysight.com/see/B1500A.

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at:
www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
(BP-9-7-17)

DEKRA Certified
ISO 9001 Quality Management System

www.keysight.com/go/quality

Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System



This information is subject to change without notice.
© Keysight Technologies, 2017
Published in USA, December 1, 2017
5989-6632EN
www.keysight.com