

Keysight Technologies

M9216A PXI 32-Channel High Voltage Data Acquisition Module

Product Fact Sheet

Industries and Applications

- Automotive
- Electronics test

Product Description


The M9216A is a high voltage data acquisition module that allows simultaneous measurement of eight channels of positive voltages ranging from 1 mV to 100 V. Each channel in the module comes with concurrent 5 V and 100 V measurement ranges, with every channel capable of acquiring digital signals that fluctuate between very low and very high voltage levels without the need for switching ranges and doing separate measurements.

The M9216A module also comes with a built-in 32 to eight multiplexer enabling 32 measurement ports to be connected to the eight acquisition channels expanding it to a full 32-channel acquisition module. Alternatively, these channels can also be routed via an auxiliary output connector for additional measurements without requiring extra multiplexers or pin matrix cards.

The M9216A is capable of doing fast parallel voltage level measurements with guaranteed accuracy, which is ideal for the automotive industry since most automotive applications do not require negative voltage measurements. The M9216A's 16-bit ADC is fully used for positive voltages, giving it better resolution, hence better accuracy.

Models

M9216A	32-channel high voltage data acquisition module
--------	---



Main Features and Benefits

Product features	Your benefit
Large input range with dual concurrent measurement range for each channel	Enables voltage level acquisition to be done for very low and very high voltages without the need for switching ranges
Built-in 32 to 8 multiplexer	Expanding to 32-channel high speed voltage acquisition capability
Auxiliary outputs from the acquisition channels	Enables additional measurements to be done without requiring external multiplexers and pin matrix cards

Specifications and Characteristics

Hardware	
Size	2 slots, 3 U
Resolution	16 bit
Accuracy	Zero offset: 5 V range – 200 μ V, 100 V range – 1 mV Gain (% of reading): 5 V range – 0.05%, 100 V range – 0.05% Noise @ 3 sigma: 5 V range – 200 μ V, 100 V range – 2 mV
Software	
Supported operating systems	Windows XP (32-bit) Windows Vista (32-bit/64-bit) Windows 7 (32-bit/64-bit)
Included device drivers	IVI-COM, IVI-C, LabVIEW G
Included GUI	Soft front panel
Chassis slot compatibility: cPCI(J1, J2), PXI-1, PXIe Hybrid	

Software Applications

The M9216A high voltage data acquisition module is supplied with a comprehensive portfolio of module drivers, documentation, examples, and software tools to help you quickly develop test systems with your software platform of choice. Support includes Microsoft development environments like C/C++, C#, or VB.NET, LabVIEW and LabWindows/CVI software platforms from National Instruments as well as MATLAB from The MathWorks.

To help you get started and complete complex tasks quickly, the module software support provides context-sensitive help, complete documentation and code examples that allow a quick module set up and basic acquisition functionalities. These code examples can be easily modified, so that the card can be quickly integrated into a measurement system. In addition, the M9216A includes a soft front panel graphical interface. This simple software application can be used to control, verify the functionality and explore the capabilities of the Keysight Technologies, Inc. data acquisition module.


Ordering Information

Model	Description
M9216A	M9216A PXI high voltage data acquisition module, 32-channel, 250KS/S, 16-BIT, 100 V input

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

http://www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES
Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

PICMG and the PICMG logo, CompactPCI and the CompactPCI logo, AdvancedT-CA and the AdvancedTCA logo are US registered trademarks of the PCI Industrial Computers Manufacturers Group.

"PCIe" and "PCI EXPRESS" are registered trademarks and/or service marks of PC-SIG.

Microsoft, Windows, Visual Studio, Visual C++, Visual C#, and Visual Basic are either registered trademark or trademarks of Microsoft Corporation in the United States and/or other countries.

www.keysight.com/find/modular

www.keysight.com/find/m9216a

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:

www.keysight.com/find/contactus
(BP-9-7-17)

DEKRA Certified
ISO 9001 Quality Management System

www.keysight.com/go/quality
Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System



This information is subject to change without notice.
© Keysight Technologies, 2017
Published in USA, December 1, 2017
5990-7587EN
www.keysight.com