

M8091UACA

Keysight Receiver Conformance Test Software for UALink 200G

Introduction

The M8091UACA Keysight receiver conformance test software for UALink 200G enables accurate and repeatable receiver test procedures following the UA Link 200G (IEEE P802.3dj/D2.0) recommendations to ensure interoperability between datacom interfaces with a lane rate of 200 Gbps. This solution covers the backplane (KR), and twinaxial copper cable (CR) interfaces.



Key Features

- Validation of digital receiver designs running at 106.25Gbaud PAM4 lane rate following the test procedure defined in IEEE P802.3dj/D2.0 *

Clause 178 200GBASE-KR1

- 178.9.3.3 Receiver amplitude tolerance
- 178.9.3.4 Receiver interference tolerance
- 178.9.3.5 Receiver jitter tolerance

Clause 179 200GBASE-CR1

- 179.9.5.2 Receiver amplitude tolerance
 - 179.9.5.3 Receiver interference tolerance
 - 179.9.5.4 Receiver jitter tolerance
-
- Guided setup, automated stressed signal calibration, and pre-conformance measurement
 - HTML test report
 - Remote control
 - Choose between node-locked, transportable, network, or USB-dongle perpetual license

* Note:

The M8091UACA electrical receiver conformance test application does **not support** *Auto-Negotiation* (Clause 73) or *Inter-sublayer Link Training* (Annex 178B). Instead, an alternative method is employed to optimise the pattern generator's de-emphasis coefficients prior to testing.

As the Device Under Test (DUT) may lack the capability to return error statistics required for estimating the *block error ratio* (Clause 174A.8), the compliance application reports the **raw Bit Error Rate (BER)** by default. If the DUT or an external error detector can provide block error ratio data, the BER target may be adjusted accordingly.

Description

The M8091UACA electrical receiver conformance test application is designed to assist and simplify the stressed signal calibration used for testing the inputs of IEEE P802.3dj/D2.0 for Chip-to-Chip (C2C) and Chip-to-Module (C2M), backplane (KR), and twinaxial copper cable (CR) electrical interfaces using a Keysight M8050A 120Gbd High-Performance BERT combined with a Keysight Infiniium UXR real-time oscilloscope. It reduces user interaction to a minimum and performs all required calibration routines and compliance testing automatically by remotely controlling all required instruments. At the same time, it offers flexibility to test different scenarios within or beyond the standard recommendations.

The test application utilizes the same framework as other Keysight conformance test applications, thereby reducing training time and offering functionalities such as remote control, scripting, and automated PDF or HTML-based test report generation. The user is guided by means of diagrams as well as text to minimize errors. Results of the individual calibration steps and tests are presented in tabular form as well as graphical form, where appropriate. Calibrations and test results can be stored in projects and recalled later.




Figure 1. Results of the reference transmitter characterization

Calibrations and Tests Covered by M8091UACA

For the receiver interference tolerance test, the broadband noise is injected into the noise path, and the receiver performance (bit error rate or, if available, the “block error ratio”) is retrieved from the Device Under Test (DUT) internal error checker.




Figure 2. Setup configuration for the C2C receiver interference tolerance test

While the backplane (KR) interface (clause 178) has different loss targets for the test channel than C2C, it follows a similar test procedure. Different parameters are used in the COM model to calculate the Channel Operating Margin.

The M8091UACA supports two different approaches for stress signal calibration. The procedure detailed in IEEE P802.3dj/D2.0 is similar to the C2C, but with a different test channel and with the noise injected at the transmitter side (TP0v)¹. The second approach described in IEEE P802.3dj/D1.4 consists of the following steps:

1. *System calibration*: Calibrate the equipment used to generate the victim transmitter (once per setup configuration)
2. *SNDR calibration*: Measure the Signal-to-Noise-Distortion-Ratio (SNDR) for varying broadband noise amplitude after the channel
3. *Link characterization*: Measure the transmitter SNDR, jitter, RLM, and pulse response after the channel
4. *COM-based calibration*: Using results from steps 2 and 3, determine the broadband noise amplitude needed to achieve the SNDR required to meet a 3 dB COM for the combined actual transmitter and test channel.

¹ For more details, refer to the M8091DJCA User Guide




Figure 3. Setup configuration for the CR receiver interference tolerance test

While the backplane (CR) interface (clause 179) has a different test channel than C2M, it follows a similar test procedure. Different parameters are used in the COM model to calculate the Channel Operating Margin and the amount of broadband noise to be injected at the transmitter side.

Overview of Test and Calibration Channels

The channels used for receiver validation have different mechanical characteristics depending on the interface being tested. In principle, any channel can be used as long as it meets the requirements defined in the specification for a compliant test channel. In particular:

- The insertion loss at the Nyquist frequency ² must fall within a specified range (see table below).
- The Effective Return Loss (ERL) must be below a defined threshold.
- The Channel Operating Margin (COM) must be greater than 3 dB.

Note that the COM of a given channel will vary depending on the interface, as each has different requirements.

Test channel characterization is typically performed using a Vector Network Analyzer (VNA), such as the Keysight PNA series, as illustrated in Figure 8.

Interface	Calibration Channel	Test Channel Insertion Loss (dB)
KR	ISI trace + cable	15, 30.5 & 34 ±0.5
CR	(ISI trace) + MCB + DAC cable + MCB	16,27, 32 & 37±0.5

² Nyquist frequency = Baudrate/2 (53.125GHz)




Figure 4. Calibration channels for CR and KR

Receiver Amplitude and Jitter Tolerance Tests

The purpose of the Jitter Tolerance Test is to test the ability of the receiver's Clock and Data Recovery (CDR) to track and compensate for both low- and high-frequency jitter. No broadband noise is added for the jitter tolerance test, but the frequency and amplitude of the sinusoidal jitter are varied according to Table 179–12.

Case	A	B	C	D	E	F	G
Frequency (MHz)	0.04	0.1333	0.4	1.333	4	12	40
Jitter amplitude (UI pk-pk)	5	1.5	0.5	0.15	0.05	0.05	0.05

The *Amplitude Tolerance Test*, as defined in IEEE P802.3dj/D2.0, Annex 120G, validates the acceptance of the differential input peak-to-peak amplitudes produced by the extreme operating conditions from the transmitter. For the Amplitude Tolerance Test, no broadband noise is added, but the signal steady-state is set to the maximum allowed value specified in Table 176C–4.

Note:

Please note that the M8091UACA receiver conformance test application does not cover additional receiver tests, such as *receiver signaling rate* (176C 6.4.1), *receiver difference ERL* (176C 6.4.3), and *receiver differential-mode to common-mode return loss* (176C 6.4.4). The dERL (Annex 176C.6.4.3 & clause 178.9.3.6) can be measured using the D90203DJC IEEE802.3dj Electrical Transmitter Test software, which applies the same ERL methodology and references the IEEE802.3dj specification.

Configuration Guide

The table below shows the required equipment for each standard option under IEEE 802.3dj. The required instrument configuration and software options are listed in the following section.

Equipment Type	
Victim pattern generator	M8042A
Interference source	M8053A
Victim error detector	DCI (DUT control interface available in M8070ADVB)
Oscilloscope (calibration)	UXR-series oscilloscopes with 90 GHz bandwidth and above (recommend BP model)

Minimum Required Instrument Configuration

The options marked * are recommended but not mandatory.

M8050A BERT Platform

M8050A-BU2 ⁴	Bundle consisting of one M9505A 5-slot AXIe Chassis with USB option
M8042A	Pattern generator module 32/64/120 GBd, 2 or 3-slot AXIe
M8042A-0G1	Pattern generator NRZ and PAM4, 1 Channel, 2-slot AXIe Module
M8042A-G12	Pattern generator, 120 GBd for NRZ and PAM4, module-wide license
M8042A-0G4	De-emphasis, module-wide license
M8069A ³	Remote Head, 120 GBd for M8042A Pattern Generator
M8059A-801	Matched cable pair 1.0 mm (m) to 1.0 mm (m), 150 mm
M8009A	Clock module
M8009A-062	Clock generator module with jitter modulation, 60 GHz, 1 slot AXIe
M8009A-0G3	Advanced jitter modulation for up to two channels, license

Interference Source

M8053A	64GHz interference source
--------	---------------------------

UXR

UXR0702/4BP ⁴	Infiniium UXR-Series real-time oscilloscope, 70 GHz bandwidth, 2 or 4 ports
N2157A-017/8	Bandwidth upgrade 2/4 Ch Infiniium UXR real-time oscilloscope 70 to 80 GHz 1mm model (License only)
N2129BU-111/7	Bandwidth upgrade – 2/4 Ch Infiniium UXR real-time oscilloscope – 80 to 90 GHz
D9320ASIA	Advanced signal integrity software (EQ, InfiiniSimAdv, crosstalk)
D9320PAMA	Pulse amplitude modulation PAM-N analysis software
D9320JITA	Jitter, vertical, and phase noise analysis software for 90000, V-, Z-, and UXR-series

³ M8059A Remote Head is supported as well but may not have enough amplitude range to cover some use-cases.

⁴ UXR B model upgrade is possible as well

Accessories and Fixtures ⁵ (Recommended)

M8053A-801	Matched cable pair, 1.85 mm, length 850 mm, matching 1 ps (for combining SI and RI)
M8053A-803	Coupling path: bandwidth 64 GHz, coupling loss 14 dB, 1.85 mm. Through path: bandwidth 110GHz, 3.5 dB, 1.0 mm
M8053A-804	Adapter 1.0 mm (m) to 1.85 mm (f) (x2)
-	Wilder OSFP 224G/1.6T MCB 1 mm Connectors
-	Wilder OSFP 224G/1.6T HCB 1 mm Connectors
-	Wilder QSFP 224G/1.6T MCB 1 mm Connectors
	Wilder QSFP 224G/1.6T HCB 1 mm Connectors
M8067A-003	ISI Channel Board Two Traces 1.4 and 4.3 inches, 1.0 mm Connectors (for KR low loss)
M8067A-004	ISI Channel Board Two Traces 2.9 and 5.8 inches, 1.0 mm Connectors (for C2C low loss)
M8067A-005	ISI Channel Board Two Traces 7.3 and 8.8 inches, 1.0 mm Connectors (for C2M, C2C, and KR high loss)

Software Configuration

M8070ADVB	Advanced measurement package for M8000 Series of BERT test solutions (node locked, transportable, floating or USB license, revisions 9.1 or later)
M8091UACA	Receiver conformance test application for IEEE 802.3dj (node-locked, transportable floating, or USB license)

⁵ Due to copper cable variability, Keysight cannot recommend any test channel for CR interfaces.

Minimum PC Configuration

The PC running the application should meet the following requirements

PC hardware requirements

- Operating system: Microsoft Windows 11 or Windows 10 (64-bit), Version 1809 or newer
- Memory: 8 GB RAM minimum
- Monitor resolution: WXGA+ (1440 x 900) minimum

PC software requirements (please refer to the software release note for version/ revision info)

- Microsoft Office
- Microsoft .NET Framework
- Keysight IO Library Suite
- Keysight License Manager 5 and Keysight Software Manager Utility
- Keysight M8070B system software for M8000 series
- M8070ADVB Advanced Measurement Package for M8000 Series
- Keysight UXR oscilloscope FW
- MATLAB Compiler Runtime

Remote Programming

The M8091UACA Receiver Conformance Test Application for IEEE 802.3dj is part of Keysight's Digital Test Apps and can be programmed via ARSL, any .NET language. For more information, see www.keysight.com/find/rpi.

Related Products

The [D90203DJC IEEE 802.3dj Electrical Transmitter Compliance Test Software](#) for real-time oscilloscopes.

The [N4917DJCA 1.6T Optical Receiver Stress Test Application](#) for 800G and 1.6T transceiver modules.

The [M8091CKCA Receiver Conformance Test Application for IEEE 802.3ck](#) for testing Chip-to-Chip (C2C) and Chip-to-Module (C2M) interfaces

Keysight enables innovators to push the boundaries of engineering by quickly solving design, emulation, and test challenges to create the best product experiences. Start your innovation journey at www.keysight.com.



This information is subject to change without notice. © Keysight Technologies, 2026, Published in USA, June 4, 2026, 3126-1055.EN