


Keysight Technologies

PCI Express® Probes for Keysight E2960B PCI Express Analysis Systems



Superior Signal Probing options to address diverse designs and form factors

As an industry leader in the innovation of non-intrusive, low load probe designs, Keysight contributes a wide range of probing solution for the E2960B PCI Express Analysis System for PCI Express Generation 1 or Generation 2. The probes from Keysight address a wide range of application needs as well as price points.

A key criteria for probe selection depends on the type of system you are trying to get insight into, add-in card, motherboard, or embedded design and also at the speed you are trying to probe.

If the design has a standard PCI Express card slot, then the easiest way to get visibility to the system is through a PCI Express Interposer probe. The interposer probe plugs in between the motherboard card slot and the add-in card. It is important to ensure that the interposer probe chosen is an analog or passive probe with good signal integrity, so that when the probe is in the system, it doesn't not change any of the electrical characteristics. The restrictions of a retiming interposer probe is that sometimes by having the probe in the system, issues are no longer visible to the system.

If you need to probe the system where there is no predesigned card slot to plug into, then a mid-bus probe or flying leads probe could be an alternative. The mid-bus probe connects to the board through a designed in "header" connection. The flying lead on the other hand can be used to solder leads directly onto the board, to provide the physical connection to the bus.

In all cases and for all probe types, Keysight provides the industry's best signal integrity with minimal signal distortion and low jitter, so that you can probe with confidence ensuring that there is no change to the signal path.




Figure 2. Keysight PCI Express 2.0 Probes Overview




Figure 3. Keysight PCI Express 1.0 Probes Overview

Keysight PCI Express 2.0 Probes Overview

Product	Link widths	2.5 Gb/s Gen1	5.0 Gb/s Gen2	Description
N5315A : Slot Interposer 2.0	x1 (N5315A-A01), x4 (N5315A-A04) x8 (N5315A-A08) x16 (N5315A-A16)	yes	yes	Keysight's N5315A slot interposer uses an analog repeating design delivering a faithful representation of the signal on the bus at 5.0 Gb/s data rates of the PCI Express Gen2 Bus. There are 4 options for the N5315A, that supports from link width x1 through x16. For link width x1 through x8, a single N5306A analyzer module is required, for x16 analysis, 2 N5306A analyzer modules are required.
N4241A : Mid-bus Probe 2.0 Straight x8	x1, x4, x8, x16 (2 required at x16)	yes	yes	Keysight's mid-bus 2.0 family of probes use the soft touch technology to give critical design insight without influencing it. The N4241A straight x8 mid-bus supports designs up to x8 link width, and two N4241A probes can be combined to probe a x16 design (two N5306A modules are required for x16 analysis).
N4242A : Mid-bus Probe 2.0 Swizzled x16	x16	yes	yes	In certain designs, the board layout constraint is such that it is not possible to layout the x16 footprint to use the straight x8 mid-bus probe from Keysight. The N4242A swizzled mid-bus probe supports the design where an x16 link is separated into 2 x8 bi-directional headers. The N4242A has the same soft touch technology with minimal capacitive loading.
N4243A : Mid-bus Probe 2.0 Split x4	2 x4 link on one footprint	yes	yes	The N4243A split x4 probe allows the designer to route 2 x4 PCI Express links into one x8 bi-directional footprint on the board. This probe splits out the signal into two analyzers, so each x4 link can be analyzed independently. The N4243A has the same soft touch technology with minimal capacitive loading.
N5328A Half Size Mid-bus Probe 2.0	x1, x4	yes	yes	As designs shrink in size, space constraints force designers to minimize the space allocation for test points. The N5328A half size mid-bus probe allows access to the signal in ½ the space of the full size probe. This probe would be a good fit in low link width applications, where space is a major constraint. The N5328A uses the same soft touch technology with minimal capacitive loading.
N4241F : Flying Leads Probe 2.0	x1, x4,x8, x16 (2 required at x16)	yes	yes	The N4241F flying leads probe allows access to PCI Express 2.0 signals without any designed in connectors. This allows insight to debug customer systems where no built-in test point is available, and embedded designs where space is constrained. As all Keysight probes, the N4241F has very low capacitive loading and it enables insight without influencing the monitored signals.
N4241Z : Flying Leads Probe 2.0 with ZIF connector	x1, x4, x8, x16 (2 required at x16)	yes yes	yes yes	The N4241Z flying leads probe allows access to PCI Express 2.0 signals without any designed connectors. This allows insight to debug systems where no built-in test point is available. The N4241Z flying leads probe uses a zero insertion force (ZIF) tip, that allows easy connection and detachment from the probe head. The probe tip (long or short wire) can also be used with a Keysight Infiniimax probe, allowing you to make both protocol and electrical measurements from the same probing point.

Keysight PCI Express 1.0 Probes Overview

Product	Link widths	2.5 Gb/s Gen1	5.0 Gb/s Gen2	Description
E2945A/E2946A/E2947A : Slot Interposer 1.0	x1 (E2945A) x4 (E2946A) x8 (E2947A)	yes	no	The E2945A/E2946A/E2947A are passive interposer probes that give a faithful representation of the signal at Gen1 (2.5 Gb/s) speeds. For current Gen1 testing, these probes are a good low cost alternative interposer probe. All three slot interposer probes should be connected through the N5317A probe adapter cable to the N5306A analyzer module.
E2960B-MEC : Express Card Probe 1.0	x1	yes	no	The E2960B-MEC allows access to PCI Express, express card slots at PCI Express 1.0 (Gen1) speeds. To connect the express card probe, plug the express card probe into the express card slot, and connect the express card on the other side. Monitor the signals on the express card bus through a mid-bus probe connected to the analyzer.
N4221A : Mid-bus Probe 1.0 straight x8	x1, x2, x4, x8	yes	no	The N4221A Mid-bus probe 1.0 uses Keysight's soft touch technology to minimize the interference and loading on the bus. For current Gen1 testing, this is a good cost alternative mid-bus probe, and the probing footprint is compatible to the Gen2 footprint. To connect the N4221A to the N5306A analyzer module, you must use the N5317A probe adapter cable and the E2941B midbus adaptor.
N4228A : Half Size Mid-bus Probe 1.0	x1, x2, x4, x8	yes	no	The N4228A Mid-bus probe 1.0 uses Keysight's soft touch technology to minimize the interference and loading on the bus. To connect the N4228A to the N5306A analyzer module, you must use the N5317A probe adapter cable and the E2941B midbus adaptor.
N4221F : Flying Lead Probe 1.0	x1, x2, x4, x8	yes	no	The N4221F flying leads probe allows access to PCI Express 1.0 signals without any designed in connectors. This allows insight even when no built-in test point is available, such as in embedded designs where space is constrained. As all Keysight probes, the N4221F has very low capacitive loading and it enables insight without influencing the monitored signals. To connect the N4221F to the N5306A analyzer module, you must use the N5317A probe adapter cable and the E2941B midbus adaptor.


Related Keysight Literature

Literature title	Literature number
The Keysight Test Portfolio for PCI Express 2.0 Brochure	5989-5594EN
Keysight E2960B Series for PCI Express 2.0x1 through x16 Gen 2 Ready Program Photo Card	5989-6395EN
Keysight E2969B Protocol Test Card for PCI Express 2.0 Photo Card	5988-7594EN
Keysight E2969A Protocol Test Card for PCI Express Photo Card	5989-9520EN
Keysight PCI Express Jammer Brochure	5990-3222EN
Keysight E2960B Series for PCI Express 2.0 Data Sheet	5989-5660EN

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

http://www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

"PCI Express" is a registered trademark of PCI-SIG

www.keysight.com/find/pcie

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at:

www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:

www.keysight.com/find/contactus
(BP-9-7-17)

DEKRA Certified
ISO 9001 Quality Management System

www.keysight.com/go/quality

Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System



This information is subject to change without notice.
© Keysight Technologies, 2017
Published in USA, December 2, 2017
5990-4123EN
www.keysight.com