Keysight NL3-Class ATE DC Electronic Load

EL4900 Series Regenerative DC Electronic Loads

The EL4900 Series DC electronic loads provide precision for power device testing, from validation to transient analysis. The regenerative feature returns up to 95% of absorbed energy to the grid, reducing energy and cooling costs without disrupting grid performance. Paired with the PathWave Advanced Power Suite software, the EL4900 Series provides robust automation of complex test scenarios, delivering deeper insights and analysis. Validate complex power devices in less space, with no compromise on performance or programmability.



Keysight EL4900 Series DC electronic loads

Operating Modes

Current priority (CC)	Voltage priority (CV)
Power priority (CP)	Resistance priority (CR)
CV+CC	CV+CR
CC+CR	CC+CV+CP+CR (Auto)

Model	10 V	32 V	80 V	300 V	500 V	800 V	1500 V
	EL49x1A	EL49x2A	EL49x3A	EL49x4A	EL49x5A	EL49x6A	EL49x7A
DC Power Ratings							
Voltage	10 V	32 V	80 V	300 V	500 V	800 V	1500 V
Current	120–720 A	80–480 A	40–240 A	20–120 A	12–72 A	8–48 A	12–24 A
Power	1.2–7.2 kW	2–12 kW	2–12 kW	2–12 kW	2–12 kW	2–12 kW	6–12 kW
Load Regulation [1]							
Voltage	≤ 4 mV	≤ 12.8 mV	≤ 16 mV	≤ 60 mV	≤ 100 mV	≤ 160 mV	≤ 300 mV
Current	≤ 120–720 mA	≤ 80–480 mA	≤ 40–240 mA	≤ 20–120 mA	≤ 12–72 mA	≤ 8-64 mA	≤ 12-24 mA
Programming Accuracy [1]							
Voltage	0.08% + 8 mV	0.05% + 22 mV	0.03% + 24 mV	0.03% + 90 mV	0.03% + 150 mV	0.03% + 240 mV	0.03% + 900 mV
Current 0.1% +	0.3% + 510 mA to 3.06 A	0.1% + 200 mA to 1.2 A	0.1% + 40 mA to 240 mA	0.1% + 30 mA to 180 mA	0.1% + 12 mA to 72 mA	0.1% + 8 mA to 48 mA	0.2% + 24 mA to 48 mA
Readback Accuracy [1]							
Voltage	0.08% + 8 mV	0.05% + 22 mV	0.03% + 24 mV	0.03% + 90 mV	0.03% + 150 mV	0.03% + 240 mV	0.03% + 900 mV
Current 0.1% +	0.3% + 510 mA to 3.06 A	0.1% + 200 mA to 1.2 A	0.1% + 60 mA to 380 mA	0.1% + 30 mA to 180 mA	0.1% + 12 mA to 72 mA	0.1% + 8 mA to 48 mA	0.2% + 24 mA to 48 mA
Programming Resolution							
Voltage	1 mV	1 mV	1 mV	1 mV	10 mV	10 mV	10 mV
Current	100 mA	10 mA	10 mA	10 mA	1–10 mA	1–10 mA	1 mA
Line Regulation							
Voltage	≤ 2 mV	≤ 3.2 mV	≤ 16 mV	≤ 30–60 mV	≤ 100 mV	≤ 160 mV	≤ 300 mV
Current	≤ 72–432 mA	≤ 48–288 mA	≤ 24–144 mA	≤ 12–36 mA	≤ 7.2–57.6 mA	≤ 4.8–28.8 mA	≤ 7.2–14.4 mA
Typical Characteristics							
Command processing time	≤ 0.1 ms						

1. Percent of value + offset; at 23 °C ± 5 °C after a 30-minute warm-up; measurement NPLC=1; valid for 1 year.

More Information: www.keysight.com/find/EL4900

High Density, High Performance

Power that adapts to every test

- Return absorbed energy to the grid with a regenerative design that returns up to 95% of absorbed energy
- Multiple operating modes: (CV, CC, CR, CP, plus combinations)
- Voltage options: 10 V, 32 V, 80 V, 300 V, 500 V, 800 V, and 1500 V
- Power range: 1.2 kW to 12 kW; parallel up to 16 units for higher sinking current
- Stackable parallel connections for higher total sinking current

Smarter tools for deeper insights

- Built-in waveform generation for battery testing
- Averaged and digitized measurement modes
- Amp-hour and watt-hour calculations
- PathWave software applications for analysis, control, and emulation

Safety and simplicity built-in

- Overvoltage, overcurrent, overpower, and overtemperature safeguards
- Fast hardware-level protection response
- Compact 1U and 2U rack designs
- Dedicated rack-mount kits
- Standard LAN, USB, and CAN; optional GPIB, RS-232, and analog
- Built-in web interface for remote control

Accessories

Part Number	Description
PW9252A	PathWave Advanced Power Control and Analysis application
RP5901C	GPIB interface board for EL4900 Series DC loads and RP5900 Series supplies
RP5902C	Analog / RS232 interface board for EL4900 Series DC loads and RP5900 Series supplies
RP5903C	Parallel kit — Fiber optics cable and transmitter module
RP5904C	Rack-mount kit 1U for EL4900 Series DC loads and RP5900 Series supplies
RP5905C	Rack-mount kit 2U for EL4900 Series DC loads and RP5900 Series supplies

For More Information

For more information on the Keysight EL4900 Series regenerative DC electronic loads, please visit:
www.keysight.com/find/EL4900

To find a distributor in your area, visit:
www.keysight.com/find/distributors

Keysight enables innovators to push the boundaries of engineering by quickly solving design, emulation, and test challenges to create the best product experiences. Start your innovation journey at www.keysight.com.

This information is subject to change without notice. © Keysight Technologies, 2025-2026, Published in USA, October 2, 2026, 3125-1391.EN