Keysight Technologies

N8825A/B Infiniium 10BASE-T / 100BASE-TX Ethernet Decoder

Data Sheet

Introduction

The N8825A/B 10BASE-T/100BASE-TX Ethernet decoder allows you to view Ethernet packet data transmitted between Ethernet devices on all Infiniium real-time oscilloscopes. Today's Ethernet devices must be backward-compatible to Ethernet technologies such as 10BASE-T/100BASE-TX standards. The N8825A/B 10BASE-T/100BASE-TX Ethernet protocol decoder provides time-correlated views of physical layer (raw data) and transaction layer packets. Unique packet-waveform correlation marker makes it easy to scroll through waveforms to view synchronized packet and symbol lists. Both IPv4 and IPv6 internet protocols are supported.



Extend your oscilloscope's capability with Keysight's Ethernet protocol decoder

The application makes it easy to debug and test Ethernet designs on your Infiniium Series oscilloscope. Debugging Ethernet signals is as simple as clicking the "Auto Setup" button and capturing Ethernet protocol data, and decoding packets can be done in less than 30 seconds. The "Auto Setup" button automatically configures the sample rate, memory depth, threshold and trigger levels.



10BASE-T and 100BASE-TX Ethernet protocol setup.

The Ethernet decoder supports various display formats including label, 4B pairs (8-bit) and 5B pairs (10-bit) decode. Also supported are descramble and electrical idles. Perform and view decode information on both live and saved waveforms. Decode up to four live or saved waveforms or functions.



Ethernet decode options.

Ethernet Setup, Protocol Triggering and Search Capabilities

Get access to a rich set of integrated protocol-level triggers. The application includes a suite of configurable protocol-level trigger conditions specific to Ethernet. When protocol triggering is selected, the application uses software-based and hardware based triggering. With software-based protocol triggering, the oscilloscope takes signals acquired using the oscilloscope analog channels and reconstructs protocol frames after each acquisition. It then inspects these protocol frames against specified protocol-level trigger conditions and triggers when the condition is met.



Basic Ethernet trigger and search.



Detailed Ethernet trigger and search.

10BASE-T and 100BASE-TX Ethernet Protocol Decode

Display bidirectional serial data from the transmitter (yellow) and receiver (green) at the same time with time-correlated data. Decoded packets are shown below the waveforms and in the decode listings windows.



Ethernet decoder interface.



Ethernet decode embedded in waveform area utilizes the oscilloscope waveform area to display decode information. Minor ticks indicate clock transitions, and major ticks show fields within each Ethernet packet.

Protocol 1 Listing : Ethernet 10BASE-T

Index	Time	IEEE 802.3	Source Port	Source MAC	Source IP	Destination Port	Destination MAC	Destination IP	FCS CRC	Checksum	Payload
55	-236.17042555 ms	IPv6 Hop-by-Hop Options (EH)		00-30-D3-21-21-83	FE80:0000:0000:0000:B560:1ABD:03F7:ACFF		33-33-00-00-00-16	FF02:0000:0000:0000:0000:0000:0000:0016	2855 BC51 (GOOD)	41FE (GOOD)	05 02 00 00 01 00 00 00 00 01 04 0
56	-225.54147803 ms	IPv6 UDP	MDNS	3C-D9-2B-60-98-0D	FE80:0000:0000:0000:656D:4A38:CE7E:FF7F	MDNS	33-33-00-00-00-FB	FF02:0000:0000:0000:0000:0000:0000:00FB	F982 E30F (GOOD)	A859 (GOOD)	00 00 00 00 00 04 00 00 00 00 00 0
57	-224.53266406 ms	IPv4 UDP	MDNS	3C-D9-2B-60-98-0D	130.29.69.150	MDNS	01-00-5E-00-00-FB	224.00.00.251	EB6B 8A67 (GOOD)	7BCD (GOOD)	00 00 00 00 00 04 00 00 00 00 00 0
58	-216.68935519 ms	IPv4 UDP	NETBIOS NS	A0-48-1C-A0-CC-36	130.29.71.182	NETBIOS NS	FF-FF-FF-FF-FF-FF	130.29.71.255	2476 998A (GOOD)	6311 (GOOD)	C5 F8 01 10 00 01 00 00 00 00 00 0
59	-205.95080600 ms	IPv4 UDP	49647	24-BE-05-09-8D-AD	130.29.70.219	1947	FF-FF-FF-FF-FF-FF	255.255.255.255	A48C 7C62 (GOOD)	0164 (GOOD)	64 4C 51 33 55 50 77 4D 41 41 41 7
60	-202.49995849 ms	IPv6 UDP	MDNS	A0-D3-C1-28-BC-AA	FE80:0000:0000:0000:7C06:159A:8E76:2985	MDNS	33-33-00-00-00-FB	FF02:0000:0000:0000:0000:0000:0000:00FB	3AB0 3EBA (GOOD)	DC61 (GOOD)	00 00 00 00 00 04 00 00 00 00 00 0
61	-199.46911660 ms	IPv4 UDP	MDNS	A0-D3-C1-28-BC-AA	130.29.69.83	MDNS	01-00-5E-00-00-FB	224.00.00.251	9221 3E18 (GOOD)	6733 (GOOD)	00 00 00 00 00 04 00 00 00 00 00 0
62	-197.66549131 ms	IPv4 UDP	NETBIOS NS	B8-AC-6F-81-F4-D2	130.29.70.28	NETBIOS NS	FF-FF-FF-FF-FF-FF	130.29.71.255	F0C5 553D (GOOD)	FD05 (GOOD)	F9 93 01 10 00 01 00 00 00 00 00 0
63	-187.59695169 ms	IPv6 UDP	MDNS	00-30-D3-20-9D-23	FE80:0000:0000:0000:78BB:DA13:A168:F1BD	MDNS	33-33-00-00-00-FB	FF02:0000:0000:0000:0000:0000:0000:00FB	D181 B249 (GOOD)	7147 (GOOD)	00 00 84 00 00 00 00 04 00 00 00 0
64	-185.98372859 ms	IPv4 UDP	MDNS	00-30-D3-20-9D-23	130.29.71.233	MDNS	01-00-5E-00-00-FB	224.00.00.251	D6C2 F52F (GOOD)	41EC (GOOD)	00 00 84 00 00 00 00 04 00 00 00 0
65	-170.20471033 ms	IPv4 UDP	NETBIOS NS	64-31-50-A4-9B-B0	130.29.69.183	NETBIOS NS	FF-FF-FF-FF-FF-FF	130.29.71.255	C3A6 BC4A (GOOD)	1E6E (GOOD)	BF 88 01 10 00 01 00 00 00 00 00 0
66	-150.45763662 ms	IPv6 UDP	MDNS	00-30-D3-21-21-75	FE80:0000:0000:0000:3423:3F02:5C2D:3236	MDNS	33-33-00-00-00-FB	FF02:0000:0000:0000:0000:0000:0000:00FB	AEF1 8E99 (GOOD)	DD5A (GOOD)	00 00 00 00 00 01 00 00 00 01 00 0
67	-143.29633702 ms	IPv4 UDP	MDNS	00-30-D3-21-21-75	130.29.69.92	MDNS	01-00-5E-00-00-FB	224.00.00.251	5951 72CF (GOOD)	34ED (GOOD)	00 00 00 00 00 01 00 00 00 01 00 0
68	-141.06110559 ms	ARP		00-30-64-0B-C6-17			FF-FF-FF-FF-FF-FF		32D2 3D08 (GOOD)		00 00 00 00 00 00 00 00 00 00 00 0
69	-122.56004834 ms	IPv6 UDP	DHCPv6	B4-B5-2F-CA-46-49	FE80:0000:0000:0000:6161:9CF1:BDBB:3E97	DHCPv6	33-33-00-01-00-02	FF02:0000:0000:0000:0000:0000:0001:0002	A667 3002 (GOOD)	6D09 (GOOD)	01 70 79 A2 00 08 00 02 00 64 00 0
70	-72.38575239 ms	ARP		00-30-64-25-D7-B0			FF-FF-FF-FF-FF-FF		1DFF 032A (GOOD)		00 00 00 00 00 00 00 00 00 00 00 0
71	-70.90893654 ms	ARP		00-08-E3-FF-FD-90			00-30-64-25-D7-B0		2591 EDE3 (GOOD)		00 00 00 00 00 00 00 00 00 00 00 0
72	-67.57248572 ms	ARP		2C-44-FD-66-16-DA			FF-FF-FF-FF-FF-FF		243A A5E4 (GOOD)		00 00 00 00 00 00 00 00 00 00 00 0
73	12.12902064 ms	ARP		00-08-E3-FF-FD-90			FF-FF-FF-FF-FF-FF		075E D809 (GOOD)		00 00 00 00 00 00 00 00 00 00 00 0
74	19.04711634 ms	IPv4 UDP	51526	A0-D3-C1-9D-C4-FF	130.29.71.110	1211	FF-FF-FF-FF-FF-FF	255.255.255.255	84A6 6425 (GOOD)	F380 (GOOD)	01 03 80 64 70 70 3A 2F 2F 2F 66 6
75	30.35407351 ms	IPv4 UDP	Dropbox	B4-B5-2F-FB-8D-8E	130.29.70.157	Dropbox	FF-FF-FF-FF-FF-FF	255.255.255.255	9F3A 5C6F (GOOD)	80FD (GOOD)	7B 22 68 6F 73 74 5F 69 6E 74 22 3
76	36.83576277 ms	IPv4 UDP	Dropbox	B4-B5-2F-FB-8D-8E	130.29.70.157	Dropbox	FF-FF-FF-FF-FF-FF	255.255.255.255	874D E7E9 (GOOD)	80FD (GOOD)	7B 22 68 6F 73 74 5F 69 6E 74 22 3
77	37.06296726 ms	IPv4 UDP	Dropbox	B4-B5-2F-FB-8D-8E	130.29.70.157	Dropbox	FF-FF-FF-FF-FF-FF	255.255.255.255	70C5 2D8E (GOOD)	80FD (GOOD)	7B 22 68 6F 73 74 5F 69 6E 74 22 3
78	37.77817652 ms	IPv4 UDP	Dropbox	B4-B5-2F-FB-8D-8E	130.29.70.157	Dropbox	FF-FF-FF-FF-FF-FF	255.255.255.255	F6A5 E03F (GOOD)	80FD (GOOD)	7B 22 68 6F 73 74 5F 69 6E 74 22 3
79	38.00697968 ms	IPv4 UDP	Dropbox	B4-B5-2F-FB-8D-8E	130.29.70.157	Dropbox	FF-FF-FF-FF-FF-FF	130.29.71.255	86B3 3DBC (GOOD)	B6E0 (GOOD)	7B 22 68 6F 73 74 5F 69 6E 74 22 3
80	67.77299280 ms	ARP		D8-9D-67-CB-09-C5			FF-FF-FF-FF-FF-FF		021F 5FB9 (GOOD)		00 00 00 00 00 00 00 00 00 00 00 0
81	77.07952171 ms	ARP		88-51-FB-51-59-36			FF-FF-FF-FF-FF-FF		53FE A5D4 (GOOD)		00 00 00 00 00 00 00 00 00 00 00 0
82	100.53464729 ms	IPv6 UDP	MDNS	00-30-D3-21-21-75	FE80:0000:0000:0000:3423:3F02:5C2D:3236	MDNS	33-33-00-00-00-FB	FF02:0000:0000:0000:0000:0000:0000:00FB	63F2 4A35 (GOOD)	5D5B (GOOD)	00 00 00 00 00 01 00 00 00 01 00 0
83	102.28987222 ms	IPv4 UDP	MDNS	00-30-D3-21-21-75	130.29.69.92	MDNS	01-00-5E-00-00-FB	224.00.00.251	3B5A 032C (GOOD)	B4ED (GOOD)	00 00 00 00 00 01 00 00 00 01 00 0
84	137.93476687 ms	IPv6 UDP	DHCPv6	F0-92-1C-E0-61-A7	FE80:0000:0000:0000:210A:1B28:B99D:9071	DHCPv6	33-33-00-01-00-02	FF02:0000:0000:0000:0000:0000:0001:0002	4BAE 90B2 (GOOD)	3F1F (GOOD)	01 7D 8C A7 00 08 00 02 00 00 00 0
85	155.17700606 ms	IPv4 UDP	55713	AC-16-2D-5C-6D-C9	130.29.71.42	MS SSDP	01-00-5E-7F-FF-FA	239.255.255.250	A683 8A5B (GOOD)	BE9A (GOOD)	4D 2D 53 45 41 52 43 48 20 2A 20 4
86	161.84669817 ms	Ethernet Packet		88-43-E1-0D-9D-EC			01-80-C2-00-00-00		92D2 FE24 (GOOD)		42 42 03 00 00 00 00 00 61 90 00 0
87	209.82296409 ms	IPv4 UDP	Dropbox	A0-48-1C-84-58-FC	130.29.69.66	Dropbox	FF-FF-FF-FF-FF-FF	255.255.255.255	0137 EDD6 (GOOD)	803D (GOOD)	7B 22 68 6F 73 74 5F 69 6E 74 22 3
88	211.41978702 ms	IPv4 UDP	Dropbox	A0-48-1C-84-58-FC	130.29.69.66	Dropbox	FF-FF-FF-FF-FF-FF	130.29.71.255	7A20 9E66 (GOOD)	B620 (GOOD)	7B 22 68 6F 73 74 5F 69 6E 74 22 3
89	212.14259647 ms	IPv6 UDP	63805	B4-B5-2F-32-E5-A0	FE80:0000:0000:0000:FCD6:46C0:62E3:6E14	5355	33-33-00-01-00-03	FF02:0000:0000:0000:0000:0000:0001:0003	0371 9DAD (GOOD)	D870 (GOOD)	A8 CE 00 00 00 01 00 00 00 00 00 0
90	215.24543990 ms	IPv4 UDP	49912	B4-B5-2F-32-E5-A0	130.29.71.120	5355	01-00-5E-00-00-FC	224.00.00.252	AC11 2CF2 (GOOD)	763A (GOOD)	A8 CE 00 00 00 01 00 00 00 00 00 0
91	236.77133846 ms	IPv6 UDP	MDNS	00-30-D3-21-21-75	FE80:0000:0000:0000:3423:3F02:5C2D:3236	MDNS	33-33-00-00-00-FB	FF02:0000:0000:0000:0000:0000:0000:00FB	2CE7 B887 (GOOD)	F4C3 (GOOD)	00 00 84 00 00 00 00 09 00 00 00 0
92	239.10217088 ms	IPv6 UDP	MDNS	74-46-A0-90-F1-05	FE80:0000:0000:0000:4D5B:539A:E323:9626	MDNS	33-33-00-00-00-FB	FF02:0000:0000:0000:0000:0000:0000:00FB	9231 D3EF (GOOD)	2D5F (GOOD)	00 00 00 00 00 02 00 00 00 00 00 0
93	246.43867250 ms	IPv4 UDP	MDNS	00-30-D3-21-21-75	130.29.69.92	MDNS	01-00-5E-00-00-FB	224.00.00.251	8A31 774A (GOOD)	8525 (GOOD)	00 00 84 00 00 00 00 09 00 00 00 0
94	246.96707939 ms	IPv6 Hop-by-Hop Options (EH)		00-30-D3-21-21-83	FE80:0000:0000:0000:B560:1ABD:03F7:ACFF		33-33-00-00-00-16	FF02:0000:0000:0000:0000:0000:0000:0016	2855 BC51 (GOOD)	41FE (GOOD)	05 02 00 00 01 00 00 00 00 01 04 0
95	273.58984921 ms	IPv6 UDP	MDNS	3C-D9-2B-60-98-0D	FE80:0000:0000:0000:656D:4A38:CE7E:FF7F	MDNS	33-33-00-00-00-FB	FF02:0000:0000:0000:0000:0000:0000:00FB	58E2 349D (GOOD)	8CC5 (GOOD)	00 00 00 00 00 04 00 00 00 00 00 0
96	274.77626600 ms	IPv4 UDP	MDNS	3C-D9-2B-60-98-0D	130.29.69.150	MDNS	01-00-5E-00-00-FB	224.00.00.251	8A48 47A7 (GOOD)	6039 (GOOD)	00 00 00 00 00 04 00 00 00 00 00 0
97	285.01680746 ms	ARP		B4-B5-2F-D9-4E-EC			FF-FF-FF-FF-FF-FF		2484 F685 (GOOD)		00 00 00 00 00 00 00 00 00 00 00 0
98	288.93406190 ms	ARP		10-60-4B-6D-BA-38			FF-FF-FF-FF-FF-FF		C621 4240 (GOOD)		00 00 00 00 00 00 00 00 00 00 00 0
99	308.08112766 ms	IPv6 UDP	DHCPv6	00-30-64-0E-FE-A0	FE80:0000:0000:0000:8030:AE2E:E302:3C73	DHCPv6	33-33-00-01-00-02	FF02:0000:0000:0000:0000:0000:0001:0002	787B D586 (GOOD)	2716 (GOOD)	01 04 4C 74 00 08 00 02 01 2C 00 0
100	312.31198714 ms	IPv6 UDP	MDNS	A0-D3-C1-28-BC-AA	FE80:0000:0000:0000:7C06:159A:8E76:2985	MDNS	33-33-00-00-00-FB	FF02:0000:0000:0000:0000:0000:0000:00FB	B79C AADD (GOOD)	C0CD (GOOD)	00 00 00 00 00 04 00 00 00 00 00 0
101	313.33360088 ms	IPv4 UDP	MDNS	A0-D3-C1-28-BC-AA	130.29.69.83	MDNS	01-00-5E-00-00-FB	224.00.00.251	A38A 683C (GOOD)	607C (GOOD)	00 00 00 00 00 04 00 00 00 00 00 0

Expand the lister window to show just the packet information in an organized color-coded packet listing format. Dark blue line indicates the trigger or search location.



Get all the details you're looking for on packet information, payload data and header information.

10BASE-T and 100BASE-TX Ethernet Decoder Application Specifications and Characteristics

The N8825A/B 10/100 Ethernet protocol viewer software offers several features to simplify the validation of your Ethernet designs:

- Supports 10BASE-T and 100BASE-TX Ethernet standards
- Internet protocol support for both IPv4 and IPv6
- User datagram protocol - UDP support
- Transmission control protocol - TCP support

Decode packet types:

- MAC destination addresses
- MAC source addresses
- MAC length/type
- Data
- IPv4 header
- IPv6 header
- UDP header
- TCP header
- Frame check sequence – FCS
- Cyclic redundancy check -CRC
- End of packet
- Error
- 802.1Q
- 802.AD

Decoder features:

- Setup wizard for quick setup, configuration and test
- Packet-level decode
- Simultaneous display of packet/ symbol lists and waveform overlay
- Capability to save symbol and packet data lists to .csv and .txt files
- Packet decode details tab provides detailed information on packets
- Channel information
- Listing index
- Control symbols
- Data payload popup
- Packet length
- Payload display shows data payload
- Unique packet-waveform correlation marker “blue line” makes it easy to scroll through waveforms to view synchronized packet and symbol lists
- Comprehensive serial search capabilities
  - Trigger and stop on search
  - Packet search capability

Recommended oscilloscopes

The N8825A/B 10BASE-T/100BASE-TX Ethernet protocol decoder is compatible with Keysight Technologies Infiniium Series oscilloscopes with operating software revision 5.50 or higher. S-Series oscilloscopes have hardware serial trigger for 10BASE-T. For oscilloscopes with earlier revisions, free upgrade software is available here: **www.keysight.com/find/scope-apps-sw.**

Data rate	Minimum bandwidth	Minimum channels	Compatible oscilloscopes
10BASE-T (10Mb/s) 100BASE-TX (100Mb/s)	500 MHz	1	All Infiniium Series

Other hardware, probes and accessories

Model number	Description	Quantity
N2750A	1.5 GHz InfiniiMode differential active probes	1 (2 probes required for RX and TX)
Or		
1130A InfiniiMax	1.5 GHz InfiniiMax probe	1 (2 probes required for RX and TX)
E2678A InfiniiMax	Differential socketed probe head and accessories	1 (2 probe heads required for RX and TX)

Note: Please contact Keysight for information on the Ethernet decoder fixture.

Optional accessories

5959-9334	Probe leads	5
01130-63201	Probe head adapter	2

Oscilloscope software options

<table>
<tr><th></th><th colspan="2">License type</th><th>Z-Series</th><th>S-Series</th><th>90000A Series</th><th>9000 Series</th><th>90000 X-Series</th><th>V-Series</th></tr>
<tr><td rowspan="4">10/100 Ethernet decoder</td><td rowspan="2">Fixed</td><td>Factory-installed</td><td>Option 089</td><td>Option 089</td><td>Option 084</td><td>Option 076</td><td>Option 087</td><td>Option 089</td></tr>
<tr><td>User-installed</td><td>N8825A-1FP</td><td>N8825B-1FP</td><td>N8825A-1NL</td><td>N8825A-1NL</td><td>N8825A-1NL</td><td>N8825A-1FP</td></tr>
<tr><td rowspan="2">Floating</td><td>Transportable</td><td>N8825A-1TP</td><td>N8825B-1TP</td><td>N8825A-1TP</td><td>N8825A-1TP</td><td>N8825A-1TP</td><td>N8825A-1TP</td></tr>
<tr><td>Server-based</td><td colspan="6">N5435A-088</td></tr>
</table>

Related literature

Publication title	Publication type	Publication number
Infiniium 9000 Series Oscilloscopes	Data sheet	5990-3746EN
Infiniium S-Series Oscilloscopes	Data sheet	5991-3904EN
Infiniium 90000 X-Series Oscilloscopes	Data sheet	5990-5271EN
Infiniium 90000A Series Oscilloscopes	Data sheet	5989-7819EN
Infiniium 90000 Q-Series Oscilloscopes	Data sheet	5990-9712EN
Infiniium Z-Series Oscilloscopes	Data sheet	5991-3868EN
N5392A/B/C Ethernet Compliance Application with EEE	Data sheet	5991-1901EN

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.
From Hewlett-Packard to Agilent to Keysight.





myKeysight

myKeysight
www.keysight.com/find/mykeysight
A personalized view into the information most relevant to you.

www.keysight.com/find/emt_product_registration
Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES
Accelerate Technology Adoption. Lower costs.

Keysight Services
www.keysight.com/find/service
Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.

Keysight Assurance Plans
www.keysight.com/find/AssurancePlans
Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners
www.keysight.com/find/channelpartners
Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at:
www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
(BP-9-7-17)

DEKRA Certified
ISO9001 Quality Management System

www.keysight.com/go/quality
Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System

KEYSIGHT TECHNOLOGIES

Published in USA, December 1, 2017
5992-0592EN
www.keysight.com