


Keysight Technologies

E6701J GSM/GPRS and E6704A EGPRS Lab Applications

For the 8960 (E5515C/E) Wireless
Communications Test Set


Technical Overview



Combining the benefits of GSM/GPRS/EGPRS network emulation with the Keysight Technologies, Inc. global leadership in analysis technologies, the E5515C/E test set and the E6701J lab application provide mobile development engineers with a single desktop instrument – helping you get better devices to market sooner.

Develop, integrate, and validate high data rate EGPRS UEs


With the E6701J/E6704A GSM/GPRS/EGPRS lab application, developers have the only instrument available providing a systematic approach to root-cause analysis of high throughput issues in the mobile protocol stack; from decoded L1 to IP.



Test all the critical RF parameters


The E6701J provides flexible measurements including:

- Transmit power (TxP)
- Power vs time (PvT)
- Phase and amplitude vs time (PAvT)
- RF output spectrum (ORFS)
- Error vector magnitude (EVM)
- Bad frame indicator (BFI)
- FACCH frame erasure rate (FER)
- All the connections types required to fully analyze and debug your mobile device RF characteristics



Quick-turn just about any design change

With support for voice, video, short message service (SMS), multi-media messaging service (MMS), cell broadcast SMS (CBSMS), circuit-switched data, packet data call connections, DTM, multiple and secondary PDP contexts, design changes in anything from RF to TCP can be quickly validated with a complete regression test of mobile functions right at your desk.



Helping You Get Your Job Done Faster

Fast and flexible signaling –
with you in control of
network operations

Our network emulation is designed to make connecting calls fast and simple – and give you choices. We have pulled some of the most commonly requested parameters up from the protocol stack, providing many different connection scenarios without requiring you to fully understand the 3GPP stack and a complex scripting language. The E6701J delivers the control you need to get your job done faster.

The world's wireless
applications brought right to
your fingertips

Keysight Technologies, Inc. lab applications bring testing and tuning end-user applications right to your desk – without limiting how far your device may search when looking for real content. With our industry-leading SMS/MMS/cell broadcast messaging capabilities, push-to-talk over cellular, and blazing fast packet connections to the Internet over RF, you have the capability to test most mobile applications fully without leaving your office.

Developing more than just
GSM/GPRS/EGPRS devices?
Just hook it up and go!

If your development needs go beyond GSM/GPRS/EGPRS, with additional firmware that same box on your desk can connect calls from AMPS to HSPA+ and everything in between. What's more, Keysight leads the industry in support of 2G and 3G solutions for 1xEV-DO and W-CDMA/HSPA. Contact your Keysight sales engineer to learn how the E5515C/E test set gives you the flexibility to adapt quickly to emerging standards and technologies.

Get started with the GSM/GPRS/
EGPRS lab applications today at;
www.keysight.com/find/8960manuals

NCC (Network Colour Code)	1
BCC (Base Station Colour Code)	5
Get INEI at Call Setup	On
Mobile DTX State	Off
Paging Mode	Normal
Paging Multiframe	2
Repeat Paging	Off
Tx Level FACCH Signaling	On
Uplink Frame Segmentation	Asymmetric

IMSI Attach State	Off
Call Originate Timeout	10 s
Persistent Attach State	Off
Dual Transfer Mode	On
Extended Uplink TBF State	Off
Cell Identity	0
CS Paging Identity Type	IMSI
IMSI	21430000



Cell Broadcast Message 3 Setup		Value
Geographical Scope	Content	Cell / Normal
Message Code	Text1	0
Update Number	Text2	0
Message Identifier	Custom Text	0
Data Coding Scheme	Custom Data	Language
Data Coding Scheme		English
Data Coding Scheme		1
Content		Text1



MMS



Voice

CD-HSDPA

HSPA+

HSUPA

HSDPA

W-CDMA

TD-HSUPA

TD-HSDPA

TD-SCDMA

EGPRS

DB-DC-HSDPA

GPRS

HSDPA-MIMO

GSM

1xEV-DO

cdma2000®

IS-95

EDGE Evolution

EGPRS

GPRS

GSM

Find Design Issues Earlier, Resolve Them Faster

Functional test analysis

Reduce development and verification cycle time by systematically engaging mobile device layers “up the stack” to find design problems early — before they are found by your customers.

Validate a phone’s data throughput capability while using SMS, MMS, data transfer, video, PoC, WAP, email, or other services.

Drive down defect resolution cost by finding complex hardware, protocol, and application related issues that are specific to how the phone will function on the network, early in the design cycle.

All this for a price that is significantly less than traditional script-based test equipment.

```
C:\ Telnet 10.10.10.40
GHIJKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./
HIJKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0
IJKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./01
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./012
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./01234
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./012345
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./01234567
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./012345678
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:;
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:;<
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:;<=
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:;<=>
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:;<=>?
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:;<=>?@
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:;<=>?@A
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:;<=>?@AB
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:;<=>?@ABC
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:;<=>?@ABCD
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:;<=>?@ABCDE
JKLMNOPQRSTUUVWXYZ[\]^_`abcdefghijklmnopqrstuvwxyz{|}~ !"#$%&'()*+,-./0123456789:;<=>?@ABCDE
```

Base station emulation

From basic network settings like country code and cell ID, lab application variables for network emulation extend into such things as network operating mode, TMSI assignment, authentication, neighbor list management, and PDP context rejection, giving you the flexibility you need.

Call Setup Screen					
Cell Info		Cell Info		Call Params	
Cell Operation	Cell Operation		Cell Parameters		BCH Parameters
Cell Parameters	Serving Cell:	GPRS	GSM NS TX Max CCH:	39 dBm	TCH Parameters
	PBCCCH:	Off	GPRS NS Tx Max CCH:	39 dBm	
	PRACH Length:	8	Rx Lev Access Min:	< -110 dBm	
	NSC/SGSN Rev:	R99+	C2 Penalty Time:	20 s	
Cell Identification	Repeat FACCH:	Off	C2 Temp Offset:	0 dB	PDCTH Parameters
	Dual Transfer:	On	Reselect Offset:	6 dB	
	Persist Attach:	Off	Reselect Hyst:	6 dB	
	Mobile DTX:	Off	DRX Timer Max:	0 s	
Cell Operation			Value		Handover Parameters
Cell Lists	BCH Type		Combined		
	Dual Transfer Mode		On		
	Extended Uplink TBF State		Off		
External Trigger Setup	NSC/SGSN Revision		R99 onwards		Receiver Control
	Mobile DTX State		Off		
	Packet Control Ack Type		RLC/MAC Ctrl		
Close Menu	Persistent Attach State		Off		
	PBCCCH		Off		
		Cell Off	Sys Type: GPRS		
			Logging: No Conn.		
		IntRef	Offset		

The pulse of mobile/network interactions

Wireless protocol advisor software gives you all messages for the mobile and network from MAC layer all the way to IP. Triggering and filtering functionality lets you set up troublesome scenarios, such as intermittent failures. That means you can begin the scenario on Friday and come back Monday morning to a bounded and focused protocol log of exactly what happened surrounding the particular issue.

Octet	MSB	Bin	LSB	Hex	Description
7	0000	0110	1	2b	RR Skip Indicator= 0(hex)
8	0010	1011	1	0d	RR Message Type=Handover Command
9	0000	1101	1	0d	BS Colour Code= 5
10	0000	1101	1	0d	PLMN Colour Code= 1
11	0000	1101	1	0d	BCCH ARFCN= 31
12	0000	1111	1	1f	Channel Type and TDMA Offset=TCH/F + FACCH/F + SACCH/F
13	0000	1100	1	0c	Channel Description Timeslot Number= 4(dec)
14	1010	0000	1	a0	Training Sequence Code= 5(dec)
15	1010	0000	1	a0	Hopping Channel= Single RF channel
16	1010	0000	1	a0	Spare= 0(dec)
17	1010	0000	1	a0	Absolute RF Channel Number= 30(dec)

95	<- Rev/Up	GSM L3	Setup
96	For/Dow...	GSM L3	Call Proceeding
97	For/Dow...	GSM L3	Alerting
98	For/Dow...	GSM L3	Connect
99	<- Rev/Up	GSM L3	Connect Ack
100	For/Dow...	GSM L3	Handover Command
101	For/Dow...	GSM L3	Physical Information
102	<- Rev/Up	GSM L3	Handover Complete
103	For/Dow...	GSM L3	DTM Information
104	For/Dow...	GSM L3	SystemInfo Type 5

E6701 Family of Lab Applications

E6701J is our latest application release for the industry leading call box and the right choice for R&D engineers needing world-class functionality in a single instrument. E6701J has several new capabilities including VAMOS type II, and LTE/2G interRAT capabilities such as SRVCC voice capability, SMS over SGs, and LTE neighbors and measurement reports.

E6701J with E6720A-001 is our emerging high-performance application. This is designed for engineers who need early access to leading-edge technologies.

This application also supports baseband fading with the N5106A PXB baseband generator and channel emulator. This functionality requires hardware options E5515E-004, or E5515C-003 and 004.

For a complete comparison of our 8960 GSM/GPRS/EGPRS products please see http://www.home.keysight.com/upload/cmc_upload/All/E1968A_E6701x_FeatureComparison.pdf

Technical Specifications

These specifications apply to an E5515C/E mainframe with Option 002 installed when used with the latest shipping version of the E6701J lab application.

The above application also includes functionality described within the latest shipping version of E1968A GSM/GPRS/EGPRS test application with firmware. Please refer to the E1968A data sheet for details and specifications for all functionality covered within the E1968A at <http://literature.cdn.keysight.com/litweb/pdf/5990-5708EN.pdf>

Specifications describe the test set's warranted performance and are valid for the unit's operation within the stated environmental ranges unless otherwise noted.

Supplemental characteristics are intended to provide typical, but non-warranted, performance parameters that may be useful in applying the instrument. These characteristics are shown in italics and labeled as "typical". All units shipped from the factory meet these typical numbers at +25 °C ambient temperature without including measurement uncertainty.

myKeysight



myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

Three-Year Warranty

www.keysight.com/find/ThreeYearWarranty

Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.

Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.

www.keysight.com/go/quality

Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2008
Quality Management System

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

cdma2000 is a US registered certification mark of the Telecommunications Industry Association.

www.keysight.com/find/e6701j

www.keysight.com/find/e6704a

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	0800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
(BP-09-04-14)