

# Keysight Technologies

## 11909A Low Noise Amplifier

### Data Sheet



## Keysight Technologies, Inc. 11909A Specifications

<b>Frequency range</b>	9 kHz to 1 GHz (-3 dB)
<b>Amplifier gain</b>	32 dB $\pm$ 1.5 dB @ 100 MHz
<b>Gain flatness</b>	$\pm$ 0.5 dB (25 kHz to 800 MHz)
<b>Noise figure</b>	2.5 dB max and 1.8 dB typ. (5~500 MHz) 2.5 dB typ. (1 GHz)
<b>Output power @ 1 dB compression</b>	+10 dBm
<b>Impedance</b>	50 ohms
<b>Input return loss</b>	8 dB
<b>Output return loss</b>	10 dB
<b>Reverse isolation</b>	35 dB
<b>Maximum input for linear operation</b>	$\pm$ 24 mV (approximate)
<b>Input damage level</b>	$\pm$ 2 V DC

## General Specifications

<b>Temperature range</b>	Operating 0 °C to 55 °C Storage -25 °C to 75 °C
<b>Power requirements</b>	100, 120, 220, or 240 V AC 50/60 Hz, 20 VA
<b>Weight</b>	3.3 lbs/1.5 kg
<b>Dimensions</b>	91 mm H, 109 mm W, 183 mm D 3.6" H, 4.3" W, and 7.2" D
<b>Input/output connector</b>	Type "N"
<b>Warranty</b>	3 year

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

[www.keysight.com/find/emc](http://www.keysight.com/find/emc)  
[www.keysight.com/find/accessories](http://www.keysight.com/find/accessories)

This information is subject to change without notice.  
© Keysight Technologies, 2009 - 2014  
Published in USA, July 31, 2014  
5968-1373E  
[www.keysight.com](http://www.keysight.com)