

Ixia Net Tool Optimizer[®]

Advanced Feature Module (AFM)

Reliable and Intelligent Packet Processing

For better network security and higher profits, enterprises today need complete and efficient access to the data that traverses their networks. Yet privacy compliance mandates strict control of corporate data and customer personally identifiable information (PII).

The Ixia Net Tool Optimizer (NTO) Advanced Feature Module (AFM) processes packets at line rate and prepares data for analysis by security and monitoring tools. It delivers advanced functions like real-time packet de-duplication, timestamping, and masking of personally identifiable information (PII). With AFM, enterprises can look deeper into their networks while maintaining compliance to privacy regulations and delivering higher security for their corporate and customer data.

Zero-loss: Because every packet counts

Ixia's primary competitive differentiator with AFM is its predictable, accurate, and lossless performance. The AFM architecture ensures that no data is lost under any conditions by dedicating high performance hardware to the advanced packet processing. Ixia's solution always delivers the full 160Gbps of traffic no matter the configuration or network conditions.

Other vendors' products often use software-based approaches to try to deliver similar functionality, but their solutions max out at 40Gbps or less. Even then, third-

Highlights

- Protects monitoring tools and helps them operate more effectively with all redundant packets removed, at full line rate with no loss
- Gives monitoring tools every packet they need, even when aggregate bandwidth exceeds port capacity
- Boosts tool performance and keeps sensitive user data secure by removing payload data from the monitored network traffic
- Removes PII, such as credit card or social security numbers, before providing the data to analysis tools
- Enables tools to analyze encapsulated traffic by removing VLAN or QinQ, GTP, MPLS, VNTag, VxLAN, FabricPath, ERSPAN, and L2GRE/NVGRE headers from the packet stream
- Terminates L2GRE tunnels from vTap and delivers plain Ethernet traffic to tools
- Enables tools that cannot process GTP header information to analyze the tunneled packets
- Allows latency-sensitive monitoring tools to know, with nanosecond resolution and accuracy, when a packet traverses a particular point in the network



party testing from Tolly¹ demonstrated that those products are unable to meet their advertised performance rating or guarantee steady results as network conditions change.

Key Features

Packet de-duplication – Packet duplicates occur in visibility networks when a packet traverses multiple taps or SPAN ports that generate multiple copies of the same packet. De-duplicating packets reduces the amount of redundant data sent to analysis tools, directly improving tool efficiencies and preserving tool integrity. Flexible configuration parameters allow ignoring specific headers and controlling whether the deduplication window is packet- or time-based (Up to 1/2 second for 10/40G and 1 second for 1G).

- **Extended burst protection** – Deep buffering allows monitoring tools to see every packet, even under microburst conditions where aggregate bandwidth temporarily exceeds port capacity. This condition commonly occurs when traffic from a high-speed network is adapted to feed a lower-speed tool. Ixia's extended burst protection allows data flow from higher-speed, bursty traffic to 1G tools.
- **Packet trimming** – Many monitoring tools, especially legacy ones, only need to analyze packet headers. In other monitoring applications, regulatory compliance requires tools remove sensitive data from captured network traffic. The AFM can remove payload data from the monitored network traffic, which boosts tool performance and keeps sensitive user data secure.
- **Protocol stripping** – Monitoring tools, legacy or even modern ones, cannot analyze traffic encapsulated inside of an unsupported protocol. The AFM enables tools to monitor all required data by removing VLAN or QinQ, GTP, MPLS, VxLAN, VNTag, FabricPath, ERSPAN, and L2GRE/NVGRE headers from the packet stream.
- **L2GRE tunnel termination** – Many virtual taps, including Ixia's Phantom vTap, will originate VM traffic in L2GRE encapsulation. AFM can terminate the L2GRE tunnel so plain Ethernet traffic can be directed to tools for processing; hence removing the burden of tunnel termination from the attached tools.
- **Data masking** – Network operators commonly need to remove PII, such as credit card or social security numbers, before providing the data to analysis tools. The AFM removes the data from the packet in real-time and replaces it with a fixed-field value before forwarding to security and monitoring tools.
- **Timestamping** – Network operators require high-accuracy timestamps on packets to correlate events with other device logs in low-latency financial data centers and to correlate traffic events across a WAN. AFM can insert a high-accuracy timestamp into every packet at ingress. Timestamp sources include local, NTP, and PTP (7300).
- **Double your ports** – Network operators need more density to address the space and power constraints of modern data centers. Ixia's innovative Double Your Ports (Simplex) feature enables the ports on an AFM module to be logically divided into two interfaces: one that connects to the network tap, and the other that connects to the security or monitoring tool. This configuration allows users to potentially double the number of active ports in use without adding any new hardware.

¹ <http://tolly.com/Docdetail.aspx?Docnumber=216100>

| Feature | AFM16 ports | AFM4Q ports | 311-AF "netport" | AFM2 ports |
|--------------------|-----------------|-------------|------------------|-----------------|
| De-duplication | X | X | - | X |
| Burst protection | X (1 Gbps only) | - | - | X (1 Gbps only) |
| Packet trimming | X | X | X | X |
| Protocol stripping | X | X | X | X |
| Data masking | X | - | - | - |
| Timestamping | X | X | X | X |
| Double your ports | X | - | X | - |

Specifications

| | AFM2 | AFM16 & 7300 cassette | AFM4Q | 7300 carrier | 7300 AFM netport |
|-------------------|---|--|---|---|---|
| Ports | 2x10G | 16x10G | 4x40G | 4x40G (non-advanced) 2x cassette bays | 8x40G and 16x10G |
| Size and weight | 4.4" x 7.2" x 1.0" (inches) 0.6lb (0.27kg) | 6.4" x 9.8" x 1.4" (inches) 2.25lbs (1.02kg) | 6.4" x 9.8" x 1.4" (inches) 2.25lbs (1.02kg) | 1.75" x 17.5" x 15" (inches) 18lbs (8.2kg) | 1.75" x 17.5" x 15" (inches) 14.8lbs (6.7kg) |
| Power consumption | 25W | 100W | 100W | 300W with 2x AFM16 Cassettes | 225W |
| Environmental | Operating temp: 0 to 30°C Operating humidity: 10 to 85%, noncondensing Fans: Automatic temperature-controlled DC fans | Operating temp: 5°C to 40°C Short-term* -5°C to 55°C Short-term* with fan failure: -5°C to 40°C *not to exceed 96 consecutive hours | | | |

Ordering Information

| Part number | Description |
|---|--|
| AFM4Q: Compatible with 7300 Family | |
| MOD-7315-IFMOD-AFM4 | 4x 40G Advance Feature Module Cassette |
| AFM16: Advanced Feature Module-16 (AFM16) – Compatible with NTO 5288, NTO 5293, NTO 5263, NTO 5268; up to four modules per unit | |
| MOD-P5200-X8D-ADV | 8 x 10G Optical SFP+ Ethernet Port Advanced Feature Module with - quantity 8 ports licensed |
| MOD-P5200-X16D-ADV | 16 x 10G Optical SFP+ Ethernet Port Advanced Feature Module with - quantity 16 ports licensed |
| LIC-P5200-X8D-ADV-UP | Upgrade MOD-P5200-X8D-ADV Advanced Feature Module to MOD-P5200-X16D-ADV |
| LIC-P5200-X4D-ADV-UP | License to enable four (4) additional advanced feature module (AFM) ports on a MOD-P5200-X8D-ADV module |
| AFM2: Compatible with 5236 and 5273; up to two modules per unit | |
| MOD-P5200-X2D-ADV | Advanced Feature Module with 10G or 1G Optical SFP/SFP+ Ethernet Ports - quantity two. Ports can be used with SFP or SFP+ transceivers |
| 7300 Carrier and 16-Port 10G Advance Feature Module Cassette | |
| MOD-7300-CARRIER | 7300- Carrier Line Module - This module provides four licensed 40G ports, and 2 optional cassette slots for advanced hardware features |
| MOD-7215-IFMOD-AFM16 | 7300- 16-Port 10G Advance Feature Module Cassette (992-0067) |
| 7300 AFM NetPort | |
| MOD-7311-IFMOD-AF | 7300 – Single, 8x40G and 16x10G advanced feature module |

Learn more at: www.keysight.com

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

