

Keysight Technologies

# N8241A Arbitrary Waveform Generator Synthetic Instrument Module

1.25 GSa/s or 625 MSa/s

Technical Overview



The Keysight Technologies, Inc. N8241A arbitrary waveform generator (AWG) is capable of creating high-resolution waveforms for radar, satellite, and frequency agile communication systems.

- 15 bits of vertical resolution per channel and either 1.25 Gigasamples per second (GSa/s) or 625 Megasample per second (MSa/s) provides exceptionally realistic wideband waveforms
- Dual output channels drive both single-ended and balanced designs without the need for baluns or hybrids
- Extended waveform memory and advanced sequencing engine offers long scenario simulations
- Multiple module synchronization provides multi-emitter simulations
- Multiple programmatic interfaces enable easy integration into existing test environments
- Fully compliant to LXI Class A standards 

## Generate Wide Bandwidth and Wide Dynamic Range Signals – Simultaneously

Each channel of the N8241A operates at either 1.25 GSa/s sample rate (Option 125) or 25 MSa/s sample rate (Option 062) and features 15 bits of vertical resolution giving designers the most realistic, wideband waveforms available from a commercial AWG. This LXI synthetic instrument module offers dual differential output channels to drive both single-ended and balanced designs. The AWG also supports advanced sequencing and triggering modes to create event-based signal simulations. Multiple N8241A modules can be synchronized for the generation of phase-coherent, multi-emitter scenarios. Waveform development tasks are simplified using the AWG's numerous programmatic interfaces including complete instrument control from the MATLAB® command line. When the N8241A is combined with a wideband I/Q upconverter, modulation bandwidths of 1 GHz can be realized at microwave frequencies for authentic signal simulations for IF and RF subsystem test.<sup>1</sup>

1. Keysight E8267D PSG signal generator with Option 016, wideband I/O inputs or Keysight N8211A performance vector upconverter with Option 016; either option could be used.




Figure 1. Generate wide band waveforms with unprecedented signal fidelity.

## Unprecedented performance

The N8241A gives designers access to the most advanced Digital-to-Analog (DAC) technology available in a commercial AWG. Each module incorporates two high-speed DACs to create 500 MHz of signal bandwidth and  $\leq -65$  dBc spurious free dynamic range (SFDR) across each channel. Users have the choice of driving their designs differentially from the DAC outputs or single-ended through multiple signal-conditioning paths.

Although some AWGs require users to make a trade-off between the number of output channels and differential outputs, the N8241A provides both – allowing you to drive your designs and eliminating the need for baluns or hybrids in the test path. In addition, each channel can output waveforms as an IF or as a baseband signal for I/Q upconversion.




Figure 2. Create sophisticated signal scenarios by looping and nesting waveforms.

### Create long scenario simulations

Multiply the effective size of on-board memory through the use of the N8241A's advanced sequencing engine. Uniquely define how waveform segments are played through looping and nesting of stored waveforms. This capability also gives users the ability to create new signals from existing waveforms by playing only subsegments of waveform memory.




Figure 3. Closing targets can be simulated by ranging parameters on each pulse.






Figure 5. Directly import and play waveforms from the Quick Play menu.




Figure 6. Play waveform files directly from the MATLAB command line.

## Enhanced Capabilities for the N8241

### Dynamic sequencing (Option 300)

The dynamic sequencing software enables radar and military communications engineers to build custom signal scenarios on the fly. Engineers can dynamically access up to 16 k of previously stored sequences through a 16-bit interface and replay these complex waveforms to respond to changing threat environments, or to create signals where the next waveform to be played is not known in advance.

### Direct digital synthesis (Option 330)

The direct digital synthesis (DDS) software enables radar and emerging communications engineers to create basic waveforms in the AWG's memory and then modify their behavior with profiles for amplitude modulation, phase modulation, and frequency modulation. This enables engineers to simulate testing without the time and expense of field trials, such as in-flight and in-orbit testing. This option can also be used to simulate fading profiles in receiver testing for satellite and 4 G signals, such as multiple input, and multiple output formats (MIMO).




Figure 7. Create signals where the next waveform to be played is not known in advance.




Figure 8. Define signals by carrier frequency and modulation – instant by instant.

## Key Characteristics

Channels	Two independent channels available as baseband or IF outputs <ul style="list-style-type: none"> <li>– CH1: Single-ended and differential</li> <li>– CH2: Single-ended and differential</li> </ul>	
Modulation bandwidth	1.25 GSa/s sample rate (Option 125) 500 MHz per channel (1 GHz I/Q bandwidth)	625 MSa/s sample rate (Option 062) 250 MHz per channel (500 MHz I/Q bandwidth)
Resolution	15 bits (1/32,768 levels)	
Output spectral purity – (CH1 and CH2)	1.25 GSa/s sample rate (Option 125)	625 MSa/s sample rate (Option 062)
Harmonic distortion <ul style="list-style-type: none"> <li>– Non-harmonic spurious</li> <li>– Noise floor</li> </ul>	<ul style="list-style-type: none"> <li><math>\leq -65</math> dBc for each channel DC to 500 MHz</li> <li><math>\leq -75</math> dBc for each channel 1 kHz to 500 MHz</li> <li><math>\leq -150</math> dBc/Hz across the channel bandwidth</li> </ul>	<ul style="list-style-type: none"> <li><math>\leq -65</math> dBc for each channel DC to 250 MHz</li> <li><math>\leq -75</math> dBc for each channel 1 kHz to 250 MHz</li> <li><math>\leq -150</math> dBc/Hz across the channel bandwidth</li> </ul>




Figure 9. Excellent harmonic and spurious performance are available across the full bandwidth of each channel.




Figure 10. Spurious performance outstanding at low signal frequencies.

Sample clock	
Internal	Fixed 1.25 GSa/s (Option 125) Fixed 625 MSa/s (Option 062)
Internal clock output	+3 dBm nominal
External clock input	Tunable 100 MS/s to 1.25 GSa/s (Option 125) Tunable 100 MS/s to 625 MSa/s (Option 062)
External clock input drive level	+5 to -15 dBm typical
Phase noise characteristics	
1 kHz	-95 dBc/Hz
10 kHz	-115 dBc/Hz
100 kHz	-138 dBc/Hz
1 MHz	-150 dBc/Hz
Noise floor	-150 dBc/Hz
Accuracy	Same as 10 MHz timebase input

## Key Characteristics (continued)

Frequency reference	
Input drive level	+2 to +12 dBm into 50 ohms (+2 dBm nominal)
Waveform length	8 MSa per channel (16 MSa with Option 016)
Minimum waveform length	128 samples
Waveform granularity	8 samples
Segments	1 to 32 k unique segments can be defined consisting of waveform start and stop address, repetitions, and marker enable flags.
Segment loops	A total of 1 million (220) loops can be defined for each segment. Loops can be configured to advance in one of four modes:
Single	The segment loop plays once and waits at the end of the loop for a trigger.
Continuous	Segment loop is repeated continuously until a trigger is received.
Auto	Automatically advances to the next segment after completing the specified number of loop repetitions.
Repeat	The waveform loop repeats until the number of waveform loop repetitions is met.
Sequences	Up to 32 k total unique waveform sequences can be defined. A sequence is a contiguous series of waveform segments.
Advanced sequencing	Enables users to build and playback scenarios, which are comprised of one or more sequences.
Scenarios	1 to 16 k pointers can be assigned to play pre-defined sequences. Sequence play begins with the first sequence entry and continues uninterrupted until the last entry is played. The table repeats until stopped.
Sequence jump modes	Sequence jumps determine how a sequence responds to a jump trigger. There are no discontinuities in a sequence jump other than those imposed by the waveform data. Three modes are available to control sequence jumps:
Jump immediate	Jumps immediately to the next specified sequence address with a fixed latency.
End of waveform	The current segment (including waveform repeats) is completed before jumping to a new sequence.
End of sequence	The current sequence is completed before jumping to a new sequence. Jump latency is the longer of either the jump immediate latency or the length of the remaining sequence.
<b>Dynamic sequencing (Option 300)</b>	
Input	20-pin mini-D connector
Input levels	All pins configured as 2.5 V LVCMOS inputs. A logic low must fall within the -0.2 to +0.5 V window. A logic high must be within the window of +2.0 to +2.8 V.
Number of address bits	13 bits per channel
Total number of addressable scenarios	16 k
Data rate for dynamic data	100 ns
Data latency	Same as front panel trigger inputs. Software pointers may also be used to point to pre-defined scenarios, though latencies are not deterministic.
<b>Direct digital synthesis (Option 330)</b>	
Output frequency resolution	1 Hz
Frequency modulation	Deviation from 0 to 125 MHz (250 MHz peak-peak)
Phase modulation	Deviation from -180 to +180 degrees in 0.022 degree steps
Amplitude modulation	Modulation depth from 0 to 100% with 15 bit resolution
Single channel bandwidth	400 MHz (800 MHz I/Q)

## Key Characteristics (continued)

<b>External triggers</b>	
Number of inputs	8 each (4 SMB female front-panel connectors plus four software triggers over the LXI interface from host processor)
Trigger polarity	Negative/positive
Trigger impedance	2 k ohms
Maximum input level	± 4.5 V
Input sensitivity	250 mV
Trigger threshold	-4.3 V to +4.3 V
Trigger timing resolution (clock/8)	
Option 125	6.4 ns at 1.25 GSa/s rate
Option 062	12.8 ns at 625 MSa/s rate
Trigger latency (34 x clock/8)	
Option 125	217.6 ns at 1.25 GSa/s rate
Option 062	435.2 ns at 625 MSa/s rate
Trigger uncertainty	< 50 ps
Minimum trigger width	
Option 125	12.8 ns at 1.25 GSa/s clock rate
Option 062	25.6 ns at 625 MSa/s clock rate
Trigger delay	Programmable from 1 to 256 sync clock cycles with 1 sync clock cycle resolution <sup>1</sup>
<b>LXI triggering modes</b>	
Driver command based	A driver interface on the controlling computer is used to directly transmit a command to the module.
Direct LAN messaging	A data packet containing triggering information (including a time stamp) is sent directly from one module to another via the LAN.
Time based events	An IEEE 1588 based time trigger is set and executed internally in a module.
LXI trigger bus-based	A module function is triggered via a voltage on the LXI trigger bus.
The LXI triggering conforms to the specifications of the LXI standard, revision 1.0, <a href="http://www.lxistandards.org">www.lxistandards.org</a>	
<b>External markers</b>	
Markers	Can be defined for each waveform segment.
Number of outputs	4 each SMB female
Marker polarity	Negative, positive
Output impedance	50 ohms
Marker low level	100 mV nominal into high impedance load
Marker high level	3.2 V nominal into high impedance load
Marker timing resolution (clock/8)	
Option 125	6.4 ns at 1.25 GSa/s rate
Option 062	42.8 ns at 625 MSa/s rate
Marker latency	Marker precedes analog output and is adjustable in 2 sample clock period steps.
Marker latency repeatability	< 100 ps
Marker width	Programmable from 1 to 256 sync clock cycles <sup>1</sup>
Marker delay	Programmable from 8 to 502 sample clock cycles, with 2 sample clock cycle resolution
LXI markers	Two LXI markers are available
Module synchronization	Supports system scaling for any number of N8241A modules. A single module can support a fan-out of 8 N8241A modules for precise triggering and repeatability. Driver boards may be used to scale any number of modules.
Sync clock output level	800 mV p-p (50 ohms, AC coupled)
Sync clock input sensitivity	100 mV p-p minimum into 50 ohms AC coupled

1. A sync clock cycle is clock/8

## Key Characteristics (continued)

<b>Analog output</b>	
Output connector	SMA female
Output impedance	50 ohms
Analog output levels	The following output levels are specified into 50 ohms
	Single-ended                      Differential
Passive mode	0.5 V <sub>p-p</sub> N/A
Active mode	1 V <sub>p-p</sub> with ± 0.2 V offset      N/A
Direct DAC mode	N/A                                      1 V <sub>p-p</sub> (0 V offset)
Uncorrected passband flatness	± 1 dB DC to 200 MHz; ± 2.5 dB DC - 500 MHz (with 1.25 GHz clock)
Uncorrected passband group delay	± 500 ps DC to 200 MHz; ± 1 ns DC - 500 MHz (with 1.25 GHz clock)
Reconstruction filters	500 MHz and 250 MHz realized as 7-pole Cauer Chebychev filters plus thru-line output
Pulse response	
Rise time (10 to 90%)	< 1 ns
Fall time (10 to 90%)	< 1 ns
Amplitude	0.5 V <sub>p-p</sub>
<b>LXI Class A certified</b>	
<b>Power</b>	
Line power	100/120/220/240 VAC, 50/60 Hz, 100 W maximum
<b>Environmental</b>	Samples of this product have been type tested in accordance with the Keysight Environmental Test Manual and verified to be robust against the environmental stresses of storage, transportation, and end-use; those stresses include, but are not limited to temperature, humidity, shock vibration, altitude, and power line conditions. Test methods are aligned with IEC 60068-2 and levels are similar to MIL-PRF-28800F Class 3.
Operating temperature	0 to +50 °C (0 to 47 °C at 15,000 ft altitude)
Storage temperature	-40 to +70 °C
<b>Relative humidity</b>	
Type tested	0 to 95% at 40 °C (non-condensing)
Altitude	0 to 4500 m (15,000 ft) above sea level
<b>Weight</b>	5.66 kg (12.5 lb)
<b>Security</b>	All user data stored in volatile memory
<b>Dimensions</b>	
Height	89 mm (3.5 inch)
Width	213 mm (8.375 inch)
Depth	422 mm (16.625 inch)
<b>ISO compliance</b>	This instrument is manufactured in an ISO-9001 registered facility in concurrence with Keysight Technologies, Inc. commitment to quality. <ul style="list-style-type: none"> <li>- Electrostatic Discharge Immunity – IEC 61000-4-2: passes criterion C</li> </ul> Testing according to IEC 61000-4-2: showed that the exposure of the data port to electrostatic discharge may interrupt operation of the N8241A/42A. Operation can be restored by reloading the desired waveforms and restarting. This required operator intervention results in a criterion C classification.

## Ordering Information



Figure 11. Keysight N8241A 15-bit arbitrary waveform generator LXI module

## N8241A 15-bit arbitrary waveform generator with 8 MS memory per channel

Options	
N8241A-125	1.25 GSa/s sample rate
N8241A-062	625 MSa/s sample rate
N8241A-016	Waveform memory expansion to 16 MSa per channel
N8241A-300	Enabling software for 16-bit dynamic sequencing
N8241A-330	Direct digital synthesis software

## Web Resources

Visit our Web sites for additional product information and literature.

N8241A 15-bit arbitrary waveform generator:

[www.keysight.com/find/synthetic](http://www.keysight.com/find/synthetic)

N6030A Series of arbitrary waveform generators:

[www.keysight.com/find/awg](http://www.keysight.com/find/awg)

Signal simulation systems:

[www.keysight.com/find/signalsimulation](http://www.keysight.com/find/signalsimulation)

Aerospace and defense test and measurement products and services:

[www.keysight.com/find/ad](http://www.keysight.com/find/ad)

Test and measurement accessories:

[www.keysight.com/find/accessories](http://www.keysight.com/find/accessories)

## Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

### Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

### Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

### Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus) (BP-9-7-17)

**DEKRA Certified**  
ISO 9001 Quality Management System

[www.keysight.com/go/quality](http://www.keysight.com/go/quality)  
Keysight Technologies, Inc.  
DEKRA Certified ISO 9001:2015  
Quality Management System

### myKeysight

#### myKeysight

[www.keysight.com/find/mykeysight](http://www.keysight.com/find/mykeysight)

A personalized view into the information most relevant to you.

[http://www.keysight.com/find/emt\\_product\\_registration](http://www.keysight.com/find/emt_product_registration)

Register your products to get up-to-date product information and find warranty information.

### KEYSIGHT SERVICES

Accelerate Technology Adoption.  
Lower costs.

#### Keysight Services

[www.keysight.com/find/service](http://www.keysight.com/find/service)

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



#### Keysight Assurance Plans

[www.keysight.com/find/AssurancePlans](http://www.keysight.com/find/AssurancePlans)

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

#### Keysight Channel Partners

[www.keysight.com/find/channelpartners](http://www.keysight.com/find/channelpartners)

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.



Unlocking Measurement Insights

This information is subject to change without notice.  
© Keysight Technologies, 2017  
Published in USA, December 1, 2017  
5989-2595EN  
[www.keysight.com](http://www.keysight.com)