


M9300A PXIe Frequency Reference

Overview

Product description

The Keysight Technologies, Inc. M9300A PXIe frequency reference is a PXIe modular instrument that can be used as a 10 MHz or 100 MHz reference in various solutions. A single M9300A can be shared with up to four PXI VSAs, VSGs or VXTs in one chassis, as shown in Figure 1, to form a multi-channel solution.

Instrument control is provided through a soft front panel and programmatic interfaces tuned to your application development environment of choice.



Product features

- Locks to another reference with a value from 1 to 110 MHz.
- Five 100 MHz outputs
- One 10 MHz output
- Internal 10 MHz OCXO timebase output

Uncompromising values

- Reduces development time and simplifies integration into existing test environments with multiple drivers and programmatic interfaces.
- Reduces startup time with Keysight IO libraries easy configuration, one-step software install, and soft front panel.
- Fast repair turnaround time with Calibrated Core Exchange strategy.



Figure 1. M9300A PXIe Frequency Reference inserted in slot 10, above, can be shared with four M9393A PXIe Vector Signal Analyzers in one chassis.

Technical Specifications and Characteristics

Block diagram




Figure 2. M9300A PXIe frequency reference block diagram.

Definitions for specifications

Temperatures referred to in this document are defined as follows:

- Operating ambient temperature = 0 to 55 °C and individual module temperature of ≤ 75 °C
- Room temperature = 20 to 30 °C and individual module temperature of ≤ 55 °C

Specifications describe the warranted performance of calibrated instruments. Data represented in this document are specifications unless otherwise noted.

Specifications are warranted under the following conditions:

- Calibrated instruments that have been stored for a minimum of 2 hours within the operating ambient temperature range
- 30 minute warm-up time
- Calibration cycle maintained

Characteristics describe product performance that is useful in the application of the product. Characteristics are often referred to as Typical or Nominal values and are italicized.

- **Typical** describes characteristic performance, which 80% of instruments will meet when operated at room temperature.
- **Nominal** describes representative performance that is useful in the application of the product when operated at room temperature.

Note: All graphs contain measured data from several units at room temperature unless otherwise noted.

Recommended best practices in use

- Use slot blockers and EMC filler panels in empty module slots to ensure proper operating temperatures.
- Keysight chassis and slot blockers optimize module temperature performance and reliability of test.
- At operating ambient temperatures above 45 °C, chassis fan should be set to high.

| Reference outputs | |
|--|--|
| 100 MHz Out (Out 1 through Out 5) | |
| Amplitude | ≥ 10 dBm, <i>13 dBm, typical</i> |
| Connectors | SMB (M) 5 ports |
| Impedance | <i>50 Ω, nominal</i> |
| 10 MHz Out | |
| Amplitude | <i>9.5 dBm, nominal</i> |
| Connectors | SMB (M) 1 port |
| Impedance | <i>50 Ω, nominal</i> |
| OCXO Out | |
| Amplitude | <i>11.5 dBm, nominal</i> |
| Connectors | SMB (M) 1 port |
| Impedance | <i>50 Ω, nominal</i> |

| Phase noise | Offset | 100 MHz/10 MHz/OCXO Out, dBc/Hz, nominal |
|-------------|---------|--|
| Standard | 10 Hz | -97/-117/-124 |
| | 100 Hz | -127/-147/-140 |
| | 1 kHz | -157/-165/-146 |
| | 10 kHz | -169/-173/-147 |
| | 100 kHz | -173/-181/-161 |
| | 1 MHz | -174/-182/-162 |
| Option S01 | 10 Hz | -91/-111/-124 |
| | 100 Hz | -114/-135/-140 |
| | 1 kHz | -139/-158/-146 |
| | 10 kHz | -160/-172/-147 |
| | 100 kHz | -173/-177/-161 |
| | 1 MHz | -174/-178/-162 |

| Frequency accuracy | |
|--|---|
| Same as accuracy of internal time base or external reference input | |
| Internal timebase | |
| Accuracy | \pm (time since last adjustment x aging rate) |
| | \pm temperature effects |
| | \pm calibration accuracy |
| Frequency stability - Aging rate | |
| Daily | $< \pm .5$ ppb/day, after 72 hour warm-up |
| Yearly | $< \pm .10$ ppm/year, after 72 hours warm-up |
| Total 10 years | $< \pm 0.6$ ppm/10yrs, after 72 hours warm-up |
| Achievable initial calibration accuracy (at time of shipment) | |
| | $\pm 5 \times 10^{-8}$ |
| Frequency stability - Temperature effects | |
| 20 to 30 °C | $< \pm 10$ ppb |
| Full temperature range | $< \pm 50$ ppb |
| External reference input | |
| Frequency | 1 MHz to 110 MHz, sine wave |
| Lock range | ± 1 ppm, nominal |
| Amplitude | 0 to 10 dBm, nominal |
| Connector | SMB (M) 1 port |
| Impedance | 50 Ω , nominal |

| Environmental and physical specifications | | |
|---|--|---------------|
| Temperature | Operating | 0 to 55 °C |
| | Non-Operating (Storage) | -40 to +70 °C |
| Humidity ¹ | Type tested at 95%, +40 °C (non-condensing) | |
| Altitude | Up to 15,000 feet (4,572 meters) | |
| EMC | Complies with European EMC Directive 2004/108/EC | |
| | • IEC/EN 61326-2-1 | |
| | • CISPR Pub 11 Group 1, class A | |
| | • AS/NZS CISPR 11 | |
| | • ICES/NMB-001 | |
| This ISM device complies with Canadian ICES-001. | | |
| Cet appareil ISM est conforme a la norme NMB-001 du Canada. | | |
| Warm-up time | 30 minutes | |
| Size | 1 PXIe slot | |
| Dimensions | Length 210 mm, Width 22 mm, Height 130 mm | |
| Weight | 0.551 kg (1.215 lbs) | |
| Power drawn from chassis | ≤ 18 W | |
| System requirements | | |
| Operating systems | Windows 7 (32-bit and 64-bit) | |
| Processor speed | 1 GHz 32-bit (x86), 1 GHz 64-bit (x64) (no support for Itanium 64) | |
| Available memory | 4 GB minimum | |
| | 8 GB or greater recommended | |
| Available disk space ² | 1.5 GB available hard disk space, includes: | |
| | • 1 GB available for Microsoft .NET Framework 3.5 SP1 | |
| | • 100 MB for Keysight IO Libraries Suite | |
| Video | Support for DirectX 9 graphics with 128 MB graphics memory recommended (Super VGA graphics is supported) | |
| Browser | Microsoft Internet Explorer 7.0 or greater | |

1. Samples of this product have been type tested in accordance with the Keysight Environmental Test Manual and verified to be robust against the environmental stresses of Storage, Transportation and End-use; those stresses include but are not limited to temperature, humidity, shock, vibration, altitude and power line conditions. Test Methods are aligned with IEC 60068-2 and levels are similar to MIL-PRF-28800F Class 3.
2. NET framework runtime components are installed by default with Windows 7. Therefore, you may not need this amount of available disk space.

Software

| Instrument connection software | | | |
|---|----------------------------------|--|---|
|  | <p>Keysight IO Library</p> | <p>The Suite offers a single entry point for connection to the most common instruments including AXIe, PXI, GPIB, USB, Ethernet/LAN, RS-232, and VXI test instruments from Keysight and other vendors. It automatically discovers interfaces, chassis, and instruments. The graphical user interface allows you to search for, verify and update IVI instrument and soft front panel drivers for modular and traditional instruments. The Suite safely installs in side-by-side mode with NI I/O software.</p> | <p>Free software download at www.keysight.com/find/iosuite</p> |
| Module setup and usage | | | |
|  | <p>Keysight Soft Front Panel</p> | <p>The PXI module includes a Soft Front Panel (SFP), a software-based Graphical User Interface (GUI) which enables the instrument's capabilities from your PC.</p> | <p>Included on CD-ROM shipped with module or online</p> |
| Programming | | | |
| Driver | Development environments | | |
| IVI-COM | Visual Studio | | |
| IVI-C | (VB.NET, C#, C/C++) | | |
| LabVIEW | VEE | | |
| MATLAB | LabVIEW, LabWindows/CVI, MATLAB | | |
| Programming assistance | | | |
|  | <p>Command Expert</p> | <p>Assists in finding the right instrument commands and setting correct parameters. A simple interface includes documentation, examples, syntax checking, command execution and debug tools to build sequences for integration in Excel, MATLAB, Visual Studio, LabVIEW, VEE, SystemVue.</p> | <p>Free software download at www.keysight.com/find/commandexpert</p> |

| Calibration and traceability | | |
|--|--|---|
| Factory Calibration | The M9300A PXIe Frequency Reference ships factory calibrated with an ISO-9002, NIST-traceable calibration certificate. | Included in base configuration |
| Calibration Cycle | A one year calibration cycle is recommended | |
| Calibration Sites | At Keysight's Worldwide Service Centers | More information visit www.keysight.com/find/infoline |
| | On-site by Keysight | |
| | By self-maintainers | |
| R1282A Annual Calibration Service | Keysight Calibration | Additional service, not included in the warranty |
| | Keysight Calibration + Uncertainties | |
| | Keysight Calibration + Uncertainties + Guardbanding | |
| | Standards Compliance ANSI Z540.3-2006, ISO 17025:2005, ANSI Z540-1-1994, ISO 9001:2008 | |
| N7800A Calibration and Adjustment Software | The M9300A is supported by Keysight's Calibration and Adjustment Software. This is the same software used at Keysight Service Centers to automate calibration. The software offers compliance tests for ISO 17025:2005, ANSI/NCSL Z540.3-2006, and measurement uncertainty per ISO Guide to Expression of Measurement Uncertainty. | Licensed software. For more information, visit www.keysight.com/find/calibrationsoftware |
| Keysight Calibration Status Utility | The Keysight Calibration Status utility helps ensure your M9300A is calibrated by managing the calibration interval and providing messages regarding instrument and module calibration status. | Included in base configuration |

Support

| Support | | |
|-----------------------|---|---|
| Core Exchange Program | Keysight's Replacement Core Exchange program allows fast and easy module repairs. A replacement core assembly is a fully functioning pre-calibrated module replacement that is updated with the defective module serial number, allowing the replacement module to retain the original serial number. | For qualified self-maintainers in US only |
| Self-Test Utility | A self-test utility runs a set of internal tests which verifies the health of the modules and reports their status | Included in base configuration |

Configuration and Ordering Information

Ordering Information

| Model | Description |
|--------|--|
| M9300A | PXIe Frequency Reference Includes: Software, example programs and product information on CD |

Software Information

| | Description |
|--|--|
| Supported operating systems | Microsoft Windows 7 (32/64-bit) |
| Standard compliant drivers | IVI-COM, IVI-C, LabVIEW, MATLAB |
| Supported application development environments (ADE) | VisualStudio (VB.NET, C#, C/C++), VEE, LabVIEW, LabWindows/CVI, MATLAB |
| Keysight IO Libraries(version 16.3 or newer) | Includes: VISA Libraries, Keysight Connection Expert, IO Monitor |

Accessories

| Model | Description |
|--------|--|
| Y1212A | Slot Blocker Kit: 5 modules |
| Y1213A | PXI EMC Filler Panel Kit: 5 slots |
| Y1214A | Air Inlet Kit: M9018A 18-slot chassis |
| Y1215A | Rack Mount Kit: M9018A 18-slot chassis |

Related Products

| Model | Description |
|--------|---|
| M9393A | PXIe Performance Vector Signal Analyzer |
| M9391A | PXIe Vector Signal Analyzer |
| M9381A | PXIe Vector Signal Generator |
| M9380A | PXIe CW Source |
| M9420A | PXIe Vector Transceiver |
| M9018A | 18-slot PXIe Chassis |
| M9037A | PXIe Embedded Controller |
| M9036A | PXIe Embedded Controller |
| M9393A | PXIe Performance Vector Signal Analyzer |
| M9391A | PXIe Vector Signal Analyzer |
| M9381A | PXIe Vector Signal Generator |

| Advantage services: Calibration | |
|---|-------------------------------------|
| Keysight Advantage Services is committed to your success throughout your equipment's lifetime | |
| N7800A | Calibration and Adjustment Software |

Learn more at: www.keysight.com

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

