

# Keysight Technologies

## E3620A and E3630A

### Non-programmable DC Power Supplies

Data Sheet



## Reliable Power, Repeatable Results

- Linear power supply
- Dual or triple output
- 10-turn voltage and current control
- Low noise and excellent regulation



## Affordable, Full-Featured Benchtop Power Supplies Provide Excellent Performance and Flexibility

### Multiple-output non-programmable models

The Keysight Technologies, Inc. E3620A and E3630A low-cost benchtop power supplies give you the performance of system power supplies at a decent price. Both supplies provide clean power with excellent regulation and a fast transient response.

With multiple supplies in a compact unit, the E3620A and E3630A provide excellent performance while saving space on your bench. Both instruments feature a tight 0.01 percent line and load regulation and a low normal mode noise specification of less than 0.35 mV to ensure clean power for precision circuitry. With a common mode current specification of less than 1  $\mu$ A, both multiple-output power supplies minimize the power line current injection.

The E3620A and E3630A feature separate digital panel meters so you can monitor the voltage and current simultaneously. They also protect your DUT against overload and short-circuit damage.

Smooth turn-on and turn-off transitions keep power spikes out of your circuits. Auto-tracking permits equal or proportional voltage sharing, and allows control of output voltage from one master unit. The master and slave supplies have the same output polarity with respect to a common bus or ground. This operation is useful where simultaneous turn-up, turn-down or proportional control of all power supplies is required.

### E3620A dual-output power supply

The 50-watt E3620A dual-output power supply provides two 0 V to 25 Vdc outputs with the maximum current of 1 A to satisfy most bench requirements. The outputs are completely independent and isolated.

### E3630A triple-output power supply with auto-tracking feature

The 35-watt E3630A triple-output power supply provides three DC outputs: 0 to 6 V with a maximum current of 1 to 2.5 A and 0 to 20 V and 0 to  $\pm$ 20 V with a maximum current of 0.5 A. An auto-tracking feature lets you use one voltage control to adjust the +20 V and  $\pm$ 20 V outputs simultaneously. The outputs track each other to within 1 percent, making it easy to adjust the power supply for circuits requiring balanced voltages.

## Specifications

	<b>E3620A</b>	<b>E3630A</b>
Features	Isolated dual outputs, 10 turn pots CV, CL	Tracking, CV, CL ( $\pm 20$ V) CV, CF (+6 V)
Number of outputs	2	3
Number of output ranges	1	1
DC output rating	25 V, 1 A 25 V, 1 A	+6 V, 2.5 A +20 V, 0.5 A -20 V, 0.5 A
Load and line regulation	< 0.01% + 2 mV	
Ripple and Noise (20 Hz to 20 MHz)		
Normal mode voltage	< 350 $\mu$ Vrms, < 1.5 mVpp	
Normal mode current	-	
Transient response time	< 50 $\mu$ sec following a change in output current from full load to half load for output to recover within: 15 mV	
Meter accuracy	$\pm 0.5\%$ + 2 counts at 25 °C $\pm 5$ °C	

## Supplemental Characteristics

	<b>E3620A</b>	<b>E3630A</b>
Control mode	CV/CL	CV/CL ( $\pm 20$ V) CV/CF (+ 6 V)
Common mode current	< 1 $\mu$ Arms	
Meter resolution		
Voltage	10 mV (0–20 V), 100 mV (> 20 V)	10 mV
Current	1 mA	10 mA
Temperature coefficient per °C		
Voltage	< 0.02% + 1 mV	
Current	-	
Output Drift		
Voltage	Less than 0.1% + 5 mV total drift for 8 hours after initial warm-up of 30 minutes	
Current	N/A	
Temperature range	Derate output current 50% between 40 °C to 55 °C	
Cooling	Convection cooling	
Isolation	$\pm 240$ Vdc	
AC Input	100 Vac $\pm 10\%$ , 47–63 Hz (opt. 0E9) 115 Vac $\pm 10\%$ , 47–63 Hz (std) 230 Vac $\pm 10\%$ , 47–63 Hz (0E3)	
Weight	5.0 kg (11.0 lbs) net, 6.25 kg (13.8 lbs) shipping	3.8 kg (8.4 lbs) net, 5.1 kg (11.3 lbs) shipping
Size	88.1 mm H x 212.3 mm W x 392.4 mm D 3.5" H x 8.4" W x 15.4" D	88.1 mm H x 212.3 mm W x 318.4 mm D 3.5" H x 8.4" W x 12.5" D
Warranty	Three year for E3600 Series power supplies Three months for standard shipped accessories	
Product regulation	Certified to CSA 22.2 No. 231; conforms to IEC 1010-1; carries CE mark; complies with CISPR-11, Group 1, Class A, KC South Korean EMC Mark, Canadian ICES/NMB-001, Australian C Tick Mark	

### Ordering information

E3620A Dual-output power supply  
E3630A Triple-output power supply

### Standard shipped accessories

Product reference CD, power cord

### Power options

Opt. 0E3 230 Vac  $\pm 10\%$   
Opt. 0EM 115 Vac  $\pm 10\%$   
Opt. 0E9 100 Vac  $\pm 10\%$

### Other options

Opt. 1CM or 34190A rackmount kit\*  
(Only applicable for E3620A)  
Opt. UK6 Commercial calibration  
certificate with test result data  
E3600A-100 Test lead kit

### Manual sets

Please visit  
[www.keysight.com/find/manuals](http://www.keysight.com/find/manuals)  
for the latest revisions of manuals.

### Rackmount kits\*

E3620A  
To rackmount two instruments  
side-by-side  
– Lock-link Kit (P/N 5061-9694)  
– Flange Kit (P/N 5063-9212) or 34191A

To rackmount one or two instruments in  
a sliding support shelf  
– Support Shelf (P/N 5063-9255)  
– Slide Kit (P/N 1494-0015) required  
for support shelf


For a single instrument, also order filler  
panel (P/N 5002-3999)

\* Rackmounting with 1CM or lock-link/flange kit  
requires  
– Keysight or customer support rails  
– Keysight Support Rails-E3663AC.

## Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

### Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

### Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

### Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:

[www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)  
(BP-9-7-17)

**DEKRA Certified**  
ISO9001 Quality Management System

[www.keysight.com/go/quality](http://www.keysight.com/go/quality)  
Keysight Technologies, Inc.  
DEKRA Certified ISO 9001:2015  
Quality Management System

### myKeysight

#### myKeysight

[www.keysight.com/find/mykeysight](http://www.keysight.com/find/mykeysight)

A personalized view into the information most relevant to you.

[http://www.keysight.com/find/emt\\_product\\_registration](http://www.keysight.com/find/emt_product_registration)

Register your products to get up-to-date product information and find warranty information.

**KEYSIGHT SERVICES**  
Accelerate Technology Adoption.  
Lower costs.

#### Keysight Services

[www.keysight.com/find/service](http://www.keysight.com/find/service)

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.

#### Keysight Assurance Plans

[www.keysight.com/find/AssurancePlans](http://www.keysight.com/find/AssurancePlans)

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

#### Keysight Channel Partners

[www.keysight.com/find/channelpartners](http://www.keysight.com/find/channelpartners)

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.



This information is subject to change without notice.  
© Keysight Technologies, 2009 - 2018  
Published in USA, May 3, 2018  
5968-9727EN  
[www.keysight.com](http://www.keysight.com)