

## Keysight Technologies

### BenchVue Software

# BV0004B Oscilloscope Control & Automation App

## 2020 Version Information

---

Released Date: June 8, 2020

### Requirements categories

---

PC operating system & hardware: Windows 10: 32-bit and 64-bit (Professional, Enterprise, Education, Home versions)  
Processor: 1 GHz or faster (2 GHz or greater recommended)  
RAM: 1 GB (32-bit) or 2 GB (64-bit) (3 GB or greater recommended)  
Interfaces: USB, GPIB, LAN, RS-232  
Display resolution: 1280x1024 minimum recommended for single instrument view (higher resolution recommended for multiple instrument view)

---

**Mobile Devices:** (for companion BenchVue Mobile app) Apple iPhone, iPad, iPod Touch all models; iOS 12.0 and later.

Android phone and tablets; Android 4.0.3 and later.

---

Current List of BenchVue Enabled Keysight Instruments: [www.keysight.com/find/benchvueinstruments](http://www.keysight.com/find/benchvueinstruments)

---

File Name: BenchVueScope\_2020.exe

## Notable changes

- Added support for EDUX1052A, EDUX1052G, DSOX1202A, DSOX1202G

## 2019 Update 1 Version Information

Released Date:	September 18, 2019
<b>Requirements categories</b>	
PC operating system & hardware:	Windows 10: 32-bit and 64-bit (Professional, Enterprise, Education, Home versions) Windows 8, 8.1: 32-bit and 64-bit (Professional, Enterprise, Core) Windows 7: SP1 and later 32-bit and 64-bit (Professional, Enterprise, Ultimate, Home Basic, Home Premium) Processor: 1 GHz or faster (2 GHz or greater recommended) RAM: 1 GB (32-bit) or 2 GB (64-bit) (3 GB or greater recommended) Interfaces: USB, GPIB, LAN, RS-232 Display resolution: 1280x1024 minimum recommended for single instrument view (higher resolution recommended for multiple instrument view)
<b>Mobile Devices:</b> (for companion BenchVue Mobile app)	Apple iPhone, iPad, iPod Touch all models; iOS 7.0 and later.  Android phone and tablets; Android 4.0.3 and later.
Current List of BenchVue Enabled Keysight Instruments:	<a href="http://www.keysight.com/find/benchvueinstruments">www.keysight.com/find/benchvueinstruments</a>
File Name:	BenchVueScope_2019_Update1.0.exe

### Notable changes

- Defects fixed for stability and usability
- Minor UI changes
- Usability improvements to save traces in BenchVue and recall in BenchVue.

## 2019 Version Information

Released Date:	March 18, 2019
<b>Requirements categories</b>	
PC operating system & hardware:	Windows 10: 32-bit and 64-bit (Professional, Enterprise, Education, Home versions) Windows 8, 8.1: 32-bit and 64-bit (Professional, Enterprise, Core) Windows 7: SP1 and later 32-bit and 64-bit (Professional, Enterprise, Ultimate, Home Basic, Home Premium) Processor: 1 GHz or faster (2 GHz or greater recommended) RAM: 1 GB (32-bit) or 2 GB (64-bit) (3 GB or greater

---

	recommended) Interfaces: USB, GPIB, LAN, RS-232 Display resolution: 1280x1024 minimum recommended for single instrument view (higher resolution recommended for multiple instrument view)
<b>Mobile Devices:</b> (for companion BenchVue Mobile app)	Apple iPhone, iPad, iPod Touch all models; iOS 7.0 and later.  Android phone and tablets; Android 4.0.3 and later.
Current List of BenchVue Enabled Keysight Instruments:	<a href="http://www.keysight.com/find/benchvueinstruments">www.keysight.com/find/benchvueinstruments</a>
File Name:	BenchVueSCOPEsetup_2019.exe

---

### Notable changes

- Defects fixed for stability and usability
- Added support for DSOX1204A and DSOX1204G.
- Added support for P9241A, P9242A, P9243A USB Streamline oscilloscopes

## 2018 Version Information

Released Date:	February 16, 2018
<b>Requirements categories</b>	
PC operating system & hardware:	<p>Windows 10: 32-bit and 64-bit (Professional, Enterprise, Education, Home versions)</p> <p>Windows 8, 8.1: 32-bit and 64-bit (Professional, Enterprise, Core)</p> <p>Windows 7: SP1 and later 32-bit and 64-bit (Professional, Enterprise, Ultimate, Home Basic, Home Premium)</p> <p>Processor: 1 GHz or faster (2 GHz or greater recommended)</p> <p>RAM: 1 GB (32-bit) or 2 GB (64-bit) (3 GB or greater recommended)</p> <p>Interfaces: USB, GPIB, LAN, RS-232</p> <p>Display resolution: 1280x1024 minimum recommended for single instrument view (higher resolution recommended for multiple instrument view)</p>
<b>Mobile Devices:</b> (for companion BenchVue Mobile app)	<p>Apple iPhone, iPad, iPod Touch all models; iOS 7.0 and later.</p> <p>Android phone and tablets; Android 4.0.3 and later.</p>
Current List of BenchVue Enabled Keysight Instruments:	<a href="http://www.keysight.com/find/benchvueinstruments">www.keysight.com/find/benchvueinstruments</a>
File Name:	BenchVueSCOPEsetup.exe

## Notable changes

- Defects fixed for stability and usability
- Added live trace streaming to Instrument Settings tab.
- Upgraded Screen Image tab to Quick capture and save operation.
- Added a Web-based GUI to allow full user interact with the InfiniiVision oscilloscope models.
- Upgraded chart views on Trace tab and Data Log tab to provide common chart controls – multiple axis, axis configuration, zoom controls, marker functionality, lock scaling, and auto scaling.
- Added support for additional oscilloscope measurements.
- Added support for additional triggering modes.
- Added the ability to import oscilloscope trace data into BenchVue in order to interact with the trace at a later date.
- Upgraded Screen Image tab to allow a single click capture and save operation.
- Added Test Flow support for basic scaling functions.
- Added Test Flow support for the optional WaveGen built-in function generator available on some Keysight models.
- Upgraded the Data Logger tab to include support for storing waveform segments.
- Added support for storing measurement statistics.
- Added support for Infiniium Z-Series models.

- Added support for Infiniium V-Series models.

## 2017 Version Information

Released Date:	March 29, 2017
<b>Requirements categories</b>	
PC operating system & hardware:	<p>Windows 10: 32-bit and 64-bit (Professional, Enterprise, Education, Home versions)</p> <p>Windows 8, 8.1: 32-bit and 64-bit (Professional, Enterprise, Core)</p> <p>Windows 7: SP1 and later 32-bit and 64-bit (Professional, Enterprise, Ultimate, Home Basic, Home Premium)</p> <p>Processor: 1 GHz or faster (2 GHz or greater recommended)</p> <p>RAM: 1 GB (32-bit) or 2 GB (64-bit) (3 GB or greater recommended)</p> <p>Interfaces: USB, GPIB, LAN, RS-232</p> <p>Display resolution: 1280x1024 minimum recommended for single instrument view (higher resolution recommended for multiple instrument view)</p>
<b>Mobile Devices:</b> (for companion BenchVue Mobile app)	<p>Apple iPhone, iPad, iPod Touch all models; iOS 7.0 and later.</p> <p>Android phone and tablets; Android 4.0.3 and later.</p>
Current List of BenchVue Enabled Keysight Instruments:	<a href="http://www.keysight.com/find/benchvueinstruments">www.keysight.com/find/benchvueinstruments</a>
File Name:	BenchVueSCOPEsetup.exe

## Notable changes

- BenchVue Oscilloscope app now requires a license
- App includes Test Flow automation and Command Expert blocks
- Support for new license terms

- Defects fixed for stability and usability
- Added: Support for 1000 X-Series
- Added: Export for DS file format of Keysight's Advanced Design System (ADS)
- Added: Edit and Export of channel labels for easier label changing
- Test Flow control for triggers
- Test Flow control for Run/Stop function

NOTE: Previous versions of this app are not compatible with the BenchVue 2017 Platform software. For compatibility, use the older versions of the BenchVue Platform software (3.7 and earlier). Download and install the older version of this app from the Apps tab within your version of BenchVue.