

Keysight 85070E

Dielectric Probe Kit 200 MHz to 50 GHz

Technical Overview



Swept High-Frequency Dielectric Measurements

The Keysight Technologies, Inc. 85070E Dielectric Probe Kit determines the dielectric properties, or complex permittivity, of many materials. Because a materials dielectric properties are determined by its molecular structure, if the molecular structure changes, so will the dielectric properties. Measuring them can indirectly measure other properties that are also correlated to the molecular structure, and can be a valuable alternative when the property of interest is difficult to measure directly.

Measurements are made by simply immersing the probe into liquids or semi-solids – no special fixtures or containers are required. Measurements are non-destructive and can be made in real time. These important features allow the Dielectric Probe Kit to be used in process analytic technologies.



The complete system is based on a network analyzer, which measures the material's response to RF or microwave energy. The probe transmits a signal into the material under test (MUT). Depending on the Keysight network analyzer and probe used, frequencies can extend from 200 MHz to 50 GHz.

The included software controls the network analyzer and guides the user through easy setup and measurement steps. In seconds, it calculates and displays complex permittivity in a variety of formats, including dielectric constant, dielectric loss factor, loss tangent or Cole-Cole.

Features

- Measures complex permittivity
- over a broad frequency range
- Results can be viewed in a variety of formats: ϵ' , ϵ'' , loss tangent, and Cole-Cole
- Data is easily shared with other Windows based programs or through the user programmable Component Object Model (COM) interface

New connection manager works with Keysight Connection Expert to bring ease and flexibility to interface between software and analyzer. GPIB and LAN are both supported with most PNA and ENA network analyzers.




Software displays dielectric constant and loss factor as a function of frequency.

Easy Data Analysis Display

The split screen window and marker aids in data analysis. Simply click on a point on the chart or table to activate and move the marker.

Connect to other programs

Data charts and tables can easily be copied and pasted into any Windows-based application for further analysis or report generation. The component object model (COM) interface allows the measurement to be setup, triggered, and read from a user written program. This is valuable for analyzing material changes over time. Example Visual Basic® and C++ projects are included to aid program development.



Display data in chart form, table form, or both.

Calibration Refresh Reduces Drift Errors¹


The new automated Electronic Calibration Refresh feature recalibrates the system automatically, in seconds, just before each measurement is made. This virtually eliminates cable instability and system drift errors. Processes can now be monitored over long time periods, including tests that vary MUT temperature and pressure over time.

How it works:

The Keysight Electronic Calibration module (ECal) microwave ports are connected in line between the probe and the network analyzer test port cable. The ECal module communication port is connected either to the PC or PNA Series network analyzer running the 85070E software. The software guides the user through a normal “three standard” calibration, (usually open, short, water), performed at the end of the probe. This calibration is then transferred to the ECal module. The ECal module remains in line and a complete ECal calibration is automatically performed before each measurement. Errors due to test port cable movement are removed by the new calibration.



ECal module connected in line



Water with and without Electronic Calibration Refresh

This measurement shows the effects of system drift and cable instability on a dielectric measurement of water and the improvement with Electronic calibration refresh. Both measurements were made 24 hours after the original calibration. The lighter colored, noisier, trace was made before the Electronic Calibration refresh was turned on. The darker, smoother, trace shows the improvement made after the Electronic Calibration refresh was turned on.

For systems without an ECal module, a simpler, “one standard” refresh calibration feature is also available, which can reduce the effects of system drift over time or temperature. After the initial “three standard” probe calibration is performed, the calibration can be refreshed at any time with the connection of a single standard. Any one of the three calibration standards can be defined as the refresh standard.

1. Not compatible with FieldFox RF analyzers

New Options Allow You to Configure Kit to Meet Your Needs

Now three probe designs to choose from

Performance Probe

Combines rugged, high temperature, and frequency performance in a slim design.

This probe features rugged, high temperature and frequency performance in a slim design, perfect for your most demanding applications. The probe is sealed on both the probe tip and the connector end, which make it our most rugged probe. The probe withstands a wide $-40\text{ }^{\circ}\text{C}$ to $+200\text{ }^{\circ}\text{C}$ temperature range, which allows measurements versus frequency and temperature.

The probe can be autoclaved, so it is perfect for applications in the food, medical, and chemical industries where sterilization is a must. The slim design allows it to fit easily in fermentation tanks, chemical reaction chambers, or other equipment with small apertures.


The small diameter also allows it to be used with smallest sample sizes of all Keysight's probes. It is useful for measuring liquid, semi-solid, as well as flat surfaced solid materials. The Performance Form Probe Kit comes complete with a calibration short.

Frequency range 500 MHz to 50 GHz.

2.4 mm male connector




Performance Probe Kit



High temperature probe

Survives corrosive chemicals and high temperatures
 Frequency range: 200 MHz to 20 GHz. 3.5 mm male connector.

Rugged in design, this probe features a hermetic glass-to-metal seal, which makes it resistant to corrosive or abrasive chemicals. The probe withstands a wide -40 °C to +200 °C temperature range, which allows measurements versus frequency and temperature. The large flange makes it easier to measure flat surfaced solid materials, in addition to liquids and semi-solids. The 3.5 mm aperture has a larger sensing volume than our other probes.




High Temperature Probe Kit

Slim Form Probe


Smaller diameter fits into tight spaces.
 Frequency range 500 MHz to 50 GHz. 2.4 mm male connector.

This probe features a slim design, which allows it to fit easily in fermentation tanks, chemical reaction chambers, or other equipment with small apertures. The slim design also allows it to be used with smaller sample sizes. Best used for liquids and soft semi-solids.

For castable solids, the probe is economical enough to be cast into the material and left in place. Because of the consumable nature of this design, these probes are offered in sets of three. The Slim Form probe kit comes with a sealed Slim Form holder that adapts 2.2 mm outer diameter to 10 mm inner diameter bracket included in the kit as well as commercially available "Midi" sized adapters and bushings.



Slim Form Probe measurement to 50 GHz



Three Cables to Choose From

20 GHz Flexible Cable

Cable to choose when temperature performance is not critical. SMA female connectors connect to High Temperature probe. When connecting to Slim Form probe, an additional adapter may be needed (see configuration guide).

50 GHz Flexible Cable

Cable to choose for high frequency applications. 2.4 mm female connectors connect directly to Slim Form Performance probes.

20 GHz High Temperature Cable

Use with High Temperature or Performance probes for high temperature applications from -40°C to $+200^{\circ}\text{C}$. SMA female connectors connect directly to High Temperature probe. Adapter included in kit connects High Temperature Cable to Performance probe.

Accessories

Probe Stand

The probe stand has a 13 x 7 inch porcelain base and 24 inch high by 0.5 inch diameter metal support. This stand works with mounting bracket and ECal holder included in the standard kit. It is highly recommended to stabilize measurement setup.

Software Menu Items

File

Save or recall measurement setups or previous measurement results. Print copies of the measurement results in a tabular or graphical format.

Edit

Copy the measurement results to the clipboard. Either graph or the tabular listing can be copied. This allows your measurement results to be pasted into other applications.

View

Select the section you want to view. Selections include the toolbar, status bar, table of the measurement data, and chart of the measurement data.

Calibration

Select the frequency range, number of points, linear or log sweep. Guided calibration sequence; choice of calibration materials or user-specified; refresh calibration for single standard or ECal; recalibration versus temperature; automatic refresh on or off.

Measure

Trigger a measurement.

Chart

Select the format to be displayed on the chart. Choices include ϵ' , ϵ'' , loss tangent, and Cole-Cole. Set Graticule scale factors or "autoscale". Select from linear, semi-log, or log-log representations.

Software Menu Items (continued)

Table

Choose between a tabular formatting of real and imaginary or real and loss tangent

Display

Display current measurement data; save/display up to 3 memory traces; compare data to reference trace with trace math. Turn the marker on or off.

Preferences

Select your preference of fonts, colors, and annotations used to plot and list the measurement data.

Help

On-line help including the product manual.

Toolbar

Provides single click access to the most important menu items.

Performance Characteristics

Specifications describe the warranted performance over the temperature range 0 to 55 °C. Supplemental characteristics are intended to provide information useful in applying the instrument, by giving typical but non-warranted performance parameters. These are denoted as “typical,” “nominal,” or “approximate.”

Probe Characteristics Table

	Performance Probe	Slim Form Probe	High Temperature Probe
Frequency Range (nominal)	500 MHz to 50 GHz Maximum limited by MUT properties $\frac{(285-j125)\text{GHz}}{\sqrt{ \epsilon_r^* }}$	500 MHz to 50 GHz Maximum limited by MUT properties $\frac{(285-j125)\text{GHz}}{\sqrt{ \epsilon_r^* }}$	200 MHz to 20 GHz with network analyzer 10 MHz to 3 GHz with E4991A Impedance analyzer with option 10. Maximum limited by MUT properties $\frac{100\text{ GHz}}{\sqrt{ \epsilon_r^* }}$
Temperature Range	-40 to +200 °C	0 to +125 °C	-40 to +200 °C
Temperature Slew Rate	< 10 degrees/minute	< 10 degrees/minute	< 10 degrees/minute
Immersable Length (approximate)	140 mm	200 mm	35 mm
Connector	2.4 mm male	2.4 mm male	3.5 mm male
Repeatability and Resolution	Two to four times better than accuracy	Two to four times better than accuracy	Two to four times better than accuracy
Material Under Test (assumptions)	Material is “infinite” in size, non-magnetic ($\mu_r^* = 1$), isotropic (uniform orientation), and homogeneous (uniform composition) ² . Solids have a single, smooth, flat ³ surface with gap-free contact at the probe face.	Liquid or soft semi-solid. Material is “infinite” in size, non-magnetic ($\mu_r^* = 1$), isotropic (uniform orientation), and homogeneous (uniform composition) ² .	Material is “infinite” in size, non-magnetic ($\mu_r^* = 1$), isotropic (uniform orientation), and homogeneous (uniform composition) ² . Solids have a single, smooth, flat ³ surface with gap-free contact at the probe face.
Sample size (requirements)	Minimum 5 mm insertion and 1 mm around tip of probe	Minimum 5 mm insertion and 5 mm around tip of probe	Diameter: > 20 mm 20 Thickness: > $\frac{20}{\sqrt{ \epsilon_r^* }}$ mm Granule size ⁴ : < 0.3 mm
Expected Value (requirements)	Maximum recommended ϵ_r' : < 100 Minimum recommended loss tangent > 0.05 Not recommended for low loss (loss tangent < 0.5) materials with $\epsilon_r' > 5$	Maximum recommended ϵ_r' : < 100 Minimum recommended loss tangent > 0.05 Not recommended for low loss (loss tangent < 0.5) materials with $\epsilon_r' > 5$	Maximum recommended ϵ_r' : < 100 Minimum recommended loss tangent > 0.05 Not recommended for low loss (loss tangent < 0.5) materials with $\epsilon_r' > 5$
Accuracy (typical) ¹	Dielectric constant, $\epsilon_r' = \epsilon_r' \pm 0.05 \epsilon_r^* $. $\epsilon_r'' = \epsilon_r'' \pm 0.05 \epsilon_r^* $	Dielectric constant, $\epsilon_r' = \epsilon_r' \pm 0.05 \epsilon_r^* $. $\epsilon_r'' = \epsilon_r'' \pm 0.05 \epsilon_r^* $	Dielectric constant, $\epsilon_r' = \epsilon_r' \pm 0.05 \epsilon_r^* $. $\epsilon_r'' = \epsilon_r'' \pm 0.05 \epsilon_r^* $

1. Practical frequency range, accuracy and resolution depend on properties of the MUT. Value indicates typical accuracy at 23 ± 3 °C, not including effects of probe contact and cable flexure.
2. If the material is not homogeneous, the result is an average value weighted by the intensity of the E-field, which is highest at the center conductor of the probe tip.
3. Sample must be as flat as the probe face, which is lapped to ±100 μ inches.
4. Measurement repeatability for granular materials is dependent on density variation.

Configuration Guide

Choose one of our suggested configurations

High Temperature Configuration

85070E

- Performance Probe Kit, Option 050, or High-Temperature Probe Kit, Option 020
- High Temperature Cable, Option 002
- Probe Stand, Option 001
- USB Security Key, Option UL8



High Temperature Probe Kit (Option 020)

Rugged High Frequency Configuration

85070E

- Performance Probe, Option 050
- Probe Stand, Option 001
- USB Security Key, Option UL8

Economy Configuration

85070E

- Slim Form Probe Kit, Option 030
- 20 GHz Flexible Cable, Option 022
- USB Security Key, Option UL8



Performance Probe Kit (Option 050)



Slim Form Probe Kit (Option 030)

Configuration Guide (continued)

Or, customize your own

Dielectric Probe Kit, 85070E

Includes:

- Dielectric Probe Software application on CD-Rom
- 1 mounting bracket to connect probes to Option 001 Probe Stand or similar stand
- 1 10 mm holder to connect performance probe or slim form holder to mounting bracket
- 1 3 mm hex key for 10 mm holder and Ecal holder screws
- 1 ECal holder to connect ECal module to mounting bracket
- 1 Type-N male to 3.5 mm male adapter, 1250-1743
- 1 3.5 mm male to 2.4 mm female adapter 11901D
- 1 foam lined walnut box.

Probes – Choose one or all

Performance Dielectric Probe Kit, Option 050

Includes:

- 1 Performance Dielectric Probe
- 1 Calibration Short
- 1 Conductive Elastomer Disk

High-Temperature Dielectric Probe Kit, Option 020

Includes:

- 1 High Temperature Probe
- 1 Calibration Short

Slim Form Probe Kit, Option 030

Includes:

- 3 Slim Form probes
- 1 connector saver
- 1 Calibration short
- 1 10 mm dia sealed probe holder.
- 6 O-rings

Slim Form probe replenishment Kit, Option 033

Contains 3 extra Slim Form Probes

Cables – (Optional, choose any or all)

- High Temperature Cable, Option 002
- 20 GHz Flexible Cable, Option 022
- 50 GHz Flexible Cable, Option 032

Accessory – (Optional, highly recommended)

- Probe Stand, Option 001

Security Key –

- USB Hardware Key, Option UL8

Additional available parts

- 8710-2036 High-Temperature Dielectric Probe
- 85070-60003 Shorting block and clamp for high temperature probe
- 85070-60004 Short for Slim Form Probes
- 85070-60007 Slim Form Probe holder
- 85070-60008 ECal Holder
- 85070-60009 Set of three Slim Form Probes
- 85070-60010 Performance Probe
- 85070-60012 Short for Performance Probe
- 85070-60011 10mm Holder for Performance Probe and Slim Form Probe
- 8120-6286 High Temperature Cable
- 8120-6192 20GHz Flexible Cable
- 8121-1290 50GHz Flexible Cable
- 9301-1298 Probe Stand
- 1250-3449 Connector Saver for Slim Form Probe
- 85070-20036 Conductive Elastomer Disk

85070E Dielectric Probe Kit Upgrades

Software only upgrade to the E version for customers who own the 85070D or earlier version.

- 85070EU Software Upgrade Kit

Probe hardware only upgrade kits are now available to customers who own the 85070E or 85070EU. These kits contain the probe, short and any other small accessories included in the standard probe option.

- 85070E-021 High Temperature Probe Upgrade Kit
- 85070E-031 Slim Form Probe Upgrade Kit
- 85070E-051 Performance Probe Upgrade Kit

Adapter Selection Guide

Some configurations may need extra adapters. The Keysight adapter part numbers are charted below.

Network analyzer port to cable			
Network analyzer port connector	High Temperature 20 GHz Cable	Flexible 20 GHz Cable	Flexible 50 GHz Cable
Type-N female	1250-1743 (included in kit)	1250-1743 (included in kit)	11903A
3.5 mm male	None needed	None needed	11901C
2.4 mm male	11901D (included in kit)	11901D (included in kit)	None needed
Probe to cable			
Probe	High Temperature 20 GHz Cable	Flexible 20 GHz Cable	Flexible 50 GHz Cable
High Temperature Probe	None needed	None needed	11901C
Slim Form Probe	11901D (included in kit)	11901D (included in kit)	None needed
Performance Probe	11901D (included in kit)	11901D (included in kit)	None needed

Adapters needed when using automated Electronic Calibration Refresh

Ecal module to cable			
ECal Module Connector	High Temperature 20 GHz Cable (3.5 mm female)	Flexible 20 GHz Cable (3.5 mm female)	Flexible 50 GHz Cable (2.4 mm female)
Type-N male	1250-1750	1250-1750	11903C
Type-N female	1250-1743 (included in kit)	1250-1743 (included in kit)	11903A
3.5 mm male	None needed	None needed	11901C
3.5 mm female	1250-1748	1250-1748	11901A
2.4 mm male	11901D (included in kit)	11901D (included in kit)	None needed
2.4 mm female	11901C	11901C	11900A
Ecal module to probe			
ECal Module Connector	High Temperature Probe	Performance and Slim Form Probe	
Type-N male	1250-1745	11903B	
Type-N female	1259-1744	11903D	
3.5 mm male	83059B	11901B	
3.5 mm female	None needed	11901D (included in kit)	
2.4 mm male	11901B	11900B	
2.4 mm female	11901C	None needed	

Compatible ECal modules¹

ECal module requires USB connection to PC or PNA Series network analyzer
N469xA series
8509xC series

Compatible network analyzers

A list of compatible network analyzers can be found on the 8507xE Series Support site at: <http://na.support.keysight.com/materials/>

PC requirements

- Windows XP, Windows 7
- Keysight IO Libraries
- CD drive or internet connection to load software.

Free Trial Demo

Evaluate a demo version of 85070E software for up to two weeks. Visit the Keysight web site at www.keysight.com/find/materials to download this demo program.

PC is optional for PNA and newer ENA series network analyzers where software can be installed directly on the analyzer. All other analyzers require a PC with a GPIB or LAN interface card. LAN is supported with PNA, newer ENA, and FieldFox models. GPIB is supported with newer PNA, ENA and E4991A models. Please see: <http://na.support.keysight.com/materials/> for model number and firmware requirements.

1. Optional, needed for Automated Electronic Calibration Refresh

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/materials

www.keysight.com/find/pna

www.keysight.com/find/ecal

www.keysight.com/find/accessories

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at:

www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:

www.keysight.com/find/contactus
(BP-9-7-17)

DEKRA Certified
ISO 9001 Quality Management System

www.keysight.com/go/quality

Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System

